TMS320C674x DSP CPU and Instruction Set

Reference Guide



Literature Number: SPRUFE8B July 2010



Contents

Prefa	ace		17
1	Intro	duction	19
	1.1	Overview	20
	1.2	DSP Features and Options	20
	1.3	DSP Architecture	22
		1.3.1 Central Processing Unit (CPU)	23
		1.3.2 Internal Memory	23
		1.3.3 Memory and Peripheral Options	23
2	CPU	Data Paths and Control	25
	2.1	Introduction	26
	2.2	General-Purpose Register Files	26
	2.3	Functional Units	29
	2.4	Register File Cross Paths	30
	2.5	Memory, Load, and Store Paths	31
	2.6	Data Address Paths	31
	2.7	Galois Field	31
		2.7.1 Special Timing Considerations	33
	2.8	Control Register File	34
		2.8.1 Register Addresses for Accessing the Control Registers	35
		2.8.2 Pipeline/Timing of Control Register Accesses	35
		2.8.3 Addressing Mode Register (AMR)	36
		2.8.4 Control Status Register (CSR)	
		2.8.5 Galois Field Polynomial Generator Function Register (GFPGFR)	
		2.8.6 Interrupt Clear Register (ICR)	
		2.8.7 Interrupt Enable Register (IER)	
		2.8.8 Interrupt Flag Register (IFR)	
		2.8.9 Interrupt Return Pointer Register (IRP)	
		2.8.10 Interrupt Set Register (ISR)	
		2.8.11 Interrupt Service Table Pointer Register (ISTP)	
		2.8.12 Nonmaskable Interrupt (NMI) Return Pointer Register (NRP)	
		2.8.13 E1 Phase Program Counter (PCE1)	
	2.9	Control Register File Extensions	
		2.9.1 Debug Interrupt Enable Register (DIER)	
		2.9.2 DSP Core Number Register (DNUM)	
		2.9.3 Exception Clear Register (ECR)	
		2.9.4 Exception Flag Register (EFR)	
		2.9.5 GMPY Polynomial—A Side Register (GPLYA)	
		2.9.6 GMPY Polynomial—B Side Register (GPLYB)	
		2.9.7 Internal Exception Report Register (IERR)	
		2.9.8 SPLOOP Inner Loop Count Register (ILC)	
		2.9.9 Interrupt Task State Register (ITSR)	
		2.9.10 NMI/Exception Task State Register (NTSR)	
		2.9.11 Restricted Entry Point Register (REP)	
		2.9.12 SPLOOP Reload Inner Loop Count Register (RILC)	
		2.9.13 Saturation Status Register (SSR)	54



			Time Stamp Counter Registers (TSCL and TSCH)	
	2.10		Register File Extensions for Floating-Point Operations	
		2.10.1	Floating-Point Adder Configuration Register (FADCR)	
		2.10.2	Floating-Point Auxiliary Configuration Register (FAUCR)	
		2.10.3	Floating-Point Multiplier Configuration Register (FMCR)	
_	l 4			
3			Set	
	3.1		tion Operation and Execution Notations	
	3.2		tion Syntax and Opcode Notations	
			32-Bit Opcode Maps	
			16-Bit Opcode Maps	
	3.3		ew of IEEE Standard Single- and Double-Precision Formats	
			Single-Precision Formats	
			Double-Precision Formats	
	3.4	Delay S	Slots	. 73
	3.5		l Operations	
		3.5.1	Example Parallel Code	. 76
		3.5.2	Branching Into the Middle of an Execute Packet	. 76
	3.6	Condition	onal Operations	. 77
	3.7	SPMAS	SKed Operations	. 77
	3.8	Resour	ce Constraints	. 78
		3.8.1	Constraints on Instructions Using the Same Functional Unit	. 78
			Constraints on the Same Functional Unit Writing in the Same Instruction Cycle	
			Constraints on Cross Paths (1X and 2X)	
			Cross Path Stalls	
			Constraints on Loads and Stores	
			Constraints on Long (40-Bit) Data	
			Constraints on Register Reads	
			Constraints on Register Writes	
			Constraints on AMR Writes	
		3.8.10	Constraints on Multicycle NOPs	
		3.8.11	Constraints on Unitless Instructions	
			Constraints on Floating-Point Instructions	
	2.0		<u>.</u>	
	3.9		sing ModesLinear Addressing Mode	
			· · · · · · · · · · · · · · · · · · ·	
			Circular Addressing Mode	
	0.40		Syntax for Load/Store Address Generation	
	3.10	•	ct Instructions on the CPU	
		3.10.1	Compact Instruction Overview	
		3.10.2	Header Word Format	
		3.10.3	Processing of Fetch Packets	
		3.10.4	Execute Packet Restrictions	
			Available Compact Instructions	
	3.11	Instruct	tion Compatibility	. 97
	3.12	Instruct	tion Descriptions	. 98
4	Pipeli	ine		575
	4.1		e Operation Overview	576
		•	Fetch	577
			Decode	578
			Execute	579
			Pipeline Operation Summary	580
	4.2		e Execution of Instruction Types	
	7.4	-	• •	
		7.4.1	ongle cycle metrotione minimum	550

www.ti.com

		4.2.2	Two-Cycle Instructions and .M Unit Nonmultiply Operations	
		4.2.3	Store Instructions	
		4.2.4	Extended Multiply Instructions	592
		4.2.5	Load Instructions	593
		4.2.6	Branch Instructions	594
		4.2.7	Two-Cycle DP Instructions	596
		4.2.8	Four-Cycle Instructions	597
		4.2.9	INTDP Instruction	598
		4.2.10	Double-Precision (DP) Compare Instructions	598
		4.2.11	ADDDP/SUBDP Instructions	599
		4.2.12	MPYI Instruction	599
		4.2.13	MPYID Instruction	600
		4.2.14	MPYDP Instruction	600
		4.2.15	MPYSPDP Instruction	601
		4.2.16	MPYSP2DP Instruction	601
	4.3	Function	onal Unit Constraints	602
		4.3.1	.S-Unit Constraints	602
		4.3.2	.M-Unit Constraints	606
		4.3.3	L-Unit Constraints	
		4.3.4	D-Unit Instruction Constraints	
	4.4	Perfor	mance Considerations	
		4.4.1	Pipeline Operation With Multiple Execute Packets in a Fetch Packet	
		4.4.2	Multicycle NOPs	
		4.4.3	Memory Considerations	
_	lmtan		·	
5		•		
	5.1		iew	
		5.1.1	••	
		5.1.2		
	<i>-</i> 0	5.1.3	Summary of Interrupt Control Registers	
	5.2		Ily Enabling and Disabling Interrupts	
	5.3		lual Interrupt Control	
		5.3.1	Enabling and Disabling Interrupts	
		5.3.2	Status of Interrupts	
		5.3.3	Setting and Clearing Interrupts	
	5 4	5.3.4	Returning From Interrupt Servicing	
	5.4		pt Detection and Processing	
		5.4.1	Setting the Nonreset Interrupt Flag	
		5.4.2	Conditions for Processing a Nonreset Interrupt	
		5.4.3	Saving TSR Context in Nonreset Interrupt Processing	
		5.4.4	Actions Taken During Nonreset Interrupt Processing	
		5.4.5	Conditions for Processing a Nonmaskable Interrupt	
		5.4.6	Saving of Context in Nonmaskable Interrupt Processing	
		5.4.7	Actions Taken During Nonmaskable Interrupt Processing	
		5.4.8	Setting the RESET Interrupt Flag	
		5.4.9	Actions Taken During RESET Interrupt Processing	
	5.5		mance Considerations	
		5.5.1	General Performance	
		5.5.2	Pipeline Interaction	
	5.6	•	amming Considerations	
		5.6.1	Single Assignment Programming	
		5.6.2	Nested Interrupts	
		5.6.3	Manual Interrupt Processing (polling)	
		5.6.4	Traps	651



6	CPU	Except	tions	653
	6.1	Overvi	ew	654
		6.1.1	Types of Exceptions and Signals Used	654
		6.1.2	Exception Service Vector	655
		6.1.3	Summary of Exception Control Registers	655
	6.2	Excep	tion Control	657
		6.2.1	Enabling and Disabling External Exceptions	657
		6.2.2	Pending Exceptions	657
		6.2.3	Exception Event Context Saving	
		6.2.4	Returning From Exception Servicing	
	6.3	Excep	tion Detection and Processing	659
		6.3.1	Setting the Exception Pending Flag	659
		6.3.2	Conditions for Processing an External Exception	659
		6.3.3	Actions Taken During External Exception (EXCEP) Processing	
		6.3.4	Nested Exceptions	
	6.4	Perfor	mance Considerations	
		6.4.1	General Performance	662
		6.4.2	Pipeline Interaction	662
	6.5	Progra	mming Considerations	665
		6.5.1	Internal Exceptions	665
		6.5.2	Internal Exception Report Register (IERR)	
		6.5.3	Software Exception	
7	Softv	vare Pi	pelined Loop (SPLOOP) Buffer	
-	7.1		are Pipelining	
	7.2		are Pipelining	
	7.3		nology	
	7.4		OP Hardware Support	
		7.4.1	Loop Buffer	
		7.4.2	Loop Buffer Count Register (LBC)	
		7.4.3	Inner Loop Count Register (ILC)	
		7.4.4	Reload Inner Loop Count Register (RILC)	
		7.4.5	Task State Register (TSR), Interrupt Task State Register (ITSR), and	0.0
		7.1.0	NMI/Exception Task State Register (NTSR)	670
	7.5	SPLO	OP-Related Instructions	670
		7.5.1	SPLOOP, SPLOOPD, and SPLOOPW Instructions	670
		7.5.2	SPKERNEL and SPKERNELR Instructions	671
		7.5.3	SPMASK and SPMASKR Instructions	672
	7.6	Basic	SPLOOP Example	673
		7.6.1	Some Points About the Basic SPLOOP Example	674
		7.6.2	Same Example Using the SPLOOPW Instruction	675
		7.6.3	Some Points About the SPLOOPW Example	676
	7.7	Loop E	Buffer	676
		7.7.1	Software Pipeline Execution From the Loop Buffer	677
		7.7.2	Stage Boundary Terminology	677
		7.7.3	Loop Buffer Operation	678
	7.8	Execu	tion Patterns	
		7.8.1	Prolog, Kernel, and Epilog Execution Patterns	680
		7.8.2	Early-Exit Execution Pattern	
		7.8.3	Reload Execution Pattern	
	7.9	Loop E	Buffer Control Using the Unconditional SPLOOP(D) Instruction	
		7.9.1	Initial Termination Condition Test and ILC Decrement	
		7.9.2	Stage Boundary Termination Condition Test and ILC Decrement	
		7.9.3	Using SPLOOPD for Loops with Known Minimum Iteration Counts	

www.ti.com

		7.9.4 Program Memory Fetch Enable Delay During Epilog	
		7.9.5 Stage Boundary and SPKERNEL(R) Position	
		7.9.6 Loop Buffer Reload	
		7.9.7 Restrictions on Accessing ILC and RILC	
	7.10	Loop Buffer Control Using the SPLOOPW Instruction	
		7.10.1 Initial Termination Condition Using the SPLOOPW Condition	
		7.10.2 Stage Boundary Termination Condition Using the SPLOOPW Condition	
		7.10.3 Interrupting the Loop Buffer When Using SPLOOPW	91
		7.10.4 Under-Execution of Early Stages of SPLOOPW When Termination Condition Becomes True While Interrupt Draining 69	
	7.11	Using the SPMASK Instruction	
		7.11.1 Using SPMASK to Merge Setup Code Example	
		7.11.2 Some Points About the SPMASK to Merge Setup Code Example	
		7.11.3 Using SPMASK to Merge Reset Code Example	
		7.11.4 Some Points About the SPMASK to Merge Reset Code Example	
		7.11.5 Returning from an Interrupt	
	7.12	Program Memory Fetch Control	
		7.12.1 Program Memory Fetch Disable	
		7.12.2 Program Memory Fetch Enable	
	7.13	Interrupts	
		7.13.1 Interrupting the Loop Buffer	
		7.13.2 Returning to an SPLOOP(D/W) After an Interrupt	
		7.13.3 Exceptions	
		7.13.4 Branch to Interrupt, Pipe-Down Sequence	
		7.13.5 Return from Interrupt, Pipe-Up Sequence	
		7.13.6 Disabling Interrupts During Loop Buffer Operation	
	7.14	Branch Instructions	
	7.15	Instruction Resource Conflicts and SPMASK Operation	
		7.15.1 Program Memory and Loop Buffer Resource Conflicts	
		7.15.2 Restrictions on Stall Detection Within SPLOOP Operation	
	7.16	Restrictions on Cross Path Stalls	
	7.17	Restrictions on AMR-Related Stalls	
	7.18	Restrictions on Instructions Placed in the Loop Buffer	
8	CPU	Privilege)3
	8.1	Overview)4
	8.2	Execution Modes	
		8.2.1 Privilege Mode After Reset)4
		8.2.2 Execution Mode Transitions)4
		8.2.3 Supervisor Mode)4
		8.2.4 User Mode)5
	8.3	Interrupts and Exception Handling 70)6
		8.3.1 Inhibiting Interrupts in User Mode) 6
		8.3.2 Privilege and Interrupts) 6
		8.3.3 Privilege and Exceptions) 6
		8.3.4 Privilege and Memory Protection) 6
	8.4	Operating System Entry)6
		8.4.1 Entering User Mode from Supervisor Mode)7
		8.4.2 Entering Supervisor Mode from User Mode)7
Α	Instru	ction Compatibility70)9
В		ng Between Instruction and Functional Unit71	
С		it Instructions and Opcode Maps	
	C.1	Instructions Executing in the .D Functional Unit	
	C.2	Opcode Map Symbols and Meanings	22





	C.3	32-Bit Opcode Maps	724
	C.4	16-Bit Opcode Maps	725
D	.L Unit Instructions and Opcode Maps		
	D.1	Instructions Executing in the .L Functional Unit	
	D.2	Opcode Map Symbols and Meanings	735
	D.3	32-Bit Opcode Maps	735
	D.4	16-Bit Opcode Maps	736
Ε	.M Un	it Instructions and Opcode Maps	741
	E.1	Instructions Executing in the .M Functional Unit	742
	E.2	Opcode Map Symbols and Meanings	743
	E.3	32-Bit Opcode Maps	743
	E.4	16-Bit Opcode Maps	744
F	.S Un	it Instructions and Opcode Maps	745
	F.1	Instructions Executing in the .S Functional Unit	
	F.2	Opcode Map Symbols and Meanings	747
	F.3	32-Bit Opcode Maps	747
	F.4	16-Bit Opcode Maps	75 0
G	.D, .L	or .S Unit Opcode Maps	757
	G.1	Opcode Map Symbols and Meanings	
	G.2	32-Bit Opcode Maps	758
	G.3	16-Bit Opcode Maps	759
Н	No Ur	nit Specified Instructions and Opcode Maps	763
	H.1	Instructions Executing With No Unit Specified	
	H.2	Opcode Map Symbols and Meanings	
	H.3	32-Bit Opcode Maps	765
	H.4	16-Bit Opcode Maps	765
I	Revis	ion History	769

Copyright © 2010, Texas Instruments Incorporated



List of Figures

1-1.	TMS320C674x DSP Block Diagram	22
2-1.	CPU Data Paths	27
2-2.	Storage Scheme for 40-Bit Data in a Register Pair	28
2-3.	Addressing Mode Register (AMR)	36
2-4.	Control Status Register (CSR)	38
2-5.	PWRD Field of Control Status Register (CSR)	38
2-6.	Galois Field Polynomial Generator Function Register (GFPGFR)	40
2-7.	Interrupt Clear Register (ICR)	41
2-8.	Interrupt Enable Register (IER)	
2-9.	Interrupt Flag Register (IFR)	
2-10.	Interrupt Return Pointer Register (IRP)	
2-11.	Interrupt Set Register (ISR)	
2-12.	Interrupt Service Table Pointer Register (ISTP)	
2-13.	NMI Return Pointer Register (NRP)	
2-14.	E1 Phase Program Counter (PCE1)	
2-15.	Debug Interrupt Enable Register (DIER)	
2-16.	DSP Core Number Register (DNUM)	
2-17.	Exception Flag Register (EFR)	
2-18.	GMPY Polynomial A-Side Register (GPLYA)	
2-19.	GMPY Polynomial B-Side (GPLYB)	
2-20.	Internal Exception Report Register (IERR)	
2-21.	Inner Loop Count Register (ILC)	
2-22.	Interrupt Task State Register (ITSR)	
2-23.	NMI/Exception Task State Register (NTSR)	
2-24.	Reload Inner Loop Count Register (RILC)	
2-25.	Saturation Status Register (SSR)	
2-26.	Time Stamp Counter Register - Low Half (TSCL)	
2-27.	Time Stamp Counter Register - High Half (TSCH)	
2-28.	Task State Register (TSR)	
2-29.	Floating-Point Adder Configuration Register (FADCR)	
2-30.	Floating-Point Auxiliary Configuration Register (FAUCR)	
2-31.	Floating-Point Multiplier Configuration Register (FMCR)	
3-1.	Single-Precision Floating-Point Fields	
3-2.	Double-Precision Floating-Point Fields	
3-3.	Basic Format of a Fetch Packet	
3-4.	Examples of the Detectability of Write Conflicts by the Assembler	
3-5.	Compact Instruction Header Format	
3-6.	Layout Field in Compact Header Word	
3-7.	Expansion Field in Compact Header Word	
3-8.	P-bits Field in Compact Header Word	
4-1.	Pipeline Stages	576
4-2.	Fetch Phases of the Pipeline	577
4-3.	Decode Phases of the Pipeline	578
4-4.	Execute Phases of the Pipeline	579
4-5.	Pipeline Phases	580
4-6.	Pipeline Operation: One Execute Packet per Fetch Packet	580
4-7.	Pipeline Phases Block Diagram	583
	1	





4-8.	Single-Cycle Instruction Phases	588
4-9.	Single-Cycle Instruction Execution Block Diagram	588
4-10.	Two-Cycle Instruction Phases	589
4-11.	Single 16 x 16 Multiply Instruction Execution Block Diagram	589
4-12.	Store Instruction Phases	590
4-13.	Store Instruction Execution Block Diagram	590
4-14.	Extended Multiply Instruction Phases	592
4-15.	Extended Multiply Instruction Execution Block Diagram	592
4-16.	Load Instruction Phases	593
4-17.	Load Instruction Execution Block Diagram	593
4-18.	Branch Instruction Phases	594
4-19.	Branch Instruction Execution Block Diagram	
4-20.	Two-Cycle DP Instruction Phases	
4-21.	Four-Cycle Instruction Phases	597
4-22.	INTDP Instruction Phases	598
4-23.	DP Compare Instruction Phases	598
4-24.	ADDDP/SUBDP Instruction Phases	599
4-25.	MPYI Instruction Phases	599
4-26.	MPYID Instruction Phases	
4-27.	MPYDP Instruction Phases	
4-28.	MPYSPDP Instruction Phases	
4-29.	MPYSP2DP Instruction Phases	
4-30.	Pipeline Operation: Fetch Packets With Different Numbers of Execute Packets	
4-31.	Multicycle NOP in an Execute Packet.	
4-32.	Branching and Multicycle NOPs	
4-33.	Pipeline Phases Used During Memory Accesses	
4-34.	Program and Data Memory Stalls	
5-1.	Interrupt Service Table	
5-2.	Interrupt Service Fetch Packet	631
5-3.	Interrupt Service Table With Branch to Additional Interrupt Service Code Located Outside the IST	632
5-4.	Nonreset Interrupt Detection and Processing: Pipeline Operation	
5-5.	Return from Interrupt Execution and Processing: Pipeline Operation	
5-6.	CPU Nonmaskable Interrupt Detection and Processing: Pipeline Operation	
5-7.	CPU Return from Nonmaskable Interrupt Execution and Processing: Pipeline Operation	645
5-8.	RESET Interrupt Detection and Processing: Pipeline Operation	647
6-1.	Interrupt Service Table With Branch to Additional Exception Service Code Located Outside the IST	656
6-2.	External Exception (EXCEP) Detection and Processing: Pipeline Operation	660
6-3.	Return from Exception Processing: Pipeline Operation	661
6-4.	NMI Exception Detection and Processing: Pipeline Operation	663
6-5.	Double Exception Detection and Processing: Pipeline Operation	664
7-1.	Software Pipelined Execution Flow	668
7-2.	General Prolog, Kernel, and Epilog Execution Pattern	681
7-3.	Single Kernel Stage Execution Pattern	681
7-4.	Early-Exit Execution Pattern	682
7-5.	Single Loop Iteration Execution Pattern	682
7-6.	Reload Execution Pattern	683
7-7.	Reload Early-Exit Execution Pattern	683
7-8.	Instruction Flow Using Reload	689
7-9.	Instruction Flow for strcpy() of Null String	692

www.ti.com

C-1.	1 or 2 Sources Instruction Format	724
C-2.	Extended .D Unit 1 or 2 Sources Instruction Format	724
C-3.	ADDAB/ADDAH/ADDAW Long-Immediate Operations	724
C-4.	Load/Store Basic Operations	724
C-5.	Load/Store Long-Immediate Operations	724
C-6.	Load/Store Doubleword Instruction Format	724
C-7.	Load/Store Nonaligned Doubleword Instruction Format	724
C-8.	Doff4 Instruction Format	725
C-9.	Doff4DW Instruction Format	725
C-10.	Dind Instruction Format	726
C-11.	DindDW Instruction Format	727
C-12.	Dinc Instruction Format	727
C-13.	DincDW Instruction Format	728
C-14.	Ddec Instruction Format	728
C-15.	DdecDW Instruction Format	729
C-16.	Dstk Instruction Format	729
C-17.	Dx2op Instruction Format	729
C-18.	Dx5 Instruction Format	730
C-19.	Dx5p Instruction Format	730
C-20.	Dx1 Instruction Format	730
C-21.	Dpp Instruction Format	731
D-1.	1 or 2 Sources Instruction Format	735
D-2.	Unary Instruction Format	735
D-3.	1 or 2 Sources, Nonconditional Instruction Format	735
D-4.	L3 Instruction Format	736
D-5.	L3i Instruction Format	736
D-6.	Ltbd Instruction Format	737
D-7.	L2c Instruction Format	737
D-8.	Lx5 Instruction Format	738
D-9.	Lx3c Instruction Format	738
D-10.	Lx1c Instruction Format	739
D-11.	Lx1 Instruction Format	739
E-1.	Extended M-Unit with Compound Operations	743
E-2.	Extended .M-Unit Unary Instruction Format	743
E-3.	Extended .M Unit 1 or 2 Sources, Nonconditional Instruction Format	743
E-4.	MPY Instruction Format	743
E-5.	M3 Instruction Format	744
F-1.	1 or 2 Sources Instruction Format	747
F-2.	ADDDP/ADDSP and SUBDP/SUBSP Instruction Format	747
F-3.	ADDK Instruction Format	747
F-4.	ADDKPC Instruction Format	748
F-5.	Extended .S Unit 1 or 2 Sources Instruction Format	748
F-6.	Branch Using a Displacement Instruction Format	748
F-7.	Branch Using a Register Instruction Format	748
F-8.	Branch Using a Pointer Instruction Format	748
F-9.	BDEC/BPOS Instruction Format	748
F-10.	Branch Using a Displacement with NOP Instruction Format	748
F-11.	Branch Using a Register with NOP Instruction Format	748
F-12.	Call Nonconditional, Immediate with Implied NOP 5 Instruction Format	749





F-13.	Move Constant Instruction Format	749
F-14.	Extended .S Unit 1 or 2 Sources, Nonconditional Instruction Format	749
F-15.	Unary Instruction Format	749
F-16.	Field Operations	749
F-17.	Sbs7 Instruction Format	75 0
F-18.	Sbu8 Instruction Format	750
F-19.	Scs10 Instruction Format	750
F-20.	Sbs7c Instruction Format	751
F-21.	Sbu8c Instruction Format	751
F-22.	S3 Instruction Format	751
F-23.	S3i Instruction Format	752
F-24.	Smvk8 Instruction Format	752
F-25.	Ssh5 Instruction Format	753
F-26.	S2sh Instruction Format	753
F-27.	Sc5 Instruction Format	754
F-28.	S2ext Instruction Format	754
F-29.	Sx2op Instruction Format	755
F-30.	Sx5 Instruction Format	755
F-31.	Sx1 Instruction Format	756
F-32.	Sx1b Instruction Format	756
G-1.	LSDmvto Instruction Format	759
G-2.	LSDmvfr Instruction Format	759
G-3.	LSDx1c Instruction Format	760
G-4.	LSDx1 Instruction Format	761
H-1.	DINT and RINT, SWE and SWENR Instruction Format	765
H-2.	IDLE and NOP Instruction Format	765
H-3.	Loop Buffer, Nonconditional Instruction Format	765
H-4.	Loop Buffer Instruction Format	765
H-5.	Uspl Instruction Format	765
H-6.	Uspldr Instruction Format	766
H-7.	Uspk Instruction Format	766
H-8.	Uspm Instruction Format	766
H-9.	Unop Instruction Format	767



List of Tables

2-1.	40-Bit/64-Bit Register Pairs	28
2-2.	Functional Units and Operations Performed	29
2-3.	Modulo 2 Arithmetic	31
2-4.	Modulo 5 Arithmetic	32
2-5.	Modulo Arithmetic for Field GF(2³)	33
2-6.	Control Registers	34
2-7.	Addressing Mode Register (AMR) Field Descriptions	36
2-8.	Block Size Calculations	37
2-9.	Control Status Register (CSR) Field Descriptions	38
2-10.	Galois Field Polynomial Generator Function Register (GFPGFR) Field Descriptions	40
2-11.	Interrupt Clear Register (ICR) Field Descriptions	41
2-12.	Interrupt Enable Register (IER) Field Descriptions	42
2-13.	Interrupt Flag Register (IFR) Field Descriptions	43
2-14.	Interrupt Set Register (ISR) Field Descriptions	44
2-15.	Interrupt Service Table Pointer Register (ISTP) Field Descriptions	45
2-16.	Control Register File Extensions	46
2-17.	Debug Interrupt Enable Register (DIER) Field Descriptions	47
2-18.	Exception Flag Register (EFR) Field Descriptions	49
2-19.	Internal Exception Report Register (IERR) Field Descriptions	51
2-20.	Interrupt Task State Register (ITSR) Field Descriptions	52
2-21.	NMI/Exception Task State Register (NTSR) Field Descriptions	53
2-22.	Saturation Status Register Field Descriptions	54
2-23.	Task State Register (TSR) Field Descriptions	57
2-24.	Control Register File Extensions for Floating-Point Operations	58
2-25.	Floating-Point Adder Configuration Register (FADCR) Field Descriptions	59
2-26.	Floating-Point Auxiliary Configuration Register (FAUCR) Field Descriptions	61
2-27.	Floating-Point Multiplier Configuration Register (FMCR) Field Descriptions	63
3-1.	Instruction Operation and Execution Notations	66
3-2.	Instruction Syntax and Opcode Notations	68
3-3.	IEEE Floating-Point Notations	70
3-4.	Special Single-Precision Values	71
3-5.	Hexadecimal and Decimal Representation for Selected Single-Precision Values	71
3-6.	Special Double-Precision Values	
3-7.	Hexadecimal and Decimal Representation for Selected Double-Precision Values	
3-8.	Delay Slot and Functional Unit Latency	
3-9.	Registers That Can Be Tested by Conditional Operations	
3-10.	Indirect Address Generation for Load/Store	90
3-11.	Address Generator Options for Load/Store	90
3-12.	CPU Fetch Packet Types	91
3-13.	Layout Field Description in Compact Instruction Packet Header	92
3-14.	Expansion Field Description in Compact Instruction Packet Header	93
3-15.	LD/ST Data Size Selection	94
3-16.	P-bits Field Description in Compact Instruction Packet Header	
3-17.	Available Compact Instructions	96
3-18.	Relationships Between Operands, Operand Size, Functional Units, and Opfields for Example Instruction (ADD)	100
3-19.	Program Counter Values for Branch Using a Displacement Example	152





3-20.	Program Counter Values for Branch Using a Register Example	154
3-21.	Program Counter Values for B IRP Instruction Example	156
3-22.	Program Counter Values for B NRP Instruction Example	
3-23.	Data Types Supported by LDB(U) Instruction	
3-24.	Data Types Supported by LDB(U) Instruction (15-Bit Offset)	
3-25.	Data Types Supported by LDH(U) Instruction	
3-26.	Data Types Supported by LDH(U) Instruction (15-Bit Offset)	
3-20. 3-27.	Register Addresses for Accessing the Control Registers	
3-28.	Field Allocation in stg/cyc Field	482
3-29.	Bit Allocations to Stage and Cycle in stg/cyc Field	
4-1.	Operations Occurring During Pipeline Phases	
4-2.	Execution Stage Length Description for Each Instruction Type - Part A	
4-3.	Execution Stage Length Description for Each Instruction Type - Part B	
4-4.	Execution Stage Length Description for Each Instruction Type - Part C	
4-5.	Execution Stage Length Description for Each Instruction Type - Part D	
4-6.	Single-Cycle Instruction Execution	
4-7.	Multiply Instruction Execution	589
4-8.	Store Instruction Execution	
4-9.	Extended Multiply Instruction Execution	
4-10.	Load Instruction Execution	
4-11.	Branch Instruction Execution	594
4-12.	Two-Cycle DP Instruction Execution	596
4-13.	Four-Cycle Instruction Execution	597
4-14.	INTDP Instruction Execution	598
4-15.	DP Compare Instruction Execution	
4-16.	ADDDP/SUBDP Instruction Execution	599
4-17.	MPYI Instruction Execution	599
4-18.	MPYID Instruction Execution	600
4-19.	MPYDP Instruction Execution	600
4-20.	MPYSPDP Instruction Execution	601
4-21.	MPYSP2DP Instruction Execution	601
4-22.	Single-Cycle .S-Unit Instruction Constraints	602
4-23.	DP Compare .S-Unit Instruction Constraints	603
4-24.	2-Cycle DP .S-Unit Instruction Constraints	604
4-25.	ADDSP/SUBSP .S-Unit Instruction Constraints	604
4-26.	ADDDP/SUBDP .S-Unit Instruction Constraints	605
4-27.	Branch .S-Unit Instruction Constraints	605
4-28.	16 × 16 Multiply .M-Unit Instruction Constraints	606
4-29.	4-Cycle .M-Unit Instruction Constraints	607
4-30.	MPYI .M-Unit Instruction Constraints	608
4-31.	MPYID .M-Unit Instruction Constraints	609
4-32.	MPYDP .M-Unit Instruction Constraints	610
4-33.	MPYSP .M-Unit Instruction Constraints	611
4-34.	MPYSPDP .M-Unit Instruction Constraints	612
4-35.	MPYSP2DP .M-Unit Instruction Constraints	613
4-36.	Single-Cycle .L-Unit Instruction Constraints	614
4-37.	4-Cycle .L-Unit Instruction Constraints	615
4-38.	INTDP .L-Unit Instruction Constraints	616
4-39.	ADDDP/SUBDP .L-Unit Instruction Constraints.	617



www.ti.com

4-40.	Load .D-Unit Instruction Constraints	618
4-41.	Store .D-Unit Instruction Constraints	619
4-42.	Single-Cycle .D-Unit Instruction Constraints	620
4-43.	LDDW Instruction With Long Write Instruction Constraints	620
4-44.	Program Memory Accesses Versus Data Load Accesses	625
5-1.	Interrupt Priorities	629
5-2.	Interrupt Control Registers	634
5-3.	TSR Field Behavior When an Interrupt is Taken	643
5-4.	TSR Field Behavior When an NMI Interrupt is Taken	646
6-1.	Exception-Related Control Registers	655
6-2.	NTSR Field Behavior When an Exception is Taken	658
6-3.	TSR Field Behavior When an Exception is Taken (EXC = 0)	661
7-1.	SPLOOP Instruction Flow for and	674
7-2.	SPLOOPW Instruction Flow for	675
7-3.	Software Pipeline Instruction Flow Using the Loop Buffer	677
7-4.	SPLOOPD Minimum Loop Iterations	685
7-5.	SPLOOP Instruction Flow for First Three Cycles of	694
7-6.	SPLOOP Instruction Flow for	696
A-1.	Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs	709
B-1.	Instruction to Functional Unit Mapping	715
C-1.	Instructions Executing in the .D Functional Unit	722
C-2.	.D Unit Opcode Map Symbol Definitions	722
C-3.	Address Generator Options for Load/Store	723
D-1.	Instructions Executing in the .L Functional Unit	734
D-2.	.L Unit Opcode Map Symbol Definitions	735
E-1.	Instructions Executing in the .M Functional Unit	742
E-2.	.M Unit Opcode Map Symbol Definitions	743
F-1.	Instructions Executing in the .S Functional Unit	746
F-2.	.S Unit Opcode Map Symbol Definitions	747
G-1.	.D, .L, and .S Units Opcode Map Symbol Definitions	758
H-1.	Instructions Executing With No Unit Specified	764
H-2.	No Unit Specified Instructions Opcode Map Symbol Definitions	764
I ₋ 1	Document Revision History	760

16 List of Tables SPRUFE8B-July 2010



Read This First

About This Manual

The TMS320C674x[™] DSP is the new generation floating-point DSP that combines the TMS320C67x+[™] DSP and the TMS320C64x+[™] DSP instruction set architectures into one core. This document describes the CPU architecture, pipeline, instruction set, and interrupts of the C674x[™] DSP.

Notational Conventions

This document uses the following conventions.

Hexadecimal numbers are shown with the suffix h. For example, the following number is 40 hexadecimal (decimal 64): 40h.

Related Documentation From Texas Instruments

The following documents describe the C6000 devices and related support tools. Copies of these documents are available on the Internet at www.ti.com. Tip: Enter the literature number in the search box provided at www.ti.com.

The current documentation that describes the C6000 devices, related peripherals, and other technical collateral, is available in the C6000 DSP product folder at: www.ti.com/c6000.

- SPRUFK9 TMS320C674x/OMAP-L1x Processor Peripherals Overview Reference Guide. Provides an overview and briefly describes the peripherals available on the TMS320C674x Digital Signal Processors (DSPs) and OMAP-L1x Applications Processors.
- SPRUFK5 TMS320C674x DSP Megamodule Reference Guide. Describes the TMS320C674x digital signal processor (DSP) megamodule. Included is a discussion on the internal direct memory access (IDMA) controller, the interrupt controller, the power-down controller, memory protection, bandwidth management, and the memory and cache.
- SPRUG82 TMS320C674x DSP Cache User's Guide. Explains the fundamentals of memory caches and describes how the two-level cache-based internal memory architecture in the TMS320C674x digital signal processor (DSP) can be efficiently used in DSP applications. Shows how to maintain coherence with external memory, how to use DMA to reduce memory latencies, and how to optimize your code to improve cache efficiency. The internal memory architecture in the C674x DSP is organized in a two-level hierarchy consisting of a dedicated program cache (L1P) and a dedicated data cache (L1D) on the first level. Accesses by the CPU to the these first level caches can complete without CPU pipeline stalls. If the data requested by the CPU is not contained in cache, it is fetched from the next lower memory level, L2 or external memory.

TMS320C674x, TMS320C67x+, TMS320C64x+, C674x, TMS320C67x+, TMS320C64x+, XDS510, XDS560 are trademarks of Texas Instruments.

Windows is a registered trademark of Microsoft Corporation.

SPRUFE8B-July 2010 Read This First 17

18 Read This First SPRUFE8B-July 2010



Introduction

	Topic		Page
	1.1	Overview	20
	1.2	DSP Features and Options	20
	1.3	DSP Architecture	22
ı			



Overview www.ti.com

1.1 Overview

The TMS320C674x[™] DSP is the new generation floating-point DSP that combines the TMS320C67x+[™] DSP and the TMS320C64x+[™] DSP instruction set architectures into one core.

The C674x[™] megamodule is the name used to designate the CPU together with the hardware providing memory, bandwidth management, interrupt, memory protection, and power-down support. This document describes the CPU architecture, pipeline, instruction set, and interrupts of the C674x DSP. The C674x megamodule is not described in this document since it is fully covered in the *TMS320C674x DSP Megamodule Reference Guide* (SPRUFK5).

1.2 DSP Features and Options

The C6000 devices execute up to eight 32-bit instructions per cycle. The C674x CPU consists of 64 general-purpose 32-bit registers and eight functional units. These eight functional units contain:

- Two multipliers
- Six ALUs

The C6000 generation has a complete set of optimized development tools, including an efficient C compiler, an assembly optimizer for simplified assembly-language programming and scheduling, and a Windows® operating system-based debugger interface for visibility into source code execution characteristics. A hardware emulation board, compatible with the TI XDS510™ and XDS560™ emulator interface, is also available. This tool complies with IEEE Standard 1149.1-1990, IEEE Standard Test Access Port and Boundary-Scan Architecture.

Features of the C6000 devices include:

- Advanced VLIW CPU with eight functional units, including two multipliers and six arithmetic units
 - Executes up to eight instructions per cycle for up to ten times the performance of typical DSPs
 - Allows designers to develop highly effective RISC-like code for fast development time
- Instruction packing
 - Gives code size equivalence for eight instructions executed serially or in parallel
 - Reduces code size, program fetches, and power consumption
- Conditional execution of most instructions
 - Reduces costly branching
 - Increases parallelism for higher sustained performance
- Efficient code execution on independent functional units
 - Industry's most efficient C compiler on DSP benchmark suite
 - Industry's first assembly optimizer for fast development and improved parallelization
- 8/16/32-bit data support, providing efficient memory support for a variety of applications
- 40-bit arithmetic options add extra precision for vocoders and other computationally intensive applications
- Saturation and normalization provide support for key arithmetic operations
- Field manipulation and instruction extract, set, clear, and bit counting support common operation found in control and data manipulation applications.



The C674x devices include these additional features:

- Each multiplier can perform two 16 x 16-bit or four 8 x 8 bit multiplies every clock cycle.
- Quad 8-bit and dual 16-bit instruction set extensions with data flow support
- Support for non-aligned 32-bit (word) and 64-bit (double word) memory accesses
- Special communication-specific instructions have been added to address common operations in error-correcting codes.
- Bit count and rotate hardware extends support for bit-level algorithms.
- Compact instructions: Common instructions (AND, ADD, LD, MPY) have 16-bit versions to reduce code size.
- Protected mode operation: A two-level system of privileged program execution to support higher capability operating systems and system features such as memory protection.
- Exceptions support for error detection and program redirection to provide robust code execution
- Hardware support for modulo loop operation to reduce code size
- Each multiplier can perform 32 x 32 bit multiplies
- Additional instructions to support complex multiplies allowing up to eight 16-bit multiply/add/subtracts per clock cycle

The C674x devices are enhanced for code size improvement and floating-point performance. These additional features include:

- Hardware support for single-precision (32-bit) and double-precision (64-bit) IEEE floating-point operations.
- Execute packets can span fetch packets.
- Register file size is increased to 64 registers (32 in each datapath).
- · Floating-point addition and subtraction capability in the .S unit.
- · Mixed-precision multiply instructions.
- 32 x 32-bit integer multiply with 32-bit or 64-bit result.

The VelociTI architecture of the C6000 platform of devices make them the first off-the-shelf DSPs to use advanced VLIW to achieve high performance through increased instruction-level parallelism. A traditional VLIW architecture consists of multiple execution units running in parallel, performing multiple instructions during a single clock cycle. Parallelism is the key to extremely high performance, taking these DSPs well beyond the performance capabilities of traditional superscalar designs. VelociTI is a highly deterministic architecture, having few restrictions on how or when instructions are fetched, executed, or stored. It is this architectural flexibility that is key to the breakthrough efficiency levels of the TMS320C6000 Optimizing compiler. VelociTI's advanced features include:

- · Instruction packing: reduced code size
- All instructions can operate conditionally: flexibility of code
- Variable-width instructions: flexibility of data types
- Fully pipelined branches: zero-overhead branching.



DSP Architecture www.ti.com

1.3 DSP Architecture

Figure 1-1 is the block diagram for the C674x DSP. The C6000 devices come with program memory, which, on some devices, can be used as a program cache. The devices also have varying sizes of data memory. Peripherals such as a direct memory access (DMA) controller, power-down logic, and external memory interface (EMIF) usually come with the CPU, while peripherals such as serial ports and host ports are on only certain devices. Check the data sheet for your device to determine the specific peripheral configurations you have.




Figure 1-1. TMS320C674x DSP Block Diagram



www.ti.com DSP Architecture

1.3.1 Central Processing Unit (CPU)

The C674x CPU, in Figure 1-1, contains:

- · Program fetch unit
- 16/32 bit instruction dispatch unit, advanced instruction packing
- Instruction decode unit
- Two data paths, each with four functional units
- 64 32-bit registers
- Control registers
- Control logic
- · Test, emulation, and interrupt logic
- Internal DMA (IDMA) for transfers between internal memories

The program fetch, instruction dispatch, and instruction decode units can deliver up to eight 32-bit instructions to the functional units every CPU clock cycle. The processing of instructions occurs in each of the two data paths (A and B), each of which contains four functional units (.L, .S, .M, and .D) and 32 32-bit general-purpose registers. The data paths are described in more detail in Chapter 2. A control register file provides the means to configure and control various processor operations. To understand how instructions are fetched, dispatched, decoded, and executed in the data path, see Chapter 4.

1.3.2 Internal Memory

The DSP has a 32-bit, byte-addressable address space. Internal (on-chip) memory is organized in separate data and program spaces. When off-chip memory is used, these spaces are unified on most devices to a single memory space via the external memory interface (EMIF).

The DSP has a 256-bit read-only port to access internal program memory and two 256-bit ports (read and write) to access internal data memory.

1.3.3 Memory and Peripheral Options

For an overview of the peripherals available on the C674x DSPs and OMAP-L1x Applications Processors, refer to the *TMS320C674x/OMAP-L1x Processor Peripherals Overview Reference Guide* (SPRUFK9) or to your device-specific data manual.

24 Introduction SPRUFE8B-July 2010



CPU Data Paths and Control

This chapter focuses on the CPU, providing information about the data paths and control registers. The two register files and the data cross paths are described.

Topic Page

2.1	Introduction	26
2.2	General-Purpose Register Files	26
2.3	Functional Units	29
2.4	Register File Cross Paths	30
2.5	Memory, Load, and Store Paths	31
2.6	Data Address Paths	31
2.7	Galois Field	31
2.8	Control Register File	34
2.9	Control Register File Extensions	46
2.10	Control Register File Extensions for Floating-Point Operations	58



Introduction www.ti.com

2.1 Introduction

The components of the data path for the CPU are shown in Figure 2-1. These components consist of:

- Two general-purpose register files (A and B)
- Eight functional units (.L1, .L2, .S1, .S2, .M1, .M2, .D1, and .D2)
- Two load-from-memory data paths (LD1 and LD2)
- Two store-to-memory data paths (ST1 and ST2)
- Two data address paths (DA1 and DA2)
- Two register file data cross paths (1X and 2X)

2.2 General-Purpose Register Files

There are two general-purpose register files (A and B) in the CPU data paths. Each of these files contains 32 32-bit registers (A0–A31 for file A and B0–B31 for file B), as shown in Table 2-1. The general-purpose registers can be used for data, data address pointers, or condition registers.

The DSP general-purpose register files support data ranging in size from packed 8-bit through 64-bit fixed-point data. Values larger than 32 bits, such as 40-bit and 64-bit quantities, are stored in register pairs. The 32 LSBs of data are placed in an even-numbered register and the remaining 8 or 32 MSBs in the next upper register (that is always an odd-numbered register). Packed data types store either four 8-bit values or two 16-bit values in a single 32-bit register, or four 16-bit values in a 64-bit register pair.

There are 32 valid register pairs for 40-bit and 64-bit data in the DSP cores. In assembly language syntax, a colon between the register names denotes the register pair, and the odd-numbered register is specified first.

Figure 2-2 shows the register storage scheme for 40-bit long data. Operations requiring a long input ignore the 24 MSBs of the odd-numbered register. Operations producing a long result zero-fill the 24 MSBs of the odd-numbered register. The even-numbered register is encoded in the opcode.



Even Odd register register file A file A (A0, A2, (A1, A3, src2 .L1 A4...A30) A5...A31) odd dst See note 4 even dst long src ST1b 4 32 MSB ST1a 32 LSB long src even dst See note 4 odd dst Data path A src1 src2 See note 1 dst2 See note 2 dst1 src1 src2 See note 3 32 MSB LD1b_ 32 LSB LD1a dst .D1 src1 src2 Even register Odd src2 register (B0, B2, src1 file B B4...B30) dst (B1, B3, B5...B31) 32 LSB LD2a -32 MSB LD2b _ 64 See note 3 .M2 dst1 See note 2 32 dst2 .S2 odd dst Data path B even dst long sro ST2a ◀ 32 MSB ST2b
32 LSB long sro even dst See note 4 odd dst src2 Control Register

Figure 2-1. CPU Data Paths

- 1. On .M unit, dst2 is 32 MSB.
- 2. On .M unit, dst1 is 32 MSB.
- 3. On .M unit, src2 is 64 bits.
- 4. On .L and .S units, odd dst connects to odd register files and even dst connects to even register files.


SPRUFE8B–July 2010 CPU Data Paths and Control 27



Table 2-1. 40-Bit/64-Bit Register Pairs

Register Files				
A	В			
A1:A0	B1:B0			
A3:A2	B3:B2			
A5:A4	B5:B4			
A7:A6	B7:B6			
A9:A8	B9:B8			
A11:A10	B11:B10			
A13:A12	B13:B12			
A15:A14	B15:B14			
A17:A16	B17:B16			
A19:A18	B19:B18			
A21:A20	B21:B20			
A23:A22	B23:B22			
A25:A24	B25:B24			
A27:A26	B27:B26			
A29:A28	B29:B28			
A31:A30	B31:B30			

Figure 2-2. Storage Scheme for 40-Bit Data in a Register Pair



28 CPU Data Paths and Control SPRUFE8B-July 2010



www.ti.com Functional Units

2.3 Functional Units

The eight functional units in the C6000 data paths can be divided into two groups of four; each functional unit in one data path is almost identical to the corresponding unit in the other data path. The functional units are described in Table 2-2.

Most data lines in the CPU support 32-bit operands, and some support long (40-bit) and doubleword (64-bit) operands. Each functional unit has its own 32-bit write port, so all eight units can be used in parallel every cycle, into a general-purpose register file (refer to Figure 2-1). All units ending in 1 (for example, .L1) write to register file A, and all units ending in 2 write to register file B. Each functional unit has two 32-bit read ports for source operands *src1* and *src2*. Four units (.L1, .L2, .S1, and .S2) have an extra 8-bit-wide port for 40-bit long writes, as well as an 8-bit input for 40-bit long reads. Since each DSP multiplier can return up to a 64-bit result, an extra write port has been added from the multipliers to the register file.

See Appendix B for a list of the instructions that execute on each functional unit.

Table 2-2. Functional Units and Operations Performed

Functional Unit	Fixed-Point Operations	Floating-Point Operations	
.L unit (.L1, .L2)	32/40-bit arithmetic and compare operations	Arithmetic operations	
	32-bit logical operations	$DP \to SP$ conversion operations	
	Leftmost 1 or 0 counting for 32 bits	$INT \rightarrow DP$ conversion operations	
	Normalization count for 32 and 40 bits	$INT \rightarrow SP$ conversion operations	
	Byte shifts		
	Data packing/unpacking		
	5-bit constant generation		
	Dual 16-bit arithmetic operations		
	Quad 8-bit arithmetic operations		
	Dual 16-bit minimum/maximum operations		
	Quad 8-bit minimum/maximum operations		
.S unit (.S1, .S2)	32-bit arithmetic operations	Compare	
	32/40-bit shifts and 32-bit bit-field operations	Reciprocal and reciprocal square-root operations	
	32-bit logical operations	Absolute value operations	
	Branches	$SP \rightarrow DP$ conversion operations	
	Constant generation	SP and DP adds and subtracts	
	Register transfers to/from control register file (.S2 only)	SP and DP reverse subtracts (src2 - src1)	
	Byte shifts		
	Data packing/unpacking		
	Dual 16-bit compare operations		
	Quad 8-bit compare operations		
	Dual 16-bit shift operations		
	Dual 16-bit saturated arithmetic operations		
	Quad 8-bit saturated arithmetic operations		

SPRUFE8B-July 2010 CPU Data Paths and Control 29



Table 2-2. Functional Units and Operations Performed (continued)

Functional Unit	Fixed-Point Operations	Floating-Point Operations
.M unit (.M1, .M2)	32 x 32-bit multiply operations	Floating-point multiply operations
	16 x 16-bit multiply operations	Mixed-precision multiply operations
	16 x 32-bit multiply operations	
	Quad 8 × 8-bit multiply operations	
	Dual 16 x 16-bit multiply operations	
	Dual 16 x 16-bit multiply with add/subtract operations	
	Quad 8 x 8-bit multiply with add operation	
	Bit expansion	
	Bit interleaving/de-interleaving	
	Variable shift operations	
	Rotation	
	Galois Field Multiply	
.D unit (.D1, .D2)	32-bit add, subtract, linear and circular address calculation	Load doubleword with 5-bit constant offset
	Loads and stores with 5-bit constant offset	
	Loads and stores with 15-bit constant offset (.D2 only)	
	Load and store doublewords with 5-bit constant	
	Load and store nonaligned words and doublewords	
	5-bit constant generation	
	32-bit logical operations	

2.4 Register File Cross Paths

Each functional unit reads directly from and writes directly to the register file within its own data path. That is, the .L1, .S1, .D1, and .M1 units write to register file A and the .L2, .S2, .D2, and .M2 units write to register file B. The register files are connected to the opposite-side register file's functional units via the 1X and 2X cross paths. These cross paths allow functional units from one data path to access a 32-bit operand from the opposite side register file. The 1X cross path allows the functional units of data path A to read their source from register file B, and the 2X cross path allows the functional units of data path B to read their source from register file A.

On the DSP, all eight of the functional units have access to the register file on the opposite side, via a cross path. The *src2* inputs of .M1, .M2, .S1, .S2, .D1, and .D2 units are selectable between the cross path and the same-side register file. In the case of .L1 and .L2, both *src1* and *src2* inputs are selectable between the cross path and the same-side register file.

Only two cross paths, 1X and 2X, exist in the C6000 architecture. Thus, the limit is one source read from each data path's opposite register file per cycle, or a total of two cross path source reads per cycle. In the DSP, two units on a side may read the same cross path source simultaneously.

On the DSP, a delay clock cycle is introduced whenever an instruction attempts to read a register via a cross path that was updated in the previous cycle. This is known as a cross path stall. This stall is inserted automatically by the hardware, no **NOP** instruction is needed. It should be noted that no stall is introduced if the register being read is the destination for data placed by an **LDx** instruction. For more information see Section 3.8.4. Techniques for avoiding this stall are discussed in the *TMS320C6000 Programmers Guide* (SPRU198).



2.5 Memory, Load, and Store Paths

The DSP supports doubleword loads and stores. There are four 32-bit paths for loading data from memory to the register file. For side A, LD1a is the load path for the 32 LSBs and LD1b is the load path for the 32 MSBs. For side B, LD2a is the load path for the 32 LSBs and LD2b is the load path for the 32 MSBs. There are also four 32-bit paths for storing register values to memory from each register file. For side A, ST1a is the write path for the 32 LSBs and ST1b is the write path for the 32 MSBs. For side B, ST2a is the write path for the 32 LSBs and ST2b is the write path for the 32 MSBs.

On the C6000 architecture, some of the ports for long and doubleword operands are shared between functional units. This places a constraint on which long or doubleword operations can be scheduled on a data path in the same execute packet. See Section 3.8.6.

2.6 Data Address Paths

The data address paths (DA1 and DA2) are each connected to the .D units in both data paths. This allows data addresses generated by any one path to access data to or from any register.

The DA1 and DA2 resources and their associated data paths are specified as T1 and T2, respectively. T1 consists of the DA1 address path and the LD1 and ST1 data paths. For the DSP, LD1 is comprised of LD1a and LD1b to support 64-bit loads; ST1 is comprised of ST1a and ST1b to support 64-bit stores. Similarly, T2 consists of the DA2 address path and the LD2 and ST2 data paths. For the DSP, LD2 is comprised of LD2a and LD2b to support 64-bit loads; ST2 is comprised of ST2a and ST2b to support 64-bit stores.

The T1 and T2 designations appear in the functional unit fields for load and store instructions. For example, the following load instruction uses the .D1 unit to generate the address but is using the LD2 path resource from DA2 to place the data in the B register file. The use of the DA2 resource is indicated with the T2 designation.

LDW .D1T2 *A0[3],B1

2.7 Galois Field

Modern digital communication systems typically make use of error correction coding schemes to improve system performance under imperfect channel conditions. The scheme most commonly used is the Reed-Solomon code, due to its robustness against burst errors and its relative ease of implementation.

The DSP contains Galois field multiply hardware that is used for Reed-Solomon encode and decode functions. To understand the relevance of the Galois field multiply hardware, it is necessary to first define some mathematical terms.

Two kinds of number systems that are common in algorithm development are integers and real numbers. For integers, addition, subtraction, and multiplication operations can be performed. Division can also be performed, if a nonzero remainder is allowed. For real numbers, all four of these operations can be performed, even if there is a nonzero remainder for division operations.

Real numbers can belong to a mathematical structure called a field. A field consists of a set of data elements along with addition, subtraction, multiplication, and division. A field of integers can also be created if modulo arithmetic is performed.

An example is doing arithmetic using integers modulo 2. Perform the operations using normal integer arithmetic and then take the result modulo 2. Table 2-3 illustrates addition, subtraction, and multiplication modulo 2.

Table 2-3. Modulo 2 Arithmetic

Addition						
+ 0 1						
0	0	1				
1	1	0				

Subtraction					
-	0	1			
0	0	1			
1	1	0			

Multiplication						
× 0 1						
0	0	0				
1	0	1				

SPRUFE8B-July 2010 CPU Data Paths and Control 31



Galois Field www.ti.com

Note that addition and subtraction results are the same, and in fact are equivalent to the XOR (exclusive-OR) operation in binary. Also, the multiplication result is equal to the AND operation in binary. These properties are unique to modulo 2 arithmetic, but modulo 2 arithmetic is used extensively in error correction coding. Another more general property is that division by any nonzero element is now defined. Division can always be performed, if every element other than zero has a multiplicative inverse:

$$x \times x^{-1} = 1$$

Another example, arithmetic modulo 5, illustrates this concept more clearly. The addition, subtraction, and multiplication tables are given in Table 2-4.

Table 2-4. Modulo 5 Arithmetic

Addition						
+	0	1	2	3	4	
0	0	1	2	3	4	
1	1	2	3	4	0	
2	2	3	4	0	1	
3	3	4	0	1	2	
4	4	0	1	2	3	

4
1
2
3
4
0

Multiplication						
×	0	1	2	3	4	
0	0	0	0	0	0	
1	0	1	2	3	4	
2	0	2	4	1	3	
3	0	3	1	4	2	
4	0	4	3	2	1	

In the rows of the multiplication table, element 1 appears in every nonzero row and column. Every nonzero element can be multiplied by at least one other element for a result equal to 1. Therefore, division always works and arithmetic over integers modulo 5 forms a field. Fields generated in this manner are called finite fields or Galois fields and are written as GF(X), such as GF(2) or GF(5). They only work when the arithmetic performed is modulo a prime number.

Galois fields can also be formed where the elements are vectors instead of integers if polynomials are used. Finite fields, therefore, can be found with a number of elements equal to any power of a prime number. Typically, we are interested in implementing error correction coding systems using binary arithmetic. All of the fields that are dealt with in Reed Solomon coding systems are of the form GF(2^m). This allows performing addition using XORs on the coefficients of the vectors, and multiplication using a combination of ANDs and XORs.

A final example considers the field $GF(2^3)$, which has 8 elements. This can be generated by arithmetic modulo the (irreducible) polynomial $P(x) = x^3 + x + 1$. Elements of this field look like vectors of three bits. Table 2-5 shows the addition and multiplication tables for field $GF(2^3)$.

Note that the value 1 (001) appears in every nonzero row of the multiplication table, which indicates that this is a valid field.

The channel error can now be modeled as a vector of bits, with a one in every bit position that an error has occurred, and a zero where no error has occurred. Once the error vector has been determined, it can be subtracted from the received message to determine the correct code word.

The Galois field multiply hardware on the DSP is named GMPY4. The **GMPY4** instruction performs four parallel operations on 8-bit packed data on the .M unit. The Galois field multiplier can be programmed to perform all Galois multiplies for fields of the form GF(2^m), where m can range between 1 and 8 using any generator polynomial. The field size and the polynomial generator are controlled by the Galois field polynomial generator function register (GFPGFR).

In addition to the **GMPY4** instruction, the C674x DSP has the **GMPY** instruction that uses either the GPLYA or GPLYB control register as a source for the polynomial (depending on whether the A or B side functional unit is used) and produces a 32-bit result.

The GFPGFR, shown in Figure 2-6 and described in Table 2-10, contains the Galois field polynomial generator and the field size control bits. These bits control the operation of the **GMPY4** instruction. GFPGFR can only be set via the **MVC** instruction. The default function after reset for the **GMPY4** instruction is field size = 7h and polynomial = 1Dh.



www.ti.com Galois Field

2.7.1 Special Timing Considerations

If the next execute packet after an **MVC** instruction that changes the GFPGFR value contains a **GMPY4** instruction, then the **GMPY4** is controlled by the newly loaded GFPGFR value.

Table 2-5. Modulo Arithmetic for Field GF(23)

Addition

+	000	001	010	011	100	101	110	111
000	000	001	010	011	100	101	110	111
001	001	000	011	010	101	100	111	110
010	010	011	000	001	110	111	100	101
011	011	010	001	000	111	110	101	100
100	100	101	110	111	000	001	010	011
101	101	100	111	110	001	000	011	010
110	110	111	100	101	010	011	000	001
111	111	110	101	100	011	010	001	000

Multiplication

			-					
×	000	001	010	011	100	101	110	111
000	000	000	000	000	000	000	000	000
001	000	001	010	011	100	101	110	111
010	000	010	100	110	011	001	111	101
011	000	011	110	101	111	100	001	010
100	000	100	011	111	110	010	101	001
101	000	101	001	100	010	111	011	110
110	000	110	111	001	101	011	010	100
111	000	111	101	010	001	110	100	011

SPRUFE8B-July 2010 CPU Data Paths and Control 33



Control Register File www.ti.com

2.8 Control Register File

Table 2-6 lists the control registers contained in the control register file.

Table 2-6. Control Registers

Acronym	Register Name	Section			
AMR	Addressing mode register	Section 2.8.3			
CSR	Control status register	Section 2.8.4			
GFPGFR	Galois field multiply control register	Section 2.8.5			
ICR	Interrupt clear register	Section 2.8.6			
IER	Interrupt enable register	Section 2.8.7			
IFR	Interrupt flag register	Section 2.8.8			
IRP	Interrupt return pointer register	Section 2.8.9			
ISR	Interrupt set register	Section 2.8.10			
ISTP	Interrupt service table pointer register	Section 2.8.11			
NRP	Nonmaskable interrupt return pointer register	Section 2.8.12			
PCE1	Program counter, E1 phase	Section 2.8.13			
	Control Register File Extensions				
DIER	Debug interrupt enable register	Section 2.9.1			
DNUM	DSP core number register	Section 2.9.2			
ECR	Exception clear register	Section 2.9.3			
EFR	Exception flag register	Section 2.9.4			
GPLYA	GMPY A-side polynomial register	Section 2.9.5			
GPLYB	GMPY B-side polynomial register	Section 2.9.6			
IERR	Internal exception report register	Section 2.9.7			
ILC	Inner loop count register	Section 2.9.8			
ITSR	Interrupt task state register	Section 2.9.9			
NTSR	NMI/Exception task state register	Section 2.9.10			
REP	Restricted entry point address register	Section 2.9.11			
RILC	Reload inner loop count register	Section 2.9.12			
SSR	Saturation status register	Section 2.9.13			
TSCH	Time-stamp counter (high 32) register	Section 2.9.14			
TSCL	Time-stamp counter (low 32) register	Section 2.9.14			
TSR	Task state register	Section 2.9.15			
	Control Register File Extensions for Floating-point Operations				
FADCR	Floating-point adder configuration register	Section 2.10.1			
FAUCR	Floating-point auxiliary configuration register Section 2.10.2				
FMCR	Floating-point multiplier configuration register Section 2.10.3				



www.ti.com Control Register File

2.8.1 Register Addresses for Accessing the Control Registers

Table 3-27 lists the register addresses for accessing the control register file. One unit (.S2) can read from and write to the control register file. Each control register is accessed by the **MVC** instruction. See the **MVC** instruction (see MVC) for information on how to use this instruction.

Additionally, some of the control register bits are specially accessed in other ways. For example, arrival of a maskable interrupt on an external interrupt pin, INT*m*, triggers the setting of flag bit IFR*m*. Subsequently, when that interrupt is processed, this triggers the clearing of IFR*m* and the clearing of the global interrupt enable bit, GIE. Finally, when that interrupt processing is complete, the **B IRP** instruction in the interrupt service routine restores the pre-interrupt value of the GIE. Similarly, saturating instructions like **SADD** set the SAT (saturation) bit in the control status register (CSR).

On the CPU, access to some of the registers is restricted when in User mode. See Chapter 8 for more information.

2.8.2 Pipeline/Timing of Control Register Accesses

All **MVC** instructions are single-cycle instructions that complete their access of the explicitly named registers in the E1 pipeline phase. This is true whether **MVC** is moving a general register to a control register, or conversely. In all cases, the source register content is read, moved through the .S2 unit, and written to the destination register in the E1 pipeline phase.

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.S2

Even though **MVC** modifies the particular target control register in a single cycle, it can take extra clocks to complete modification of the non-explicitly named register. For example, the **MVC** cannot modify bits in the IFR directly. Instead, **MVC** can only write 1's into the ISR or the ICR to specify setting or clearing, respectively, of the IFR bits. **MVC** completes this ISR/ICR write in a single (E1) cycle but the modification of the IFR bits occurs one clock later. For more information on the manipulation of ISR, ICR, and IFR, see Section 2.8.10, Section 2.8.6, and Section 2.8.8.

Saturating instructions, such as **SADD**, set the saturation flag bit (SAT) in CSR indirectly. As a result, several of these instructions update the SAT bit one full clock cycle after their primary results are written to the register file. For example, the **SMPY** instruction writes its result at the end of pipeline stage E2; its primary result is available after one delay slot. In contrast, the SAT bit in CSR is updated one cycle later than the result is written; this update occurs after two delay slots. (For the specific behavior of an instruction, refer to the description of that individual instruction).

The **B IRP** and **B NRP** instructions directly update the GIE and NMIE bits, respectively. Because these branches directly modify CSR and IER, respectively, there are no delay slots between when the branch is issued and when the control register updates take effect.

SPRUFE8B-July 2010 CPU Data Paths and Control 35



Control Register File www.ti.com

2.8.3 Addressing Mode Register (AMR)

36

For each of the eight registers (A4-A7, B4-B7) that can perform linear or circular addressing, the addressing mode register (AMR) specifies the addressing mode. A 2-bit field for each register selects the address modification mode: linear (the default) or circular mode. With circular addressing, the field also specifies which BK (block size) field to use for a circular buffer. In addition, the buffer must be aligned on a byte boundary equal to the block size. The mode select fields and block size fields are shown in Figure 2-3 and described in Table 2-7.

Figure 2-3. Addressing Mode Register (AMR)

31					26	25				21	20				16
Reserved					BK1				BK0						
	R-0				R/W-0				R/W-0						
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
B7 M	ODE	B6 M	ODE	B5 N	IODE	B4 MODE		A7 MODE		A6 M	A6 MODE		A5 MODE		ODE
R/W	R/W-0 R/W-0 R/W-0			R/W-0 R/W-0 R/			R/V	W-0 R/W-0			R/W-0				

LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

Table 2-7. Addressing Mode Register (AMR) Field Descriptions

Bit	Field	Value	Description
31-26	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
25-21	BK1	0-1Fh	Block size field 1. A 5-bit value used in calculating block sizes for circular addressing. Table 2-8 shows block size calculations for all 32 possibilities.
			Block size (in bytes) = $2^{(N+1)}$, where N is the 5-bit value in BK1
20-16	ВК0	0-1Fh	Block size field 0. A 5-bit value used in calculating block sizes for circular addressing. Table 2-8 shows block size calculations for all 32 possibilities.
			Block size (in bytes) = $2^{(N+1)}$, where N is the 5-bit value in BK0
15-14	B7 MODE	0-3h	Address mode selection for register file B7.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
13-12	B6 MODE	0-3h	Address mode selection for register file B6.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
11-10	B5 MODE	0-3h	Address mode selection for register file B5.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
9-8	B4 MODE	0-3h	Address mode selection for register file B4.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
7-6	A7 MODE	0-3h	Address mode selection for register file A7.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved



www.ti.com Control Register File

Table 2-7. Addressing Mode Register (AMR) Field Descriptions (continued)

Bit	Field	Value	Description
5-4	A6 MODE	0-3h	Address mode selection for register file A6.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
3-2	A5 MODE	0-3h	Address mode selection for register file a5.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved
1-0	A4 MODE	0-3h	Address mode selection for register file A4.
		0	Linear modification (default at reset)
		1h	Circular addressing using the BK0 field
		2h	Circular addressing using the BK1 field
		3h	Reserved

Table 2-8. Block Size Calculations

BKn Value	Block Size	BKn Value	Block Size
00000	2	10000	131 072
00001	4	10001	262 144
00010	8	10010	524 288
00011	16	10011	1 048 576
00100	32	10100	2 097 152
00101	64	10101	4 194 304
00110	128	10110	8 388 608
00111	256	10111	16 777 216
01000	512	11000	33 554 432
01001	1 024	11001	67 108 864
01010	2 048	11010	134 217 728
01011	4 096	11011	268 435 456
01100	8 192	11100	536 870 912
01101	16 384	11101	1 073 741 824
01110	32 768	11110	2 147 483 648
01111	65 536	11111	4 294 967 296



Control Register File www.ti.com


2.8.4 Control Status Register (CSR)

The control status register (CSR) contains control and status bits. The CSR is shown in Figure 2-4 and described in Table 2-9. For the PWRD, EN, PCC, and DCC fields, see the device-specific datasheet to see if it supports the options that these fields control. The PCC and DCC fields are ignored on the C674x CPU.

The power-down modes and their wake-up methods are programmed by the PWRD field (bits 15-10) of CSR. The PWRD field of CSR is shown in Figure 2-5. When writing to CSR, all bits of the PWRD field should be configured at the same time. A logic 0 should be used when writing to the reserved bit (bit 15) of the PWRD field.

The PWRD, PCC, DCC, and PGIE fields cannot be written in User mode. The PCC and DCC fields can only be modified in Supervisor mode. See Chapter 8 for more information.

Figure 2-4. Control Status Register (CSR)



LEGEND: R = Readable by the **MVC** instruction; W = Writeable by the **MVC** instruction; SW = Writeable by the **MVC** instruction only in supervisor mode; WC = Bit is cleared on write; -n = value after reset; -x = value is indeterminate after reset

Figure 2-5. PWRD Field of Control Status Register (CSR)

15	14	13	12	11	10
Reserved	Enabled or nonenabled interrupt wake	Enabled interrupt wake	PD3	PD2	PD1
R/SW-0	R/SW-0	R/SW-0	R/SW-0	R/SW-0	R/SW-0

LEGEND: R = Readable by the **MVC** instruction; W = Readable by the **MVC** instruction; R = Readable by the **MVC**

Table 2-9. Control Status Register (CSR) Field Descriptions

Bit	Field	Value	Description
31-24	CPU ID	0-FFh	Identifies the CPU of the device. Not writable by the MVC instruction.
		0-13h	Reserved
		14h	C674x CPU
		15h-FFh	Reserved
23-16	REVISION ID	0-FFh	Identifies silicon revision of the CPU. For the most current silicon revision information, see the device-specific datasheet. Not writable by the MVC instruction.

⁽¹⁾ See the device-specific datasheet for the default value of this field.



www.ti.com Control Register File

Table 2-9. Control Status Register (CSR) Field Descriptions (continued)

Bit	Field	Value	Description
15-10	PWRD	0-3Fh	Power-down mode field. See Figure 2-5. Writable by the MVC instruction only in Supervisor mode.
		0	No power-down.
		1h-8h	Reserved
		9h	Power-down mode PD1; wake by an enabled interrupt.
		Ah-10h	Reserved
		11h	Power-down mode PD1; wake by an enabled or nonenabled interrupt.
		12h-19h	Reserved
		1Ah	Power-down mode PD2; wake by a device reset.
		1Bh	Reserved
		1Ch	Power-down mode PD3; wake by a device reset.
		1D-3Fh	Reserved
9	SAT		Saturate bit. Can be cleared only by the MVC instruction and can be set only by a functional unit. The set by a functional unit has priority over a clear (by the MVC instruction), if they occur on the same cycle. The SAT bit is set one full cycle (one delay slot) after a saturate occurs. The SAT bit will not be modified by a conditional instruction whose condition is false.
		0	No functional units generated saturated results.
		1	One or more functional units performed an arithmetic operation which resulted in saturation.
8	EN		Endian mode. Not writable by the MVC instruction.
		0	Big endian
		1	Little endian
7-5	PCC	0-7h	Program cache control mode. This field is ignored on the C674x CPU.
		0-7h	Reserved
4-2	DCC	0-7h	Data cache control mode. This field is ignored on the C674x CPU.
		0-7h	Reserved
1	PGIE		Previous GIE (global interrupt enable). This bit contains a copy of the GIE bit at the point when interrupt is taken. It is physically the same bit as GIE bit in the interrupt task state register (ITSR). Writeable by the MVC instruction only in Supervisor mode; not writable in User mode.
		0	Interrupts will be disabled after return from interrupt.
		1	Interrupts will be enabled after return from interrupt.
0	GIE		Global interrupt enable. Physically the same bit as GIE bit in the task state register (TSR). Writable by the MVC instruction in Supervisor and User mode. See Section 5.2 for details on how the GIE bit affects interruptibility.
		0	Disables all interrupts, except the reset interrupt and NMI (nonmaskable interrupt).
		1	Enables all interrupts.



Control Register File www.ti.com

2.8.5 Galois Field Polynomial Generator Function Register (GFPGFR)

The Galois field polynomial generator function register (GFPGFR) controls the field size and the Galois field polynomial generator of the Galois field multiply hardware. The GFPGFR is shown in Figure 2-6 and described in Table 2-10. The Galois field is described in Section 2.7.

Figure 2-6. Galois Field Polynomial Generator Function Register (GFPGFR)

31		27	26	24	23		16
	Reserved		SIZE			Reserved	
	R-0		R/W-7h)		R-0	
15				8	7		0
	Res	erved				POLY	
	F	R-0				R/W-1Dh	

LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

Table 2-10. Galois Field Polynomial Generator Function Register (GFPGFR) Field Descriptions

Bit	Field	Value	Description
31-27	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
26-24	SIZE	0-7h	Field size.
23-8	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
7-0	POLY	0-FFh	Polynomial generator.



Control Register File www.ti.com


2.8.6 Interrupt Clear Register (ICR)

The interrupt clear register (ICR) allows you to manually clear the maskable interrupts (INT15-INT4) in the interrupt flag register (IFR). Writing a 1 to any of the bits in ICR causes the corresponding interrupt flag (IFn) to be cleared in IFR. Writing a 0 to any bit in ICR has no effect. Incoming interrupts have priority and override any write to ICR. You cannot set any bit in ICR to affect NMI or reset. The ISR is shown in Figure 2-7 and described in Table 2-11. See Chapter 5 for more information on interrupts.

NOTE: Any write to ICR (by the MVC instruction) effectively has one delay slot because the results cannot be read (by the MVC instruction) in IFR until two cycles after the write to ICR.

Any write to ICR is ignored by a simultaneous write to the same bit in the interrupt set register (ISR).

Figure 2-7. Interrupt Clear Register (ICR)



LEGEND: R = Read only; W = Writeable by the **MVC** instruction; -n = value after reset

Table 2-11. Interrupt Clear Register (ICR) Field Descriptions

Bit	Field	Value	Description
31-16	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
15-4	ICn		Interrupt clear.
		0	Corresponding interrupt flag (IFn) in IFR is not cleared.
		1	Corresponding interrupt flag (IFn) in IFR is cleared.
3-0	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.



Control Register File www.ti.com

2.8.7 Interrupt Enable Register (IER)

The interrupt enable register (IER) enables and disables individual interrupts. The IER is shown in Figure 2-8 and described in Table 2-12.

The IER is not accessible in User mode. See Section 8.2.4.1 for more information. See Chapter 5 for more information on interrupts.

Figure 2-8. Interrupt Enable Register (IER)




Table 2-12. Interrupt Enable Register (IER) Field Descriptions

Bit	Field	Value	Description					
31-16	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.					
15-4	IE <i>n</i>		nterrupt enable. An interrupt triggers interrupt processing only if the corresponding bit is set to 1.					
		0	Interrupt is disabled.					
		1	Interrupt is enabled.					
3-2	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.					
1	NMIE		Nonmaskable interrupt enable. An interrupt triggers interrupt processing only if the bit is set to 1.					
			The NMIE bit is cleared at reset. After reset, you must set the NMIE bit to enable the NMI and to allow INT15-INT4 to be enabled by the GIE bit in CSR and the corresponding IER bit. You cannot manually clear the NMIE bit; a write of 0 has no effect. The NMIE bit is also cleared by the occurrence of an NMI.					
		0	All nonreset interrupts are disabled.					
		1	All nonreset interrupts are enabled. The NMIE bit is set only by completing a B NRP instruction or by a write of 1 to the NMIE bit.					
0	1	1	Reset interrupt enable. You cannot disable the reset interrupt.					



www.ti.com Control Register File

2.8.8 Interrupt Flag Register (IFR)

The interrupt flag register (IFR) contains the status of INT4-INT15 and NMI interrupt. Each corresponding bit in the IFR is set to 1 when that interrupt occurs; otherwise, the bits are cleared to 0. If you want to check the status of interrupts, use the **MVC** instruction to read the IFR. (See the **MVC** instruction description (see MVC) for information on how to use this instruction.) The IFR is shown in Figure 2-9 and described in Table 2-13. See Chapter 5 for more information on interrupts.

Figure 2-9. Interrupt Flag Register (IFR)

31															16
							Rese	erved							
							R	-0							
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
IF15	IF14	IF13	IF12	IF11	IF10	IF9	IF8	IF7	IF6	IF5	IF4	Rese	erved	NMIF	0
R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0	R	-0	R-0	R-0

LEGEND: R = Readable by the **MVC** instruction; -n = value after reset

Table 2-13. Interrupt Flag Register (IFR) Field Descriptions

Bit	Field	Value	Description
31-16	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
15-4	IF <i>n</i>		Interrupt flag. Indicates the status of the corresponding maskable interrupt. An interrupt flag may be manually set by setting the corresponding bit (ISn) in the interrupt set register (ISR) or manually cleared by setting the corresponding bit (ICn) in the interrupt clear register (ICR).
		0	Interrupt has not occurred.
		1	Interrupt has occurred.
3-2	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
1	NMIF		Nonmaskable interrupt flag.
		0	Interrupt has not occurred.
		1	Interrupt has occurred.
0	0	0	Reset interrupt flag.

2.8.9 Interrupt Return Pointer Register (IRP)

The interrupt return pointer register (IRP) contains the return pointer that directs the CPU to the proper location to continue program execution after processing a maskable interrupt. A branch using the address in IRP (**B IRP**) in your interrupt service routine returns to the program flow when interrupt servicing is complete. The IRP is shown in Figure 2-10.

The IRP contains the 32-bit address of the first execute packet in the program flow that was not executed because of a maskable interrupt. Although you can write a value to IRP, any subsequent interrupt processing may overwrite that value.

See Chapter 5 for more information on interrupts.

Figure 2-10. Interrupt Return Pointer Register (IRP)



LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -x = value is indeterminate after reset



Control Register File www.ti.com


2.8.10 Interrupt Set Register (ISR)

The interrupt set register (ISR) allows you to manually set the maskable interrupts (INT15-INT4) in the interrupt flag register (IFR). Writing a 1 to any of the bits in ISR causes the corresponding interrupt flag (IFn) to be set in IFR. Writing a 0 to any bit in ISR has no effect. You cannot set any bit in ISR to affect NMI or reset. The ISR is shown in Figure 2-11 and described in Table 2-14. See Chapter 5 for more information on interrupts.

NOTE: Any write to ISR (by the MVC instruction) effectively has one delay slot because the results cannot be read (by the MVC instruction) in IFR until two cycles after the write to ISR.

Any write to the interrupt clear register (ICR) is ignored by a simultaneous write to the same bit in ISR.

Figure 2-11. Interrupt Set Register (ISR)



LEGEND: R = Read only; W = Writeable by the **MVC** instruction; -n = value after reset

Table 2-14. Interrupt Set Register (ISR) Field Descriptions

Bit	Field	Value	Description
31-16	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
15-4	ISn		Interrupt set.
		0	Corresponding interrupt flag (IFn) in IFR is not set.
		1	Corresponding interrupt flag (IFn) in IFR is set.
3-0	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.



www.ti.com Control Register File

2.8.11 Interrupt Service Table Pointer Register (ISTP)

The interrupt service table pointer register (ISTP) is used to locate the interrupt service routine (ISR). The ISTB field identifies the base portion of the address of the interrupt service table (IST) and the HPEINT field identifies the specific interrupt and locates the specific fetch packet within the IST. The ISTP is shown in Figure 2-12 and described in Table 2-15. See Section 5.1.2.2 for a discussion of the use of the ISTP.

The ISTP is not accessible in User mode. See Section 8.2.4.1 for more information. See Chapter 5 for more information on interrupts.

31 16 **ISTB** R/W-S 15 10 0 **HPEINT** 0 0 R/W-S R-0 R-0 R-0 R-0 R-0 R-0

Figure 2-12. Interrupt Service Table Pointer Register (ISTP)

LEGEND: R = Readable by the **MVC** instruction; W = Readable by the **MVC** instruction; R = Readable by the **MVC**

Table 2-15. Interrupt Service Table Pointer Register (ISTP) Field Descriptions

Bit	Field	Value	Description
31-10	ISTB	0-3F FFFFh	Interrupt service table base portion of the IST address. This field is cleared to a device-specific default value on reset; therefore, upon startup the IST must reside at this specific address. See the device-specific data manual for more information. After reset, you can relocate the IST by writing a new value to ISTB. If relocated, the first ISFP (corresponding to RESET) is never executed via interrupt processing, because reset clears the ISTB to its default value. See Example 5-1.
9-5	HPEINT	0-1Fh	Highest priority enabled interrupt that is currently pending. This field indicates the number (related bit position in the IFR) of the highest priority interrupt (as defined in Table 5-1) that is enabled by its bit in the IER. Thus, the ISTP can be used for manual branches to the highest priority enabled interrupt. If no interrupt is pending and enabled, HPEINT contains the value 0. The corresponding interrupt need not be enabled by NMIE (unless it is NMI) or by GIE.
4-0	0	0	Cleared to 0 (fetch packets must be aligned on 8-word (32-byte) boundaries).

2.8.12 Nonmaskable Interrupt (NMI) Return Pointer Register (NRP)

The NMI return pointer register (NRP) contains the return pointer that directs the CPU to the proper location to continue program execution after NMI processing. A branch using the address in NRP (**B NRP**) in your interrupt service routine returns to the program flow when NMI servicing is complete. The NRP is shown in Figure 2-13.

The NRP contains the 32-bit address of the first execute packet in the program flow that was not executed because of a nonmaskable interrupt. Although you can write a value to NRP, any subsequent interrupt processing may overwrite that value.

See Chapter 5 for more information on interrupts. See Chapter 6 for more information on exceptions.

Figure 2-13. NMI Return Pointer Register (NRP)




LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -x = value is indeterminate after reset



2.8.13 E1 Phase Program Counter (PCE1)

The E1 phase program counter (PCE1), shown in Figure 2-14, contains the 32-bit address of the fetch packet in the E1 pipeline phase.

Figure 2-14. E1 Phase Program Counter (PCE1)



LEGEND: R = Readable by the MVC instruction; -x = value is indeterminate after reset

2.9 Control Register File Extensions

Table 2-16 lists the additional control registers in the DSP.

Table 2-16. Control Register File Extensions

Acronym	Register Name	Section
DIER	Debug interrupt enable register	Section 2.9.1
DNUM	DSP core number register	Section 2.9.2
ECR	Exception clear register	Section 2.9.3
EFR	Exception flag register	Section 2.9.4
GPLYA	GMPY polynomial for A side register	Section 2.9.5
GPLYB	GMPY polynomial for B side register	Section 2.9.6
ERR	Internal exception report register	Section 2.9.7
LC	Inner loop count register	Section 2.9.8
TSR	Interrupt task state register	Section 2.9.9
NTSR	NMI/Exception task state register	Section 2.9.10
REP	Restricted entry point register	Section 2.9.11
RILC	Reload inner loop count register	Section 2.9.12
SSR	Saturation status register	Section 2.9.13
TSCH	Time stamp counter register—high half of 64 bit	Section 2.9.14
TSCL	Time stamp counter register—low half of 64 bit	Section 2.9.14
TSR	Task state register	Section 2.9.15

46 CPU Data Paths and Control SPRUFE8B-July 2010



2.9.1 Debug Interrupt Enable Register (DIER)

The debug interrupt enable register (DIER) is used to designate which interrupts and exceptions are treated as high-priority interrupts when operating in real-time emulation mode. The DIER is shown in Figure 2-15 and described in Table 2-17.

Figure 2-15. Debug Interrupt Enable Register (DIER)

31	30	29													16
NMI	EXCEP							Rese	erved						
R/W-0	R/W-0							R	-0						
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
INT15	INT14	INT13	INT12	INT11	INT10	INT9	INT8	INT7	INT6	INT5	INT4	Rese	rved	WSEL	Rsvd
R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R-	-0	R/W-0	R/W-0
LEGEN	LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; $-n$ = value after reset														

Table 2-17. Debug Interrupt Enable Register (DIER) Field Descriptions


Bit	Field	Value	Description
31	NMI		Nonmaskable interrupt (NMI).
		1	Designate NMI as high-priority interrupt.
30	EXCEP		Maskable external exception (EXCEP).
		1	Designate EXCEP as high-priority interrupt.
29-16	Reserved	0	Reserved
15	INT15		Maskable interrupt 15 (INT15).
		1	Designate INT15 as high-priority interrupt.
14	INT14		Maskable interrupt 14 (INT14).
		1	Designate INT14 as high-priority interrupt.
13	INT13		Maskable interrupt 13 (INT13).
		1	Designate INT13 as high-priority interrupt.
12	INT12		Maskable interrupt 12 (INT12).
		1	Designate INT12 as high-priority interrupt.
11	INT11		Maskable interrupt 11 (INT11).
		1	Designate INT11 as high-priority interrupt.
10	INT10		Maskable interrupt 10 (INT10).
		1	Designate INT10 as high-priority interrupt.
9	INT9		Maskable interrupt 9 (INT9).
		1	Designate INT9 as high-priority interrupt.
8	INT8		Maskable interrupt 8 (INT8).
		1	Designate INT8 as high-priority interrupt.
7	INT7		Maskable interrupt 7 (INT7).
		1	Designate INT7 as high-priority interrupt.
6	INT6		Maskable interrupt 6 (INT6).
		1	Designate INT6 as high-priority interrupt.
5	INT5		Maskable interrupt 5 (INT5).
		1	Designate INT5 as high-priority interrupt.
4	INT4		Maskable interrupt 4 (INT4).
		1	Designate INT4 as high-priority interrupt.
3-2	Reserved	0	Reserved
1	WSEL		Write control select. This bit must be cleared to 0 to modify bits 31-2.
		0	Bits 31-2 can be modified.
0	Reserved	0	Reserved



2.9.2 DSP Core Number Register (DNUM)

Multiple CPUs may be used in a system. The DSP core number register (DNUM), provides an identifier to shared resources in the system which identifies which CPU is accessing those resources. The contents of this register are set to a specific value (depending on the device) at reset. See your device-specific data manual for the reset value of this register. The DNUM is shown in Figure 2-16.

Figure 2-16. DSP Core Number Register (DNUM)



LEGEND: R = Readable by the **MVC** instruction; -n = V value after reset; S = See the device-specific data manual for the default value of this field after reset

2.9.3 Exception Clear Register (ECR)

The exception clear register (ECR) is used to clear individual bits in the exception flag register (EFR). Writing a 1 to any bit in ECR clears the corresponding bit in EFR.

The ECR is not accessible in User mode. See Section 8.2.4.1 for more information. See Chapter 6 for more information on exceptions.

48 CPU Data Paths and Control SPRUFE8B-July 2010




2.9.4 Exception Flag Register (EFR)

The exception flag register (EFR) contains bits that indicate which exceptions have been detected. Clearing the EFR bits is done by writing a 1 to the corresponding bit position in the exception clear register (ECR). Writing a 0 to the bits in this register has no effect. The EFR is shown in Figure 2-17 and described in Table 2-18.

The EFR is not accessible in User mode. See Section 8.2.4.1 for more information. See Chapter 6 for more information on exceptions.

Figure 2-17. Exception Flag Register (EFR)



LEGEND: R = Readable by the **MVC** EFR instruction only in Supervisor mode; W = Clearable by the **MVC** ECR instruction only in Supervisor mode; -n = value after reset

Table 2-18. Exception Flag Register (EFR) Field Descriptions


Bit	Field	Value	Description
31	NXF		NMI exception flag.
		0	NMI exception has not been detected.
		1	NMI exception has been detected.
30	EXF		EXCEP flag.
		0	Exception has not been detected.
		1	Exception has been detected.
29-2	Reserved	0	Reserved. Read as 0.
1	IXF		Internal exception flag.
		0	Internal exception has not been detected.
		1	Internal exception has been detected.
0	SXF		Software exception flag (set by SWE or SWENR instructions).
		0	Software exception has not been detected.
		1	Software exception has been detected.



2.9.5 GMPY Polynomial—A Side Register (GPLYA)

The **GMPY** instruction (see GMPY) uses the 32-bit polynomial in the GMPY polynomial—A side register (GPLYA), Figure 2-18, when the instruction is executed on the M1 unit.

Figure 2-18. GMPY Polynomial A-Side Register (GPLYA)




LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

2.9.6 GMPY Polynomial—B Side Register (GPLYB)

The **GMPY** instruction (see GMPY) uses the 32-bit polynomial in the GMPY polynomial—B side register (GPLYB), Figure 2-19, when the instruction is executed on the M2 unit.

Figure 2-19. GMPY Polynomial B-Side (GPLYB)



LEGEND: R = Readable by the **MVC** instruction; W = Writeable by the **MVC** instruction; -n = value after reset




2.9.7 Internal Exception Report Register (IERR)

The internal exception report register (IERR) contains flags that indicate the cause of the internal exception. In the case of simultaneous internal exceptions, the same flag may be set by different exception sources. In this case, it may not be possible to determine the exact causes of the individual exceptions. The IERR is shown in Figure 2-20 and described in Table 2-19.

The IERR is not accessible in User mode. See Section 8.2.4.1 for more information. See Chapter 6 for more information on exceptions.

Figure 2-20. Internal Exception Report Register (IERR)



LEGEND: R = Readable by the **MVC** instruction only in Supervisor mode; W = Writeable by the **MVC** instruction only in Supervisor mode; -n = Value after reset

Table 2-19. Internal Exception Report Register (IERR) Field Descriptions


Bit	Field	Value	Description
31-9	Reserved	0	Reserved. Read as 0.
8	MSX		Missed stall exception
		0	Missed stall exception is not the cause.
		1	Missed stall exception is the cause.
7	LBX		SPLOOP buffer exception
		0	SPLOOP buffer exception is not the cause.
		1	SPLOOP buffer exception is the cause.
6	PRX		Privilege exception
		0	Privilege exception is not the cause.
		1	Privilege exception is the cause.
5	RAX		Resource access exception
		0	Resource access exception is not the cause.
		1	Resource access exception is the cause.
4	RCX		Resource conflict exception
		0	Resource conflict exception is not the cause.
		1	Resource conflict exception is the cause.
3	OPX		Opcode exception
		0	Opcode exception is not the cause.
		1	Opcode exception is the cause.
2	EPX		Execute packet exception
		0	Execute packet exception is not the cause.
		1	Execute packet exception is the cause.
1	FPX		Fetch packet exception
		0	Fetch packet exception is not the cause.
		1	Fetch packer exception is the cause.
0	IFX		Instruction fetch exception
		0	Instruction fetch exception is not the cause.
		1	Instruction fetch exception is the cause.



2.9.8 SPLOOP Inner Loop Count Register (ILC)

The **SPLOOP** or **SPLOOPD** instructions use the SPLOOP inner loop count register (ILC), Figure 2-21, as the count of the number of iterations left to perform. The ILC content is decremented at each stage boundary until the ILC content reaches 0.

Figure 2-21. Inner Loop Count Register (ILC)



LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

2.9.9 Interrupt Task State Register (ITSR)

The interrupt task state register (ITSR) is used to store the contents of the task state register (TSR) in the event of an interrupt. The ITSR is shown in Figure 2-22 and described in Table 2-20. For detailed bit descriptions, see Section 2.9.15.

The GIE bit in ITSR is physically the same bit as the PGIE bit in CSR.

The ITSR is not accessible in User mode. See Section 8.2.4.1 for more information.

Figure 2-22. Interrupt Task State Register (ITSR)

31															16
							Rese	erved							
							R	-0							
15	14	13		11	10	9	8	7	6	5	4	3	2	1	0
IB	SPLX		Reserved		EXC	INT	Rsvd	C	XM	Rsvd	DBGM	XEN	GEE	SGIE	GIE
R/W-0	R/W-0		R-0		R/W-0	R/W-0	R-0	R/\	N-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0

LEGEND: R = Readable by the **MVC** instruction only in Supervisor mode; W = Writeable by the **MVC** instruction only in Supervisor mode; -n = value after reset

Table 2-20. Interrupt Task State Register (ITSR) Field Descriptions

Bit	Field	Description
31-16	Reserved	Reserved. Read as 0.
15	IB	Interrupt occurred while interrupts were blocked.
14	SPLX	Interrupt occurred during an SPLOOP.
13-11	Reserved	Reserved. Read as 0.
10	EXC	Contains EXC bit value in TSR at point of interrupt.
9	INT	Contains INT bit value in TSR at point of interrupt.
8	Reserved	Reserved. Read as 0.
7-6	CXM	Contains CXM bit value in TSR at point of interrupt.
5	Reserved	Reserved. Read as 0.
4	DBGM	Contains DBGM bit value in TSR at point of interrupt.
3	XEN	Contains XEN bit value in TSR at point of interrupt.
2	GEE	Contains GEE bit value in TSR at point of interrupt.
1	SGIE	Contains SGIE bit value in TSR at point of interrupt.
0	GIE	Contains GIE bit value in TSR at point of interrupt.

52 CPU Data Paths and Control SPRUFE8B-July 2010



2.9.10 NMI/Exception Task State Register (NTSR)

The NMI/exception task state register (NTSR) is used to store the contents of the task state register (TSR) and the conditions under which an exception occurred in the event of a nonmaskable interrupt (NMI) or an exception. The NTSR is shown in Figure 2-23 and described in Table 2-21. For detailed bit descriptions (except for the HWE bit), see Section 2.9.15. The HWE bit is set by taking a hardware exception (NMI, EXCEP, or internal) and is cleared by either **SWE** or **SWENR** instructions.

The NTSR is not accessible in User mode. See Section 8.2.4.1 for more information.

Figure 2-23. NMI/Exception Task State Register (NTSR)

31														17	16
						F	Reserved	l							HWE
							R-0								R/W-0
15	14	13		11	10	9	8	7	6	5	4	3	2	1	0
IB	SPLX		Reserved		EXC	INT	Rsvd	C>	(M	Rsvd	DBGM	XEN	GEE	SGIE	GIE
R/W-0	R/W-0		R-0		R/W-0	R/W-0	R-0	R/V	V-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0

LEGEND: R = Readable by the **MVC** instruction only in Supervisor mode; W = Writeable by the **MVC** instruction only in Supervisor mode; -n = value after reset

Table 2-21. NMI/Exception Task State Register (NTSR) Field Descriptions

Bit	Field	Description
31-17	Reserved	Reserved. Read as 0.
16	HWE	Hardware exception taken (NMI, EXCEP, or internal).
15	IB	Exception occurred while interrupts were blocked.
14	SPLX	Exception occurred during an SPLOOP.
13-11	Reserved	Reserved. Read as 0.
10	EXC	Contains EXC bit value in TSR at point exception taken.
9	INT	Contains INT bit value in TSR at point exception taken.
8	Reserved	Reserved. Read as 0.
7-6	CXM	Contains CXM bit value in TSR at point exception taken.
5	Reserved	Reserved. Read as 0.
4	DBGM	Contains DBGM bit value in TSR at point exception taken.
3	XEN	Contains XEN bit value in TSR at point exception taken.
2	GEE	Contains GEE bit value in TSR at point exception taken.
1	SGIE	Contains SGIE bit value in TSR at point exception taken.
0	GIE	Contains GIE bit value in TSR at point exception taken.

2.9.11 Restricted Entry Point Register (REP)

The restricted entry point register (REP) is used by the **SWENR** instruction as the target of the change of control when an **SWENR** instruction is issued. The contents of REP should be preinitialized by the processor in Supervisor mode before any **SWENR** instruction is issued. See Section 8.2.4.1 for more information. REP cannot be modified in User mode.



2.9.12 SPLOOP Reload Inner Loop Count Register (RILC)

Predicated **SPLOOP** or **SPLOOPD** instructions used in conjunction with a **SPMASKR** or **SPKERNELR** instruction use the SPLOOP reload inner loop count register (RILC), Figure 2-24, as the iteration count value to be written to the SPLOOP inner loop count register (ILC) in the cycle before the reload operation begins. See Chapter 7 for more information.

Figure 2-24. Reload Inner Loop Count Register (RILC)

31 0
32-bit inner loop count reload

R/W-0

LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset


2.9.13 Saturation Status Register (SSR)

The saturation status register (SSR) provides saturation flags for each functional unit, making it possible for the program to distinguish between saturations caused by different instructions in the same execute packet. There is no direct connection to the SAT bit in the control status register (CSR); writes to the SAT bit have no effect on SSR and writes to SSR have no effect on the SAT bit. Care must be taken when restoring SSR and the SAT bit when returning from a context switch. Since the SAT bit cannot be written to a value of 1 using the **MVC** instruction, restoring the SAT bit to a 1 must be done by executing an instruction that results in saturation. The saturating instruction would affect SSR; therefore, SSR must be restored after the SAT bit has been restored. The SSR is shown in Figure 2-25 and described in Table 2-22.

Instructions resulting in saturation set the appropriate unit flag in SSR in the cycle following the writing of the result to the register file. The setting of the flag from a functional unit takes precedence over a write to the bit from an **MVC** instruction. If no functional unit saturation has occurred, the flags may be set to 0 or 1 by the **MVC** instruction, unlike the SAT bit in CSR.

The bits in SSR can be set by the **MVC** instruction or by a saturation in the associated functional unit. The bits are cleared only by a reset or by the **MVC** instruction. The bits are not cleared by the occurrence of a nonsaturating instruction.

Figure 2-25. Saturation Status Register (SSR)



LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

Table 2-22. Saturation Status Register Field Descriptions

Bit	Field	Value	Description
31-6	Reserved	0	Reserved. Read as 0.
5	M2		M2 unit.
		0	Saturation did not occur on M2 unit.
		1	Saturation occurred on M2 unit.
4	M1		M1 unit.
		0	Saturation did not occur on M1 unit.
		1	Saturation occurred on M1 unit.

54 CPU Data Paths and Control SPRUFE8B-July 2010



Table 2-22. Saturation Status Register Field Descriptions (continued)

Bit	Field	Value	Description
3	S2		S2 unit.
		0	Saturation did not occur on S2 unit.
		1	Saturation occurred on S2 unit.
2	S1		S1 unit.
		0	Saturation did not occur on S1 unit.
		1	Saturation occurred on S1 unit.
1	L2		L2 unit.
		0	Saturation did not occur on L2 unit.
		1	Saturation occurred on L2 unit.
0	L1		L1 unit.
		0	Saturation did not occur on L1 unit.
		1	Saturation occurred on L1 unit.

2.9.14 Time Stamp Counter Registers (TSCL and TSCH)

The CPU contains a free running 64-bit counter that advances each CPU clock under normal operation. The counter is accessed as two 32-bit read-only control registers, TSCL (Figure 2-26) and TSCH (Figure 2-27).


Figure 2-26. Time Stamp Counter Register - Low Half (TSCL)



R-

LEGEND: R = Readable by the **MVC** instruction; -n = value after reset

Figure 2-27. Time Stamp Counter Register - High Half (TSCH)



LEGEND: R = Readable by the **MVC** instruction; -n = value after reset



2.9.14.1 Initialization

The counter is cleared to 0 after reset, and counting is disabled.

2.9.14.2 Enabling Counting

The counter is enabled by writing to TSCL. The value written is ignored. Counting begins in the cycle after the **MVC** instruction executes. If executed with the count disabled, the following code sequence shows the timing of the count starting (assuming no stalls occur in the three cycles shown).

```
MVC B0,TSCL; Start TSC
MVC TSCL,B0; B0 = 0
MVC TSCL,B1; B1 = 1
```

2.9.14.3 Disabling Counting

Once enabled, counting cannot be disabled under program control. Counting is disabled in the following cases:

- After exiting the reset state.
- · When the CPU is fully powered down.

2.9.14.4 Reading the Counter

Reading the full 64-bit count takes two sequential **MVC** instructions. A read from TSCL causes the upper 32 bits of the count to be copied into TSCH. In normal operation, only this snapshot of the upper half of the 64-bit count is available to the programmer. The value read will always be the value copied at the cycle of the last MVC TSCL, *reg* instruction. If it is read with no TSCL reads having taken place since reset, then the reset value of 0 is read.

CAUTION

Reading TSCL in the cycle before a cross path stall may give an inaccurate value in TSCH.

When reading the full 64-bit value, it must be ensured that no interrupts are serviced between the two **MVC** instructions if an ISR is allowed to make use of the time stamp counter. There is no way for an ISR to restore the previous value of TSCH (snapshot) if it reads TSCL, since a new snapshot is performed.

Two methods for reading the 64-bit count value in an uninterruptible manner are shown in Example 2-1 and Example 2-2. Example 2-1 uses the fact that interrupts are automatically disabled in the delay slots of a branch to prevent an interrupt from happening between the TSCL read and the TSCH read. Example 2-2 accomplishes the same task by explicitly disabling interrupts.

Example 2-1. Code to Read the 64-Bit TSC Value in Branch Delay Slot

```
BNOP TSC_Read_Done, 3

MVC TSCL,B0 ; Read the low half first; high half copied to TSCH

MVC TSCH,B1 ; Read the snapshot of the high half

TSC_Read_Done:
```

Example 2-2. Code to Read the 64-Bit TSC Value Using DINT/RINT

```
DINT
|| MVC TSCL,B0 ; Read the low half first; high half copied to TSCH
RINT
|| MVC TSCH,B1 ; Read the snapshot of the high half
TSC_Read_Done:
```

56 CPU Data Paths and Control SPRUFE8B-July 2010




2.9.15 Task State Register (TSR)

The task state register (TSR) contains all of the status bits that determine or indicate the current execution environment. TSR is saved in the event of an interrupt or exception to the ITSR or NTSR, respectively. All bits are readable by the **MVC** instruction. The TSR is shown in Figure 2-28 and described in Table 2-23. The SGIE bit in TSR is used by the **DINT** and **RINT** instructions to globally disable and reenable interrupts.

The GIE and SGIE bits may be written in both User mode and Supervisor mode. The remaining bits all have restrictions on how they are written. See Section 8.2.4.2 for more information.

The GIE bit in TSR is physically the same bit as the GIE bit in CSR. It is retained in CSR for compatibility reasons, but placed in TSR so that it will be copied in the event of either an exception or an interrupt.

Figure 2-28. Task State Register (TSR)



LEGEND: R = Readable by the **MVC** instruction; W = Writeable in Supervisor mode; C = Clearable in Supervisor mode; S = Can be set in Supervisor mode;

Table 2-23. Task State Register (TSR) Field Descriptions

Bit	Field	Value	Description
31-16	Reserved	0	Reserved. Read as 0.
15	IB		Interrupts blocked. Not writable by the MVC instruction; set only by hardware.
		0	Interrupts not blocked in previous cycle (interruptible point).
		1	Interrupts were blocked in previous cycle.
14	SPLX		SPLOOP executing. Not writable by the MVC instruction; set only by hardware.
		0	Not currently executing SPLOOP
		1	Currently executing SPLOOP
13-11	Reserved	0	Reserved. Read as 0.
10	EXC		Exception processing. Clearable by the MVC instruction in Supervisor mode. Not clearable by the MVC instruction in User mode.
		0	Not currently processing an exception.
		1	Currently processing an exception.
9	INT		Interrupt processing. Not writable by the MVC instruction.
		0	Not currently processing an interrupt.
		1	Currently processing an interrupt.
8	Reserved	0	Reserved. Read as 0.
7-6	СХМ	0-3h	Current execution mode. Not writable by the MVC instruction; these bits reflect the current execution mode of the execute pipeline. CXM is set to 1 when you begin executing the first instruction in User mode. See Chapter 8 for more information.
		0	Supervisor mode
		1h	User mode
		2h-3h	Reserved (an attempt to set these values is ignored)
5	Reserved	0	Reserved. Read as 0.
4	DBGM		Emulator debug mask. Writable in Supervisor and User mode. Writable by emulator.
		0	Enables emulator capabilities.
		1	Disables emulator capabilities.



Table 2-23. Task State Register (TSR) Field Descriptions (continued)

Bit	Field	Value	Description
3	XEN		Maskable exception enable. Writable only in Supervisor mode.
		0	Disables all maskable exceptions.
		1	Enables all maskable exceptions.
2	GEE		Global exception enable. Can be set to 1 only in Supervisor mode. Once set, cannot be cleared except by reset.
		0	Disables all exceptions except the reset interrupt.
		1	Enables all exceptions.
1	SGIE		Saved global interrupt enable. Contains previous state of GIE bit after execution of a DINT instruction. Writable in Supervisor and User mode.
		0	Global interrupts remain disabled by the RINT instruction.
		1	Global interrupts are enabled by the RINT instruction.
0	GIE		Global interrupt enable. Same physical bit as the GIE bit in the control status register (CSR). Writable in Supervisor and User mode. See Section 5.2 for details on how the GIE bit affects interruptibility.
		0	Disables all interrupts except the reset interrupt and NMI (nonmaskable interrupt).
		1	Enables all interrupts.

2.10 Control Register File Extensions for Floating-Point Operations

The C674x DSP has three additional configuration registers to support floating-point operations. The registers specify the desired floating-point rounding mode for the .L and .M units. They also contain fields to warn if *src1* and *src2* are NaN or denormalized numbers, and if the result overflows, underflows, is inexact, infinite, or invalid. There are also fields to warn if a divide by 0 was performed, or if a compare was attempted with a NaN source. Table 2-24 lists the additional registers used. The OVER, UNDER, INEX, INVAL, DENn, NANn, INFO, UNORD and DIV0 bits within these registers will not be modified by a conditional instruction whose condition is false.

Table 2-24. Control Register File Extensions for Floating-Point Operations

Acronym	Register Name	Section
FADCR	Floating-point adder configuration register	Section 2.10.1
FAUCR	Floating-point auxiliary configuration register	Section 2.10.2
FMCR	Floating-point multiplier configuration register	Section 2.10.3



2.10.1 Floating-Point Adder Configuration Register (FADCR)

The floating-point adder configuration register (FADCR) contains fields that specify underflow or overflow, the rounding mode, NaNs, denormalized numbers, and inexact results for instructions that use the .L. functional units. FADCR has a set of fields specific to each of the .L units: .L2 uses bits 31-16 and .L1 uses bits 15-0. FADCR is shown in Figure 2-29 and described in Table 2-25.

NOTE: The ADDSP, ADDDP, SUBSP, and SUBDP instructions executing in the .S functional unit use the rounding mode from and set the warning bits in FADCR. The warning bits in FADCR are the logical-OR of the warnings produced on the .L functional unit and the warnings produced by the ADDSP/ADDDP/SUBSP/SUBDP instructions on the .S functional unit (but not other instructions executing on the .S functional unit).

Figure 2-29. Floating-Point Adder Configuration Register (FADCR)

31		27	26	25	24	23	22	21	20	19	18	17	16
	Reserved		RMC	DDE	UNDER	INEX	OVER	INFO	INVAL	DEN2	DEN1	NAN2	NAN1
	R-0		R/V	V-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
15		11	10	9	8	7	6	5	4	3	2	1	0
15	Reserved	11	10 RMC		8 UNDER	7 INEX	6 OVER	5 INFO	4 INVAL	3 DEN2	2 DEN1	1 NAN2	0 NAN1

LEGEND: R = Readable by the **MVC** instruction; W = Writeable by the **MVC** instruction; -n = value after reset

Table 2-25. Floating-Point Adder Configuration Register (FADCR) Field Descriptions

Bit	Field	Value	Description
31-27	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
26-25	RMODE	0-3h	Rounding mode select for .L2.
		0	Round toward nearest representable floating-point number
		1h	Round toward 0 (truncate)
		2h	Round toward infinity (round up)
		3h	Round toward negative infinity (round down)
24	UNDER		Result underflow status for .L2.
		0	Result does not underflow.
		1	Result underflows.
23	INEX		Inexact results status for .L2.
		0	
		1	Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL.
22	OVER		Result overflow status for .L2.
		0	Result does not overflow.
		1	Result overflows.
21	INFO		Signed infinity for .L2.
		0	Result is not signed infinity.
		1	Result is signed infinity.
20	INVAL		
		0	A signed NaN (SNaN) is not a source.
		1	A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity.
19	DEN2		Denormalized number select for .L2 src2.
		0	src2 is not a denormalized number.
		1	src2 is a denormalized number.



Table 2-25. Floating-Point Adder Configuration Register (FADCR) Field Descriptions (continued)

Bit	Field	Value	Description
18	DEN1		Denormalized number select for .L2 src1.
		0	src1 is not a denormalized number.
		1	src1 is a denormalized number.
17	NAN2		NaN select for .L2 src2.
		0	src2 is not NaN.
		1	src2 is NaN.
16	NAN1		NaN select for .L2 src1.
		0	src1 is not NaN.
		1	src1 is NaN.
15-11	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
10-9	RMODE	0-3h	Rounding mode select for .L1.
		0	Round toward nearest representable floating-point number
		1h	Round toward 0 (truncate)
		2h	Round toward infinity (round up)
		3h	Round toward negative infinity (round down)
8	UNDER		Result underflow status for .L1.
		0	Result does not underflow.
		1	Result underflows.
7	INEX		Inexact results status for .L1.
		0	
		1	Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL.
6	OVER		Result overflow status for .L1.
		0	Result does not overflow.
		1	Result overflows.
5	INFO		Signed infinity for .L1.
		0	Result is not signed infinity.
		1	Result is signed infinity.
4	INVAL		
		0	A signed NaN (SNaN) is not a source.
		1	A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity.
3	DEN2		Denormalized number select for .L1 src2.
		0	src2 is not a denormalized number.
		1	src2 is a denormalized number.
2	DEN1		Denormalized number select for .L1 src1.
		0	src1 is not a denormalized number.
		1	src1 is a denormalized number.
1	NAN2		NaN select for .L1 src2.
		0	src2 is not NaN.
		1	src2 is NaN.
0	NAN1		NaN select for .L1 src1.
		0	src1 is not NaN.
		1	src1 is NaN.



2.10.2 Floating-Point Auxiliary Configuration Register (FAUCR)

The floating-point auxiliary register (FAUCR) contains fields that specify underflow or overflow, the rounding mode, NaNs, denormalized numbers, and inexact results for instructions that use the .S functional units. FAUCR has a set of fields specific to each of the .S units: .S2 uses bits 31-16 and .S1 uses bits 15-0. FAUCR is shown in Figure 2-30 and described in Table 2-26.

NOTE: The ADDSP, ADDDP, SUBSP, and SUBDP instructions executing in the .S functional unit use the rounding mode from and set the warning bits in the floating-point adder configuration register (FADCR). The warning bits in FADCR are the logical-OR of the warnings produced on the .L functional unit and the warnings produced by the ADDSP/ADDDP/SUBSP/SUBDP instructions on the .S functional unit (but not other instructions executing on the .S functional unit).

Figure 2-30. Floating-Point Auxiliary Configuration Register (FAUCR)

31		27	26	25	24	23	22	21	20	19	18	17	16
	Reserved		DIV0	UNORD	UND	INEX	OVER	INFO	INVAL	DEN2	DEN1	NAN2	NAN1
	R-0		R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
15		11	10	9	8	7	6	5	4	3	2	1	0
15	Reserved	11	10 DIV0	9 UNORD	8 UND	7 INEX	6 OVER	5 INFO	4 INVAL	3 DEN2	2 DEN1	1 NAN2	0 NAN1

LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

Table 2-26. Floating-Point Auxiliary Configuration Register (FAUCR) Field Descriptions

Bit	Field	Value	Description
31-27	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
26	DIV0		Source to reciprocal operation for .S2.
		0	0 is not source to reciprocal operation.
		1	0 is source to reciprocal operation.
25	UNORD		Source to a compare operation for .S2
		0	NaN is not a source to a compare operation.
		1	NaN is a source to a compare operation.
24	UND		Result underflow status for .S2.
		0	Result does not underflow.
		1	Result underflows.
23	INEX		Inexact results status for .S2.
		0	
		1	Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL.
22	OVER		Result overflow status for .S2.
		0	Result does not overflow.
		1	Result overflows.
21	INFO		Signed infinity for .S2.
		0	Result is not signed infinity.
		1	Result is signed infinity.
20	INVAL		
		0	A signed NaN (SNaN) is not a source.
		1	A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity.



Table 2-26. Floating-Point Auxiliary Configuration Register (FAUCR) Field Descriptions (continued)

Bit	Field	Value	Description
19	DEN2		Denormalized number select for .S2 src2.
		0	src2 is not a denormalized number.
		1	src2 is a denormalized number.
18	DEN1		Denormalized number select for .S2 src1.
		0	src1 is not a denormalized number.
		1	src1 is a denormalized number.
17	NAN2		NaN select for .S2 src2.
		0	src2 is not NaN.
		1	src2 is NaN.
16	NAN1		NaN select for .S2 src1.
		0	src1 is not NaN.
		1	src1 is NaN.
15-11	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
10	DIV0		Source to reciprocal operation for .S1.
		0	0 is not source to reciprocal operation.
		1	0 is source to reciprocal operation.
9	UNORD		Source to a compare operation for .S1
		0	NaN is not a source to a compare operation.
		1	NaN is a source to a compare operation.
8	UND		Result underflow status for .S1.
		0	Result does not underflow.
		1	Result underflows.
7	INEX		Inexact results status for .S1.
		0	
		1	Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL.
6	OVER		Result overflow status for .S1.
		0	Result does not overflow.
		1	Result overflows.
5	INFO		Signed infinity for .S1.
		0	Result is not signed infinity.
		1	Result is signed infinity.
4	INVAL		
		0	A signed NaN (SNaN) is not a source.
		1	A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity.
3	DEN2		Denormalized number select for .S1 src2.
		0	src2 is not a denormalized number.
		1	src2 is a denormalized number.
2	DEN1		Denormalized number select for .S1 src1.
		0	src1 is not a denormalized number.
		1	src1 is a denormalized number.
1	NAN2		NaN select for .S1 src2.
		0	src2 is not NaN.
		1	src2 is NaN.
0	NAN1		NaN select for .S1 src1.
		0	src1 is not NaN.
		1	src1 is NaN.



2.10.3 Floating-Point Multiplier Configuration Register (FMCR)

The floating-point multiplier configuration register (FMCR) contains fields that specify underflow or overflow, the rounding mode, NaNs, denormalized numbers, and inexact results for instructions that use the .M functional units. FMCR has a set of fields specific to each of the .M units: .M2 uses bits 31-16 and .M1 uses bits 15-0. FMCR is shown in Figure 2-31 and described in Table 2-27.

Figure 2-31. Floating-Point Multiplier Configuration Register (FMCR)

31		27	26	25	24	23	22	21	20	19	18	17	16
	Reserved		RMO	DDE	UNDER	INEX	OVER	INFO	INVAL	DEN2	DEN1	NAN2	NAN1
	R-0		R/V	V-0	R/W-0								
15		11	10	9	8	7	6	5	4	3	2	1	0
	Reserved		RMO	DDE	UNDER	INEX	OVER	INFO	INVAL	DEN2	DEN1	NAN2	NAN1
	R-0		R/V	V-0	R/W-0								

LEGEND: R = Readable by the MVC instruction; W = Writeable by the MVC instruction; -n = value after reset

Table 2-27. Floating-Point Multiplier Configuration Register (FMCR) Field Descriptions

Bit	Field	Value	Description
31-27	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
26-25	RMODE	0-3h	Rounding mode select for .M2.
		0	Round toward nearest representable floating-point number
		1h	Round toward 0 (truncate)
		2h	Round toward infinity (round up)
		3h	Round toward negative infinity (round down)
24	UNDER		Result underflow status for .M2.
		0	Result does not underflow.
		1	Result underflows.
23	INEX		Inexact results status for .M2.
		0	
		1	Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL.
22	OVER		Result overflow status for .M2.
		0	Result does not overflow.
		1	Result overflows.
21	INFO		Signed infinity for .M2.
		0	Result is not signed infinity.
		1	Result is signed infinity.
20	INVAL		
		0	A signed NaN (SNaN) is not a source.
		1	A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity.
19	DEN2		Denormalized number select for .M2 src2.
		0	src2 is not a denormalized number.
		1	src2 is a denormalized number.
18	DEN1		Denormalized number select for .M2 src1.
		0	src1 is not a denormalized number.
		1	src1 is a denormalized number.
17	NAN2		NaN select for .M2 src2.
		0	src2 is not NaN.
		1	src2 is NaN.



Table 2-27. Floating-Point Multiplier Configuration Register (FMCR) Field Descriptions (continued)

16	Bit	Field	Value	Description
1 sro1 is NaN. 15-11 Reserved 0 Reserved. The reserved bit location is always read as 0. A value written to this field has no effect. 10-9 RMODE 0-3h Rounding mode select for .M1. 0 Round toward onearest representable floating-point number 1 Round toward onearest representable floating-point number 2 Round toward onearest representable floating-point number 3 Round toward nearest representable floating-point number 3 Round toward nearest representable floating-point number 4 Round toward nearest representable floating-point number 8 Round toward nearest representable floating-point number 9 Round toward nearest representable floating-point number 1 Result doward nearest representable floating-point number 1 Result underflow status for .M1. 1 Result underflows. 1 Result underflows. 1 Result underflows. 1 Result does not underflow. 1 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. 1 Result overflows. 1 Result overflows. 1 Result overflows. 1 Result overflows. 1 Result is signed infinity. 2 Result is signed infinity. 3 Result is signed infinity. 4 INVAL 4 INVAL 5 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is not a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 5 DEN1 6 Denormalized number select for .M1 src2. 5 src2 is not a denormalized number. 1 src2 is a denormalized number. 1 src2 is a denormalized number. 1 src2 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 1 src2 is not NaN. 2 src2 is not NaN. 3 src2 is not NaN. 3 NaN select for .M1 src2. 4 src2 is not NaN. 4 NaN select for .M1 src2. 5 src2 is not NaN. 5 src3 is not NaN.	16	NAN1		NaN select for .M2 src1.
15-11 Reserved 0 Reserved. The reserved bit location is always read as 0. A value written to this field has no effect. 10-9 RMODE 0-3h Rounding mode select for .M1. 0 Round toward nearest representable floating-point number 1 h Round toward 0 (truncate) 2 h Round toward of initity (round up) 3 h Round toward of initity (round down) 8 UNDER Result underflow status for .M1. 0 Result does not underflow. 1 Result does not underflow. 1 Result overflows. 1 Inexact results status for .M1. 0 Result overflows. 1 Result overflow status for .M1. 0 Result overflow. 1 Result overflow. 1 Result overflow. 1 Result overflow. 1 Result is signed infinity. 4 INVAL 4 INVAL 5 JERN2 6 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 2 DEN2 6 Denormalized number select for .M1 src2. 5 src2 is a denormalized number. 5 src1 is a denormalized number. 6 NAN1 7 NAN2 7 NAN select for .M1 src2. 7 Src2 is not a denormalized number. 8 NAN2 8 NAN select for .M1 src2. 8 Src2 is not NaN. 8 NaN select for .M1 src2. 8 Src2 is not NaN. 8 NaN select for .M1 src2. 8 NAN1 8 NAN2 8 NAN select for .M1 src2. 8 NAN1 8 NAN2 8 NAN select for .M1 src2. 8 NAN1 8 NAN2 8 NAN select for .M1 src2. 8 NAN2 8 NAN3 8 NAN4 8 NAN4 8 NAN5 8 NAN			0	src1 is not NaN.
10-9 RMODE			1	src1 is NaN.
Round toward nearest representable floating-point number	15-11	Reserved	0	Reserved. The reserved bit location is always read as 0. A value written to this field has no effect.
1 h Round toward 0 (truncate) 2 h Round toward infinity (round up) 3 h Round toward infinity (round up) 3 h Round toward infinity (round down) 8 UNDER Result underflow status for .M1. 0 Result underflows. 1 INEX Inexact results status for .M1. 0 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. 0 Result overflow status for .M1. 0 Result overflows. 1 Result overflows. 5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is not signed infinity. 1 Result is signed infinity. 1 Result is signed infinity. 1 Result is signed infinity. 2 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 3 rc2 is not a denormalized number. 4 Denormalized number select for .M1 src1. 5 src1 is a denormalized number. 5 src1 is not a denormalized number. 6 NAN1 NAN2 NaN select for .M1 src2. 7 NaN select for .M1 src2. 8 NaN select for .M1 src1. 8 NaNs select for .M1 src1.	10-9	RMODE	0-3h	Rounding mode select for .M1.
2h Round toward infinity (round up) 3h Round toward negative infinity (round down) Result underflow status for .M1. Result does not underflow. 1 Result does not underflow. 1 INEX Inexact results status for .M1. 0 Inexact results status for .M1. 0 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. Result overflow status for .M1. 0 Result overflow status for .M1. 0 Result overflows. 5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is signed infinity. 4 INVAL A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 2 DEN2 Denormalized number select for .M1 src2. src2 is not a denormalized number. 1 src2 is a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. src1 is not NaN. NaN select for .M1 src1. src1 is not NaN.			0	Round toward nearest representable floating-point number
Sharper Result underflow status for .M1.			1h	Round toward 0 (truncate)
8 UNDER Result underflow status for .M1. 0 Result does not underflow. 1 Result underflows. 1 INEX Inexact results status for .M1. 0 Result does not underflow. 1 Result overflows. 1 Result overflow status for .M1. 0 Result overflow status for .M1. 0 Result overflows. 5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is signed infinity. 1 Result is signed infinity. 4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is not a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 0 src2 is not a denormalized number. 1 src2 is a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. 3 src1 is not a denormalized number. 1 src1 is a denormalized number. 1 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 0 src3 is not NaN. NaN select for .M1 src1. 0 src1 is not NaN. NaN select for .M1 src1.			2h	Round toward infinity (round up)
Result does not underflow. 1 Result underflows. 1 Result underflows. 1 Result underflows. 1 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. 1 Result does not overflow. 1 Result overflows. 1 Result overflows. 1 Result overflows. 1 Result is not signed infinity for. M1. 0 Result is not signed infinity. 1 Result is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 1 Src2 is a denormalized number. 1 Src2 is a denormalized number. 1 Src2 is a denormalized number. 1 Src1 is a denormalized number. 1 Src2 is not NaN. 1 Src2 is not NaN. 1 Src2 is not NaN. 1 Src2 is NaN. 1 Src2 is NaN. 1 Src2 is NaN. 1 Src1 is not NaN. 1 Src2 is not NaN. 1 Src1 is not NaN. 1 Src1 is not NaN. 1 Src2			3h	Round toward negative infinity (round down)
1 Result underflows. 7 INEX INEX Inexact results status for .M1. 0 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. 6 OVER Result overflow status for .M1. 0 Result does not overflow. 1 Result overflows. 5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is signed infinity. 4 INVAL 0 A signed Nan (SNaN) is not a source. 1 A signed Nan (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 0 src2 is not a denormalized number. 1 src1 is a denormalized number. 1 Denormalized number. 1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN. NaN select for .M1 src1. 5 src2 is not NaN.	8	UNDER		Result underflow status for .M1.
INEX			0	Result does not underflow.
Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. Result overflow status for .M1.			1	Result underflows.
1 Result differs from what would have been computed had the exponent range and precision been unbounded; never set with INVAL. Result overflow status for .M1. Result does not overflow. 1 Result overflows. Signed infinity for .M1. Result is not signed infinity. A signed NaN (SNaN) is not a source. A signed NaN (SNaN) is not a source. A signed NaN (SNaN) is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. DEN2 Denormalized number select for .M1 src2. src2 is not a denormalized number. src1 is a denormalized number. Denormalized number. src1 is a denormalized number. NAN2 NaN select for .M1 src2. NaN select for .M1 src2. src2 is not NaN. NaN select for .M1 src1. src1 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1.	7	INEX		Inexact results status for .M1.
unbounded; never set with INVAL. Result overflow status for .M1. Result does not overflow. Result overflows. Signed infinity for .M1. Result is not signed infinity. A signed NaN (SNaN) is not a source. A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. DEN2 Denormalized number select for .M1 src2. src2 is not a denormalized number. DEN1 Denormalized number select for .M1 src1. src1 is a denormalized number. 1 src1 is a denormalized number. NAN2 NaN select for .M1 src2. src2 is not NaN. NaN select for .M1 src1. src1 is not NaN. NaN select for .M1 src1. src2 is NaN. NaN select for .M1 src1.			0	
Result overflow status for .M1. Result overflow. Result overflow. Result overflows. Signed infinity for .M1. Result is not signed infinity. Result is signed infinity. A signed NaN (SNaN) is not a source. A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. Denormalized number select for .M1 src2. src2 is not a denormalized number. Denormalized number. Denormalized number. Denormalized number. Denormalized number. NaN2 NaN select for .M1 src2. src2 is not NaN. src2 is not NaN. NaN select for .M1 src2. src2 is not NaN. NaN select for .M1 src2. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN.			1	
0 Result does not overflow. 1 Result overflows. 5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is signed infinity. 4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 0 src2 is not a denormalized number. 1 src2 is a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. src1 is not a denormalized number. 1 src1 is a denormalized number. 1 src1 is a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. 0 NAN1 NaN select for .M1 src1.				unbounded; never set with INVAL.
1 Result overflows. Signed infinity for .M1. Result is not signed infinity. Result is signed infinity. INVAL A signed NaN (SNaN) is not a source. A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. Denormalized number select for .M1 src2. src2 is not a denormalized number. src2 is a denormalized number. Denormalized number select for .M1 src1. src1 is not a denormalized number. NAN2 NaN select for .M1 src2. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1. src2 is not NaN. NaN select for .M1 src1. src1 is not NaN.	6	OVER		Result overflow status for .M1.
5 INFO Signed infinity for .M1. 0 Result is not signed infinity. 1 Result is signed infinity. 4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 5 src2 is not a denormalized number. 1 src2 is a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. 5 src1 is not a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 5 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 5 src1 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 5 src1 is not NaN.			0	Result does not overflow.
0 Result is not signed infinity. 1 Result is signed infinity. 4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 0 src2 is not a denormalized number. 1 src1 is not a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. src1 is not a denormalized number. 1 src1 is a denormalized number. NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. 0 NAN1 NaN select for .M1 src1. 0 src1 is not NaN.			1	Result overflows.
1 Result is signed infinity. 4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. src2 is not a denormalized number. 1 src2 is a denormalized number. Denormalized number select for .M1 src1. src1 is not a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. src2 is not NaN. 1 src2 is NaN. 0 NAN1 NaN select for .M1 src1. src1 is not NaN.	5	INFO		Signed infinity for .M1.
4 INVAL 0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 0 src2 is not a denormalized number. 1 src2 is a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. src1 is not a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. src1 is not NaN.			0	Result is not signed infinity.
0 A signed NaN (SNaN) is not a source. 1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 5 src2 is not a denormalized number. 1 src2 is a denormalized number. Denormalized number select for .M1 src1. 5 src1 is not a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 5 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 5 src1 is not NaN. 1 src2 is not NaN. NaN select for .M1 src1. 0 src1 is not NaN.			1	Result is signed infinity.
1 A signed NaN (SNaN) is a source. NaN is a source in a floating-point to integer conversion or when infinity is subtracted from infinity. 3 DEN2 Denormalized number select for .M1 src2. 5 src2 is not a denormalized number. 1 src2 is a denormalized number. Denormalized number select for .M1 src1. 5 src1 is not a denormalized number. 1 src1 is a denormalized number. NAN2 NaN select for .M1 src2. 5 src2 is not NaN. 1 src2 is NaN. NaN select for .M1 src1. 5 src1 is not NaN. NaN select for .M1 src1. 7 src1 is not NaN.	4	INVAL		
infinity is subtracted from infinity. Denormalized number select for .M1 src2. o src2 is not a denormalized number. src2 is a denormalized number. Denormalized number select for .M1 src1. Denormalized number select for .M1 src1. src1 is not a denormalized number. src1 is a denormalized number. NAN2 NaN select for .M1 src2. src2 is not NaN. src2 is not NaN. NaN select for .M1 src1. src1 is not NaN.			0	A signed NaN (SNaN) is not a source.
0 src2 is not a denormalized number. 1 src2 is a denormalized number. 2 DEN1 Denormalized number select for .M1 src1. 0 src1 is not a denormalized number. 1 src1 is a denormalized number. 1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. 0 NAN1 NaN select for .M1 src1. 0 src1 is not NaN.			1	
1	3	DEN2		Denormalized number select for .M1 src2.
2 DEN1 Denormalized number select for .M1 src1. 0 src1 is not a denormalized number. 1 src1 is a denormalized number. NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. 0 NAN1 NAN select for .M1 src1. 0 src1 is not NaN.			0	src2 is not a denormalized number.
0			1	src2 is a denormalized number.
1	2	DEN1		Denormalized number select for .M1 src1.
1 NAN2 NaN select for .M1 src2. 0 src2 is not NaN. 1 src2 is NaN. 0 NAN1 NaN select for .M1 src1. 0 src1 is not NaN.			0	src1 is not a denormalized number.
0			1	src1 is a denormalized number.
1 src2 is NaN. 0 NAN1 NaN select for .M1 src1. 0 src1 is not NaN.	1	NAN2		NaN select for .M1 src2.
0 NAN1 NaN select for .M1 src1. 0 src1 is not NaN.			0	src2 is not NaN.
0 src1 is not NaN.			1	src2 is NaN.
	0	NAN1		NaN select for .M1 src1.
1 <i>src1</i> is NaN.			0	src1 is not NaN.
			1	src1 is NaN.



Instruction Set

This chapter describes the assembly language instructions of the TMS320C674x DSP. Also described are parallel operations, conditional operations, resource constraints, and addressing modes.

The C674x DSP uses all of the instructions available to the TMS320C62x, TMS320C64x, TMS320C64x+, TMS320C67x, and TMS320C67x+ DSPs. The C674x DSP instructions include 8-bit and 16-bit extensions, nonaligned word loads and stores, data packing/unpacking operations.

Topic Page

3.1	Instruction Operation and Execution Notations	66
3.2	Instruction Syntax and Opcode Notations	68
3.3	Overview of IEEE Standard Single- and Double-Precision Formats	70
3.4	Delay Slots	73
3.5	Parallel Operations	74
3.6	Conditional Operations	77
3.7	SPMASKed Operations	77
3.8	Resource Constraints	78
3.9	Addressing Modes	87
3.10	Compact Instructions on the CPU	91
3.11	Instruction Compatibility	97
3.12	Instruction Descriptions	98



3.1 Instruction Operation and Execution Notations

Table 3-1 explains the symbols used in the instruction descriptions.

Table 3-1. Instruction Operation and Execution Notations

Symbol	Meaning	
abs(x)	Absolute value of x	
and	Bitwise AND	
-a	Perform 2s-complement subtraction using the addressing mode defined by the AMR	
+a	Perform 2s-complement addition using the addressing mode defined by the AMR	
b _i	Select bit i of source/destination b	
bit_count	count the number of bits that are 1 in a specified byte	
bit_reverse	Reverse the order of bits in a 32-bit register	
byte0	8-bit value in the least-significant byte position in 32-bit register (bits 0-7)	
byte1	8-bit value in the next to least-significant byte position in 32-bit register (bits 8-15)	
byte2	8-bit value in the next to most-significant byte position in 32-bit register (bits 16-23)	
byte3	8-bit value in the most-significant byte position in 32-bit register (bits 24-31)	
bv2	Bit vector of two flags for s2 or u2 data type	
bv4	Bit vector of four flags for s4 or u4 data type	
b _{yz}	Selection of bits y through z of bit string b	
cond	Check for either creg equal to 0 or creg not equal to 0	
creg	3-bit field specifying a conditional register, see Section 3.6	
<i>cst</i> n	n-bit constant field (for example, cst5)	
dint	64-bit integer value (two registers)	
dp	Double-precision floating-point register value	
dst_e	Isb32 of 64-bit dst (placed in even-numbered register of a 64-bit register pair)	
dst_h	msb8 of 40-bit <i>dst</i> (placed in odd-numbered register of 64-bit register pair)	
dst_I	Isb32 of 40-bit dst (placed in even-numbered register of a 64-bit register pair)	
dst_o	msb32 of 64-bit dst (placed in odd-numbered register of 64-bit register pair)	
dws4	Four packed signed 16-bit integers in a 64-bit register pair	
dwu4	Four packed unsigned 16-bit integers in a 64-bit register pair	
gmpy	Galois Field Multiply	
i2	Two packed 16-bit integers in a single 32-bit register	
i4	Four packed 8-bit integers in a single 32-bit register	
int	32-bit integer value	
Imb0(x)	Leftmost 0 bit search of x	
lmb1(x)	Leftmost 1 bit search of x	
long	40-bit integer value	
Isbn or LSBn	n least-significant bits (for example, lsb16)	
msbn or MSBn	n most-significant bits (for example, msb16)	
nop	No operation	
norm(x)	Leftmost nonredundant sign bit of x	
not	Bitwise logical complement	
ор	Opfields	
or	Bitwise OR	
R	Any general-purpose register	
ROTL	Rotate left	
sat	Saturate	
sbyte0	Signed 8-bit value in the least-significant byte position in 32-bit register (bits 0-7)	
sbyte0 sbyte1	Signed 8-bit value in the next to least-significant byte position in 32-bit register (bits 8-15)	
-	Signed 8-bit value in the next to reast-significant byte position in 32-bit register (bits 6-13)	
sbyte2	orgined orbit value in the next to most-significant byte position in 32-bit register (bits 10-23)	



Table 3-1. Instruction Operation and Execution Notations (continued)

Symbol	Meaning
sbyte3	Signed 8-bit value in the most-significant byte position in 32-bit register (bits 24-31)
scst <i>n</i>	n-bit signed constant field
sdint	Signed 64-bit integer value (two registers)
se	Sign-extend
sint	Signed 32-bit integer value
slong	Signed 40-bit integer value
sllong	Signed 64-bit integer value
slsb16	Signed 16-bit integer value in lower half of 32-bit register
smsb16	Signed 16-bit integer value in upper half of 32-bit register
sp	Single-precision floating-point register value that can optionally use cross path
src1_e or src2_e	lsb32 of 64-bit src (placed in even-numbered register of a 64-bit register pair)
src1_h or src2_h	msb8 of 40-bit src (placed in odd-numbered register of 64-bit register pair)
src1_l or src2_l	lsb32 of 40-bit src (placed in even-numbered register of a 64-bit register pair)
src1_o or src2_o	msb32 of 64-bit src (placed in odd-numbered register of 64-bit register pair)
32	Two packed signed 16-bit integers in a single 32-bit register
s4	Four packed signed 8-bit integers in a single 32-bit register
s	Perform 2s-complement subtraction and saturate the result to the result size, if an overflow occurs
+S	Perform 2s-complement addition and saturate the result to the result size, if an overflow occurs
ubyte0	Unsigned 8-bit value in the least-significant byte position in 32-bit register (bits 0-7)
ıbyte1	Unsigned 8-bit value in the next to least-significant byte position in 32-bit register (bits 8-15)
ibyte2	Unsigned 8-bit value in the next to most-significant byte position in 32-bit register (bits 16-23)
ubyte3	Unsigned 8-bit value in the most-significant byte position in 32-bit register (bits 24-31)
ucst <i>n</i>	n-bit unsigned constant field (for example, ucst5)
uint	Unsigned 32-bit integer value
ılong	Unsigned 40-bit integer value
ıllong	Unsigned 64-bit integer value
ulsb16	Unsigned 16-bit integer value in lower half of 32-bit register
ımsb16	Unsigned 16-bit integer value in upper half of 32-bit register
1 2	Two packed unsigned 16-bit integers in a single 32-bit register
ı 4	Four packed unsigned 8-bit integers in a single 32-bit register
cclear b,e	Clear a field in x, specified by b (beginning bit) and e (ending bit)
ext I,r	Extract and sign-extend a field in x, specified by I (shift left value) and r (shift right value)
extu <i>I,r</i>	Extract an unsigned field in x, specified by I (shift left value) and r (shift right value)
set <i>b,e</i>	Set field in x to all 1s, specified by b (beginning bit) and e (ending bit)
кdр	Double-precision floating-point register value that can optionally use cross path
kint	32-bit integer value that can optionally use cross path
cor	Bitwise exclusive-ORs
sint	Signed 32-bit integer value that can optionally use cross path
kslsb16	Signed 16 LSB of register that can optionally use cross path
smsb16	Signed 16 MSB of register that can optionally use cross path
csp	Single-precision floating-point register value that can optionally use cross path
cs2	Two packed signed 16-bit integers in a single 32-bit register that can optionally use cross path
rs4	Four packed signed 8-bit integers in a single 32-bit register that can optionally use cross path
kuint	Unsigned 32-bit integer value that can optionally use cross path
kulsb16	Unsigned 16 LSB of register that can optionally use cross path
xumsb16	Unsigned 16 MSB of register that can optionally use cross path
xu2	Two packed unsigned 16-bit integers in a single 32-bit register that can optionally use cross path

SPRUFE8B-July 2010 Instruction Set 67



Table 3-1. Instruction Operation and Execution Notations (continued)

Symbol	Meaning	
xu4	Four packed unsigned 8-bit integers in a single 32-bit register that can optionally use cross path	
\rightarrow	Assignment	
+	Addition	
++	Increment by 1	
×	Multiplication	
-	Subtraction	
==	Equal to	
>	Greater than	
>=	Greater than or equal to	
<	Less than	
<=	Less than or equal to	
<<	Shift left	
>>	Shift right	
>>S	Shift right with sign extension	
>>Z	Shift right with a zero fill	
~	Logical inverse	
&	Logical AND	

3.2 Instruction Syntax and Opcode Notations

Table 3-2 explains the syntaxes and opcode fields used in the instruction descriptions.

Table 3-2. Instruction Syntax and Opcode Notations

Symbol	Meaning	
baseR	base address register	
creg	3-bit field specifying a conditional register, see Section 3.6	
cst	constant	
csta	constant a	
cstb	constant b	
cstn	n-bit constant field	
dst	destination	
dw	doubleword; 0 = word, 1 = doubleword	
fcyc	SPLOOP fetch cycle	
fstg	SPLOOP fetch stage	
h	MVK or MVKH instruction	
ii _n	bit n of the constant ii	
ld/st	load or store; 0 = store, 1 = load	
mode	addressing mode, see Section 3.9	
na	nonaligned; 0 = aligned, 1 = nonaligned	
N3	3-bit field	
offsetR	register offset	
ор	opfield; field within opcode that specifies a unique instruction	
op_n	bit n of the opfield	
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel	
ptr	offset from either A4-A7 or B4-B7 depending on the value of the s bit. The ptr field is the 2 least-significant bits of the src2 (baseR) field—bit 2 of register address is forced to 1.	



Table 3-2. Instruction Syntax and Opcode Notations (continued)

Symbol	Meaning	
r	LDDW/LDNDW/LDNW instruction	
rsv	reserved	
S	side A or B for destination; 0 = side A, 1 = side B.	
SC	scaling mode; 0 = nonscaled, offsetR/ucst5 is not shifted; 1 = scaled, offsetR/ucst5 is shifted	
scstn	n-bit signed constant field	
scst _n	bit n of the signed constant field	
sn	sign	
src	source	
src1	source 1	
src2	source 2	
stg _n	bit n of the constant stg	
SZ	data size select; 0 = primary size, 1 = secondary size (see Section 3.10.2.2)	
t	side of source/destination (src/dst) register; 0 = side A, 1 = side B	
ucstn	n-bit unsigned constant field	
ucst _n	bit n of the unsigned constant field	
unit	unit decode	
x	cross path for src2; 0 = do not use cross path, 1 = use cross path	
У	.D1 or .D2 unit; 0 = .D1 unit, 1 = .D2 unit	
Z	test for equality with zero or nonzero	

3.2.1 32-Bit Opcode Maps

The 32-bit opcodes are mapped in Appendix C through Appendix H.

3.2.2 16-Bit Opcode Maps

The 16-bit opcodes used for compact instructions are mapped in Appendix C through Appendix H. See Section 3.10 for more information about compact instructions.

SPRUFE8B-July 2010 Instruction Set 69



3.3 Overview of IEEE Standard Single- and Double-Precision Formats

Floating-point operands are classified as single-precision (SP) and double-precision (DP). Single-precision floating-point values are 32-bit values stored in a single register. Double-precision floating-point values are 64-bit values stored in a register pair. The register pair consists of consecutive even and odd registers from the same register file. The 32 least-significant-bits are loaded into the even register; the 32 most-significant-bits containing the sign bit and exponent are loaded into the next register (that is always the odd register). The register pair syntax places the odd register first, followed by a colon, then the even register (that is, A1:A0, B1:B0, A3:A2, B3:B2, etc.).

Instructions that use DP sources fall in two categories: instructions that read the upper and lower 32-bit words on separate cycles, and instructions that read both 32-bit words on the same cycle. All instructions that produce a double-precision result write the low 32-bit word one cycle before writing the high 32-bit word. If an instruction that writes a DP result is followed by an instruction that uses the result as its DP source and it reads the upper and lower words on separate cycles, then the second instruction can be scheduled on the same cycle that the high 32-bit word of the result is written. The lower result is written on the previous cycle. This is because the second instruction reads the low word of the DP source one cycle before the high word of the DP source.

IEEE floating-point numbers consist of normal numbers, denormalized numbers, NaNs (not a number), and infinity numbers. Denormalized numbers are nonzero numbers that are smaller than the smallest nonzero normal number. Infinity is a value that represents an infinite floating-point number. NaN values represent results for invalid operations, such as (+infinity + (-infinity)).

Normal single-precision values are always accurate to at least six decimal places, sometimes up to nine decimal places. Normal double-precision values are always accurate to at least 15 decimal places, sometimes up to 17 decimal places.

Table 3-3 shows notations used in discussing floating-point numbers.

Symbol Meaning s Sign bit е Exponent field Fraction (mantissa) field Can have value of 0 or 1 (don't care) Not-a-Number (SNaN or QNaN) NaN **SNaN** Signal NaN QNaN Quiet NaN NaN_out QNaN with all bits in the f field = 1 Inf **LFPN** Largest floating-point number **SFPN** Smallest floating-point number **LDFPN** Largest denormalized floating-point number **SDFPN** Smallest denormalized floating-point number signed Inf +infinity or -infinity signed NaN_out $NaN_out with s = 0 or 1$

Table 3-3. IEEE Floating-Point Notations



3.3.1 Single-Precision Formats

Figure 3-1 shows the fields of a single-precision floating-point number represented within a 32-bit register.

Figure 3-1. Single-Precision Floating-Point Fields

31	30 23	22 0
S	е	f

LEGEND: s = sign bit (0 = positive, 1 = negative); e = 8-bit exponent (0 < e < 255); f = 23-bit fraction ($0 < f < 1 \times 2^{-1} + 1 \times 2^{-2} + ... + 1 \times 2^{-23}$ or $0 < f < ((2^{23}) - 1)/(2^{23})$

The floating-point fields represent floating-point numbers within two ranges: normalized (e is between 0 and 255) and denormalized (e is 0). The following formulas define how to translate the s, e, and f fields into a single-precision floating-point number.

Normalized: $-1^{s} \times 2^{(e-127)} \times 1.f$ 0 < e < 255

Denormalized (Subnormal): $-1^s \times 2^{-126} \times 0.f$ e = 0; f is nonzero

Table 3-4 shows the s, e, and f values for special single-precision floating-point numbers.

Table 3-4. Special Single-Precision Values

Symbol	Sign (s)	Exponent (e)	Fraction (f)
+0	0	0	0
-0	1	0	0
+Inf	0	255	0
-Inf	1	255	0
NaN	х	255	nonzero
QNaN	x	255	1xxx
SNaN	х	255	0xxx and nonzero

Table 3-5 shows hexadecimal and decimal values for some single-precision floating-point numbers.

Table 3-5. Hexadecimal and Decimal Representation for Selected Single-Precision Values

Symbol	Hex Value	Decimal Value
NaN_out	7FFF FFFF	QNaN
0	0000 0000	0.0
-0	8000 0000	-0.0
1	3F80 0000	1.0
2	4000 0000	2.0
LFPN	7F7F FFFF	3.40282347e+38
SFPN	0000 0000	1.17549435e-38
LDFPN	007F FFFF	1.17549421e-38
SDFPN	0000 0001	1.40129846e-45

SPRUFE8B-July 2010 Instruction Set 71



3.3.2 Double-Precision Formats

Figure 3-2 shows the fields of a double-precision floating-point number represented within a pair of 32-bit registers.

Figure 3-2. Double-Precision Floating-Point Fields

31	30 20	19 0	31 0
S	е	f	f
		Odd register	Even register

LEGEND: s = sign bit (0 = positive, 1 = negative); e = 11-bit exponent (0 < e < 2047); f = 52-bit fraction (0 < $f < 1 \times 2^{-1} + 1 \times 2^{-2} + ... + 1 \times 2^{-52}$ or $0 < f < ((2^{52}) - 1)/(2^{52})$

The floating-point fields represent floating-point numbers within two ranges: normalized (e is between 0 and 2047) and denormalized (e is 0). The following formulas define how to translate the s, e, and f fields into a double-precision floating-point number.

Normalized: $-1^{s} \times 2^{(e-1023)} \times 1.f$ 0 < e < 2047

Denormalized (Subnormal): $-1^s \times 2^{-1022} \times 0.f$ e = 0; f is nonzero

Table 3-6 shows the s, e, and f values for special double-precision floating-point numbers.

Table 3-6. Special Double-Precision Values

Symbol	Sign (s)	Exponent (e)	Fraction (f)
+0	0	0	0
-0	1	0	0
+Inf	0	2047	0
-Inf	1	2047	0
NaN	х	2047	nonzero
QNaN	х	2047	1xxx
SNaN	x	2047	0xxx and nonzero

Table 3-7 shows hexadecimal and decimal values for some double-precision floating-point numbers.

Table 3-7. Hexadecimal and Decimal Representation for Selected Double-Precision Values

Symbol	Hex Value	Decimal Value
NaN_out	7FFF FFFF FFFF FFFF	QNaN
0	0000 0000 0000 0000	0.0
-0	8000 0000 0000 0000	-0.0
1	3FF0 0000 0000 0000	1.0
2	4000 0000 0000 0000	2.0
LFPN	7FEF FFFF FFFF FFFF	1.7976931348623157e+308
SFPN	0010 0000 0000 0000	2.2250738585072014e-308
LDFPN	000F FFFF FFFF FFFF	2.2250738585072009e-308
SDFPN	0000 0000 0000 0001	4.9406564584124654e-324



www.ti.com Delay Slots

3.4 Delay Slots

The execution of floating-point instructions can be defined in terms of delay slots and functional unit latency. The number of delay slots is equivalent to the number of additional cycles required after the source operands are read for the result to be available for reading. For a single-cycle type instruction, operands read in cycle i produce a result that can be read in cycle i + 1. For a 4-cycle instruction, operands read in cycle i produce a result that can be read in cycle i + 4. Table 3-8 shows the number of delay slots associated with each type of instruction.

The functional unit latency is equivalent to the number of cycles that must pass before the functional unit can start executing the next instruction. The double-precision floating-point addition, subtraction, multiplication, compare, and the 32-bit integer multiply instructions have a functional unit latency that is greater than 1. Most instructions have a functional unit latency of 1, meaning that the next instruction can begin execution in cycle i + 1. The **ADDDP** instruction has a functional unit latency of 2. Operands are read on cycle i and cycle i + 1. Therefore, a new instruction cannot begin until cycle i + 2, rather than cycle i + 1. **ADDDP** produces a result that can be read in cycle i + 7, because it has six delay slots.

Table 3-8. Delay Slot and Functional Unit Latency

Instruction Type	Delay Slots	Functional Unit Latency	Read Cycles (1)	Write Cycles (1)
Single cycle	0	1	i	i
2-cycle DP	1	1	i	i, i + 1
DP compare	1	2	i, i + 1	i + 1
4-cycle	3	1	i	i + 3
INTDP	4	1	i	i + 3, i + 4
Load	4	1	i	i, i + 4 ⁽²⁾
MPYSP2DP	4	2	i	i + 3, i + 4
ADDDP/SUBDP	6	2	i, i + 1	i + 5, i + 6
MPYSPDP	6	3	i, i + 1	i + 5, i + 6
MPYI	8	4	i, i + 1, 1 + 2, i + 3	i + 8
MPYID	9	4	i, i + 1, 1 + 2, i + 3	i + 8, i + 9
MPYDP	9	4	i, i + 1, 1 + 2, i + 3	i + 8, i + 9

⁽¹⁾ Cycle i is in the E1 pipeline phase.

⁽²⁾ A write on cycle i + 4 uses a separate write port from other .D unit instructions.




Parallel Operations www.ti.com

3.5 Parallel Operations

Instructions are always fetched eight words at a time. This constitutes a *fetch packet*. On the CPU, this may be as many as 14 instructions due to the existence of compact instructions in a header based fetch packet. The basic format of a fetch packet is shown in Figure 3-3. Fetch packets are aligned on 256-bit (8-word) boundaries.

Figure 3-3. Basic Format of a Fetch Packet



The CPU supports compact 16-bit instructions. Unlike the normal 32-bit instructions, the p-bit information for compact instructions is not contained within the instruction opcode. Instead, the p-bit is contained within the p-bits field within the fetch packet header. See Section 3.10 for more information.

The execution of the individual noncompact instructions is partially controlled by a bit in each instruction, the p-bit. The p-bit (bit 0) determines whether the instruction executes in parallel with another instruction. The p-bits are scanned from left to right (lower to higher address). If the p-bit of instruction I is 1, then instruction I is to be executed in parallel with (in the same cycle as) instruction I. If the p-bit of instruction I is 0, then instruction I is executed in the cycle after instruction I. All instructions executing in parallel constitute an execute packet. An execute packet can contain up to eight instructions. Each instruction in an execute packet must use a different functional unit.

On the CPU, the execute packet can cross fetch packet boundaries, but will be limited to no more than eight instructions in a fetch packet. The last instruction in an execute packet will be marked with its *p*-bit cleared to zero. There are three types of *p*-bit patterns for fetch packets. These three *p*-bit patterns result in the following execution sequences for the eight instructions:


- Fully serial
- Fully parallel
- · Partially serial

Example 3-1 through Example 3-3 show the conversion of a *p*-bit sequence into a cycle-by-cycle execution stream of instructions.




www.ti.com Parallel Operations

Example 3-1. Fully Serial p-Bit Pattern in a Fetch Packet



Cycle/Execute Packet	Instructions
1	A
2	В
3	С
4	D
5	E
6	F
7	G
8	Н

Example 3-2. Fully Parallel p-Bit Pattern in a Fetch Packet




Cycle/Execute Packet				Instru	ctions			
1	Α	В	С	D	E	F	G	Н



Parallel Operations www.ti.com

Example 3-3. Partially Serial p-Bit Pattern in a Fetch Packet



Cycle/Execute Packet	Instructions			
1	A			
2	В			
3	С	D	Е	
4	F	G	Н	

3.5.1 Example Parallel Code

The vertical bars || signify that an instruction is to execute in parallel with the previous instruction. The code for the fetch packet in Example 3-3 would be represented as this:

```
instruction A
instruction B
instruction C
instruction D
instruction E
instruction F
instruction G
instruction H
```

3.5.2 Branching Into the Middle of an Execute Packet

If a branch into the middle of an execute packet occurs, all instructions at lower addresses are ignored. In Example 3-3, if a branch to the address containing instruction D occurs, then only D and E execute. Even though instruction C is in the same execute packet, it is ignored. Instructions A and B are also ignored because they are in earlier execute packets. If your result depends on executing A, B, or C, the branch to the middle of the execute packet will produce an erroneous result.



Conditional Operations www.ti.com

Conditional Operations 3.6

Most instructions can be conditional. The condition is controlled by a 3-bit opcode field (creg) that specifies the condition register tested, and a 1-bit field (z) that specifies a test for zero or nonzero. The four MSBs of every opcode are creg and z. The specified condition register is tested at the beginning of the E1 pipeline stage for all instructions. For more information on the pipeline, see Chapter 4. If z = 1, the test is for equality with zero; if z = 0, the test is for nonzero. The case of creq = 0 and z = 0 is treated as always true to allow instructions to be executed unconditionally. The creg field is encoded in the instruction opcode as shown in Table 3-9.

Compact (16-bit) instructions on the DSP do not contain a creg field and always execute unconditionally. See Section 3.10 for more information.

Specified Conditional		creg				
Register	Bit:	31	30	29	28	
Unconditional		0	0	0	0	
Reserved		0	0	0	1	
B0		0	0	1	Z	
B1		0	1	0	Z	
B2		0	1	1	z	
A1		1	0	0	z	
A2		1	0	1	Z	
A0		1	1	0	Z	
Reserved		1	1	1	x ⁽¹⁾	

Table 3-9. Registers That Can Be Tested by Conditional Operations

Conditional instructions are represented in code by using square brackets, [], surrounding the condition register name. The following execute packet contains two ADD instructions in parallel. The first ADD is conditional on B0 being nonzero. The second ADD is conditional on B0 being zero. The character! indicates the inverse of the condition.

```
[B0]
                               .L1
                 ADD
                                           A1,A2,A3
\prod
       [!B0]
                 ADD
                                           B1,B2,B3
                               .L2
```

The above instructions are mutually exclusive, only one will execute. If they are scheduled in parallel, mutually exclusive instructions are constrained as described in Section 3.8. If mutually exclusive instructions share any resources as described in Section 3.8, they cannot be scheduled in parallel (put in the same execute packet), even though only one will execute.

The act of making an instruction conditional is often called predication and the conditional register is often called the predication register.

3.7 **SPMASKed Operations**

On the CPU, the SPMASK and SPMASKR instructions can be used to inhibit the execution of instructions from the SPLOOP buffer. The selection of which instruction to inhibit can be specified by the SPMASK or SPMASKR instruction argument or can be marked by the addition of a caret (^) next to the parallel code marker as shown below:

```
SPMASK
LDW
       .D1
             *A0,A1
                                  ;This instruction is SPMASKed
LDW
       .D2
              *B0,B1
                                  ;This instruction is SPMASKed
                                  ;This instruction is Not SPMASKed
MPY
       .M1
             A3,A4,A5
```

See Chapter 7 for more information.

x can be any value.



Resource Constraints www.ti.com

3.8 Resource Constraints

No two instructions within the same execute packet can use the same resources. Also, no two instructions can write to the same register during the same cycle. The following sections describe how an instruction can use each of the resources.

3.8.1 Constraints on Instructions Using the Same Functional Unit

Two instructions using the same functional unit cannot be issued in the same execute packet.

The following execute packet is invalid:

```
ADD .S1 A0, A1, A2 ;.S1 is used for | SHR .S1 A3, 15, A4 ;...both instructions
```

The following execute packet is valid:

```
ADD .L1 A0, A1, A2 ;Two different functional | SHR .S1 A3, 15, A4 ;...units are used
```

3.8.2 Constraints on the Same Functional Unit Writing in the Same Instruction Cycle

The .M unit has two 32-bit write ports; so the results of a 4-cycle 32-bit instruction and a 2-cycle 32-bit instruction operating on the same .M unit can write their results on the same instruction cycle. Any other combination of parallel writes on the .M unit will result in a conflict. On the C674x DSP this will result in an exception.

On the C674x DSP, this will result in erroneous values being written to the destination registers.

For example, the following sequence is valid and results in both A2 and A5 being written by the .M1 unit on the same cycle.

```
DOTP2 .M1 A0,A1,A2 ;This instruction has 3 delay slots
NOP
AVG2 .M1 A4,A5 ;This instruction has 1 delay slot
NOP ;Both A2 and A5 get written on this cycle
```

The following sequence is invalid. The attempt to write 96 bits of output through 64-bits of write port will fail.

```
SMPY2 .M1 A5,A6,A9:A8 ;This instruction has 3 delay slots; but generates a 64 bit result NOP MPY .M1 A1,A2,A3 ;This instruction has 1 delay slot NOP
```

3.8.3 Constraints on Cross Paths (1X and 2X)

Up to two units (.S, .L, .D, or .M unit) per data path, per execute packet, can read a source operand from its opposite register file via the cross paths (1X and 2X) provided that each unit is reading the same operand.

For example, the .S1 unit can read both its operands from the A register file; or it can read an operand from the B register file using the 1X cross path and the other from the A register file. The use of a cross path is denoted by an X following the functional unit name in the instruction syntax (as in S1X).

The following execute packet is invalid because the 1X cross path is being used for two different B register operands:

```
MV .S1X B0, A0 ; Invalid. Instructions are using the 1X cross path \mid \mid MV .L1X B1, A1 ; with different B registers
```



www.ti.com Resource Constraints

The following execute packet is valid because all uses of the 1X cross path are for the same B register operand, and all uses of the 2X cross path are for the same A register operand:

```
ADD .L1X A0,B1,A1 ; Instructions use the 1X with B1

|| SUB .S1X A2,B1,A2 ; 1X cross paths using B1

|| AND .D1 A4,A1,A3 ;

|| MPY .M1 A6,A1,A4 ;

|| ADD .L2 B0,B4,B2 ;

|| SUB .S2X B4,A4,B3 ; 2X cross paths using A4

|| AND .D2X B5,A4,B4 ; 2X cross paths using A4

|| MPY .M2 B6,B4,B5 ;
```

The following execute packet is invalid because more than two functional units use the same cross path operand:

```
MV .L2X A0, B0 ; 1st cross path move || MV .S2X A0, B1 ; 2nd cross path move || MV .D2X A0, B2 ; 3rd cross path move
```

The operand comes from a register file opposite of the destination, if the x bit in the instruction field is set.

3.8.4 Cross Path Stalls

The DSP introduces a delay clock cycle whenever an instruction attempts to read a register via a cross path that was updated in the previous cycle. This is known as a cross path stall. This stall is inserted automatically by the hardware, no **NOP** instruction is needed. It should be noted that no stall is introduced if the register being read has data placed by a load instruction, or if an instruction reads a result one cycle after the result is generated.

Here are some examples:

```
AO, AO, A1 ; / Stall is introduced; A1 is updated
                        1 cycle before it is used as a
ADD
    .S2X A1, B0, B1 ; \ cross path source
          AO, AO, A1 ; / No stall is introduced; AO not updated
    .S1
ADD
                      ; 1 cycle before it is used as a cross
     .S2X A0, B0, B1 ; \ path source
ADD
    .D1 *++A0[1], A1 ; / No stall is introduced; A1 is the load
LDW
                         destination
                      ; NOP 4 represents 4 instructions to
NOP
ADD
    .S2X A1, B0, B1 ; \ be executed between the load and add.
    .D1 *++A0[1], A1; / Stall is introduced; A0 is updated
    .S2X A0, B0, B1; 1 cycle before it is used as a
ADD
                      ; \ cross path source
```

It is possible to avoid the cross path stall by scheduling an instruction that reads an operand via the cross path at least one cycle after the operand is updated. With appropriate scheduling, the DSP can provide one cross path operand per data path per cycle with no stalls. In many cases, the TMS320C6000 Optimizing Compiler and Assembly Optimizer automatically perform this scheduling.



Resource Constraints www.ti.com

3.8.5 Constraints on Loads and Stores

The data address paths named DA1 and DA2 are each connected to the .D units in both data paths. Load and store instructions can use an address pointer from one register file while loading to or storing from the other register file. Two load and store instructions using a destination/source from the same register file cannot be issued in the same execute packet. The address register must be on the same side as the .D unit used.

The DA1 and DA2 resources and their associated data paths are specified as T1 and T2, respectively. T1 consists of the DA1 address path and the LD1 and ST1 data paths. LD1 is comprised of LD1a and LD1b to support 64-bit loads; ST1 is comprised of ST1a and ST1b to support 64-bit stores. Similarly, T2 consists of the DA2 address path and the LD2 and ST2 data paths. LD2 is comprised of LD2a and LD2b to support 64-bit loads; ST2 is comprised of ST2a and ST2b to support 64-bit stores. The T1 and T2 designations appear in the functional unit fields for load and store instructions.

The DSP can access words and doublewords at any byte boundary using nonaligned loads and stores. As a result, word and doubleword data does not need alignment to 32-bit or 64-bit boundaries. No other memory access may be used in parallel with a nonaligned memory access. The other .D unit can be used in parallel, as long as it is not performing a memory access.

The following execute packet is invalid:

```
LDNW .D2T2 *B2[B12],B13 ; \ Two memory operations, 
 || LDB .D1T1 *A2,A14 ; / one non-aligned
```

The following execute packet is valid:

3.8.6 Constraints on Long (40-Bit) Data

Both the C62x and C67x device families had constraints on the number of simultaneous reads and writes of 40-bit data due to shared data paths.

The C674x CPU maintains separate datapaths to each functional unit, so these constraints are removed.

The following, for example, is valid:

```
DDOTPL2
         .M1
                A1:A0,A2,A5:A4
DDOTPL2
         .M2
                B1:B0,B2,B5:B4
STDW
         .D1
                A9:A8,*A6
STDW
         .D2
                B9:B8,*B6
SUB
         .L1
                A25:A24,A20,A31:A30
              B25:B24,B20,B31:B30
SUB
         .L2
                A11:A10,5,A13:A12
SHL
         .S1
                B11:B10,8,B13:B12
SHL
         .S2
```



www.ti.com Resource Constraints

3.8.7 Constraints on Register Reads

More than four reads of the same register cannot occur on the same cycle. Conditional registers are not included in this count.

The following execute packets are invalid:

```
MPY .M1 A1, A1, A4 ; five reads of register A1
|| ADD .L1 A1, A1, A5
|| SUB .D1 A1, A2, A3

MPY .M1 A1, A1, A4 ; five reads of register A1
|| ADD .L1 A1, A1, A5
|| SUB .D2x A1, B2, B3
```

The following execute packet is valid:

```
MPY .M1 A1, A1, A4 ; only four reads of A1
|| [A1] ADD .L1 A0, A1, A5
|| SUB .D1 A1, A2, A3
```

3.8.8 Constraints on Register Writes

Two instructions cannot write to the same register on the same cycle. Two instructions with the same destination can be scheduled in parallel as long as they do not write to the destination register on the same cycle. For example, an **MPY** issued on cycle I followed by an **ADD** on cycle I + 1 cannot write to the same register because both instructions write a result on cycle I + 1. Therefore, the following code sequence is invalid unless a branch occurs after the **MPY**, causing the **ADD** not to be issued.

```
MPY .M1 A0, A1, A2
ADD .L1 A4, A5, A2
```

However, this code sequence is valid:

```
MPY .M1 A0, A1, A2
```

Figure 3-4 shows different multiple-write conflicts. For example, **ADD** and **SUB** in execute packet L1 write to the same register. This conflict is easily detectable.

MPY in packet L2 and **ADD** in packet L3 might both write to B2 simultaneously; however, if a branch instruction causes the execute packet after L2 to be something other than L3, a conflict would not occur. Thus, the potential conflict in L2 and L3 might not be detected by the assembler. The instructions in L4 do not constitute a write conflict because they are mutually exclusive. In contrast, because the instructions in L5 may or may not be mutually exclusive, the assembler cannot determine a conflict. If the pipeline does receive commands to perform multiple writes to the same register, the result is undefined.

Figure 3-4. Examples of the Detectability of Write Conflicts by the Assembler

```
.L2
                          B5,B6,B7
                                       ; \ detectable, conflict
L1:
                 ADD
                     .S2 B8,B9,B7
      SUB
                                       ;
L2:
                     .M2 B0,B1,B2
                                       ; \ not detectable
                 MPY
                      .L2 B3,B4,B2
                 ADD
L3:
                                       ; /
          [!B0] ADD
                      .L2 B5,B6,B7
T.4:
                                       ; \ detectable, no conflict
      || [B0]
                 SUB .S2 B8,B9,B7
                                       ; /
T.5:
          [!B1] ADD .L2 B5,B6,B7
                                      ; \ not detectable
      || [B0]
                 SUB .S2 B8,B9,B7
```



Resource Constraints www.ti.com

3.8.9 Constraints on AMR Writes

A write to the addressing mode register (AMR) using the **MVC** instruction that is immediately followed by a **LD, ST, ADDA**, or **SUBA** instruction causes a 1 cycle stall, if the **LD, ST, ADDA**, or **SUBA** instruction uses the A4-A7 or B4-B7 registers for addressing.

3.8.10 Constraints on Multicycle NOPs

Two instructions that generate multicycle NOPs cannot share the same execute packet. Instructions that generate a multicycle **NOP** are:

- NOP n (where n > 1)
- IDLE
- BNOP target, *n* (for all values of *n*, regardless of predication)
- ADDKPC label, reg, *n* (for all values of *n*, regardless of predication)

3.8.11 Constraints on Unitless Instructions

3.8.11.1 SPLOOP Restrictions

The **NOP**, **NOP** *n*, and **BNOP** instructions are the only unitless instructions allowed to be used in an SPLOOP(D/W) body. The assembler disallows the use of any other unitless instruction in the loop body.

See Chapter 7 for more information.

3.8.11.2 BNOP <disp>,n

A **BNOP** instruction cannot be placed in parallel with the following instructions if the **BNOP** has a non-zero NOP count:

- ADDKPC
- CALLP
- NOP n

3.8.11.3 DINT

A **DINT** instruction cannot be placed in parallel with the following instructions:

- MVC reg, TSR
- MVC reg, CSR
- B IRP
- B NRP
- IDLE
- NOP n (if n > 1)
- RINT
- SPKERNEL(R)
- SPLOOP(D/W)
- SPMASK(R)
- SWE
- SWENR

A **DINT** instruction can be placed in parallel with the **NOP** instruction.



www.ti.com Resource Constraints

3.8.11.4 IDLE

An **IDLE** instruction cannot be placed in parallel with the following instructions:

- DINT
- NOP *n* (if *n* > 1)
- RINT
- SPKERNEL(R)
- SPLOOP(D/W)
- SPMASK(R)
- SWE
- SWENR

An **IDLE** instruction can be placed in parallel with the **NOP** instruction.

3.8.11.5 NOP n

A **NOP** n (with n > 1) instruction cannot be placed in parallel with other multicycle **NOP** counts (**ADDKPC**, **BNOP**, **CALLP**) with the exception of another **NOP** n where the NOP count is the same. A **NOP** n (with n > 1) instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- RINT
- SPKERNEL(R)
- SPLOOP(D/W)
- SPMASK(R)
- SWE
- SWENR

3.8.11.6 RINT

A **RINT** instruction cannot be placed in parallel with the following instructions:

- MVC reg, TSR
- MVC reg, CSR
- B IRP
- B NRP
- DINT
- IDLE
- NOP *n* (if *n* > 1)
- SPKERNEL(R)
- SPLOOP(D/W)
- SPMASK(R)
- SWE
- SWENR

A **RINT** instruction can be placed in parallel with the **NOP** instruction.

3.8.11.7 **SPKERNEL(R)**

An **SPKERNEL(R)** instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- NOP *n* (if *n* > 1)
- RINT
- SPLOOP(D/W)



Resource Constraints www.ti.com

- SPMASK(R)
- SWE
- SWENR

An **SPKERNEL(R)** instruction can be placed in parallel with the **NOP** instruction.

3.8.11.8 SPLOOP(D/W)

An SPLOOP(D/W) instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- NOP *n* (if *n* > 1)
- RINT
- SPKERNEL(R)
- SPMASK(R)
- SWE
- SWENR

An SPLOOP(D/W) instruction can be placed in parallel with the NOP instruction:

3.8.11.9 SPMASK(R)

An SPMASK(R) instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- NOP n (if n > 1)
- RINT
- SPLOOP(D/W)
- SPKERNEL(R)
- SWE
- SWENR

An SPMASK(R) instruction can be placed in parallel with the NOP instruction.

3.8.11.10 SWE

An **SWE** instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- NOP n (if n > 1)
- RINT
- SPLOOP(D/W)
- SPKERNEL(R)
- SWENR

An **SWE** instruction can be placed in parallel with the **NOP** instruction.

3.8.11.11 SWENR

An **SWENR** instruction cannot be placed in parallel with the following instructions:

- DINT
- IDLE
- NOP n (if n > 1)
- RINT
- SPLOOP(D/W)



www.ti.com Resource Constraints

- SPKERNEL(R)
- SWE

An **SWENR** instruction can be placed in parallel with the **NOP** instruction.

3.8.12 Constraints on Floating-Point Instructions

If an instruction has a multicycle functional unit latency, it locks the functional unit for the necessary number of cycles. Any new instruction dispatched to that functional unit during this locking period causes undefined results. If an instruction with a multicycle functional unit latency has a condition that is evaluated as false during E1, it still locks the functional unit for subsequent cycles.

An instruction of the following types scheduled on cycle I has the following constraints:

DP compare No other instruction can use the functional unit on cycles I and I + 1. ADDDP/SUBDP No other instruction can use the functional unit on cycles I and I + 1.

MPYI No other instruction can use the functional unit on cycles I, I + 1, I + 2, and I + 3. MPYID No other instruction can use the functional unit on cycles I, I + 1, I + 2, and I + 3. MPYDP No other instruction can use the functional unit on cycles I, I + 1, I + 2, and I + 3.

If a cross path is used to read a source in an instruction with a multicycle functional unit latency, you must ensure that no other instructions executing on the same side uses the cross path.

An instruction of the following types scheduled on cycle I using a cross path to read a source, has the following constraints:

DP compare No other instruction on the same side can used the cross path on cycles I and I + 1.

ADDDP/SUBDP No other instruction on the same side can use the cross path on cycles I and I + 1.

MPYI No other instruction on the same side can use the cross path on cycles I, I + 1, I + 2,

and I + 3.

MPYID No other instruction on the same side can use the cross path on cycles I, I + 1, I + 2,

and I + 3.

MPYDP No other instruction on the same side can use the cross path on cycles I, I + 1, I + 2,

and I + 3.

Other hazards exist because instructions have varying numbers of delay slots, and need the functional unit read and write ports of varying numbers of cycles. A read or write hazard exists when two instructions on the same functional unit attempt to read or write, respectively, to the register file on the same cycle.



Resource Constraints www.ti.com

An instruction of the following types scheduled on cycle I has the following constraints:

2-cycle DP A single-cycle instruction cannot be scheduled on that functional unit on cycle I + 1

due to a write hazard on cycle I + 1.

Another 2-cycle DP instruction cannot be scheduled on that functional unit on cycle

I + 1 due to a write hazard on cycle I + 1.

4-cycle A single-cycle instruction cannot be scheduled on that functional unit on cycle I + 3

due to a write hazard on cycle I + 3.

A multiply (16 16-bit) instruction cannot be scheduled on that functional unit on cycle

I + 2 due to a write hazard on cycle I + 3.

INTDP A single-cycle instruction cannot be scheduled on that functional unit on cycle I + 3 or

I + 4 due to a write hazard on cycle I + 3 or I + 4, respectively.

An INTDP instruction cannot be scheduled on that functional unit on cycle I + 1 due to

a write hazard on cycle I + 1.

A 4-cycle instruction cannot be scheduled on that functional unit on cycle I + 1 due to a

write hazard on cycle I + 1.

MPYI A 4-cycle instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5,

or I + 6.

A MPYDP instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5,

or I + 6.

A multiply (16 16-bit) instruction cannot be scheduled on that functional unit on cycle

I + 6 due to a write hazard on cycle I + 7.

MPYID A 4-cycle instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5,

or I + 6.

A MPYDP instruction cannot be scheduled on that functional unit on cycles I + 4, I + 5,

or I + 6.

A multiply (16 16-bit) instruction cannot be scheduled on that functional unit on cycle I

+ 7 or I + 8 due to a write hazard on cycle I + 8 or I + 9, respectively.

MPYDP A 4-cycle instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5,

or I + 6.

A MPYI instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5, or

l **+** 6.

A MPYID instruction cannot be scheduled on that functional unit on cycle I + 4, I + 5,

or I + 6.

A multiply (16 x 16-bit) instruction cannot be scheduled on that functional unit on cycle

I + 7 or I + 8 due to a write hazard on cycle I + 8 or I + 9, respectively.

ADDDP/SUBDP A single-cycle instruction cannot be scheduled on that functional unit on cycle I + 5 or

I + 6 due to a write hazard on cycle I + 5 or I + 6, respectively.

A 4-cycle instruction cannot be scheduled on that functional unit on cycle I + 2 or I + 3

due to a write hazard on cycle I + 5 or I + 6, respectively.

An INTDP instruction cannot be scheduled on that functional unit on cycle I + 2 or I + 3

due to a write hazard on cycle I + 5 or I + 6, respectively.



www.ti.com Addressing Modes

All of the previous cases deal with double-precision floating-point instructions or the **MPYI** or **MPYID** instructions except for the 4-cycle case. A 4-cycle instruction consists of both single- and double-precision floating-point instructions. Therefore, the 4-cycle case is important for the following single-precision floating-point instructions:

- ADDSP
- SUBSP
- SPINT
- SPTRUNC
- INTSP
- MPYSP

3.9 Addressing Modes

The addressing modes on the DSP are linear, circular using BK0, and circular using BK1. The addressing mode is specified by the addressing mode register (AMR), described in Section 2.8.3.

All registers can perform linear addressing. Only eight registers can perform circular addressing: A4-A7 are used by the .D1 unit, and B4-B7 are used by the .D2 unit. No other units can perform circular addressing. LDB(U)/LDH(U)/LDW, STB/STH/STW, LDNDW, LDNW, STNDW, STNW, LDDW, STDW, ADDAB/ADDAH/ADDAW/ADDAD, and SUBAB/SUBAH/SUBAW instructions all use AMR to determine what type of address calculations are performed for these registers. There is no SUBAD instruction.

3.9.1 Linear Addressing Mode

3.9.1.1 LD and ST Instructions

For load and store instructions, linear mode simply shifts the *offsetR/cst* operand to the left by 3, 2, 1, or 0 for doubleword, word, halfword, or byte access, respectively; and then performs an add or a subtract to *baseR* (depending on the operation specified). The **LDNDW** and **STNDW** instructions also support nonscaled offsets. In nonscaled mode, the *offsetR/cst* is not shifted before adding or subtracting from the *baseR*.

For the preincrement, predecrement, positive offset, and negative offset address generation options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of *baseR* before the addition or subtraction is the address to be accessed from memory.

3.9.1.2 ADDA and SUBA Instructions

For integer addition and subtraction instructions, linear mode simply shifts the *src1/cst* operand to the left by 3, 2, 1, or 0 for doubleword, word, halfword, or byte data sizes, respectively, and then performs the add or subtract specified.



Addressing Modes www.ti.com

3.9.2 Circular Addressing Mode

The BK0 and BK1 fields in AMR specify the block sizes for circular addressing, see Section 2.8.3.

3.9.2.1 LD and ST Instructions

As with linear address arithmetic, offsetR/cst is shifted left by 3, 2, 1, or 0 according to the data size, and is then added to or subtracted from baseR to produce the final address. Circular addressing modifies this slightly by only allowing bits N through 0 of the result to be updated, leaving bits 31 through N + 1 unchanged after address arithmetic. The resulting address is bounded to $2^{(N+1)}$ range, regardless of the size of the offsetR/cst.

The circular buffer size in AMR is not scaled; for example, a block-size of 8 is 8 bytes, not 8 times the data size (byte, halfword, word). So, to perform circular addressing on an array of 8 words, a size of 32 should be specified, or N = 4. Example 3-4 shows an **LDW** performed with register A4 in circular mode and BKO = 4, so the buffer size is 32 bytes, 16 halfwords, or 8 words. The value in AMR for this example is 0004 0001h.

Example 3-4. LDW Instruction in Circular Mode

LDW .D1 *++A4[9],A1	
---------------------	--

	Before LDW		1 cycle after LDW (1)		5 cycles after LDW
A4	0000 0100h	A4	0000 0104h	A4	0000 0104h
A1	xxxx xxxxh	A1	xxxx xxxxh	A1	1234 5678h
mem 104h	1234 5678h	mem 104h	1234 5678h	mem 104h	1234 5678h

⁽¹⁾ **Note:** 9h words is 24h bytes. 24h bytes is 4 bytes beyond the 32-byte (20h) boundary 100h-11Fh; thus, it is wrapped around to (124h - 20h = 104h).

3.9.2.2 ADDA and SUBA Instructions

As with linear address arithmetic, offsetR/cst is shifted left by 3, 2, 1, or 0 according to the data size, and is then added to or subtracted from baseR to produce the final address. Circular addressing modifies this slightly by only allowing bits N through 0 of the result to be updated, leaving bits 31 through N + 1 unchanged after address arithmetic. The resulting address is bounded to $2^{(N+1)}$ range, regardless of the size of the offsetR/cst.

The circular buffer size in AMR is not scaled; for example, a block size of 8 is 8 bytes, not 8 times the data size (byte, halfword, word). So, to perform circular addressing on an array of 8 words, a size of 32 should be specified, or N = 4. Example 3-5 shows an **ADDAH** performed with register A4 in circular mode and BKO = 4, so the buffer size is 32 bytes, 16 halfwords, or 8 words. The value in AMR for this example is $0004\ 0001h$.

Example 3-5. ADDAH Instruction in Circular Mode

	Before ADDAH		1 cycle after ADDAH (1)
A4	0000 0100h	A4	0000 0106h
Α1	0000 0013h	A1	0000 0013h

⁽¹⁾ **Note:** 13h halfwords is 26h bytes. 26h bytes is 6 bytes beyond the 32-byte (20h) boundary 100h-11Fh; thus, it is wrapped around to (126h - 20h = 106h).



www.ti.com Addressing Modes


3.9.2.3 Circular Addressing Considerations with Nonaligned Memory

Circular addressing may be used with nonaligned accesses. When circular addressing is enabled, address updates and memory accesses occur in the same manner as for the equivalent sequence of byte accesses.

On the CPU, the circular buffer size must be at least 32 bytes. Nonaligned access to circular buffers that are smaller than 32 bytes will cause undefined results.

Nonaligned accesses to a circular buffer apply the circular addressing calculation to *logically adjacent* memory addresses. The result is that nonaligned accesses near the boundary of a circular buffer will correctly read data from both ends of the circular buffer, thus seamlessly causing the circular buffer to "wrap around" at the edges.

Consider, for example, a circular buffer size of 16 bytes. A circular buffer of this size at location 20h, would look like this in physical memory:



The effect of circular buffering is to make it so that memory accesses and address updates in the 20h-2Fh range stay completely inside this range. Effectively, the memory map behaves in this manner:



Example 3-6 shows an **LDNW** performed with register A4 in circular mode and BK0 = 4, so the buffer size is 32 bytes, 16 halfwords, or 8 words. The value in AMR for this example is 0004 0001h. The buffer starts at address 0020h and ends at 0040h. The register A4 is initialized to the address 003Ah.

Example 3-6. LDNW in Circular Mode



	Before LDNW	1 cycle after LDNW ⁽¹⁾		5 cycles after LDNW	
A4	0000 003Ah	A4	0000 0022h	A4	0000 0022h
A1	xxxx xxxxh	A1	xxxx xxxxh	A1	5678 9ABCh
mem 0022h	5678 9ABCh	mem 0022h	5678 9ABCh	mem 0022h	5678 9ABCh

Note: 2h words is 8h bytes. 8h bytes is 2 bytes beyond the 32-byte (20h) boundary starting at address 003Ah; thus, it is wrapped around to 0022h (003Ah + 8h = 0022h).



Addressing Modes www.ti.com

3.9.3 Syntax for Load/Store Address Generation

The DSP has a load/store architecture, which means that the only way to access data in memory is with a load or store instruction. Table 3-10 shows the syntax of an indirect address to a memory location. Sometimes a large offset is required for a load/store. In this case, you can use the B14 or B15 register as the base register, and use a 15-bit constant (*ucst15*) as the offset.

Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

Table 3-10. Indirect Address Generation for Load/Store

Addressing Type	No Modification of Address Register	Preincrement or Predecrement of Address Register	Postincrement or Postdecrement of Address Register
Register indirect	*R	*++R	*R++
		*R	*R
Register relative	*+R[<i>ucst5</i>]	*++R[<i>ucst5</i>]	*R++[<i>ucst5</i>]
	*-R[<i>ucst5</i>]	*R[<i>ucst5</i>]	*R[<i>ucst5</i>]
Register relative with 15-bit constant offset	*+B14/B15[ucst15]	not supported	not supported
Base + index	*+R[offsetR]	*++R[offsetR]	*R++[offsetR]
	*-R[<i>offsetR</i>]	*R[offsetR]	*R[<i>offsetR</i>]

Table 3-11. Address Generator Options for Load/Store

	Mode	Field		Syntax	Modification Performed
0	0	0	0	*-R[ucst5]	Negative offset
0	0	0	1	*+R[<i>ucst5</i>]	Positive offset
0	1	0	0	*-R[offsetR]	Negative offset
0	1	0	1	*+R[offsetR]	Positive offset
1	0	0	0	*R[<i>ucst5</i>]	Predecrement
1	0	0	1	*++R[<i>ucst5</i>]	Preincrement
1	0	1	0	*R[<i>ucst5</i>]	Postdecrement
1	0	1	1	*R++[<i>ucst5</i>]	Postincrement
1	1	0	0	*R[offsetR]	Predecrement
1	1	0	1	*++R[offsetR]	Preincrement
1	1	1	0	*R[offsetR]	Postdecrement
1	1	1	1	*R++[offsetR]	Postincrement



3.10 Compact Instructions on the CPU

The CPU supports a header based set of 16-bit-wide compact instructions in addition to the normal 32-bit wide instructions.

3.10.1 Compact Instruction Overview

The availability of compact instructions is enabled by the replacement of the eighth word of a fetch packet with a 32-bit header word. The header word describes which of the other seven words of the fetch packet contain compact instructions, which of the compact instructions in the fetch packet operate in parallel, and also contains some decoding information which supplements the information contained in the 16-bit compact opcode. Table 3-12 compares the standard fetch packet with a header-based fetch packet containing compact instructions.

Table 3-12. CPU Fetch Packet Types

Word		
0	16-bit opcode	16-bit opcode
1	32-bit (opcode
2	16-bit opcode	16-bit opcode
3	32-bit (opcode
4	16-bit opcode	16-bit opcode
5	32-bit (opcode
6	16-bit opcode	16-bit opcode
7	Hea	ader
	1 2 3 4 5	1 32-bit of 16-bit opcode 3 32-bit of 4 16-bit opcode 5 32-bit of 6 16-bit opcode

Within the other seven words of the fetch packet, each word may be composed of a single 32-bit opcode or two 16-bit opcodes. The header word specifies which words contain compact opcodes and which contain 32-bit opcodes.

The compiler will automatically code instructions as 16-bit compact instructions when possible.

There are a number of restrictions to the use of compact instructions:

- No dedicated predication field
- 3-bit register address field
- Very limited 3 operand instructions
- Subset of 32-bit instructions



3.10.2 Header Word Format

Figure 3-5 describes the format of the compact instruction header word.

Figure 3-5. Compact Instruction Header Format

31	30	29	28	27 21	20 14	13 0
1	1	1	0	Layout	Expansion	p-bits
				7	7	14

Bits 27-21 (Layout field) indicate which words in the fetch packet contain 32-bit opcodes and which words contain two 16-bit opcodes.

Bits 20-14 (Expansion field) contain information that contributes to the decoding of all compact instructions in the fetch packet.

Bits 13-0 (p-bits field) specify which compact instructions are run in parallel.

3.10.2.1 Layout Field in Compact Header Word

Bits 27-21 of the compact instruction header contains the layout field. This field specifies which of the other seven words in the current fetch packet contain 32-bit full-sized instructions and which words contain two 16-bit compact instructions.

Figure 3-6 shows the layout field in the compact header word and Table 3-13 describes the bits.

Figure 3-6. Layout Field in Compact Header Word

27	26	25	24	23	22	21
L7	L6	L5	L4	L3	L2	L1

Table 3-13. Layout Field Description in Compact Instruction Packet Header

Bit	Field	Value	Description
27	L7	0	Seventh word of fetch packet contains a single 32-bit opcode.
		1	Seventh word of fetch packet contains two 16-bit compact instructions.
26	L6	0	Sixth word of fetch packet contains a single 32-bit opcode.
		1	Sixth word of fetch packet contains two 16-bit compact instructions.
25	L5	0	Fifth word of fetch packet contains a single 32-bit opcode.
		1	Fifth word of fetch packet contains two 16-bit compact instructions.
24	L4	0	Fourth word of fetch packet contains a single 32-bit opcode.
		1	Fourth word of fetch packet contains two 16-bit compact instructions.
23	L3	0	Third word of fetch packet contains a single 32-bit opcode.
		1	Third word of fetch packet contains two 16-bit compact instructions.
22	L2	0	Second word of fetch packet contains a single 32-bit opcode.
		1	Second word of fetch packet contains two 16-bit compact instructions.
21	L1	0	First word of fetch packet contains a single 32-bit opcode.
		1	First word of fetch packet contains two 16-bit compact instructions.



3.10.2.2 Expansion Field in Compact Header Word

Bits 20-14 of the compact instruction header contains the opcode expansion field. This field specifies properties that apply to all compact instructions contained in the current fetch packet.

Figure 3-7 shows the expansion field in the compact header word and Table 3-14 describes the bits.

Figure 3-7. Expansion Field in Compact Header Word

20	19	18		16	15	14	
PROT	RS		DSZ		BR	SAT	1

Table 3-14. Expansion Field Description in Compact Instruction Packet Header

Bit	Field	Value	Description
20	PROT	0	Loads are nonprotected (NOPs must be explicit).
		1	Loads are protected (4 NOP cycles added after every LD instruction).
19	RS	0	Instructions use low register set for data source and destination.
		1	Instructions use high register set for data source and destination.
18-16	DSZ	0-7h	Defines primary and secondary data size (see Table 3-15)
15	BR	0	Compact instructions in the S unit are not decoded as branches
		1	Compact Instructions in the S unit are decoded as branches.
14	SAT	0	Compact instructions do not saturate.
		1	Compact instructions saturate.

Bit 20 (PROT) selects between protected and nonprotected mode for all **LD** instructions within the fetch packet. When PROT is 1, four cycles of NOP are added after each **LD** instruction within the fetch packet whether the **LD** is in 16-bit compact format or 32-bit format.

Bit 19 (RS) specifies which register set is used by compact instructions within the fetch packet. The register set defines which subset of 8 registers on each side are data registers. The 3-bit register field in the compact opcode indicates which one of eight registers is used. When RS is 1, the high register set (A16-A23 and B16-B23) is used; when RS is 0, the low register set (A0-A7 and B0-B7) is used.

Bits 18-16 (DSZ) determine the two data sizes available to the compact versions of the **LD** and **ST** instructions in a fetch packet. Bit 18 determines the primary data size that is either word (W) or doubleword (DW). In the case of DW, an opcode bit selects between aligned (DW) and nonaligned (NDW) accesses. Bits 17 and 16 determine the secondary data size: byte unsigned (BU), byte (B), halfword unsigned (HU), halfword (W), or nonaligned word (NW). Table 3-15 describes how the bits map to data size.

Bit 15 (BR). When BR is 1, instructions in the S unit are decoded as branches.

Bit 14 (SAT). When SAT is 1, the **ADD**, **SUB**, **SHL**, **MPY**, **MPYH**, **MPYLH**, and **MPYHL** instructions are decoded as **SADD**, **SUBS**, **SSHL**, **SMPY**, **SMPYH**, **SMPYLH**, and **SMPYHL**, respectively.



Table 3-15. LD/ST Data Size Selection

	DSZ Bits		Primary	Secondary	
18	17	16	Data Size (1)	Data Size (2)	
0	0	0	W	BU	
0	0	1	W	В	
0	1	0	W	HU	
0	1	1	W	Н	
1	0	0	DW/NDW	W	
1	0	1	DW/NDW	В	
1	1	0	DW/NDW	NW	
1	1	1	DW/NDW	Н	

⁽¹⁾ Primary data size is word W) or doubleword (DW). In the case of DW, aligned (DW) or nonaligned (NDW).

⁽²⁾ Secondary data size is byte unsigned (BU), byte (B), halfword unsigned (HU), halfword (H), word (W), or nonaligned word (NW).



3.10.2.3 P-bit Field in Compact Header Word

Unlike normal 32-bit instructions in which the *p*-bit filed in each opcode determines whether the instruction executes in parallel with other instructions; the parallel/nonparallel execution information for compact instructions is contained in the compact instruction header word.

Bits 13-0 of the compact instruction header contain the *p*-bit field. This field specifies which of the compact instructions within the current fetch packet are executed in parallel. If the corresponding bit in the layout field is 0 (indicating that the word is a noncompact instruction), then the bit in the *p*-bit field must be zero; that is, 32-bit instructions within compact fetch packets use their own *p*-bit field internal to the 32-bit opcode; therefore, the associated *p*-bit field in the header should always be zero.

Figure 3-8 shows the p-bits field in the compact header word and Table 3-16 describes the bits.

Figure 3-8. P-bits Field in Compact Header Word

13	12	11	10	9	8	7	6	5	4	3	2	1	0
P13	P12	P11	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1	P0

Table 3-16. P-bits Field Description in Compact Instruction Packet Header

Bit	Field	Value	Description
13	P13	0	Word 6 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 6 (16 most-significant bits) of fetch packet has parallel bit set.
12	P12	0	Word 6 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 6 (16 least-significant bits) of fetch packet has parallel bit set.
11	P11	0	Word 5 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 5 (16 most-significant bits) of fetch packet has parallel bit set.
10	P10	0	Word 5 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 5 (16 least-significant bits) of fetch packet has parallel bit set.
9	P9	0	Word 4 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 4 (16 most-significant bits) of fetch packet has parallel bit set.
8	P8	0	Word 4 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 4 (16 least-significant bits) of fetch packet has parallel bit set.
7	P7	0	Word 3 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 3 (16 most-significant bits) of fetch packet has parallel bit set.
6	P6	0	Word 3 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 3 (16 least-significant bits) of fetch packet has parallel bit set.
5	P5	0	Word 2 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 2 (16 most-significant bits) of fetch packet has parallel bit set.
4	P4	0	Word 2 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 2 (16 least-significant bits) of fetch packet has parallel bit set.
3	P3	0	Word 1 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 1 (16 most-significant bits) of fetch packet has parallel bit set.
2	P2	0	Word 1 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 1 (16 least-significant bits) of fetch packet has parallel bit set.
1	P1	0	Word 0 (16 most-significant bits) of fetch packet has parallel bit cleared.
		1	Word 0 (16 most-significant bits) of fetch packet has parallel bit set.
0	P0	0	Word 0 (16 least-significant bits) of fetch packet has parallel bit cleared.
		1	Word 0 (16 least-significant bits) of fetch packet has parallel bit set.



3.10.3 Processing of Fetch Packets

The header information is used to fully define the 32-bit version of the 16-bit instructions. In the case where an execute packet crosses fetch packet boundaries, there are two headers in use simultaneously. Each instruction uses the header information from its fetch packet header.

3.10.4 Execute Packet Restrictions

Execute packets that span fetch packet boundaries may not be the target of branches in the case where one of the two fetch packets involved are header-based. The only exception to this is where an interrupt is taken in the cycle before a spanning execute packet reaches E1. The target of the return may be a normally disallowed target.

If the execute packet contains eight instructions, then neither of the two fetch packets may be header-based.

3.10.5 Available Compact Instructions

Table 3-17 lists the available compact instructions and their functional unit.

Table 3-17. Available Compact Instructions

Instruction	L Unit	M Unit	S Unit	D Unit
ADD	✓		✓	✓
ADDAW				✓
ADDK			✓	
AND	✓			
BNOP displacement			✓	
CALLP			✓	
CLR			✓	
CMPEQ	✓			
CMPGT	✓			
CMPGTU	✓			
CMPLT	✓			
CMPLTU	✓			
EXT			✓	
EXTU			✓	
LDB				✓
LDBU				✓
LDDW				✓
LDH				✓
LDHU				✓
LDNDW				✓
LDNW				✓
LDW				✓
LDW (15-bit offset)				✓
MPY		✓		
MPYH		✓		
MPYHL		✓		
MPYLH		✓		
MV	✓		✓	✓
MVC			✓	
MVK	✓		✓	✓
NEG	✓			



www.ti.com Instruction Compatibility

Table 3-17. Available Compact Instructions (continued)

Instruction	L Unit	M Unit	S Unit	D Unit
NOP		No	unit	
OR	✓			
SADD	✓		✓	
SET			✓	
SHL			✓	
SHR			✓	
SHRU			✓	
SMPY		✓		
SMPYH		✓		
SMPYHL		✓		
SMPYLH		✓		
SPKERNEL		No	unit	
SPLOOP		No	unit	
SPLOOPD		No	unit	
SPMASK		No	unit	
SPMASKR		No	unit	
SSHL			✓	
SSUB	✓			
STB				✓
STDW				✓
STH				✓
STNDW				✓
STNW				✓
STW				✓
STW (15-bit offset)				✓
SUB	✓		✓	✓
SUBAW				✓
XOR	✓			

3.11 Instruction Compatibility

See Appendix A for a list of the instructions that are common to the C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs.



Instruction Descriptions www.ti.com

3.12 Instruction Descriptions

This section gives detailed information on the instruction set. Each instruction may present the following information:

- Assembler syntax
- Functional units
- Operands
- Opcode
- Description
- Execution
- Pipeline
- Instruction type
- Delay slots
- Functional Unit Latency
- Examples

The **ADD** instruction is used as an example to familiarize you with the way each instruction is described. The example describes the kind of information you will find in each part of the individual instruction description and where to obtain more information.



Example

The way each instruction is described.

Syntax

EXAMPLE (.unit) src, dst

.unit = .L1, .L2, .S1, .S2, .D1, .D2

src and dst indicate source and destination, respectively. The (.unit) dictates which functional unit the instruction is mapped to (.L1, .L2, .S1, .S2, .M1, .M2, .D1, or .D2).

A table is provided for each instruction that gives the opcode map fields, units the instruction is mapped to, types of operands, and the opcode.

The opcode shows the various fields that make up each instruction. These fields are described in Table 3-2.

There are instructions that can be executed on more than one functional unit. Table 3-18 shows how this is documented for the **ADD** instruction. This instruction has three opcode map fields: src1, src2, and dst. In the fifth group, the operands have the types cst5, long,and long for src1, src2, and dst, respectively. The ordering of these fields implies $cst5 + long \rightarrow long$, where + represents the operation being performed by the **ADD**. This operation can be done on .L1 or .L2 (both are specified in the unit column). The s in front of each operand signifies that src1 (scst5), src2 (slong), and dst (slong) are all signed values.

In the ninth group, *src1*, *src2*, and *dst* are *int*, *cst5*, and *int*, respectively. The *u* in front of the *cst5* operand signifies that *src1* (*ucst5*) is an unsigned value. Any operand that begins with *x* can be read from a register file that is different from the destination register file. The operand comes from the register file opposite the destination, if the x bit in the instruction is set (shown in the opcode map).

Description

Instruction execution and its effect on the rest of the processor or memory contents are described. Any constraints on the operands imposed by the processor or the assembler are discussed. The description parallels and supplements the information given by the execution block.

Execution

The execution describes the processing that takes place when the instruction is executed. The symbols are defined in Table 3-1. For example:

Execution for .L1, .L2 and .S1, .S2 Opcodes

if (cond) $src1 + src2 \rightarrow dst$ else nop

Execution for .D1, .D2 Opcodes

if (cond) $src2 + src1 \rightarrow dst$ else nop

Pipeline

This section contains a table that shows the sources read from, the destinations written to, and the functional unit used during each execution cycle of the instruction.

Instruction Type

This section gives the type of instruction. See Section 4.2 for information about the pipeline execution of this type of instruction.

Delay Slots

This section gives the number of delay slots the instruction takes to execute See Section 3.4 for an explanation of delay slots.



Functional Unit Latency This section gives the number of cycles that the functional unit is in use during the execution of the instruction.

Example

Examples of instruction execution. If applicable, register and memory values are given before and after instruction execution.

Table 3-18. Relationships Between Operands, Operand Size, Functional Units, and Opfields for Example Instruction (ADD)

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	000 0011
src2	xsint		
dst	sint		
src1	sint	.L1, .L2	010 0011
src2	xsint		
dst	slong		
src1	xsint	.L1, .L2	010 0001
src2	slong		
dst	slong		
src1	scst5	.L1, .L2	000 0010
src2	xsint		
dst	sint		
src1	scst5	.L1, .L2	010 0000
src2	slong		
dst	slong		
src1	sint	.S1, .S2	00 0111
src2	xsint		
dst	sint		
src1	scst5	.S1, .S2	00 0110
src2	xsint		
dst	sint		
src2	sint	.D1, .D2	01 0000
src1	sint		
dst	sint		
src2	sint	.D1, .D2	01 0010
src1	ucst5		
dst	sint		



ABS Absolute Value With Saturation

Syntax ABS (.unit) src2, dst

or

ABS (.unit) src2_h:src2_l,dst_h:dst_l

unit = .L1 or .L2

Opcode

31 2	29	28	27	23	22	18	17	16	15	14	13	12	11	5 4	3	2	1	0
creg		Z	dst		src2		0	0	0	0	0	Х	ор	1	1	0	s	p
3		1	5		5							1	7				1	1

Opcode map field used	For operand type	Unit	Opfield
src2 dst	xsint sint	.L1, .L2	001 1010
src2 dst	slong slong	.L1, L2	011 1000

Description

The absolute value of src2 is placed in dst.

The absolute value of src2 when src2 is an sint is determined as follows:

- 1. If src2 > 0, then $src2 \rightarrow dst$
- 2. If src2 < 0 and $src2 \neq -2^{31}$, then $-src2 \rightarrow dst$
- 3. If $src2 = -2^{31}$, then $2^{31} 1 \rightarrow dst$

The absolute value of src2 when src2 is an slong is determined as follows:

- 1. If src2 > 0, then $src2 \rightarrow dst_h:dst_l$
- 2. If src2 < 0 and $src2 \neq -2^{39}$, then $-src2 \rightarrow dst_h:dst_l$
- 3. If $src2 = -2^{39}$, then $2^{39} 1 \rightarrow dst_h: dst_l$

Execution

if (cond) else nop

 $abs(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L



Instruction Type Single-cycle

Delay Slots 0

See Also ABS2

Example 1

ABS .L1 A1,A5

	Before instruction			1 cycle after instruction	
A1	8000 4E3Dh	-2,147,463,619	A1	8000 4E3Dh	
A5	xxxx xxxxh		A5	7FFF B1C3h	2,147,463,619

Example 2

ABS .L1 A1,A5

	Before instruction			1 cycle after instruction	
A1	3FF6 0010h	1,073,086,480	A1	3FF6 0010h	
A5	xxxx xxxxh		A5	3FF6 0010h	1,073,086,480

Example 3

ABS .L1 A1:A0,A5:A4

	Before instruction			1 cycle after instruction	
A0	FFFF FFFFh	1,073,086,480	A0	FFFF FFFFh	1,073,086,480
A1	0000 00FFh		A1	0000 00FFh	
A4	xxxx xxxxh		A4	0000 0001h	
A5	xxxx xxxxh		A5	0000 0000h	




ABS2	Absolute	Value With	n Saturation,	Sianed.	Packed	16-Bit

Syntax ABS2 (.unit) src2, dst

unit = .L1 or .L2


Opcode



Opcode map field used	For operand type	Unit
src2	xs2	.L1, .L2
dst	s2	

Description

The absolute values of the upper and lower halves of the *src2* operand are placed in the upper and lower halves of the *dst*.



Specifically, this instruction performs the following steps for each halfword of *src2*, then writes its result to the appropriate halfword of *dst*:

- 1. If the value is between 0 and 2^{15} , then value $\rightarrow dst$
- 2. If the value is less than 0 and not equal to -2^{15} , then -value $\rightarrow dst$
- 3. If the value is equal to -2^{15} , then $2^{15} 1 \rightarrow dst$

NOTE: This operation is performed on each 16-bit value separately. This instruction does not affect the SAT bit in the CSR.

Execution

```
if (cond)  \{ \\ abs(lsb16(\textit{src2})) \rightarrow lsb16(\textit{dst}) \\ abs(msb16(\textit{src2})) \rightarrow msb16(\textit{dst}) \\ \} \\ else nop
```



Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ABS

Examples Example 1

ABS2 .L1 A0,A2

Before instruction				1 cycle after instruction	
A0	FF68 4E3Dh	-152 20029	A0	FF68 4E3Dh	
A2	xxxx xxxxh		A2	0098 4E3Dh	152 20029

Example 2

ABS2 .L1 A0,A2

	Before instruction			1 cycle after instruction	
A0	3FF6 F105h	16374 -3835	A0	3FF6 F105h	
A2	xxxx xxxxh		A2	3FF6 0EFBh	16374 3835






ABSDP Absolute Value, Double-Precision Floating-Point

Syntax ABSDP (.unit) src2, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
src2	xdp	.S1, .S2
dst	dp	

Description

The absolute value of *src2* is placed in *dst*. The 64-bit double-precision operand is read in one cycle by using the *src2* port for the 32 MSBs and the *src1* port for the 32 LSBs.

The absolute value of src2 is determined as follows:

- 1. If $src2 \ge 0$, then $src2 \rightarrow dst$
- 2. If src2 < 0, then $-src2 \rightarrow dst$

NOTE:

- If scr2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- If src2 is denormalized, +0 is placed in dst and the INEX and DEN2 bits are set.
- If src2 is +infinity or -infinity, +infinity is placed in dst and the INFO bit is set.

Execution

if (cond) else nop

 $abs(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src2_l, src2_h	
Written	dst_l	dst_h
Unit in use	.S	

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

ABSDP — Absolute Value, Double-Precision Floating-Point

www.ti.com

Instruction Type Two-cycle DP

Delay Slots 1
Functional Unit Latency 1

See Also ABS, ABSSP

Example ABSDP .S1 A1:A0,A3:A2

	Before instruction				2 cycles after instruction		
A1:A0	C004 0000h	0000 0000h	-2.5	A1:A0	C004 0000h	0000 0000h	
A3:A2	xxxx xxxxh	xxxx xxxxh		A3:A2	4004 0000h	0000 0000h	2.5




ABSSP Absolute Value, Single-Precision Floating-Point

Syntax ABSSP (.unit) src2, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit	
src2	xsp	.S1, .S2	
dst	sp		

Description

The absolute value of src2 is placed in dst.

The absolute value of *src2* is determined as follows:

- 1. If $src2 \ge 0$, then $src2 \rightarrow dst$
- 2. If src2 < 0, then $-src2 \rightarrow dst$

NOTE:

- If scr2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- If src2 is denormalized, +0 is placed in dst and the INEX and DEN2 bits are set.
- If src2 is +infinity or -infinity, +infinity is placed in dst and the INFO bit is set.

Execution

if (cond) else nop

 $abs(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.S



ABSSP — Absolute Value, Single-Precision Floating-Point

www.ti.com

Instruction Type Single-cycle

Delay Slots 0
Functional Unit Latency 1

See Also ABS, ABSDP

Example ABSSP .S1X B1,A5

	Before instruction		1 cycle after instruction		
B1	C020 0000h	-2.5	B1	C020 0000h	
A5	xxxx xxxxh		A5	4020 0000h	2.5



ADD

Add Two Signed Integers Without Saturation

Syntax

ADD (.unit) src1, src2, dst

or

ADD (.L1 or .L2) src1, src2_h:src2_l, dst_h:dst_l

or

ADD (.D1 or .D2) *src2*, *src1*, *dst* (if the cross path form is not used)

or

ADD (.D1 or .D2) *src1*, *src2*, *dst* (if the cross path form is used)

or

ADD (.D1 or .D2) src2, src1, dst (if the cross path form is used with a constant)

unit = .D1, .D2, .L1, .L2, .S1, .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L3	Figure D-4
	L3i	Figure D-5
	Lx1	Figure D-11
.S	S3	Figure F-22
	Sx2op	Figure F-29
	Sx1	Figure F-31
.D	Dx2op	Figure C-17
.L, .S, .D	LSDx1	Figure G-4

ADD — Add Two Signed Integers Without Saturation

www.ti.com

Opco	ode			.L unit														
31	29	28	27	23	22	18	17		13	12	11		5	4	3	2	1	0
CI	reg	Z		dst	src2			src1		Х		ор		1	1	0	s	p
	3	1	•	5	5		•	5		1		7			•		1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	000 0011
src2	xsint		
dst	sint		
src1	sint	.L1, .L2	010 0011
src2	xsint		
dst	slong		
src1	xsint	.L1, .L2	010 0001
src2	slong		
dst	slong		
src1	scst5	.L1, .L2	000 0010
src2	xsint	·	
dst	sint		
src1	scst5	.L1, .L2	010 0000
src2	slong	·	
dst	slong		

Opcode .S unit

31 29	28	27	23	22 18	17	13 12	6	6	5	4	3	2	1	0
creg	Z	dst		src2	src1	Х	ор		1	0	0	0	s	р
3	1	5		5	5	1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.S1, .S2	00 0111
src2	xsint	•	
dst	sint		
src1	scst5	.S1, .S2	00 0110
src2	xsint	•	
dst	sint		

Description for .L1, .L2 and .S1, .S2 Opcodes src2 is added to src1. The result is placed in dst.

Execution for .L1, .L2 and .S1, .S2 Opcodes

if (cond)
$$src1 + src2 \rightarrow dst$$
 else nop





Opcode	.D unit (if the cross path form is not used)

31 29	28	27 23	22 18	17 13	12 7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	ор	1	0	0	0	0	s	p
3	1	5	5	5	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	01 0000
src2 src1 dst	sint ucst5 sint	.D1, .D2	01 0010

Opcode

.D unit (if the cross path form is used)

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2	src1		Х	1	0	1	0	1	0	1	1	0	0	s	р
3		1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2	sint	.D1, .D2
src2	xsint	
dst	sint	

Opcode

.D unit (if the cross path form is used with a constant)

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	9	Z		dst	src2	src1		Х	1	0	1	0	1	1	1	1	0	0	S	р
3		1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	scst5	.D1, .D2
src2	xsint	
dst	sint	

Description for .D1, .D2 Opcodes src1 is added to src2. The result is placed in dst.

Execution for .D1, .D2 Opcodes

if (cond)
$$src2 + src1 \rightarrow dst$$

else nop



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single-cycle

Delay Slots 0

See Also ADDU, ADD2, SADD

Examples Example 1

ADD .L2X A1,B1,B2

	Before instructi	on		1 cycle after instruction
A1	0000 325Ah	12,890	A1	0000 325Ah
B1	FFFF FF12h	-238	B1	FFFF FF12h
B2	xxxx xxxxh		B2	0000 316Ch 12,652

Example 2

ADD .L1 A1,A3:A2,A5:A4

	Before instructio	n			1 cycle after inst	ruction	
A1	0000 325Ah	12,890		A1	0000 325Ah		
A3:A2	0000 00FFh	FFFF FF12h	-228 ⁽¹⁾	A3:A2	0000 00FFh	FFFF FF12h	
A5:A4	0000 0000h	0000 0000h		A5:A4	0000 0000h	0000 316Ch	12,652 ⁽¹⁾

⁽¹⁾ Signed 40-bit (long) integer

Example 3

ADD .L1 -13,A1,A6

	Before instruction			1 cycle after instru	ction
A1	0000 325Ah	12,890	A1	0000 325Ah	
A6	xxxx xxxxh		A6	0000 324Dh	12,877

Example 4

ADD .D1 A1,26,A6

	Before instruction			1 cycle after instru	ction
A1	0000 325Ah	12,890	A1	0000 325Ah	
A6	xxxx xxxxh		A6	0000 3274h	12,916



Example 5

ADD .D1 B0,5,A2

	Before instruction		1 cycle after instruc	ction
В0	0000 0007h	В0	0000 0007h	
A2	xxxx xxxxh	A2	0000 000Ch	12



ADDAB Add Using Byte Addressing Mode

Syntax ADDAB (.unit) src2, src1, dst

or

ADDAB (.unit) B14/B15, ucst15, dst

unit = .D1 or .D2

Opcode

31 2	9 28	27	23	22 18	17 13	12	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1	ор		1	0	0	0	0	s	p
3	1	5		5	5	6							1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	11 0000
src2 src1 dst	sint ucst <i>5</i> sint	.D1, .D2	11 0010

Description

src1 is added to *src2* using the byte addressing mode specified for *src2*. The addition defaults to linear mode. However, if *src2* is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).The result is placed in *dst*.

Execution

if (cond) $src2 + src1 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D





Opcode

3	1	30	29	28	27 23	22 8	7	6	5	4	3	2	1	0
(0	0	0	1	dst	ucst15	У	0	1	1	1	1	s	р
					5	15	1						1	1

Description

This instruction reads a register (baseR), B14 (y = 0) or B15 (y = 1), and adds a 15-bit unsigned constant (ucst15) to it, writing the result to a register (dst). This instruction is executed unconditionally, it cannot be predicated.

The offset, *ucst15*, is added to *baseR*. The result of the calculation is written into *dst*. The addressing arithmetic is always performed in linear mode.

The s bit determines the unit used (D1 or D2) and the file the destination is written to: s = 0 indicates the unit is D1 and dst is in the A register file; and s = 1 indicates the unit is D2 and dst is in the B register file.

Execution

B14/B15 + *ucst15* → *dst*

Pipeline

Pipeline Stage	E1
Read	B14/B15
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also ADDAD, ADDAH, ADDAW

Examples Example 1

ADDAB .D1 A4,A2,A4

	Before instruction (1)		1 cycle after instruction
A2	0000 000Bh	A2	0000 000Bh
A4	0000 0100h	A4	0000 0103h
AMR	0002 0001h	AMR	0002 0001h

⁽¹⁾ BK0 = 2: block size = 8

A4 in circular addressing mode using BK0

Example 2

ADDAB .D1X B14,42h,A4

	Before instruction (1)		1 cycle after instruction		
B14	0020 1000h	A4	0020 1042h		

⁽¹⁾ Using linear addressing.



Example 3

ADDAB .D2 B14,7FFFh,B4

	Before instruction (1)		1 cycle after instruction	on
B14	0010 0000h	B4	0010 7FFFh	

⁽¹⁾ Using linear addressing.






ADDAD Add Using Doubleword Addressing Mode

Syntax ADDAD (.unit) src2, src1, dst

unit = .D1 or .D2

Opcode



Opcode map field used	For operand type	Unit	Opfield
src2 src1	sint sint	.D1, .D2	11 1100
dst	sint		
src2 src1 dst	sint ucst5 sint	.D1, .D2	11 1101

Description

src1 is added to src2 using the doubleword addressing mode specified for src2. The addition defaults to linear mode. However, if src2 is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3). src1 is left shifted by 3 due to doubleword data sizes. The result is placed in dst.

NOTE: There is no SUBAD instruction.

Execution

if (cond) $src2 + src1 << 3 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also ADDAB, ADDAH, ADDAW



ADDAD — Add Using Doubleword Addressing Mode

www.ti.com

Example ADDAD .D1 A1,A2,A3

	Before instruction			1 cycle after instruction	
A1	0000 1234h	4660	A1	0000 1234h	
A2	0000 0002h	2	A2	0000 0002h	
А3	xxxx xxxxh		А3	0000 1244h	4676



ADDAH Add Using Halfword Addressing Mode

Syntax ADDAH (.unit) src2, src1, dst

or

ADDAH (.unit) B14/B15, ucst15, dst

unit = .D1 or .D2

Opcode

31 29	28	27 2	3 22 18	17 13	12	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	ор		1	0	0	0	0	s	p
3	1	5	5	5	6							1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	11 0100
src2 src1 dst	sint ucst <i>5</i> sint	.D1, .D2	11 0110

Description

src1 is added to *src2* using the halfword addressing mode specified for *src2*. The addition defaults to linear mode. However, if *src2* is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3). *src1* is left shifted by 1. The result is placed in *dst*.

Execution

if (cond) $src2 + src1 << 1 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D



Opcode

31	30	29	28	27 23	22 8	7	6	5	4	3	2	1	0
0	0	0	1	dst	ucst15	У	1	0	1	1	1	s	р
				5	15	1						1	1

Description

This instruction reads a register (baseR), B14 (y = 0) or B15 (y = 1), and adds a scaled 15-bit unsigned constant (ucst15) to it, writing the result to a register (dst). This instruction is executed unconditionally, it cannot be predicated.

The offset, *ucst15*, is scaled by a left-shift of 1 and added to *baseR*. The result of the calculation is written into *dst*. The addressing arithmetic is always performed in linear mode.

The s bit determines the unit used (D1 or D2) and the file the destination is written to: s = 0 indicates the unit is D1 and dst is in the A register file; and s = 1 indicates the unit is D2 and dst is in the B register file.

Execution

B14/B15 + (ucst15 << 1) → dst

Pipeline

Pipeline Stage	E 1
Read	B14/B15
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also ADDAB, ADDAD, ADDAW

Examples Example 1

ADDAH .D1 A4,A2,A4

	Before instruction (1)		1 cycle after instruction				
A2	0000 000Bh	A2	0000 000Bh				
A4	0000 0100h	A4	0000 0106h				
AMR	0002 0001h	AMR	0002 0001h				

⁽¹⁾ BK0 = 2: block size = 8

A4 in circular addressing mode using BK0

Example 2

ADDAH .D1X B14,42h,A4

	Before instruction (1)		1 cycle after instruction		
B14	0020 1000h	A4	0020 1084h		

⁽¹⁾ Using linear addressing.





Example 3

ADDAH .D2 B14,7FFFh,B4

	Before instruction (1)		1 cycle after instruction	n
B14	0010 0000h	B4	0010 FFFEh	

⁽¹⁾ Using linear addressing.



ADDAW

Add Using Word Addressing Mode

Syntax

ADDAW (.unit) src2, src1, dst

or

ADDAW (.unit) B14/B15, ucst15, dst

unit = .D1 or .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Dx5	Figure C-18
	Dx5p	Figure C-19

Opcode

31	29	28	27	23	22	8	17 13	12	7	6	5	4	3	2	1	0
	creg	Z	dst		src2		src1	ор		1	0	0	0	0	S	p
	3	1	5		5		5	6							1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	11 1000
src2 src1 dst	sint ucst5 sint	.D1, .D2	11 1010

Description

src1 is added to src2 using the word addressing mode specified for src2. The addition defaults to linear mode. However, if src2 is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3). src1 is left shifted by 2. The result is placed in dst.

Execution

if (cond) $src2 + src1 << 2 \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D





Opcode

31	30	29	28	27 23	22 8	7	6	5	4	3	2	1	0
0	0	0	1	dst	ucst15	У	1	1	1	1	1	S	р
				5	15	1						1	1

Description

This instruction reads a register (baseR), B14 (y = 0) or B15 (y = 1), and adds a scaled 15-bit unsigned constant (ucst15) to it, writing the result to a register (dst). This instruction is executed unconditionally, it cannot be predicated.

The offset, *ucst15*, is scaled by a left-shift of 2 and added to *baseR*. The result of the calculation is written into *dst*. The addressing arithmetic is always performed in linear mode.

The s bit determines the unit used (D1 or D2) and the file the destination is written to: s = 0 indicates the unit is D1 and dst is in the A register file; and s = 1 indicates the unit is D2 and dst is in the B register file.

Execution

 $B14/B15 + (ucst15 << 2) \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	B14/B15
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also ADDAB, ADDAD, ADDAH

Examples Example 1

ADDAW .D1 A4,2,A4

	Before instruction (1)		1 cycle after instruction
A4	0002 0000h	A4	0002 0000h
AMR	0002 0001h	AMR	0002 0001h

⁽¹⁾ BK0 = 2: block size = 8

A4 in circular addressing mode using BK0

Example 2

ADDAW .D1X B14,42h,A4

	Before instruction (1)		1 cycle after instruction	n
B14	0020 1000h	A4	0020 1108h	

(1) Using linear addressing.



Example 3

ADDAW .D2 B14,7FFFh,B4

	Before instruction (1)		1 cycle after instruction	n
B14	0010 0000h	B4	0011 FFFCh	

⁽¹⁾ Using linear addressing.



ADDDP Add Two Double-Precision Floating-Point Values

Syntax ADDDP (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode

31 29	28	27 2		17 13	12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	Х	ор		1	1	0	s	p
3	1	5	5	5	1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	dp xdp dp	.L1, .L2	001 1000
src1 src2 dst	dp xdp dp	.S1, .S2	111 0010

Description

src2 is added to src1. The result is placed in dst.

NOTE:

- This instruction takes the rounding mode from and sets the warning bits in the floating-point adder configuration register (FADCR), not in the floating-point auxiliary configuration register (FAUCR) as for other .S unit instructions.
- 2. If rounding is performed, the INEX bit is set.
- If one source is SNaN or QNaN, the result is NaN_out. If either source is SNaN, the INVAL bit is also set.
- If one source is +infinity and the other is -infinity, the result is NaN_out and the INVAL bit is set.
- If one source is signed infinity and the other source is anything except NaN or signed infinity of the opposite sign, the result is signed infinity and the INFO bit is set.
- If overflow occurs, the INEX and OVER bits are set and the results are rounded as follows (LFPN is the largest floating-point number):

Overflow Output Rounding Mode				
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+infinity	+LFPN	+infinity	+LFPN
-	-infinity	-LFPN	-LFPN	-infinity

 If underflow occurs, the INEX and UNDER bits are set and the results are rounded as follows (SPFN is the smallest floating-point number):

		Underflow Outpu	ut Rounding Mode	
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+0	+0	+SFPN	+0
-	-0	-0	-0	-SFPN



- 8. If the sources are equal numbers of opposite sign, the result is +0 unless the rounding mode is -infinity, in which case the result is -0.
- If the sources are both 0 with the same sign or both are denormalized with the same sign, the sign of the result is negative for negative sources and positive for positive sources.
- A signed denormalized source is treated as a signed 0 and the DENn bit is set. If the other source is not NaN or signed infinity, the INEX bit is set.

Execution

if (cond) $src1 + src2 \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7
Read	src1_l, src2_l	src1_h, src2_h					
Written						dst_l	dst_h
Unit in use	.L or .S	.L or .S					

The low half of the result is written out one cycle earlier than the high half. If *dst* is used as the source for the ADDDP, CMPEQDP, CMPLTDP, CMPGTDP, MPYDP, MPYSPDP, MPYSP2DP, or SUBDP instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type ADDDP/SUBDP

Delay Slots 6

Functional Unit Latency 2

See Also ADD, ADDSP, ADDU, SUBDP

Example ADDDP .L1X B1:B0,A3:A2,A5:A4

	Before instruction	l		7 cycles after in	struction	
B1:B0	4021 3333h	3333 3333h	B1:B0	4021 3333h	4021 3333h	8.6
A3:A2	C004 0000h	0000 0000h	A3:A2	C004 0000h	0000 0000h	-2.5
A5:A4	xxxx xxxxh	xxxx xxxxh	A5:A4	4018 6666h	6666 6666h	6.1





ADDK Add Signed 16-Bit Constant to Register

Syntax ADDK (.unit) cst, dst

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sx5	Figure F-30

Opcode

31 29	28	27 23	22	7	6	5	4	3	2	1	0
creg	Z	dst	cst16		1	0	1	0	0	s	p
3	1	5	16							1	1

Opcode map field used	For operand type	Unit
cst16	scst16	.S1, .S2
dst	uint	

Description A 16-bit signed constant, *cst16*, is added to the *dst* register specified. The result is

placed in dst.

Execution

if (cond) $cst16 + dst \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	cst16
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

Example ADDK .S1 15401,A1

	Before instruction			1 cycle after instruction	
A1	0021 37E1h	2,176,993	A1	0021 740Ah	2,192,394




ADDKPC

Add Signed 7-Bit Constant to Program Counter

Syntax

unit = .S2

Opcode



Opcode map field used	For operand type	Unit
src1 src2	scst7 ucst3	.S2
dst	uint	

Description

A 7-bit signed constant, *src1*, is shifted 2 bits to the left, then added to the address of the first instruction of the fetch packet that contains the **ADDKPC** instruction (PCE1). The result is placed in *dst*. The 3-bit unsigned constant, *src2*, specifies the number of NOP cycles to insert after the current instruction. This instruction helps reduce the number of instructions needed to set up the return address for a function call.

The following code:

LABEL

could be replaced by:

LABEL

The 7-bit value coded as *src1* is the difference between LABEL and PCE1 shifted right by 2 bits. The address of LABEL must be within 9 bits of PCE1.

Only one **ADDKPC** instruction can be executed per cycle. An **ADDKPC** instruction cannot be paired with any relative branch instruction in the same execute packet. If an **ADDKPC** and a relative branch are in the same execute packet, and if the **ADDKPC** instruction is executed when the branch is taken, behavior is undefined.

The **ADDKPC** instruction cannot be paired with any other multicycle **NOP** instruction in the same execute packet. Instructions that generate a multicycle **NOP** are: **IDLE**, **BNOP**, and the multicycle **NOP**.

Execution

if (cond)
$$(scst7 << 2) + PCE1 \rightarrow dst$$
 else nop





Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also B, BNOP

Example ADDKPC .S2 LABEL, B3, 4

LABEL:

Before instruction (1)		1 cycle after instruction
PCE1	0040 13DCh	
В3	xxxx xxxxh	B3 0040 13E0h

⁽¹⁾ LABEL is equal to 0040 13DCh.



ADDSP Add Two Single-Precision Floating-Point Values

Syntax ADDSP (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode

31 29	28	27 23	22 18	17 13	3 12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	ор		1	1	0	s	р
3	1	5	5	5	1	7					1	1

Opcode map field used	For operand type	Unit			
src1	sp	.L1, .L2	001 0000		
src2	xsp				
dst	sp				
src1	sp	.S1, .S2	111 0000		
src1 src2	xsp				
dst	sp				

Description

src2 is added to src1. The result is placed in dst.

NOTE:

- This instruction takes the rounding mode from and sets the warning bits in the floating-point adder configuration register (FADCR), not in the floating-point auxiliary configuration register (FAUCR) as for other .S unit instructions.
- 2. If rounding is performed, the INEX bit is set.
- If one source is SNaN or QNaN, the result is NaN_out. If either source is SNaN, the INVAL bit is also set.
- If one source is +infinity and the other is −infinity, the result is NaN_out and the INVAL bit is set.
- If one source is signed infinity and the other source is anything except NaN or signed infinity of the opposite sign, the result is signed infinity and the INFO bit is set.
- If overflow occurs, the INEX and OVER bits are set and the results are rounded as follows (LFPN is the largest floating-point number):

		Overflow Output	Rounding Mode	
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+infinity	+LFPN	+infinity	+LFPN
-	-infinity	-LFPN	-LFPN	-infinity

7. If underflow occurs, the INEX and UNDER bits are set and the results are rounded as follows (SPFN is the smallest floating-point number):

		Underflow Outpu	ıt Rounding Mode	
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+0	+0	+SFPN	+0
-	-0	-0	-0	-SFPN



- If the sources are equal numbers of opposite sign, the result is +0
 unless the rounding mode is -infinity, in which case the result is -0.
- 9. If the sources are both 0 with the same sign or both are denormalized with the same sign, the sign of the result is negative for negative sources and positive for positive sources.
- A signed denormalized source is treated as a signed 0 and the DENn bit is set. If the other source is not NaN or signed infinity, the INEX bit is set.

Execution

if (cond) $src1 + src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.L or .S			

Instruction Type 4-cycle

Delay Slots 3

Functional Unit Latency 1

See Also ADD, ADDSP, ADDU, SUBSP

Example ADDSP .L1 A1,A2,A3

	Before instruction		4 cycles after instruction					
A1	C020 0000h	A1	C020 0000h	-2.5				
A2	4109 999Ah	A2	4109 999Ah	8.6				
A3	xxxx xxxxh	А3	40C3 3334h	6.1				




ADDSUB Parallel ADD and SUB Operations On Common Inputs

Syntax ADDSUB (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	

Description The following is performed in parallel:

1. src2 is added to src1. The result is placed in dst_o.

2. src2 is subtracted from src1. The result is placed in dst_e.

Execution

$$src1 + src2 \rightarrow dst_o$$

 $src1 - src2 \rightarrow dst_e$

Instruction Type Single-cycle

Delay Slots 0

See Also ADDSUB2, SADDSUB

Examples Example 1

ADDSUB .L1 A0,A1,A3:A2

	Before instruction		1 cycle after instruction	
A0	0700 C005h	A2	0700 C006h	
A1	FFFF FFFFh	А3	0700 C004h	

Example 2

ADDSUB .L2X B0,A1,B3:B2

	Before instruction		1 cycle after instruction			
В0	7FFF FFFFh	B2	7FFF FFFEh			
A1	0000 0001h	В3	8000 0000h			



ADDSUB2 Parallel ADD2 and SUB2 Operations On Common Inputs

Syntax ADDSUB2 (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode

31	30	29	28	27	24	23	22 18	8 1	17 13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst		0	src2		src1	Х	0	0	0	1	1	0	1	1	1	0	S	р
				4			5		5	1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	

Description

For the **ADD2** operation, the upper and lower halves of the *src2* operand are added to the upper and lower halves of the *src1* operand. The values in *src1* and *src2* are treated as signed, packed 16-bit data and the results are written in signed, packed 16-bit format into *dst_o*.

For the **SUB2** operation, the upper and lower halves of the *src2* operand are subtracted from the upper and lower halves of the *src1* operand. The values in *src1* and *src2* are treated as signed, packed 16-bit data and the results are written in signed, packed 16-bit format into *dst_e*.

Execution

$$\begin{split} & \mathsf{lsb16}(\mathit{src1}) + \mathsf{lsb16}(\mathit{src2}) \to \mathsf{lsb16}(\mathit{dst_o}) \\ & \mathsf{msb16}(\mathit{src1}) + \mathsf{msb16}(\mathit{src2}) \to \mathsf{msb16}(\mathit{dst_o}) \\ & \mathsf{lsb16}(\mathit{src1}) - \mathsf{lsb16}(\mathit{src2}) \to \mathsf{lsb16}(\mathit{dst_e}) \\ & \mathsf{msb16}(\mathit{src1}) - \mathsf{msb16}(\mathit{src2}) \to \mathsf{msb16}(\mathit{dst_e}) \end{split}$$

Instruction Type Single-cycle

Delay Slots 0

See Also ADDSUB, SADDSUB2

Example 1

ADDSUB2 .L1 A0,A1,A3:A2

	Before instruction		1 cycle after instruction			
A0	0700 C005h	A2	0701 C004h			
A1	FFFF 0001h	А3	06FF C006h			

Example 2

ADDSUB2 .L2X B0,A1,B3:B2



ADDSUB2 — Parallel ADD2 and SUB2 Operations On Common Inputs

www.ti.com

	Before instruction		1 cycle after instruction	
В0	7FFF 8000h	B2	8000 8001h	
A1	FFFF FFFFh	В3	7FFE 7FFFh	

Example 3

ADDSUB2 .L1 A0,A1,A3:A2

	Before instruction		1 cycle after instruction
A0	9000 9000h	A2	1000 1000h
A1	8000 8000h	А3	1000 1000h

Example 4

ADDSUB2 .L1 A0,A1,A3:A2

	Before instruction		1 cycle after instruction	
A0	9000 8000h	A2	1000 F000h	
A1	8000 9000h	А3	1000 1000h	





ADDU Add Two Unsigned Integers Without Saturation

Syntax ADDU (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31	29	28	27	23	22	18	1/ 1-	3	12	11		5	4	3	2	1	0
creg	9	Z	ds	st	src2		src1		Χ		ор		1	1	0	s	p
3		1	5	5	5		5		1		7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint ulong	.L1, .L2	010 1011
src1 src2 dst	xuint ulong ulong	.L1, .L2	010 1001

Description src2 is added to src1. The result is placed in dst.

Execution

if (cond) $src1 + src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ADD, SADD



Example 1

ADDU .L1 A1,A2,A5:A4

	Before instruction	on		1 cycle after inst	ruction	
A1	0000 325Ah	12,890 ⁽¹⁾	A1	0000 325Ah		
A2	FFFF FF12h	4,294,967,058 ⁽¹⁾	A2	FFFF FF12h		
A5:A4	xxxx xxxxh		A5:A4	0000 0001h	0000 316Ch	4,294,979,948(2)

⁽¹⁾ Unsigned 32-bit integer

Example 2

ADDU .L1 A1,A3:A2,A5:A4

	Before instruct	ion			1 cycle after in	struction	
A1	0000 325Ah	12,890 ⁽¹⁾		A1	0000 325Ah		
A3:A2	0000 00FFh	FFFF FF12h	1,099,511,627,538(2)	A3:A2	0000 00FFh	FFFF FF12h	
A5:A4	0000 0000h	0000 0000h	0	A5:A4	0000 0000h	0000 316Ch	12,652 ⁽²⁾

⁽¹⁾ Unsigned 32-bit integer

⁽²⁾ Unsigned 40-bit (long) integer

⁽²⁾ Unsigned 40-bit (long) integer





ADD2 Add Two 16-Bit Integers on Upper and Lower Register Halves

Syntax ADD2 (.unit) src1, src2, dst

unit = .S1, .S2, .L1, .L2, .D1, .D2

Opcode .S unit

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	0	0	1	1	0	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src2	xi2	
dst	i2	

Opcode .L Unit

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	0	0	0	0	1	0	1	1	1	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src2	xi2	
src1 src2 dst	i2	

Opcode .D unit

31 29	28		23 22	18 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2	1	src1		Х	1	0	0	1	0	0	1	1	0	0	s	р
3	1	5	5		5		1											1	1


Opcode map field used	For operand type	Unit
src1	i2	.D1, .D2
src1 src2	xi2	
dst	i2	



Description

The upper and lower halves of the *src1* operand are added to the upper and lower halves of the *src2* operand. The values in *src1* and *src2* are treated as signed, packed 16-bit data and the results are written in signed, packed 16-bit format into *dst*.

For each pair of signed packed 16-bit values found in the *src1* and *src2*, the sum between the 16-bit value from *src1* and the 16-bit value from *src2* is calculated to produce a 16-bit result. The result is placed in the corresponding positions in the *dst*. The carry from the lower half add does not affect the upper half add.



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S, .L, .D

Instruction Type Single-cycle

Delay Slots 0

See Also ADD, ADD4, SADD2, SUB2

Examples Example 1

ADD2 .S1X A1,B1,A2

	Before instruction			1 cycle after instruction	
A1	0021 37E1h	33 14305	A1	0021 37E1h	
A2	xxxx xxxxh		A2	03BB 1C99h	955 7321
B1	039A E4B8h	922 58552	B1	039A E4B8h	



Example 2

ADD2 .L1 A0,A1,A2

	Before instruction			1 cycle after instruction	1
A0	0021 37E1h	33 14305 signed	A0	0021 37E1h	
A1	039A E4B8h	922 -6984 signed	A1	039A E4B8h	
A2	xxxx xxxxh		A2	03BB 1C99h	955 7321 signed



ADD4

Add Without Saturation, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

ADD4 (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 2	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	1	0	0	1	0	1	1	1	0	S	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i4	.L1, .L2
src2	xi4	
dst	i4	

Description

Performs 2s-complement addition between packed 8-bit quantities. The values in *src1* and *src2* are treated as packed 8-bit data and the results are written into *dst* in a packed 8-bit format.

For each pair of packed 8-bit values in *src1* and *src2*, the sum between the 8-bit value from *src1* and the 8-bit value from *src2* is calculated to produce an 8-bit result. No saturation is performed. The carry from one 8-bit add does not affect the add of any other 8-bit add. The result is placed in the corresponding positions in *dst*:

- The sum of src1 byte0 and src2 byte0 is placed in byte0 of dst.
- The sum of src1 byte1 and src2 byte1 is placed in byte1 of dst.
- The sum of src1 byte2 and src2 byte2 is placed in byte2 of dst.
- The sum of src1 byte3 and src2 byte3 is placed in byte3 of dst.

31	2	24 23	16 15		8 7		0			
	a_3	a_2		a_1		a_0	← src1			
•	+	+		+		+				
ADD4										
	b_3	b_2		b_1		b_0	← src2			
	=	=		=		=				
31	:	24 23	16 15		8 7		0			
	a_3 + b_3	a_2+b_2		a_1 + b_1		a_0 + b_0	← dst			



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ADD, ADD2, SADDU4, SUB4

Example 1

ADD4 .L1 A0,A1,A2

	Before instruction			1 cycle after instruction	
A0	FF 68 4E 3Dh	-1 104 78 61	A0	FF 68 4E 3Dh	
A1	3F F6 F1 05h	63 -10 -15 5	A1	3F F6 F1 05h	
A2	xxxx xxxxh		A2	3E 5E 3F 42h	62 94 63 66

Example 2

ADD4 .L1 A0,A1,A2

	Before instruction			1 cycle after instruction	
A0	4A E2 D3 1Fh	74 226 211 31	A0	4A E2 D3 1Fh	
A1	32 1A C1 28h	50 26 -63 40	A1	32 1A C1 28h	
A2	xxxx xxxxh		A2	7C FC 94 47h	124 252 148 71



AND — Bitwise AND www.ti.com

AND

Syntax AND (.unit) src1, src2, dst

Bitwise AND

unit = .L1, .L2, .S1, .S2, .D1, .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7

Opcode .L unit

31 29	28	27	23	22 18	17	13 1	2	11 5	5	4	3	2	1	0
creg	Z	dst		src2	src1	>		ор		1	1	0	S	p
3	1	5		5	5	1	1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.L1, .L2	111 1011
src1 src2 dst	scst5 xuint uint	.L1, .L2	111 1010

Opcode .S unit

31	29	28	27	23	22 18	17	13	12	11	6	5	4	3	2	1	0
cre	g	Z		dst	src2	src1		Х	ор		1	0	0	0	s	р
3		1		5	5	5		1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src1	uint	.S1, .S2	01 1111
src2	xuint	·	
dst	uint		
src1	scst5	.S1, .S2	01 1110
src2	xuint	•	
dst	uint		



www.ti.com AND — Bitwise AND

Орс	ode			.D unit																	
31	29	28	27	23	22		18	17		13	12	11	10	9	6	5	4	3	2	1	0
C	reg	Z		dst		src2			src1		Х	1	0	0	ט	1	1	0	0	s	p
	3	1		5		5			5		1									1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.D1, .D2	0110
src1 src2 dst	scst5 xuint uint	.D1, .D2	0111

Description Performs a bitwise AND operation between *src1* and *src2*. The result is placed in *dst*.

The scst5 operands are sign extended to 32 bits.

Execution

if (cond) $src1 \text{ AND } src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single-cycle

Delay Slots 0

See Also ANDN, OR, XOR

Examples Example 1

AND .L1X A1,B1,A2

	Before instruction	1 cycle after instruction
A1	F7A1 302Ah	A1 F7A1 302Ah
A2	xxxx xxxxh	A2 02A0 2020h
B1	02B6 E724h	B1 02B6 E724h



AND — Bitwise AND www.ti.com

Example 2

AND .L1 15,A1,A3

	Before instruction	1 cycle after instruction
A1	32E4 6936h	A1 32E4 6936h
А3	xxxx xxxxh	A3 0000 0006h



www.ti.com



ANDN Bitwise AND Invert

ANDN (.unit) src1, src2, dst **Syntax**

unit = .L1, .L2, S1, .S2, .D1, .D2

Opcode .L unit

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	1	1	1	0	0	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.L1, .L2
src2	xuint	
dst	uint	

Opcode .S unit

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
C	reg	Z	a	lst	src2	src1		Х	1	1	0	1	1	0	1	1	0	0	s	р
	3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.S1, .S2
src2	xuint	
dst	uint	

Opcode .D unit

31 29	28	27	23 22	18 17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2		src1	х	1	0	0	0	0	0	1	1	0	0	s	p
3	1	5	5		5	1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	uint xuint uint	.D1, .D2

Description

Performs a bitwise logical AND operation between src1 and the bitwise logical inverse of src2. The result is placed in dst.



Execution

if (cond) $src1 \text{ AND } \sim src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single-cycle

Delay Slots 0

See Also AND, OR, XOR

Example ANDN .L1 A0,A1,A2

	Before instruction			1 cycle after instruction
A0	1957 21ABh		A0	1957 21ABh
A1	081C 17E6h	F7E3 E819h	A1	081C 17E6h
A2	xxxx xxxxh		A2	1143 2009h



Syntax AVG2 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src		Х	0	1	0	0	1	1	1	1	0	0	s	р
3	1	5		5	5		1											1	1


Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src1 src2	xs2	
dst	s2	

Description

Performs an averaging operation on packed 16-bit data. For each pair of signed 16-bit values found in *src1* and *src2*, **AVG2** calculates the average of the two values and returns a signed 16-bit quantity in the corresponding position in the *dst*.

The averaging operation is performed by adding 1 to the sum of the two 16-bit numbers being averaged. The result is then right-shifted by 1 to produce a 16-bit result.

No overflow conditions exist.



Execution

```
if (cond)  \{ \\ ((lsb16(src1) + lsb16(src2) + 1) >> 1) \rightarrow lsb16(dst); \\ ((msb16(src1) + msb16(src2) + 1) >> 1) \rightarrow msb16(dst); \\ \}  else nop
```



Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also AVGU4

Example AVG2 .M1 A0,A1,A2

	Before instruction			2 cycles after instruction	1
A0	6198 4357h	24984 17239	A0	6198 4357h	
A1	7582 AE15	30082 -20971	A1	7582 AE15h	
A2	xxxx xxxxh		A2	6B8D F8B6h	27533 -1866



AVGU4

Average, Unsigned, Packed 8-Bit

Syntax

```
AVGU4 (.unit) src1, src2, dst
```

unit = .M1 or .M2

Opcode

31 29	28		3 22 18	17 13		11	10	9 8	3 7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	0	1	0 (0	1	1	0	0	s	p
3	1	5	5	5	1										1	1


Opcode map field used	For operand type	Unit
src1	u4	.M1, .M2
src2	xu4	
dst	u4	

Description

Performs an averaging operation on packed 8-bit data. The values in src1 and src2 are treated as unsigned, packed 8-bit data and the results are written in unsigned, packed 8-bit format. For each unsigned, packed 8-bit value found in src1 and src2, **AVGU4** calculates the average of the two values and returns an unsigned, 8-bit quantity in the corresponding positions in the dst.

The averaging operation is performed by adding 1 to the sum of the two 8-bit numbers being averaged. The result is then right-shifted by 1 to produce an 8-bit result.

No overflow conditions exist.



Execution

```
if (cond)  \{ \\ ((\text{ubyte0}(\textit{src1}) + \text{ubyte0}(\textit{src2}) + 1) >> 1) \rightarrow \text{ubyte0}(\textit{dst}); \\ ((\text{ubyte1}(\textit{src1}) + \text{ubyte1}(\textit{src2}) + 1) >> 1) \rightarrow \text{ubyte1}(\textit{dst}); \\ ((\text{ubyte2}(\textit{src1}) + \text{ubyte2}(\textit{src2}) + 1) >> 1) \rightarrow \text{ubyte2}(\textit{dst}); \\ ((\text{ubyte3}(\textit{src1}) + \text{ubyte3}(\textit{src2}) + 1) >> 1) \rightarrow \text{ubyte3}(\textit{dst}) \\ \} \\ \text{else nop}
```



Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also AVG2

Example AVGU4 .M1 A0,A1,A2

	Before instruction			2 cycles after instructio	n
A0	1A 2E 5F 4Eh	26 46 95 78 unsigned	A0	1A 2E 5F 4Eh	
A1	9E F2 6E 3Fh	158 242 110 63 unsigned	A1	9E F2 6E 3Fh	
A2	xxxx xxxxh		A2	5C 90 67 47h	92 144 103 71 unsigned




B Branch Using a Displacement

Syntax

B (.unit) label

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
cst21	scst21	.S1, .S2

Description

A 21-bit signed constant, *cst21*, is shifted left by 2 bits and is added to the address of the first instruction of the fetch packet that contains the branch instruction. The result is placed in the program fetch counter (PFC). The assembler/linker automatically computes the correct value for *cst21* by the following formula:

If two branches are in the same execute packet and both are taken, behavior is undefined.

Two conditional branches can be in the same execute packet if one branch uses a displacement and the other uses a register, IRP, or NRP. As long as only one branch has a true condition, the code executes in a well-defined way.

NOTE:

- PCE1 (program counter) represents the address of the first instruction in the fetch packet in the E1 stage of the pipeline. PFC is the program fetch counter.
- The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- 3. See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.
- A relative branch instruction cannot be in the same execute packet as an ADDKPC instruction.

Execution

if (cond)
$$(cst21 \ll 2) + PCE1 \rightarrow PFC$$

else nop



Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read							
Written							
Branch taken							✓
Unit in use	.S						

Branch Instruction Type Delay Slots 5 Example Table 3-19 gives the program counter values and actions for the following code example. .S1 LOOP 0000 0000 0000 0004 ADD .L1 A1, A2, A3 8000 0000 ADD .L2 B1, B2, B3 0000 000C LOOP: .M1X A3, B3, A4 MPY 0000 0010 SUB .D1 A5, A6, A6 0000 0014 .M1 A3, A6, A5 .M1 A6, A7, A8 MPY 0000 0018 MPY 0000 001C SHR .S1 A4, 15, A4 0000 0020 ADD .D1 A4, A6, A4

Table 3-19. Program Counter Values for Branch Using a Displacement Example

Cycle	Program Counter Value	Action
Cycle 0	0000 0000h	Branch command executes (target code fetched)
Cycle 1	0000 0004h	
Cycle 2	0000 000Ch	
Cycle 3	0000 0014h	
Cycle 4	0000 0018h	
Cycle 5	0000 001Ch	
Cycle 6	0000 000Ch	Branch target code executes
Cycle 7	0000 0014h	






B Branch Using a Register

Syntax B (.unit) src2

unit = .S2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.S2

Description

src2 is placed in the program fetch counter (PFC).

If two branches are in the same execute packet and are both taken, behavior is undefined.

Two conditional branches can be in the same execute packet if one branch uses a displacement and the other uses a register, IRP, or NRP. As long as only one branch has a true condition, the code executes in a well-defined way.

NOTE:

- 1. This instruction executes on .S2 only. PFC is program fetch counter.
- The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.

Execution

if (cond) $src2 \rightarrow PFC$

else nop

Pipeline

		Target Instruction					
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	src2						
Written							
Branch taken							✓
Unit in use	.\$2						



Instruction Type	Branch		
Delay Slots	5		
Example	Table 3-20 gives the program In this example, the B10 regis		ues and actions for the following code example. e value 1000 000Ch.
	1000 0000 1000 0004 1000 0008 1000 000C 1000 0010 1000 0014 1000 0018 1000 001C 1000 0020	B ADD ADD MPY SUB MPY MPY STR MPY ADD	.S2 B10 .L1 A1, A2, A3 .L2 B1, B2, B3 .M1X A3, B3, A4 .D1 A5, A6, A6 .M1 A3, A6, A5 .M1 A6, A7, A8 .S1 A4, 15, A4 .D1 A4, A6, A4

Table 3-20. Program Counter Values for Branch Using a Register Example

Cycle	Program Counter Value	Action
Cycle 0	1000 0000h	Branch command executes (target code fetched)
Cycle 1	1000 0004h	
Cycle 2	1000 000Ch	
Cycle 3	1000 0014h	
Cycle 4	1000 0018h	
Cycle 5	1000 001Ch	
Cycle 6	1000 000Ch	Branch target code executes
Cycle 7	1000 0014h	





B IRP Branch Using an Interrupt Return Pointer

Syntax B (.unit) IRP

unit = .S2

Opcode

31	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z	0	0	0	0	0	0	0	1	1	0	0	0	0	0	0	0	0	0	0	0	1	1	1	0	0	0	1	р
3		1																												1

Description

IRP is placed in the program fetch counter (PFC). This instruction also moves the PGIE bit value to the GIE bit. The PGIE bit is unchanged.

If two branches are in the same execute packet and are both taken, behavior is undefined.

Two conditional branches can be in the same execute packet if one branch uses a displacement and the other uses a register, IRP, or NRP. As long as only one branch has a true condition, the code executes in a well-defined way.

NOTE:

- This instruction executes on .S2 only. PFC is the program fetch counter.
- 2. Refer to Chapter 5 for more information on IRP, PGIE, and GIE.
- The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.

Execution

if (cond) IRP \rightarrow PFC else nop

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	IRP						
Written							
Branch taken							✓
Unit in use	.S2						



Instruction Type Branch

Delay Slots 5

Example Table 3-21 gives the program counter values and actions for the following code example.

Given that an interrupt occurred at

PC = 0000 1000 IRP = 0000 1000 0000 0020 .S2 IRP В 0000 0024 ADD .S1 A0, A2, A1 MPY NOP SHR ADD 0000 0028 .M1 A1, A0, A1 0000 002C 0000 0030 .S1 A1, 15, A1 0000 0034 .L1 A1, A2, A1 0000 0038 ADD .L2 B1, B2, B3

Table 3-21. Program Counter Values for B IRP Instruction Example

Cycle	Program Counter Value	Action
Cycle 0	0000 0020	Branch command executes (target code fetched)
Cycle 1	0000 0024	
Cycle 2	0000 0028	
Cycle 3	0000 002C	
Cycle 4	0000 0030	
Cycle 5	0000 0034	
Cycle 6	0000 1000	Branch target code executes



B NRP Branch Using NMI Return Pointer

Syntax B (.unit) NRP

unit = .S2

Opcode

3	1 2	9	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg		Z	0	0	0	0	0	0	0	1	1	1	0	0	0	0	0	0	0	0	0	0	1	1	1	0	0	0	1	р
	3		1																												1

Description

NRP is placed in the program fetch counter (PFC). This instruction also sets the NMIE bit. The PGIE bit is unchanged.

If two branches are in the same execute packet and are both taken, behavior is undefined.

Two conditional branches can be in the same execute packet if one branch uses a displacement and the other uses a register, IRP, or NRP. As long as only one branch has a true condition, the code executes in a well-defined way.

NOTE:

- 1. This instruction executes on .S2 only. PFC is program fetch counter.
- 2. Refer to Chapter 5 for more information on NRP and NMIE.
- 3. The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- 4. See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.

Execution

if (cond) else nop $NRP \rightarrow PFC$

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	NRP						
Written							
Branch taken							✓
Unit in use	.\$2						



Instruction Type	Branch
------------------	--------

Delay Slots 5

Example Table 3-22 gives the program counter values and actions for the following code example.

Given that an interrupt occurred at PC = 0000 1000 IRP = 0000 1000

PC =	0000	TOOO	IRP	=	0000	1000			
0000	0020		В			.S2	NRP		
0000	0024		ΑI	DD		.S1	Α0,	A2,	A1
0000	0028		MI	PΥ		.M1	A1,	Α0,	A1
0000	002C		NO	DΡ					
0000	0030		SI	ΙR		.S1	A1,	15,	A1
0000	0034		ΑI	DD		.L1	A1,	A2,	A1
0000	0038		AI	DD		.L2	В1,	в2,	В3

Table 3-22. Program Counter Values for B NRP Instruction Example

Cycle	Program Counter Value	Action
Cycle 0	0000 0020	Branch command executes (target code fetched)
Cycle 1	0000 0024	
Cycle 2	0000 0028	
Cycle 3	0000 002C	
Cycle 4	0000 0030	
Cycle 5	0000 0034	
Cycle 6	0000 1000	Branch target code executes

158 Instruction Set SPRUFE8B-July 2010



BDEC Branch and Decrement

Syntax BDEC (.unit) src, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
src	scst10	.S1, .S2
dst	int	

Description

If the predication and decrement register (*dst*) is positive (greater than or equal to 0), the **BDEC** instruction performs a relative branch and decrements *dst* by 1. The instruction performs the relative branch using a 10-bit signed constant, *scst10*, in *src*. The constant is shifted 2 bits to the left, then added to the address of the first instruction of the fetch packet that contains the **BDEC** instruction (PCE1). The result is placed in the program fetch counter (PFC).

This instruction helps reduce the number of instructions needed to decrement a register and conditionally branch based upon the value of the register. Note also that any register can be used that can free the predicate registers (A0-A2 and B0-B2) for other uses.

The following code:

could be replaced by:

NOTE:

- Only one BDEC instruction can be executed per cycle. The BDEC instruction can be predicated by using any conventional condition register. The conditions are effectively ANDed together. If two branches are in the same execute packet, and if both are taken, behavior is undefined.
- See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.
- The BDEC instruction cannot be in the same execute packet as an ADDKPC instruction.



Execution

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	dst						
Written	dst, PC						
Branch taken							✓
Unit in use	.S						

Instruction Type Branch

Delay Slots 5

Example 1

BDEC .S1 100h,A10

	Before instruction	After branch has been taken
PCE1	0100 0000h	
PC	xxxx xxxxh	PC 0100 0400h
A10	0000 000Ah	A10 0000 0009h

Example 2

BDEC .S1 300h,A10 ; 300h is sign extended

	Before instruction	After branch has been tak
PCE1	0100 0000h	
PC	xxxx xxxxh	PC 00FF FC00h
A10	0000 0010h	A10 0000 000Fh

160 Instruction Set SPRUFE8B-July 2010



BITC4 Bit Count, Packed 8-Bit

Syntax BITC4 (.unit) src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		1	1	1	1	0	Х	0	0	0	0	1	1	1	1	0	0	s	р
3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	xu4	.M1, .M2
dst	u4	

Description

Performs a bit-count operation on 8-bit quantities. The value in *src2* is treated as packed 8-bit data, and the result is written in packed 8-bit format. For each of the 8-bit quantities in *src2*, the count of the number of 1 bits in that value is written to the corresponding position in *dst*.

31	24	23 1	6 15 8	7 0	
	ub_3	ub_2	ub_1	ub_0	← src2
		В	ITC4		
	\downarrow	\downarrow	\downarrow	\downarrow	
31	24	23 1	6 15 8	7 0	
	bit_count(ub_3)	bit_count(ub_2)	bit_count(ub_1)	bit_count(ub_0)	← dst

Execution

```
if (cond)  \{ \\ bit\_count(src2(ubyte0)) \rightarrow ubyte0(\textit{dst}); \\ bit\_count(src2(ubyte1)) \rightarrow ubyte1(\textit{dst}); \\ bit\_count(src2(ubyte2)) \rightarrow ubyte2(\textit{dst}); \\ bit\_count(src2(ubyte3)) \rightarrow ubyte3(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1	E2
Read	src2	
Written		dst
Unit in use	.M	



BITC4 — Bit Count, Packed 8-Bit

www.ti.com

Instruction Type Two-cycle

Delay Slots 1

Example BITC4 .M1 A1,A2

	Before instruction	2 cycles after instruction
A1	9E 52 6E 30h	A1 9E 52 6E 30h
A2	xxxx xxxxh	A2 05 03 05 02h




www.ti.com BITR — Bit Reverse

BITR Bit Reverse

Syntax BITR (.unit) src2, dst

unit = .M1 or .M2


Opcode



Opcode map field used	For operand type	Unit
src2 dst	xuint uint	.M1, .M2

Description

Implements a bit-reversal function that reverses the order of bits in a 32-bit word. This means that bit 0 of the source becomes bit 31 of the result, bit 1 of the source becomes bit 30 of the result, bit 2 becomes bit 29, and so on.



Execution

if (cond) else nop $bit_reverse(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1



BITR — Bit Reverse www.ti.com

Example BITR .M2 B4,B5

	Before instruction	2 cycles after instruction
B4	A6E2 C179h	B4 A6E2 C179h
B5	xxxx xxxxh	B5 9E83 4765h



BNOP

Branch Using a Displacement With NOP


Syntax

BNOP (.unit) src2, src1 unit = .S1, .S2, or none

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sbs7	Figure F-17
	Sbu8	Figure F-18
	Sbs7c	Figure F-20
	Sbu8c	Figure F-21
	Sx1b	Figure F-32

Opcode



Opcode map field used	For operand type	Unit
src2	scst12	.S1, .S2
src1	ucst3	

Description

The constant displacement form of the **BNOP** instruction performs a relative branch with **NOP** instructions. The instruction performs the relative branch using the 12-bit signed constant specified by *src2*. The constant is shifted 2 bits to the left, then added to the address of the first instruction of the fetch packet that contains the **BNOP** instruction (PCE1). The result is placed in the program fetch counter (PFC).

The 3-bit unsigned constant specified in src1 gives the number of delay slot **NOP** instructions to be inserted, from 0 to 7. With src1 = 0, no **NOP** cycles are inserted.

This instruction helps reduce the number of instructions to perform a branch when **NOP** instructions are required to fill the delay slots of a branch.

The following code:

B .S1 LABEL NOP N LABEL: ADD

could be replaced by:

BNOP .S1 LABEL, N LABEL: ADD



NOTE:

- BNOP instructions may be predicated. The predication condition controls whether or not the branch is taken, but does not affect the insertion of NOPs. BNOP always inserts the number of NOPs specified by N, regardless of the predication condition.
- 2. The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- 3. See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.

Only one branch instruction can be executed per cycle. If two branches are in the same execute packet, and if both are taken, the behavior is undefined. It should also be noted that when a predicated **BNOP** instruction is used with a **NOP** count greater than 5, the CPU inserts the full delay slots requested when the predicated condition is false.

For example, the following set of instructions will insert 7 cycles of **NOP**s:

```
ZERO .L1 A0
[A0] BNOP .S1 LABEL,7 ; branch is not taken and ; 7 cycles of NOPs are inserted
```

Conversely, when a predicated **BNOP** instruction is used with a **NOP** count greater than 5 and the predication condition is true, the branch will be taken and the multi-cycle **NOP** is terminated when the branch is taken.

For example in the following set of instructions, only 5 cycles of **NOP** are inserted:

```
MVK .D1 1,A0 [A0] BNOP .S1 LABEL,7 ; branch is taken and ; 5 cycles of NOPs are inserted
```

The **BNOP** instruction cannot be paired with any other multicycle **NOP** instruction in the same execute packet. Instructions that generate a multicycle **NOP** are: **IDLE**, **ADDKPC**, **CALLP**, and the multicycle **NOP**.

The **BNOP** instruction does not require the use of the .S unit. If no unit is specified, then it may be scheduled in parallel with instructions executing on both the .S1 and .S2 units. If either the .S1 or .S2 unit is specified for **BNOP**, then the .S unit specified is not available for another instruction in the same execute packet. This is enforced by the assembler.

It is possible to branch into the middle of a 32-bit instruction. The only case that will be detected and result in an exception is when the 32-bit instruction is contained in a compact header-based fetch packet. The header cannot be the target of a branch instruction. In the event that the header is the target of a branch, an exception will be raised.



Execution (if instruction is within compact instruction fetch packet)

Execution (if instruction is not within compact instruction fetch packet)

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	src2						
Written	PC						
Branch taken							✓
Unit in use	.S						

Instruction Type Branch

Delay Slots 5

See Also ADDKPC, B, NOP

Example BNOP .S1 30h,2

	Before instruction	After branch has been taken			
PCE1	0100 0500h				
PC	xxxx xxxxh	PC	C	0100 1100h	



BNOP


Branch Using a Register With NOP

Syntax

BNOP (.unit) src2, src1

unit = .S2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.S2
src1	ucst3	

Description

The register form of the **BNOP** instruction performs an absolute branch with **NOP** instructions. The register specified in *src2* is placed in the program fetch counter (PFC).

For branch targets residing in compact header-based fetch packets, the 31 most-significant bits of the register are used to determine the branch target. For branch targets not residing in compact header-based fetch packets, the 30 most-significant bits of the register are used to determine the branch target.

The 3-bit unsigned constant specified in src1 gives the number of delay slots **NOP** instructions to be inserted, from 0 to 7. With src1 = 0, no NOP cycles are inserted.

This instruction helps reduce the number of instructions to perform a branch when **NOP** instructions are required to fill the delay slots of a branch.

The following code:

B .S2 B3 NOP N

could be replaced by:

BNOP .S2 B3,N

NOTE:

- BNOP instructions may be predicated. The predication condition controls whether or not the branch is taken, but does not affect the insertion of NOPs. BNOP always inserts the number of NOPs specified by N, regardless of the predication condition.
- 2. The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- 3. See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.

Only one branch instruction can be executed per cycle. If two branches are in the same execute packet, and if both are taken, the behavior is undefined. It should also be noted that when a predicated **BNOP** instruction is used with a **NOP** count greater than 5, the CPU inserts the full delay slots requested when the predicated condition is false.



For example, the following set of instructions will insert 7 cycles of **NOPs**:

```
ZERO .L1 A0 [{\rm A0}] BNOP .S2 B3,7 ; branch is not taken and 7 cycles of NOPs are inserted
```

Conversely, when a predicated **BNOP** instruction is used with a **NOP** count greater than 5 and the predication condition is true, the branch will be taken and multi-cycle **NOP** is terminated when the branch is taken.

For example, in the following set of instructions only 5 cycles of **NOP** are inserted:

```
MVK .Dl 1,A0 [{\rm A0}] BNOP .S2 B3,7 ; branch is taken and 5 cycles of NOPs are inserted
```

The **BNOP** instruction cannot be paired with any other multicycle **NOP** instruction in the same execute packet. Instructions that generate a multicycle **NOP** are: **IDLE**, **ADDKPC**, **CALLP**, and the multicycle **NOP**.

Execution

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	src2						
Written	PC						
Branch taken							✓
Unit in use	.\$2						

Instruction Type Branch

Delay Slots 5

See Also ADDKPC, B, NOP

Example BNOP .S2 A5,2

	Before instruction	After branch has been taken
PCE1	0010 0000h	
PC	xxxx xxxxh	PC 0100 F000h
A5	0100 F000h	A5 0100 F000h



BPOS — Branch Positive www.ti.com

BPOS

Branch Positive

Syntax

BPOS (.unit) src, dst

unit = .S1 or .S2

Opcode

31 29	28	27 23	22 13	12	/ 1	1 1	U	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src	0	0) ()	0	0	0	0	1	0	0	0	s	p
3	1	5	10													1	1

Opcode map field used	For operand type	Unit
src	scst10	.S1, .S2
dst	int	

Description

If the predication register *(dst)* is positive (greater than or equal to 0), the **BPOS** instruction performs a relative branch. If *dst* is negative, the **BPOS** instruction takes no other action.

The instruction performs the relative branch using a 10-bit signed constant, *scst10*, in *src*. The constant is shifted 2 bits to the left, then added to the address of the first instruction of the fetch packet that contains the **BPOS** instruction (PCE1). The result is placed in the program fetch counter (PFC).


Any register can be used that can free the predicate registers (A0-A2 and B0-B2) for other uses.

NOTE:

- Only one BPOS instruction can be executed per cycle. The BPOS instruction can be predicated by using any conventional condition register. The conditions are effectively ANDed together. If two branches are in the same execute packet, and if both are taken, behavior is undefined.
- 2. The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.
- See Section 3.5.2 for information on branching into the middle of an execute packet.
- A branch to an execute packet that spans two fetch packets will cause a stall while the second fetch packet is fetched.
- The BPOS instruction cannot be in the same execute packet as an ADDKPC instruction.

Execution

170 Instruction Set SPRUFE8B-July 2010





Pipeline

www.ti.com

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	dst						
Written	PC						
Branch taken							✓
Unit in use	.S						

Instruction Type Branch

Delay Slots 5

Example BPOS .S1 200h,A10

	Before instruction	After branch has been tak
PCE1	0010 0000h	
PC	xxxx xxxxh	PC 0100 0800h
A10	0000 000Ah	A10 0000 000Ah



CALLP Call Using a Displacement

Syntax CALLP (.unit) label, A3/B3

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Scs10	Figure F-19

Opcode

3	31 30 29 28 27	1	ь	5	4	3	2	1	U
(0 0 0 1 cst21		0	0	1	0	0	s	р
	21							1	1

Opcode map field used	For operand type	Unit
cst21	scst21	.S1, .S2

Description

A 21-bit signed constant, *cst21*, is shifted left by 2 bits and is added to the address of the first instruction of the fetch packet that contains the branch instruction. The result is placed in the program fetch counter (PFC). The assembler/linker automatically computes the correct value for *cst21* by the following formula:

The address of the execute packet immediately following the execute packet containing the **CALLP** instruction is placed in A3, if the S1 unit is used; or in B3, if the S2 unit is used. This write occurs in E1. An implied **NOP 5** is inserted into the instruction pipeline occupying E2-E6.

Since this branch is taken unconditionally, it cannot be placed in the same execute packet as another branch. Additionally, no other branches should be pending when the **CALLP** instruction is executed.

CALLP, like other relative branch instructions, cannot have an **ADDKPC** instruction in the same execute packet with it.

NOTE:

- PCE1 (program counter) represents the address of the first instruction in the fetch packet in the E1 stage of the pipeline. PFC is the program fetch counter. retPC represents the address of the first instruction of the execute packet in the DC stage of the pipeline.
- 2. The execute packets in the delay slots of a branch cannot be interrupted. This is true regardless of whether the branch is taken.





Execution

(cst21 << 2) + PCE1 \rightarrow PFC if (unit = S2), retPC \rightarrow B3 else if (unit = S1), retPC \rightarrow A3 nop 5

Pipeline

				Target In	struction		
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read							
Written	A3/B3						
Branch taken							✓
Unit in use	.S						

Instruction Type Branch

Delay Slots 5



CLR — Clear a Bit Field www.ti.com

CLR

Clear a Bit Field

Syntax

CLR (.unit) src2, csta, cstb, dst

or

CLR (.unit) src2, src1, dst


unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sc5	Figure F-27

Opcode

Constant form



Opcode map field used	For operand type	Unit
src2	uint	.S1, .S2
csta	ucst5	
cstb	ucst5	
dst	uint	

Opcode

Register form

31	29	28	27	23	22 18	8 17	7	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	1	Z	C	lst	src2		src1		Х	1	1	1	1	1	1	1	0	0	0	S	р
3		1		5	5		5		1									-		1	1

Opcode map field used	For operand type	Unit
src2	xuint	.S1, .S2
src1	uint	
dst	uint	


Description

For $cstb \ge csta$, the field in src2 as specified by csta to cstb is cleared to all 0s in dst. The csta and cstb operands may be specified as constants or in the 10 LSBs of the src1 register, with cstb being bits 0–4 ($src1_{4..0}$) and csta being bits 5–9 ($src1_{9..5}$). csta is the LSB of the field and cstb is the MSB of the field. In other words, csta and cstb represent the beginning and ending bits, respectively, of the field to be cleared to all 0s in dst. The LSB location of src2 is bit 0 and the MSB location of src2 is bit 31.



www.ti.com CLR — Clear a Bit Field

In the following example, *csta* is 15 and *cstb* is 23. For the register version of the instruction, only the 10 LSBs of the *src1* register are valid. If any of the 22 MSBs are non-zero, the result is invalid.



For cstb < csta, the src2 register is copied to dst. The csta and cstb operands may be specified as constants or in the 10 LSBs of the src1 register, with cstb being bits 0-4 ($src1_{4..0}$) and csta being bits 5-9 ($src1_{9..5}$).

Execution

If the constant form is used when $cstb \ge csta$:

if (cond) else nop

src2 clear csta, $cstb \rightarrow dst$

If the register form is used when $cstb \ge csta$:

if (cond) else nop

src2 clear src1 $_{9..5}$, src1 $_{4..0} \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also SET

Examples Example 1

CLR .S1 A1,4,19,A2

	Before instruction	1 cycle after instruction
A1	07A4 3F2Ah	A1 07A4 3F2Ah
A2	xxxx xxxxh	A2 07A0 000Ah



CLR — Clear a Bit Field www.ti.com

Example 2

CLR .S2 B1,B3,B2

	Before instruction	1 cycle after instruction
B1	03B6 E7D5h	B1 03B6 E7D5h
B2	xxxx xxxxh	B2 03B0 0001h
В3	0000 0052h	B3 0000 0052h



CMPEQ

Compare for Equality, Signed Integer

Syntax

CMPEQ (.unit) src1, src2, dst

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
	Lx3c	Figure D-9

Opcode

31 29	28	27 23	22 18	17 13	3 12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	Х	ор		1	1	0	s	p
3	1	5	5	5	1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	101 0011
src2	xsint		
dst	uint		
src1	scst5	.L1, .L2	101 0010
src2	xsint		
dst	uint		
src1	xsint	.L1, .L2	101 0001
src2	slong		
dst	uint		
src1	scst5	.L1, .L2	101 0000
src2	slong		
dst	uint		

Description

Compares src1 to src2. If src1 equals src2, then 1 is written to dst, otherwise, 0 is written to dst.

Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

CMPEQ — Compare for Equality, Signed Integer

www.ti.com

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ2, CMPEQ4

Example 1

CMPEQ .L1X A1,B1,A2

	Before instruction		1 cycle after instruction		
A1	0000 04B8h	1208	A1	0000 04B8h	
A2	xxxx xxxxh		A2	0000 0000h	false
B1	0000 04B7h	1207	B1	0000 04B7h	

Example 2

CMPEQ .L1 Ch,A1,A2

	Before instruction			1 cycle after instruction			
A1	0000 000Ch	12	A1	0000 000Ch			
A2	xxxx xxxxh		A2	0000 0001h	true		

Example 3

CMPEQ .L2X A1,B3:B2,B1

	Before instruction			1 cycle after instructio	n
A1	F23A 3789h		A1	F23A 3789h	
B1	xxxx xxxxh		B1	0000 0001h	true
B3:B2	0000 00FFh	F23A 3789h	B3:B2	0000 00FFh	F23A 3789h



CMPEQ2

Compare for Equality, Packed 16-Bit

Syntax

```
CMPEQ2 (.unit) src1, src2, dst
```

unit =
$$.S1$$
 or $.S2$


Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	0	1	1	1	0	1	1	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	bv2	

Description

Performs equality comparisons on packed 16-bit data. Each 16-bit value in *src1* is compared against the corresponding 16-bit value in *src2*, returning either a 1 if equal or a 0 if not equal. The equality results are packed into the two least-significant bits of *dst*. The result for the lower pair of values is placed in bit 0, and the results for the upper pair of values are placed in bit 1. The remaining bits of *dst* are cleared to 0.



Execution

```
if (cond)  \{ \\  & \text{if (lsb16(src1) == lsb16(src2)), 1} \rightarrow \textit{dst}_0 \\  & \text{else } 0 \rightarrow \textit{dst}_0; \\  & \text{if (msb16(src1) == msb16(src2)), 1} \rightarrow \textit{dst}_1 \\  & \text{else } 0 \rightarrow \textit{dst}_1 \\  & \} \\ & \text{else nop}
```



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ, CMPEQ4, CMPGT2, XPND2

Examples Example 1

CMPEQ2 .S1 A3,A4,A5

	Before instruction	1 cycle after instruction	
АЗ	1105 6E30h	A3 1105 6E30h	
A4	1105 6980h	A4 1105 6980h	
A5	xxxx xxxxh	A5 0000 0002h	true, false

Example 2

CMPEQ2 .S2 B2,B8,B15

	Before instruction	1 cycle after instruction	1
B2	F23A 3789h	B2 F23A 3789h	
B8	04B8 3789h	B8 04B8 3789h	
B15	xxxx xxxxh	B15 0000 0001h	false, true

Example 3

CMPEQ2 .S2 B2,B8,B15

	Before instruction		1 cycle after instruction	1
B2	01B6 2451h	B2	01B6 2451h	
B8	01B6 2451h	B8	01B6 2451h	
B15	xxxx xxxxh	B15	0000 0003h	true, true





CMPEQ4

Compare for Equality, Packed 8-Bit

Syntax

CMPEQ4 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode


31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	0	1	1	1	0	0	1	0	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s4	.S1, .S2
src1 src2	xs4	
dst	bv4	

Description

Performs equality comparisons on packed 8-bit data. Each 8-bit value in *src1* is compared against the corresponding 8-bit value in *src2*, returning either a 1 if equal or a 0 if not equal. The equality comparison results are packed into the four least-significant bits of *dst*.

The 8-bit values in each input are numbered from 0 to 3, starting with the least-significant byte, then working towards the most-significant byte. The comparison results for byte 0 are written to bit 0 of the result. Likewise the results for byte 1 to 3 are written to bits 1 to 3 of the result, respectively, as shown in the diagram below. The remaining bits of *dst* are cleared to 0.





Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ, CMPEQ2, CMPGTU4, XPND4

Example 1

CMPEQ4 .S1 A3,A4,A5

	Before instruction		1 cycle after instruction	
А3	02 3A 4E 1Ch	A3	02 3A 4E 1Ch	
A4	02 B8 4E 76h	A4	02 B8 4E 76h	
A5	xxxx xxxxh	A5	0000 000Ah	true, false, false, false

Example 2

CMPEQ4 .S2 B2,B8,B13

	Before instruction		1 cycle after instruction	
B2	F2 3A 37 89h	B2	F2 3A 37 89h	
B8	04 B8 37 89h	B8	04 B8 37 89h	
B13	xxxx xxxxh	B13	0000 0003h	false, false, true, true





Example 3

CMPEQ4 .S2 B2,B8,B13

	Before instruction		1 cycle after instruction	
B2	01 B6 24 51h	B2	01 B6 24 51h	
B8	05 B6 24 51h	B8	05 B6 24 51h	
B13	xxxx xxxxh	B13	0000 0007h	false, true, true, true



CMPEQDP

Compare for Equality, Double-Precision Floating-Point Values

Syntax

CMPEQDP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23	22 18	17	•	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		src1		Х	1	0	1	0	0	0	1	0	0	0	s	p
3	1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	dp	.S1, .S2
src2	xdp	
dst	sint	

Description

Compares src1 to src2. If src1 equals src2, then 1 is written to dst, otherwise, 0 is written to dst.

Special cases of inputs:

lnı	put		FAUC	R Bits
src1	src2	Output	UNORD	INVAL
NaN	don't care	0	1	0
don't care	NaN	0	1	0
NaN	NaN	0	1	0
+/-denormalized	+/-0	1	0	0
+/-0	+/-denormalized	1	0	0
+/-0	+/-0	1	0	0
+/-denormalized	+/-denormalized	1	0	0
+infinity	+infinity	1	0	0
+infinity	other	0	0	0
-infinity	-infinity	1	0	0
-infinity	other	0	0	0

NOTE:

- 1. In the case of NaN compared with itself, the result is false.
- 2. No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.



Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1_l, src2_l	src1_h, src2_h
Written		dst
Unit in use	.S	.S

Instruction Type DP compare

Delay Slots 1
Functional Unit Latency 2

See Also CMPEQ, CMPEQSP, CMPGTDP, CMPLTDP

Example CMPEQDP .S1 A1:A0,A3:A2,A4

	Before instruction	on		7 cycles after instruction						
A1:A0	4021 3333h	3333 3333h	A1:A0	4021 3333h	3333 3333h	8.6				
A3:A2	C004 0000h	0000 0000h	A3:A2	C004 0000h	0000 0000h	-2.5				
A4	xxxx xxxxh		A4	0000 0000h	false					



CMPEQSP

Compare for Equality, Single-Precision Floating-Point Values

Syntax

CMPEQSP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23 22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	sro	2	src1		Х	1	1	1	0	0	0	1	0	0	0	S	p
3	1	5	5	,	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.S1, .S2
src2	xsp	
dst	sint	

Description

Compares src1 to src2. If src1 equals src2, then 1 is written to dst, otherwise, 0 is written to dst.

Special cases of inputs:

Input			FAUC	R Bits
src1	src2	Output	UNORD	INVAL
NaN	don't care	0	1	0
don't care	NaN	0	1	0
NaN	NaN	0	1	0
+/-denormalized	+/-0	1	0	0
+/-0	+/-denormalized	1	0	0
+/-0	+/-0	1	0	0
+/-denormalized	+/-denormalized	1	0	0
+infinity	+infinity	1	0	0
+infinity	other	0	0	0
-infinity	-infinity	1	0	0
-infinity	other	0	0	0

NOTE:

- 1. In the case of NaN compared with itself, the result is false.
- 2. No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0
Functional Unit Latency 1

See Also CMPEQ, CMPEQDP, CMPGTSP, CMPLTSP

Example CMPEQSP .S1 A1,A2,A3

	Before instruction		1 cycle after instru	ıction
A1	C020 0000h	A1	C020 0000h	-2.5
A2	4109 999Ah	A2	4109 999Ah	8.6
А3	xxxx xxxxh	А3	0000 0000h	false



CMPGT Compare for Greater Than, Signed Integers

Syntax CMPGT (.unit) src1, src2, dst

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
	Lx1c	Figure D-10

Opcode

31	29	28	27	23	22 18	17	13	12	11	5	4	3	2	1	0
	creg	Z	dst	t	src2	src1		Х	ор		1	1	0	s	p
	3	1	5		5	5		1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	100 0111
src2	xsint		
dst	uint		
src1	scst5	.L1, .L2	100 0110
src2	xsint		
dst	uint		
src1	xsint	.L1, .L2	100 0101
src2	slong	·	
dst	uint		
src1	scst5	.L1, .L2	100 0100
src2	slong		
dst	uint		

Description

Performs a signed comparison of *src1* to *src2*. If *src1* is greater than *src2*, then a 1 is written to *dst*; otherwise, a 0 is written to *dst*.



NOTE: The CMPGT instruction allows using a 5-bit constant as src1. If src2 is a 5-bit constant, as in

```
CMPGT .L1 A4, 5, A0
```

Then to implement this operation, the assembler converts this instruction

```
CMPLT .L1 5, A4, A0
```

These two instructions are equivalent, with the second instruction using the conventional operand types for src1 and src2.

Similarly, the CMPGT instruction allows a cross path operand to be used as src2. If src1 is a cross path operand as in

```
CMPGT .L1x B4, A5, A0
```

Then to implement this operation the assembler converts this instruction

```
CMPLT .L1x A5, B4, A0
```

In both of these operations the listing file (.lst) will have the first implementation, and the second implementation will appear in the debugger.

Execution

```
if (cond)
                         if (src1 > src2), 1 \rightarrow dst
                         else 0 \rightarrow dst
else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Single-cycle **Instruction Type**

Delay Slots 0

CMPGT2, CMPGTU, CMPGTU4 See Also

Examples Example 1

CMPGT .L1X A1,B1,A2

	Before instruction			1 cycle after instruction	
A1	0000 01B6h	438	A1	0000 01B6h	
A2	xxxx xxxxh		A2	0000 0000h	false
B1	0000 08BDh	2237	B1	0000 08BDh	



Example 2

CMPGT .L1X A1,B1,A2

	Before instruction			1 cycle after instruction	
A1	FFFF FE91h	-367	A1	FFFF FE91h	
A2	xxxx xxxxh		A2	0000 0001h	true
B1	FFFF FDC4h	-572	B1	FFFF FDC4h	

Example 3

CMPGT .L1 8,A1,A2

	Before instruction			1 cycle after instruction	
A1	0000 0023h	35	A1	0000 0023h	
A2	xxxx xxxxh		A2	0000 0000h	false

Example 4

CMPGT .L1X A1,B1,A2

	Before instruction			1 cycle after instruction	
A1	0000 00EBh	235	A1	0000 00EBh	
A2	xxxx xxxxh		A2	0000 0000h	false
B1	0000 00EBh	235	B1	0000 00EBh	



CMPGT2

Compare for Greater Than, Packed 16-Bit

Syntax

```
CMPGT2 (.unit) src1, src2, dst unit = .S1 or .S2
```


Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	0	1	0	1	0	0	1	0	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	bv2	

Description

Performs comparisons for greater than values on signed, packed 16-bit data. Each signed 16-bit value in *src1* is compared against the corresponding signed 16-bit value in *src2*, returning a 1 if *src1* is greater than *src2* or returning a 0 if it is not greater. The comparison results are packed into the two least-significant bits of *dst*. The result for the lower pair of values is placed in bit 0, and the results for the upper pair of values are placed in bit 1. The remaining bits of *dst* are cleared to 0.



Execution

```
if (cond)  \{ \\  & \text{if (lsb16(}\textit{src1}\text{)} > \text{lsb16(}\textit{src2}\text{)), 1} \rightarrow \textit{dst}_0 \\  & \text{else } 0 \rightarrow \textit{dst}_0; \\  & \text{if (msb16(}\textit{src1}\text{)} > \text{msb16(}\textit{src2}\text{)), 1} \rightarrow \textit{dst}_1 \\  & \text{else } 0 \rightarrow \textit{dst}_1 \\  & \} \\ \\ & \text{else nop}
```



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ2, CMPGT, CMPGTU4, CMPLT2, XPND2

Examples Example 1

CMPGT2 .S1 A3,A4,A5

	Before instruction			1 cycle after instruction	
А3	1105 6E30h	4357 28208	А3	1105 6E30h	
A4	1105 6980h	4357 27008	A4	1105 6980h	
A5	xxxx xxxxh		A5	0000 0001h	false, true

Example 2

CMPGT2 .S2 B2,B8,B15

	Before instruction			1 cycle after instruction	
B2	F348 3789h	-3526 14217	B2	F348 3789h	
B8	04B8 4975h	1208 18805	B8	04B8 4975h	
B15	xxxx xxxxh		B15	0000 0000h	false, false

Example 3

CMPGT2 .S2 B2, B8, B15

	Before instruction			1 cycle after instruction	n
B2	01A6 2451h	422 9297	B2	01A6 2451h	
B8	0124 A051h	292 -24495	В8	0124 A051h	
B15	xxxx xxxxh		B15	0000 0003h	true, true



CMPGTDP

Compare for Greater Than, Double-Precision Floating-Point Values

Syntax

CMPGTDP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	0	1	0	0	1	1	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	dp	.S1, .S2
src2	xdp	
dst	sint	

Description

Compares *src1* to *src2*. If *src1* is greater than *src2*, then 1 is written to *dst*, otherwise, 0 is written to *dst*.

Special cases of inputs:

Inj	put		FAUC	R Bits
src1	src2	Output	UNORD	INVAL
NaN	don't care	0	1	1
don't care	NaN	0	1	1
NaN	NaN	0	1	1
+/-denormalized	+/-0	0	0	0
+/-0	+/-denormalized	0	0	0
+/-0	+/-0	0	0	0
+/-denormalized	+/-denormalized	0	0	0
+infinity	+infinity	0	0	0
+infinity	other	1	0	0
-infinity	-infinity	0	0	0
-infinity	other	0	0	0

NOTE: No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.

Execution



Pipeline

Pipeline Stage	E1	E2
Read	src1_l, src2_l	src1_h, src2_h
Written		dst
Unit in use	.S	.S

Instruction Type DP compare

Delay Slots 1

Functional Unit Latency 2

See Also CMPEQDP, CMPGT, CMPGTSP, CMPGTU, CMPLTDP

Example CMPGTDP .S1 A1:A0,A3:A2,A4

	Before instruction	1			7 cycles after ins	truction
A1:A0	4021 3333h	3333 3333h	8.6	A1:A0	4021 3333h	3333 3333h
A3:A2	C004 0000h	0000 0000h	-2.5	A3:A2	C004 0000h	0000 0000h
A4	xxxx xxxxh			A4	0000 0001h	true



CMPGTSP

Compare for Greater Than, Single-Precision Floating-Point Values

Syntax

CMPGTSP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	(dst	src2	src1		Х	1	1	1	0	0	1	1	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.S1, .S2
src2	xsp	
dst	sint	

Description

Compares *src1* to *src2*. If *src1* is greater than *src2*, then 1 is written to *dst*; otherwise, 0 is written to *dst*.

Special cases of inputs:

Input			FAUC	R Bits
src1	src2	Output	UNORD	INVAL
NaN	don't care	0	1	1
don't care	NaN	0	1	1
NaN	NaN	0	1	1
+/-denormalized	+/-0	0	0	0
+/-0	+/-denormalized	0	0	0
+/-0	+/-0	0	0	0
+/-denormalized	+/-denormalized	0	0	0
+infinity	+infinity	0	0	0
+infinity	other	1	0	0
-infinity	-infinity	0	0	0
-infinity	other	0	0	0

NOTE: No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.

Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0
Functional Unit Latency 1

See Also CMPEQSP, CMPGT, CMPGTDP, CMPGTU, CMPLTSP

Example CMPGTSP .S1X A1,B2,A3

	Before instruction			1 cycle after instruction	
A1	C020 0000h	-2.5	A1	C020 0000h	
B2	4109 999Ah	8.6	B2	4109 999Ah	
A3	xxxx xxxxh		A3	0000 0000h	false



CMPGTU

Compare for Greater Than, Unsigned Integers

Syntax

CMPGTU (.unit) src1, src2, dst

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
	Lx1c	Figure D-10

Opcode

31 29	28	27	23	22 18	17	13	12	11	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	ор		1	1	0	s	p
3	1	5		5	5		1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 uint		.L1, .L2	100 1111
src2	xuint		
dst	uint		
src1	ucst4	.L1, .L2	100 1110
src2	xuint		
dst	uint		
src1	xuint	.L1, .L2	100 1101
src2	ulong	·	
dst	uint		
src1	ucst5	.L1, .L2	100 1100
src2	ulong		
dst	uint		

Description

Performs an unsigned comparison of *src1* to *src2*. If *src1* is greater than *src2*, then a 1 is written to *dst*, otherwise, a 0 is written to *dst*.

Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also CMPGT, CMPGT2, CMPGTU4

Example 1

CMPGTU .L1 A1,A2,A3

Before	Before instruction			1 cycle after instruction	on
A1 0000 0	128h	296 ⁽¹⁾	A1	0000 0128h	
A2 FFFF F	FDEh .	4,294,967,262 ⁽¹⁾	A2	FFFF FFDEh	
A3 xxxx xx	xxh		А3	0000 0000h	false

⁽¹⁾ Unsigned 32-bit integer

Example 2

CMPGTU .L1 0Ah,A1,A2

Before instruction	Before instruction		1 cycle after instruction	on
A1 0000 0005h	5 ⁽¹⁾	A1 (0000 0005h	
A2 xxxx xxxxh		A2 (0000 0001h	true

⁽¹⁾ Unsigned 32-bit integer

Example 3

CMPGTU .L1 0Eh,A3:A2,A4

	Before instruction				1 cycle after instruction		
A3:A2	0000 0000h	0000 000Ah	10 ⁽¹⁾	A3:A2	0000 0000h	0000 000Ah	
A4	xxxx xxxxh			A4	0000 0001h	true	

⁽¹⁾ Unsigned 40-bit (long) integer



CMPGTU4


Compare for Greater Than, Unsigned, Packed 8-Bit

Syntax

CMPGTU4 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode




Opcode map field used	For operand type	Unit
src1	u4	.S1, .S2
src1 src2	xu4	
dst	bv4	

Description

Performs comparisons for greater than values on packed 8-bit data. Each unsigned 8-bit value in *src1* is compared against the corresponding unsigned 8-bit value in *src2*, returning a 1 if the byte in *src1* is greater than the corresponding byte in *src2* or a 0 if is not greater. The comparison results are packed into the four least-significant bits of *dst*.

The 8-bit values in each input are numbered from 0 to 3, starting with the least-significant byte, then working towards the most-significant byte. The comparison results for byte 0 are written to bit 0 of the result. Likewise, the results for byte 1 to 3 are written to bits 1 to 3 of the result, respectively, as shown in the diagram below. The remaining bits of *dst* are cleared to 0.





Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ4, CMPGT, CMPGT2, CMPGTU, CMPLT, XPND4

Example 1

CMPGTU4 .S1 A3,A4,A5

	Before instruction			1 cycle after instruction	
А3	25 3A 1C E4h 37 58 28 228		А3	25 3A 1C E4h	
A4	02 B8 4E 76h	2 184 78 118	A4	02 B8 4E 76h	
A5	xxxx xxxxh		A5	0000 0009h	true, false, false, true

Example 2

CMPGTU4 .S2 B2, B8, B13

	Before instruction			1 cycle after instruction	ı
B2	89 F2 3A 37h	137 242 58 55	B2	89 F2 3A 37h	
B8	04 8F 17 89h	4 143 23 137	B8	04 8F 17 89h	
B13	xxxx xxxxh		B13	0000 000Eh	true, true, true, false



Example 3

CMPGTU4 .S2 B2,B8,B13

	Before instruction			1 cycle after instruction	
B2	12 33 9D 51h	12 33 9D 51h 18 51 157 81		12 33 9D 51h	
B8	75 67 24 C5h	117 103 36 197	B8	75 67 24 C5h	
B13	xxxx xxxxh		B13	0000 0002h	false, false, true, false



CMPLT Compare for Less Than, Signed Integers

Syntax CMPLT (.unit) src1, src2, dst

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
	Lx1c	Figure D-10

Opcode

31	29	28	27	23	22 18	17	13	12	11	5	4	3	2	1	0
	creg	Z	dst	t	src2	src1		Х	ор		1	1	0	s	p
	3	1	5		5	5		1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	101 0111
src2	xsint		
dst	uint		
src1	scst5	.L1, .L2	101 0110
src2	xsint		
dst	uint		
src1	xsint	.L1, .L2	101 0101
src2	slong		
dst	uint		
src1	scst5	.L1, .L2	101 0100
src2	slong		
dst	uint		

Description

Performs a signed comparison of *src1* to *src2*. If *src1* is less than *src2*, then 1 is written to *dst*, otherwise, 0 is written to *dst*.



NOTE: The CMPLT instruction allows using a 5-bit constant as src1. If src2 is a 5-bit constant, as in

CMPLT .L1 A4, 5, A0

Then to implement this operation, the assembler converts this instruction

CMPGT .L1 5, A4, A0

These two instructions are equivalent, with the second instruction using the conventional operand types for src1 and src2.

Similarly, the CMPLT instruction allows a cross path operand to be used as src2. If src1 is a cross path operand as in

CMPLT .L1x B4, A5, A0

Then to implement this operation, the assembler converts this instruction

CMPGT .L1x A5, B4, A0

In both of these operations the listing file (.lst) will have the first implementation, and the second implementation will appear in the debugger.

Execution

```
if (cond)
                         if (src1 < src2), 1 \rightarrow dst
                         else 0 \rightarrow dst
else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Single-cycle **Instruction Type**

Delay Slots 0

CMPLT2, CMPLTU, CMPLTU4 See Also

Examples Example 1

CMPLT .L1 A1, A2, A3

	Before instruction		1 cycle after instruction					
A1	0000 07E2h	2018	A1	0000 07E2h				
A2	0000 0F6Bh	3947	A2 0000 0F6Bh					
A3	xxxx xxxxh		A3	0000 0001h				



Example 2

CMPLT .L1 A1,A2,A3

	Before instruction			1 cycle after instruction	
A1	FFFF FED6h	-298 A		FFFF FED6h	
A2	0000 000Ch	12	A2	0000 000Ch	
А3	xxxx xxxxh		A3	0000 0001h	true

Example 3

CMPLT .L1 9,A1,A2

	Before instruction			1 cycle after instruction								
A1	0000 0005h	5	A1	0000 0005h								
A2	xxxx xxxxh		A2	0000 0000h	false							



CMPLT2

Compare for Less Than, Packed 16-Bit

Syntax

CMPLT2 (.unit) src2, src1, dst

unit = .S1 or .S2

Opcode

31	29	28	27	23	22 1	8 ′	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	3	Z		dst	src2		src1		Х	0	1	0	1	0	0	1	0	0	0	S	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	bv2	

Description

The **CMPLT2** instruction is a pseudo-operation used to perform less-than comparisons on signed, packed 16-bit data. Each signed 16-bit value in *src2* is compared against the corresponding signed 16-bit value in *src1*, returning a 1 if *src2* is less than *src1* or returning a 0 if it is not less than. The comparison results are packed into the two least-significant bits of *dst*. The result for the lower pair of values is placed in bit 0, and the results for the upper pair of values are placed in bit 1. The remaining bits of *dst* are cleared to 0.

The assembler uses the operation **CMPGT2** (.unit) *src1*, *src2*, *dst* to perform this task (see CMPGT2).

Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type

Single-cycle

0

Delay Slots

See Also

CMPEQ2, CMPGT2, CMPLT, CMPLTU, CMPLTU4, XPND2



Examples

Example 1

CMPLT2 .S1 A4,A3,A5; assembler treats as CMPGT2 A3,A4,A5

	Before instruction			1 cycle after instruction							
А3	1105 6E30h	4357 28208	A3 1105 6E30h								
A4	1105 6980h	4357 27008	A4 1105 6980h								
A5	xxxx xxxxh		A5	0000 0001h	false, true						

Example 2

CMPLT2 .S2 B8,B2,B15; assembler treats as CMPGT2 B2,B8,B15

	Before instruction			1 cycle after instruction							
B2	F23A 3789h	-3526 14217	B2 F23A 3789h								
B8	04B8 4975h	1208 18805	B8	04B8 4975h							
B15	xxxx xxxxh		B15 0000 0000h		false, false						

Example 3

CMPLT2 .S2 B8,B2,B12; assembler treats as CMPGT2 B2,B8,B15

	Before instruction		1 cycle after instruction						
B2	01A6 2451h	422 9297	B2 01A6 2451h						
B8	0124 A051h	292 -24495	B8 0124 A051h						
B12	xxxx xxxxh		B12 0000 0003h		true, true				



CMPLTDP

Compare for Less Than, Double-Precision Floating-Point Values

Syntax

CMPLTDP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23		18 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	1	0	1	0	1	0	1	0	0	0	s	p
3	1	5	5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	dp	.S1, .S2
src2	xdp	
dst	sint	

Description

Compares src1 to src2. If src1 is less than src2, then 1 is written to dst, otherwise, 0 is written to dst.

Special cases of inputs:

Inj	put		FAUC	R Bits
src1	src2	Output	UNORD	INVAL
NaN	don't care	0	1	1
don't care	NaN	0	1	1
NaN	NaN	0	1	1
+/-denormalized	+/-0	0	0	0
+/-0	+/-denormalized	0	0	0
+/-0	+/-0	0	0	0
+/-denormalized	+/-denormalized	0	0	0
+infinity	+infinity	0	0	0
+infinity	other	0	0	0
-infinity	-infinity	0	0	0
-infinity	other	1	0	0

NOTE: No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.

Execution



Pipeline

Pipeline Stage	E1	E2				
Read	src1_l, src2_l					
Written		dst				
Unit in use	.S	.S				

Instruction Type DP compare

Delay Slots 1

Functional Unit Latency 2

See Also CMPEQDP, CMPGTDP, CMPLT, CMPLTSP, CMPLTU

Example CMPLTDP .S1X A1:A0,B3:B2,A4

	Before instructio	n			2 cycles after instruction					
A1:A0	4021 3333h	3333 3333h	8.6	A1:A0	4021 3333h	3333 3333h				
B3:B2	C004 0000h	0000 0000h	-2.5	B3:B2	C004 0000h	0000 0000h				
A4	xxxx xxxxh			A4	0000 0000h	false				



CMPLTSP

Compare for Less Than, Single-Precision Floating-Point Values

Syntax

CMPLTSP (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23		18 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2		src1		Х	1	1	1	0	1	0	1	0	0	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.S1, .S2
src2	xsp	
dst	sint	

Description

Compares src1 to src2. If src1 is less than src2, then 1 is written to dst, otherwise, 0 is written to dst.

Special cases of inputs:

Inj	out		FAUCR Bits				
src1	src2	Output	UNORD	INVAL			
NaN	don't care	0	1	1			
don't care	NaN	0	1	1			
NaN	NaN	0	1	1			
+/-denormalized	+/-0	0	0	0			
+/-0	+/-denormalized	0	0	0			
+/-0	+/-0	0	0	0			
+/-denormalized	+/-denormalized	0	0	0			
+infinity	+infinity	0	0	0			
+infinity	other	0	0	0			
-infinity	-infinity	0	0	0			
-infinity	other	1	0	0			

NOTE: No configuration bits other than those in the preceding table are set, except the NaNn and DENn bits when appropriate.

Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

Functional Unit Latency 1

See Also CMPEQSP, CMPGTSP, CMPLT, CMPLTDP, CMPLTU

Example CMPLTSP .S1 A1,A2,A3

	Before instruction			1 cycle after instruction	
A1	C020 0000h	-2.5	A1	C020 0000h	
A2	4109 999Ah	8.6	A2	4109 999Ah	
A3	xxxx xxxxh		A3	0000 0001h	



CMPLTU

Compare for Less Than, Unsigned Integers

Syntax

CMPLTU (.unit) src1, src2, dst

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
	Lx1c	Figure D-10

Opcode

31 29	9 28	27	23	22 18		13 ′	12	11	5	4	3	2	1	0
creg	Z		dst	src2	src1		х	ор		1	1	0	s	p
3	1		5	5	5		1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	uint	.L1, .L2	101 1111
src2	xuint		
dst	uint		
src1	ucst4	.L1, .L2	101 1110
src2	xuint		
dst	uint		
src1	xuint	.L1, .L2	101 1101
src2	ulong	·	
dst	uint		
src1	ucst5	.L1, .L2	101 1100
src2	ulong	·	
dst	uint		

Description

Performs an unsigned comparison of *src1* to *src2*. If *src1* is less than *src2*, then 1 is written to *dst*, otherwise, 0 is written to *dst*.

Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L



Instruction Type Single-cycle

Delay Slots 0

See Also CMPLT, CMPLT2, CMPLTU4

Example 1

CMPLTU .L1 A1,A2,A3

	Before instruction			1 cycle after instruc		
A1	0000 289Ah	10,394(1)	A1	0000 289Ah		
A2	FFFF F35Eh	4,294,964,062(1)	A2	FFFF F35Eh		
АЗ	xxxx xxxxh		A3	0000 0001h		

⁽¹⁾ Unsigned 32-bit integer

Example 2

CMPLTU .L1 14,A1,A2

	Before instruction		1 cycle after instruction						
A1	0000 000Fh	15 ⁽¹⁾ A1	0000 000Fh						
A2	xxxx xxxxh	A2	0000 0001h	true					

Unsigned 32-bit integer

Example 3

CMPLTU .L1 A1,A5:A4,A2

	Before instruction					tion
A1	003B 8260h	3,900,000(1)		A1	003B 8260h	
A2	xxxx xxxxh			A2	0000 0000h	false
A5:A4	0000 0000h	003A 0002h	3,801,090 ⁽²⁾	A5:A4	0000 0000h	003A 0002h

⁽¹⁾ Unsigned 32-bit integer

⁽²⁾ Unsigned 40-bit (long) integer



CMPLTU4

Compare for Less Than, Unsigned, Packed 8-Bit

Syntax

```
CMPLTU4 (.unit) src2, src1, dst unit = .S1 or .S2
```

Opcode

31 29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	0	1	0	1	0	1	1	0	0	0	S	р
3	1	5	5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.S1, .S2
src2	xu4	
dst	bv4	

Description

The **CMPLTU4** instruction is a pseudo-operation that performs less-than comparisons on packed 8-bit data. Each unsigned 8-bit value in *src2* is compared against the corresponding unsigned 8-bit value in *src1*, returning a 1 if the byte in *src2* is less than the corresponding byte in *src1* or a 0 it if is not less than. The comparison results are packed into the four least-significant bits of *dst*.

The 8-bit values in each input are numbered from 0 to 3, starting with the least-significant byte, and moving towards the most-significant byte. The comparison results for byte 0 are written to bit 0 of the result. Similarly, the results for byte 1 to 3 are written to bits 1 to 3 of the result, respectively, as shown in the diagram below. The remaining bits of *dst* are cleared to 0.

The assembler uses the operation **CMPGTU4** (.unit) *src1*, *src2*, *dst* to perform this task (see CMPGTU4).

Execution

```
if (cond)  \{ \\ & \text{if (ubyte0(src2) < ubyte0(src1)), } 1 \rightarrow \textit{dst}_0 \\ & \text{else } 0 \rightarrow \textit{dst}_0; \\ & \text{if (ubyte1(src2) < ubyte1(src1)), } 1 \rightarrow \textit{dst}_1 \\ & \text{else } 0 \rightarrow \textit{dst}_1; \\ & \text{if (ubyte2(src2) < ubyte2(src2)), } 1 \rightarrow \textit{dst}_2 \\ & \text{else } 0 \rightarrow \textit{dst}_2; \\ & \text{if (ubyte3(src2) < ubyte3(src1)), } 1 \rightarrow \textit{dst}_3 \\ & \text{else } 0 \rightarrow \textit{dst}_3 \\ \} \\ & \text{else nop}
```



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CMPEQ4, CMPGT, CMPLT2, CMPLTU, XPND4

Example 1

CMPLTU4 .S1 A4,A3,A5; assembler treats as CMPGTU4 A3,A4,A5

	Before instruction		·	1 cycle after instruction	
A3	25 3A 1C E4h	37 58 28 228	А3	25 3A 1C E4h	
A4	02 B8 4E 76h	2 184 78 118	A4	02 B8 4E 76h	
A5	xxxx xxxxh		A5	0000 0009h	true, false, false, true

Example 2

CMPLTU4 .S2 B8,B2,B13; assembler treats as CMPGTU4 B2,B8,B13

	Before instruction			1 cycle after instruction	
B2	89 F2 3A 37h	137 242 58 55	B2	89 F2 3A 37h	
B8	04 8F 17 89h	4 143 23 137	B8	04 8F 17 89h	
B13	xx xx xx xxh		B13	0000 000Eh	true, true, true, false

Example 3

 ${\tt CMPLTU4~.S2~B8,B2,B13;~assembler~treats~as~CMPGTU4~B2,B8,B13}$

	Before instruction			1 cycle after instruction	n
B2	12 33 9D 51h	18 51 157 81	B2	12 33 9D 51h	
B8	75 67 24 C5h	117 103 36 197	B8	75 67 24 C5h	
B13	xx xx xx xxh		B13	0000 0002h	false, false, true, false



CMPY Complex Multiply Two Pairs, Signed, Packed 16-Bit

CMPY (.unit) src1, src2, dst o:dst e **Syntax**

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	0	1	0	1	0	1	1	0	0	S	р
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xs2	
dst	dint	

Description

Returns two dot-products between two pairs of signed, packed 16-bit values. The values in src1 and src2 are treated as signed, packed 16-bit quantities. The signed results are written to a 64-bit register pair.

The product of the lower halfwords of src1 and src2 is subtracted from the product of the upper halfwords of src1 and src2. The result is written to dst_o.

The product of the upper halfword of src1 and the lower halfword of src2 is added to the product of the lower halfword of src1 and the upper halfword of src2. The result is written to dst_e.

If the result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the result is written to dst_e.

This instruction executes unconditionally.

NOTE: In the overflow case, where all four halfwords in src1 and src2 are 8000h, the saturation value 7FFF FFFFh is written into the 32-bit dst_e register.

Execution

 $sat((lsb16(src1) \times msb16(src2)) + (msb16(src1) \times lsb16(src2))) \rightarrow dst_e$ $(msb16(src1) \times msb16(src2)) - (lsb16(src1) \times lsb16(src2)) \rightarrow dst_o$

Four-cycle Instruction Type

Delay Slots 3

See Also CMPYR, CMPYR1, DOTP2, DOTPN2



Examples

Example 1

CMPY .M1 A0,A1,A3:A2

	Before instruction 4 cycles after instruction (1)				
A0	0008 0004h	A2	0000 0034h		
A1	0009 0002h	A3	0000 0040h		

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

CMPY .M2X B0,A1,B3:B2

	Before instruction		4 cycles after instruction (1)	
В0	7FFF 7FFFh	B2	FFFF 8001h	
A1	7FFF 8000h	В3	7FFE 8001h	

⁽¹⁾ CSR.SAT and SSR.M2 unchanged by operation

Example 3

CMPY .M1 A0,A1,A3:A2

	Before instruction		4 cycles after instruction (1))
A0	8000 8000h	A2	7FFF FFFFh	
A1	8000 8000h	А3	0000 0000h	

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation



CMPYR Complex Multiply Two Pairs, Signed, Packed 16-Bit With Rounding

Syntax CMPYR (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

	31	30	29	28	27	23 2	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
Ī	0	0	0	1	dst		src2		src1		Χ	0	0	1	0	1	1	1	1	0	0	s	р
					5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xs2	
dst	s2	

Description

Performs two dot-products between two pairs of signed, packed 16-bit values. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The signed results are rounded with saturation, shifted, packed and written to a 32-bit register.

The product of the lower halfwords of *src1* and *src2* is subtracted from the product of the upper halfwords of *src1* and *src2*. The result is rounded by adding 2¹⁵ to it. The 16 most-significant bits of the rounded value are written to the upper half of *dst*.

The product of the upper halfword of src1 and the lower halfword of src2 is added to the product of the lower halfword of src1 and the upper halfword of src2. The result is rounded by adding 2^{15} to it. The 16 most-significant bits of the rounded value are written to the lower half of dst.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the result is written to *dst*.

This instruction executes unconditionally.

Execution

```
 \begin{array}{l} {\rm sat}(({\rm lsb16}(src1)\times {\rm msb16}(src2)) + ({\rm msb16}(src1)\times {\rm lsb16}(src2))) \to tmp\_e \\ {\rm msb16}({\rm sat}(tmp\_e + 0000\ 8000h)) \to {\rm lsb16}(dst) \\ {\rm sat}(({\rm msb16}(src1)\times {\rm msb16}(src2)) - ({\rm lsb16}(src1)\times {\rm lsb16}(src2))) \to tmp\_o \\ {\rm msb16}({\rm sat}(tmp\_o + 0000\ 8000h)) \to {\rm msb16}(dst) \\ \end{array}
```

Instruction Type Four-cycle

Delay Slots 3

See Also CMPY, CMPYR1, DOTP2, DOTPN2



Examples

Example 1

CMPYR .M1 A0,A1,A2

	Before instruction		4 cycles after instruction (1)
A0	0800 0400h	A2	0040 0034h	
A1	0900 0200h			

Example 2

CMPYR .M2X B0,A1,B2

	Before instruction		4 cycles after instruction (1)
В0	7FFF 7FFFh	B2	7FFF 0000h
A1	7FFF 8000h		

⁽¹⁾ CSR.SAT and SSR.M2 unchanged by operation

Example 3

CMPYR .M1 A0,A1,A2

	Before instruction		4 cycles after instruction
A0	8000 8000h	A2	0000 7FFFh
A1	8000 8000h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction

Example 4

CMPYR .M2 B0,B1,B2

	Before instruction		4 cycles after instruction	
В0	8000 8000h	B2	0001 7FFFh	
B1	8000 8001h			
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h	
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h	

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation



CMPYR1 Complex Multiply Two Pairs, Signed, Packed 16-Bit With Rounding

Syntax CMPYR1 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

;	31	30	29	28	27	23 22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	0	0	0	1	dst	S	rc2	src1		Х	0	0	1	1	0	0	1	1	0	0	S	p
					5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xs2	
dst	s2	

Description

Performs two dot-products between two pairs of signed, packed 16-bit values. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The signed results are rounded with saturation to 31 bits, shifted, packed and written to a 32-bit register.

The product of the lower halfwords of *src1* and *src2* is subtracted from the product of the upper halfwords of *src1* and *src2*. The intermediate result is rounded by adding 2¹⁴ to it. This value is shifted left by 1 with saturation. The 16 most-significant bits of the shifted value are written to the upper half of *dst*.

The product of the upper halfword of src1 and the lower halfword of src2 is added to the product of the lower halfword of src1 and the upper halfword of src2. The intermediate result is rounded by adding 2^{14} to it. This value is shifted left by 1 with saturation. The 16 most-significant bits of the shifted value are written to the lower half of dst.

If either result saturates in the rounding or shifting process, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to dst.

This instruction executes unconditionally.

Execution

```
 \begin{array}{l} {\rm sat}(({\rm lsb16}(src1)\times {\rm msb16}(src2)) + ({\rm msb16}(src1)\times {\rm lsb16}(src2))) \to tmp\_e \\ {\rm msb16}({\rm sat}((tmp\_e + 0000 \ 4000h) << 1)) \to {\rm lsb16}(dst) \\ {\rm sat}(({\rm msb16}(src1)\times {\rm msb16}(src2)) - ({\rm lsb16}(src1)\times {\rm lsb16}(src2))) \to tmp\_o \\ {\rm msb16}({\rm sat}((tmp\_e + 0000 \ 4000h) << 1)) \to {\rm msb16}(dst) \\ \end{array}
```

Instruction Type Four-cycle

Delay Slots 3

See Also CMPY, CMPYR, DOTP2, DOTPN2



Examples

Example 1

CMPYR1 .M1 A0,A1,A2

	Before instruction		4 cycles after instruction (1)
A0	0800 0400h	A2	0080 0068h	
A1	0900 0200h			

Example 2

CMPYR1 .M2X B0,A1,B2

	Before instruction		4 cycles after instruction				
В0	7FFF 7FFFh	B2	7FFF FFFFh				
A1	7FFF 8000h						
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h				
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h				

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction

Example 3

CMPYR1 .M1 A0,A1,A2

	Before instruction		4 cycles after instruction
A0	8000 8000h	A2	0000 7FFFh
A1	8000 8000h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction

Example 4

CMPYR1 .M2 B0,B1,B2

	Before instruction		4 cycles after instruction
В0	C000 C000h	B2	0001 7FFFh
B1	8000 8001h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation



DDOTP4

Double Dot Product, Signed, Packed 16-Bit and Signed, Packed 8-Bit

Syntax

DDOTP4 (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31	30	29	28	27 23		17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	1	1	0	0	0	1	1	0	0	s	р
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	ds2	.M1, .M2
src2	xs4	
dst	dint	

Description


Performs two **DOTP2** operations simultaneously.

The lower byte of the lower halfword of *src2* is sign-extended to 16 bits and multiplied by the lower halfword of *src1*. The upper byte of the lower halfword of *src2* is sign-extended to 16 bits and multiplied by the upper halfword of *src1*. The two products are added together and the result is then written to *dst_e*.

The lower byte of the upper halfword of *src2* is sign-extended to 16 bits and multiplied by the lower halfword of *src1*. The upper byte of the upper halfword of *src2* is sign-extended to 16 bits and multiplied by the upper halfword of *src1*. The two products are added together and the result is then written to *dst_o*.

There are no saturation cases possible.

This instruction executes unconditionally.





Execution

 $(\text{msb16}(\textit{src1}) \times \text{msb8}(\text{lsb16}(\textit{src2}))) + (\text{lsb16}(\textit{src1}) \times \text{lsb8}(\text{lsb16}(\textit{src2}))) \rightarrow \textit{dst_e} \\ (\text{msb16}(\textit{src1}) \times \text{msb8}(\text{msb16}(\textit{src2}))) + (\text{lsb16}(\textit{src1}) \times \text{lsb8}(\text{msb16}(\textit{src2}))) \rightarrow \textit{dst_o} \\$

Instruction Type Four-cycle

Delay Slots 3

Examples Example 1

DDOTP4 .M1 A4,A5,A9:A8

	Before instruction			4 cycles after instru	ction	ı
A4	0005 0003h	5, 3	A8	0000 001Bh	$(5 \times 3) + (3 \times 4) = 27$	ı
A5	0102 0304h	1, 2, 3, 4	A9	0000 000Bh	$(5 \times 1) + (3 \times 2) = 11$	ı

Example 2

DDOTP4 .M1X A4,B5,A9:A8

	Before instruction		4 cycles after instru	ction
A4	8000 8000h	A8	FF81 0000h	
B5	8080 7F7Fh	A9	0080 0000h	



DDOTPH2

Double Dot Product, Two Pairs, Signed, Packed 16-Bit

Syntax

DDOTPH2 (.unit) src1_o:src1_e, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17 1:	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1	Х	0	1	0	1	1	1	1	1	0	0	S	р
				5	5	5	1											1	1

Opcode map field used	For operand type	Unit
src1	ds2	.M1, .M2
src2	xs2	
dst	dint	

Description


Returns two dot-products between two pairs of signed, packed 16-bit values. The values in *src1_e*, *src1_o*, and *src2* are treated as signed, packed 16-bit quantities. The signed results are written to a 64-bit register pair.

The product of the lower halfwords of *src1_o* and *src2* is added to the product of the upper halfwords of *src1_o* and *src2*. The result is then written to *dst_o*.

The product of the upper halfword of *src2* and the lower halfword of *src1_o* is added to the product of the lower halfword of *src2* and the upper halfword of *src1_e*. The result is then written to *dst_e*.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to $dst_o:dst_e$.

This instruction executes unconditionally.





Execution

Instruction Type Four-cycle

Delay Slots 3

See Also DDOTPL2, DDOTPL2R

Example 1

DDOTPH2 .M1 A5:A4,A6,A9:A8

	Before instruction			4 cycles after instru	iction ⁽¹⁾
A4	0005 0003h	5,3	A8	0000 0021h	$(4 \times 7) + (5 \times 1) = 33$
A5	0002 0004h	2,4	A9	0000 0012h	$(2 \times 7) + (4 \times 1) = 18$
A6	0007 0001h	7 , 1			

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

DDOTPH2 .M1 A5:A4,A6,A9:A8

	Before instruction	4 cycles after instruction
A4	8000 5678h	A8 7FFF FFFFh
A5	1234 8000h	A9 36E6 0000h
A6	8000 8000h	
CSR	0001 0100h	CSR ⁽¹⁾ 0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾ 0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction

Example 3

DDOTPH2 .M2X B5:B4,A6,B9:B8

	Before instruction	4 cycles after instruction (1)
B4	46B4 16BAh	B8 F41B 4AFFh
B5	BBAE D169h	B9 F3B4 FAADh
A6	340B F73Bh	

⁽¹⁾ CSR.SAT and SSR.M2 unchanged by operation



DDOTPH2R

Double Dot Product With Rounding, Two Pairs, Signed, Packed 16-Bit

Syntax

DDOTPH2R (.unit) src1_o:src1_e, src2, dst

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	1	0	1	0	1	1	1	0	0	S	р
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	ds2	.M1, .M2
src2	xs2	
dst	s2	

Description

Returns two dot-products between two pairs of signed, packed 16-bit values. The values in *src1_e*, *src1_o*, and *src2* are treated as signed, packed 16-bit quantities. The signed results are rounded, shifted right by 16 and packed into a 32-bit register.

The product of the lower halfwords of *src1_o* and *src2* is added to the product of the upper halfwords of *src1_o* and *src2*. The result is rounded by adding 2¹⁵ to it and saturated if appropriate. The 16 most-significant bits of the result are written to the 16 most-significant bits of *dst*.

The product of the upper halfword of *src2* and the lower halfword of *src1_o* is added to the product of the lower halfword of *src2* and the upper halfword of *src1_e*. The result is rounded by adding 2¹⁵ to it and saturated if appropriate. The 16 most-significant bits of the result are written to the 16 least-significant bits of *dst*.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to *dst*.

This instruction executes unconditionally.

Execution

 $\begin{array}{l} {\rm msb16(sat((msb16(\textit{src1_o}) \times msb16(\textit{src2})) + } \\ {\rm (lsb16(\textit{src1_o}) \times lsb16(\textit{src2})) + 0000 \ 8000h)) \rightarrow msb16(\textit{dst})} \\ {\rm msb16(sat((lsb16(\textit{src1_o}) \times msb16(\textit{src2})) + } \\ {\rm (msb16(\textit{src1_e}) \times lsb16(\textit{src2})) + 0000 \ 8000h)) \rightarrow lsb16(\textit{dst})} \end{array}$

Instruction Type Four-cycle

Delay Slots 3

See Also DDOTPL2, DDOTPL2R



Example 1

DDOTPH2R .M1 A5:A4,A6,A8

	Before instruction	4 cycles after instruction ⁽¹⁾
A4	46B4 16BAh	A8 F3B5 F41Bh
A5	BBAE D169h	
A6	340B F73Bh	

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

DDOTPH2R .M1 A5:A4,A6,A8

	Before instruction	4 cycles after instructio
A4	8000 5678h	A8 36E6 7FFFh
A5	1234 8000h	
A6	8000 8001h	
CSR	0001 0100h	CSR ⁽¹⁾ 0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾ 0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction

Example 3

DDOTPH2R .M2 B5:B4,B6,B8

	Before instruction		4 cycles after instruction
B4	8000 8000h	B8	7FFF 7FFFh
B5	8000 8000h		
B6	8000 8001h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction



DDOTPL2

Double Dot Product, Two Pairs, Signed, Packed 16-Bit

Syntax

DDOTPL2 (.unit) src1_o:src1_e, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18		3 1	2 1	1 10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1	>		0 1	0	1	1	0	1	1	0	0	s	р
				5	5	5	1	1										1	1

Opcode map field used	For operand type	Unit
src1	ds2	.M1, .M2
src2	xs2	
dst	dint	


Description

Returns two dot-products between two pairs of signed, packed 16-bit values. The values in *src1_e*, *src1_o*, and *src2* are treated as signed, packed 16-bit quantities. The signed results are written to a 64-bit register pair.

The product of the lower halfwords of *src1*_e and *src2* is added to the product of the upper halfwords of *src1*_e and *src2*. The result is then written to *dst_e*.

The product of the upper halfword of *src2* and the lower halfword of *src1_o* is added to the product of the lower halfword of *src2* and the upper halfword of *src1_e*. The result is then written to *dst_o*.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to $dst_o:dst_e$.





Execution

Instruction Type Four-cycle

Delay Slots 3

See Also DDOTPH2, DDOTPH2R

Example 1

DDOTPL2 .M1 A5:A4,A6,A9:A8

	Before instruction			4 cycles after instru	iction (1)
A4	0005 0003h	5,3	A8	0000 0026h	$(4 \times 7) + (5 \times 1) = 33$
A5	0002 0004h	2,4	A9	0000 0021h	$(2 \times 7) + (4 \times 1) = 18$
A6	0007 0001h	7 , 1			

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

DDOTPL2 .M1 A5:A4,A6,A9:A8

	Before instruction	4 cycles after instruction (1)
A4	46B4 16BAh	A8 0D98 4C9Ah
A5	BBAE D169h	A9 F41B 4AFFh
A6	340B F73Bh	

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 3

DDOTPL2 .M1 A5:A4,A6,A9:A8

	Before instruction	4 cycles after instruction
A4	8000 5678h	A8 14C4 0000h
A5	1234 8000h	A9 7FFF FFFFh
A6	8000 8000h	
CSR	0001 0100h	CSR ⁽¹⁾ 0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾ 0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction



DDOTPL2R

Double Dot Product With Rounding, Two Pairs, Signed Packed 16-Bit

Syntax

DDOTPL2R (.unit) src1_o:src1_e, src2, dst

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	1	0	1	0	0	1	1	0	0	s	р
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	ds2	.M1, .M2
src2	xs2	
dst	s2	

Description

Returns two dot-products between two pairs of signed, packed 16-bit values. The values in *src1_e*, *src1_o*, and *src2* are treated as signed, packed 16-bit quantities. The signed results are rounded, shifted right by 16 and packed into a 32-bit register.

The product of the lower halfwords of *src1_e* and *src2* is added to the product of the upper halfwords of *src1_e* and *src2*. The result is rounded by adding 2¹⁵ to it and saturated if appropriate. The 16 most-significant bits of the result are written to the 16 least-significant bits of *dst*.

The product of the upper halfword of *src2* and the lower halfword of *src1_o* is added to the product of the lower halfword of *src2* and the upper halfword of *src1_e*. The result is rounded by adding 2¹⁵ to it and saturated if appropriate. The 16 most-significant bits of the result are written to the 16 most-significant bits of *dst*.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to dst.

Execution

msb16(sat((msb16($src1_e$) × msb16(src2)) + (lsb16($src1_e$) × lsb16(src2)) + 0000 8000h)) → lsb16(dst) msb16(sat((lsb16($src1_e$) × msb16(src2)) + (msb16($src1_e$) × lsb16(src2)) + 0000 8000h)) → msb16(dst)

Instruction Type Four-cycle

Delay Slots 3

See Also DDOTPH2R, DDOTPH2, DDOTPH2



Examples Example 1

DDOTPL2R .M1 A5:A4,A6,A8

	Before instruction	4 cycles after instruction (1)
A4	46B4 16BAh	A8 F41B 0D98h
A5	BBAE D169h	
A6	340B F73Bh	

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

DDOTPL2R .M1 A5:A4,A6,A8

	Before instruction	4 cycles after instruction
A4	8000 5678h	A8 7FFF 14C4h
A5	1234 8000h	
A6	8000 8001h	
CSR	0001 0100h	CSR ⁽¹⁾ 0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾ 0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction

Example 3

DDOTPL2R .M2 B5:B4,B6,B8

	Before instruction		4 cycles after instruction
B4	8000 8000h	B8	7FFF 7FFFh
B5	8000 8000h		
B6	8000 8001h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction



DEAL Deinterleave and Pack

Syntax DEAL (.unit) src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		1	1	1	0	1	Х	0	0	0	0	1	1	1	1	0	0	S	р
3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.M1, .M2
dst	uint	

Description

Performs a deinterleave and pack operation on the bits in *src2*. The odd and even bits of *src2* are extracted into two separate, 16-bit quantities. These 16-bit quantities are then packed such that the even bits are placed in the lower halfword, and the odd bits are placed in the upper halfword.


As a result, bits 0, 2, 4, ..., 28, 30 of src2 are placed in bits 0, 1, 2, ..., 14, 15 of dst. Likewise, bits 1, 3, 5, ..., 29, 31 of src2 are placed in bits 16, 17, 18, ..., 30, 31 of dst.




NOTE: The DEAL instruction is the exact inverse of the SHFL instruction (see SHFL).

Execution

```
if (cond)  \begin{cases} src2_{31,29,27...1} \rightarrow dst_{31,30,29...16} \\ src2_{30,28,26...0} \rightarrow dst_{15,14,13...0} \\ \end{cases}  else nop
```





www.ti.com

Pipeline

Pipeline Stage	E1	E2
Read	src2	_
Written		dst
Unit in use	.M	

Two-cycle **Instruction Type**

Delay Slots

See Also SHFL

Example DEAL .M1 A1,A2

	Before instruction	2 cycles after	rinstruction
A1	9E52 6E30h	A1 9E52 6E30h	
A2	xxxx xxxxh	A2 B174 6CA4h	





DINT Disable Interrupts and Save Previous Enable State

DINT Syntax

unit = none

Opcode

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	р

1

Description

Disables interrupts in the current cycle, copies the contents of the GIE bit in TSR into the SGIE bit in TSR, and clears the GIE bit in both TSR and CSR. The PGIE bit in CSR is unchanged.

The CPU will not service a maskable interrupt in the cycle immediately following the **DINT** instruction. This behavior differs from writes to GIE using the **MVC** instruction. See section 5.2 for details.

The **DINT** instruction cannot be placed in parallel with the following instructions: **MVC** reg, TSR; MVC reg, CSR; B IRP; B NRP; NOP n; RINT; SPKERNEL; SPKERNELR; SPLOOP; SPLOOPD; SPLOOPW; SPMASK; or SPMASKR.

This instruction executes unconditionally.

NOTE: The use of the DINT and RINT instructions in a nested manner, like the following code:

DINT

DINT

RINT RINT

leaves interrupts disabled. The first DINT leaves TSR.GIE cleared to 0, so the second DINT leaves TSR,.SGIE cleared to 0. The RINT instructions, therefore, copy zero to TSR.GIE (leaving interrupts disabled).

Execution

Disable interrupts in current cycle

GIE bit in TSR → SGIE bit in TSR

 $0 \rightarrow GIE$ bit in TSR

 $0 \rightarrow GIE$ bit in CSR

Instruction Type Single-cycle

Delay Slots

See Also **RINT**



DMV	Move Two Independent Registers to Register Pair
-----	---

Syntax DMV (.unit) src1, src2, dst_o:dst_e

unit = .S1 or .S2

Opcode

31 29	28	27	23		8 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		src1		Х	1	1	1	0	1	1	1	1	0	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.S1, .S2
src2	xsint	
dst	dint	

Description

The *src1* operand is written to the odd register of the register pair specified by *dst* and the *src2* operand is written to the even register of the register pair specified by *dst*.

Execution

if (cond)
$$\begin{cases} src2 \rightarrow dst_e \\ src1 \rightarrow dst_o \\ \end{cases}$$

else nop

Instruction Type Single-cycle

Delay Slots 0

Examples Example 1

DMV .S1 A0,A1,A3:A2

	Before instruction	1 cycle after instruction
A0	8765 4321h	A2 1234 5678h
A1	1234 5678h	A3 8765 4321h

Example 2

DMV .S2X B0,A1,B3:B2

	Before instruction	1 cycle after instruction
В0	0007 0009h	B2 1234 5678h
A1	1234 5678h	B3 0007 0009h



DOTP2

Dot Product, Signed, Packed 16-Bit

Syntax

DOTP2 (.unit) src1, src2, dst

or

DOTP2 (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 29	28	27	23 2		17 1	3 12	10	6	5	4	3	2	1	0
creg	Z	dst		src2	src1	х	ор		1	1	0	0	s	р
3	1	5		5	5	1	5						1	1


Opcode map field used	For operand type	Unit	Opfield
src1	s2	.M1, .M2	01100
src2	xs2		
dst	int		
src1	s2	.M1, .M2	01011
src2	xs2		
dst	sllong		

Description

Returns the dot-product between two pairs of signed, packed 16-bit values. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The signed result is written either to a single 32-bit register, or sign-extended into a 64-bit register pair.


The product of the lower halfwords of *src1* and *src2* is added to the product of the upper halfwords of *src1* and *src2*. The result is then written to the *dst*.

If the result is sign-extended into a 64-bit register pair, the upper word of the register pair always contains either all 0s or all 1s, depending on whether the result is positive or negative, respectively.





The 32-bit result version returns the same results that the 64-bit result version does in the lower 32 bits. The upper 32-bits are discarded.



NOTE: In the overflow case, where all four halfwords in *src1* and *src2* are 8000h, the value 8000 0000h is written into the 32-bit *dst* and 0000 0000 8000 0000h is written into the 64-bit *dst*.

Execution

if (cond) (lsb16(src1) × lsb16(src2)) + (msb16(src1) × msb16(src2)) $\rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTPN2

Example 1

DOTP2 .M1 A5,A6,A8

	Before instructio	n		4 cycles after instruction	on
A5	6A32 1193h	27186 4499	A5	6A32 1193h	
A6	B174 6CA4h	-20108 27812	A6	B174 6CA4h	
A8	xxxx xxxxh		A8	E6DF F6D4h -	421,529,900



Example 2

DOTP2 .M1 A5,A6,A9:A8

	Before instruction	1		4 cycles after ins	truction
A5	6A32 1193h	27186 4499	A5	6A32 1193h	
A6	B174 6CA4h	-20108 27812	A6	B174 6CA4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	FFFF FFFFh	E6DF F6D4h
		1			-421,529,900

Example 3

DOTP2 .M2 B2,B5,B8

	Before instruction			4 cycles after instruct	ion
B2	1234 3497h	4660 13463	B2	1234 3497h	
B5	21FF 50A7h	8703 20647	B5	21FF 50A7h	
B8	xxxx xxxxh		B8	12FC 544Dh	318,526,541

Example 4

DOTP2 .M2 B2,B5,B9:B8

	Before instructio	n		4 cycles after ins	struction
B2	1234 3497h	4660 13463	B2	1234 3497h	
B5	21FF 50A7h	8703 20647	B5	21FF 50A7h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	0000 0000h	12FC 544Dh
					318,526,541



DOTPN2 Dot Product With Negate, Signed, Packed 16-Bit

Syntax DOTPN2 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode


31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	1	0	0	1	1	1	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xs2	
dst	int	

Description

Returns the dot-product between two pairs of signed, packed 16-bit values where the second product is negated. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The signed result is written to a single 32-bit register.

The product of the lower halfwords of *src1* and *src2* is subtracted from the product of the upper halfwords of *src1* and *src2*. The result is then written to *dst*.



Execution

Note that unlike **DOTP2**, no overflow case exists for this instruction.

if (cond) else nop

 $(msb16(src1) \times msb16(src2)) - (lsb16(src1) \times lsb16(src2)) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTP2





Example 1

DOTPN2 .M1 A5,A6,A8

	Before instruction			4 cycles after instruction	
A5	3629 274Ah	13865 10058	A5	3629 274Ah	
A6	325C 8036h	12892 -32714	A6	325C 8036h	
A8	xxxx xxxxh		A8	1E44 2F20h	507,784,992

Example 2

DOTPN2 .M2 B2,B5,B8

	Before instruction			4 cycles after instruction	
B2	3FF6 5010h	16374 20496	B2	3FF6 5010h	
B5	B1C3 0244h	-20029 580	B5	B1C3 0244h	
B8	xxxx xxxxh		B8	EBBE 6A22h	-339,842,526



DOTPNRSU2

Dot Product With Negate, Shift and Round, Signed by Unsigned, Packed 16-Bit

Syntax

DOTPNRSU2 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 2	29	28	27	23	22	18	17	13		11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2		src	1	Х	0	0	0	1	1	1	1	1	0	0	s	p
3		1		5	5		5		1											1	1


Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xu2	
dst	int	

Description

Returns the dot-product between two pairs of packed 16-bit values, where the second product is negated. This instruction takes the result of the dot-product and performs an additional round and shift step. The values in *src1* are treated as signed, packed 16-bit quantities; whereas, the values in *src2* are treated as unsigned, packed 16-bit quantities. The results are written to *dst*.

The product of the lower halfwords of *src1* and *src2* is subtracted from the product of the upper halfwords of *src1* and *src2*. The value 2¹⁵ is then added to this sum, producing an intermediate 33-bit result. The intermediate result is signed shifted right by 16, producing a rounded, shifted result that is sign extended and placed in *dst*.

The intermediate results of the **DOTPNRSU2** instruction are maintained to a 33-bit precision, ensuring that no overflow may occur during the subtracting and rounding steps.



Execution





Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTP2, DOTPN2, DOTPRSU2

Examples Example 1

DOTPNRSU2 .M1 A5, A6, A8

	Before instruction			4 cycles after instruction
A5	3629 274Ah	13865 10058 signed	A5	3629 274Ah
A6	325C 8036h	12892 32822 unsigned	A6	325C 8036h
A8	xxxx xxxxh		A8	FFFF F6FAh -2310 (signed)

Example 2

DOTPNRSU2 .M2 B2, B5, B8

	Before instruction			4 cycles after instruction
B2	3FF6 5010h	16374 20496 signed	B2	3FF6 5010h
B5	B1C3 0244h	45507 580 unsigned	B5	B1C3 0244h
B8	xxxx xxxxh		B8	0000 2BB4h 11188 (signed)

Example 3

DOTPNRSU2 .M2 B12, B23, B11

	Before instruction			4 cycles after instruction	on
B12	7FFF 8000h	32767 -32768 signed	B12	7FFF 8000h	
B23	FFFF FFFFh	65535 65535 unsigned	B23	FFFF FFFFh	
B11	xxxx xxxxh		B11	xxxx xxxxh	Overflow occurs; result undefined



DOTPNRUS2

Dot Product With Negate, Shift and Round, Unsigned by Signed, Packed 16-Bit

Syntax

DOTPNRUS2 (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23		8 17	7	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	0	0	0	1	1	1	1	1	0	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xu2	
dst	int	

Description

The **DOTPNRUS2** pseudo-operation performs the dot-product between two pairs of packed 16-bit values, where the second product is negated. This instruction takes the result of the dot-product and performs an additional round and shift step. The values in *src1* are treated as signed, packed 16-bit quantities; whereas, the values in *src2* are treated as unsigned, packed 16-bit quantities. The results are written to *dst*. The assembler uses the **DOTPNRSU2** *src1*, *src2*, *dst* instruction to perform this task (see DOTPNRSU2).

The product of the lower halfwords of *src1* and *src2* is subtracted from the product of the upper halfwords of *src1* and *src2*. The value 2¹⁵ is then added to this sum, producing an intermediate 32 or 33-bit result. The intermediate result is signed shifted right by 16, producing a rounded, shifted result that is sign extended and placed in *dst*.

The intermediate results of the **DOTPNRUS2** pseudo-operation are maintained to a 33-bit precision, ensuring that no overflow may occur during the subtracting and rounding steps.

Execution

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			



www.ti.com DOTPNRUS2 — Dot Product With Negate, Shift and Round, Unsigned by Signed, Packed 16-Bit

Instruction Type Four-cycle

Delay Slots 3

See Also DOTP2, DOTPN2, DOTPNRSU2, DOTPRUS2



DOTPRSU2

Dot Product With Shift and Round, Signed by Unsigned, Packed 16-Bit

Syntax

DOTPRSU2 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23		18 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	0	0	1	1	0	1	1	1	0	0	s	p
3	1	5		5		5		1											1	1


Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xu2	
dst	int	

Description

Returns the dot-product between two pairs of packed 16-bit values. This instruction takes the result of the dot-product and performs an additional round and shift step. The values in src1 are treated as signed packed 16-bit quantities; whereas, the values in src2 are treated as unsigned packed 16-bit quantities. The results are written to dst.

The product of the lower halfwords of src1 and src2 is added to the product of the upper halfwords of src1 and src2. The value 2¹⁵ is then added to this sum, producing an intermediate 32 or 33-bit result. The intermediate result is signed shifted right by 16, producing a rounded, shifted result that is sign extended and placed in dst.

The intermediate results of the **DOTPRSU2** instruction are maintained to a 33-bit precision, ensuring that no overflow may occur during the subtracting and rounding steps.



NOTE: Certain combinations of operands for the DOTPRSU2 instruction results in an overflow condition. If an overflow does occur, the result is undefined. Overflow can be avoided if the sum of the two products plus the rounding term is less than or equal to 231 - 1 for a positive sum and greater than or equal to -2^{31} for a negative sum.

> The intermediate results of the DOTPRSU2 instruction are maintained to 33-bit precision, ensuring that no overflow may occur during the adding and rounding steps.



Execution

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTP2, DOTPN2, DOTPNRSU2

Examples Example 1

DOTPRSU2 .M1 A5, A6, A8

	Before instruction			4 cycles after instruction
A5	3629 274Ah	13865 10058 signed	A5	3629 274Ah
A6	325C 8036h	12892 32822 unsigned	A6	325C 8036h
A8	xxxx xxxxh		A8	0000 1E55h 7765 (signed)

Example 2

DOTPRSU2 .M2 B2, B5, B8

	Before instruction	1		4 cycles after instruction					
B2	B1C3 0244h	-20029 580 signed	B2	B1C3 0244h	20029 580 signed				
B5	3FF6 5010h	16374 20496 unsigned	B5	3FF6 5010h	16374 20496 unsigned				
В8	xxxx xxxxh		B8	FFFF ED29h	-4823 (signed)				



Example 3

DOTPRSU2 .M2 B12, B23, B11

	Before instruction			4 cycles after ins	struction
B12	7FFF 7FFFh	32767 32767 signed	B12	7FFF 7FFFh	
B23	FFFF FFFFh	65535 65535 unsigned	B23	FFFF FFFFh	
B11	xxxx xxxxh		B11	xxxx xxxxh	Overflow occurs; result undefined



DOTPRUS2

Dot Product With Shift and Round, Unsigned by Signed, Packed 16-Bit

Syntax

DOTPRUS2 (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23		18 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	0	0	1	1	0	1	1	1	0	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src1 src2 dst	xu2	
dst	int	

Description

The **DOTPRUS2** pseudo-operation returns the dot-product between two pairs of packed 16-bit values. This instruction takes the result of the dot-product, and performs an additional round and shift step. The values in *src1* are treated as signed packed 16-bit quantities; whereas, the values in *src2* are treated as unsigned packed 16-bit quantities. The results are written to *dst*. The assembler uses the **DOTPRSU2** (.unit) *src1*, *src2*, *dst* instruction to perform this task (see **DOTPRSU2**).

The product of the lower halfwords of src1 and src2 is added to the product of the upper halfwords of src1 and src2. The value 2^{15} is then added to this sum, producing an intermediate 32-bit result. The intermediate result is signed shifted right by 16, producing a rounded, shifted result that is sign extended and placed in dst.

The intermediate results of the **DOTPRUS2** pseudo-operation are maintained to a 33-bit precision, ensuring that no overflow may occur during the subtracting and rounding steps.

Execution

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			



DOTPRUS2 — Dot Product With Shift and Round, Unsigned by Signed, Packed 16-Bit

www.ti.com

Instruction Type Four-cycle

Delay Slots 3

See Also DOTP2, DOTPN2, DOTPNRUS2, DOTPRSU2



DOTPSU4

Dot Product, Signed by Unsigned, Packed 8-Bit

Syntax

```
DOTPSU4 (.unit) src1, src2, dst
```

unit = .M1 or .M2

Opcode


31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	0	1	0	1	1	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s4	.M1, .M2
src2	xu4	
dst	int	

Description

Returns the dot-product between four sets of packed 8-bit values. The values in *src1* are treated as signed packed 8-bit quantities; whereas, the values in *src2* are treated as unsigned 8-bit packed data. The signed result is written into *dst*.

For each pair of 8-bit quantities in *src1* and *src2*, the signed 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*. The four products are summed together, and the resulting dot product is written as a signed 32-bit result to *dst*.



Execution

```
if (cond)  \{ \\ (\text{sbyte0}(\textit{src1}) \times \text{ubyte0}(\textit{src2})) + \\ (\text{sbyte1}(\textit{src1}) \times \text{ubyte1}(\textit{src2})) + \\ (\text{sbyte2}(\textit{src1}) \times \text{ubyte2}(\textit{src2})) + \\ (\text{sbyte3}(\textit{src1}) \times \text{ubyte3}(\textit{src2})) \rightarrow \textit{dst} \\ \} \\ \text{else nop}
```



Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTPU4

Example 1

DOTPSU4 .M1 A5, A6, A8

	Before instruction			4 cycles after instructio	n
A5	6A 32 11 93h] 106 50 17 -109 signed	A5	6A 32 11 93h	
A6	B1 74 6C A4h	177 116 108 164 unsigned	A6	B1 74 6C A4h	
A8	xxxx xxxxh		A8	0000 214Ah	8522 (signed)

Example 2

DOTPSU4 .M2 B2, B5, B8

	Before instruction			4 cycles after instructio	n
B2	3F F6 50 10h	63 -10 80 16 signed	B2	3F F6 50 10h	
B5	C3 56 02 44h] 195 86 2 68 unsigned	B5	C3 56 02 44h	
B8	xxxx xxxxh		B8	0000 3181h	12,673 (signed)



DOTPUS4

Dot Product, Unsigned by Signed, Packed 8-Bit

Syntax

DOTPUS4 (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	0	1	0	1	1	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s4	.M1, .M2
src2	xu4	
src1 src2 dst	int	

Description

The **DOTPUS4** pseudo-operation returns the dot-product between four sets of packed 8-bit values. The values in *src1* are treated as signed packed 8-bit quantities; whereas, the values in *src2* are treated as unsigned 8-bit packed data. The signed result is written into *dst*. The assembler uses the **DOTPSU4** (.unit) *src1*, *src2*, *dst* instruction to perform this task (see DOTPSU4).

For each pair of 8-bit quantities in *src1* and *src2*, the signed 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*. The four products are summed together, and the resulting dot-product is written as a signed 32-bit result to *dst*.

Execution

```
if (cond)  \{ \\ (\text{ubyte0}(\textit{src2}) \times \text{sbyte0}(\textit{src1})) + \\ (\text{ubyte1}(\textit{src2}) \times \text{sbyte1}(\textit{src1})) + \\ (\text{ubyte2}(\textit{src2}) \times \text{sbyte2}(\textit{src1})) + \\ (\text{ubyte3}(\textit{src2}) \times \text{sbyte3}(\textit{src1})) \rightarrow \textit{dst} \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type

Four-cycle

Delay Slots

3

See Also

DOTPU4, DOTPSU4



DOTPU4

Dot Product, Unsigned, Packed 8-Bit

Syntax

unit = .M1 or .M2

Opcode


31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	C	dst	src2	src1		Х	0	0	0	1	1	0	1	1	0	0	s	p
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.M1, .M2
src2	xu4	
dst	uint	

Description

Returns the dot-product between four sets of packed 8-bit values. The values in both *src1* and *src2* are treated as unsigned, 8-bit packed data. The unsigned result is written into *dst*.

For each pair of 8-bit quantities in *src1* and *src2*, the unsigned 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*. The four products are summed together, and the resulting dot-product is written as a 32-bit result to *dst*.



Execution

```
if (cond)  \{ \\ (\text{ubyte0}(\textit{src1}) \times \text{ubyte0}(\textit{src2})) + \\ (\text{ubyte1}(\textit{src1}) \times \text{ubyte1}(\textit{src2})) + \\ (\text{ubyte2}(\textit{src1}) \times \text{ubyte2}(\textit{src2})) + \\ (\text{ubyte3}(\textit{src1}) \times \text{ubyte3}(\textit{src2})) \rightarrow \textit{dst} \\ \} \\ \text{else nop}
```





Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			_
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also DOTPSU4

Example DOTPU4 .M1 A5, A6, A8

	Before instruction			4 cycles after instr	ruction
A5	6A 32 11 93h	106 50 17 147 unsigned	A5	6A 32 11 93h	
A6	B1 74 6C A4h	177 116 108 164 unsigned	A6	B1 74 6C A4h	
A8	xxxx xxxxh		A8	0000 C54Ah	50,506 (unsigned)



DPACK2 Parallel PACK2 and PACKH2 Operations

Syntax DPACK2 (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode

3	1	30	29	28	27	24	23	22 18	B 1	17 13	12	11	10	9	8	7	6	5	4	3	2	1	0
0		0	0	1	dst		0	src2		src1	Х	0	1	1	0	1	0	0	1	1	0	s	р
					4			5		5	1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	


Description

Executes a PACK2 instruction in parallel with a PACKH2 instruction.

The **PACK2** function of the **DPACK2** instruction takes the lower halfword from *src1* and the lower halfword from *src2*, and packs them both into *dst_e*. The lower halfword of *src1* is placed in the upper halfword of *dst_e*. The lower halfword of *src2* is placed in the lower halfword of *dst_e*.

The **PACKH2** function of the **DPACK2** instruction takes the upper halfword from *src1* and the upper halfword from *src2*, and packs them both into *dst_o*. The upper halfword of *src1* is placed in the upper halfword of *dst_o*. The upper halfword of *src2* is placed in the lower halfword of *dst_o*.

This instruction executes unconditionally.



Execution

 $lsb16(src1) \rightarrow msb16(dst_e)$

 $lsb16(src2) \rightarrow lsb16(dst_e)$

 $msb16(src1) \rightarrow msb16(dst_o)$

 $msb16(src2) \rightarrow lsb16(dst_o)$



Instruction Type

www.ti.com

Single-cycle

Delay Slots 0

Example DPACK2 .L1 A0,A1,A3:A2

	Before instruction	1 cycle after instruction
A0	8765 4321h	A2 4321 5678h
A1	1234 5678h	A3 8765 1234h



DPACKX2

Parallel PACKLH2 Operations

Syntax

DPACKX2 (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode

3	1	30	29	28	27	24	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0)	0	0	1	dst		0	src2	src1		Х	0	1	1	0	0	1	1	1	1	0	S	p
					4			5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	


Description

Executes two PACKLH2 instructions in parallel.

One **PACKLH2** function of the **DPACKX2** instruction takes the lower halfword from *src1* and the upper halfword from *src2*, and packs them both into *dst_e*. The lower halfword of *src1* is placed in the upper halfword of *dst_e*. The upper halfword of *src2* is placed in the lower halfword of *dst_e*.

The other **PACKLH2** function of the **DPACKX2** instruction takes the upper halfword from *src1* and the lower halfword from *src2*, and packs them both into *dst_o*. The upper halfword of *src1* is placed in the lower halfword of *dst_o*. The lower halfword of *src2* is placed in the upper halfword of *dst_o*.

This instruction executes unconditionally.



Execution

 $lsb16(src1) \rightarrow msb16(dst_e)$

 $msb16(src2) \rightarrow lsb16(dst_e)$

 $msb16(src1) \rightarrow lsb16(dst_o)$

 $lsb16(src2) \rightarrow msb16(dst_o)$



TEXAS INSTRUMENTS

Instruction Type Single-cycle

Delay Slots 0

Example 1

DPACKX2 .L1 A0,A1,A3:A2

	Before instruction	1 cycle after instruction
A0	8765 4321h	A2 4321 1234h
A1	1234 5678h	A3 5678 8765h

Example 2

DPACKX2 .L1X A0,B0,A3:A2

	Before instruction	1 cycle after instruction
A0	3FFF 8000h	A2 8000 4000h
В0	4000 7777h	A3 7777 3FFFh




DPINT Convert Double-Precision Floating-Point Value to Integer

Syntax DPINT (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	dp	.L1, .L2
dst	sint	

Description

The 64-bit double-precision value in *src2* is converted to an integer and placed in *dst*. The operand is read in one cycle by using the *src2* port for the 32 MSBs and the *src1* port for the 32 LSBs.

NOTE:

- 1. If *src2* is NaN, the maximum signed integer (7FFF FFFh or 8000 0000h) is placed in *dst* and the INVAL bit is set.
- If src2 is signed infinity or if overflow occurs, the maximum signed integer (7FFF FFFFh or 8000 0000h) is placed in dst and the INEX and OVER bits are set. Overflow occurs if src2 is greater than 2³¹ 1 or less than -2³¹.
- If src2 is denormalized, 0000 0000h is placed in dst and the INEX and DEN2 bits are set.
- 4. If rounding is performed, the INEX bit is set.

Execution

if (cond) $int(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2_l, src2_h			
Written				dst
Unit in use	.L			

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also DPSP, DPTRUNC, INTDP, SPINT



www.ti.com
Example

DPINT .L1 A1:A0,A4

	Before instruction	n			4 cycles after instruction				
A1:A0	4021 3333h	3333 3333h	8.6	A1:A0	4021 3333h	3333 3333h			
A4	xxxx xxxxh			A4	0000 0009h	9			



DPSP Convert Double-Precision Floating-Point Value to Single-Precision Floating-Point

Value

Syntax DPSP (.unit) src2, dst

unit = .L1 or .L2

Opcode

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z		dst	src2		0	0	0	0	0	Х	0	0	0	1	0	0	1	1	1	0	S	p
	3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	dp	.L1, .L2
dst	sp	

Description

The double-precision 64-bit value in *src2* is converted to a single-precision value and placed in *dst*. The operand is read in one cycle by using the *src2* port for the 32 MSBs and the *src1* port for the 32 LSBs.

NOTE:

- 1. If rounding is performed, the INEX bit is set.
- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 3. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- If src2 is a signed denormalized number, signed 0 is placed in dst and the INEX and DEN2 bits are set.
- If src2 is signed infinity, the result is signed infinity and the INFO bit is set.
- 6. If overflow occurs, the INEX and OVER bits are set and the results are set as follows (LFPN is the largest floating-point number):

	Overflow Output Rounding Mode								
Result Sign	Nearest Even	Zero	+Infinity	Infinity					
+	+infinity	+LFPN	+infinity	+LFPN					
-	-infinity	-LFPN	-LFPN	-infinity					

7. If underflow occurs, the INEX and UNDER bits are set and the results are set as follows (SPFN is the smallest floating-point number):

	Underflow Output Rounding Mode								
Result Sign	Nearest Even	Zero	+Infinity	Infinity					
+	+0	+0	+SFPN	+0					
-	-0	-0	-0	-SFPN					





Execution

if (cond) $sp(src2) \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2_l, src2_h			
Written				dst
Unit in use	.L			

Instruction Type Four-cycle

Delay Slots 3
Functional Unit Latency 1

See Also DPINT, DPTRUNC, INTSP, SPDP

Example DPSP .L1 A1:A0,A4

	Before instruction	n			4 cycles after instruction				
A1:A0	4021 3333h 33333h		8.6	A1:A0	4021 3333h	3333 3333h			
A4	xxxx xxxxh			A4	4109 999Ah	8.6			



DPTRUNC

Convert Double-Precision Floating-Point Value to Integer With Truncation

Syntax

DPTRUNC (.unit) src2, dst

unit = .L1 or .L2

Opcode

31 2	28	3 27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		0	0	0	0	0	Х	0	0	0	0	0	0	1	1	1	0	s	р
3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	dp	.L1, .L2
dst	sint	

Description

The 64-bit double-precision value in *src2* is converted to an integer and placed in *dst*. This instruction operates like **DPINT** except that the rounding modes in the floating-point adder configuration register (FADCR) are ignored; round toward zero (truncate) is always used. The 64-bit operand is read in one cycle by using the *src2* port for the 32 MSBs and the *src1* port for the 32 LSBs.

NOTE:

- 1. If *src2* is NaN, the maximum signed integer (7FFF FFFh or 8000 0000h) is placed in *dst* and the INVAL bit is set.
- If src2 is signed infinity or if overflow occurs, the maximum signed integer (7FFF FFFFh or 8000 0000h) is placed in dst and the INEX and OVER bits are set. Overflow occurs if src2 is greater than 2³¹ 1 or less than -2³¹.
- If src2 is denormalized, 0000 0000h is placed in dst and the INEX and DEN2 bits are set.
- 4. If rounding is performed, the INEX bit is set.

Execution

if (cond) else nop

 $int(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2_l, src2_h			
Written				dst
Unit in use	.L			

Instruction Type

Four-cycle

Delay Slots

3

Functional Unit Latency 1



www.ti.com DPTRUNC — Convert Double-Precision Floating-Point Value to Integer With Truncation

See Also DPINT, DPSP, SPTRUNC

Example DPTRUNC .L1 A1:A0,A4

	Before instruction				4 cycles after instruc	tion
A1:A0	4021 3333h 3333 3333h		8.6	A1:A0	4021 3333h	3333 3333h
A4	xxxx xxxxh			A4	0000 0008h	8



EXT Extract and Sign-Extend a Bit Field

Syntax EXT (.unit) src2, csta, cstb, dst

or

EXT (.unit) src2, src1, dst

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	S2ext	Figure F-28

Opcode Constant form

31 2	9 28	27	23	22 18	17 13	12 8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	csta	cstb	0	1	0	0	1	0	s	р
3	1		5	5	5	5							1	1

Opcode map field used	For operand type	Unit
src2	sint	.S1, .S2
csta	ucst5	
cstb	ucst5	
dst	sint	

Opcode Register form


31 29	28	21 2	3 22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1		Х	1	0	1	1	1	1	1	0	0	0	s	р
3	1	5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src2	xsint	.S1, .S2
src1	uint	
dst	sint	



Description

The field in *src2*, specified by *csta* and *cstb*, is extracted and sign-extended to 32 bits. The extract is performed by a shift left followed by a signed shift right. *csta* and *cstb* are the shift left amount and shift right amount, respectively. This can be thought of in terms of the LSB and MSB of the field to be extracted. Then *csta* = 31 - MSB of the field and *cstb* = *csta* + LSB of the field. The shift left and shift right amounts may also be specified as the ten LSBs of the *src1* register with *cstb* being bits 0-4 and *csta* bits 5-9. In the example below, *csta* is 12 and *cstb* is 11 + 12 = 23. Only the ten LSBs are valid for the register version of the instruction. If any of the 22 MSBs are non-zero, the result is invalid.



Execution If the constant form is used:

if (cond) else nop

src2 ext csta, $cstb \rightarrow dst$

If the register form is used:

if (cond) else nop

src2 ext src1 $_{9..5}$, src1 $_{4..0} \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also EXTU



Examples

Example 1

EXT .S1 A1,10,19,A2

	Before instruction	1 cycle after instruction
A1	07A4 3F2Ah	A1 07A4 3F2Ah
A2	xxxx xxxxh	A2 FFFF F21Fh

Example 2

EXT .S1 A1,A2,A3

	Before instruction	1 cycle after instruction
A1	03B6 E7D5h	A1 03B6 E7D5h
A2	0000 0073h	A2 0000 0073h
А3	xxxx xxxxh	A3 0000 03B6h

266 Instruction Set SPRUFE8B-July 2010



EXTU Extract and Zero-Extend a Bit Field

Syntax EXTU (.unit) src2, csta, cstb, dst

or

EXTU (.unit) src2, src1, dst

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sc5	Figure F-27
	S2ext	Figure F-28

Opcode Constant form:

31 29	28	27	23	22 18	1/ 1	3 12	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	csta		cstb	0	0	0	0	1	0	s	p
3	1	5		5	5		5							1	1

Opcode map field used	For operand type	Unit
src2	uint	.S1, .S2
csta	ucst5	
cstb	ucst5	
dst	uint	

Opcode Register form:


3		28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2		src1		Х	1	0	1	0	1	1	1	0	0	0	S	р
	3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.S1, .S2
src1	uint	
dst	uint	



Description

The field in *src2*, specified by *csta* and *cstb*, is extracted and zero extended to 32 bits. The extract is performed by a shift left followed by an unsigned shift right. *csta* and *cstb* are the amounts to shift left and shift right, respectively. This can be thought of in terms of the LSB and MSB of the field to be extracted. Then *csta* = 31 - MSB of the field and *cstb* = *csta* + LSB of the field. The shift left and shift right amounts may also be specified as the ten LSBs of the *src1* register with *cstb* being bits 0-4 and *csta* bits 5-9. In the example below, *csta* is 12 and *cstb* is 11 + 12 = 23. Only the ten LSBs are valid for the register version of the instruction. If any of the 22 MSBs are non-zero, the result is invalid.



Execution If the constant form is used:

if (cond) else nop

src2 extu csta, $cstb \rightarrow dst$

If the register form is used:

if (cond) else nop

src2 extu src1 $_{9..5}$, src1 $_{4..0} \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also EXT





Example 1

EXTU .S1 A1,10,19,A2

	Before instruction	1 cycle after instruction
A1	07A4 3F2Ah	A1 07A4 3F2Ah
A2	xxxx xxxxh	A2 0000 121Fh

Example 2

EXTU .S1 A1,A2,A3

	Before instruction	1 cycle after instruction
A1	03B6 E7D5h	A1 03B6 E7D5h
A2	0000 0156h	A2 0000 0156h
А3	xxxx xxxxh	A3 0000 036Eh



GMPY

Galois Field Multiply

Syntax

```
GMPY (.unit) src1, src2, dst
```

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17 1	13 1	2 1	1 10	9 8	7 6	5 4	3 2	1	0
0	0	0	1	dst	src2	src1	,	x (0 1	1 1	1 1	1 1	0 0	s	p
				5	5	5		1						1	1

Opcode map field used	For operand type	Unit
src1	uint	.M1, .M2
src2	uint	
dst	uint	

Description

Performs a Galois field multiply, where *src1* is 32 bits and *src2* is limited to 9 bits. This utilizes the existing hardware and produces a 32-bit result. This multiply connects all levels of the gmpy4 together and only extends out by 8 bits, the resulting data is XORed down by the 32-bit polynomial.

The polynomial used comes from either the GPLYA or GPLYB control register depending on which side (A or B) the instruction executes. If the A-side M1 unit is used, the polynomial comes from GPLYA; if the B-side M2 unit, the polynomial comes from GPLYB.

This instruction executes unconditionally.

```
uword gmpy(uword src1,uword src2,uword polynomial)
 // the multiply is always between GF(2^9) and GF(2^32)
 // so no size information is needed
 uint pp;
 uint mask, tpp;
 uint I;
     mask = 0x00000100; // multiply by computing
                      // partial products.
     for ( I=0; i<8; I++ ){
      if ( src2 & mask ) pp ^= src1;
       mask >>= 1;
       tpp = pp << 1;
       if (pp & 0x80000000) pp = polynomial ^ tpp;
                   pp = tpp;
if ( src2 & 0x1 ) pp ^= src1;
return (pp); // leave it asserted left.
```

270 Instruction Set SPRUFE8B-July 2010





Execution

```
if (unit = M1)
GMPY\_poly = GPLYA
lsb9(src2) gmpy src1 \rightarrow dst
else if (unit = M2)
GMPY\_poly = GPLYB
lsb9(src2) gmpy src1 \rightarrow dst
```

Instruction Type Four-cycle

Delay Slots 3

See Also GMPY4, XORMPY, XOR

Example GMPY .M1 A0,A1,A2 GPLYA = 87654321

	Before instruction	4 cycles after instruction
A0	1234 5678h	A2 C721 A0EFh
A1	0000 0126h	



GMPY4

Galois Field Multiply, Packed 8-Bit

Syntax

GMPY4 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode


31 29	28	27	23	22 18	3 17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	1		dst	src2	src1		Х	0	1	0	0	0	1	1	1	0	0	S	p
3			5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.M1, .M2
src2	xu4	
dst	u4	

Description

Performs the Galois field multiply on four values in *src1* with four parallel values in *src2*. The four products are packed into dst. The values in both *src1* and *src2* are treated as unsigned, 8-bit packed data.

For each pair of 8-bit quantities in *src1* and *src2*, the unsigned, 8-bit value from *src1* is Galois field multiplied (gmpy) with the unsigned, 8-bit value from *src2*. The product of *src1* byte 0 and *src2* byte 0 is written to byte0 of *dst*. The product of *src1* byte 1 and *src2* byte 1 is written to byte1 of *dst*. The product of *src1* byte 2 and *src2* byte 2 is written to byte2 of *dst*. The product of *src1* byte 3 and *src2* byte 3 is written to the most-significant byte in *dst*.



The size and polynomial are controlled by the Galois field polynomial generator function register (GFPGFR). All registers in the control register file can be written using the **MVC** instruction (see MVC).

The default field generator polynomial is 1Dh, and the default size is 7. This setting is used for many communications standards.

Note that the **GMPY4** instruction is commutative, so:

GMPY4 .M1 A10,A12,A13

is equivalent to:

GMPY4 .M1 A12,A10,A13



Execution

```
if (cond)  \{ \\ (\text{ubyte0}(\textit{src1}) \text{ gmpy ubyte0}(\textit{src2})) \rightarrow \text{ubyte0}(\textit{dst}); \\ (\text{ubyte1}(\textit{src1}) \text{ gmpy ubyte1}(\textit{src2})) \rightarrow \text{ubyte1}(\textit{dst}); \\ (\text{ubyte2}(\textit{src1}) \text{ gmpy ubyte2}(\textit{src2})) \rightarrow \text{ubyte2}(\textit{dst}); \\ (\text{ubyte3}(\textit{src1}) \text{ gmpy ubyte3}(\textit{src2})) \rightarrow \text{ubyte3}(\textit{dst}) \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also GMPY, MVC, XOR

Example 1

GMPY4 .M1 A5,A6,A7; polynomial = 0x1d

	Before instruction			4 cycles after instruc	tion
A5	45 23 00 01h	69 35 0 1 unsigned	A5	45 23 00 01h	
A6	57 34 00 01h	87 52 0 1 unsigned	A6	57 34 00 01h	
A7	xxxx xxxxh		A7	72 92 00 01h	114 146 0 1 unsigned

Example 2

GMPY4 .M1 A5, A6, A7; field size is 0x7

	Before instruction			4 cycles after instruc	ction	
A5	FF FE 02 1Fh	255 254 2 31 unsigned	A5	FF FE 02 1Fh		
A6	FF FE 02 01h	255 254 2 1 unsigned	A6	FF FE 02 01h		
A7	xxxx xxxxh		A7	E2 E3 04 1Fh	226 227 4 31 unsigned	



IDLE Multicycle NOP With No Termination Until Interrupt

Syntax IDLE

unit = none

Opcode

31 30 29 28 27 26 25 24 23 22 21 20 19 18 17 16 15 14 13 12 11 10 р

Description Performs an infinite multicycle **NOP** that terminates upon servicing an interrupt, or a

branch occurs due to an **IDLE** instruction being in the delay slots of a branch.

The **IDLE** instruction cannot be paired with any other multicycle **NOP** instruction in the same execute packet. Instructions that generate a multicycle **NOP** are: **ADDKPC**,

BNOP, and the multicycle NOP.

Instruction Type NOP

Delay Slots 0




INTDP Convert Signed Integer to Double-Precision Floating-Point Value

Syntax INTDP (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	xsint	.L1, .L2
dst	dp	

Description

The signed integer value in src2 is converted to a double-precision value and placed in

dst.

You cannot set configuration bits with this instruction.

Execution

if (cond) $dp(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	src2				
Written				dst_l	dst_h
Unit in use	.L				

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type INTDP

Delay Slots 4

Functional Unit Latency 1

See Also DPINT, INTDPU, INTSP, INTSPU

Example INTDP .L1X B4,A1:A0

	Before instruction	on		4 cycles after ins	struction
B4	1965 1127h	426,053,927	B4	1965 1127h	
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	41B9 6511h	2700 0000h
	ļ			<u> </u>	4.2605393 E08




INTDPU Convert Unsigned Integer to Double-Precision Floating-Point Value

Syntax INTDPU (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.L1, .L2
dst	dp	

Description

The unsigned integer value in src2 is converted to a double-precision value and placed

in *dst*.

You cannot set configuration bits with this instruction.

Execution

if (cond) $dp(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	src2				
Written				dst_l	dst_h
Unit in use	.L				

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type INTDP

Delay Slots 4

Functional Unit Latency 1

See Also DPINT, INTDP, INTSP, INTSPU

Example INTDPU .L1 A4,A1:A0

	Before instruction	n		4 cycles after ins	truction
A4	FFFF FFDEh	4,294,967,262	A4	FFFF FFDEh	
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	41EF FFFFh	FBC0 0000h
			•	,	4.2949673 E09



INTSP Convert Signed Integer to Single-Precision Floating-Point Value

Syntax INTSP (.unit) src2, dst

unit = .L1 or .L2

Opcode

31 2	9	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		z	dst		src2		0	0	0	0	0	Х	1	0	0	1	0	1	0	1	1	0	s	р
3		1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xsint	.L1, .L2
dst	dp	

Description

The signed integer value in src2 is converted to a single-precision value and placed in

dst

The only configuration bit that can be set is the INEX bit and only if the mantissa is

rounded.

Execution

if (cond)

else nop

 $sp(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2			
Written				dst
Unit in use	.L			

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also INTDP, INTDPU, INTSPU

Example INTSP .L1 A1,A2

	Before instruction			4 cycles after instru	ction
A1	1965 1127h	426,053,927	A1	1965 1127h	
A2	xxxx xxxxh		A2	4DCB 2889h	4.2605393 E08




INTSPU Convert Unsigned Integer to Single-Precision Floating-Point Value

Syntax INTSPU (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.L1, .L2
dst	dp	

Description

The unsigned integer value in src2 is converted to a single-precision value and placed in

dst.

The only configuration bit that can be set is the INEX bit and only if the mantissa is rounded.

Execution

if (cond) $sp(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2			
Written				dst
Unit in use	.L			

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also INTDP, INTDPU, INTSP

Example INTSPU .L1X B1,A2

	Before instruction			4 cycles after instruc	ction
B1	FFFF FFDEh	4,294,967,262	B1	FFFF FFDEh	
A2	xxxx xxxxh		A2	4F80 0000h	4.2949673 E09



LDB(U)

Load Byte From Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset

LDB (.unit) *+baseR[offsetR], dst

10

LDBU (.unit) *+baseR[offsetR], dst

unit = .D1 or .D2

Unsigned Constant Offset

LDB (.unit) *+baseR[ucst5], dst

or

LDBU (.unit) *+baseR[ucst5], dst

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31 29	28	27	23	22	18	17	13	12	9	8	7	6	4	3	2	1	0
creg	Z	a	lst	baseR		offsetR/ucst5		mode		0	У	ор	,	0	1	s	p
3	1		5	5		5		4			1	3				1	1

Description

Loads a byte from memory to a general-purpose register (*dst*). Table 3-23 summarizes the data types supported by loads. Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*). If an offset is not given, the assembler assigns an offset of zero.

Table 3-23. Data Types Supported by LDB(U) Instruction

Mnemonic		op Field		Load Data Type	Slze	Left Shift of Offset
LDB	0	1	0	Load byte	8	0 bits
LDBU	0	0	1	Load byte unsigned	8	0 bits

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 0 bits. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed in memory.

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).



For **LDB(U)**, the values are loaded into the 8 LSBs of *dst*. For **LDB**, the upper 24 bits of *dst* values are sign-extended; for **LDBU**, the upper 24 bits of *dst* are zero-filled. The *s* bit determines which file *dst* will be loaded into: s = 0 indicates *dst* will be loaded in the A register file and s = 1 indicates *dst* will be loaded in the B register file.

Increments and decrements default to 1 and offsets default to 0 when no bracketed register or constant is specified. Loads that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst5* offset is left-shifted by 0. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Execution

if (cond) else nop

 $mem \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	
Read	baseR, offsetR					
Written	baseR					
Unit in use	.D					

Instruction Type Load

Delay Slots 4 for loaded value

0 for address modification from pre/post increment/decrement

For more information on delay slots for a load, see Chapter 4.

See Also LDH, LDW

Examples Example 1

LDB .D1 *-A5[4],A7

	Before instruction		1 cycle after instruction		5 cycles after instruction
A5	0000 0204h	A5	0000 0204h	A5	0000 0204h
A7	1951 1970h	A7	1951 1970h	A7	FFFF FFE1h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 200h	E1h	mem 200h	E1h	mem 200h	E1h



Example 2

LDB .D1 *++A4[5],A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 0400h	A4	0000 4005h	A4	0000 4005h
A8	0000 0000h	A8	0000 0000h	A8	0000 0067h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 4000h	0112 2334h	mem 4000h	0112 2334h	mem 4000h	0112 2334h
mem 4004h	4556 6778h	mem 4004h	4556 6778h	mem 4004h	4556 6778h

Example 3

LDB .D1 *A4++[5],A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 0400h	A4	0000 4005h	A4	0000 4005h
A8	0000 0000h	A8	0000 0000h	A8	0000 0034h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 4000h	0112 2334h	mem 4000h	0112 2334h	mem 4000h	0112 2334h
mem 4004h	4556 6778h	mem 4004h	4556 6778h	mem 4004h	4556 6778h

Example 4

LDB .D1 *++A4[A12],A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 0400h	A4	0000 4006h	A4	0000 4006h
A8	0000 0000h	A8	0000 0000h	A8	0000 0056h
A12	0000 0006h	A12	0000 0006h	A12	0000 0006h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 4000h	0112 2334h	mem 4000h	0112 2334h	mem 4000h	0112 2334h
mem 4004h	4556 6778h	mem 4004h	4556 6778h	mem 4004h	4556 6778h



LDB(U)

Load Byte From Memory With a 15-Bit Unsigned Constant Offset

Syntax

LDB (.unit) *+B14/B15[ucst15], dst

or

LDBU (.unit) *+B14/B15[ucst15], dst

unit = .D2

Opcode

31 2	9 28		23	22	8	7	6	4	3	2	1	0
creg	Z	,	dst	ucst15		У	ор		1	1	s	p
3	1		5	15		1	3				1	1

Description

Loads a byte from memory to a general-purpose register (dst). Table 3-24 summarizes the data types supported by loads. The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction operates only on the .D2 unit.

The offset, *ucst15*, is scaled by a left shift of 0 bits. After scaling, *ucst15* is added to *baseR*. Subtraction is not supported. The result of the calculation is the address sent to memory. The addressing arithmetic is always performed in linear mode.

For **LDB(U)**, the values are loaded into the 8 LSBs of *dst*. For **LDB**, the upper 24 bits of *dst* values are sign-extended; for **LDBU**, the upper 24 bits of *dst* are zero-filled. The *s* bit determines which file *dst* will be loaded into: s = 0 indicates *dst* will be loaded in the A register file and s = 1 indicates *dst* will be loaded in the B register file.

Square brackets, [], indicate that the *ucst*15offset is left-shifted by 0. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Table 3-24. Data Types Supported by LDB(U) Instruction (15-Bit Offset)

Mnemonic		op Field		Load Data Type	Size	Left Shift of Offset
LDB	0	1	0	Load byte	8	0 bits
LDBU	0	0	1	Load byte unsigned	8	0 bits

Execution

if (cond) $mem \rightarrow dst$ else nop

NOTE: This instruction executes only on the B side (.D2).



www.ti.com

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	B14/B15				
Written					dst
Unit in use	.D2				

Instruction Type Load

Delay Slots 4

See Also LDH, LDW

Example LDB .D2 *+B14[36],B1

	Before instruction		1 cycle after instruction
B1	xxxx xxxxh	B1	xxxx xxxxh
B14	0000 0100h	B14	0000 0100h
mem 124-127h	4E7A FF12h	mem 124-127h	4E7A FF12h
mem 124h	12h	mem 124h	12h
			5 cycles after instruction
		B1	0000 0012h
		B14	0000 0100h
		mem 124-127h	4E7A FF12h
		mem 124h	12h



LDDW

Load Doubleword From Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset
LDDW (.unit) *+baseR[offsetR], dst

Unsigned Constant Offset LDDW (.unit) *+baseR[ucst5], dst

unit = .D1 or .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4DW	Figure C-9
	DindDW	Figure C-11
	DincDW	Figure C-13
	DdecDW	Figure C-15
	Dpp	Figure C-21

Opcode

3	1 29	28	27 23	5 22 18	3 1/ 1	13 ′	12	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst	baseR	offsetR/ucst5		mode		1	У	1	1	0	0	1	s	p
	3	1	5	5	5		4			1						1	1

Description

Loads a 64-bit quantity from memory into a register pair $dst_o:dst_e$. Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (baseR) and an optional offset that is either a register (offsetR) or a 5-bit unsigned constant (ucst5).

Both offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and the register file used: y = 0 selects the .D1 unit and the baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file. The s bit determines the register file into which the dst is loaded: s = 0 indicates that dst is in the A register file, and s = 1 indicates that dst is in the B register file. The dst field must always be an even value because the **LDDW** instruction loads register pairs. Therefore, bit 23 is always zero.

The offsetR/ucst5 is scaled by a left-shift of 3 to correctly represent doublewords. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the shifted value of baseR before the addition or subtraction is the address to be accessed in memory.

Increments and decrements default to 1 and offsets default to 0 when no bracketed register, bracketed constant, or constant enclosed in parentheses is specified. Square brackets, [], indicate that *ucst5* is left shifted by 3. Parentheses, (), indicate that *ucst5* is not left shifted. In other words, parentheses indicate a byte offset rather than a doubleword offset. You must type either brackets or parenthesis around the specified offset if you use the optional offset parameter.



The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The destination register pair must consist of a consecutive even and odd register pair from the same register file. The instruction can be used to load a double-precision floating-point value (64 bits), a pair of single-precision floating-point words (32 bits), or a pair of 32-bit integers. The 32 least-significant bits are loaded into the even-numbered register and the 32 most-significant bits (containing the sign bit and exponent) are loaded into the next register (which is always odd-numbered register). The register pair syntax places the odd register first, followed by a colon, then the even register (that is, A1:A0, B1:B0, A3:A2, B3:B2, etc.).

All 64 bits of the double-precision floating point value are stored in big- or little-endian byte order, depending on the mode selected. When the **LDDW** instruction is used to load two 32-bit single-precision floating-point values or two 32-bit integer values, the order is dependent on the endian mode used. In little-endian mode, the first 32-bit word in memory is loaded into the even register. In big-endian mode, the first 32-bit word in memory is loaded into the odd register. Regardless of the endian mode, the doubleword address must be on a doubleword boundary (the three LSBs are zero).

Execution

if (cond) else nop

 $mem \rightarrow dst$

Pipeline

Pipeline Stage	E 1	E2	E3	E4	E5		
Read	baseR, offsetR						
Written	baseR	baseR					
Unit in use	.D						

Instruction Type Load

Delay Slots

Functional Unit Latency 1

Example 1

LDDW .D2 *+B10[1],A1:A0

	Before instruct	tion			5 cycles after instruction			
A1:A0	xxxx xxxxh	xxxx xxxxh		A1:A0	4021 3333h	3333 3333h		
B10	0000 0010h		16	B10	0000 0010h			
mem 18h	3333 3333h	4021 3333h	8.6	mem 18h	3333 3333h	4021 3333h		
					Little-endian mo	ode		



Example 2

LDDW .D1 *++A10[1],A1:A0

	Before instruct	tion			1 cycle after in	struction	
A1:A0	xxxx xxxxh	xxxx xxxxh		A1:A0	xxxx xxxxh	xxxx xxxxh	
A10	0000 0010h		16	A10	0000 0018h		24
mem 18h	4021 3333h	3333 3333h	8.6	mem 18h	4021 3333h	3333 3333h	
_					5 cycles after i		
				A1:A0	4021 3333h	3333 3333h	
				A10	0000 0018h		24
				mem 18h	4021 3333h	3333 3333h	
					Big-endian mod	е	

Example 3

LDDW .D1 *A4++[5],A9:A8

	Before instruction	on		1 cycle after ins	truction		
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	xxxx xxxxh	xxxx xxxxh		
A4	0000 40B0h		A4	0000 40B0h			
mem 40B0h	0112 2334h	4556 6778h	mem 40B0h	0112 2334h	4556 6778h		
				5 cycles after instruction			
			A9:A8	4556 6778h	0112 2334h		
			A4	0000 40B0h			
			mem 40B0h	0112 2334h	4556 6778h		
				Little-endian mod	e		



Example 4

LDDW .D1 *++A4[A12],A9:A8

	Before instructi	on			1 cycle after instruction				
A9:A8	xxxx xxxxh	xxxx xxxxh		A9:A8	xxxx xxxxh	xxxx xxxxh			
A4	0000 40B0h			A4	0000 40E0h				
A12	0000 0006h			A12	0000 0006h				
mem 40E0h	0112 2334h 4556 6778h		8	mem 40E0h	0112 2334h	4556 6778h			
					5 cycles after in	struction			
				A9:A8	4556 6778h	0112 2334h			
				A4	0000 40E0h				
				A12	0000 0006h				
				mem 40E0h	0112 2334h	4556 6778h			
					Little-endian mod	le			

Example 5

LDDW .D1 *++A4(16),A9:A8

	Before instruction	on		1 cycle after instruction					
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	xxxx xxxxh	xxxx xxxxh				
A4	0000 40B0h		A4	0000 40C0h					
mem 40C0h	4556 6778h	899A ABBCh	mem 40C0h	4556 6778h	899A ABBCh				
				5 cycles after ins	struction				
			A9:A8	899A ABBCh	4556 6778h				
			A4	0000 40C0h					
			mem 40C0h	4556 6778h	899A ABBCh				
				Little-endian mode	9				



LDH(U)

Load Halfword From Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset

LDH (.unit) *+baseR[offsetR], dst

or

LDHU (.unit) *+baseR[offsetR], dst

unit = .D1 or .D2

Unsigned Constant Offset

LDH (.unit) *+baseR[ucst5], dst

OI

LDHU (.unit) *+baseR[ucst5], dst

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

3	1 29	28	27	23		8 1	17 13	12		9	8	7	6	4	3	2	1	0
	creg	Z	dst		baseR		offsetR/ucst5		mode		0	У	ор		0	1	s	р
	3	1	5		5		5		4			1	3				1	1

Description

Loads a halfword from memory to a general-purpose register (*dst*). Table 3-25 summarizes the data types supported by halfword loads. Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*). If an offset is not given, the assembler assigns an offset of zero.

Table 3-25. Data Types Supported by LDH(U) Instruction

Mnemonic	op Field			Load Data Type	Size	Left Shift of Offset			
LDH	1	0	0	Load halfword	16	1 bit			
LDHU	0	0	0	Load halfword unsigned	16	1 bit			

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 1 bit. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed in memory.





The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

For **LDH(U)**, the values are loaded into the 16 LSBs of *dst*. For **LDH**, the upper 16 bits of *dst* are sign-extended; for **LDHU**, the upper 16 bits of *dst* are zero-filled. The *s* bit determines which file *dst* will be loaded into: s = 0 indicates *dst* will be loaded in the A register file and s = 1 indicates *dst* will be loaded in the B register file.

Increments and decrements default to 1 and offsets default to 0 when no bracketed register or constant is specified. Loads that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst5* offset is left-shifted by 1. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Halfword addresses must be aligned on halfword (LSB is 0) boundaries.

Execution

if (cond) else nop

 $mem \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	baseR, offsetR				
Written	baseR				dst
Unit in use	.D				

Instruction Type Load

Delay Slots 4 for loaded value

0 for address modification from pre/post increment/decrement For more information on delay slots for a load, see Chapter 4.

See Also LDB, LDW

Example LDH .D1 *++A4[A1],A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A1	0000 0002h	A1	0000 0002h	A1	0000 0002h
A4	0000 0020h	A4	0000 0024h	A4	0000 0024h
A8	1103 51FFh	A8	1103 51FFh	A8	FFFF A21Fh
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 24h	A21Fh	mem 24h	A21Fh	mem 24h	A21Fh



LDH(U)

Load Halfword From Memory With a 15-Bit Unsigned Constant Offset

Syntax

LDH (.unit) *+B14/B15[ucst15], dst

or

LDHU (.unit) *+B14/B15[ucst15], dst

unit = .D2

Opcode

31 2	9 2	8 27	7 23	22	8	7	6	4	3	2	1	0
creg	Z	<u> </u>	dst	ucst15		у	ор		1	1	s	р
3	1		5	15		1	3				1	1

Description

Loads a halfword from memory to a general-purpose register (dst). Table 3-26 summarizes the data types supported by loads. The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction operates only on the .D2 unit.

The offset, *ucst15*, is scaled by a left shift of 1 bit. After scaling, *ucst15* is added to *baseR*. Subtraction is not supported. The result of the calculation is the address sent to memory. The addressing arithmetic is always performed in linear mode.

For **LDH(U)**, the values are loaded into the 16 LSBs of dst. For **LDH**, the upper 16 bits of dst are sign-extended; for **LDHU**, the upper 16 bits of dst are zero-filled. The s bit determines which file dst will be loaded into: s = 0 indicates dst will be loaded in the A register file and s = 1 indicates dst will be loaded in the B register file.

Square brackets, [], indicate that the *ucst*15offset is left-shifted by 1. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Halfword addresses must be aligned on halfword (LSB is 0) boundaries.

Table 3-26. Data Types Supported by LDH(U) Instruction (15-Bit Offset)

Mnemonic		op Field		Load Data Type	Slze	Left Shift of Offset
LDH	1	0	0	Load halfword	16	1 bit
LDHU	0	0	0	Load halfword unsigned	16	1 bit

Execution

if (cond) $mem \rightarrow dst$ else nop

NOTE: This instruction executes only on the B side (.D2).



www.ti.com

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	B14/B15				
Written					dst
Unit in use	.D2				

Instruction Type Load

Delay Slots 4

See Also LDB, LDW



LDNDW

Load Nonaligned Doubleword From Memory With Constant or Register Offset

Syntax

Register Offset
LDNDW (.unit) *+baseR[offsetR], dst
unit = .D1 or .D2

Unsigned Constant Offset LDNDW (.unit) *+baseR[ucst5], dst

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4DW	Figure C-9
	DindDW	Figure C-11
	DincDW	Figure C-13
	DdecDW	Figure C-15

Opcode

31 2	9 28	27	24	23	22	18	17 13	5 '	12	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	sc	baseR		offsetR/ucst5		mode		1	У	0	1	0	0	1	S	р
3	1		4	1	5		5		4			1						1	1

Opcode map field used	For operand type	Unit
baseR	uint	.D1, .D2
offsetR	uint	
dst	ullong	
baseR	uint	.D1, .D2
offsetR	ucst5	
dst	ullong	

Description

Loads a 64-bit quantity from memory into a register pair, *dst_o:dst_e*. Table 3-11 describes the addressing generator options. The **LDNDW** instruction may read a 64-bit value from any byte boundary. Thus alignment to a 64-bit boundary is not required. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

Both offsetR and baseR must be in the same register file, and on the same side, as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

The **LDNDW** instruction supports both scaled offsets and nonscaled offsets. The *sc* field is used to indicate whether the *offsetR/ucst5* is scaled or not. If *sc* is 1 (scaled), the *offsetR/ucst5* is shifted left 3 bits before adding or subtracting from the *baseR*. If *sc* is 0 (nonscaled), the *offsetR/ucst5* is not shifted before adding or subtracting from the *baseR*. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of *baseR* before the addition or subtraction is the address to be accessed from memory.



The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The dst field of the instruction selects a register pair, a consecutive even-numbered and odd-numbered register pair from the same register file. The instruction can be used to load a pair of 32-bit integers. The 32 least-significant bits are loaded into the even-numbered register and the 32 most-significant bits are loaded into the next register (that is always an odd-numbered register).

The dst can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file dst will be loaded into: s = 0 indicates dst will be in the A register file and s = 1 indicates dst will be loaded in the B register file.

NOTE: No other memory access may be issued in parallel with a nonaligned memory access. The other .D unit can be used in parallel as long as it is not performing a memory access.

Assembler Notes

When no bracketed register or constant is specified, the assembler defaults increments and decrements to 1 and offsets to 0. Loads that do no modification to the baseR can use the assembler syntax *R. Square brackets, [], indicate that the ucst5 offset is left-shifted by 3 for doubleword loads.

Parentheses, (), can be used to tell the assembler that the offset is a non-scaled offset.

For example, LDNDW (.unit) *+baseR (14), dst represents an offset of 14 bytes, and the assembler writes out the instruction with offsetC = 14 and sc = 0.

LDNDW (.unit) *+baseR [16], dst represents an offset of 16 doublewords, or 128 bytes, and the assembler writes out the instruction with offsetC = 16 and sc = 1.

Either brackets or parentheses must be typed around the specified offset if the optional offset parameter is used.

Execution

if (cond) else nop $mem \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	baseR, offsetR				
Written	baseR				dst
Unit in use	.D				

Instruction Type

Load

Delay Slots

4 for loaded value

0 for address modification from pre/post increment/decrement

See Also

LDNW, STNDW, STNW



Examples

Example 1

LDNDW .D1 *A0++, A3:A2

	Before instruction			1 cycle after instr	ruction
A0	0000 1001h		A0	0000 1009h	
A3:A2	xxxx xxxxh	xxxx xxxxh	A3:A2	xxxx xxxxh	xxxx xxxxh
mem 1000h	12B6 C5D4h		mem 1000h	12B6 C5D4h	
mem 1004h	1C4F 29A8h		mem 1004h	1C4F 29A8h	
mem 1008h	0569 345Eh		mem 1008h	0569 345Eh	
				5 cycles after ins	truction
			A0	0000 1009h	
			A3:A2	5E1C 4F29h	A812 B6C5h
				Little-endian mode	,
			mem 1000h	12B6 C5D4h	
			mem 1004h	1C4F 29A8h	
			mem 1008h	0569 345Eh	

Byte Memory Address	100C	100B	100A	1009	1008	1007	1006	1005	1004	1003	1002	1001	1000
Data Value	11	05	69	34	5E	1C	4F	29	A8	12	B6	C5	D4



Example 2

LDNDW .D1 *A0++, A3:A2

	Before instruction	1		1 cycle after inst	ruction
A0	0000 1003h		Α0	0000 100Bh	
A3:A2	xxxx xxxxh	xxxx xxxxh	A3:A2	xxxx xxxxh	xxxx xxxxh
mem 1000h	12B6 C5D4h		mem 1000h	12B6 C5D4h	
mem 1004h	1C4F 29A8h		mem 1004h	1C4F 29A8h	
mem 1008h	0569 345Eh		mem 1008h	0569 345Eh	
				5 cycles after ins	struction
			A0	0000 100Bh	
			A3:A2	6934 5E1Ch	4F29 A812h
				Little-endian mode	е
			mem 1000h	12B6 C5D4h	
			mem 1004h	1C4F 29A8h	
			mem 1008h	0569 345Eh	

Byte Memory Address	100C	100B	100A	1009	1008	1007	1006	1005	1004	1003	1002	1001	1000
Data Value	11	05	69	34	5E	1C	4F	29	A8	12	B6	C5	D4



LDNW

Load Nonaligned Word From Memory With Constant or Register Offset

Syntax

Register Offset LDNW (.unit) *+baseR[offsetR], dst unit = .D1 or .D2 Unsigned Constant Offset LDNW (.unit) *+baseR[ucst5], dst

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31	29	28	27	23	22	18	17 13	12		9	8	7	6	5	4	3	2	1	0
creg	1	Z	dst		baseR		offsetR/ucst5		mode		1	У	0	1	1	0	1	s	p
3		1	5		5		5		4			1						1	1

Opcode map field used	For operand type	Unit
baseR	uint	.D1, .D2
offset	uint	
dst	int	
baseR	uint	.D1, .D2
offset	ucst5	
dst	int	

Description

Loads a 32-bit quantity from memory into a 32-bit register, *dst.* Table 3-11 describes the addressing generator options. The **LDNW** instruction may read a 32-bit value from any byte boundary. Thus alignment to a 32-bit boundary is not required. The memory address is formed from a base address register (*baseR*), and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*). If an offset is not given, the assembler assigns an offset of zero.

Both offsetR and baseR must be in the same register file, and on the same side, as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

The offsetR/ucst5 is scaled by a left shift of 2 bits. After scaling, offsetR/ucst5 is added to, or subtracted from, baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed from memory.



The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The dst can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file dst will be loaded into: s = 0 indicates dst will be in the A register file and s = 1 indicates dst will be loaded in the B register file.

NOTE: No other memory access may be issued in parallel with a nonaligned memory access. The other .D unit can be used in parallel, as long as it is not doing a memory access.

Assembler Notes

When no bracketed register or constant is specified, the assembler defaults increments and decrements to 1 and offsets to 0. Loads that do no modification to the baseR can use the assembler syntax *R. Square brackets, [], indicate that the ucst5 offset is left-shifted by 2 for word loads.

Parentheses, (), can be used to tell the assembler that the offset is a nonscaled, constant offset. The assembler right shifts the constant by 2 bits for word loads before using it for the ucst5 field. After scaling by the LDNW instruction, this results in the same constant offset as the assembler source if the least-significant two bits are zeros.

For example, LDNW (.unit) *+baseR (12), dst represents an offset of 12 bytes (3 words), and the assembler writes out the instruction with ucst5 = 3.

LDNW (.unit) *+baseR [12], dst represents an offset of 12 words, or 48 bytes, and the assembler writes out the instruction with ucst5 = 12.

Either brackets or parentheses must be typed around the specified offset if the optional offset parameter is used.

Execution

if (cond) else nop $mem \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	baseR, offsetR				
Written	baseR				dst
Unit in use	.D				

Instruction Type

Delay Slots 4 for loaded value

0 for address modification from pre/post increment/decrement

See Also LDNDW, STNDW, STNW

Load



Examples

Example 1

LDNW .D1 *A0++, A2

	Before instruction		1 cycle after instruction		5 cycles after instruction
A0	0000 1001h	A0	0000 1005h	A0	0000 1005h
A2	xxxx xxxxh	A2	xxxx xxxxh	A2	A812 B6C5h
					Little-endian mode
mem 1000h	12B6 C5D4h	mem 1000h	12B6 C5D4h	mem 1000h	12B6 C5D4h
mem 1004h	1C4F 29A8h	mem 1004h	1C4F 29A8h	mem 1004h	1C4F 29A8h

Byte Memory Address	1007	1006	1005	1004	1003	1002	1001	1000
Data Value	1C	4F	29	A8	12	B6	C5	D4

Example 2

LDNW .D1 *A0++, A2

	Before instruction		1 cycle after instruction		5 cycles after instruction
A0	0000 1003h	A0	0000 1007h	A0	0000 1007h
A2	xxxx xxxxh	A2	xxxx xxxxh	A2	4F29 A812h
				•	Little-endian mode
mem 1000h	12B6 C5D4h	mem 1000h	12B6 C5D4h	mem 1000h	12B6 C5D4h
mem 1004h	1C4F 29A8h	mem 1004h	1C4F 29A8h	mem 1004h	1C4F 29A8h

Byte Memory Address	1007	1006	1005	1004	1003	1002	1001	1000
Data Value	1C	4F	29	A8	12	B6	C5	D4



LDW

Load Word From Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset LDW (.unit) *+baseR[offsetR], dst unit = .D1 or .D2

Unsigned Constant Offset LDW (.unit) *+baseR[ucst5], dst

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

3		28	27	23	')') 1	18 1	17 13	12		9	8	7	6	5	4	3	2	1	0
	creg	z		dst	baseR		offsetR/ucst5		mode		0	У	1	1	0	0	1	s	p
	3	1		5	5		5		4			1						1	1

Description

Loads a word from memory to a general-purpose register (*dst*). Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*). If an offset is not given, the assembler assigns an offset of zero.

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 2 bits. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed in memory.

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

For **LDW**, the entire 32 bits fills dst. dst can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file dst will be loaded into: s = 0 indicates dst will be loaded in the A register file and s = 1 indicates dst will be loaded in the B register file.

Increments and decrements default to 1 and offsets default to 0 when no bracketed register or constant is specified. Loads that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst5* offset is left-shifted by 2. Parentheses, (), can be used to set a nonscaled, constant offset. For example, **LDW** (.unit) *+baseR (12), dst represents an offset of 12 bytes; whereas, **LDW** (.unit) *+baseR [12], dst represents an offset of 12 words, or 48 bytes. You must type either



brackets or parentheses around the specified offset, if you use the optional offset parameter.

Word addresses must be aligned on word (two LSBs are 0) boundaries.

Execution

if (cond) else nop

 $mem \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	baseR, offsetR				
Written	baseR				dst
Unit in use	.D				

Instruction Type Load

Delay Slots 4 for loaded value

0 for address modification from pre/post increment/decrement For more information on delay slots for a load, see Chapter 4.

See Also LDB, LDH

Example 1

LDW .D1 *A10,B1

	Before instruction		1 cycle after instruction		5 cycles after instruction
B1	0000 0000h	B1	0000 0000h	B1	21F3 1996h
A10	0000 0100h	A10	0000 0100h	A10	0000 0100h
mem 100h	21F3 1996h	mem 100h	21F3 1996h	mem 100h	21F3 1996h

Example 2

LDW .D1 *A4++[1],A6

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 0100h	A4	0000 0104h	A4	0000 0104h
A6	1234 4321h	A6	1234 4321h	A6	0798 F25Ah
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 100h	0798 F25Ah	mem 100h	0798 F25Ah	mem 100h	0798 F25Ah
mem 104h	1970 19F3h	mem 104h	1970 19F3h	mem 104h	1970 19F3h



Example 3

LDW .D1 *++A4[1],A6

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 0100h	A4	0000 0104h	A4	0000 0104h
A6	1234 5678h	A6	1234 5678h	A6	0217 6991h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 104h	0217 6991h	mem 104h	0217 6991h	mem 104h	0217 6991h

Example 4

LDW .D1 *++A4[A12],A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 40B0h	A4	0000 40C8h	A4	0000 40C8h
A8	0000 0000h	A8	0000 0000h	A8	DCCB BAA8h
A12	0000 0006h	A12	0000 0006h	A12	0000 0006h
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 40C8h	DCCB BAA8h	mem 40C8h	DCCB BAA8h	mem 40C8h	DCCB BAA8h

Example 5

LDW .D1 *++A4(8),A8

	Before instruction		1 cycle after instruction		5 cycles after instruction
A4	0000 40B0h	A4	0000 40B8h	A4	0000 40B8h
A8	0000 0000h	A8	0000 0000h	A8	9AAB BCCDh
AMR	0000 0000h	AMR	0000 0000h	AMR	0000 0000h
mem 40B8h	9AAB BCCDh	mem 40B8h	9AAB BCCDh	mem 40B8h	9AAB BCCDh



LDW

Load Word From Memory With a 15-Bit Unsigned Constant Offset

Syntax

LDW (.unit) *+B14/B15[ucst15], dst

unit = .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Dstk	Figure C-16
	Dpp	Figure C-21

Opcode

31 29	28	27 23	22 8	7	6	5	4	3	2	1	0
creg	Z	dst	ucst15	У	1	1	0	1	1	s	р
3	1	5	15	1						1	1

Description

Load a word from memory to a general-purpose register (dst). The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction operates only on the .D2 unit.

The offset, *ucst15*, is scaled by a left shift of 2 bits. After scaling, *ucst15* is added to *baseR*. Subtraction is not supported. The result of the calculation is the address sent to memory. The addressing arithmetic is always performed in linear mode.

For **LDW**, the entire 32 bits fills dst. dst can be in either register file. The s bit determines which file dst will be loaded into: s = 0 indicates dst will be loaded in the A register file and s = 1 indicates dst will be loaded in the B register file.

Square brackets, [], indicate that the ucst15 offset is left-shifted by 2. Parentheses, (), can be used to set a nonscaled, constant offset. For example,

LDW (.unit) *+B14/B15(60), dst represents an offset of 60 bytes; whereas,

LDW (.unit) *+B14/B15[60], *dst* represents an offset of 60 words, or 240 bytes. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Word addresses must be aligned on word (two LSBs are 0) boundaries.

Execution

if (cond) $mem \rightarrow dst$ else nop

NOTE: This instruction executes only on the B side (.D2).

302 Instruction Set SPRUFE8B-July 2010



www.ti.com

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	B14/B15				
Written					dst
Unit in use	.D2				

Instruction Type Load

Delay Slots 4

See Also LDB, LDH



LMBD Leftmost Bit Detection

Syntax LMBD (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 2	 28	27	23	22	18	17 13	3	12	11	5	4	3	•	2	1	0
creg	z	dst	•	src2		src1/cst5		Х	ор		1	1		0	s	p
3	1	5		5		5		1	7						1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.L1, .L2	110 1011
src1 src2 dst	cst5 xuint uint	.L1, .L2	110 1010

Description

The LSB of the *src1* operand determines whether to search for a leftmost 1 or 0 in *src2*. The number of bits to the left of the first 1 or 0 when searching for a 1 or 0, respectively, is placed in *dst*.

The following diagram illustrates the operation of **LMBD** for several cases.

When searching for 0 in src2, LMBD returns 0:

_	-											20											-	-	-	-	-	-	-	_	-	-	
()	1	х	х	х	х	х	х	Х	х	х	х	Х	х	х	х	х	х	х	х	х	Х	Х	х	х	х	х	х	Х	х	Х	Х	

When searching for 1 in src2, LMBD returns 4:

		29																				-	-	-	-	-	-	-	_	-	-
0	0	0	0	1	Х	х	Х	х	х	х	Х	х	х	х	х	х	Х	Х	Х	Х	х	х	х	Х	Х	х	х	Х	Х	Х	Х

When searching for 0 in src2, LMBD returns 32:

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

Example LMBD .L1 A1,A2,A3

	Before instruction	1 cycle after instruction
A1	0000 0001h	A1 0000 0001h
A2	009E 3A81h	A2 009E 3A81h
А3	xxxx xxxxh	A3 0000 0008h



MAX2 Maximum, Signed, Packed 16-Bit

Syntax MAX2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	0	0	0	0	1	0	1	1	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.L1, .L2
src1 src2	xs2	
dst	s2	


Opcode .S unit

	31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Ī	creg	Z		dst	src2	src1		Х	1	1	1	1	0	1	1	1	0	0	s	p
	3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	s2	

Description

Performs a maximum operation on signed, packed 16-bit values. For each pair of signed 16-bit values in *src1* and *src2*, **MAX2** places the larger value in the corresponding position in *dst*.





Execution

```
if (cond)  \{ \\  & \text{if (lsb16}(\textit{src1}) >= \text{lsb16}(\textit{src2})), \, \text{lsb16}(\textit{src1}) \rightarrow \text{lsb16}(\textit{dst}) \\  & \text{else lsb16}(\textit{src2}) \rightarrow \text{lsb16}(\textit{dst}); \\  & \text{if (msb16}(\textit{src1}) >= \text{msb16}(\textit{src2})), \, \text{msb16}(\textit{src1}) \rightarrow \text{msb16}(\textit{dst}) \\  & \text{else msb16}(\textit{src2}) \rightarrow \text{msb16}(\textit{dst}) \\  & \text{} \} \\ \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also MAXU4, MIN2, MINU4

Example 1

MAX2 .L1 A2, A8, A9

	Before instruction		1 cycle after instruction	
A2	3789 F23Ah	A2	3789 F23Ah	14217 -3526
A8	04B8 4975h	A8	04B8 4975h	1208 18805
A9	xxxx xxxxh	A9	3789 4975h	14217 18805

Example 2

MAX2 .L2X A2, B8, B12

	Before instruction		1 cycle after instruction	
A2	0124 2451h	A2	0124 2451h	292 9297
B8	01A6 A051h	B8	01A6 A051h	422 -24495
B12	xxxx xxxxh	B12	01A6 2451h	422 9297



Example 3

MAX2 .S1 A2, A8, A9

	Before instruction		1 cycle after instruction	
A2	3789 F23Ah	A2	3789 F23Ah	14217 -3526
A8	04B8 4975h	A8	04B8 4975h	1208 18805
A9	xxxx xxxxh	A9	3789 4975h	14217 18805

Example 4

MAX2 .S2X A2, B8, B12

	Before instruction		1 cycle after instruction	
A2	0124 2451h	A2	0124 2451h	292 9297
B8	01A6 A051h	В8	01A6 A051h	422 -24495
B12	xxxx xxxxh	B12	01A6 2451h	422 9297



MAXU4 Maximum, Unsigned, Packed 8-Bit

Syntax

MAXU4 (.unit) src1, src2, dst

unit = .L1 or .L2


Opcode

31 2	9 28	27	23	22 18	3 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	d	lst	src2		src1		Χ	1	0	0	0	0	1	1	1	1	0	s	p
3	1	Ę	5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.L1, .L2
src2	xu4	
dst	u4	

Description

Performs a maximum operation on unsigned, packed 8-bit values. For each pair of unsigned 8-bit values in *src1* and *src2*, **MAXU4** places the larger value in the corresponding position in *dst*.



Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also MAX2, MIN2, MINU4

Example 1

MAXU4 .L1 A2, A8, A9

	Before instruction		1 cycle after instruct	ion
A2	37 89 F2 3Ah	A2	37 89 F2 3Ah	55 137 242 58 unsigned
A8	04 B8 49 75h	A8	04 B8 49 75h	4 184 73 117 unsigned
A9	xxxx xxxxh	A9	37 B8 F2 75h	55 184 242 117 unsigned

Example 2

MAXU4 .L2X A2, B8, B12

	Before instruction		1 cycle after instruct	ion
A2	01 24 24 B9h	A2	01 24 24 B9h	1 36 36 185 unsigned
B8	01 A6 A0 51h	В8	01 A6 A0 51h	1 166 160 81 unsigned
B12	xxxx xxxxh	B12	01 A6 A0 B9h	1 166 160 185 unsigned



MIN2 Minimum, Signed, Packed 16-Bit

Syntax MIN2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src	1	Х	1	0	0	0	0	0	1	1	1	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.L1, .L2
src1 src2	xs2	
dst	s2	


Opcode .S unit

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	(dst	src2	src1		Х	1	1	1	1	0	0	1	1	0	0	s	p
3	1		5	5	5		1										-	1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src1 src2	xs2	
dst	s2	

Description

Performs a minimum operation on signed, packed 16-bit values. For each pair of signed 16-bit values in *src1* and *src2*, **MIN2** instruction places the smaller value in the corresponding position in *dst*.





Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also MAX2, MAXU4, MINU4

Example 1

MIN2 .L1 A2, A8, A9

	Before instruction	1 cycle after instruction
A2	3789 F23Ah	A2 3789 F23Ah 14217 -3526
A8	04B8 4975h	A8 04B8 4975h 1208 18805
A9	xxxx xxxxh	A9 04B8 F23Ah 1208 -3526

Example 2

MIN2 .L2X A2, B8, B12

	Before instruction		1 cycle after instr	uction
A2	0124 8003h	A2	0124 8003h	292 -32765
B8	0A37 8001h	B8	0A37 8001h	2615 -32767
B12	xxxx xxxxh	B12	0124 8001h	292 -32767

312 Instruction Set SPRUFE8B-July 2010





Example 3

MIN2 .S1 A2, A8, A9

	Before instruction		1 cycle after instr	uction
A2	3789 F23Ah	A2	3789 F23Ah	14217 -3526
A8	04B8 4975h	A8	04B8 4975h	1208 18805
A9	xxxx xxxxh	A9	04B8 F23Ah	1208 -3526

Example 4

MIN2 .S2X A2, B8, B12

	Before instruction		1 cycle after instruct	ion
A2	0124 8003h	A2	0124 8003h	292 -32765
B8	0A37 8001h	B8	0A37 8001h	2615 -32767
B12	xxxx xxxxh	B12	0124 8001h	292 -32767



MINU4

Minimum, Unsigned, Packed 8-Bit

Syntax

```
MINU4 (.unit) src1, src2, dst
```

unit = .L1 or .L2


Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	0	0	1	0	0	0	1	1	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.L1, .L2
src2	xu4	
dst	u4	

Description

Performs a minimum operation on unsigned, packed 8-bit values. For each pair of unsigned 8-bit values in *src1* and *src2*, **MINU4** places the smaller value in the corresponding position in *dst*.



Execution

```
if (cond)  \{ \\ & \text{if (ubyte0(} \textit{src1}) \textit{<=} \text{ubyte0(} \textit{src2})), \text{ubyte0(} \textit{src1}) \rightarrow \text{ubyte0(} \textit{dst}) \\ & \text{else ubyte0(} \textit{src2}) \rightarrow \text{ubyte0(} \textit{dst}); \\ & \text{if (ubyte1(} \textit{src1}) \textit{<=} \text{ubyte1(} \textit{src2})), \text{ubyte1(} \textit{src1}) \rightarrow \text{ubyte1(} \textit{dst}); \\ & \text{else ubyte1(} \textit{src2}) \rightarrow \text{ubyte1(} \textit{dst}); \\ & \text{if (ubyte2(} \textit{src1}) \textit{<=} \text{ubyte2(} \textit{src2})), \text{ubyte2(} \textit{src1}) \rightarrow \text{ubyte2(} \textit{dst}); \\ & \text{else ubyte3(} \textit{src1}) \textit{<=} \text{ubyte3(} \textit{src2})), \text{ubyte3(} \textit{src1}) \rightarrow \text{ubyte3(} \textit{dst}) \\ & \text{else ubyte3(} \textit{src2}) \rightarrow \text{ubyte3(} \textit{dst}) \\ & \text{else nop}
```





Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also MAX2, MAXU4, MIN2

Example 1

MINU4 .L1 A2, A8, A9

	Before instruction		1 cycle after instruct	ion
A2	37 89 F2 3Ah	A2	37 89 F2 3Ah	55 137 242 58 unsigned
A8	04 B8 49 75h	A8	04 B8 49 75h	4 184 73 117 unsigned
A9	xxxx xxxxh	А9	04 89 49 3Ah	4 137 73 58 unsigned

Example 2

MINU4 .L2 B2, B8, B12

	Before instruction		1 cycle after instruct	ion
B2	01 24 24 B9h	B2	01 24 24 B9h	1 36 36 185 unsigned
B8	01 A6 A0 51h	B8	01 A6 A0 51h	1 166 160 81 unsigned
B12	xxxx xxxxh	B12	01 24 24 51h	1 36 36 81 unsigned



MPY Multiply Signed 16 LSB × Signed 16 LSB

Syntax MPY (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 2	9 28	27	23	22 18	17	13 12	_	11	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1	х	(ор		0	0	0	0	0	S	р
3	1		5	5	5	1	1	5							1	1

Opcode map field used	For operand type	Unit	Opfield
src1	slsb16	.M1, .M2	11001
src2	xslsb16		
dst	sint		
src1	scst5	.M1, .M2	11000
src2	xslsb16		
dst	sint		

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are signed by default.

Execution

if (cond) $lsb16(src1) \times lsb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYU, MPYSU, MPYUS, SMPY





Example 1

MPY .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0000 0123h	291(1)	A1	0000 0123h	
A2	01E0 FA81h	-1407 ⁽¹⁾	A2	01E0 FA81h	
A3	xxxx xxxxh		А3	FFF9 C0A3h	-409,437

⁽¹⁾ Signed 16-LSB integer

Example 2

MPY .M1 13,A1,A2

	Before instruction			2 cycles after instruction	
A1	3497 FFF3h	-13 ⁽¹⁾	A1	3497 FFF3h	
A2	xxxx xxxxh		A2	FFFF FF57h	-169

⁽¹⁾ Signed 16-LSB integer



MPYDP Multiply Two Double-Precision Floating-Point Values

Syntax MPYDP (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2		src1		Χ	0	1	1	1	0	0	0	0	0	0	S	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	dp	.M1, .M2
src2	xdp	
dst	dp	

Description

The src1 operand is multiplied by the src2 operand. The result is placed in dst.

NOTE:

- If one source is SNaN or QNaN, the result is a signed NaN_out. If either source is SNaN, the INVAL bit is set also. The sign of NaN_out is the exclusive-OR of the input signs.
- Signed infinity multiplied by signed infinity or a normalized number (other than signed 0) returns signed infinity. Signed infinity multiplied by signed 0 returns a signed NaN_out and sets the INVAL bit.
- If one or both sources are signed 0, the result is signed 0 unless the other source is NaN or signed infinity, in which case the result is signed NaN_out.
- 4. A denormalized source is treated as signed 0 and the DENn bit is set. The INEX bit is set except when the other source is signed infinity, signed NaN, or signed 0. Therefore, a signed infinity multiplied by a denormalized number gives a signed NaN_out and sets the INVAL bit.
- 5. If rounding is performed, the INEX bit is set.

Execution

if (cond) $src1 \times src2 \rightarrow dst$ else nop





Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E 7	E8	E9	E10
Read	src1_l,	src1_l,	src1_h,	src1_h,						
	src2_I	src2_h	src2_l	src2_h						
Written									dst_l	dst_h
Unit in use	.M	.M	.M	.M						

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYSP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type MPYDP

Delay Slots 9

Functional Unit Latency 4

See Also MPY, MPYSP

Example MPYDP .M1 A1:A0,A3:A2,A5:A4

	Before instruction	on			10 cycles after in	nstruction	
A1:A0	4021 3333h	3333 3333h	8.6	A1:A0	4021 3333h	4021 3333h	
A3:A2	C004 0000h	0000 0000h	-2.5	A3:A2	C004 0000h	0000 0000h	
A5:A4	xxxx xxxxh	xxxx xxxxh		A5:A4	C035 8000h	0000 0000h	-21.5



MPYH Multiply Signed 16 MSB × Signed 16 MSB

Syntax MPYH (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src	1	Х	0	0	0	0	1	0	0	0	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	smsb16 xsmsb16 sint	.M1, .M2

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are signed by default.

Execution

if (cond)

else nop

 $msb16(src1) \times msb16(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYHU, MPYHSU, MPYHUS, SMPYH





Example MPYH .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0023 0000h	35 ⁽¹⁾	A1	0023 0000h	
A2	FFA7 1234h	-89 ⁽¹⁾	A2	FFA7 1234h	
A3	xxxx xxxxh		А3	FFFF F3D5h	-3115

⁽¹⁾ Signed 16-MSB integer



MPYHI Multiply 16 MSB × 32-Bit Into 64-Bit Result

Syntax MPYHI (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 29	28	27 23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1		Х	0	1	0	1	0	0	1	1	0	0	s	p
3	1	5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	sllong	

Description Performs a 16-bit by 32-bit multiply. The upper half of *src1* is used as a signed 16-bit

input. The value in src2 is treated as a signed 32-bit value. The result is written into the

lower 48 bits of a 64-bit register pair, $dst_o:dst_e$, and sign extended to 64 bits.

Execution

if (cond) msb16(src1) × $src2 \rightarrow dst_o:dst_e$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYLI





Examples	Example 1
----------	-----------

MPYHI .M1 A5,A6,A9:A8

	Before instruction	1		4 cycles after inst	ruction
A5	6A32 1193h	27,186	A5	6A32 1193h	
A6	B174 6CA4h	-1,317,770,076	A6	B174 6CA4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	FFFF DF6Ah	DDB9 2008h
				-35,824,897,286,13	36

Example 2

MPYHI .M2 B2,B5,B9:B8

	Before instruction			4 cycles after instruction				
B2	1234 3497h	4660	B2	1234 3497h				
B5	21FF 50A7h	570,380,455	B5	21FF 50A7h				
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	0000 026Ah	DB88 1FECh			
				2,657,972,920,300				



MPYHIR

Multiply 16 MSB x 32-Bit, Shifted by 15 to Produce a Rounded 32-Bit Result

Syntax

MPYHIR (.unit) src1, src2, dst

unit = .M1 or .M2


Opcode

31	29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2		src1		Х	0	1	0	0	0	0	1	1	0	0	s	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	

Description

Performs a 16-bit by 32-bit multiply. The upper half of *src1* is treated as a signed 16-bit input. The value in *src2* is treated as a signed 32-bit value. The product is then rounded to a 32-bit result by adding the value 2¹⁴ and then this sum is right shifted by 15. The lower 32 bits of the result are written into *dst*.



Execution

if (cond) else nop

 $lsb32(((msb16(src1) \times (src2)) + 4000h) >> 15) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

www.ti.com MPYHIR — Multiply 16 MSB x 32-Bit, Shifted by 15 to Produce a Rounded 32-Bit Result

Instruction Type Four-cycle

Delay Slots 3

See Also MPYLIR

Example MPYHIR .M2 B2,B5,B9

	Before instruction			4 cycles after instruction	
B2	1234 3497h	4660	B2	1234 3497h	
B5	21FF 50A7h	570,380,455	B5	21FF 50A7h	
В9	xxxx xxxxh		B9	04D5 B710h	81,114,8

SPRUFE8B-July 2010 Instruction Set 325



MPYHL Multiply Signed 16 MSB x Signed 16 LSB

Syntax MPYHL (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	(dst	src2	src1		Х	0	1	0	0	1	0	0	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2	smsb16 xslsb16	.M1, .M2
dst	sint	

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are signed by default.

Execution

if (cond)

else nop

 $msb16(src1) \times lsb16(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYHLU, MPYHSLU, MPYHULS, SMPYHL





Example MPYHL .M1 A1,A2,A3

	Before instruction			2 cycles after instru	ction
A1	008A 003Eh	138 ⁽¹⁾	A1	008A 003Eh	
A2	21FF 00A7h	167 ⁽²⁾	A2	21FF 00A7h	
А3	xxxx xxxxh		А3	0000 5A06h	23,046

⁽¹⁾ Signed 16-MSB integer (2) Signed 16-LSB integer



MPYHLU Multiply Unsigned 16 MSB × Unsigned 16 LSB

Syntax MPYHLU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	0	1	1	1	1	0	0	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	umsb16	.M1, .M2
src2	xulsb16	
dst	uint	

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are unsigned by default.

Execution

if (cond) msb16(src1) x lsb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots

See Also MPYHL, MPYHSLU, MPYHULS



MPYHSLU Multiply Signed 16 MSB × Unsigned 16 LSB

Syntax MPYHSLU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 2	29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2		src1		Х	0	1	0	1	1	0	0	0	0	0	s	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	smsb16	.M1, .M2
src2	xulsb16	
dst	sint	

Description The signed operand *src1* is multiplied by the unsigned operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) msb16(src1) x lsb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYHL, MPYHLU, MPYHULS



MPYHSU Multiply Signed 16 MSB × Unsigned 16 MSB

Syntax MPYHSU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st .	src2	src1		Х	0	0	0	1	1	0	0	0	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	smsb16	.M1, .M2
src2	xumsb16	
dst	sint	

Description The signed operand *src1* is multiplied by the unsigned operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) msb16(src1) × msb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYH, MPYHU, MPYHUS

Example MPYHSU .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0023 0000h	35 ⁽¹⁾	A1	0023 0000h	
A2	FFA7 FFFFh	65,447 ⁽²⁾	A2	FFA7 FFFFh	
А3	xxxx xxxxh		А3	0022 F3D5h	2,290,645

⁽¹⁾ Signed 16-MSB integer

⁽²⁾ Unsigned 16-MSB integer



MPYHU Multiply Unsigned 16 MSB × Unsigned 16 MSB

Syntax MPYHU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	0	0	1	1	1	0	0	0	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	umsb16	.M1, .M2
src2	xumsb16	
dst	uint	

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are unsigned by default.

Execution

if (cond) msb16(src1) x msb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYH, MPYHSU, MPYHUS

Example MPYHU .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0023 0000h	35 ⁽¹⁾	A1	0023 0000h	
A2	FFA7 1234h	65,447 ⁽¹⁾	A2	FFA7 1234h	
А3	xxxx xxxxh		A3	0022 F3D5h	2,290,645 ⁽²⁾

⁽¹⁾ Unsigned 16-MSB integer

⁽²⁾ Unsigned 32-bit integer



MPYHULS Multiply Unsigned 16 MSB × Signed 16 LSB

Syntax MPYHULS (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23		8 1	7	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	z		dst	src2		src1		Χ	0	1	1	0	1	0	0	0	0	0	s	р
3	1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	umsb16	.M1, .M2
src2	xslsb16	
dst	sint	

Description The unsigned operand *src1* is multiplied by the signed operand *src2*. The result is placed

in dst. The **S** is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) msb16(src1) × lsb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYHL, MPYHLU, MPYHSLU



MPYHUS Multiply Unsigned 16 MSB × Signed 16 MSB

Syntax MPYHUS (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 18	8 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2		src1		Х	0	0	1	0	1	0	0	0	0	0	s	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	umsb16	.M1, .M2
src2	xsmsb16	
dst	sint	

Description The unsigned operand *src1* is multiplied by the signed operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) msb16(src1) x msb16(src2) $\rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYH, MPYHU, MPYHSU



MPYI Multiply 32-Bit × 32-Bit Into 32-Bit Result

Syntax MPYI (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 2	9 28	27	23	22 18	17	13 12	11		7	6	5	4	3	2	1	0
creg	Z	C	dst	src2	src1	Х		ор		0	0	0	0	0	s	p
3	1		5	5	5	1		5							1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.M1, .M2	00100
src2	xsint		
dst	sint		
src1	cst5	.M1, .M2	00110
src1 src2	xsint		
dst	sint		

Description The *src1* operand is multiplied by the *src2* operand. The lower 32 bits of the result are

placed in dst.

Execution

if (cond) $lsb32(src1 \times src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7	E8	E9
Read	src1, src2	src1, src2	src1, src2	src1, src2					
Written									dst
Unit in use	.M	.M	.M	.M					

Instruction Type MPYI

Delay Slots 8

Functional Unit Latency 4

See Also MPYID

Example MPYI .M1X A1,B2,A3

	Before instruction			9 cycles after instruction	
A1	0034 5678h	3,430,008	A1	0034 5678h	
B2	0011 2765h	1,124,197	B2	0011 2765h	
А3	xxxx xxxxh		А3	CBCA 6558h	-875,928,232





MPYID Multiply 32-Bit × 32-Bit Into 64-Bit Result

Syntax MPYID (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 2	9 28	27	23	22 18	17	13 12	11		7	6	5	4	3	2	1	0
creg	Z	C	dst	src2	src1	Х		ор		0	0	0	0	0	s	p
3	1		5	5	5	1		5							1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.M1, .M2	01000
src2	xsint		
dst	sdint		
src1	cst5	.M1, .M2	01100
src1 src2	xsint		
dst	sdint		

Description The *src1* operand is multiplied by the *src2* operand. The 64-bit result is placed in the *dst*

register pair.

Execution

if (cond) $lsb32(src1 \times src2) \rightarrow dst_l$

 $msb32(src1 \times src2) \rightarrow dst_h$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7	E8	E9	E10
Read	src1, src2	src1, src2	src1, src2	src1, src2						
Written									dst_l	dst_h
Unit in use	.M	.M	.M	.M						

Instruction Type MPYID

Delay Slots 9 (8 if *dst_l* is *src* of next instruction)

Functional Unit Latency 4

See Also MPYI



Example

MPYID .M1 A1,A2,A5:A4

	Before instruction	n		10 cycles after in	struction
A1	0034 5678h	3,430,008	A1	0034 5678h	
B2	0011 2765h	1,124,197	B2	0011 2765h	
A5:A4	xxxx xxxxh	xxxx xxxxh	A5:A4	0000 0381h	CBCA 6558h
	,			3,856,004,703,576	;





MPYIH Multiply 32-Bit × 16-MSB Into 64-Bit Result

Syntax MPYIH (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 18	3 17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2	src1		Х	0	1	0	1	0	0	1	1	0	0	s	p
3		1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	sllong	

Description The **MPYIH** pseudo-operation performs a 16-bit by 32-bit multiply. The upper half of *src1*

is used as a signed 16-bit input. The value in *src2* is treated as a signed 32-bit value. The result is written into the lower 48 bits of a 64-bit register pair, *dst_o:dst_e*, and sign extended to 64 bits. The assembler uses the **MPYHI** (.unit) *src1*, *src2*, *dst* instruction to

perform this operation (see MPYHI).

Execution

if (cond)

 $src2 \times msb16(src1) \rightarrow dst_o:dst_e$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYHI, MPYIL



MPYIHR Multiply 32-Bit × 16 MSB, Shifted by 15 to Produce a Rounded 32-Bit Result

Syntax MPYIHR (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2		src1		Х	0	1	0	0	0	0	1	1	0	0	s	p
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	

Description The **MPYIHR** pseudo-operation performs a 16-bit by 32-bit multiply. The upper half of

src1 is treated as a signed 16-bit input. The value in src2 is treated as a signed 32-bit value. The product is then rounded to a 32-bit result by adding the value 2¹⁴ and then this sum is right shifted by 15. The lower 32 bits of the result are written into dst. The assembler uses the MPYHIR (.unit) src1, src2, dst instruction to perform this operation

(see MPYHIR).

Execution

if (cond) $lsb32((((src2) \times msb16(src1)) + 4000h) >> 15) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYHIR, MPYILR





MPYIL Multiply 32-Bit × 16 LSB Into 64-Bit Result

Syntax MPYIL (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 1	18 1	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		src1		Х	0	1	0	1	0	1	1	1	0	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	sllong	

Description The **MPYIL** pseudo-operation performs a 16-bit by 32-bit multiply. The lower half of src1

is used as a signed 16-bit input. The value in *src2* is treated as a signed 32-bit value. The result is written into the lower 48 bits of a 64-bit register pair, *dst_o:dst_e*, and sign extended to 64 bits. The assembler uses the **MPYLI** (.unit) *src1*, *src2*, *dst* instruction to

perform this operation (see MPYLI).

Execution

if (cond) else nop

 $src2 \times lsb16(src1) \rightarrow dst_o:dst_e$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYIH, MPYLI



MPYILR Multiply 32-Bit × 16 LSB, Shifted by 15 to Produce a Rounded 32-Bit Result

Syntax MPYILR (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	z		dst	src2			src1		Х	0	0	1	1	1	0	1	1	0	0	s	p
3		1		5	5			5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	

Description

The **MPYILR** pseudo-operation performs a 16-bit by 32-bit multiply. The lower half of *src1* is used as a signed 16-bit input. The value in *src2* is treated as a signed 32-bit value. The product is then rounded to a 32-bit result by adding the value 2¹⁴ and then this sum is right shifted by 15. The lower 32 bits of the result are written into *dst*. The assembler uses the **MPYLIR** (.unit) *src1*, *src2*, *dst* instruction to perform this operation (see MPYLIR).

Execution

if (cond) else nop

 $lsb32((((src2) \times lsb16(src1)) + 4000h) >> 15) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYIHR, MPYLIR





MPYLH Multiply Signed 16 LSB x Signed 16 MSB

Syntax MPYLH (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31	29	28	27	23	22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src2		,	src1		Х	1	0	0	0	1	0	0	0	0	0	S	р
3		1		5	5			5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	slsb16 xsmsb16 sint	.M1, .M2

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are signed by default.

Execution

if (cond)

else nop

 $lsb16(src1) \times msb16(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYLHU, MPYLSHU, MPYLUHS, SMPYLH

SPRUFE8B-July 2010 Instruction Set 341



Example

MPYLH .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0900 000Eh	14 ⁽¹⁾	A1	0900 000Eh	
A2	0029 00A7h	41 (2)	A2	0029 00A7h	
A3	xxxx xxxxh		A3	0000 023Eh	574

⁽¹⁾ Signed 16-LSB integer

⁽²⁾ Signed 16-MSB integer





MPYLHU Multiply Unsigned 16 LSB × Unsigned 16 MSB

Syntax MPYLHU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 10	8	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	dst		src2		src1		Х	1	0	1	1	1	0	0	0	0	0	s	p
3		1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	ulsb16	.M1, .M2
src2	xumsb16	
dst	uint	

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are unsigned by default.

Execution

if (cond) $lsb16(src1) \times msb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots

See Also MPYLH, MPYLSHU, MPYLUHS

SPRUFE8B-July 2010 Instruction Set 343



MPYLI Multiply 16 LSB x 32-Bit Into 64-Bit Result

Syntax MPYLI (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 1	8 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2		src1		Х	0	1	0	1	0	1	1	1	0	0	s	р
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	sllong	

Description Performs a 16-bit by 32-bit multiply. The lower half of *src1* is used as a signed 16-bit

input. The value in *src2* is treated as a signed 32-bit value. The result is written into the lower 48 bits of a 64-bit register pair, *dst_o:dst_e*, and sign extended to 64 bits.

Execution

if (cond) $lsb16(src1) \times src2 \rightarrow dst_o:dst_e$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYHI

Example 1

MPYLI .M1 A5,A6,A9:A8

	Before instruction	ı		4 cycles after inst	truction
A5	6A32 1193h	4499	A5	6A32 1193h	
A6	B174 6CA4h	-1,317,770,076	A6	B174 6CA4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	FFFF FA9Bh	A111 462Ch
			<u>-</u>	-5,928,647,571,924	4



Example 2

MPYLI .M2 B2,B5,B9:B8

	Before instruction			4 cycles after instruct	tion
B2	1234 3497h	13,463	B2	1234 3497h	
B5	21FF 50A7h	570,380,455	B5	21FF 50A7h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	0000 06FBh	E9FA 7E81h
			•	7,679,032,065,665	<u>. </u>

SPRUFE8B-July 2010 Instruction Set 345




MPYLIR Multiply 16 LSB × 32-Bit, Shifted by 15 to Produce a Rounded 32-Bit Result

Syntax MPYLIR (.unit) src1, src2, dst

unit = .M1 or .M2


Opcode



Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	

Description

Performs a 16-bit by 32-bit multiply. The lower half of *src1* is treated as a signed 16-bit input. The value in *src2* is treated as a signed 32-bit value. The product is then rounded into a 32-bit result by adding the value 2¹⁴ and then this sum is right shifted by 15. The lower 32 bits of the result are written into *dst*.



Execution

if (cond) $lsb32(((lsb16(src1) \times (src2)) + 4000h) >> 15) \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			



www.ti.com

Instruction Type Four-cycle

Delay Slots 3

See Also MPYHIR

Example MPYLIR .M2 B2,B5,B9

	Before instruction			4 cycles after instruc	tion
B2	1234 3497h	13,463	B2	1234 3497h	
B5	21FF 50A7h	570,380,455	B5	21FF 50A7h	
В9	xxxx xxxxh		В9	0DF7 D3F5h	234,345,461

SPRUFE8B-July 2010 Instruction Set 347



MPYLSHU Multiply Signed 16 LSB × Unsigned 16 MSB

Syntax MPYLSHU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27 23	22 18	17	13 12	11	10	9	8 7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	Х	1	0	0	1 1	0	0	0	0	0	s	р
3	1	5	5	5	1										1	1

Opcode map field used	For operand type	Unit
src1	slsb16	.M1, .M2
src2	xumsb16	
dst	sint	

Description The signed operand *src1* is multiplied by the unsigned operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) $lsb16(src1) \times msb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYLH, MPYLHU, MPYLUHS



MPYLUHS Multiply Unsigned 16 LSB × Signed 16 MSB

Syntax MPYLUHS (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 18	0 17	/ 1	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	dst		src2		src1		Х	1	0	1	0	1	0	0	0	0	0	s	p
3		1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	ulsb16	.M1, .M2
src2	xsmsb16	
dst	sint	

Description The unsigned operand *src1* is multiplied by the signed operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) $lsb16(src1) \times msb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPYLH, MPYLHU, MPYLSHU



MPYSP Multiply Two Single-Precision Floating-Point Values

Syntax MPYSP (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	t	src2			src1		Х	1	1	1	0	0	0	0	0	0	0	s	p
3	1	5		5			5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.M1, .M2
src2	xsp	
dst	sp	

Description

The src1 operand is multiplied by the src2 operand. The result is placed in dst.

NOTE:

- If one source is SNaN or QNaN, the result is a signed NaN_out. If either source is SNaN, the INVAL bit is set also. The sign of NaN_out is the exclusive-OR of the input signs.
- Signed infinity multiplied by signed infinity or a normalized number (other than signed 0) returns signed infinity. Signed infinity multiplied by signed 0 returns a signed NaN_out and sets the INVAL bit.
- If one or both sources are signed 0, the result is signed 0 unless the other source is NaN or signed infinity, in which case the result is signed NaN_out.
- 4. A denormalized source is treated as signed 0 and the DENn bit is set. The INEX bit is set except when the other source is signed infinity, signed NaN, or signed 0. Therefore, a signed infinity multiplied by a denormalized number gives a signed NaN_out and sets the INVAL bit.
- 5. If rounding is performed, the INEX bit is set.

Execution

if (cond) $src1 \times src2 \rightarrow dst$ else nop



Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also MPY, MPYDP, MPYSP2DP

Example MPYSP .M1X A1,B2,A3

	Before instruction			4 cycles after instruction	
A1	C020 0000h	-2.5	A1	C020 0000h	
B2	4109 999Ah	8.6	B2	4109 999Ah	
A3	xxxx xxxxh		А3	C1AC 0000h	-21.5

SPRUFE8B-July 2010 Instruction Set 351



MPYSPDP

Multiply Single-Precision Floating-Point Value × Double-Precision Floating-Point

Value

Syntax

MPYSPDP (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	0	1	0	1	1	0	1	1	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.M1, .M2
src2	xdp	
dst	dp	

Description

The single-precision *src1* operand is multiplied by the double-precision *src2* operand to produce a double-precision result. The result is placed in *dst*.

NOTE:

- If one source is SNaN or QNaN, the result is a signed NaN_out. If either source is SNaN, the INVAL bit is set also. The sign of NaN_out is the exclusive-OR of the input signs.
- Signed infinity multiplied by signed infinity or a normalized number (other than signed 0) returns signed infinity. Signed infinity multiplied by signed 0 returns a signed NaN_out and sets the INVAL bit.
- If one or both sources are signed 0, the result is signed 0 unless the other source is NaN or signed infinity, in which case the result is signed NaN out.
- 4. A denormalized source is treated as signed 0 and the DENn bit is set. The INEX bit is set except when the other source is signed infinity, signed NaN, or signed 0. Therefore, a signed infinity multiplied by a denormalized number gives a signed NaN_out and sets the INVAL bit.
- 5. If rounding is performed, the INEX bit is set.

Execution

if (cond) $src1 \times src2 \rightarrow dst$

else nop



www.ti.com

MPYSPDP — Multiply Single-Precision Floating-Point Value x Double-Precision Floating-Point Value

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7
Read	src1, src2_l	src1, src2_h					
Written						dst_l	dst_h
Unit in use	.M	.M					

The low half of the result is written out one cycle earlier than the high half. If *dst* is used as the source for the ADDDP, CMPEQDP, CMPLTDP, CMPGTDP, MPYDP, MPYSPDP, or SUBDP instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type MPYSPDP

Delay Slots 6

Functional Unit Latency 3

See Also MPY, MPYDP, MPYSP, MPYSP2DP



MPYSP2DP

Multiply Two Single-Precision Floating-Point Values for Double-Precision Result

Syntax

MPYSP2DP (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	9 28	27	23	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		src1		Χ	0	1	0	1	1	1	1	1	0	0	s	p
3	1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	sp	.M1, .M2
src2	xsp	
dst	dp	

Description

The *src1* operand is multiplied by the *src2* operand to produce a double-precision result. The result is placed in *dst*.

NOTE:

- If one source is SNaN or QNaN, the result is a signed NaN_out. If either source is SNaN, the INVAL bit is set also. The sign of NaN_out is the exclusive-OR of the input signs.
- Signed infinity multiplied by signed infinity or a normalized number (other than signed 0) returns signed infinity. Signed infinity multiplied by signed 0 returns a signed NaN_out and sets the INVAL bit.
- If one or both sources are signed 0, the result is signed 0 unless the other source is NaN or signed infinity, in which case the result is signed NaN_out.
- 4. A denormalized source is treated as signed 0 and the DENn bit is set. The INEX bit is set except when the other source is signed infinity, signed NaN, or signed 0. Therefore, a signed infinity multiplied by a denormalized number gives a signed NaN_out and sets the INVAL bit.
- 5. If rounding is performed, the INEX bit is set.

Execution

if (cond) $src1 \times src2 \rightarrow dst$ else nop

www.ti.com

MPYSP2DP — Multiply Two Single-Precision Floating-Point Values for Double-Precision Result

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5
Read	src1, src2				
Written				dst_l	dst_h
Unit in use	.M				

The low half of the result is written out one cycle earlier than the high half. If *dst* is used as the source for the ADDDP, CMPEQDP, CMPLTDP, CMPGTDP, MPYDP, MPYSPDP, or SUBDP instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type Five-cycle

Delay Slots 4

Functional Unit Latency 2

See Also MPY, MPYDP, MPYSP, MPYSPDP



MPYSU Multiply Signed 16 LSB × Unsigned 16 LSB

Syntax MPYSU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28		23 22	18 17	13 12	11 7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	ор	0	0	0	0	0	s	р
3	1	5	5	5	1	5						1	1

Opcode map field used	For operand type	Unit	Opfield
src1	slsb16	.M1, .M2	11011
src2	xulsb16		
dst	sint		
src1	scst5	.M1, .M2	11110
src2	xulsb16		
dst	sint		

Description

The signed operand *src1* is multiplied by the unsigned operand *src2*. The result is placed in *dst*. The **S** is needed in the mnemonic to specify a signed operand when both signed and unsigned operands are used.

Execution

if (cond) else nop

 $lsb16(src1) \times lsb16(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPY, MPYU, MPYUS

Example MPYSU .Ml 13,Al,A2

	Before instruction			2 cycles after instruction	
A1	3497 FFF3h	65,523 ⁽¹⁾	A1	3497 FFF3h	
A2	xxxx xxxxh		A2	000C FF57h	851,779

⁽¹⁾ Unsigned 16-LSB integer



MPYSU4

Multiply Signed × Unsigned, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

MPYSU4 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	1	0	1	1	1	0	0	S	р
3	1	5		5	5		1											1	1


Opcode map field used	For operand type	Unit
src1	s4	.M1, .M2
src2	xu4	
dst	dws4	

Description

Returns the product between four sets of packed 8-bit values producing four signed 16-bit results. The four signed 16-bit results are packed into a 64-bit register pair, $dst_o:dst_e$. The values in src1 are treated as signed 8-bit packed quantities; whereas, the values in src2 are treated as unsigned 8-bit packed data.

For each pair of 8-bit quantities in *src1* and *src2*, the signed 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*:

- The product of src1 byte 0 and src2 byte 0 is written to the lower half of dst_e.
- The product of src1 byte 1 and src2 byte 1 is written to the upper half of dst_e.
- The product of src1 byte 2 and src2 byte 2 is written to the lower half of dst_o.
- The product of src1 byte 3 and src2 byte 3 is written to the upper half of dst_o.



SPRUFE8B-July 2010 Instruction Set 357



Execution

```
if (cond)  \{ \\ (\text{sbyte0}(\textit{src1}) \times \text{ubyte0}(\textit{src2})) \rightarrow \text{lsb16}(\textit{dst\_e}); \\ (\text{sbyte1}(\textit{src1}) \times \text{ubyte1}(\textit{src2})) \rightarrow \text{msb16}(\textit{dst\_e}); \\ (\text{sbyte2}(\textit{src1}) \times \text{ubyte2}(\textit{src2})) \rightarrow \text{lsb16}(\textit{dst\_o}); \\ (\text{sbyte3}(\textit{src1}) \times \text{ubyte3}(\textit{src2})) \rightarrow \text{msb16}(\textit{dst\_o}); \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYU4

Example 1

MPYSU4 .M1 A5,A6,A9:A8

	Before instruction			4 cycles after inst	ruction
A5	6A 32 11 93h	106 50 17 -109 signed	A5	6A 32 11 93h	
A6	B1 74 6C A4h	177 116 108 164 unsigned	A6	B1 74 6C A4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	494A 16A8h	072C BA2Ch
			<u></u>	18762 5800	1386 -17876 signed

Example 2

MPYSU4 .M2 B5,B6,B9:B8

	Before instruction			4 cycles after inst	ruction
B5	3F F6 50 10h	63 -10 80 16 signed	B5	3F F6 50 10h	
B6	C3 56 02 44h	195 86 2 68 unsigned	B6	C3 56 02 44h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	2FFD FCA4h	00A0 0440h
		,		12285 -680	160 1088 signed





MPYU Multiply Unsigned 16 LSB × Unsigned 16 LSB

Syntax MPYU (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	C	dst	src2		src1		Χ	1	1	1	1	1	0	0	0	0	0	s	p
3	1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	ulsb16	.M1, .M2
src2	xulsb16	
dst	uint	

Description The *src1* operand is multiplied by the *src2* operand. The result is placed in *dst*. The

source operands are unsigned by default.

Execution

if (cond) $lsb16(src1) \times lsb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPY, MPYSU, MPYUS

Example MPYU .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	0000 0123h	291 ⁽¹⁾	A1	0000 0123h	
A2	0F12 FA81h	64,129 ⁽¹⁾	A2	0F12 FA81h	
А3	xxxx xxxxh		A3	011C C0A3h	18,661,539 ⁽²⁾

⁽¹⁾ Unsigned 16-LSB integer

⁽²⁾ Unsigned 32-bit integer



MPYU4

Multiply Unsigned × Unsigned, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

MPYU4 (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31	29	28	27	23	22 1	8	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	z		dst	src2		src1		Х	0	0	0	1	0	0	1	1	0	0	s	p
3		1		5	5		5		1											1	1


Opcode map field used	For operand type	Unit
src1	u4	.M1, .M2
src2	xu4	
dst	dwu4	

Description

Returns the product between four sets of packed 8-bit values producing four unsigned 16-bit results that are packed into a 64-bit register pair, *dst_o:dst_e*. The values in both *src1* and *src2* are treated as unsigned 8-bit packed data.

For each pair of 8-bit quantities in *src1* and *src2*, the unsigned 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*:

- The product of *src1* byte 0 and *src2* byte 0 is written to the lower half of *dst_e*.
- The product of src1 byte 1 and src2 byte 1 is written to the upper half of dst_e.
- The product of *src1* byte 2 and *src2* byte 2 is written to the lower half of *dst_o*.
- The product of *src1* byte 3 and *src2* byte 3 is written to the upper half of *dst_o*.





Execution

```
if (cond)  \{ \\ (\text{ubyte0}(\textit{src1}) \times \text{ubyte0}(\textit{src2})) \rightarrow \text{lsb16}(\textit{dst\_e}); \\ (\text{ubyte1}(\textit{src1}) \times \text{ubyte1}(\textit{src2})) \rightarrow \text{msb16}(\textit{dst\_e}); \\ (\text{ubyte2}(\textit{src1}) \times \text{ubyte2}(\textit{src2})) \rightarrow \text{lsb16}(\textit{dst\_o}); \\ (\text{ubyte3}(\textit{src1}) \times \text{ubyte3}(\textit{src2})) \rightarrow \text{msb16}(\textit{dst\_o}); \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYSU4

Example 1

MPYU4 .M1 A5,A6,A9:A8

	Before instruction			4 cycles after inst	ruction
A5	68 32 C1 93h	104 50 193 147 unsigned	A5	68 32 C1 93h	
A6	B1 74 2C ABh	177 116 44 171 unsigned	A6	B1 74 2C ABh	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	47E8 16A8h	212C 6231h
				18408 5800	8492 25137 unsigned

Example 2

MPYU4 .M2 B2,B5,B9:B8

	Before instruction			4 cycles after inst	ruction
B2	3D E6 50 7Fh	61 230 80 127 unsigned	B2	3D E6 50 7Fh	
B5	C3 56 02 44h	195 86 2 68 unsigned	B5	C3 56 02 44h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	2E77 4D44h	00A0 21BCh
				11895 19780	160 8636 unsigned



MPYUS Multiply Unsigned 16 LSB × Signed 16 LSB

Syntax MPYUS (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	1	1	1	0	1	0	0	0	0	0	s	р
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	ulsb16	.M1, .M2
src2	xslsb16	
dst	sint	

Description The unsigned operand *src1* is multiplied by the signed operand *src2*. The result is placed

in dst. The S is needed in the mnemonic to specify a signed operand when both signed

and unsigned operands are used.

Execution

if (cond) $lsb16(src1) \times lsb16(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Multiply (16×16)

Delay Slots 1

See Also MPY, MPYU, MPYSU

Example MPYUS .M1 A1,A2,A3

	Before instruction			2 cycles after instruction	
A1	1234 FFA1h	65,441 ⁽¹⁾	A1	1234 FFA1h	
A2	1234 FFA1h	-95 ⁽²⁾	A2	1234 FFA1h	
А3	xxxx xxxxh		А3	FFA1 2341h	-6,216,895

⁽¹⁾ Unsigned 16-LSB integer

⁽²⁾ Signed 16-LSB integer



MPYUS4

Multiply Unsigned × Signed, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

```
MPYUS4 (.unit) src2, src1, dst
```

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	3 17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	C	dst	src2	src1		Х	0	0	0	1	0	1	1	1	0	0	s	p
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s4	.M1, .M2
src2	xu4	
dst	dws4	

Description

The **MPYUS4** pseudo-operation returns the product between four sets of packed 8-bit values, producing four signed 16-bit results. The four signed 16-bit results are packed into a 64-bit register pair, *dst_o:dst_e*. The values in *src1* are treated as signed 8-bit packed quantities; whereas, the values in *src2* are treated as unsigned 8-bit packed data. The assembler uses the **MPYSU4** (.unit) *src1*, *src2*, *dst* instruction to perform this operation (see MPYSU4).

For each pair of 8-bit quantities in *src1* and *src2*, the signed 8-bit value from *src1* is multiplied with the unsigned 8-bit value from *src2*:

- The product of src1 byte 0 and src2 byte 0 is written to the lower half of dst e.
- The product of src1 byte 1 and src2 byte 1 is written to the upper half of dst_e.
- The product of src1 byte 2 and src2 byte 2 is written to the lower half of dst o.
- The product of src1 byte 3 and src2 byte 3 is written to the upper half of dst_o.

Execution

```
if (cond)  \{ \\ (\text{ubyte0}(\textit{src2}) \times \text{sbyte0}(\textit{src1})) \rightarrow \text{lsb16}(\textit{dst\_e}); \\ (\text{ubyte1}(\textit{src2}) \times \text{sbyte1}(\textit{src1})) \rightarrow \text{msb16}(\textit{dst\_e}); \\ (\text{ubyte2}(\textit{src2}) \times \text{sbyte2}(\textit{src1})) \rightarrow \text{lsb16}(\textit{dst\_o}); \\ (\text{ubyte3}(\textit{src2}) \times \text{sbyte3}(\textit{src1})) \rightarrow \text{msb16}(\textit{dst\_o}); \\ \} \\ \text{else nop}
```



Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYSU4, MPYU4



MPY2

Multiply Signed by Signed, 16 LSB x 16 LSB and 16 MSB x 16 MSB

Syntax

MPY2 (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	0	0	0	1	1	0	0	s	р
3	1	5		5	5		1											1	1


Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src1 src2	xs2	
dst	ullong	

Description

Performs two 16-bit by 16-bit multiplications between two pairs of signed, packed 16-bit values. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The two 32-bit results are written into a 64-bit register pair.

The product of the lower halfwords of *src1* and *src2* is written to the even destination register, *dst_e*. The product of the upper halfwords of *src1* and *src2* is written to the odd destination register, *dst_o*.

This instruction helps reduce the number of instructions required to perform two 16-bit by 16-bit multiplies on both the lower and upper halves of two registers.



The following code:

MPY .M1 A0, A1, A2 MPYH .M1 A0, A1, A3

may be replaced by:

MPY2 .M1 A0, A1, A3:A2



Execution

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			_
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPYSU4, MPY2IR, SMPY2

Examples Example 1

MPY2 .M1 A5,A6, A9:A8

	Before instruction	1		4 cycles after inst	ruction
A5	6A32 1193h	27186 4499	A5	6A32 1193h	
A6	B174 6CA4h	-20108 27812	A6	B174 6CA4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	DF6A B0A8h	0775 462Ch
	<u> </u>			-546,656,088	125,126,188

Example 2

MPY2 .M2 B2, B5, B9:B8

	Before instruction	1		4 cycles after inst	ruction
B2	1234 3497h	4660 13463	B2	1234 3497h	
B5	21FF 50A7h	7h 8703 20647 E		21FF 50A7h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	026A D5CCh	1091 7E81h
	<u> </u>			40,555,980	277,970,561



MPY2IR Multiply Two 16-Bit x 32-Bit, Shifted by 15 to Produce a Rounded 32-Bit Result

MPY2IR (.unit) src1, src2, dst_o:dst_e **Syntax**

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18		12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1	х	0	0	1	1	1	1	1	1	0	0	s	р
				5	5	5	1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	dint	

Description

Performs two 16-bit by 32-bit multiplies. The upper and lower halves of src1 are treated as 16-bit signed inputs. The value in src2 is treated as a 32-bit signed value. The products are then rounded to a 32-bit result by adding the value 214 and then these sums are right shifted by 15. The lower 32 bits of the two results are written into dst_o:dst_e.

If either result saturates, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to dst o:dst e.

This instruction executes unconditionally and cannot be predicated.

NOTE: In the overflow case, where the 16-bit input to the MPYIR operation is 8000h and the 32-bit input is 8000 0000h, the saturation value 7FFF FFFFh is written into the corresponding 32-bit dst register.

Execution

if (msb16(src1) = 8000h && src2 = 8000 0000h), 7FFF FFFFh \rightarrow dst_o else lsb32(((msb16(src1) × (src2)) + 4000h) >> 15) \rightarrow dst_o; if (lsb16(src1) = 8000h && src2 = 8000 0000h), 7FFF FFFFh \rightarrow dst e else lsb32(((lsb16(src1) × (src2)) + 4000h) >> 15) \rightarrow dst_e

Instruction Type Four-cycle

Delay Slots 3

See Also MPYLIR, MPYHIR



Examples

Example 1

MPY2IR .M2 B2,B5,B9:B8

	Before instruction		4 cycles after instruction
B2	8000 8001h	B8	7FFF 0000h
B5	8000 0000h	В9	7FFF FFFFh
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0020h

⁽¹⁾ CSR.SAT and SSR.M2 set to 1, 5 cycles after instruction

Example 2

MPY2IR .M1X A2,B5,A9:A8

	Before instruction		4 cycles after instruction
A2	8765 4321h	A8	098C 16C1h
B5	1234 5678h	A9	EED8 E38Fh
CSR	0001 0100h	CSR ⁽¹⁾	0001 0100h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0000h

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation





MPY32 Multiply Signed 32-Bit × Signed 32-Bit Into 32-Bit Result

MPY32 (.unit) src1, src2, dst **Syntax**

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	0	0	0	0	0	0	0	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	

Performs a 32-bit by 32-bit multiply. *src1* and *src2* are signed 32-bit values. Only the lower 32 bits of the 64-bit result are written to *dst*. Description

Execution

if (cond) $src1 \times src2 \rightarrow dst$

else nop

Four-cycle **Instruction Type**

Delay Slots 3

MPY32, MPY32SU, MPY32US, MPY32U, SMPY32 See Also



MPY32 Multiply Signed 32-Bit × Signed 32-Bit Into Signed 64-Bit Result

Syntax MPY32 (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	d	lst	src2	src1		Х	1	0	1	0	0	0	0	0	0	0	s	p
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	dint	

Description Performs a 32-bit by 32-bit multiply. *src1* and *src2* are signed 32-bit values. The signed

64-bit result is written to the register pair specified by dst.

Execution

if (cond) $src1 \times src2 \rightarrow dst_o:dst_e$

else nop

Instruction Type Four-cycle

Delay Slots 3

See Also MPY32, MPY32SU, MPY32US, MPY32U, SMPY32



MPY32SU Multiply Signed 32-Bit × Unsigned 32-Bit Into Signed 64-Bit Result

Syntax MPY32SU (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	0	1	1	0	0	0	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xuint	
dst	dint	

Description Performs a 32-bit by 32-bit multiply. *src1* is a signed 32-bit value and *src2* is an unsigned

32-bit value. The signed 64-bit result is written to the register pair specified by dst.

Execution

if (cond) $src1 \times src2 \rightarrow dst_o:dst_e$

else nop

Instruction Type Four-cycle

Delay Slots 3

See Also MPY32, MPY32U, MPY32US, SMPY32



MPY32U Multiply Unsigned 32-Bit × Unsigned 32-Bit Into Unsigned 64-Bit Result

Syntax MPY32U (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	0	1	1	0	0	0	1	1	0	0	s	p
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.M1, .M2
src2	xuint	
dst	duint	

Description Performs a 32-bit by 32-bit multiply. *src1* and *src2* are unsigned 32-bit values. The

unsigned 64-bit result is written to the register pair specified by dst.

Execution

if (cond) $src1 \times src2 \rightarrow dst_o:dst_e$

else nop

Instruction Type Four-cycle

Delay Slots 3

See Also MPY32, MPY32SU, MPY32US, SMPY32



MPY32US Multiply Unsigned 32-Bit × Signed 32-Bit Into Signed 64-Bit Result

Syntax MPY32US (.unit) src1, src2, dst_o:dst_e

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	d	st	src2	src1		Х	0	1	1	0	0	1	1	1	0	0	s	р
3	1	5	5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.M1, .M2
src2	xint	
dst	dint	

Description Performs a 32-bit by 32-bit multiply. *src1* is an unsigned 32-bit value and *src2* is a signed

32-bit value. The signed 64-bit result is written to the register pair specified by dst.

Execution

if (cond) $src1 \times src2 \rightarrow dst_o:dst_e$

else nop

Instruction Type Four-cycle

Delay Slots 3

See Also MPY32, MPY32SU, MPY32U, SMPY32



MV Move From Register to Register

Syntax MV (.unit) src2, dst

unit = .L1, .L2, .S1, .S2, .D1, .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.L, .S, .D	LSDmvto	Figure G-1
	LSDmvtfr	Figure G-2

Opcode

.L unit (if the cross path form is not used)

31	29	28	27	23	22 18	8	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z		dst	src2		0	0	0	0	0	0	0	1	0	0	0	0	0	1	1	0	s	р
	3	1		5	5																		1	1

Opcode map field used	For operand type	Unit
src2 dst	slong slong	.L1, .L2

Opcode

.L unit (if the cross path form is used)

31	29	28	27	23	22	18	17	16	15	14	13	12	11		5	4	3	2	1	0
cre	g	Z		dst	src2		0	0	0	0	0	Х		ор		1	1	0	s	p
3		1		5	5							1		7					1	1

Opcode map field used	For operand type	Unit	Opfield
src2 dst	xsint sint	.L1, .L2	000 0010
src2 dst	xuint uint	.L1, .L2	111 1110





Орсс	ode			.S ur	iit																				
31	29	28	27		23 2	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
С	reg	Z		dst		src2		0	0	0	0	0	х	0	0	0	1	1	0	1	0	0	0	s	р
	3	1		5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xsint	.S1, .S2
dst	sint	

Opcode

.D unit (if the cross path form is not used)

3	1 29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2		0	0	0	0	0	0	1	0	0	1	0	1	0	0	0	0	S	р
	3	1	5		5																		1	1

Opcode map field used	For operand type	Unit
src2	sint	.D1, .D2
dst	sint	

Opcode

.D unit (if the cross path form is used)

31	29	28	27	23	22 18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2	0	0	0	0	0	Х	1	0	0	0	1	1	1	1	0	0	s	р
3		1		5	5						1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.D1, .D2
dst	uint	

Description

The **MV** pseudo-operation moves a value from one register to another. The assembler will either use the **ADD** (.unit) 0, *src2*, *dst* instruction (see ADD) or the **OR** (.unit) 0, *src2*, *dst* instruction (see OR) to perform this operation.

Execution

if (cond) else nop $0 + src2 \rightarrow dst$

Instruction Type

Single-cycle

Delay Slots 0



MVC Move Between Control File and Register File

Syntax MVC (.unit) src2, dst

unit = .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sx1	Figure F-31

Opcode

Operands when moving from the control file to the register file:

31	29	28	27	23	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	1	Z		dst	crlo		crhi		Х	0	0	1	1	1	1	1	0	0	0	1	р
3		1		5	5		5		1												1

Opcode map field used	For operand type	Unit
crlo	ucst5	.S2
dst	uint	
crhi	ucst5	

Description

The contents of the control file specified by the *crhi* and *crlo* fields is moved to the register file specified by the *dst* field. Valid assembler values for *crlo* and *crhi* are shown in Table 3-27.

Operands when moving from the register file to the control file:

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	crl	0	src2	crhi		Х	0	0	1	1	1	0	1	0	0	0	1	p
3	1	5		5	5		1												1

Opcode map field used	For operand type	Unit
src2	xuint	.S2
crlo	ucst5	
crhi	ucst5	

Description

The contents of the register file specified by the *src2* field is moved to the control file specified by the *crhi* and *crlo* fields. Valid assembler values for *crlo* and *crhi* are shown in Table 3-27.





Execution

if (cond) else nop

 $src2 \rightarrow dst$

NOTE: The MVC instruction executes only on the B side (.S2).

Refer to the individual control register descriptions for specific behaviors and restrictions in accesses via the **MVC** instruction.

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.S2

Instruction Type Single-cycle

Any write to the ISR or ICR (by the **MVC** instruction) effectively has one delay slot because the results cannot be read (by the **MVC** instruction) in the IFR until two cycles after the write to the ISR or ICR.

Delay Slots

Example MVC .S2 B1,AMR

	Before instruction		1 cycle after instruction	
B1	F009 0001h	B1	F009 0001h	
AMR	0000 0000h	AMR	0009 0001h	

NOTE: The six MSBs of the AMR are reserved and therefore are not written to.



Table 3-27. Register Addresses for Accessing the Control Registers

		Add	Iress	Supervisor	User
Acronym	Register Name	crhi	crlo	Read/Write (1)	Read/Write (1)
AMR	Addressing mode register	00000	00000	R, W	R, W
		0xxxx	00000		
CSR	Control status register	00000	00001	R, W*	R, W*
		00001	00001		
		0xxxx	00001		
DIER	Debug interrupt enable register	00000	11001	R, W	X
DNUM	DSP core number register	00000	10001	R	R
ECR	Exception clear register	00000	11101	W	X
EFR	Exception flag register	00000	11101	R	X
FADCR	Floating-point adder configuration register	00000	10010	R, W	R, W
FAUCR	Floating-point auxiliary configuration register	00000	10011	R, W	R, W
FMCR	Floating-point multiplier configuration register	00000	10100	R, W	R, W
GFPGFR	Galois field multiply control register	00000	11000	R, W	R, W
GPLYA	GMPY A-side polynomial register	00000	10110	R, W	R, W
GPLYB	GMPY B-side polynomial register	00000	10111	R, W	R, W
ICR	Interrupt clear register	00000	00011	W	X
		0xxxx	00011		
IER	Interrupt enable register	00000	00100	R, W	X
		0xxxx	00100		
IERR	Internal exception report register	00000	11111	R,W	X
IFR	Interrupt flag register	00000	00010	R	X
		00010	00010		
ILC	Inner loop count register	00000	01101	R, W	R, W
IRP	Interrupt return pointer register	00000	00110	R, W	R, W
		0xxxx	00110		
ISR	Interrupt set register	00000	00010	W	X
		0xxxx	00010		
ISTP	Interrupt service table pointer register	00000	00101	R, W	X
		0xxxx	00101		
ITSR	Interrupt task state register	00000	11011	R, W	X
NRP	Nonmaskable interrupt or exception return pointer	00000	00111	R, W	R, W
	register	0xxxx	00111		
NTSR	NMI/Exception task state register	00000	11100	R, W	X
PCE1	Program counter, E1 phase	00000	10000	R	R
		10000	10000		
REP	Restricted entry point address register	00000	01111	R, W	X
RILC	Reload inner loop count register	00000	01110	R, W	R, W
SSR	Saturation status register	00000	10101	R, W	R, W
TSCH	Time-stamp counter (high 32 bits) register	00000	01011	R	R
TSCL	Time-stamp counter (low 32 bits) register	00000	01010	R	R
TSR	Task state register	00000	11010	R, W*	R,W*

⁽¹⁾ R = Readable by the **MVC** instruction; W = Writeable by the **MVC** instruction; W* = Partially writeable by the **MVC** instruction; X = Access causes exception





MVD Move From Register to Register, Delayed

Syntax MVD (.unit) src2, dst

unit = .M1 or .M2

Opcode

31 2	9 28	3 27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2		1	1	0	1	0	х	0	0	0	0	1	1	1	1	0	0	s	p
3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	xint	.M1, .M2
dst	int	

Description

Moves data from the *src2* register to the *dst* register over 4 cycles. This is done using the multiplier path.

MVD .M2x A0, B0 ;
NOP ;
NOP ;
NOP ; B0 = A0

Execution

if (cond) $src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2			_
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

Example MVD .M2X A5,B8

	Before instruction	4 cycles after instruction
A5	6A32 1193h	A5 6A32 1193h
В8	xxxx xxxxh	B8 6A32 1193h



MVK Move Signed Constant Into Register and Sign Extend

Syntax MVK (.unit) cst, dst

unit = .L1, .L2, .S1, .S2, .D1, .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	Lx5	Figure D-8
.S	Smvk8	Figure F-24
.L, .S, .D	LSDx1c	Figure G-3
	LSDx1	Figure G-4

Opcode .S unit

31 29	28	27	23	22	7	6	5	4	3	2	1	0
creg	Z	dst			cst16	0	1	0	1	0	S	р
3	1	5			16						1	1

Opcode map field used	For operand type	Unit
cst16 dst	scst16 sint	.S1, .S2

Opcode .L unit

31 29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	C	lst	cst5		0	0	1	0	1	Х	0	0	1	1	0	1	0	1	1	0	s	р
3	1		5	5							1											1	1

Opcode map field used	For operand type	Unit
cst5	scst5	.L1, .L2
dst	sint	





Орсо	de			.D	unit																					
31	29	28	27		23	22	21	20	19	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
cr	eg	Z		dst		0	0	0	0	0		cst5		0	0	0	0	0	0	1	0	0	0	0	s	р
:	3	1		5								5													1	1

Opcode map field used	For operand type	Unit
cst5 dst	scst5 sint	.D1, .D2

Description

The constant *cst* is sign extended and placed in *dst*. The .S unit form allows for a 16-bit signed constant.

Since many nonaddress constants fall into a 5-bit sign constant range, this allows the flexibility to schedule the **MVK** instruction on the .L or .D units. In the .D unit form, the constant is in the position normally used by *src1*, as for address math.

In most cases, the C6000 assembler and linker issue a warning or an error when a constant is outside the range supported by the instruction. In the case of **MVK** .S, a warning is issued whenever the constant is outside the signed 16-bit range, -32768 to 32767 (or FFFF 8000h to 0000 7FFFh).

For example:

MVK .S1 0x00008000X, A0

will generate a warning; whereas:

MVK .S1 0xFFFF8000, A0

will not generate a warning.

Execution

if (cond) $scst \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single cycle

Delay Slots 0

else nop

See Also MVKH, MVKL, MVKLH



Examples

Example 1

MVK .L2 -5,B8

	Before instruction	1 c	cycle after instruction
B8	xxxx xxxxh	B8 FF	FF FFFBh

Example 2

MVK .D2 14,B8

	Before instruction		1 cycle after instruction	
B8	xxxx xxxxh	B8	0000 000Eh	
			·	



MVKH/MVKLH

Move 16-Bit Constant Into Upper Bits of Register

Syntax


MVKH (.unit) cst, dst

or

MVKLH (.unit) cst, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
cst16 dst	uscst16 sint	.S1, .S2

Description

The 16-bit constant, cst16, is loaded into the upper 16 bits of dst. The 16 LSBs of dst are unchanged. For the MVKH instruction, the assembler encodes the 16 MSBs of a 32-bit constant into the cst16 field of the opcode. For the MVKLH instruction, the assembler encodes the 16 LSBs of a constant into the cst16 field of the opcode.

NOTE: Use the MVK instruction (see MVK) to load 16-bit constants. The assembler generates a warning for any constant over 16 bits. To load 32-bit constants, such as 1234 5678h, use the following pair of instructions:

> MVKL 0x12345678 MVKH 0x12345678

If you are loading the address of a label, use:

MVKL label MVKH label

Execution

For the MVKLH instruction:

if (cond) else nop

$$((cst_{15..0}) << 16) \text{ or } (dst_{15..0}) \rightarrow dst$$

For the **MVKH** instruction:

if (cond) else nop

$$((cst_{31..16}) << 16) \text{ or } (dst_{15..0}) \rightarrow dst$$



Pipeline

Pipeline Stage	E1
Read	
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also MVK, MVKL

Example 1

MVKH .S1 0A329123h,A1

	Before instruction	1 cycle after instr	uction
A1	0000 7634h	A1 0A32 7634h	

Example 2

MVKLH .S1 7A8h,A1

	Before instruction	1 cycle after instruction	
A1	FFFF F25Ah	A1 07A8 F25Ah	






MVKL Move Signed Constant Into Register and Sign Extend

Syntax MVKL (.unit) cst, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
cst16	scst16	.S1, .S2
dst	sint	

Description

The 16-bit constant, cst16, is sign extended and placed in dst.

The MVKL instruction is equivalent to the MVK instruction (see MVK), except that the MVKL instruction disables the constant range checking normally performed by the assembler/linker. This allows the MVKL instruction to be paired with the MVKH instruction (see MVKH) to generate 32-bit constants.

To load 32-bit constants, such as 1234 ABCDh, use the following pair of instructions:

MVKL .S1 0x0ABCD, A4 MVKLH .S1 0x1234, A4

This could also be used:

MVKL .S1 0x1234ABCD, A4 MVKH .S1 0x1234ABCD, A4

Use this to load the address of a label:

MVKL .S2 label, B5 MVKH .S2 label, B5

Execution

if (cond) else nop $scst \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	
Written	dst
Unit in use	.S

Instruction Type Single cycle

Delay Slots 0

See Also MVK, MVKH, MVKLH



MVKL — Move Signed Constant Into Register and Sign Extend

www.ti.com

Examples

Example 1

MVKL .S1 5678h,A8

	Before instruction	1 cycle after instruction
A8	xxxx xxxxh	A8 0000 5678h

Example 2

MVKL .S1 0C678h,A8

	Before instruction		1 cycle after instruction					
A8	xxxx xxxxh	A8	FFFF C678h					
	·							



www.ti.com NEG — Negate

NEG Negate


Syntax NEG (.unit) src2, dst

or

NEG (.L1 or .L2) src2_h:src2_l, dst_h:dst_l

unit = .L1, .L2, .S1, .S2

Opcode .S unit



Opcode map field used	For operand type	Unit
src2	xsint	.S1, .S2
dst	sint	

Opcode .L unit

3	31 29	28	27	23	22	18	17	16	15	14	13	12	11	5 4	4	3	2	1	0
	creg	Z	dst		src2		0	0	0	0	0	Х	ор		1	1	0	s	p
	3	1	5		5							1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src2 dst	xsint sint	.L1, .L2	000 0110
src2 dst	slong slong	.L1, .L2	010 0100

Description The **NEG** pseudo-operation negates *src2* and places the result in *dst*. The assembler

uses the SUB (.unit) 0, src2, dst instruction to perform this operation (see SUB).

Execution

if (cond) $0 -s src2 \rightarrow dst$

else nop

Instruction Type Single-cycle

Delay Slots 0

See Also SUB



NOP — No Operation www.ti.com

NOP No Operation

Syntax NOP [count]

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Unop	Figure H-9

Opcode

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	0	0	0	0	0	0	0	0	0	0	0	0		src		0	0	0	0	0	0	0	0	0	0	0	0	р
																1														1

Opcode map field used	For operand type	Unit
src	ucst4	none

Description

src is encoded as count - 1. For src + 1 cycles, no operation is performed. The maximum value for count is 9. NOP with no operand is treated like NOP 1 with src encoded as 0000.

A multicycle **NOP** will not finish if a branch is completed first. For example, if a branch is initiated on cycle n and a **NOP 5** instruction is initiated on cycle n + 3, the branch is complete on cycle n + 6 and the **NOP** is executed only from cycle n + 3 to cycle n + 5. A single-cycle **NOP** in parallel with other instructions does not affect operation.

A multicycle **NOP** instruction cannot be paired with any other multicycle **NOP** instruction in the same execute packet. Instructions that generate a multicycle **NOP** are: **ADDKPC**, **BNOP**, **CALLP**, and **IDLE**.

Execution No operation for *count* cycles

Instruction Type NOP

Delay Slots 0

Examples Example 1

NOP

MVK .S1 125h,A1

 Before NOP
 1 cycle after NOP (No operation executes)
 1 cycle after MVK

 A1
 1234 5678h
 A1
 1234 5678h
 A1
 0000 0125h



www.ti.com NOP — No Operation

Example 2

MVK .S1 1,A1 MVKLH .S1 0,A1 NOP 5 ADD .L1 A1,A2,A1

	Before NOP 5		1 cycle after ADD instruction (6 cycles after NOP 5)	
A1	0000 0001h	A1	0000 0004h	
A2	0000 0003h	A2	0000 0003h	



NORM Normalize Integer

Syntax NORM (.unit) src2, dst

or

NORM (.unit) src2_h:src2_l, dst

unit = .L1 or .L2

Opcode

31 29	28	27 23		17	16	15	14	13	12	11	5	4	3	2	1	0
creg	Z	dst	src2	0	0	0	0	0	Х	ор		1	1	0	s	р
3	1	5	5						1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src2 dst	xsint uint	.L1, .L2	110 0011
src2 dst	slong uint	.L1, .L2	110 0000

Description The number of redundant sign bits of *src2* is placed in *dst*. Several examples are shown

in the following diagram.

In this case, NORM returns 0:

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	1	х	Х	Х	Х	Х	Х	Х	х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	х

In this case, **NORM** returns 3:

	30	-	_		_	_		_			-	_	_		_	_		_			-	-	_		-	-		-			-
0	0	0	0	1	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	х	х

In this case, **NORM** returns 30:

3	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	0

In this case, **NORM** returns 31:

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1





Execution

if (cond) $\operatorname{norm}(src) \to dst$ else nop

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

Example 1

NORM .L1 A1,A2

	Before instruction		1 cycle after instruction	
A1	02A3 469Fh	A1	02A3 469Fh	
A2	xxxx xxxxh	A2	0000 0005h	5

Example 2

NORM .L1 A1,A2

	Before instruction		1 cycle after instruction	
A1	FFFF F25Ah	A1	FFFF F25Ah	
A2	xxxx xxxxh	A2	0000 0013h] -

Example 3

NORM .L1 A1:A0,A3

	Before instruction		1 cycle after instruction
A0	0000 0007h	A0	0000 0007h
A1	0000 0000h	A1	0000 0000h
А3	xxxx xxxxh	A3	0000 0024h



NOT — Bitwise NOT www.ti.com

NOT Bitwise NOT

Syntax NOT(.unit) src2, dst

unit = .L1, .L2, .S1, .S2, .D1, .D2

Opcode .L unit

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	ds	st	src2		1	1	1	1	1	Х	1	1	0	1	1	1	0	1	1	0	S	р
3		1	5	5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.L1, .L2
dst	uint	

Opcode .S unit

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2		1	1	1	1	1	Х	0	0	1	0	1	0	1	0	0	0	s	р
	3	1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2 dst	xuint uint	.S1, .S2

Opcode .D unit

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	9	Z		dst	src2		1	1	1	1	1	Х	1	0	1	1	1	1	1	1	0	0	S	р
3		1		5	5							1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.D1, .D2
dst	uint	

Description

The **NOT** pseudo-operation performs a bitwise **NOT** on the *src2* operand and places the result in *dst*. The assembler uses the **XOR** (.unit) -1, *src2*, *dst* instruction to perform this operation (see XOR).



www.ti.com NOT — Bitwise NOT

Execution

if (cond) -1 XOR $src2 \rightarrow dst$

else nop

Instruction Type Single-cycle

Delay Slots 0

See Also XOR



OR — Bitwise OR www.ti.com

OR Bitwise OR

Syntax OR (.unit) src1, src2, dst

unit =.D1, .D2, .L1, .L2, .S1, .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7

Opcode .D unit

31	29	28	27	23	22 18	17		13	12	11	10	9	6	5	4	3	2	1	0
CI	eg	Z	(dst	src2		src1		Х	1	0	ор		1	1	0	0	S	р
	3	1		5	5		5		1			4						1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.D1, .D2	0010
src1 src2 dst	scst5 xuint uint	.D1, .D2	0011

Opcode .L unit

31 29	28	27 23	22 18	17 13	3 12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	Х	ор		1	1	0	s	р
3	1	5	5	5	1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	uint .	.L1, .L2	111 1111
src2 dst	xuint uint		
src1	scst5	.L1, .L2	111 1110
src2	xuint	.LI, .LZ	111 1110
dst	uint		



www.ti.com OR — Bitwise OR

Орс	ode			.S unit																
31	29	28	27	23	22		18	17		13	12	11		6	5	4	3	2	1	0
C	reg	Z		dst		src2			src1		Х		ор		1	0	0	0	s	р
	3	1		5		5			5		1		6						1	1

Opcode map field used	For operand type	Unit	Opfield		
src1 src2 dst	uint xuint uint	.S1, .S2	01 1011		
src1 src2 dst	scst5 xuint uint	.S1, .S2	01 1010		

Description

Performs a bitwise **OR** operation between *src1* and *src2*. The result is placed in *dst*. The *scst*5 operands are sign extended to 32 bits.

Execution

if (cond) $src1 ext{ OR } src2 o dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single-cycle

Delay Slots 0

See Also AND, ANDN, XOR

Example 1

OR .S1 A3,A4,A5

	Before instruction		1 cycle after instruction
А3	08A3 A49Fh	А3	08A3 A49Fh
A4	00FF 375Ah	A4	00FF 375Ah
A5	xxxx xxxxh	A5	08FF B7DFh



OR — Bitwise OR www.ti.com

Example 2

OR .D2 -12,B2,B8

	Before instruction	1 cycle after instruction
B2	0000 3A41h	B2 0000 3A41h
B8	xxxx xxxxh	B8 FFFF FFF5h



PACK2 Pack Two 16 LSBs Into Upper and Lower Register Halves

Syntax PACK2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31	29	28	27	23	22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z	(dst	src2			src1		Х	0	0	0	0	0	0	0	1	1	0	S	р
3		1		5	5			5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src1 src2	xi2	
dst	i2	

Opcode .S unit


31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2	src1		Х	1	1	1	1	1	1	1	1	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src2	xi2	
src1 src2 dst	i2	

Description

Moves the lower halfwords from src1 and src2 and packs them both into dst. The lower halfword of src1 is placed in the upper halfword of dst. The lower halfword of src2 is placed in the lower halfword of dst.

This instruction is useful for manipulating and preparing pairs of 16-bit values to be used by the packed arithmetic operations, such as **ADD2** (see ADD2).





Execution

```
if (cond)  \{ \\ lsb16(\textit{src2}) \rightarrow lsb16(\textit{dst}); \\ lsb16(\textit{src1}) \rightarrow msb16(\textit{dst}) \\ \}  else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also PACKH2, PACKHL2, PACKLH2, SPACK2

Examples Example 1

PACK2 .L1 A2,A8,A9

	Before instruction		1 cycle after instruction
A2	3789 F23Ah	A2	3789 F23Ah
A8	04B8 4975h	A8	04B8 4975h
A9	xxxx xxxxh	A9	F23A 4975h

Example 2

PACK2 .S2 B2,B8,B12

	Before instruction		1 cycle after instruction								
B2	0124 2451h	B2	0124 2451h								
B8	01A6 A051h	B8	01A6 A051h								
B12	xxxx xxxxh	B12	2451 A051h								





PACKH2 Pack Two 16 MSBs Into Upper and Lower Register Halves

Syntax PACKH2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	0	0	1	1	1	1	0	1	1	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src1 src2	xi2	
dst	i2	

Opcode .S unit


3	1 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2	src1		Х	0	0	1	0	0	1	1	0	0	0	s	р
	3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src1 src2	xi2	
dst	i2	

Description

Moves the upper halfwords from src1 and src2 and packs them both into dst. The upper halfword of src1 is placed in the upper half-word of dst. The upper halfword of src2 is placed in the lower halfword of dst.

This instruction is useful for manipulating and preparing pairs of 16-bit values to be used by the packed arithmetic operations, such as **ADD2** (see ADD2).





Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also PACK2, PACKHL2, PACKLH2, SPACK2

Examples Example 1

PACKH2 .L1 A2,A8,A9

	Before instruction		1 cycle after instruction
A2	3789 F23Ah	A2	3789 F23Ah
A8	04B8 4975h	A8	04B8 4975h
A9	xxxx xxxxh	A9	3789 04B8h

Example 2

PACKH2 .S2 B2,B8,B12

	Before instruction		1 cycle after instruction	
B2	0124 2451h	B2	0124 2451h	
B8	01A6 A051h	B8	01A6 A051h	
B12	xxxx xxxxh	B12	0124 01A6h	



PACKH4

Pack Four High Bytes Into Four 8-Bit Halfwords

Syntax

```
PACKH4 (.unit) src1, src2, dst
```

unit = .L1 or .L2

Opcode

31 29	28	27	23		8 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		src1		Х	1	1	0	1	0	0	1	1	1	0	s	p
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	i4	.L1, .L2
src1 src2 dst	xi4	
dst	i4	

Description

Moves the high bytes of the two halfwords in *src1* and *src2*, and packs them into *dst*. The bytes from *src1* are packed into the most-significant bytes of *dst*, and the bytes from *src2* are packed into the least-significant bytes of *dst*.

- The high byte of the upper halfword of *src1* is moved to the upper byte of the upper halfword of *dst*. The high byte of the lower halfword of *src1* is moved to the lower byte of the upper halfword of *dst*.
- The high byte of the upper halfword of src2 is moved to the upper byte of the lower halfword of dst. The high byte of the lower halfword of src2 is moved to the lower byte of the lower halfword of dst.

31	24	23	16 15		8 7		0
á	a_3	a_2		a_1		a_0	← src1
			PACKH4				
k	o_3	b_2		b_1		b_0	← src2
			\downarrow				
31	24	23	16 15		8 7		0
a	a_3	a_1		b_3		b_1	← dst

Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also PACKL4, SPACKU4

Example 1

PACKH4 .L1 A2,A8,A9

	Before instruction		1 cycle after instruction
A2	37 89 F2 3Ah	A2	37 89 F2 3Ah
A8	04 B8 49 75h	A8	04 B8 49 75h
A9	xxxx xxxxh	А9	37 F2 04 49h

Example 2

PACKH4 .L2 B2,B8,B12

	Before instruction		1 cycle after instruction	
B2	01 24 24 51h	B2	01 24 24 51h	
B8	01 A6 A0 51h	B8	01 A6 A0 51h	
B12	xxxx xxxxh	B12	01 24 01 A0h	





PACKHL2 Pack 16 MSB Into Upper and 16 LSB Into Lower Register Halves

Syntax PACKHL2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
CI	eg	Z	C	dst	src2	src1		Х	0	0	1	1	1	0	0	1	1	0	s	р
	3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src1 src2	xi2	
dst	i2	

Opcode .S unit


3	31 29	28	27 23		17 1:	3 1	12 1	11 10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst	src2	src1		Х	0 0	1	0	0	0	1	0	0	0	s	р
	3	1	5	5	5		1										1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src1 src2	xi2	
dst	i2	

Description

Moves the upper halfword from *src1* and the lower halfword from *src2* and packs them both into *dst*. The upper halfword of *src1* is placed in the upper halfword of *dst*. The lower halfword of *src2* is placed in the lower halfword of *dst*.

This instruction is useful for manipulating and preparing pairs of 16-bit values to be used by the packed arithmetic operations, such as **ADD2** (see ADD2).





Execution

```
if (cond)  \{ \\ lsb16(\textit{src2}) \rightarrow lsb16(\textit{dst}); \\ msb16(\textit{src1}) \rightarrow msb16(\textit{dst}) \\ \}  else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also PACK2, PACKH2, PACKLH2, SPACK2

Examples Example 1

PACKHL2 .L1 A2,A8,A9

	Before instruction		1 cycle after instruction
A2	3789 F23Ah	A2	3789 F23Ah
A8	04B8 4975h	A8	04B8 4975h
A9	xxxx xxxxh	A9	3789 4975h

Example 2

PACKHL2 .S2 B2, B8, B12

	Before instruction		1 cycle after instruction						
B2	0124 2451h	B2	0124 2451h						
B8	01A6 A051h	B8	01A6 A051h						
B12	xxxx xxxxh	B12	0124 A051h						





PACKLH2 Pack 16 LSB Into Upper and 16 MSB Into Lower Register Halves

Syntax PACKLH2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 29	28	27	23 22	18 17	13 12	11 1	10 9	8	7 6	5 4	3 2	1	0
creg	Z	dst	src2	src1	х	0	0 1	1	0 1	1 1	1 0	s	р
3	1	5	5	5	1							1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src1 src2	xi2	
dst	i2	

Opcode .S unit


31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	dst		src2	src1		Х	0	1	0	0	0	0	1	0	0	0	s	р
3		1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src2	xi2	
src1 src2 dst	i2	

Description

Moves the lower halfword from *src1*, and the upper halfword from *src2*, and packs them both into *dst*. The lower halfword of *src1* is placed in the upper halfword of *dst*. The upper halfword of *src2* is placed in the lower halfword of *dst*.

This instruction is useful for manipulating and preparing pairs of 16-bit values to be used by the packed arithmetic operations, such as **ADD2** (see ADD2).





Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also PACK2, PACKH2, PACKHL2, SPACK2

Examples Example 1

PACKLH2 .L1 A2,A8,A9

	Before instruction	1 cycle after instruction
A2	3789 F23Ah	A2 3789 F23Ah
A8	04B8 4975h	A8 04B8 4975h
A9	xxxx xxxxh	A9 F23A 04B8h

Example 2

PACKLH2 .S2 B2, B8, B12

	Before instruction	1 cycle after instruction
B2	0124 2451h	B2 0124 2451h
B8	01A6 A051h	B8 01A6 A051h
B12	xxxx xxxxh	B12 2451 01A6h



PACKL4

Pack Four Low Bytes Into Four 8-Bit Halfwords

Syntax

PACKL4 (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	0	1	0	0	0	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i4	.L1, .L2
src2	xi4	
src1 src2 dst	i4	

Description

Moves the low bytes of the two halfwords in *src1* and *src2*, and packs them into *dst*. The bytes from *src1* are packed into the most-significant bytes of *dst*, and the bytes from *src2* are packed into the least-significant bytes of *dst*.

- The low byte of the upper halfword of *src1* is moved to the upper byte of the upper halfword of *dst*. The low byte of the lower halfword of *src1* is moved to the lower byte of the upper halfword of *dst*.
- The low byte of the upper halfword of src2 is moved to the upper byte of the lower halfword of dst. The low byte of the lower halfword of src2 is moved to the lower byte of the lower halfword of dst.

31	24	23	16 15		8 7		0
á	a_3	a_2		a_1		a_0	← src1
			PACKL	4			
k	o_3	b_2		b_1		b_0	← src2
			\downarrow				
31	24	23	16 15		8 7		0
a	a_2	a_0		b_2		b_0	← dst

Execution



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also PACKH4, SPACKU4

Examples Example 1

PACKL4 .L1 A2,A8,A9

	Before instruction	1 cycle after instruction
A2	37 89 F2 3Ah	A2 37 89 F2 3Ah
A8	04 B8 49 75h	A8 04 B8 49 75h
A9	xxxx xxxxh	A9 89 3A B8 75h

Example 2

PACKL4 .L2 B2,B8,B12

	Before instruction		1 cycle after instruction
B2	01 24 24 51h	B2	01 24 24 51h
B8	01 A6 A0 51h	B8	01 A6 A0 51h
B12	xxxx xxxxh	B12	24 51 A6 51h



RCPDP


Double-Precision Floating-Point Reciprocal Approximation

Syntax

RCPDP (.unit) src2, dst

unit = .S1, .S2

Opcode



Opcode map field used	For operand type	Unit
src2	dp	.S1, .S2
dst	dp	

Description

The 64-bit double-precision floating-point reciprocal approximation value of *src2* is placed in *dst*. The operand is read in one cycle by using the *src1* port for the 32 LSBs and the *src2* port for the 32 MSBs.

The **RCPDP** instruction provides the correct exponent, and the mantissa is accurate to the eighth binary position (therefore, mantissa error is less than 2⁻⁸). This estimate can be used as a seed value for an algorithm to compute the reciprocal to greater accuracy.

The Newton-Rhapson algorithm can further extend the mantissa's precision:

$$x[n + 1] = x[n](2 - v \times x[n])$$

where v = the number whose reciprocal is to be found.

x[0], the seed value for the algorithm, is given by **RCPDP**. For each iteration, the accuracy doubles. Thus, with one iteration, accuracy is 16 bits in the mantissa; with the second iteration, the accuracy is 32 bits; with the third iteration, the accuracy is the full 52 bits.

NOTE:

- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- 3. If *src2* is a signed denormalized number, signed infinity is placed in *dst*and the DIV0, INFO, OVER, INEX, and DEN2 bits are set.
- If src2 is signed 0, signed infinity is placed in dst and the DIV0 and INFO bits are set.
- 5. If src2 is signed infinity, signed 0 is placed in dst.
- 6. If the result underflows, signed 0 is placed in dst and the INEX and UNDER bits are set. Underflow occurs when $2^{1022} < src2 <$ infinity.

Execution

if (cond) else nop

 $rcp(src2) \rightarrow dst$



Pipeline

Pipeline Stage	E1	E2
Read	src2_l, src2_h	
Written	dst_l	dst_h
Unit in use	.S	

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type Two-cycle DP

Delay Slots 1

Functional Unit Latency 1

See Also RCPSP, RSQRDP

Example RCPDP .S1 A1:A0,A3:A2

	Before instruction			2 cycles after instruction							
A1:A0	4010 0000h	0000 0000h	A1:A0	4010 0000h	0000 0000h	4.00					
A3:A2	xxxx xxxxh	xxxx xxxxh	A3:A2	3FD0 0000h	0000 0000h	0.25					



RCPSP


Single-Precision Floating-Point Reciprocal Approximation

Syntax

RCPSP (.unit) src2, dst

unit = .S1, .S2

Opcode



Opcode map field used	For operand type	Unit
src2	xsp	.S1, .S2
dst	sp	

Description

The single-precision floating-point reciprocal approximation value of src2 is placed in dst.

The **RCPSP** instruction provides the correct exponent, and the mantissa is accurate to the eighth binary position (therefore, mantissa error is less than 2⁻⁸). This estimate can be used as a seed value for an algorithm to compute the reciprocal to greater accuracy.

The Newton-Rhapson algorithm can further extend the mantissa's precision:

$$x[n + 1] = x[n](2 - v \times x[n])$$

where v = the number whose reciprocal is to be found.

x[0], the seed value for the algorithm, is given by **RCPSP**. For each iteration, the accuracy doubles. Thus, with one iteration, accuracy is 16 bits in the mantissa; with the second iteration, the accuracy is the full 23 bits.

NOTE:

- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- 3. If *src2* is a signed denormalized number, signed infinity is placed in *dst*and the DIV0, INFO, OVER, INEX, and DEN2 bits are set.
- 4. If *src2* is signed 0, signed infinity is placed in *dst* and the DIV0 and INFO bits are set.
- 5. If src2 is signed infinity, signed 0 is placed in dst.
- If the result underflows, signed 0 is placed in dst and the INEX and UNDER bits are set. Underflow occurs when 2¹²⁶ < src2 < infinity.

Execution

if (cond) else nop $rcp(src2) \rightarrow dst$



Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

Functional Unit Latency 1

See Also RCPDP, RSQRSP

Example RCPSP .S1 A1,A2

	Before instruction	1 cycle after instruction							
A1	4080 0000h	A1	4080 0000h	4.00					
A2	xxxx xxxxh	A2	3E80 0000h	0.25					





RINT Restore Previous Enable State

RINT Syntax

unit = none

Opcode

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	0	0	0	0	0	0	0	0	0	0	0	0	р

Description

Copies the contents of the SGIE bit in TSR into the GIE bit in TSR and CSR, and clears the SGIE bit in TSR. The value of the SGIE bit in TSR is used for the current cycle as the GIE indication; if restoring the GIE bit to 1, interrupts are enabled and can be taken after the E1 phase containing the RINT instruction.

The CPU may service a maskable interrupt in the cycle immediately following the RINT instruction. See section 5.2 for details.

The RINT instruction cannot be placed in parallel with: MVC reg, TSR; MVC reg, CSR; B IRP; B NRP; NOP n; DINT; SPKERNEL; SPKERNELR; SPLOOP; SPLOOPD; SPLOOPW; SPMASK; or SPMASKR.

This instruction executes unconditionally and cannot be predicated.

NOTE: The use of the DINT and RINT instructions in a nested manner, like the following code:

DINT

DINT

RINT RINT

leaves interrupts disabled. The first DINT leaves TSR.GIE cleared to 0, so the second DINT leaves TSR,.SGIE cleared to 0. The RINT instructions, therefore, copy zero to TSR.GIE (leaving interrupts disabled).

Execution

Enable interrupts in current cycle

SGIE bit in TSR \rightarrow GIE bit in TSR SGIE bit in TSR → GIE bit in CSR

 $0 \rightarrow \text{SGIE}$ bit in TSR

Instruction Type Single-cycle

Delay Slots

See Also DINT



ROTL — Rotate Left www.ti.com

ROTL Rotate Left

Syntax ROTL (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode


31 29	28	27	23	22 18		13 12	2 11	10 6	3	5 4	4	3	2	1	0
creg	Z	dst		src2	src1	х		ор		1	1	0	0	s	р
3	1	5		5	5	1		5						1	1

Opcode map field used	For operand type	Unit	Opfield
src1	uint	.M1, .M2	11101
src2	xuint	·	
dst	uint		
src1	ucst5	.M1, .M2	11110
src2	xuint	·	
dst	uint		

Description

Rotates the 32-bit value of *src2* to the left, and places the result in *dst*. The number of bits to rotate is given in the 5 least-significant bits of *src1*. Bits 5 through 31 of *src1* are ignored and may be non-zero.

In the following figure, src1 is equal to 8.



NOTE: The **ROTL** instruction is useful in cryptographic applications.

Execution

if (cond)
$$(src2 \ll src1) \mid (src2 \gg (32 - src1)) \rightarrow dst$$
 else nop



www.ti.com ROTL — Rotate Left

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	_
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also SHL, SHLMB, SHRMB, SHR, SHRU

Example 1

ROTL .M2 B2,B4,B5

	Before instruction		2 cycles after instruction
B2	A6E2 C179h	B2	A6E2 C179h
B4	1458 3B69h	В4	1458 3B69h
B5	xxxx xxxxh	B5	C582 F34Dh

Example 2

ROTL .M1 A4,10h,A5

	Before instruction		2 cycles after instruction					
A4	187A 65FCh	A4	187A 65FCh					
A5	xxxx xxxxh	A5	65FC 187Ah					



RPACK2 Shift With Saturation and Pack Two 16 MSBs Into Upper and Lower Register

Halves

Syntax RPACK2 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31	30	29	28	27 23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	1	1	1	0	1	1	1	1	0	0	s	p
				5	5	5		1											1	1


Opcode map field used	For operand type	Unit
src1	sint	.S1, .S2
src2	xsint	
dst	s2	

Description

src1 and *src2* are shifted left by 1 with saturation. The 16 most-significant bits of the shifted *src1* value are placed in the 16 most-significant bits of *dst*. The 16 most-significant bits of the shifted *src2* value are placed in the 16 least-significant bits of *dst*.

If either value saturates, the S1 or S2 bit in SSR and the SAT bit in CSR are written one cycle after the result is written to *dst*.

This instruction executes unconditionally and cannot be predicated.



Execution

 $\begin{tabular}{ll} msb16(sat(src1 << 1)) \to msb16(dst) \\ msb16(sat(src2 << 1)) \to lsb16(dst) \\ \end{tabular}$

Instruction Type Single-cycle

Delay Slots 0

See Also PACK2, PACKH2, SPACK2



www.ti.com RPACK2 — Shift With Saturation and Pack Two 16 MSBs Into Upper and Lower Register Halves

Example 1

RPACK2 .S1 A0,A1,A2

	Before instruction	1 cycle after ins	struction
A0	FEDC BA98h	A2 FDBA 2468h	
A1	1234 5678h		
CSR	0001 0100h	CSR ⁽¹⁾ 0001 0100h	
SSR	0000 0000h	SSR ⁽¹⁾ 0000 0000h	

⁽¹⁾ CSR.SAT and SSR.S1 unchanged by operation

Example 2

RPACK2 .S2X B0,A1,B2

	Before instruction		1 cycle after instruction
В0	8765 4321h	B2	8000 2468h
A1	1234 5678h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0008h

⁽¹⁾ CSR.SAT and SSR.S2 set to 1, 2 cycles after instruction



RSQRDP

Double-Precision Floating-Point Square-Root Reciprocal Approximation

Syntax

RSQRDP (.unit) src2, dst

unit = .S1, .S2

Opcode

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	dst		src2		0	0	0	0	0	Х	1	0	1	1	1	0	1	0	0	0	s	p
3		1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	dp	.S1, .S2
dst	dp	

Description

The 64-bit double-precision floating-point square-root reciprocal approximation value of *src2* is placed in *dst*. The operand is read in one cycle by using the *src1* port for the 32 LSBs and the *src2* port for the 32 MSBs.

The **RSQRDP** instruction provides the correct exponent, and the mantissa is accurate to the eighth binary position (therefore, mantissa error is less than 2⁻⁸). This estimate can be used as a seed value for an algorithm to compute the reciprocal square root to greater accuracy.

The Newton-Rhapson algorithm can further extend the mantissa's precision:

$$x[n + 1] = x[n](1.5 - (v/2) \times x[n] \times x[n])$$

where v = the number whose reciprocal square root is to be found.

x[0], the seed value for the algorithm is given by **RSQRDP**. For each iteration the accuracy doubles. Thus, with one iteration, the accuracy is 16 bits in the mantissa; with the second iteration, the accuracy is 32 bits; with the third iteration, the accuracy is the full 52 bits.

NOTE:

- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- If src2 is a negative, nonzero, nondenormalized number, NaN_out is placed in dst and the INVAL bit is set.
- 4. If *src2* is a signed denormalized number, signed infinity is placed in *dst* and the DIV0, INEX, and DEN2 bits are set.
- If src2 is signed 0, signed infinity is placed in dst and the DIV0 and INFO bits are set. The Newton-Rhapson approximation cannot be used to calculate the square root of 0 because infinity multiplied by 0 is invalid.
- 6. If src2 is positive infinity, positive 0 is placed in dst.



Execution

if (cond) $sqrcp(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2
Read	src2_l, src2_h	
Written	dst_l	dst_h
Unit in use	.S	

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type Two-cycle DP

Delay Slots 1

Functional Unit Latency 1

See Also RCPDP, RSQRSP

Example RSQRDP .S1 A1:A0,A3:A2

	Before instruction			2 cycles after instruct		
A1:A0	4010 0000h	0000 0000h	A1:A0	4010 0000h	0000 0000h	4.0
A3:A2	xxxx xxxxh	xxxx xxxxh	A3:A2	3FE0 0000h	0000 0000h	0.5



RSQRSP

Single-Precision Floating-Point Square-Root Reciprocal Approximation

Syntax

RSQRSP (.unit) src2, dst

unit = .S1, .S2

Opcode

31 29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		0	0	0	0	0	Х	1	1	1	1	1	0	1	0	0	0	s	p
3	1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xsp	.S1, .S2
dst	sp	

Description

The single-precision floating-point square-root reciprocal approximation value of *src2* is placed in *dst*.

The **RSQRSP** instruction provides the correct exponent, and the mantissa is accurate to the eighth binary position (therefore, mantissa error is less than 2⁻⁸). This estimate can be used as a seed value for an algorithm to compute the reciprocal square root to greater accuracy.

The Newton-Rhapson algorithm can further extend the mantissa's precision:

$$x[n + 1] = x[n](1.5 - (v/2) \times x[n] \times x[n])$$

where v = the number whose reciprocal square root is to be found.

x[0], the seed value for the algorithm, is given by **RSQRSP**. For each iteration, the accuracy doubles. Thus, with one iteration, accuracy is 16 bits in the mantissa; with the second iteration, the accuracy is the full 23 bits.

NOTE:

- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- 3. If *src2* is a negative, nonzero, nondenormalized number, NaN_out is placed in *dst* and the INVAL bit is set.
- 4. If *src2* is a signed denormalized number, signed infinity is placed in *dst* and the DIV0, INEX, and DEN2 bits are set.
- If src2 is signed 0, signed infinity is placed in dst and the DIV0 and INFO bits are set. The Newton-Rhapson approximation cannot be used to calculate the square root of 0 because infinity multiplied by 0 is invalid.
- 6. If src2 is positive infinity, positive 0 is placed in dst.

Execution

if (cond) else nop $sqrcp(src2) \rightarrow dst$

420 Instruction Set SPRUFE8B-July 2010





Pipeline

Pipeline Stage	E 1
Read	src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

Functional Unit Latency 1

See Also RCPSP, RSQRDP

Example 1

RSQRSP .S1 A1,A2

	Before instruction	1 cycle after instruction	
A1	4080 0000h	A1 4080 0000h	4.0
A2	xxxx xxxxh	A2 3F00 0000h	0.5

Example 2

RSQRSP .S2X A1,B2

	Before instruction		1 cycle after instruction	
A1	4109 999Ah	A1	4109 999Ah	8.6
B2	xxxx xxxxh	B2	3EAE 8000h	0.34082031



SADD Add Two Signed Integers With Saturation

Syntax SADD (.unit) src1, src2, dst

or

SADD (.L1 or .L2) src1, src2_h:src2_l, dst_h:dst_l

unit = .L1, .L2, .S1, .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L3	Figure D-4
.S	S 3	Figure F-22

Opcode .L unit

31 29	28	27	23	22 18	17	13 12	11	5 4	3	2	1	0
creg	Z	dst		src2	src1	х	ор	1	1	0	s	p
3	1	5		5	5	1	7				1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	001 0011
src2	xsint		
dst	sint		
src1	xsint	.L1, .L2	011 0001
src2	slong		
dst	slong		
src1	scst5	.L1, .L2	001 0010
src2	xsint	·	
dst	sint		
src1	scst5	.L1, .L2	011 0000
src2	slong	,	
dst	slong		

Opcode .S unit

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	ds	st	src2	S	rc1	Х	1	0	0	0	0	0	1	0	0	0	S	р
	3	1	5		5		5	1											1	1

Opcode map field used	For operand type	Unit
src1 src2	sint xsint	.S1, .S2
dst	sint	





Description

src1 is added to src2 and saturated, if an overflow occurs according to the following rules:

- 1. If the dst is an int and $src1 + src2 > 2^{31} 1$, then the result is $2^{31} 1$.
- 2. If the dst is an int and $src1 + src2 < -2^{31}$, then the result is -2^{31} .
- 3. If the dst is a long and $src1 + src2 > 2^{39} 1$, then the result is $2^{39} 1$.
- 4. If the dst is a long and $src1 + src2 < -2^{39}$, then the result is -2^{39} .

The result is placed in *dst*. If a saturate occurs, the SAT bit in the control status register (CSR) is set one cycle after *dst* is written.

Execution

if (cond) else nop

 $src1 + s src2 \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also ADD

Example 1

SADD .L1 A1,A2,A3

	Before instruction			1 cycle after instru	ction
A1	5A2E 51A3h	1,512,984,995	A1	5A2E 51A3h	
A2	012A 3FA2h	19,546,018	A2	012A 3FA2h	
A3	xxxx xxxxh		A3	5B58 9145h	1,532,531,013
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				2 cycles after instr	uction
			A1	5A2E 51A3h	
			A2	012A 3FA2h	
			A3	5B58 9145h	
			CSR	0001 0100h	Not saturated
			SSR	0000 0000h	



Example 2

SADD .L1 A1,A2,A3

	Before instruction			1 cycle after instruction	
A1	4367 71F2h	1,130,852,850	A1	4367 71F2h	
A2	5A2E 51A3h	1,512,984,995	A2	5A2E 51A3h	
А3	xxxx xxxxh		A3	7FFF FFFFh	2,147,483,647
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				2 cycles after instructio	n
			A1	4367 71F2h	
			A2	5A2E 51A3h	
			А3	7FFF FFFFh	
			CSR	0001 0300h	Saturated
			SSR	0000 0001h	

Example 3

SADD .L1X B2,A5:A4,A7:A6

	Before instruction			1 cycle after instru	uction
A5:A4	0000 0000h	7C83 39B1h	A5:A4	0000 0000h	7C83 39B1h
	2,088,974,769(1)	1			'
A7:A6	xxxx xxxxh	xxxx xxxxh	A7:A6	0000 0000h	8DAD 7953h
	,			2,376,956,243(1)	
B2	112A 3FA2h	287,981,474	B2	112A 3FA2h	
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				2 cycles after inst	ruction
			A5:A4	0000 0000h	7C83 39B1h
			A7:A6	0000 0000h	8DAD 7953h
			B2	112A 3FA2h	
			CSR	0001 0100h	Not saturated
			SSR	0000 0000h	

⁽¹⁾ Signed 40-bit (long) integer

www.ti.com SADD2 — Add Two Signed 16-Bit Integers on Upper and Lower Register Halves With Saturation


SADD2 Add Two Signed 16-Bit Integers on Upper and Lower Register Halves With

Saturation

Syntax SADD2 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	s2	


Description

Performs 2s-complement addition between signed, packed 16-bit quantities in *src1* and *src2*. The results are placed in a signed, packed 16-bit format into *dst*.

For each pair of 16-bit quantities in *src1* and *src2*, the sum between the signed 16-bit value from *src1* and the signed 16-bit value from *src2* is calculated and saturated to produce a signed 16-bit result. The result is placed in the corresponding position in *dst*.

Saturation is performed on each 16-bit result independently. For each sum, the following tests are applied:

- If the sum is in the range 2¹⁵ to 2 ¹⁵ 1, inclusive, then no saturation is performed and the sum is left unchanged.
- If the sum is greater than 2¹⁵ 1, then the result is set to 2¹⁵ 1.
- If the sum is less than 2¹⁵, then the result is set to 2¹⁵.



NOTE: This operation is performed on each halfword separately. This instruction does not affect the SAT bit in CSR.



Execution

```
if (cond)  \{ \\ sat(msb16(\textit{src1}) + msb16(\textit{src2})) \rightarrow msb16(\textit{dst}); \\ sat(lsb16(\textit{src1}) + lsb16(\textit{src2})) \rightarrow lsb16(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also ADD2, SADD, SADDUS2, SADDU4, SUB2

Examples Example 1

SADD2 .S1 A2,A8,A9

	Before instruction			1 cycle after instruction							
A2	5789 F23Ah	22409 -3526	A2	5789 F23Ah							
A8	74B8 4975h	29880 18805	A8	74B8 4975h							
A9	xxxx xxxxh		A9	7FFF 3BAFh	32767 15279						

Example 2

SADD2 .S2 B2,B8,B12

	Before instruction			1 cycle after instruction	
B2	0124 847Ch	292 -31260	B2	0124 847Ch	
B8	01A6 A051h	422 -24495	B8	01A6 A051h	
B12	xxxx xxxxh		B12	02CA 8000h	714 -32768




SADDSUB Parallel SADD and SSUB Operations On Common Inputs

Syntax SADDSUB (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	

Description

The following is performed in parallel:

- 1. src2 is added with saturation to src1. The result is placed in dst_o.
- 2. src2 is subtracted with saturation from src1. The result is placed in dst_e.

If either result saturates, the L1 or L2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to $dst_o:dst_e$.

This instruction executes unconditionally and cannot be predicated.

Execution

$$sat(src1 + src2) \rightarrow dst_o$$

 $sat(src1 - src2) \rightarrow dst_e$

Instruction Type Single-cycle

Delay Slots 0

See Also ADDSUB, SADDSUB2

Examples Example 1

SADDSUB .L1 A0,A1,A3:A2

	Before instruction	1 cycle after instruction					
A0	0700 C005h	A2	0700 C006h				
A1	FFFF FFFFh	A3	0700 C004h				
CSR	0001 0100h	CSR ⁽¹⁾	0001 0100h				
SSR	0000 0000h	SSR ⁽¹⁾	0000 0000h				

⁽¹⁾ CSR.SAT and SSR.L1 unchanged by operation



Example 2

SADDSUB .L2X B0,A1,B3:B2

	Before instruction		1 cycle after instruction
В0	7FFF FFFFh	B2	7FFF FFFEh
A1	0000 0001h	B3	7FFF FFFFh
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0002h

⁽¹⁾ CSR.SAT and SSR.L2 set to 1, 2 cycles after instruction

Example 3

SADDSUB .L1X A0,B1,A3:A2

	Before instruction		1 cycle after instruction
A0	8000 0000h	A2	8000 0000h
B1	0000 0001h	A3	8000 0001h
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0001h

⁽¹⁾ CSR.SAT and SSR.L1 set to 1, 2 cycles after instruction



SADDSUB2

Parallel SADD2 and SSUB2 Operations On Common Inputs

Syntax

SADDSUB2 (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode

31	30	29	28	27	24	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst		0	src2	src1		Х	0	0	0	1	1	1	1	1	1	0	s	р
				4			5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	

Description

A **SADD2** and a **SSUB2** operation are done in parallel.

For the SADD2 operation, the upper and lower halves of the src2 operand are added with saturation to the upper and lower halves of the src1 operand. The values in src1 and src2 are treated as signed, packed 16-bit data and the results are written in signed, packed 16-bit format into dst_o.

For the **SSUB2** operation, the upper and lower halves of the *src2* operand are subtracted with saturation from the upper and lower halves of the src1 operand. The values in src1 and src2 are treated as signed, packed 16-bit data and the results are written in signed, packed 16-bit format into dst_e.

This instruction executes unconditionally and cannot be predicated.

NOTE: These operations are performed separately on each halfword. This instruction does not affect the SAT bit in CSR or the L1 or L2 bits in SSR.

Execution

 $sat(lsb16(src1) + lsb16(src2)) \rightarrow lsb16(dst_o)$ $sat(msb16(src1) + msb16(src2)) \rightarrow msb16(dst_o)$ $sat(lsb16(src1) - lsb16(src2)) \rightarrow lsb16(dst_e)$ $sat(msb16(src1) - msb16(src2)) \rightarrow msb16(dst_e)$

Instruction Type Single-cycle

Delay Slots

See Also ADDSUB2, SADDSUB

SADDSUB2 — Parallel SADD2 and SSUB2 Operations On Common Inputs

www.ti.com

Example 1

SADDSUB2 .L1 A0,A1,A3:A2

	Before instruction		1 cycle after instruction
A0	0700 C005h	A2	0701 C004h
A1	FFFF 0001h	А3	06FF C006h
CSR	0001 0100h	CSR ⁽¹⁾	0001 0100h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0000h

⁽¹⁾ CSR.SAT and SSR.L1 unchanged by operation

Example 2

SADDSUB2 .L2X B0,A1,B3:B2

	Before instruction		1 cycle after instruction
В0	7FFF 8000h	B2	7FFF 8001h
A1	FFFF FFFFh	ВЗ	7FFE 8000h
CSR	0001 0100h	CSR ⁽¹⁾	0001 0100h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0000h

⁽¹⁾ CSR.SAT and SSR.L2 unchanged by operation



SADDSU2

Add Two Signed and Unsigned 16-Bit Integers on Register Halves With Saturation

Syntax

```
SADDSU2 (.unit) src2, src1, dst
```

unit =
$$.S1$$
 or $.S2$

Opcode

31 29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2		src1		Х	1	1	0	0	0	1	1	1	0	0	s	р
3	1	5	5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	u2	.S1, .S2
src2	xs2	
dst	u2	

Description

The **SADDSU2** pseudo-operation performs 2s-complement addition between unsigned and signed packed 16-bit quantities. The values in *src1* are treated as unsigned packed 16-bit quantities, and the values in *src2* are treated as signed packed 16-bit quantities. The results are placed in an unsigned packed 16-bit format into *dst*. The assembler uses the **SADDUS2** (.unit) *src1*, *src2*, *dst* instruction to perform this operation (see SADDUS2).

For each pair of 16-bit quantities in *src1* and *src2*, the sum between the unsigned 16-bit value from *src1* and the signed 16-bit value from *src2* is calculated and saturated to produce a signed 16-bit result. The result is placed in the corresponding position in *dst*.

Saturation is performed on each 16-bit result independently. For each sum, the following tests are applied:

- If the sum is in the range 0 to 2¹⁶ 1, inclusive, then no saturation is performed and the sum is left unchanged.
- If the sum is greater than 2¹⁶ 1, then the result is set to 2¹⁶ 1.
- If the sum is less than 0, then the result is cleared to 0.

Execution

```
if (cond)  \{ \\ sat(smsb16(src2) + umsb16(src1)) \rightarrow umsb16(dst); \\ sat(slsb16(src2) + ulsb16(src1)) \rightarrow ulsb16(dst); \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S



SADDSU2 — Add Two Signed and Unsigned 16-Bit Integers on Register Halves With Saturation

www.ti.com

Instruction Type Single-cycle

Delay Slots 0

See Also SADD, SADD2, SADDUS2, SADDU4



SADDUS2

Add Two Unsigned and Signed 16-Bit Integers on Register Halves With Saturation

Syntax

SADDUS2 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	a	lst	src2	sro	:1	Х	1	1	0	0	0	1	1	1	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u2	.S1, .S2
src1 src2 dst	xs2	
dst	u2	


Description

Performs 2s-complement addition between unsigned and signed, packed 16-bit quantities. The values in src1 are treated as unsigned, packed 16-bit quantities; and the values in src2 are treated as signed, packed 16-bit quantities. The results are placed in an unsigned, packed 16-bit format into dst.

For each pair of 16-bit quantities in src1 and src2, the sum between the unsigned 16-bit value from src1 and the signed 16-bit value from src2 is calculated and saturated to produce a signed 16-bit result. The result is placed in the corresponding position in dst.

Saturation is performed on each 16-bit result independently. For each sum, the following tests are applied:

- If the sum is in the range 0 to 2^{16} 1, inclusive, then no saturation is performed and the sum is left unchanged.
- If the sum is greater than 2^{16} 1, then the result is set to 2^{16} 1.
- If the sum is less than 0, then the result is cleared to 0.



NOTE: This operation is performed on each halfword separately. This instruction does not affect the SAT bit in CSR.



Execution

```
if (cond)  \{ \\ sat(umsb16(\textit{src1}) + smsb16(\textit{src2})) \rightarrow umsb16(\textit{dst}); \\ sat(ulsb16(\textit{src1}) + slsb16(\textit{src2})) \rightarrow ulsb16(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also ADD2, SADD, SADD2, SADDU4

Examples Example 1

SADDUS2 .S1 A2, A8, A9

	Before instruction			1 cycle after instruction	
A2	5789 F23Ah	22409 62010 unsigned	A2	5789 F23Ah	
A8	74B8 4975h	29880 18805 signed	A8	74B8 4975h	
A9	xxxx xxxxh		A9	CC41 FFFF	52289 65535 unsigned

Example 2

SADDUS2 .S2 B2, B8, B12

	Before instruction			1 cycle after instruction	
B2	147C 0124h	5244 292 unsigned	B2	147C 0124h	
B8	A051 01A6h	-24495 422 signed	B8	A051 01A6h	
B12	xxxx xxxxh		B12	0000 02CAh	0 714 unsigned



SADDU4

Add With Saturation, Four Unsigned 8-Bit Pairs for Four 8-Bit Results

Syntax

SADDU4 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	0	0	1	1	1	1	0	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.S1, .S2
src2	xu4	
dst	u4	


Description

Performs 2s-complement addition between unsigned, packed 8-bit quantities. The values in *src1* and *src2* are treated as unsigned, packed 8-bit quantities and the results are written into *dst* in an unsigned, packed 8-bit format.

For each pair of 8-bit quantities in *src1* and *src2*, the sum between the unsigned 8-bit value from *src1* and the unsigned 8-bit value from *src2* is calculated and saturated to produce an unsigned 8-bit result. The result is placed in the corresponding position in *dst*.

Saturation is performed on each 8-bit result independently. For each sum, the following tests are applied:

- If the sum is in the range 0 to 28 1, inclusive, then no saturation is performed and the sum is left unchanged.
- If the sum is greater than 28 1, then the result is set to 28 1.



NOTE: This operation is performed on each 8-bit quantity separately. This instruction does not affect the SAT bit in CSR.



Execution

```
if (cond)  \{ \\ sat(ubyte0(src1) + ubyte0(src2)) \rightarrow ubyte0(dst); \\ sat(ubyte1(src1) + ubyte1(src2)) \rightarrow ubyte1(dst); \\ sat(ubyte2(src1) + ubyte2(src2)) \rightarrow ubyte2(dst); \\ sat(ubyte3(src1) + ubyte3(src2)) \rightarrow ubyte3(dst) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also ADD4, SADD, SADD2, SADDUS2, SUB4

Examples Example 1

SADDU4 .S1 A2, A8, A9

	Before instruction			1 cycle after instruction	
A2	57 89 F2 3Ah	87 137 242 58 unsigned	A2	57 89 F2 3Ah	
A8	74 B8 49 75h	116 184 73 117 unsigned	A8	74 B8 49 75h	
A9	xxxx xxxxh		A9	CB FF FF AFh	203 255 255 175 unsigned

Example 2

SADDU4 .S2 B2, B8, B12

	Before instruction			1 cycle after instruction	
B2	14 7C 01 24h	20 124 1 36 unsigned	B2	14 7C 01 24h	
B8	A0 51 01 A6h	160 81 1 166 unsigned	B8	A0 51 01 A6h	
B12	xxxx xxxxh		B12	B4 CD 02 CA	180 205 2 202 unsigned



SAT

Saturate a 40-Bit Integer to a 32-Bit Integer

Syntax

unit = .L1 or .L2

Opcode

31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	ds	st	src2		0	0	0	0	0	Х	1	0	0	0	0	0	0	1	1	0	s	р
3		1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2 dst	slong sint	.L1, .L2

Description

A 40-bit *src2* value is converted to a 32-bit value. If the value in *src2* is greater than what can be represented in 32-bits, *src2* is saturated. The result is placed in *dst*. If a saturate occurs, the SAT bit in the control status register (CSR) is set one cycle after *dst* is written.

Execution

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L

Instruction Type

Single-cycle

Delay Slots

0



Examples

Example 1

SAT .L2 B1:B0,B5

	Before instruction			1 cycle after instru	ıction
B1:B0	0000 001Fh	3413 539Ah	B1:B0	0000 001Fh	3413 539Ah
B5	xxxx xxxxh		B5	7FFF FFFFh	
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				0	
				2 cycles after inst	ruction
			B1:B0	0000 001Fh	3413 539Ah
			B1:B0 B5	_	
				0000 001Fh	

Example 2

SAT .L2 B1:B0,B5

	Before instruction			1 cycle after instru	uction
B1:B0	0000 0000h	A190 7321h	B1:B0	0000 0000h	A190 7321h
B5	xxxx xxxxh		B5	7FFF FFFFh	
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				2 cycles after inst	ruction
			B1:B0	0000 0000h	A190 7321h
			B5	7FFF FFFFh	
			CSR	0001 0300h	Saturated
			SSR	0000 0002h	



Example 3

SAT .L2 B1:B0,B5

	Before instruction			1 cycle after instru	uction
B1:B0	0000 00FFh	A190 7321h	B1:B0	0000 00FFh	A190 7321h
B5	xxxx xxxxh		B5	A190 7321h	
CSR	0001 0100h		CSR	0001 0100h	
SSR	0000 0000h		SSR	0000 0000h	
				2 cycles after inst	ruction
			B1:B0	0000 00FFh	A190 7321h
			B1:B0 B5	0000 00FFh A190 7321h	A190 7321h
			-		A190 7321h Not saturated



SET — Set a Bit Field www.ti.com

SET Set a Bit Field

Syntax SET (.unit) src2, csta, cstb, dst

or

SET (.unit) src2, src1, dst

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Sc5	Figure F-27

Opcode Constant form:

31 29	28	27	23	22 18	17 13	(17	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	csta	cstb		1	0	0	0	1	0	s	р
3	1	5		5	5	5								1	1

Opcode map field used	For operand type	Unit
src2	uint	.S1, .S2
csta	ucst5	
cstb	ucst5	
dst	uint	

Opcode Register form:

31	29	28	27	23	22 18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2		src1		Х	1	1	1	0	1	1	1	0	0	0	s	р
3		1		5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src2	xuint	.S1, .S2
src1	uint	
dst	uint	




www.ti.com SET — Set a Bit Field

Description

For $cstb \ge csta$, the field in src2 as specified by csta to cstb is set to all 1s in dst. The csta and cstb operands may be specified as constants or in the 10 LSBs of the src1 register, with cstb being bits 0-4 ($src1_{4..0}$) and csta being bits 5-9 ($src1_{9..5}$). csta is the LSB of the field and cstb is the MSB of the field. In other words, csta and cstb represent the beginning and ending bits, respectively, of the field to be set to all 1s in dst. The LSB location of src2 is bit 0 and the MSB location of src2 is bit 31.

In the following example, *csta* is 15 and *cstb* is 23. For the register version of the instruction, only the 10 LSBs of the *src1* register are valid. If any of the 22 MSBs are non-zero, the result is invalid.



For cstb < csta, the src2 register is copied to dst. The csta and cstb operands may be specified as constants or in the 10 LSBs of the src1 register, with cstb being bits 0–4 ($src1_{4.0}$) and csta being bits 5–9 ($src1_{9.5}$).

Execution

If the constant form is used when $cstb \ge csta$:

if (cond) else nop

src2 SET csta, $cstb \rightarrow dst$

If the register form is used when $cstb \ge csta$:

if (cond) else nop

src2 SET src1 $_{9..5}$, src1 $_{4..0} \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also CLR



SET — Set a Bit Field www.ti.com

Example 1

SET .S1 A0,7,21,A1

	Before instruction	1 cycle after instruction
A0	4B13 4A1Eh	A0 4B13 4A1Eh
A1	xxxx xxxxh	A1 4B3F FF9Eh

Example 2

SET .S2 B0,B1,B2

	Before instruction	1 cycle after instruction
В0	9ED3 1A31h	B0 9ED3 1A31h
B1	0000 C197h	B1 0000 C197h
B2	xxxx xxxxh	B2 9EFF FA31h




www.ti.com SHFL — Shuffle

SHFL Shuffle

Syntax SHFL (.unit) src2, dst

unit = .M1 or .M2

Opcode




Opcode map field used	For operand type	Unit
src2	xuint	.M1, .M2
dst	uint	

Description

Performs an interleave operation on the two halfwords in *src2*. The bits in the lower halfword of *src2* are placed in the even bit positions in *dst*, and the bits in the upper halfword of *src2* are placed in the odd bit positions in *dst*.

As a result, bits 0, 1, 2, ..., 14, 15 of *src2* are placed in bits 0, 2, 4, ..., 28, 30 of *dst*. Likewise, bits 16, 17, 18, .. 30, 31 of *src2* are placed in bits 1, 3, 5, ..., 29, 31 of *dst*.



NOTE: The **SHFL** instruction is the exact inverse of the **DEAL** instruction (see **DEAL**).

Execution

```
if (cond)  \{ \\ src2_{31,30,29...16} \rightarrow dst_{31,29,27...1} \\ src2_{15,14,13...0} \rightarrow dst_{30,28,26...0} \\ \}  else nop
```



SHFL — Shuffle www.ti.com

Pipeline

Pipeline Stage	E1	E2
Read	src2	_
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also DEAL

Example SHFL .M1 A1,A2

	Before instruction		2 cycles after instruction				
A1	B174 6CA4h	A1	B174 6CA4h				
A2	xxxx xxxxh	A2	9E52 6E30h				



SHFL3 3-Way Bit Interleave On Three 16-Bit Values Into a 48-Bit Result

Syntax SHFL3 (.unit) src1, src2, dst_o:dst_e

unit = .L1 or .L2

Opcode

31	30	29	28	27	23	22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst		src2			src1		Χ	0	1	1	0	1	1	0	1	1	0	s	р
				5		5			5		1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.L1, .L2
src2	xsint	
dst	dint	

Description

Performs a 3-way bit interleave on three 16-bit values and creating a 48-bit result.

This instruction executes unconditionally and cannot be predicated.

31						16	15						0	
a15	a14	a13		a2	a1	a0	b15	b14	b13		b2	b1	b0	← src1
c15	c14	c13		c2	c1	c0	d15	d14	d13		d2	d1	d0	← src2
	SHFL3													
							ļ							
31						16	15						0	
0	0	0		0	0	0	a15	b15	d15		b11	d11	a10	← dst_o
b10				·			1							7
	d10	a9	I	d6	a5	b5	d5	a4	b4	l	a0	b0	d0	←dst_

Execution

```
int inp0, inp1, inp2
dword result;
inp0 = src2 & FFFFh;
inp1 = src1 & FFFFh;
inp2 = src1 >> 16 & FFFFh;
result = 0;
for (I = 0; I < 16; I++)
{
    result |= (inp0 >> I & 1) << (I × 3) ;
    result |= (inp1 >> I & 1) << ((I × 3) + 1);
    result |= (inp2 >> I & 1) << I ((I × 3) + 2)
}</pre>
```



SHFL3 — 3-Way Bit Interleave On Three 16-Bit Values Into a 48-Bit Result

www.ti.com

Instruction Type Single-cycle

Delay Slots 0

Example SHFL3 .L1 A0,A1,A3:A2

	Before instruction	1 cycle after instruction
A0	8765 4321h	A2 7E17 9306h
A1	1234 5678h	A3 0000 8C11h



SHL

Arithmetic Shift Left

Syntax

SHL (.unit) src2, src1, dst

or

SHL (.unit) src2_h:src2_l, src1, dst_h:dst_l

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	S3i	Figure F-23
	Ssh5	Figure F-25
	S2sh	Figure F-26

Opcode

31 29	28	21 2	23 22 18	17 13	12	11	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	ор		1	0	0	0	s	р
3	1	5	5	5	1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src2	xsint	.S1, .S2	11 0011
src1	uint		
dst	sint		
src2	slong	.S1, .S2	11 0001
src1	uint		
dst	slong		
src2	xuint	.S1, .S2	01 0011
src1	uint		
dst	ulong		
src2	xsint	.S1, .S2	11 0010
src1	ucst5		
dst	sint		
src2	slong	.S1, .S2	11 0000
src1	ucst5	•	
dst	slong		
src2	xuint	.S1, .S2	01 0010
src1	ucst5	·	
dst	ulong		

Description

The *src2* operand is shifted to the left by the *src1* operand. The result is placed in *dst*. When a register is used, the six LSBs specify the shift amount and valid values are 0-40. When an immediate is used, valid shift amounts are 0-31. If *src2* is a register pair, only the bottom 40 bits of the register pair are shifted. The upper 24 bits of the register pair are unused.

If 39 < src1 < 64, src2 is shifted to the left by 40. Only the six LSBs of src1 are used by the shifter, so any bits set above bit 5 do not affect execution.

SHL — Arithmetic Shift Left www.ti.com

Execution

if (cond) $(src2 \& 0xFFFFFF) \ll src1 \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also ROTL, SHLMB, SHR, SSHL, SSHVL

Example 1

SHL .S1 A0,4,A1

	Before instruction	1 cycle after instruction	
A0	29E3 D31Ch	A0 29E3 D31Ch	
A1	xxxx xxxxh	A1 9E3D 31C0h	

Example 2

SHL .S2 B0,B1,B2

	Before instruction		1 cycle after instruction	
В0	4197 51A5h	В0	4197 51A5h	
B1	0000 0009h	B1	0000 0009h	
B2	xxxx xxxxh	B2	2EA3 4A00h	

Example 3

SHL .S2 B1:B0,B2,B3:B2

	Before instruction			1 cycle after instructio	n
B1:B0	0000 0009h	4197 51A5h	B1:B0	0000 0009h	4197 51A5h
B2	0000 0022h		B2	0000 0000h	
B3:B2	xxxx xxxxh	xxxx xxxxh	B3:B2	0000 0094h	0000 0000h

Example 4

SHL .S1 A5:A4,0,A1:A0

	Before instruction	1		1 cycle after instruction				
A5:A4	FFFF FFFFh	FFFF FFFFh	A5:A4	FFFF FFFFh	FFFF FFFFh			
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	0000 00FFh	FFFF FFFFh			





SHLMB Shift Left and Merge Byte

Syntax SHLMB (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 2	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	1	0	0	0	0	1	1	1	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.L1, .L2
src2	xu4	
dst	u4	

Opcode .S unit

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	1	1	1	0	0	1	1	1	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.S1, .S2
src2	xu4	
dst	u4	

Description

Shifts the contents of *src2* left by 1 byte, and then the most-significant byte of *src1* is merged into the least-significant byte position. The result is placed in *dst*.

31		24 2	23	16	15	8	7	0	
	ua_3		ua_2		ua_1		ua_0		← src1
SHLMB									
	ub_3		ub_2		ub_1		ub_0		← src2
					\downarrow				
31		24 2	23	16	15	8	7	0	
	ub_2		ub_1		ub_0		ua_3		← dst



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also ROTL, SHL, SHRMB

Examples Example 1

SHLMB .L1 A2, A8, A9

	Before instruction		1 cycle after instruction	
A2	3789 F23Ah	A2	3789 F23Ah	
A8	04B8 4975h	A8	04B8 4975h]
A9	xxxx xxxxh	A9	B849 7537h	

Example 2

SHLMB .S2 B2,B8, B12

	Before instruction		1 cycle after instruction
B2	0124 2451h	B2	0124 2451h
B8	01A6 A051h	В8	01A6 A051h
B12	xxxx xxxxh	B12	A6A0 5101h

450 Instruction Set SPRUFE8B-July 2010



SHR

Arithmetic Shift Right

Syntax

SHR (.unit) src2, src1, dst

or

SHR (.unit) src2_h:src2_l, src1, dst

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	S3i	Figure F-23
	Ssh5	Figure F-25
	S2sh	Figure F-26

Opcode

31 2	29	28	27	23	22 18	17	13	12	11	6	5	4	3	2	1	0
creg		Z		dst	src2	src1		Х	ор		1	0	0	0	s	р
3		1		5	5	5		1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src2	xsint	.S1, .S2	11 0111
src1	uint		
dst	sint		
src2	slong	.S1, .S2	11 0101
src1	uint		
dst	slong		
src2	xsint	.S1, .S2	11 0110
src1	ucst5	•	
dst	sint		
src2	slong	.S1, .S2	11 0100
src1	ucst5	•	
dst	slong		

Description

The *src2* operand is shifted to the right by the *src1* operand. The sign-extended result is placed in *dst*. When a register is used, the six LSBs specify the shift amount and valid values are 0-40. When an immediate value is used, valid shift amounts are 0-31. If *src2* is a register pair, only the bottom 40 bits of the register pair are shifted. The upper 24 bits of the register pair are unused.

If 39 < *src1* < 64, *src2* is shifted to the right by 40. Only the six LSBs of *src1* are used by the shifter, so any bits set above bit 5 do not affect execution.

Execution

if (cond) else nop

 $(src2 \& 0xFFFFFF) >> s src1 \rightarrow dst$



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also SHL, SHR2, SHRMB, SHRU, SHRU2, SSHVR

Examples Example 1

SHR .S1 A0,8,A1

	Before instruction	1 cycle after instruction
A0	F123 63D1h	A0 F123 63D1h
A1	xxxx xxxxh	A1 FFF1 2363h

Example 2

SHR .S2 B0,B1,B2

	Before instruction	1 cycle after instruction			
В0	1492 5A41h	В0	1492 5A41h		
B1	0000 0012h	B1	0000 0012h		
B2	xxxx xxxxh	B2	0000 0524h		

Example 3

SHR .S2 B1:B0,B2,B3:B2

	Before instruction			1 cycle after instruction						
B1:B0	0000 0012h	1492 5A41h	B1:B0	0000 0012h	1492 5A41h					
B2	0000 0019h		B2	0000 090Ah						
B3:B2	xxxx xxxxh	xxxx xxxxh	B3:B2	0000 0000h	0000 090Ah					

Example 4

SHR .S1 A5:A4,0,A1:A0

	Before instruction			1 cycle after instru	uction
A5:A4	FFFF FFFFh	FFFF FFFFh	A5:A4	FFFF FFFFh	FFFF FFFFh
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	0000 00FFh	FFFF FFFFh



SHR2 Arithmetic Shift Right, Signed, Packed 16-Bit

Syntax SHR2 (.unit) src2, src1, dst

unit = .S1 or .S2

Opcode .S unit (uint form)

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	'	Z		dst	src2	src1		Х	1	1	0	1	1	1	1	1	0	0	s	p
3		1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.S1, .S2
src2	xs2	
dst	s2	

Opcode .S unit (cst form)


31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
(creg	Z	(dst	src2	src1		Х	0	1	1	0	0	0	1	0	0	0	S	p
	3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	ucst5	.S1, .S2
src2	xs2	
dst	s2	

Description

Performs an arithmetic shift right on signed, packed 16-bit quantities. The values in *src2* are treated as signed, packed 16-bit quantities. The lower 5 bits of *src1* are treated as the shift amount. The results are placed in a signed, packed 16-bit format into *dst*.

For each signed 16-bit quantity in *src2*, the quantity is shifted right by the number of bits specified in the lower 5 bits of *src1*. Bits 5 through 31 of *src1* are ignored and may be non-zero. The shifted quantity is sign-extended, and placed in the corresponding position in *dst*. Bits shifted out of the least-significant bit of the signed 16-bit quantity are discarded.





NOTE: If the shift amount specified in *src1* is in the range 16 to 31, the behavior is identical to a shift value of 15.

Execution

```
if (cond)  \{ \\ smsb16(\textit{src2}) >> \textit{src1} \rightarrow smsb16(\textit{dst}); \\ slsb16(\textit{src2}) >> \textit{src1} \rightarrow slsb16(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also SHL, SHR, SHRMB, SHRU, SHRU2

Examples Example 1

SHR2 .S2 B2,B4,B5

	Before instruction		1 cycle after instruction			
B2	A6E2 C179h		B2	A6E2 C179h		
B4	1458 3B69h	shift value 9	B4	1458 3B69h		
B5	xxxx xxxxh		B5	FFD3 FFE0h		

Example 2

 ${\tt SHR2}$.S1 A4,0fh,A5 ; shift value is 15

	Before instruction	1 cycle after instruction
A4	000A 87AFh	A4 000A 87AFh
A5	xxxx xxxxh	A5 0000 FFFFh

454 Instruction Set SPRUFE8B-July 2010





SHRMB Shift Right and Merge Byte

Syntax SHRMB (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	1	0	0	0	1	0	1	1	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.L1, .L2
src2	xu4	
dst	u4	

Opcode .S unit

31 29	28	27 23	22 18	17 13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	1	1	1	0	1	0	1	1	0	0	s	p
3	1	5	5	5	1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.S1, .S2
src2	xu4	
dst	u4	

Description

Shifts the contents of *src2* right by 1 byte, and then the least-significant byte of *src1* is merged into the most-significant byte position. The result is placed in *dst*.

31	24	23	16 15		8 7		0						
	ua_3	ua_2		ua_1		ua_0	← src1						
SHRMB													
	ub_3	ub_2		ub_1		ub_0	← src2						
			\downarrow										
31	24	23	16 15		8 7		0						
	ua_0	ub_3		ub_2		ub_1	← dst						



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also SHL, SHLMB, SHR, SHR2, SHRU, SHRU2

Example 1

SHRMB .L1 A2,A8,A9

	Before instruction		1 cycle after instruction
A2	3789 F23Ah	A2	3789 F23Ah
A8	04B8 4975h	A8	04B8 4975h
A9	xxxx xxxxh	А9	3A04 B849h

Example 2

SHRMB .S2 B2,B8,B12

	Before instruction	1 cycle after instruction					
B2	0124 2451h	B2 0124 2451h					
B8	01A6 A051h	B8 01A6 A051h					
B12	xxxx xxxxh	B12 5101 A6A0h					

456 Instruction Set SPRUFE8B-July 2010



SHRU

Logical Shift Right

Syntax

SHRU (.unit) src2, src1, dst

or

SHRU (.unit) src2_h:src2_l, src1, dst_h:dst_l

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Ssh5	Figure F-25
	S2sh	Figure F-26

Opcode

31	29	28	27	23	22 18	17	13	12	11	6	5	4	3	2	1	0
creg		Z		dst	src2	src1		Х	ор		1	0	0	0	s	р
3		1		5	5	5		1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src2	xuint	.S1, .S2	10 0111
src1	uint		
dst	uint		
src2	ulong	.S1, .S2	10 0101
src1	uint		
dst	ulong		
src2	xuint	.S1, .S2	10 0110
src1	ucst5		
dst	uint		
src2	ulong	.S1, .S2	10 0100
src1	ucst5	·	
dst	ulong		

Description

The *src2* operand is shifted to the right by the *src1* operand. The zero-extended result is placed in *dst*. When a register is used, the six LSBs specify the shift amount and valid values are 0-40. When an immediate value is used, valid shift amounts are 0-31. If *src2* is a register pair, only the bottom 40 bits of the register pair are shifted. The upper 24 bits of the register pair are unused.

If 39 < *src1* < 64, *src2* is shifted to the right by 40. Only the six LSBs of *src1* are used by the shifter, so any bits set above bit 5 do not affect execution.

Execution

if (cond) else nop

 $(src2 \& 0xFFFFFF) >> z src1 \rightarrow dst$



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also SHL, SHR, SHR2, SHRMB, SHRU2

Example 1

SHRU .S1 A0,8,A1

	Before instruction	1 cycle after instruction
A0	F123 63D1h	A0 F123 63D1h
A1	xxxx xxxxh	A1 00F1 2363h

Example 2

SHRU .S1 A5:A4,0,A1:A0

	Before instruction			1 cycle after instructio	n
A5:A4	FFFF FFFFh	FFFF FFFFh	A5:A4	FFFF FFFFh	FFFF FFFFh
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	0000 00FFh	FFFF FFFFh



SHRU2 Arithmetic Shift Right, Unsigned, Packed 16-Bit

Syntax SHRU2 (.unit) src2, src1, dst

unit = .S1 or .S2

Opcode .S unit (uint form)

31 29	28	27 2		17 1	13 1	12 1	11 10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1		Х	1 1	1	0	0	0	1	1	0	0	s	р
3	1	5	5	5		1										1	1

Opcode map field used	For operand type	Unit
src1	uint	.S1, .S2
src2	xu2	
dst	u2	

Opcode .S unit (cst form)

3	1 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2	src1		Х	0	1	1	0	0	1	1	0	0	0	s	р
	3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	ucst5	.S1, .S2
src2	xu2	
dst	u2	


Description

Performs an arithmetic shift right on unsigned, packed 16-bit quantities. The values in *src2* are treated as unsigned, packed 16-bit quantities. The lower 5 bits of *src1* are treated as the shift amount. The results are placed in an unsigned, packed 16-bit format into *dst*.

For each unsigned 16-bit quantity in *src2*, the quantity is shifted right by the number of bits specified in the lower 5 bits of *src1*. Bits 5 through 31 of *src1* are ignored and may be non-zero. The shifted quantity is zero-extended, and placed in the corresponding position in *dst*. Bits shifted out of the least-significant bit of the signed 16-bit quantity are discarded.

NOTE: If the shift amount specified in *src1* is in the range of 16 to 31, the *dst* will be cleared to all zeros.





Execution

```
if (cond)  \{ \\ \text{umsb16}(\textit{src2}) >> \textit{src1} \rightarrow \text{umsb16}(\textit{dst}); \\ \text{ulsb16}(\textit{src2}) >> \textit{src1} \rightarrow \text{ulsb16}(\textit{dst}); \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also SHL, SHR, SHR2, SHRMB, SHRU

Examples Example 1

SHRU2 .S2 B2,B4,B5

	Before instruction			1 cycle after instruction
B2	A6E2 C179h		B2	A6E2 C179h
B4	1458 3B69h	Shift value 9	B4	1458 3B69h
B5	xxxx xxxxh		B5	0053 0060h

Example 2

SHRU2 .S1 A4,0Fh,A5 ; Shift value is 15

	Before instruction	1 cycle after instruction
A4	000A 87AFh	A4 000A 87AFh
A5	xxxx xxxxh	A5 0000 0001h



SMPY Multiply Signed 16 LSB × Signed 16 LSB With Left Shift and Saturation

Syntax SMPY (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 29	9 28	27	23		8 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	d	st	src2		src1		Х	1	1	0	1	0	0	0	0	0	0	s	p
3	1	5	5	5		5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	slsb16 xslsb16 sint	.M1, .M2

Description

The 16 least-significant bits of *src1* operand is multiplied by the 16 least-significant bits of the *src2* operand. The result is left shifted by 1 and placed in *dst*. If the left-shifted result is 8000 0000h, then the result is saturated to 7FFF FFFFh. If a saturate occurs, the SAT bit in CSR is set one cycle after *dst* is written. The source operands are signed by default.

Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Single-cycle (16 \times 16)

Delay Slots 1

See Also MPY, SMPYH, SMPYHL, SMPYLH



Example

SMPY .M1 A1,A2,A3

	Before instruction			2 cycles after inst	ruction
A1	0000 0123h	291 ⁽¹⁾	A1	0000 0123h	
A2	01E0 FA81h	-1407 ⁽¹⁾	A2	01E0 FA81h	
A3	xxxx xxxxh		А3	FFF3 8146h	-818,874
CSR	0001 0100h		CSR	0001 0100h	Not saturated
SSR	0000 0000h		SSR	0000 0000h	

⁽¹⁾ Signed 16-LSB integer



SMPYH

Multiply Signed 16 MSB × Signed 16 MSB With Left Shift and Saturation

Syntax

SMPYH (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 2	9 28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2	src1		Χ	0	0	0	1	0	0	0	0	0	0	s	p
3	1	5	5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	smsb16 xsmsb16 sint	.M1, .M2

Description

The 16 most-significant bits of *src1* operand is multiplied by the 16 most-significant bits of the *src2* operand. The result is left shifted by 1 and placed in *dst*. If the left-shifted result is 8000 0000h, then the result is saturated to 7FFF FFFFh. If a saturation occurs, the SAT bit in CSR is set one cycle after *dst* is written. The source operands are signed by default.

Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type

Single-cycle (16 \times 16)

Delay Slots

1

See Also MPYH, SMPY, SMPYHL, SMPYLH



SMPYHL Multiply Signed 16 MSB × Signed 16 LSB With Left Shift and Saturation

Syntax SMPYHL (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	0	1	0	1	0	0	0	0	0	0	s	р
3	1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2	smsb16 xslsb16	.M1, .M2
dst	sint	

Description

The 16 most-significant bits of the *src1* operand is multiplied by the 16 least-significant bits of the *src2* operand. The result is left shifted by 1 and placed in *dst*. If the left-shifted result is 8000 0000h, then the result is saturated to 7FFF FFFFh. If a saturation occurs, the SAT bit in CSR is set one cycle after *dst* is written.

Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Single-cycle (16 \times 16)

Delay Slots 1

See Also MPYHL, SMPY, SMPYH, SMPYLH



www.ti.com

Example SMPYHL .M1 A1,A2,A3

	Before instruction			2 cycles after instr	uction
A1	008A 0000h	138 ⁽¹⁾	A1	008A 0000h	
A2	0000 00A7h	167 ⁽²⁾	A2	0000 00A7h	
A3	xxxx xxxxh		A3	0000 B40Ch	46,092
CSR	0001 0100h		CSR	0001 0100h	Not saturated
SSR	0000 0000h		SSR	0000 0000h	

⁽¹⁾ Signed 16-MSB integer

⁽²⁾ Signed 16-LSB integer



SMPYLH

Multiply Signed 16 LSB x Signed 16 MSB With Left Shift and Saturation

Syntax

SMPYLH (.unit) src1, src2, dst

unit = .M1 or .M2

Compact Instruction Format

Unit	Opcode Format	Figure
.M	M3	Figure E-5

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	0	0	1	0	0	0	0	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1 src2 dst	slsb16 xsmsb16 sint	.M1, .M2

Description

The 16 least-significant bits of the *src1* operand is multiplied by the 16 most-significant bits of the *src2* operand. The result is left shifted by 1 and placed in *dst*. If the left-shifted result is 8000 0000h, then the result is saturated to 7FFF FFFFh. If a saturation occurs, the SAT bit in CSR is set one cycle after *dst* is written.

Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type

Single-cycle (16 \times 16)

Delay Slots

See Also MPYLH, SMPY, SMPYH, SMPYHL



www.ti.com

Example SMPYLH .M1 A1,A2,A3

	Before instruction			2 cycles after instr	uction
A1	0000 8000h	-32,768 ⁽¹⁾	A1	0000 8000h	
A2	8000 0000h	-32,768(2)	A2	8000 0000h	
A3	xxxx xxxxh		A3	7FFF FFFFh	2,147,483,647
CSR	0001 0100h		CSR	0001 0300h	Saturated
SSR	0000 0000h		SSR	0000 0010h	

⁽¹⁾ Signed 16-LSB integer

⁽²⁾ Signed 16-MSB integer



www.ti.com

SMPY2

Multiply Signed by Signed, 16 LSB x 16 LSB and 16 MSB x 16 MSB With Left Shift and Saturation

Syntax

SMPY2 (.unit) src1, src2, dst o:dst e

unit = .M1 or .M2

Opcode

31	29	28	27	23	22	18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	z		dst	src2		src	1	Х	0	0	0	0	0	1	1	1	0	0	s	p
3		1		5	5		5		1											1	1


Opcode map field used	For operand type	Unit
src1	s2	.M1, .M2
src2	xs2	
dst	sllong	

Description

Performs two 16-bit by 16-bit multiplies between two pairs of signed, packed 16-bit values, with an additional left-shift and saturate. The values in src1 and src2 are treated as signed, packed 16-bit quantities. The two 32-bit results are written into a 64-bit register pair.

The SMPY2 instruction produces two 16 x 16 products. Each product is shifted left by 1. If the left-shifted result is 8000 0000h, the output value is saturated to 7FFF FFFFh.

The saturated product of the lower halfwords of src1 and src2 is written to the even destination register, dst_e. The saturated product of the upper halfwords of src1 and src2 is written to the odd destination register, dst o.



NOTE: If either product saturates, the SAT bit is set in CSR one cycle after the cycle that the result is written to dst_o:dst_e. If neither product saturates, the SAT bit in CSR remains unaffected.



www.ti.com SMPY2 — Multiply Signed by Signed, 16 LSB x 16 LSB and 16 MSB x 16 MSB With Left Shift and Saturation

The **SMPY2** instruction helps reduce the number of instructions required to perform two 16-bit by 16-bit saturated multiplies on both the lower and upper halves of two registers.

The following code:

```
SMPY .M1 A0, A1, A2
SMPYH .M1 A0, A1, A3
```

may be replaced by:

SMPY2 .M1 A0, A1, A3:A2

Execution

```
if (cond)  \{ \\ sat((lsb16(\textit{src1}) \times lsb16(\textit{src2})) << 1) \rightarrow \textit{dst\_e}; \\ sat((msb16(\textit{src1}) \times msb16(\textit{src2})) << 1) \rightarrow \textit{dst\_o} \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Instruction Type Four-cycle

Delay Slots 3

See Also MPY2, SMPY

Examples Example 1

SMPY2 .M1 A5,A6,A9:A8

	Before instruction			4 cycles after instructio	n
A5	6A32 1193h	27186 4499	A5	6A32 1193h	
A6	B174 6CA4h	-20108 27812	A6	B174 6CA4h	
A9:A8	xxxx xxxxh	xxxx xxxxh	A9:A8	BED5 6150h	0EEA 8C58h
			•	-1,093,312,176	250,252,376

Example 2

SMPY2 .M2 B2, B5, B9:B8

	Before instruction			4 cycles after instruction	on
B2	1234 3497h	4660 13463	B2	1234 3497h	
B5	21FF 50A7h	8703 20647	B5	21FF 50A7h	
B9:B8	xxxx xxxxh	xxxx xxxxh	B9:B8	04D5 AB98h	2122 FD02h
	<u> </u>			81,111,960	555,941,122



SMPY32 Multiply Signed 32-Bit × Signed 32-Bit Into 64-Bit Result With Left Shift and

Saturation

Syntax SMPY32 (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	1	1	0	0	1	1	1	0	0	S	p
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit				
src1	int	.M1, .M2				
src2	xint					
dst	int					

Description

Performs a 32-bit by 32-bit multiply. src1 and src2 are signed 32-bit values. The 64-bit result is shifted left by 1 with saturation, and the 32 most-significant bits of the shifted value are written to dst.

If the result saturates either on the multiply or the shift, the M1 or M2 bit in SSR and the SAT bit in CSR are written one cycle after the results are written to dst.

This instruction executes unconditionally and cannot be predicated.

NOTE: When both inputs are 8000 0000h, the shifted result cannot be represented as a 32-bit signed value. In this case, the saturation value 7FFF FFFFh is written into dst.

Execution

 $msb32(sat((src2 \times src1) << 1)) \rightarrow dst$

Instruction Type Four-cycle

Delay Slots 3

MPY32, SMPY2 See Also



www.ti.com SMPY32 — Multiply Signed 32-Bit x Signed 32-Bit Into 64-Bit Result With Left Shift and Saturation

Example 1

SMPY32 .M1 A0,A1,A2

	Before instruction		4 cycle after instruction
A0	8765 4321h	A2	EED8 ED1Ah
A1	1234 5678h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0100h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0000h

⁽¹⁾ CSR.SAT and SSR.M1 unchanged by operation

Example 2

SMPY32 .L1 A0,A1,A2

	Before instruction		4 cycles after instruction
A0	8000 0000h	A2	7FFF FFFFh
A1	8000 0000h		
CSR	0001 0100h	CSR ⁽¹⁾	0001 0300h
SSR	0000 0000h	SSR ⁽¹⁾	0000 0010h

⁽¹⁾ CSR.SAT and SSR.M1 set to 1, 5 cycles after instruction



SPACK2

Saturate and Pack Two 16 LSBs Into Upper and Lower Register Halves

Syntax

SPACK2 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 2	9 28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1		Х	1	1	0	0	1	0	1	1	0	0	s	p
3	1		5	5	5		1											1	1


Opcode map field used	For operand type	Unit
src1	int	.S1, .S2
src2	xint	
dst	s2	

Description

Takes two signed 32-bit quantities in src1 and src2 and saturates them to signed 16-bit quantities. The signed 16-bit results are then packed into a signed, packed 16-bit format and written to dst. Specifically, the saturated 16-bit signed value of src1 is written to the upper halfword of dst, and the saturated 16-bit signed value of src2 is written to the lower halfword of dst.

Saturation is performed on each input value independently. The input values start as signed 32-bit quantities, and are saturated to 16-bit quantities according to the following rules:

- If the value is in the range 2^{15} to 2^{15} 1, inclusive, then no saturation is performed and the value is truncated to 16 bits.
- If the value is greater than 2^{15} 1, then the result is set to 2^{15} 1.
- If the value is less than 2^{15} , then the result is set to 2^{15} .



The SPACK2 instruction is useful in code that manipulates 16-bit data at 32-bit precision for its intermediate steps, but that requires the final results to be in a 16-bit representation. The saturate step ensures that any values outside the signed 16-bit range are clamped to the high or low end of the range before being truncated to 16 bits.

NOTE: This operation is performed on each 16-bit value separately. This instruction does not affect the SAT bit in CSR.



Execution

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also PACK2, PACKH2, PACKHL2, PACKLH2, RPACK2, SPACKU4

Examples Example 1

SPACK2 .S1 A2,A8,A9

	Before instruction			1 cycle after instruction	
A2	3789 F23Ah	931,787,322	A2	3789 F23Ah	
A8	04B8 4975h	79,186,293	A8	04B8 4975h	
A9	xxxx xxxxh		A9	7FFF 7FFFh	32767 32767

Example 2

SPACK2 .S2 B2,B8,B12

	Before instruction			1 cycle after instruction	
B2	A124 2451h	-1,591,466,927	B2	A124 2451h	
B8	01A6 A051h	27,697,233	B8	01A6 A051h	
B12	xxxx xxxxh		B12	8000 7FFFh	-32768 32767



SPACKU4

Saturate and Pack Four Signed 16-Bit Integers Into Four Unsigned 8-Bit Halfwords

Syntax

SPACKU4 (.unit) src1, src2, dst

unit = .S1 or .S2

Opcode

31 29	28	27	23	22	18	17	13		11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		sro	1	Х	1	1	0	1	0	0	1	1	0	0	s	р
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.S1, .S2
src2	xs2	
dst	u4	


Description

Takes four signed 16-bit values and saturates them to unsigned 8-bit quantities. The values in *src1* and *src2* are treated as signed, packed 16-bit quantities. The results are written into *dst* in an unsigned, packed 8-bit format.

Each signed 16-bit quantity in *src1* and *src2* is saturated to an unsigned 8-bit quantity as described below. The resulting quantities are then packed into an unsigned, packed 8-bit format. Specifically, the upper halfword of *src1* is used to produce the most-significant byte of *dst*. The lower halfword of *src1* is used to produce the second most-significant byte (bits 16 to 23) of *dst*. The upper halfword of *src2* is used to produce the third most-significant byte (bits 8 to 15) of *dst*. The lower halfword of *src2* is used to produce the least-significant byte of *dst*.

Saturation is performed on each signed 16-bit input independently, producing separate unsigned 8-bit results. For each value, the following tests are applied:

- If the value is in the range 0 to 2⁸ 1, inclusive, then no saturation is performed and the result is truncated to 8 bits.
- If the value is greater than 28 1, then the result is set to 28 1.
- If the value is less than 0, the result is cleared to 0.





The SPACKU4 instruction is useful in code that manipulates 8-bit data at 16-bit precision for its intermediate steps, but that requires the final results to be in an 8-bit representation. The saturate step ensures that any values outside the unsigned 8-bit range are clamped to the high or low end of the range before being truncated to 8 bits.

NOTE: This operation is performed on each 8-bit quantity separately. This instruction does not affect the SAT bit in CSR.

Execution

```
if (cond)
                      {
                      if (msb16(src1) >> 0000 00FFh), FFh \rightarrow ubyte3(dst) or
                      if (msb16(src1) \ll 0), 0 \rightarrow ubyte3(dst)
                           else truncate(msb16(src1)) \rightarrow ubyte3(dst);
                      if (lsb16(src1) >> 0000 00FFh), FFh \rightarrow ubyte2(dst) or
                      if (lsb16(src1) \ll 0), 0 \rightarrow ubyte2(dst)
                           else truncate(lsb16(src1)) \rightarrow ubyte2(dst);
                      if (msb16(src2) >> 0000 00FFh), FFh \rightarrow ubyte1(dst) or
                      if (msb16(src2) << 0), 0 \rightarrow ubyte1(dst)
                           else truncate(msb16(src2)) \rightarrow ubyte1(dst);
                      if (lsb16(src2) >> 0000 00FFh), FFh \rightarrow ubyte0(dst) or
                      if (lsb16(src2) \ll 0), 0 \rightarrow ubyte0(dst)
                           else truncate(lsb16(src2)) \rightarrow ubyte0(dst)
                      }
else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Single-cycle Instruction Type

Delay Slots

See Also PACKH4, PACKL4, SPACK2

Examples Example 1

SPACKU4 .S1 A2,A8,A9

	Before instruction			1 cycle after instruction	
A2	3789 F23Ah	14217 -3526	A2	3789 F23Ah	
A8	04B8 4975h	1208 18805	A8	04B8 4975h	
A9	xxxx xxxxh		A9	FF 00 FF FFh	255 0 255 255



Example 2

SPACKU4 .S2 B2,B8,B12

	Before instruction			1 cycle after instruction	
B2	A124 2451h	-24284 9297	B2	A124 2451h	
B8	01A6 A051h	422 -24495	B8	01A6 A051h	
B12	xxxx xxxxh		B12	00 FF FF 00h	0 255 255 0



www.ti.com SPDP — Convert Single-Precision Floating-Point Value to Double-Precision Floating-Point Value


SPDP Convert Single-Precision Floating-Point Value to Double-Precision Floating-Point

Value

Syntax SPDP (.unit) src2, dst

unit = .S1 or .S2

Opcode



Opcode map field used	For operand type	Unit
src2	xsp	.S1, .S2
dst	dp	

Description

The single-precision value in *src2* is converted to a double-precision value and placed in *dst*.

NOTE:

- If src2 is SNaN, NaN_out is placed in dst and the INVAL and NAN2 bits are set.
- 2. If src2 is QNaN, NaN_out is placed in dst and the NAN2 bit is set.
- If src2 is a signed denormalized number, signed 0 is placed in dst and the INEX and DEN2 bits are set.
- 4. If src2 is signed infinity, INFO bit is set.
- 5. No overflow or underflow can occur.

Execution

if (cond) else nop $dp(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2
Read	src2	
Written	dst_l	dst_h
Unit in use	.S	

If *dst* is used as the source for the **ADDDP**, **CMPEQDP**, **CMPLTDP**, **CMPGTDP**, **MPYDP**, or **SUBDP** instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.



SPDP — Convert Single-Precision Floating-Point Value to Double-Precision Floating-Point Value

www.ti.com

Instruction Type Two-cycle DP

Delay Slots 1
Functional Unit Latency 1

See Also DPSP, INTDP, SPINT, SPTRUNC

Example SPDP .S1X B2,A1:A0

Before instruction						
B2	4109 999Ah		B2	4109 999Ah		8.6
A1:A0	xxxx xxxxh	xxxx xxxxh	A1:A0	4021 3333h	4000 0000h	8.6




SPINT Convert Single-Precision Floating-Point Value to Integer

Syntax SPINT (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	xsp	.L1, .L2
dst	sint	

Description

The single-precision value in src2 is converted to an integer and placed in dst.

NOTE:

- 1. If *src2* is NaN, the maximum signed integer (7FFF FFFh or 8000 0000h) is placed in *dst* and the INVAL bit is set.
- If src2 is signed infinity or if overflow occurs, the maximum signed integer (7FFF FFFFh or 8000 0000h) is placed in dst and the INEX and OVER bits are set. Overflow occurs if src2 is greater than 2³¹ 1 or less than -2³¹.
- 3. If *src2* is denormalized, 0000 0000h is placed in *dst* and the INEX and DEN2 bits are set.
- 4. If rounding is performed, the INEX bit is set.

Execution

if (cond) $int(src2) \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2			_
Written				dst
Unit in use	.L			

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also DPINT, INTSP, SPDP, SPTRUNC



SPINT — Convert Single-Precision Floating-Point Value to Integer

www.ti.com

Example SPINT .L1 A1,A2

	Before instruction		4 cycles after instruction				
A1	4109 999Ah	A1	4109 999Ah	8.6			
A2	xxxx xxxxh	A2	0000 0009h	9			



SPKERNEL Software Pipelined Loop (SPLOOP) Buffer Operation Code Boundary

Syntax SPKERNEL (fstg, fcyc)

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Uspk	Figure H-7

Opcode

31	30	29	28	27	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	0	fstg/fcyc		0	0	0	0	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0	S	p
				6																						1	1

Description

The **SPKERNEL** instruction is placed in parallel with the last execute packet of the SPLOOP code body indicating there are no more instructions to load into the loop buffer. The **SPKERNEL** instruction also controls at what point in the epilog the execution of post-SPLOOP instructions begins. This point is specified in terms of stage and cycle counts, and is derived from the *fstg/fcyc* field.

The stage and cycle values for both the post-SPLOOP fetch and reload cases are derived from the *fstg/fcyc* field. The 6-bit field is interpreted as a function of the *ii* value from the associated **SPLOOP(D)** instruction. The number of bits allocated to stage and cycle vary according to *ii*. The value for cycle starts from the least-significant end; the value for stage starts from the most-significant end, and they grow together. The number of epilog stages and the number of cycles within those stages are shown in Table 3-28. The exact bit allocation to stage and cycle is shown in Table 3-29.

The following restrictions apply to the use of the **SPKERNEL** instruction:

- The **SPKERNEL** instruction must be the first instruction in the execute packet containing it.
- The SPKERNEL instruction cannot be placed in the same execute packet as any
 instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n
 (n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The SPKERNEL instruction cannot be placed in the execute packet immediately following an execute packet containing any instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n(n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The SPKERNEL instruction cannot be placed in parallel with DINT or RINT instructions.
- The SPKERNEL instruction cannot be placed in parallel with SPMASK, SPLOOP, SPLOOPD, or SPLOOPW instructions.
- When the **SPKERNEL** instruction is used with the **SPLOOPW** instruction, *fstg* and *fcyc* should both be zero.



NOTE: The delay specified by the SPKERNEL fstg/fcyc parameters will not extend beyond the end of the kernel epilog. If the end of the kernel epilog is reached prior to the end of the delay specified by fstg/fcyc parameters due to either an excessively large value specified for parameters or due to an early exit from the loop, program fetch will begin immediately and the value specified by the fstg/fcyc will be ignored.

Table 3-28. Field Allocation in stg/cyc Field

ii	Number of Bits for Stage	Number of Bits for Cycle
1	6	0
2	5	1
3-4	4	2
5-8	3	3
9-14	2	4

Table 3-29. Bit Allocations to Stage and Cycle in stg/cyc Field

ii	stg/cyc[5]	stg/cyc[4]	stg/cyc[3]	stg/cyc[2]	stg/cyc[1]	stg/cyc[0]
1	stage[0]	stage[1]	stage[2]	stage[3]	stage[4]	stage[5]
2	stage[0]	stage[1]	stage[2]	stage[3]	stage[4]	cycle[0]
3-4	stage[0]	stage[1]	stage[2]	stage[3]	cycle[1]	cycle[0]
5-8	stage[0]	stage[1]	stage[2]	cycle[2]	cycle[1]	cycle[0]
9-14	stage[0]	stage[1]	cycle[3]	cycle[2]	cycle[1]	cycle[0]

Execution See Chapter 7 for more information

SPKERNELR See Also



SPKERNELR Software Pipelined Loop (SPLOOP) Buffer Operation Code Boundary

Syntax SPKERNELR

unit = none

Opcode

;	31	30	_	_		_	_		-			20	_	_		_	_		_			_	-	-		-	_		-		1	0
	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	1	0	1	1	0	0	0	0	0	0	0	0	0	0	0	s	p

1

Description

The **SPKERNELR** instruction is placed in parallel with the last execute packet of the SPLOOP code body indicating there are no more instructions to load into the loop buffer. The **SPKERNELR** instruction also indicates that the execution of both post-SPLOOP instructions and instructions reloaded from the buffer begin in the first cycle of the epilog.

The following restrictions apply to the use of the **SPKERNELR** instruction:

- The SPKERNELR instruction must be the first instruction in the execute packet containing it.
- The SPKERNELR instruction cannot be placed in the same execute packet as any
 instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n
 (n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The SPKERNELR instruction cannot be placed in the execute packet immediately following an execute packet containing any instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n (n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The SPKERNELR instruction cannot be placed in parallel with DINT or RINT instructions.
- The SPKERNELR instruction cannot be placed in parallel with SPMASK, SPMASKR, SPLOOP, SPLOOPD, or SPLOOPW instructions.
- The SPKERNELR instruction can only be used when the SPLOOP instruction that began the SPLOOP buffer operation was predicated.
- The **SPKERNELR** instruction cannot be paired with an **SPLOOPW** instruction.

This instruction executes unconditionally and cannot be predicated.

Execution

See Chapter 7 for more information.

See Also

SPKERNEL



SPLOOP Software Pipelined Loop (SPLOOP) Buffer Operation


Syntax SPLOOP ii

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Uspl	Figure H-5

Opcode



Description

The **SPLOOP** instruction invokes the loop buffer mechanism. See Chapter 7 for more details.

When the **SPLOOP** instruction is predicated, it indicates that the loop is a nested loop using the SPLOOP reload capability. The decision of whether to reload is determined by the predicate register selected by the *creg* and *z* fields.

The following restrictions apply to the use of the **SPLOOP** instruction:

- The SPLOOP instruction must be the first instruction in the execute packet containing
 it
- The SPLOOP instruction cannot be placed in the same execute packet as any
 instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n
 (n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The **SPLOOP** instruction cannot be placed in parallel with **DINT** or **RINT** instructions.
- The SPLOOP instruction cannot be placed in parallel with SPMASK, SPMASKR, SPKERNEL, or SPKERNELR instructions.

Execution

See Chapter 7 for more information.

See Also

SPLOOPD, SPLOOPW



SPLOOPD Software Pipelined Loop (SPLOOP) Buffer Operation With Delayed Testing

Syntax SPLOOPD ii

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Uspl	Figure H-5
	Uspldr	Figure H-6

Opcode

3	31 29	28	27	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	ii - 1		0	0	0	0	0	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	s	р
	3	1	5																							1	1

Description

The **SPLOOPD** instruction invokes the loop buffer mechanism. The testing of the termination condition is delayed for four cycles. See Chapter 7 for more details.

When the **SPLOOPD** instruction is predicated, it indicates that the loop is a nested loop using the SPLOOP reload capability. The decision of whether to reload is determined by the predicate register selected by the *creq* and *z* fields.

The following restrictions apply to the use of the **SPLOOPD** instruction:

- The SPLOOPD instruction must be the first instruction in the execute packet containing it.
- The SPLOOPD instruction cannot be placed in the same execute packet as any
 instruction that initiates multicycle NOPs. This includes BNOP, CALLP, NOP n
 (n > 1), and protected loads (see compact instruction discussion in Section 3.10).
- The SPLOOPD instruction cannot be placed in parallel with DINT or RINT instructions.
- The SPLOOPD instruction cannot be placed in parallel with SPMASK, SPMASKR, SPKERNEL, or SPKERNELR instructions.

Execution

See Chapter 7 for more information.

See Also

SPLOOP, SPLOOPW

SPLOOPW — Software Pipelined Loop (SPLOOP) Buffer Operation With Delayed Testing and No Epilog

www.ti.com

SPLOOPW Software Pipelined Loop (SPLOOP) Buffer Operation With Delayed Testing and

No Epilog

Syntax SPLOOPW ii

unit = none

Opcode

31	29	28	27	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	∍g	Z	ii -	1	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	s	р
3		1	5	5																						1	1

Description

The **SPLOOPW** instruction invokes the loop buffer mechanism. The testing of the termination condition is delayed for four cycles. See Chapter 7 for more details.

The **SPLOOPW** instruction is always predicated. The termination condition is the value of the predicate register selected by the *creg* and *z* fields.

The following restrictions apply to the use of the **SPLOOPW** instruction:

- The SPLOOPW instruction must be the first instruction in the execute packet containing it.
- The SPLOOPW instruction cannot be placed in the same execute packet as any
 instruction that initiates multicycle NOPs. This includes BNOP, NOP n (n > 1), and
 protected loads (see compact instruction discussion in Section 3.10).
- The SPLOOPW instruction cannot be placed in parallel with DINT or RINT instructions.
- The SPLOOPW instruction cannot be placed in parallel with SPMASK, SPMASKR, SPKERNEL, or SPKERNELR instructions.

Execution See Chapter 7 for more information.

See Also SPLOOP, SPLOOPD



SPMASK

Software Pipelined Loop (SPLOOP) Buffer Operation Load/Execution Control

Syntax

SPMASK unitmask

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Uspm	Figure H-8

Opcode

							24																								
0	0	0	0	0	0	M2	M1	D2	D1	S2	S1	L2	L1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	S	р
						1	1	1	1	1	1	1	1																	1	1

Description

The **SPMASK** instruction serves two purposes within the SPLOOP mechanism:

- The SPMASK instruction inhibits the execution of specified instructions from the buffer within the current execute packet.
- The SPMASK inhibits the loading of specified instructions into the buffer during loading phase, although the instruction will execute normally.

If the SPLOOP is reloading after returning from an interrupt, the **SPMASK**ed instructions coming from the buffer execute, but the **SPMASK**ed instructions from program memory do not execute and are not loaded into the buffer.

An **SPMASK**ed instruction encountered outside of the SPLOOP mechanism shall be treated as a NOP.

The **SPMASK**ed instruction must be the first instruction in the execute packet containing it.

The SPMASK instruction cannot be placed in parallel with SPLOOP, SPLOOPD, SPKERNEL, or SPKERNELR instructions.

The **SPMASK** instruction executes unconditionally and cannot be predicated.

There are two ways to specify which instructions within the current execute packet will be masked:

- 1. The functional units of the instruction can be specified as the SPMASK argument.
- 2. The instruction to be masked can be marked with a caret (^) in the instruction code. The following three examples are equivalent:

	DEMADIC	ע, בע	_
	MV	.D2	B0,B1
	MV	.L1	A0,A1
	SPMASK	D2	
	MV	.D2	B0,B1
^	MV	.L1	A0,A1
	SPMASK		
^	MV	.D2	B0,B1
^	MV	.L1	A0,A1

SPMASK D2 L1



The following two examples mask two \mathbf{MV} instructions, but do not mask the \mathbf{MPY} instruction.

	SPMASK	D1,	D2		
	MV	.D1	A0,A1	;This unit is SPM	IASKed
Ϊİ	MV	.D2	B0,B1	;This unit is SPM	IASKed
Ħ	MPY	.L1	A0,B1	;This unit is Not	SPMASKed
	SPMASK				
^	MV	.D1	A0,A1	;This unit is SPM	IASKed
^	MV	.D2	B0,B1	;This unit is SPM	IASKed
	MPY	.L1	A0,B1	;This unit is Not	SPMASKed

Execution See Chapter 7

See Also SPMASKR



SPMASKR Software Pipelined Loop (SPLOOP) Buffer Operation Load/Execution Control

Syntax SPMASKR unitmask

unit = none

Compact Instruction Format

Unit	Opcode Format	Figure
none	Uspm	Figure H-8

Opcode

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	0	0	0	M2	M1	D2	D1	S2	S1	L2	L1	1	1	0	0	1	0	0	0	0	0	0	0	0	0	0	0	S	р
						1	1	1	1	1	1	1	1																	1	1

Description

The **SPMASKR** instruction serves three purposes within the SPLOOP mechanism. Similar to the **SPMASK** instruction:

- 1. The **SPMASKR** instruction inhibits the execution of specified instructions from the buffer within the current execute packet.
- 2. The **SPMASKR** instruction inhibits the loading of specified instructions into the buffer during loading phase, although the instruction will execute normally.

In addition to the functionality of the **SPMASK** instruction:

3. The SPMASKR instruction controls the reload point for nested loops.

The **SPMASKR** instruction is placed in the execute packet (in the post-SPKERNEL code) preceding the execute packet that will overlap with the first cycle of the reload operation.

The **SPKERNELR** and the **SPMASKR** instructions cannot coexist in the same SPLOOP operation. In the case where reload is intended to start in the first epilog cycle, the **SPKERNELR** instruction is used and the **SPMASKR** instruction is not used for that nested loop.

The **SPMASKR** instruction cannot be used in a loop using the **SPLOOPW** instruction.

An **SPMASKR** instruction encountered outside of the SPLOOP mechanism shall be treated as a NOP.

The **SPMASKR** instruction executes unconditionally and cannot be predicated.

The **SPMASKR** instruction must be the first instruction in the execute packet containing it.

The SPMASKR instruction cannot be placed in parallel with SPLOOP, SPLOOPD, SPKERNEL, or SPKERNELR instructions.



There are two ways to specify which instructions within the current execute packet will be masked:

- 1. The functional units of the instruction can be specified as the SPMASKR argument.
- 2. The instruction to be masked can be marked with a caret (^) in the instruction code. The following three examples are equivalent:

```
SPMASKR D2,L1
    MV
             .D2 B0,B1
    MV
             .L1 A0,A1
SPMASKR
             .D2 B0,B1
    MV
    MV
             .L1 A0,A1
    SPMASKR
    MV
             .D2 B0,B1
    MV
             .L1 A0,A1
```

The following two examples mask two **MV** instructions, but do not mask the **MPY** instruction. The presence of a caret (^) in the instruction code specifies which instructions are **SPMASK**ed.

```
SPMASKR D1,D2
         .D1 A0,A1
                             ;This unit is SPMASKed
MV
MV
         .D2 B0,B1
                             ;This unit is SPMASKed
         .L1 A0,B1
                             ;This unit is Ned SPMASKed
MPY
SPMASKR
         .D1 A0,A1
                             ;This unit is SPMASKED
MV
MV
         .D2 B0,B1
                             ;This unit is SPMASKED
MPY
         .L1 A0,B1
                             ;This unit is Not SPMASKed
```

Execution See Chapter 7

See Also SPMASK

Example

```
        SPMASKR

        ||^ LDW
        .D1
        *A0,A1
        ;This unit is SPMASKed

        ||^ LDW
        .D2
        *B0,B1
        ;This unit is SPMASKed

        || MPY
        .M1
        A3,A4,A5
        ;This unit is Not SPMASKed
```



SPTRUNC


Convert Single-Precision Floating-Point Value to Integer With Truncation

Syntax

SPTRUNC (.unit) src2, dst

unit = .L1 or .L2

Opcode



Opcode map field used	For operand type	Unit
src2	xsp	.L1, .L2
dst	sint	

Description

The single-precision value in *src2* is converted to an integer and placed in *dst*. This instruction operates like **SPINT** except that the rounding modes in the floating-point adder configuration register (FADCR) are ignored, and round toward zero (truncate) is always used.

NOTE:

- 1. If *src2* is NaN, the maximum signed integer (7FFF FFFh or 8000 0000h) is placed in *dst* and the INVAL bit is set.
- If src2 is signed infinity or if overflow occurs, the maximum signed integer (7FFF FFFFh or 8000 0000h) is placed in dst and the INEX and OVER bits are set. Overflow occurs if src2 is greater than 2³¹ 1 or less than -2³¹.
- If src2 is denormalized, 0000 0000h is placed in dst and INEX and DEN2 bits are set.
- 4. If rounding is performed, the INEX bit is set.

Execution

if (cond) else nop

 $int(src2) \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src2			
Written				dst
Unit in use	.L			

Instruction Type

Four-cycle

Delay Slots

3

Functional Unit Latency 1

See Also

DPTRUNC, SPDP, SPINT



SPTRUNC — Convert Single-Precision Floating-Point Value to Integer With Truncation

www.ti.com

Example SPTRUNC .L1X B1,A2

	Before instruction		4 cycles after instruction						
B1	4109 999Ah	B1	4109 999Ah	8.6					
A2	xxxx xxxxh	A2	0000 0008h	8					



SSHL Shift Left With Saturation

SSHL (.unit) src2, src1, dst **Syntax**

unit = .S1 or .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.S	Ssh5	Figure F-25
	S2sh	Figure F-26

Opcode

;	31 29	28	27 23	22 18	17 13		11	6	5	4	3	2	1	0
	creg	Z	dst	src2	src1	х	ор		1	0	0	0	s	р
	3	1	5	5	5	1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src2	xsint	.S1, .S2	10 0011
src1	uint	•	
dst	sint		
src2 src1	xsint	.S1, .S2	10 0010
src1	ucst5	•	
dst	sint		

Description

The src2 operand is shifted to the left by the src1 operand. The result is placed in dst. When a register is used to specify the shift, the 5 least-significant bits specify the shift amount. Valid values are 0 through 31, and the result of the shift is invalid if the shift amount is greater than 31. The result of the shift is saturated to 32 bits. If a saturate occurs, the SAT bit in CSR is set one cycle after dst is written.

NOTE: When a register is used to specify the shift, the 6 least-significant bits specify the shift amount. Valid values are 0 through 63. If the shift count value is greater than 32, then the result is saturated to 32 bits when src2 is non-zero.

Execution

```
if (cond)
                   if (bit(31) through bit(31 - src1) of src2 are all 1s or all 0s),
                   dst = src2 \ll src1;
                   else if (src2 > 0), saturate dst to 7FFF FFFFh;
                   else if (src2 < 0), saturate dst to 8000 0000h
                   }
else nop
```



Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.S

Instruction Type Single-cycle

Delay Slots 0

See Also ROTL, SHL, SHLMB, SHR, SSHVL

Example 1

SSHL .S1 A0,2,A1

	Before instruction		1 cycle after instruction	n	2 cycles after instructi	on
A0	02E3 031Ch	A0	02E3 031Ch	A0	02E3 031Ch	
A1	xxxx xxxxh	A1	0B8C 0C70h	A1	0B8C 0C70h	
CSR	0001 0100h	CSR	0001 0100h	CSR	0001 0100h	Not saturated
SSR	0000 0000h SSR		0000 0000h	SSR	0000 0000h	

Example 2

SSHL .S1 A0,A1,A2

	Before instruction		1 cycle after instru	uction	2 cycles after instr	uction
A0	4719 1925h	A0	4719 1925h	A0	4719 1925h	
A1	0000 0006h	A1	0000 0006h	A1	0000 0006h	
A2	xxxx xxxxh	A2	7FFF FFFFh	A2	7FFF FFFFh	
CSR	0001 0100h	CSR	0001 0100h	CSR	0001 0300h	Saturated
SSR	0000 0000h	SSR	0000 0000h	SSR	0000 0004h	



SSHVL Variable Shift Left

Syntax SSHVL (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23		18 ′		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2		src1		Х	0	1	1	1	0	0	1	1	0	0	s	р
3	1	5		5		5		1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	


Description

Shifts the signed 32-bit value in *src2* to the left or right by the number of bits specified by *src1*, and places the result in *dst*.

The *src1* argument is treated as a 2s-complement shift value which is automatically limited to the range -31 to 31. If *src1* is positive, *src2* is shifted to the left. If *src1* is negative, *src2* is shifted to the right by the absolute value of the shift amount, with the sign-extended shifted value being placed in *dst*. It should also be noted that when *src1* is negative, the bits shifted right past bit 0 are lost.

Saturation is performed when the value is shifted left under the following conditions:

- If the shifted value is in the range -2³¹ to 2³¹ 1, inclusive, then no saturation is performed, and the result is truncated to 32 bits.
- If the shifted value is greater than 2³¹ 1, then the result is saturated to 2³¹ 1.
- If the shifted value is less than 2³¹, then the result is saturated to 2³¹.



NOTE: If the shifted value is saturated, then the SAT bit is set in CSR one cycle after the result is written to dst. If the shifted value is not saturated, then the SAT bit is unaffected.



Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also SHL, SHLMB, SSHL, SSHVR

Example 1

SSHVL .M2 B2, B4, B5

	Before instruction			2 cycles after instruction
B2	FFFF F000h]	B2	FFFF F000h
B4	FFFF FFE1h	-31	B4	FFFF FFE1h
B5	xxxx xxxxh		B5	FFFF FFFFh

Example 2

SSHVL .M1 A2,A4,A5

	Before instruction			2 cycles after instru	iction
A2	F14C 2108h		A2	F14C 2108h	
A4	0000 0001Fh	31	A4	0000 0001Fh	
A5	xxxx xxxxh		A5	8000 0000h	Saturated to most negative value

Example 3

SSHVL .M2 B12, B24, B25

	Before instruction		2 cycles after instruction
B12	187A 65FCh	B12	187A 65FCh
B24	FFFF FFFFh	-1 B24	FFFF FFFFh
B25	xxxx xxxxh	B25	03CD 32FEh

496 Instruction Set SPRUFE8B-July 2010



SSHVR Variable Shift Right

Syntax SSHVR (.unit) src2, src1, dst

unit = .M1 or .M2

Opcode

31 29	28	27	23	22 18	1;		2 1	1 10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	st	src2	src1	>		0 1	1	0	1	0	1	1	0	0	s	р
3	1	5	,	5	5	1											1	1

Opcode map field used	For operand type	Unit
src1	int	.M1, .M2
src2	xint	
dst	int	


Description

Shifts the signed 32-bit value in *src2* to the left or right by the number of bits specified by *src1*, and places the result in *dst*.

The *src1* argument is treated as a 2s-complement shift value that is automatically limited to the range -31 to 31. If *src1* is positive, *src2* is shifted to the right by the value specified with the sign-extended shifted value being placed in *dst*. It should also be noted that when *src1* is positive, the bits shifted right past bit 0 are lost. If *src1* is negative, *src2* is shifted to the left by the absolute value of the shift amount value and the result is placed in *dst*.

Saturation is performed when the value is shifted left under the following conditions:

- If the shifted value is in the range -2³¹ to 2³¹ 1, inclusive, then no saturation is performed, and the result is truncated to 32 bits.
- If the shifted value is greater than 2³¹ 1, then the result is saturated to 2³¹ 1.
- If the shifted value is less than 2³¹, then the result is saturated to 2³¹.



NOTE: If the shifted value is saturated, then the SAT bit is set in CSR one cycle after the result is written to dst. If the shifted value is not saturated, then the SAT bit is unaffected.



Execution

Pipeline

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also SHR, SHR2, SHRMB, SHRU, SHRU2, SSHVL

Example 1

SSHVR .M2 B2,B4,B5

	Before instruction			2 cycles after instruction	n
B2	FFFF F000h		B2	FFFF F000h	
B4	FFFF FFE1h	-31	B4	FFFF FFE1h	
B5	xxxx xxxxh		B5	8000 0000h	Saturated to most negative value

Example 2

SSHVR .M1 A2,A4,A5

	Before instruction			2 cycles after instruction
A2	F14C 2108h		A2	F14C 2108h
A4	0000 0001Fh	31	A4	0000 0001Fh
A5	xxxx xxxxh		A5	FFFF FFFFh

Example 3

SSHVR .M2 B12, B24, B25

	Before instruction			2 cycles after instruction
B12	187A 65FCh	B1	2	187A 65FCh
B24	FFFF FFFFh	-1 B2	4	FFFF FFFFh
B25	xxxx xxxxh	B2	5	30F4 CBF8h

498 Instruction Set SPRUFE8B-July 2010



SSUB Subtract Two Signed Integers With Saturation

Syntax SSUB (.unit) src1, src2, dst

or

SSUB (.unit) src1, src2_h:src2_l, dst_h:dst_l

unit = .L1 or .L2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L3	Figure D-4

Opcode

31 29	28		23 22 1	18 17 1:	3 12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	х	ор		1	1	0	s	р
3	1	5	5	5	1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	000 1111
src2	xsint		
dst	sint		
src1	xsint	.L1, .L2	001 1111
src2	sint		
dst	sint		
src1	scst5	.L1, .L2	000 1110
src2	xsint		
dst	sint		
src1	scst5	.L1, .L2	010 1100
src2	slong	,	
dst	slong		

Description

src2 is subtracted from src1 and is saturated to the result size according to the following rules:

- 1. If the result is an int and $src1 src2 > 2^{31} 1$, then the result is $2^{31} 1$.
- 2. If the result is an int and $src1 src2 < -2^{31}$, then the result is -2^{31} .
- 3. If the result is a long and $src1 src2 > 2^{39} 1$, then the result is $2^{39} 1$.
- 4. If the result is a long and $src1 src2 < -2^{39}$, then the result is -2^{39} .

The result is placed in *dst*. If a saturate occurs, the SAT bit in CSR is set one cycle after *dst* is written.



Execution

if (cond) $src1 - s src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also SUB, SSUB2

Example 1

SSUB .L2 B1,B2,B3

	Before instruction		1 cycle after instruction				
B1	5A2E 51A3h	1,512,984,995	B1	5A2E 51A3h			
B2	802A 3FA2h	-2,144,714,846	B2	802A 3FA2h			
В3	xxxx xxxxh		В3	7FFF FFFFh	2,147,483,647		
CSR	0001 0100h		CSR	0001 0100h			
SSR	0000 0000h		SSR	0000 0000h			
			2 cycles after instruct		n		
			B1	5A2E 51A3h			
			B2	802A 3FA2h			
			В3	7FFF FFFFh			
			CSR	0001 0300h	Saturated		
			SSR	0000 0002h			



Example 2

SSUB .L1 A0,A1,A2

	Before instruction			1 cycle after instruction						
A0	4367 71F2h	1,130,852,850	A0	4367 71F2h						
A1	5A2E 51A3h	1,512,984,995	A1	5A2E 51A3h						
A2	xxxx xxxxh		A2	E939 204Fh	-382,132,145					
CSR	0001 0100h		CSR	0001 0100h						
SSR	0000 0000h		SSR	0000 0000h						
				2 cycles after instruction	n					
			A0	4367 71F2h						
			A1	5A2E 51A3h						
			A2	E939 204Fh						
			CSR	0001 0100h	Not saturated					
			SSR	0000 0000h						



SSUB₂

Subtract Two Signed 16-Bit Integers on Upper and Lower Register Halves With

Saturation

Syntax

SSUB2 (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	0	0	1	0	0	1	1	0	S	p
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	s2	.L1, .L2
src1 src2	xs2	
dst	s2	


Description

Performs 2s-complement subtraction between signed, packed 16-bit quantities in *src1* and *src2*. The results are placed in a signed, packed 16-bit format into *dst*.

For each pair of 16-bit quantities in *src1* and *src2*, the difference between the signed 16-bit value from *src1* and the signed 16-bit value from *src2* is calculated and saturated to produce a signed 16-bit result. The result is placed in the corresponding position in *dst*.

Saturation is performed on each 16-bit result independently. For each sum, the following tests are applied:

- If the difference is in the range 2¹⁵ to 2 ¹⁵ 1, inclusive, then no saturation is performed and the sum is left unchanged.
- If the difference is greater than 2¹⁵ 1, then the result is set to 2¹⁵ 1.
- If the difference is less than 2¹⁵, then the result is set to 2¹⁵.



NOTE: This operation is performed on each halfword separately. This instruction does not affect the SAT bit in CSR or the L1 or L2 bit in SSR.





```
Execution
```

```
if (cond)  \{ \\ sat(msb16(\textit{src1}) - msb16(\textit{src2})) \rightarrow msb16(\textit{dst}); \\ sat(lsb16(\textit{src1}) - lsb16(\textit{src2})) \rightarrow lsb16(\textit{dst}) \\ \} \\ else nop
```

Instruction Type Single-cycle

Delay Slots 0

See Also ADD2, SUB, SUB4, SSUB2

Examples Example 1

SSUB2 .L1 A0,A1,A2

	Before instruction	1 cycle after instruction
A0	0007 0005h	A2 0008 0006h
A1	FFFF FFFFh	

Example 2

SSUB2 .L1 A0,A1,A2

	Before instruction		1 cycle after instruction	
A0	0007 0005h	A2	7FFF 0006h	
A1	8000 FFFFh			



STB

Store Byte to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset
STB (.unit) src, *+baseR[offsetR]
unit = .D1 or .D2

Unsigned Constant Offset STB (.unit) src, *+baseR[ucst5]

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31 29	28	27	23	22	18	17 13	12		9	8	7	6	5	4	3	2	1	0
creg	Z	src		baseR		offsetR/ucst5		mode		0	У	0	1	1	0	1	s	p
3	1	5		5		5		4			1						1	1

Description

Stores a byte to memory from a general-purpose register (*src*). Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 0 bits. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is sent to memory.

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

For **STB**, the 8 LSBs of the *src* register are stored. *src* can be in either register file, regardless of the .D unit or *baseR* or *offsetR* used. The *s* bit determines which file *src* is read from: s = 0 indicates *src* will be in the A register file and s = 1 indicates *src* will be in the B register file.

Increments and decrements default to 1 and offsets default to zero when no bracketed register or constant is specified. Stores that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst*5 offset is left-shifted by 0. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.



Execution

if (cond) else nop

 $src \rightarrow mem$

Pipeline

Pipeline Stage	E1
Read	baseR, offsetR, src
Written	baseR
Unit in use	.D2

Instruction Type Store

Delay Slots 0

For more information on delay slots for a store, see Chapter 4.

See Also STH, STW

Example 1

STB .D1 A1,*A10

	Before instruction		1 cycle after instruction		3 cycles after instruction
A1	9A32 7634h	A1	9A32 7634h	A1	9A32 7634h
A10	0000 0100h	A10	0000 0100h	A10	0000 0100h
mem 100h	11h	mem 100h	11h	mem 100h	34h

Example 2

STB .D1 A8,*++A4[5]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4025h	A4	0000 4025h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
mem 4024:27h	xxxx xxxxh	mem 4024:27h	xxxx xxxxh	mem 4024:27h	xxxx 67xxh

Example 3

STB .D1 A8, *A4++[5]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4025h	A4	0000 4025h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
mem 4020:23h	xxxx xxxxh	mem 4020:23h	xxxx xxxxh	mem 4020:23h	xxxx xx67h



Example 4

STB .D1 A8,*++A4[A12]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4026h	A4	0000 4026h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
A12	0000 0006h	A12	0000 0006h	A12	0000 0006h
mem 4024:27h	xxxx xxxxh	mem 4024:27h	xxxx xxxxh	mem 4024:27h	xx67 xxxxh



STB Store Byte to Memory With a 15-Bit Unsigned Constant Offset

Syntax STB(.unit) *src*, *+B14/B15[*ucst15*]

unit = .D2

Opcode

31 29	28	27 23	22 8	7	6	5	4	3	2	1	0
creg	Z	src	ucst15	У	0	1	1	1	1	s	р
3	1	5	15	1						1	1

Description

Stores a byte to memory from a general-purpose register (src). The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction executes only on the .D2 unit.

The offset, *ucst15*, is scaled by a left-shift of 0 bits. After scaling, *ucst15* is added to *baseR*. The result of the calculation is the address that is sent to memory. The addressing arithmetic is always performed in linear mode.

For **STB**, the 8 LSBs of the *src* register are stored. *src* can be in either register file. The *s* bit determines which file *src* is read from: s = 0 indicates *src* is in the A register file and s = 1 indicates *src* is in the B register file.

Square brackets, [], indicate that the *ucst15* offset is left-shifted by 0. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Execution

if (cond) else nop

 $src \rightarrow mem$

NOTE: This instruction executes only on the B side (.D2).

Pipeline

Pipeline Stage	E1
Read	B14/B15, src
Written	
Unit in use	.D2

Instruction Type Store

Delay Slots 0

See Also STH, STW



STB — Store Byte to Memory With a 15-Bit Unsigned Constant Offset

www.ti.com

Example

STB .D2 B1,*+B14[40]

	Before instruction		1 cycle after instruction		3 cycles after instruction
B1	1234 5678h	B1	1234 5678h	B1	1234 5678h
B14	0000 1000h	B14	0000 1000h	B14	0000 1000h
mem 1028h	42h	mem 1028h	42h	mem 1028h	78h



STDW

Store Doubleword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset STDW (.unit) src, *+baseR[offsetR]

Unsigned Constant Offset STDW (.unit) src, *+baseR[ucst5]

unit = .D1 or .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4DW	Figure C-9
	DindDW	Figure C-11
	DincDW	Figure C-13
	DdecDW	Figure C-15
	Dpp	Figure C-21

Opcode

31 2		27	23		8 17	13	12		9	8	7	6	5	4	3	2	1	0
creg	Z	,	src	baseR		offsetR/ucst5		mode		1	У	1	0	0	0	1	s	p
3	1		5	5		5		4			1						1	1

Opcode map field used	For operand type	Unit
src baseR offsetR	ullong uint uint	.D1, .D2
src baseR offsetR	ullong uint ucst5	.D1, .D2

Description

Stores a 64-bit quantity to memory from a 64-bit register, *src.* Table 3-11 describes the addressing generator options. Alignment to a 64-bit boundary is required. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*). If an offset is not given, the assembler assigns an offset of zero.

Both offsetR and baseR must be in the same register file, and on the same side, as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

The offsetR/ucst5 is scaled by a left shift of 3 bits. After scaling, offsetR/ucst5 is added to, or subtracted from, baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed from memory.



The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The src pair can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file src will be loaded from: s = 0 indicates src will be in the A register file and s = 1 indicates src will be in the B register file.

Assembler Notes

When no bracketed register or constant is specified, the assembler defaults increments and decrements to 1 and offsets to 0. Stores that do no modification to the *baseR* can use the assembler syntax *R. Square brackets, [], indicate that the *ucst5* offset is left-shifted by 3 for doubleword stores.

Parentheses, (), can be used to tell the assembler that the offset is a non-scaled, constant offset. The assembler right shifts the constant by 3 bits for doubleword stores before using it for the *ucst5* field. After scaling by the **STDW** instruction, this results in the same constant offset as the assembler source if the least-significant three bits are zeros.

For example, **STDW** (.unit) src, *+baseR (16) represents an offset of 16 bytes (2 doublewords), and the assembler writes out the instruction with ucst5 = 2. **STDW** (.unit) src, *+baseR [16] represents an offset of 16 doublewords, or 128 bytes, and the assembler writes out the instruction with ucst5 = 16.

Either brackets or parentheses must be typed around the specified offset if the optional offset parameter is used. The register pair syntax always places the odd-numbered register first, a colon, followed by the even-numbered register (that is, A1:A0, B1:B0, A3:A2, B3:B2, etc.).

Execution

if (cond) else nop

 $src \rightarrow mem$

Pipeline

Pipeline Stage	E1
Read	baseR, offsetR, src
Written	baseR
Unit in use	.D

Instruction Type Store

Delay Slots

See Also LDDW, STW

www.ti.com

STDW — Store Doubleword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Example 1

STDW .D1 A3:A2,*A0++

	Before instruction			1 cycle after instruction	n
A0	0000 1000h		A0	0000 1008h	
A3:A2	A176 3B28h	6041 AD65h	A3:A2	A176 3B28h	6041 AD65h

Byte Memory Address	1009	1008	1007	1006	1005	1004	1003	1002	1001	1000
Data Value Before Store	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	00	A1	76	3B	28	60	41	AD	65

Example 2

STDW .D1 A3:A2, *A0++

	Before instruction	1		1 cycle after instr	uction
A0	0000 1004h		A0	0000 100Ch	
A3:A2	A176 3B28h	6041 AD65h	A3:A2	A176 3B28h	6041 AD65h

Byte Memory Address	100D	100C	100B	100A	1009	1008	1007	1006	1005	1004	1003
Data Value Before Store	00	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	00	A1	76	3B	28	60	41	AD	65	00

Example 3

STDW .D1 A9:A8, *++A4[5]

	Before instruction		1 cycle after instruction							
A4	0000 4020h		A4	0000 4048h						
A9:A8	ABCD EF98h	0123 4567h	A9:A8	ABCD EF98h	0123 4567h					

Byte Memory Address	4051	4050	404F	404E	404D	404C	404B	404A	4049	4048	4047
Data Value Before Store	00	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	00	AB	CD	EF	98	01	23	45	67	00



Example 4

STDW .D1 A9:A8, *++A4(16)

	Before instruction			1 cycle after instruction	n
A4	0000 4020h		A4	0000 4030h	
A9:A8	ABCD EF98h	0123 4567h	A9:A8	ABCD EF98h	0123 4567h

Byte Memory Address	4039	4038	4037	4036	4035	4034	4033	4032	4031	4030	402F
Data Value Before Store	00	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	00	AB	CD	EF	98	01	23	45	67	00

Example 5

STDW .D1 A9:A8, *++A4[A12]

	Before instruction			on	
A4	0000 4020h		A4	0000 4030h	
A9:A8	ABCD EF98h	0123 4567h	A9:A8	ABCD EF98h	0123 4567h
A12	0000 0006h		A12	0000 0006h	

Byte Memory Address	4059	4058	4057	4056	4055	4054	4053	4052	4051	4050	404F
Data Value Before Store	00	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	00	AB	CD	EF	98	01	23	45	67	00



STH

Store Halfword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset STH (.unit) src, *+baseR[offsetR] Unsigned Constant Offset STH (.unit) src, *+baseR[ucst5]

Compact Instruction Format

unit = .D1 or .D2

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31	29	28	27	23	22	18	17 13	3	12	9	8	7	6	5	4	3	2	1	0
cre	g	Z		src	baseR		offsetR/ucst5		mode		0	У	1	0	1	0	1	s	p
3		1		5	5		5		4			1						1	1

Description

Stores a halfword to memory from a general-purpose register (*src*). Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 1 bit. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is sent to memory.

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

For **STH**, the 16 LSBs of the *src* register are stored. *src* can be in either register file, regardless of the .D unit or *baseR* or *offsetR* used. The *s* bit determines which file *src* is read from: s = 0 indicates *src* will be in the A register file and s = 1 indicates *src* will be in the B register file.

Increments and decrements default to 1 and offsets default to zero when no bracketed register or constant is specified. Stores that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst*5 offset is left-shifted by 1. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Halfword addresses must be aligned on halfword (LSB is 0) boundaries.



Execution

if (cond) $src \rightarrow mem$ else nop

Pipeline

Pipeline Stage	E1
Read	baseR, offsetR, src
Written	baseR
Unit in use	.D2

Instruction Type Store

Delay Slots 0

For more information on delay slots for a store, see Chapter 4.

See Also STB, STW

Example 1

STH .D1 A1,*+A10(4)

	Before instruction		1 cycle after instruction		3 cycles after instruction
A1	9A32 7634h	A1	9A32 7634h	A1	9A32 7634h
B10	0000 1000h	A10	0000 1000h	A10	0000 1000h
mem 104h	1134h	mem 104h	1134h	mem 104h	7634h

Example 2

STH .D1 A1, *A10--[A11]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A1	9A32 2634h	A1	9A32 2634h	A1	9A32 2634h
A10	0000 0100h	A10	0000 00F8h	A10	0000 00F8h
A11	0000 0004h	A11	0000 0004h	A11	0000 0004h
mem F8h	0000h	mem F8h	0000h	mem F8h	0000h
mem 100h	0000h	mem 100h	0000h	mem 100h	2634h



STH Store Halfword to Memory With a 15-Bit Unsigned Constant Offset

Syntax STH(.unit) *src*, *+B14/B15[*ucst15*]

unit = .D2

Opcode

31	29	28	27	23	22	;	8 7	7	6	5	4	3	2	1	0
creg	9	Z	S	src		ucst15	ز	/	1	0	1	1	1	s	р
3		1		5		15	,						-	1	1

Description

Stores a halfword to memory from a general-purpose register (src). The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction executes only on the .D2 unit.

The offset, *ucst15*, is scaled by a left-shift of 1 bit. After scaling, *ucst15* is added to *baseR*. The result of the calculation is the address that is sent to memory. The addressing arithmetic is always performed in linear mode.

For **STH**, the 16 LSBs of the *src* register are stored. *src* can be in either register file. The *s* bit determines which file *src* is read from: s = 0 indicates *src* is in the A register file and s = 1 indicates *src* is in the B register file.

Square brackets, [], indicate that the *ucst15* offset is left-shifted by 1. Parentheses, (), can be used to set a nonscaled, constant offset. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Halfword addresses must be aligned on halfword (LSB is 0) boundaries.

Execution

if (cond) else nop

 $src \rightarrow mem$

NOTE: This instruction executes only on the B side (.D2).

Pipeline

Pipeline Stage	E1					
Read	B14/B15, src					
Written						
Unit in use	.D2					

Instruction Type Store

Delay Slots 0

See Also STB, STW



STNDW

Store Nonaligned Doubleword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset STNDW (.unit) src, *+baseR[offsetR] unit = .D1 or .D2 Unsigned Constant Offset STNDW (.unit) src, *+baseR[ucst5]

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4DW	Figure C-9
	DindDW	Figure C-11
	DincDW	Figure C-13
	DdecDW	Figure C-15

Opcode

31	29	28	27	24	23	22	18	17	13	12		9	8	7	6	5	4	3	2	1	0
cre	eg	Z		src	SC		baseR		offsetR/ucst5		mode		1	У	1	1	1	0	1	s	p
9	3	1		4	1		5		5		4			1						1	1

Opcode map field used	For operand type	Unit		
src baseR offsetR	ullong uint uint	.D1, .D2		
src baseR offsetR	ullong uint ucst5	.D1, .D2		

Description

Stores a 64-bit quantity to memory from a 64-bit register pair, *src.* Table 3-11 describes the addressing generator options. The **STNDW** instruction may write a 64-bit value to any byte boundary. Thus alignment to a 64-bit boundary is not required. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

Both offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

The **STNDW** instruction supports both scaled offsets and non-scaled offsets. The *sc* field is used to indicate whether the *offsetR/ucst5* is scaled or not. If *sc* is 1 (scaled), the *offsetR/ucst5* is shifted left 3 bits before adding or subtracting from the *baseR*. If *sc* is 0 (nonscaled), the *offsetR/ucst5* is not shifted before adding to or subtracting from the *baseR*. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or post-decrement addressing, the value of *baseR* before the addition or subtraction is the address to be accessed from memory.



STNDW — Store Nonaligned Doubleword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset www.ti.com

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The src pair can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file src will be loaded from: s = 0 indicates src will be in the A register file and s = 1 indicates src will be in the B register file.

NOTE: No other memory access may be issued in parallel with a nonaligned memory access. The other .D unit can be used in parallel, as long as it is not performing a memory access.

Assembler Notes

When no bracketed register or constant is specified, the assembler defaults increments and decrements to 1, and offsets to 0. Loads that do no modification to the baseR can use the assembler syntax *R. Square brackets, [], indicate that the ucst5 offset is left-shifted by 3 for doubleword stores.

Parentheses, (), can be used to indicate to the assembler that the offset is a nonscaled offset.

For example, STNDW (.unit) src, *+baseR (12) represents an offset of 12 bytes and the assembler writes out the instruction with offsetC = 12 and sc = 0.

STNDW (.unit) src, *+baseR [16] represents an offset of 16 doublewords, or 128 bytes, and the assembler writes out the instruction with offsetC = 16 and sc = 1.

Either brackets or parentheses must be typed around the specified offset if the optional offset parameter is used.

Execution

if (cond) else nop $src \rightarrow mem$

Pipeline

Pipeline Stage	E1						
Read	baseR, offsetR, src						
Written	baseR						
Unit in use	.D						

Instruction Type Store

Delay Slots 0

See Also LDNW, LDNDW, STNW



STNDW — Store Nonaligned Doubleword to Memory With a 5-Bit Unsigned Constant Offset or Register Offset www.ti.com

Example 1

STNDW .D1 A3:A2, *A0++

	Before instruction			1 cycle after instructio	n
A0	0000 1001h		A0	0000 1009h	
A3	A176 3B28h	6041 AD65h	A3:A2	A176 3B28h	6041 AD65h

Byte Memory Address	1009	1008	1007	1006	1005	1004	1003	1002	1001	1000
Data Value Before Store	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	A1	76	3B	28	60	41	AD	65	00

Example 2

STNDW .D1 A3:A2, *A0++

	Before instruction	1		1 cycle after instr	uction
A0	0000 1003h		A0	0000 100Bh	
A3:A2	A176 3B28h	6041 AD65h	A3:A2	A176 3B28h	6041 AD65h

Byte Memory Address	100B	100A	1009	1008	1007	1006	1005	1004	1003	1002	1001	1000
Data Value Before Store	00	00	00	00	00	00	00	00	00	00	00	00
Data Value After Store	00	A1	76	3B	28	60	41	AD	65	00	00	00

518 Instruction Set SPRUFE8B-July 2010



STNW

Store Nonaligned Word to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset STNW (.unit) src, *+baseR[offsetR] unit = .D1 or .D2 Unsigned Constant Offset STNW (.unit) src, *+baseR[ucst5]

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31	29	28	27	23	22	18	17 13	12	2	9	8	7	6	5	4	3	2	1	0
	creg	Z		src	baseR		offsetR/ucst5		mode		1	У	1	0	1	0	1	s	р
	3	1		5	5		5		4			1						1	1

Opcode map field used For operand type		Unit
src	uint	.D1, .D2
baseR	uint	
offsetR	uint	
src	uint	.D1, .D2
baseR	uint	
offsetR	ucst5	

Description

Stores a 32-bit quantity to memory from a 32-bit register, *src.* Table 3-11 describes the addressing generator options. The **STNW** instruction may write a 32-bit value to any byte boundary. Thus alignment to a 32-bit boundary is not required. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

Both offsetR and baseR must be in the same register file, and on the same side, as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

The offsetR/ucst5 is scaled by a left shift of 2 bits. After scaling, offsetR/ucst5 is added to, or subtracted from, baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is the address to be accessed from memory.



The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

The src can be in either register file, regardless of the .D unit or baseR or offsetR used. The s bit determines which file src will be loaded from: s = 0 indicates src will be in the A register file and s = 1 indicates src will be in the B register file.

NOTE: No other memory access may be issued in parallel with a nonaligned memory access. The other .D unit can be used in parallel as long as it is not performing memory access.

Assembler Notes

When no bracketed register or constant is specified, the assembler defaults increments and decrements to 1 and offsets to 0. Loads that do no modification to the baseR can use the assembler syntax *R. Square brackets, [], indicate that the ucst5 offset is left-shifted by 2 for word stores.

Parentheses, (), can be used to tell the assembler that the offset is a non-scaled, constant offset. The assembler right shifts the constant by 2 bits for word stores before using it for the ucst5 field. After scaling by the STNW instruction, this results in the same constant offset as the assembler source if the least-significant two bits are zeros.

For example, **STNW** (.unit) src,*+baseR (12) represents an offset of 12 bytes (3 words), and the assembler writes out the instruction with ucst5 = 3.

STNW (.unit) src,*+baseR [12] represents an offset of 12 words, or 48 bytes, and the assembler writes out the instruction with ucst5 = 12.

Either brackets or parentheses must be typed around the specified offset if the optional offset parameter is used.

Execution

if (cond) else nop

 $src \rightarrow mem$

Pipeline

Pipeline Stage	E1
Read	baseR, offsetR, src
Written	baseR
Unit in use	.D

Instruction Type Store

Delay Slots 0

See Also LDNW, LDNDW, STNDW



www.ti.com STNW — Store Nonaligned Word to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Examples

Example 1

STNW .D1 A3, *A0++

	Before instruction	1 cycle after instruction
A0	0000 1001h	A0 0000 1005h
А3	A176 3B28h	A3 A176 3B28h

Byte Memory Address	1007	1006	1005	1004	1003	1002	1001	1000
Data Value Before Store	00	00	00	00	00	00	00	00
Data Value After Store	00	00	00	A1	76	3B	28	00

Example 2

STNW .D1 A3, *A0++

	Before instruction	1 cycle after instruction
A0	0000 1003h	A0 0000 1007h
А3	A176 3B28h	A3 A176 3B28h

Byte Memory Address	1007	1006	1005	1004	1003	1002	1001	1000
Data Value Before Store	00	00	00	00	00	00	00	00
Data Value After Store	00	A1	76	3B	28	00	00	00



STW

Store Word to Memory With a 5-Bit Unsigned Constant Offset or Register Offset

Syntax

Register Offset
STW (.unit) src, *+baseR[offsetR]

Unsigned Constant Offset STW (.unit) src, *+baseR[ucst5]

Compact Instruction Format

unit = .D1 or .D2

Unit	Opcode Format	Figure
.D	Doff4	Figure C-8
	Dind	Figure C-10
	Dinc	Figure C-12
	Ddec	Figure C-14

Opcode

31	29	28	27	23	22	18	17 1	3	12	9	8	7	6	5	4	3	2	1	0
С	reg	Z		src	baseR		offsetR/ucst5		mode		0	У	1	1	1	0	1	s	р
	3	1		5	5		5		4			1						1	1

Description

Stores a word to memory from a general-purpose register (*src*). Table 3-11 describes the addressing generator options. The memory address is formed from a base address register (*baseR*) and an optional offset that is either a register (*offsetR*) or a 5-bit unsigned constant (*ucst5*).

offsetR and baseR must be in the same register file and on the same side as the .D unit used. The y bit in the opcode determines the .D unit and register file used: y = 0 selects the .D1 unit and baseR and offsetR from the A register file, and y = 1 selects the .D2 unit and baseR and offsetR from the B register file.

offsetR/ucst5 is scaled by a left-shift of 2 bits. After scaling, offsetR/ucst5 is added to or subtracted from baseR. For the preincrement, predecrement, positive offset, and negative offset address generator options, the result of the calculation is the address to be accessed in memory. For postincrement or postdecrement addressing, the value of baseR before the addition or subtraction is sent to memory.

The addressing arithmetic that performs the additions and subtractions defaults to linear mode. However, for A4-A7 and for B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).

For **STW**, the entire 32-bits of the *src* register are stored. *src* can be in either register file, regardless of the .D unit or *baseR* or *offsetR* used. The *s* bit determines which file *src* is read from: s = 0 indicates *src* will be in the A register file and s = 1 indicates *src* will be in the B register file.

Increments and decrements default to 1 and offsets default to zero when no bracketed register or constant is specified. Stores that do no modification to the *baseR* can use the syntax *R. Square brackets, [], indicate that the *ucst*5 offset is left-shifted by 2. Parentheses, (), can be used to set a nonscaled, constant offset. For example, **STW** (.unit) *src*, *+*baseR*(12) represents an offset of 12 bytes; whereas, **STW** (.unit) *src*, *+*baseR*[12] represents an offset of 12 words, or 48 bytes. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Word addresses must be aligned on word (two LSBs are 0) boundaries.



Execution

if (cond) else nop

 $src \rightarrow mem$

Pipeline

Pipeline Stage	E1
Read	baseR, offsetR, src
Written	baseR
Unit in use	.D2

Instruction Type Store

Delay Slots 0

For more information on delay slots for a store, see Chapter 4.

See Also STB, STH

Example 1

STW .D1 A1,*++A10[1]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A1	9A32 7634h	A1	9A32 7634h	A1	9A32 7634h
A10	0000 0100h	A10	0000 0104h	A10	0000 0104h
mem 100h	1111 1134h	mem 100h	1111 1134h	mem 100h	1111 1134h
mem 104h	0000 1111h	mem 104h	0000 1111h	mem 104h	9A32 7634h

Example 2

STW .D1 A8,*++A4[5]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4034h	A4	0000 4034h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh
mem 4034h	xxxx xxxxh	mem 4034h	xxxx xxxxh	mem 4034h	0123 4567h



Example 3

STW .D1 A8,*++A4(8)

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4028h	A4	0000 4028h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh
mem 4028h	xxxx xxxxh	mem 4028h	xxxx xxxxh	mem 4028h	0123 4567h

Example 4

STW .D1 A8,*++A4[A12]

	Before instruction		1 cycle after instruction		3 cycles after instruction
A4	0000 4020h	A4	0000 4038h	A4	0000 4038h
A8	0123 4567h	A8	0123 4567h	A8	0123 4567h
A12	0000 0006h	A12	0000 0006h	A12	0000 0006h
mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh	mem 4020h	xxxx xxxxh
mem 4038h	xxxx xxxxh	mem 4038h	xxxx xxxxh	mem 4038h	0123 4567h



STW

Store Word to Memory With a 15-Bit Unsigned Constant Offset

Syntax

STW(.unit) *src*, *+B14/B15[*ucst15*]

unit = .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Dstk	Figure C-16
	Dpp	Figure C-21

Opcode

31	29	28	27	23	22 8	7	6	5	4	3	2	1	0
creg		Z		src	ucst15	У	1	1	1	1	1	s	р
3	•	1		5	15	1		·			·	1	1

Description

Stores a word to memory from a general-purpose register (src). The memory address is formed from a base address register B14 (y = 0) or B15 (y = 1) and an offset, which is a 15-bit unsigned constant (ucst15). The assembler selects this format only when the constant is larger than five bits in magnitude. This instruction executes only on the .D2 unit.

The offset, *ucst15*, is scaled by a left-shift of 2 bits. After scaling, *ucst15* is added to *baseR*. The result of the calculation is the address that is sent to memory. The addressing arithmetic is always performed in linear mode.

For **STW**, the entire 32-bits of the *src* register are stored. *src* can be in either register file. The *s* bit determines which file *src* is read from: s = 0 indicates *src* is in the A register file and s = 1 indicates *src* is in the B register file.

Square brackets, [], indicate that the *ucst15* offset is left-shifted by 2. Parentheses, (), can be used to set a nonscaled, constant offset. For example,

STW (.unit) src, *+B14/B15(60) represents an offset of 12 bytes; whereas,

STW (.unit) *src*, *+B14/B15[60] represents an offset of 60 words, or 240 bytes. You must type either brackets or parentheses around the specified offset, if you use the optional offset parameter.

Word addresses must be aligned on word (two LSBs are 0) boundaries.

Execution

if (cond) else nop $src \rightarrow mem$

NOTE: This instruction executes only on the B side (.D2).



Pipeline

Pipeline Stage	E1
Read	B14/B15, src
Written	
Unit in use	.D2

Instruction Type Store

Delay Slots 0

See Also STB, STH



SUB

Subtract Two Signed Integers Without Saturation

Syntax

SUB (.unit) src1, src2, dst

SUB (.L1 or .L2) src1, src2, dst_h:dst_l

SUB (.D1 or .D2) *src2*, *src1*, *dst* (if the cross path form is not used)

or

SUB (.D1 or .D2) *src1*, *src2*, *dst* (if the cross path form is used)

unit = .D1, .D2, .L1, .L2, .S1, .S2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L3	Figure D-4
	Lx1	Figure D-11
.S	S3	Figure F-22
	Sx2op	Figure F-29
	Sx1	Figure F-31
.D	Dx2op	Figure C-17
	Dx1	Figure C-20

NOTE: Subtraction with a signed constant on the .L and .S units allows either the first or the second operand to be the signed 5-bit constant.

> SUB (.unit) src1, scst5, dst is encoded as ADD (.unit) -scst5, src2, dst where the src1 register is now src2 and scst5 is now -scst5.

The .D unit, when the cross path form is not used, provides only the second operand as a constant since it is an unsigned 5-bit constant. ucst5 allows a greater offset for addressing with the .D unit.



SUB — Subtract Two Signed Integers Without Saturation

www.ti.com

Орсо	de			.L unit														
31	29	28	27	23	22	18	17		13	12	11		5	4	3	2	1	0
CI	reg	Z		dst	src2			src1		Х		ор		1	1	0	s	p
	3	1		5	5			5		1		7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.L1, .L2	000 0111
src2	xsint		
dst	sint		
src1	xsint	.L1, .L2	001 0111
src2	sint		
dst	sint		
src1	sint	.L1, .L2	010 0111
src2	xsint		
dst	slong		
src1	xsint	.L1, .L2	011 0111
src2	sint		
dst	slong		
src1	scst5	.L1, .L2	000 0110
src2	xsint		
dst	sint		
src1	scst5	.L1, .L2	010 0100
src2	slong		
dst	slong		





Орс	ode			.S unit															
31	29	28	27	23	22	1	8	17	13	12	11		6	5	4	3	2	1	0
	creg	Z		dst		src2		src1		х		ор		1	0	0	0	s	р
	3	1		5		5		5		1		6						1	1

Opcode map field used	For operand type	Unit	Opfield
src1	sint	.S1, .S2	01 0111
src2	xsint	•	
dst	sint		
src1	scst5	.S1, .S2	01 0110
src2	xsint	•	
dst	sint		

src2 - src1:

31 29	28	27	23	22 18	17	13	12	11	10	9 8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	0 1	0	1	1	1	0	0	s	р
3	1	5		5	5		1										1	1

Opcode map field used	For operand type	Unit
src2	xsint	.S1, .S2
src1	sint	
dst	sint	

Description for .L1, .L2 and .S1, .S2 Opcodes src2 is subtracted from src1. The result is placed in dst.

Execution for .L1, .L2 and .S1, .S2 Opcodes

if (cond)
$$src1 - src2 \rightarrow dst$$
 else nop



SUB — Subtract Two Signed Integers Without Saturation

www.ti.com

Opcode	.D unit (if the cross path form is not
--------	--

31 29	28		23 22 18	3 17 13	12	7	6	5	4	3	2	1	0
creg	Z	dst	src2	src1	ор		1	0	0	0	0	s	р
3	1	5	5	5	6							1	1

used)

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	01 0001
src2 src1 dst	sint ucst <i>5</i> sint	.D1, .D2	01 0011

Description *src1* is subtracted from *src2*. The result is placed in *dst*.

Execution

if (cond) $src2 - src1 \rightarrow dst$

else nop

Opcode .D unit (if the cross path form is used)

31	29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2	src1		Х	1	0	1	1	0	0	1	1	0	0	s	р
3		1		5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	sint	.D1, .D2
src1 src2	xsint	
dst	sint	

Description src2 is subtracted from src1. The result is placed in dst.

Execution

if (cond) $src1 - src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D





Instruction Type Single-cycle

Delay Slots 0

See Also ADD, NEG, SUBC, SUBU, SSUB, SUB2

Example SUB .L1 A1,A2,A3

	Before instruction			1 cycle after instruction	
A1	0000 325Ah	12,890	A1	0000 325Ah	
A2	FFFF FF12h	-238	A2	FFFF FF12h	
А3	xxxx xxxxh		A3	0000 3348h	13,128



SUBAB Subtract Using Byte Addressing Mode

Syntax SUBAB (.unit) src2, src1, dst

unit = .D1 or .D2

Opcode

31 29	28	27	23	22 18) 1/	3 12		7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		ор		1	0	0	0	0	s	р
3	1	5		5	5		6							1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	11 0001
src2 src1 dst	sint ucst5 sint	.D1, .D2	11 0011

Description

src1 is subtracted from *src2* using the byte addressing mode specified for *src2*. The subtraction defaults to linear mode. However, if *src2* is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3).The result is placed in *dst*.

Execution

if (cond)

else nop

 $src2 - src1 \rightarrow dst$

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also SUB, SUBAH, SUBAW





Example SUBAB .D1 A5,A0,A5

	Before instruction (1)	1 cycle after instruction			
A0	0000 0004h	Α0	0000 0004h		
A5	0000 4000h	A5	0000 400Ch		
AMR	0003 0004h	AMR	0003 0004h		

⁽¹⁾ BK0 = 3 → size = 16 A5 in circular addressing mode using BK0



SUBABS4

Subtract With Absolute Value, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

SUBABS4 (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst	!	src2	src1		Х	1	0	1	1	0	1	0	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	u4	.L1, .L2
src2	xu4	
dst	u4	

Description

Calculates the absolute value of the differences between the packed 8-bit data contained in the source registers. The values in *src1* and *src2* are treated as unsigned, packed 8-bit quantities. The result is written into *dst* in an unsigned, packed 8-bit format.

For each pair of unsigned 8-bit values in *src1* and *src2*, the absolute value of the difference is calculated. This result is then placed in the corresponding position in *dst*.

- The absolute value of the difference between *src1* byte0 and *src2* byte0 is placed in byte0 of *dst*.
- The absolute value of the difference between *src1* byte1 and *src2* byte1 is placed in byte1 of *dst*.
- The absolute value of the difference between *src1* byte2 and *src2* byte2 is placed in byte2 of *dst*.
- The absolute value of the difference between *src1* byte3 and *src2* byte3 is placed in byte3 of *dst*.

The **SUBABS4** instruction aids in motion-estimation algorithms, and other algorithms, that compute the "best match" between two sets of 8-bit quantities.

31	24	23 16	6 15	8 7	0
	ua_3	ua_2	ua_1	ua_	_0 ← src1
	-	-	-	-	·
		SUE	BABS4		
	ub_3	ub_2	ub_1	ub_	_0 ← src2
	=	=	=	=	:
31	24	23 16	6 15	8 7	0
	abs(ua_3 - ub_3)	abs(ua_2 - ub_2)	abs(ua_1 - u	b_1) abs(ua_0) - ub_0) ← dst



Execution

```
if (cond)  \{ \\ abs(ubyte0(\textit{src1}) - ubyte0(\textit{src2})) \rightarrow ubyte0(\textit{dst}); \\ abs(ubyte1(\textit{src1}) - ubyte1(\textit{src2})) \rightarrow ubyte1(\textit{dst}); \\ abs(ubyte2(\textit{src1}) - ubyte2(\textit{src2})) \rightarrow ubyte2(\textit{dst}); \\ abs(ubyte3(\textit{src1}) - ubyte3(\textit{src2})) \rightarrow ubyte3(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ABS, SUB, SUB4

Example SUBABS4 .L1 A2, A8, A9

	Before instruction			1 cycle after instruction	
A2	37 89 F2 3Ah	55 137 242 58 unsigned	A2	37 89 F2 3Ah	
A8	04 B8 49 75h	4 184 73 117 unsigned	A8	04 B8 49 75h	
A9	xxxx xxxxh		A9	33 2F A9 3Bh	51 47 169 59 unsigned



SUBAH Subtract Using Halfword Addressing Mode

Syntax SUBAH (.unit) src2, src1, dst

unit = .D1 or .D2

Opcode

31 29	28	27	23 22	18	17 1:	3 17		7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		ор		1	0	0	0	0	S	p
3	1	5		5	5		6							1	1

Opcode map field used	For operand type	Unit	Opfield
src2 src1 dst	sint sint sint	.D1, .D2	11 0101
src2 src1 dst	sint ucst5 sint	.D1, .D2	11 0111

Description

src1 is subtracted from *src2* using the halfword addressing mode specified for *src2*. The subtraction defaults to linear mode. However, if *src2* is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3). *src1* is left shifted by 1. The result is placed in *dst*.

Execution

if (cond)

 $src2 - src1 << 1 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also SUB, SUBAB, SUBAW





SUBAW Subtract Using Word Addressing Mode

Syntax SUBAW (.unit) src2, src1, dst

unit = .D1 or .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.D	Dx5p	Figure C-19

Opcode

31 29	28	27	23	22 18		13	12	7	6	5	4	3	2	1	0
creg	z	dst		src2	SI	rc1		ор	1	0	0	0	0	s	p
3	1	5		5		5		6						1	1

Opcode map field used	For operand type	Unit	Opfield		
src2	sint	.D1, .D2	11 1001		
src1	sint				
dst	sint				
src2	sint	.D1, .D2	11 1011		
src1	ucst5				
dst	sint				

Description

src1 is subtracted from src2 using the word addressing mode specified for src2. The subtraction defaults to linear mode. However, if src2 is one of A4-A7 or B4-B7, the mode can be changed to circular mode by writing the appropriate value to the AMR (see Section 2.8.3). src1 is left shifted by 2. The result is placed in dst.

Execution

if (cond) $src2 - src1 << 2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E 1
Read	src1, src2
Written	dst
Unit in use	.D

Instruction Type Single-cycle

Delay Slots 0

See Also SUB, SUBAB, SUBAH

SUBAW — Subtract Using Word Addressing Mode

www.ti.com

Example SUBAW .D1 A5,2,A3

	Before instruction (1)	1 cycle after instruction			
A3	xxxx xxxxh	A3	0000 0108h		
A5	0000 0100h	A5	0000 0100h		
AMR	0003 0004h	AMR	0003 0004h		

BK0 = 3 → size = 16
A5 in circular addressing mode using BK0



SUBC Subtract Conditionally and Shift—Used for Division

Syntax SUBC (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	0	0	1	0	1	1	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.L1, .L2
src2	xuint	
dst	uint	

Description

Subtract *src2* from *src1*. If result is greater than or equal to 0, left shift result by 1, add 1 to it, and place it in *dst*. If result is less than 0, left shift *src1* by 1, and place it in *dst*. This step is commonly used in division.

Execution

Pipeline

Pipeline Stage	E 1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ADD, SSUB, SUB, SUBDP, SUBSP, SUBU, SUB2



SUBC — Subtract Conditionally and Shift—Used for Division

www.ti.com

Example 1

SUBC .L1 A0,A1,A0

	Before instruction			1 cycle after instruction	
A0	0000 125Ah	4698	A0	0000 024B4h	9396
A1	0000 1F12h	7954	A1	0000 1F12h	

Example 2

SUBC .L1 A0,A1,A0

	Before instruction			1 cycle after instruction				
A0	0002 1A31h	137,777	A0	0000 47E5h	18,405			
A1	0001 F63Fh 128,575		A1	0001 F63Fh				

540 Instruction Set SPRUFE8B-July 2010



SUBDP

Subtract Two Double-Precision Floating-Point Values

Syntax

SUBDP (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode

31 29	28	27 23	22 18	17 13	12	11	5 4	3	3 2	1	0
creg	Z	dst	src2	src1	Х	ор	1	1	0	s	р
3	1	5	5	5	1	7				1	1

Opcode map field used	For operand type	Unit	Opfield	
src1	dp	.L1, .L2	001 1001	
src2	xdp			
dst	dp			
src1	xdp	.L1, .L2	001 1101	
src2	dp			
dst	dp			
src1	dp	.S1, .S2	111 0011	
src2	xdp			
dst	dp			
src1	dp	.S1, .S2	111 0111	
src2	xdp	•	src2 - src1	
dst	dp			

NOTE: The assembly syntax allows a cross-path operand to be used for either src1 or src2. The assembler selects between the two opcodes based on which source operand in the assembly instruction requires the cross path. If src1 requires the cross path, the assembler chooses the second (reverse) form of the instruction syntax and reverses the order of the operands in the encoded instruction.

Description

src2 is subtracted from src1. The result is placed in dst.

NOTE:

- 1. This instruction takes the rounding mode from and sets the warning bits in the floating-point adder configuration register (FADCR), not the floating-point auxiliary configuration register (FAUCR) as for other .S unit instructions.
- The source specific warning bits set in FADCR are set according to the registers sources in the actual machine instruction and not according to the order of the sources in the assembly form.
- If rounding is performed, the INEX bit is set.
- If one source is SNaN or QNaN, the result is NaN_out. If either source is SNaN, the INVAL bit is set also.
- If both sources are +infinity or -infinity, the result is NaN_out and the INVAL bit is set.
- If one source is signed infinity and the other source is anything except NaN or signed infinity of the same sign, the result is signed infinity and the INFO bit is set.
- If overflow occurs, the INEX and OVER bits are set and the results are set as follows (LFPN is the largest floating-point number):



		Overflow Output	Rounding Mode	
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+infinity	+LFPN	+infinity	+LFPN
-	-infinity	-LFPN	-LFPN	-infinity

If underflow occurs, the INEX and UNDER bits are set and the results are set as follows (SPFN is the smallest floating-point number):

	Underflow Output Rounding Mode						
Result Sign	Nearest Even	Zero	+Infinity	Infinity			
+	+0	+0	+SFPN	+0			
-	-0	-0	-0	-SFPN			

- If the sources are equal numbers of the same sign, the result is +0
 unless the rounding mode is -infinity, in which case the result is -0.
- 10. the sources are both 0 with opposite signs or both denormalized with opposite signs, the sign of the result is the same as the sign of *src1*.
- 11. A signed denormalized source is treated as a signed 0 and the DENn bit is set. If the other source is not NaN or signed infinity, the INEX bit is also set.

Execution

if (cond) else nop

 $src1 - src2 \rightarrow dst$

Pipeline

Pipeline Stage	E1	E2	E3	E4	E5	E6	E 7
Read	src1_l, src2_l	src1_h, src2_h					
Written						dst_l	dst_h
Unit in use	.L or .S	.L or .S					

The low half of the result is written out one cycle earlier than the high half. If *dst* is used as the source for the ADDDP, CMPEQDP, CMPLTDP, CMPGTDP, MPYDP, MPYSPDP, MPYSP2DP, or SUBDP instruction, the number of delay slots can be reduced by one, because these instructions read the lower word of the DP source one cycle before the upper word of the DP source.

Instruction Type ADDDP/SUBDP

Delay Slots 6
Functional Unit Latency 2

See Also ADDDP, SUB, SUBSP, SUBU





Example SUBDP .L1X B1:B0,A3:A2,A5:A4

	Before instruction	n		7 cycles after ins	truction	
B1:B0	4021 3333h	3333 3333h	B1:B0	4021 3333h	4021 3333h	8.6
A3:A2	C004 0000h	0000 0000h	A3:A2	C004 0000h	0000 0000h	-2.5
A5:A4	xxxx xxxxh	xxxx xxxxh	A5:A4	4026 3333h	3333 3333h	11.1



SUBSP

Subtract Two Single-Precision Floating-Point Values

Syntax

SUBSP (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2

Opcode

31 29	28	27	23	22 18		13 12	11	5 4	3	2	1	0
creg	Z	dst	•	src2	src1	х		op 1	1	0	s	р
3	1	5		5	5	1		7			1	1

Opcode map field used	For operand type	Unit	Opfield	
src1	sp	.L1, .L2	001 0001	
src2	xsp			
dst	sp			
src1	xsp	.L1, .L2	001 0101	
src2	sp			
dst	sp			
src1	sp	.S1, .S2	111 0001	
src2	xsp			
dst	sp			
src1	sp	.S1, .S2	111 0101	
src2	xsp	,	src2 - src1	
dst	sp			

NOTE: The assembly syntax allows a cross-path operand to be used for either src1or src2. The assembler selects between the two opcodes based on which source operand in the assembly instruction requires the cross path. If src1 requires the cross path, the assembler chooses the second (reverse) form of the instruction syntax and reverses the order of the operands in the encoded instruction.

Description

src2 is subtracted from src1. The result is placed in dst.

NOTE:

- This instruction takes the rounding mode from and sets the warning bits in the floating-point adder configuration register (FADCR), not the floating-point auxiliary configuration register (FAUCR) as for other .S unit instructions.
- The source specific warning bits set in FADCR are set according to the registers sources in the actual machine instruction and not according to the order of the sources in the assembly form.
- If rounding is performed, the INEX bit is set.
- If one source is SNaN or QNaN, the result is NaN_out. If either source is SNaN, the INVAL bit is set also.
- If both sources are +infinity or -infinity, the result is NaN_out and the INVAL bit is set.
- If one source is signed infinity and the other source is anything except NaN or signed infinity of the same sign, the result is signed infinity and the INFO bit is set.
- If overflow occurs, the INEX and OVER bits are set and the results are set as follows (LFPN is the largest floating-point number):



		Overflow Output	Rounding Mode	
Result Sign	Nearest Even	Zero	+Infinity	Infinity
+	+infinity	+LFPN	+infinity	+LFPN
-	-infinity	-LFPN	-LFPN	-infinity

 If underflow occurs, the INEX and UNDER bits are set and the results are set as follows (SPFN is the smallest floating-point number):

	Underflow Output Rounding Mode						
Result Sign	Nearest Even	Zero	+Infinity	Infinity			
+	+0	+0	+SFPN	+0			
-	-0	-0	-0	-SFPN			

- If the sources are equal numbers of the same sign, the result is +0
 unless the rounding mode is -infinity, in which case the result is -0.
- If the sources are both 0 with opposite signs or both denormalized with opposite signs, the sign of the result is the same as the sign of src1
- 11. A signed denormalized source is treated as a signed 0 and the DENn bit is set. If the other source is not NaN or signed infinity, the INEX bit is also set.

Execution

if (cond) $src1 - src2 \rightarrow dst$ else nop

Pipeline

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.L or .S			

Instruction Type Four-cycle

Delay Slots 3

Functional Unit Latency 1

See Also ADDDP, SUB, SUBDP, SUBU

Example SUBSP .L1X A2,B1,A3

	Before instruction		4 cycles after instruction	
A2	4109 999Ah	A2	4109 999Ah	8.6
B1	C020 0000h	B1	C020 0000h	-2.5
А3	xxxx xxxxh	A3	4131 999Ah	11.1



SUBU Subtract Two Unsigned Integers Without Saturation

Syntax SUBU (.unit) src1, src2, dst

or

SUBU (.unit) src1, src2, dst_h:dst_l

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18	17	13	12	11		5	4	3	2	1	0
creg	Z	dst		src2	src1		Х		ор		1	1	0	s	p
3	1	5		5	5		1		7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint ulong	.L1, .L2	010 1111
src1 src2 dst	xuint uint ulong	.L1, .L2	011 1111

Description src2 is subtracted from src1. The result is placed in dst.

Execution

if (cond) $src1 - src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ADDU, SSUB, SUB, SUBC, SUBDP, SUBSP, SUB2





Example

SUBU .L1 A1,A2,A5:A4

	Before instructi	ion		1 cycle after in	struction	
A1	0000 325Ah	12,890 ⁽¹⁾	A1	0000 325Ah		
A2	FFFF FF12h	4,294,967,058 ⁽¹⁾	A2	FFFF FF12h		
A5:A4	xxxx xxxxh	xxxx xxxxh	A5:A4	0000 00FFh	0000 3348h	-4,294,954,168 ⁽²⁾

⁽¹⁾ Unsigned 32-bit integer (2) Signed 40-bit (long) integer



SUB2 Subtract Two 16-Bit Integers on Upper and Lower Register Halves

Syntax SUB2 (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2, .D1, .D2

Opcode .L unit

31 29	28	27	23	22 18		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2	src1		Х	0	0	0	0	1	0	0	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.L1, .L2
src1 src2	xi2	
dst	i2	

Opcode .S unit

3		28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2	src1		Х	0	1	0	0	0	1	1	0	0	0	s	p
	3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.S1, .S2
src1 src2	xi2	·
dst	i2	

Opcode .D unit

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	0	0	1	0	1	1	1	0	0	s	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i2	.D1, .D2
src2	xi2	
dst	i2	



Description

The upper and lower halves of *src2* are subtracted from the upper and lower halves of *src1* and the result is placed in *dst*. Any borrow from the lower-half subtraction does not affect the upper-half subtraction. Specifically, the upper-half of *src2* is subtracted from the upper-half of *src1* and placed in the upper-half of *dst*. The lower-half of *dst*. subtracted from the lower-half of *src1* and placed in the lower-half of *dst*.

31		16 15		0
	a_hi		a_lo	← src1
	-		-	
		SUB2		
	b_hi		b_lo	← src2
	=		=	
31		16 15		0
	a_hi - b_hi		a_lo - b_lo	← dst

NOTE: Unlike the **SUB** instruction, the argument ordering on the .D unit form of .S2 is consistent with the argument ordering for the .L and .S unit forms.

Execution

```
if (cond)  \{ \\ (lsb16(\textit{src1}) - lsb16(\textit{src2})) \rightarrow lsb16(\textit{dst}); \\ (msb16(\textit{src1}) - msb16(\textit{src2})) \rightarrow msb16(\textit{dst}); \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, .D

Instruction Type Single-cycle

Delay Slots 0

See Also ADD2, SUB, SUBU, SUB4, SSUB2



Examples

Example 1

SUB2 .S1 A3, A4, A5

	Before instruction			1 cycle after instruction	
А3	1105 6E30h	4357 28208	А3	1105 6E30h	
A4	1105 6980h	4357 27008	A4	1105 6980h	
A5	xxxx xxxxh		A5	0000 04B0h	0 1200

Example 2

SUB2 .D2 B2, B8, B15

	Before instruction			1 cycle after instruction	
B2	F23A 3789h	-3526 14217	B2	F23A 3789h	
B8	04B8 6732h	1208 26418	B8	04B8 6732h	
B15	xxxx xxxxh		B15	ED82 D057h	-4734 -12201

Example 3

SUB2 .S2X B1,A0,B2

	Before instruction			1 cycle after instruction	
A0	0021 3271h	33 ⁽¹⁾ 12913 ⁽²⁾	A0	0021 3271h	
B1	003A 1B48h	58 ⁽¹⁾ 6984 ⁽²⁾	B1	003A 1B48h	
B2	xxxx xxxxh		B2	0019 E8D7h	25 ⁽¹⁾ -5929 ⁽²⁾

⁽¹⁾ Signed 16-MSB integer

⁽²⁾ Signed 16-LSB integer



SUB4

Subtract Without Saturation, Four 8-Bit Pairs for Four 8-Bit Results

Syntax

SUB4 (.unit) src1, src2, dst

unit = .L1 or .L2

Opcode

31 29	28	27	23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	1	1	0	0	1	1	0	1	1	0	S	р
3	1	5		5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	i4	.L1, .L2
src2 dst	xi4	
dst	i4	

Description

Performs 2s-complement subtraction between packed 8-bit quantities. The values in *src1* and *src2* are treated as packed 8-bit data and the results are written into *dst* in a packed 8-bit format.

For each pair of 8-bit values in *src1* and *src2*, the difference between the 8-bit value from *src1* and the 8-bit value from *src2* is calculated to produce an 8-bit result. No saturation is performed. The result is placed in the corresponding position in *dst*:

- The difference between src1 byte0 and src2 byte0 is placed in byte0 of dst.
- The difference between src1 byte1 and src2 byte1 is placed in byte1 of dst.
- The difference between src1 byte2 and src2 byte2 is placed in byte2 of dst.
- The difference between src1 byte3 and src2 byte3 is placed in byte3 of dst.

31		24 23		16 1	5	8 7		0
	a_3		a_2		a_1		a_0	← src1
	-		-		-		-	
				SUB4	1			
	b_3		b_2		b_1		b_0	← src2
	=		=		=		=	
31		24 23		16 1	5	8 7		0
	a_3 - b_3		a_2 - b_2		a_1 - b_1		a_0 - b_0	← dst



Execution

```
if (cond)  \{ \\ (\text{byte0}(\textit{src1}) - \text{byte0}(\textit{src2})) \rightarrow \text{byte0}(\textit{dst}); \\ (\text{byte1}(\textit{src1}) - \text{byte1}(\textit{src2})) \rightarrow \text{byte1}(\textit{dst}); \\ (\text{byte2}(\textit{src1}) - \text{byte2}(\textit{src2})) \rightarrow \text{byte2}(\textit{dst}); \\ (\text{byte3}(\textit{src1}) - \text{byte3}(\textit{src2})) \rightarrow \text{byte3}(\textit{dst}) \\ \} \\ \text{else nop}
```

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also ADD4, SUB, SUB2

Example SUB4 .L1 A2, A8, A9

	Before instruction			1 cycle after instruction	
A2	37 89 F2 3Ah	55 137 242 58	A2	37 89 F2 3Ah	
A8	04 B8 49 75h	04 184 73 117	A8	04 B8 49 75h	
A9	xxxx xxxxh		A9	33 D1 A9 C5h	51 -47 169 -59



SWAP2 Swap Bytes in Upper and Lower Register Halves

Syntax SWAP2 (.unit) src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit



Opcode map field used	For operand type	Unit
src2	s2	.L1, .L2
dst	s2	


Opcode .S unit



Opcode map field used	For operand type	Unit
src2	s2	.S1, .S2
dst	s2	

Description

The **SWAP2** pseudo-operation takes the lower halfword from *src2* and places it in the upper halfword of *dst*, while the upper halfword from *src2* is placed in the lower halfword of *dst*. The assembler uses the **PACKLH2** (.unit) *src1*, *src2*, *dst* instruction to perform this operation (see PACKLH2).



The **SWAP2** instruction can be used in conjunction with the **SWAP4** instruction (see SWAP4) to change the byte ordering (and therefore, the endianess) of 32-bit data.



Execution

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L, .S

Instruction Type Single-cycle

Delay Slots 0

See Also SWAP4

Example 1

SWAP2 .L1 A2,A9

	Before instruction			1 cycle after instruction	
A2	3789 F23Ah	14217 -3526	A2	3789 F23Ah	
A9	xxxx xxxxh		A9	F23A 3789h	-3526 14217

Example 2

SWAP2 .S2 B2,B12

	Before instruction			1 cycle after instruction	
B2	0124 2451h	292 9297	B2	0124 2451h	
B12	xxxx xxxxh		B12	2451 0124h	9297 292



SWAP4

Swap Byte Pairs in Upper and Lower Register Halves

Syntax

```
SWAP4 (.unit) src2, dst
```

unit =
$$.L1$$
 or $.L2$

Opcode


31	29	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	ds	t	src		0	0	0	0	1	Х	0	0	1	1	0	1	0	1	1	0	S	р
3		1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xu4	.L1, .L2
dst	u4	

Description

Exchanges pairs of bytes within each halfword of *src2*, placing the result in *dst*. The values in *src2* are treated as unsigned, packed 8-bit values.

Specifically the upper byte in the upper halfword is placed in the lower byte in the upper halfword, while the lower byte of the upper halfword is placed in the upper byte of the upper halfword. Also the upper byte in the lower halfword is placed in the lower byte of the lower halfword, while the lower byte in the lower halfword is placed in the upper byte of the lower halfword.



By itself, this instruction changes the ordering of bytes within halfwords. This effectively changes the endianess of 16-bit data packed in 32-bit words. The endianess of full 32-bit quantities can be changed by using the **SWAP4** instruction in conjunction with the **SWAP2** instruction (see SWAP2).

Execution



Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L

Instruction Type Single-cycle

Delay Slots 0

See Also SWAP2

Example SWAP4 .L1 A1,A2

	Before instruction			1 cycle after instruction	
A1	9E 52 6E 30h	158 82 110 48	A1	9E 52 6E 30h	
A2	xxxx xxxxh		A2	52 9E 30 6Eh	82 158 48 110



SWE Software Exception

Syntax SWE

unit = none

Opcode

	30																					-	-	-	-	-	-	-	_	-	-
0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	р

1

Description

Causes an internal exception to be taken. It can be used as a mechanism for User mode programs to request Supervisor mode services. Execution of the **SWE** instruction results in an exception being recognized in the E1 pipeline phase containing the **SWE** instruction. The SXF bit in EFR is set to 1. The HWE bit in NTSR is cleared to 0. If exceptions have been globally enabled, this causes an exception to be recognized before execution of the next execute packet. The address of that next execute packet is placed in NRP.

Execution

 $1 \rightarrow SXF$ bit in EFR $0 \rightarrow HWE$ bit in TSR

Instruction Type Single-cycle

Delay Slots 0

See Also SWENR



SWENR Software Exception—No Return

Syntax SWENR

unit = none

Opcode

31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	p

1

Description

Causes an internal exception to be taken. It is intended for use in systems supporting a secure operating mode. It can be used as a mechanism for User mode programs to request Supervisor mode services. It differs from the **SWE** instruction in four ways:

- 1. TSR is not copied into NTSR.
- 2. No return address is placed in NRP (it remains unmodified).
- 3. The IB bit in TSR is set to 1. This will be observable only in the case where another exception is recognized simultaneously.
- 4. A branch to REP (restricted entry point register) is forced in the context switch rather than the ISTP-based exception (NMI) vector.

This instruction executes unconditionally.

If another exception (internal or external) is recognized simultaneously with the SWENR-raised exception then the other exception(s) takes priority and normal exception behavior occurs; that is, NTSR and NRP are used and execution is directed to the NMI vector.

Execution

 $1 \rightarrow SXF$ bit in EFR

 $0 \rightarrow HWE$ bit in TSR

Instruction Type Single-cycle

Delay Slots 0

See Also SWE



www.ti.com UNPKHU4 — Unpack 16 MSB Into Two Lower 8-Bit Halfwords of Upper and Lower Register Halves


UNPKHU4 Unpack 16 MSB Into Two Lower 8-Bit Halfwords of Upper and Lower Register

Halves

Syntax UNPKHU4 (.unit) src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit



Opcode map field used	For operand type	Unit
src2	xu4	.L1, .L2
dst	u2	

Opcode .S unit


31 2	9	28	27	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	dst		src2		0	0	0	1	1	Х	1	1	1	1	0	0	1	0	0	0	s	р
3		1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xu4	.S1, .S2
dst	u2	

Description

Moves the two most-significant bytes of *src2* into the two low bytes of the two halfwords of *dst*.

Specifically the upper byte in the upper halfword is placed in the lower byte in the upper halfword, while the lower byte of the upper halfword is placed in the lower byte of the lower halfword. The *src2* bytes are zero-extended when unpacked, filling the two high bytes of the two halfwords of *dst* with zeros.





Execution

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L, .S

Instruction Type Single cycle

Delay Slots 0

See Also UNPKLU4

Examples Example 1

UNPKHU4 .L1 A1,A2

	Before instruction	1 cycle after instruction
A1	9E 52 6E 30h	A1 9E 52 6E 30h
A2	xxxx xxxxh	A2 00 9E 00 52h

Example 2

UNPKHU4 .L2 B17,B18

	Before instruction	1 cycle after instruction					
B17	11 05 69 34h	B17	11 05 69 34h				
B18	xxxx xxxxh	B18	00 11 00 05h				

www.ti.com UNPKLU4 — Unpack 16 LSB Into Two Lower 8-Bit Halfwords of Upper and Lower Register Halves


UNPKLU4 Unpack 16 LSB Into Two Lower 8-Bit Halfwords of Upper and Lower Register

Halves

Syntax UNPKLU4 (.unit) src2, dst

unit = .L1, .L2, .S1, .S2

Opcode .L unit



Opcode map field used	For operand type	Unit
src2	xu4	.L1, .L2
dst	u2	

Opcode .S unit


31 29	28	27	23	22 1	8 1	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z	ds	t	src2		0	0	0	1	0	Х	1	1	1	1	0	0	1	0	0	0	s	р
3	1	5		5							1											1	1

Opcode map field used	For operand type	Unit
src2	xu4	.S1, .S2
dst	u2	

Description

Moves the two least-significant bytes of *src2* into the two low bytes of the two halfwords of *dst*.

Specifically, the upper byte in the lower halfword is placed in the lower byte in the upper halfword, while the lower byte of the lower halfword is kept in the lower byte of the lower halfword. The *src2* bytes are zero-extended when unpacked, filling the two high bytes of the two halfwords of *dst* with zeros.





Execution

Pipeline

Pipeline Stage	E1
Read	src2
Written	dst
Unit in use	.L, .S

Instruction Type Single cycle

Delay Slots 0

See Also UNPKHU4

Examples Example 1

UNPKLU4 .L1 A1,A2

	Before instruction	1 cycle after instruction
A1	9E 52 6E 30h	A1 9E 52 6E 30h
A2	xxxx xxxxh	A2 00 6E 00 30h

Example 2

UNPKLU4 .L2 B17,B18

Before instruction			1 cycle after instruction)
B17	11 05 69 34h	B17	11 05 69 34h	
B18	xxxx xxxxh	B18	00 69 00 34h	



XOR Bitwise Exclusive OR

Syntax XOR (.unit) src1, src2, dst

unit = .L1, .L2, .S1, .S2, .D1, .D2

Compact Instruction Format

Unit	Opcode Format	Figure
.L	L2c	Figure D-7
.L, .S, .D	LSDx1	Figure G-4

Opcode .L unit

31	29	28	27	23	22 1	18 17		13	12	11	5	4	3	2	1	0
creg	'	Z	dst	•	src2		src1		х	ор		1	1	0	s	р
3		1	5		5		5		1	7					1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.L1, .L2	110 1111
src1 src2 dst	scst5 xuint uint	.L1, .L2	110 1110

Opcode .S unit

31 29	28	27	23	22 18	17	13	12	11	6	5	4	3	2	1	0
creg	Z	dst		src2	src1		Х	ор		1	0	0	0	s	р
3	1	5		5	5		1	6						1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.S1, .S2	00 1011
src1 src2 dst	scst5 xuint uint	.S1, .S2	00 1010



XOR — Bitwise Exclusive OR

www.ti.com

Opcode

.D unit

31	29 2	28	27 23	22 18	17	13	12	11	10	9	6	5	4	3	2	1	0
creg		z	dst	src2	src1		Χ	1	0	ор		1	1	0	0	s	p
3		1	5	5	5		1			4						1	1

Opcode map field used	For operand type	Unit	Opfield
src1 src2 dst	uint xuint uint	.D1, .D2	1110
src1 src2 dst	scst5 xuint uint	.D1, .D2	1111

Description

Performs a bitwise exclusive-OR (XOR) operation between *src1* and *src2*. The result is

placed in dst. The scst5 operands are sign extended to 32 bits.

Execution

if (cond)

 $src1 XOR src2 \rightarrow dst$

else nop

Pipeline

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, or .D

Instruction Type Single-cycle

Delay Slots 0

See Also AND, ANDN, NOT, OR

Examples Example 1

XOR .S1 A3, A4, A5

	Before instruction		1 cycle after instruction	
А3	0721 325Ah	A3	0721 325Ah	
A4	0019 0F12h	A4	0019 0F12h	
A5	xxxx xxxxh	A5	0738 3D48h	





Example 2

XOR .D2 B1, ODh, B8

	Before instruction		1 cycle after instruction	
B1	0000 1023h	B1	0000 1023h	
B8	xxxx xxxxh	B8	0000 102Eh	



XORMPY

Galois Field Multiply With Zero Polynomial

Syntax

XORMPY (.unit) src1, src2, dst

unit = .M1 or .M2

Opcode

31	30	29	28	27 23	22 18	17	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	dst	src2	src1		Х	0	1	1	0	1	1	1	1	0	0	s	р
				5	5	5		1											1	1

Opcode map field used	For operand type	Unit
src1	uint	.M1, .M2
src2	xuint	
dst	uint	

Description

Performs a Galois field multiply, where *src1* is 32 bits and *src2* is limited to 9 bits. This multiply connects all levels of the gmpy4 together and only extends out by 8 bits. The **XORMPY** instruction is identical to a **GMPY** instruction executed with a zero-value polynomial.

Execution

GMPY_poly = 0 (lsb9(src2) gmpy uint(src1)) \rightarrow uint(dst)

Instruction Type Four-cycle

Delay Slots 3

See Also GMPY, GMPY4, XOR



www.ti.com

Example XORMPY .M1 A0,A1,A2 GPLYA = FFFFFFFF (ignored)

	Before instruction	1 cycle after instruction
A0	1234 5678h	A2 1E65 4210h
A1	0000 0126h	



XPND2


Expand Bits to Packed 16-Bit Masks

Syntax

XPND2 (.unit) src2, dst

unit = .M1 or .M2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.M1, .M2
dst	uint	

Description

Reads the two least-significant bits of *src2* and expands them into two halfword masks written to *dst*. Bit 1 of *src2* is replicated and placed in the upper halfword of *dst*. Bit 0 of *src2* is replicated and placed in the lower halfword of *dst*. Bits 2 through 31 of *src2* are ignored.

31	24	23	16 15		8 7		0
	XXXXXXX	XXXXXXX		XXXXXXXX		XXXXXX10	← si
			XPND2				
			\downarrow				
31	24	23	16 15		8 7		0
	11111111	11111111		00000000		00000000	← d-

The **XPND2** instruction is useful, when combined with the output of the **CMPGT2** or **CMPEQ2** instruction, for generating a mask that corresponds to the individual halfword positions that were compared. That mask may then be used with **ANDN**, **AND**, or **OR** instructions to perform other operations like compositing. This is an example:

```
CMPGT2 .S1 A3, A4, A5 ; Compare two registers, both upper ; and lower halves.

XPND2 .M1 A5, A2 ; Expand the compare results into ; two 16-bit masks.

NOP

AND .D1 A2, A7, A8 ; Apply the mask to a value to create result.
```

Because the **XPND2** instruction only examines the two least-significant bits of *src2*, it is possible to store a large bit mask in a single 32-bit word and expand it using multiple **SHR** and **XPND2** instruction pairs. This can be useful for expanding a packed 1-bit-per-pixel bitmap into full 16-bit pixels in imaging applications.



Execution

```
if (cond)  \{ \\ XPND2(\textit{src2} \& 1) \rightarrow lsb16(\textit{dst}); \\ XPND2(\textit{src2} \& 2) \rightarrow msb16(\textit{dst}) \\ \}  else nop
```

Pipeline

Pipeline Stage	E1	E2
Read	src2	
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also CMPEQ2, CMPGT2, XPND4

Example 1

XPND2 .M1 A1,A2

	Before instruction			2 cycles after instruction
A1	B174 6CA1h	2 LSBs are 01	A1	B174 6CA1h
A2	xxxx xxxxh		A2	0000 FFFFh

Example 2

XPND2 .M2 B1,B2

	Before instruction			2 cycles after instruction
B1	0000 0003h	2 LSBs are 11	B1	0000 0003h
B2	xxxx xxxxh		B2	FFFF FFFFh



XPND4


Expand Bits to Packed 8-Bit Masks

Syntax

XPND4 (.unit) src2, dst

unit = .M1 or .M2

Opcode



Opcode map field used	For operand type	Unit
src2	xuint	.M1, .M2
dst	uint	

Description

Reads the four least-significant bits of *src2* and expands them into four-byte masks written to *dst*. Bit 0 of *src2* is replicated and placed in the least-significant byte of *dst*. Bit 1 of *src2* is replicated and placed in second least-significant byte of *dst*. Bit 2 of *src2* is replicated and placed in second most-significant byte of *dst*. Bit 3 of *src2* is replicated and placed in most-significant byte of *dst*. Bits 4 through 31 of *src2* are ignored.

31	24	23	16	15		8	7		0	
	XXXXXXXX	XXXXXXXX			XXXXXXX			XXXX1001		← src2
XPND4										
				\downarrow						
31	24	23	16	15		8	7		0	
	11111111	0000000			00000000			11111111		← dst

The **XPND4** instruction is useful, when combined with the output of the **CMPGT4** or **CMPEQ4** instruction, for generating a mask that corresponds to the individual byte positions that were compared. That mask may then be used with **ANDN**, **AND**, or **OR** instructions to perform other operations like compositing.

This is an example:

```
CMPEQ4 .S1 A3, A4, A5 ; Compare two 32-bit registers all four bytes. XPND4 .M1 A5, A2 ; Expand the compare results into ; four 8-bit masks.

NOP
AND .D1 A2, A7, A8 ; Apply the mask to a value to create result.
```

Because the **XPND4** instruction only examines the four least-significant bits of *src2*, it is possible to store a large bit mask in a single 32-bit word and expand it using multiple **SHR** and **XPND4** instruction pairs. This can be useful for expanding a packed, 1-bit-per-pixel bitmap into full 8-bit pixels in imaging applications.



Execution

```
if (cond)  \{ \\ XPND4(src2 \ \& \ 1) \rightarrow byte0(\textit{dst}); \\ XPND4(src2 \ \& \ 2) \rightarrow byte1(\textit{dst}); \\ XPND4(src2 \ \& \ 4) \rightarrow byte2(\textit{dst}); \\ XPND4(src2 \ \& \ 8) \rightarrow byte3(\textit{dst}) \\ \} \\ else nop
```

Pipeline

Pipeline Stage	E1	E2
Read	src2	_
Written		dst
Unit in use	.M	

Instruction Type Two-cycle

Delay Slots 1

See Also CMPEQ4, CMPGTU4, XPND2

Example 1

XPND4 .M1 A1,A2

	Before instruction			2 cycles after instruction
A1	B174 6CA4h	4 LSBs are 0100	A1	B174 6CA4h
A2	xxxx xxxxh		A2	00 FF 00 00h

Example 2

XPND4 .M2 B1,B2

	Before instruction			2 cycles after instruction
B1	0000 000Ah	4 LSBs are 1010	B1	00 00 00 0Ah
B2	xxxx xxxxh		B2	FF 00 FF 00h



ZERO Zero a Register

Syntax ZERO (.unit) dst

or

ZERO (.unit) dst_o:dst_e

unit = .L1, .L2, .D1, .D2, .S1, .S2

Opcode

Opcode map field used	For operand type	Unit	Opfield
dst	sint	.L1, .L2	001 0111
dst	slong	.L1, .L2	011 0111
dst	sint	.D1, .D2	01 0001
dst	sint	.S1, .S2	01 0111

Description This is a pseudo-operation used to fill the destination register or register pair with 0s.

When the destination is a single register, the assembler uses the \mathbf{MVK} instruction to load

it with zeros: MVK (.unit) 0, dst (see MVK).

When the destination is a register pair, the assembler uses the **SUB** instruction (see SUB) to subtract a value from itself and store the result in the destination pair.

Execution

if (cond) $0 \rightarrow dst$

else nop

or

if (cond) $src - src \rightarrow dst_o:dst_e$

else nop

Instruction Type Single-cycle

Delay Slots 0

See Also MVK, SUB

Example 1

ZERO .D1 A1

	Before instruction		1 cycle after instruction	
A1	B174 6CA1h	A1	0000 0000h	



Example 2

ZERO .L1 A1:A0

	Before instruction	1 cycle after instruction
A0	B174 6CA1h	A0 0000 0000h
A1	1234 5678h	A1 0000 0000h

574 Instruction Set SPRUFE8B-July 2010



Pipeline

The DSP pipeline provides flexibility to simplify programming and improve performance. These two factors provide this flexibility:

- 1. Control of the pipeline is simplified by eliminating pipeline interlocks.
- 2. Increased pipelining eliminates traditional architectural bottlenecks in program fetch, data access, and multiply operations. This provides single-cycle throughput.

This chapter starts with a description of the pipeline flow. Highlights are:

- The pipeline can dispatch eight parallel instructions every cycle.
- Parallel instructions proceed simultaneously through each pipeline phase.
- Serial instructions proceed through the pipeline with a fixed relative phase difference between instructions.
- Load and store addresses appear on the CPU boundary during the same pipeline phase, eliminating read-after-write memory conflicts.

All instructions require the same number of pipeline phases for fetch and decode, but require a varying number of execute phases. This chapter contains a description of the number of execution phases for each type of instruction.

Finally, this chapter contains performance considerations for the pipeline. These considerations include the occurrence of fetch packets that contain multiple execute packets, execute packets that contain multicycle **NOP**s, and memory considerations for the pipeline. For more information about fully optimizing a program and taking full advantage of the pipeline, see the *TMS320C6000 Programmer's Guide* (SPRU198).

Topic Page

4.1	Pipeline Operation Overview	576
4.2	Pipeline Execution of Instruction Types	585
4.3	Functional Unit Constraints	602
4.4	Performance Considerations	621

SPRUFE8B-July 2010 Pipeline 575



4.1 Pipeline Operation Overview

The pipeline phases are divided into three stages:

- Fetch
- Decode
- Execute

All instructions in the DSP instruction set flow through the fetch, decode, and execute stages of the pipeline. The fetch stage of the pipeline has four phases for all instructions, and the decode stage has two phases for all instructions. The execute stage of the pipeline requires a varying number of phases, depending on the type of instruction. The stages of the DSP pipeline are shown in Figure 4-1.

Figure 4-1. Pipeline Stages





4.1.1 Fetch

The fetch phases of the pipeline are:

- PG: Program address generate
- PS: Program address send
- PW: Program access ready wait
- PR: Program fetch packet receive

The DSP uses a fetch packet (FP) of eight words. All eight of the words proceed through fetch processing together, through the PG, PS, PW, and PR phases. Figure 4-2(a) shows the fetch phases in sequential order from left to right. Figure 4-2(b) is a functional diagram of the flow of instructions through the fetch phases. During the PG phase, the program address is generated in the CPU. In the PS phase, the program address is sent to memory. In the PW phase, a memory read occurs. Finally, in the PR phase, the fetch packet is received at the CPU. Figure 4-2(c) shows fetch packets flowing through the phases of the fetch stage of the pipeline. In Figure 4-2(c), the first fetch packet (in PR) is made up of four execute packets, and the second and third fetch packets (in PW and PS) contain two execute packets each. The last fetch packet (in PG) contains a single execute packet of eight instructions.

CPU PG PS PW PR Functional (b) units PW Registers PR Memory PS (c) Fetch 256 **SMPYH** LDW LDW SHR SHR SMPYH MV NOP PG SMPYH LDW LDW **SMPY** SADD SADD В MVK PS SMPYH LDW LDW MVKLH MV **SMPY** MVK В PW LDW LDW MVK ADD LDW LDW MVK SHL PR Decode

Figure 4-2. Fetch Phases of the Pipeline



4.1.2 Decode

The decode phases of the pipeline are:

DP: Instruction dispatchDC: Instruction decode

In the DP phase of the pipeline, the fetch packets are split into execute packets. Execute packets consist of one instruction or from two to eight parallel instructions. During the DP phase, the instructions in an execute packet are assigned to the appropriate functional units. In the DC phase, the source registers, destination registers, and associated paths are decoded for the execution of the instructions in the functional units.

Figure 4-3(a) shows the decode phases in sequential order from left to right. Figure 4-3(b) shows a fetch packet that contains two execute packets as they are processed through the decode stage of the pipeline. The last six instructions of the fetch packet (FP) are parallel and form an execute packet (EP). This EP is in the dispatch phase (DP) of the decode stage. The arrows indicate each instruction's assigned functional unit for execution during the same cycle. The **NOP** instruction in the eighth slot of the FP is not dispatched to a functional unit because there is no execution associated with it.

The first two slots of the fetch packet (shaded below) represent an execute packet of two parallel instructions that were dispatched on the previous cycle. This execute packet contains two **MPY** instructions that are now in decode (DC) one cycle before execution. There are no instructions decoded for the .L, .S, and .D functional units for the situation illustrated.




Figure 4-3. Decode Phases of the Pipeline


A NOP is not dispatched to a functional unit.




4.1.3 Execute

The execute portion of the pipeline is subdivided into five phases (E1-E5). Different types of instructions require different numbers of these phases to complete their execution. These phases of the pipeline play an important role in your understanding the device state at CPU cycle boundaries. The execution of different types of instructions in the pipeline is described in Section 4.2. Figure 4-4(a) shows the execute phases of the pipeline in sequential order from left to right. Figure 4-4(b) shows the portion of the functional block diagram in which execution occurs.

Figure 4-4. Execute Phases of the Pipeline







4.1.4 Pipeline Operation Summary

Figure 4-5 shows all the phases in each stage of the pipeline in sequential order, from left to right.

Figure 4-5. Pipeline Phases




Figure 4-6 shows an example of the pipeline flow of consecutive fetch packets that contain eight parallel instructions. In this case, where the pipeline is full, all instructions in a fetch packet are in parallel and split into one execute packet per fetch packet. The fetch packets flow in lockstep fashion through each phase of the pipeline.

For example, examine cycle 7 in Figure 4-6. When the instructions from FPn reach E1, the instructions in the execute packet from FP n +1 are being decoded. FP n + 2 is in dispatch while FPs n + 3, n + 4, n + 5, and n + 6 are each in one of four phases of program fetch. See Section 4.4 for additional detail on code flowing through the pipeline. Table 4-1 summarizes the pipeline phases and what happens in each phase.

Figure 4-6. Pipeline Operation: One Execute Packet per Fetch Packet

								Clock cy	cle								
Fetch packet	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
n	PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6	E7	E8	E9	E10	
n+1		PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6	E7	E8	E9	E10
n+2			PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6	E7	E8	E9
n+3				PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6	E7	E8
n+4					PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6	E7
n+5						PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5	E6
n+6							PG	PS	PW	PR	DP	DC	E1	E2	E3	E4	E5
n+7								PG	PS	PW	PR	DP	DC	E1	E2	E3	E4
n+8									PG	PS	PW	PR	DP	DC	E1	E2	E3
n+9										PG	PS	PW	PR	DP	DC	E1	E2
n+10											PG	PS	PW	PR	DP	DC	E1



Table 4-1. Operations Oc	ccurring During	Pipeline Phase
--------------------------	-----------------	----------------

Stage	Phase	Symbol	During This Phase
Program fetch	Program address generate	PG	The address of the fetch packet is determined.
	Program address send	PS	The address of the fetch packet is sent to memory.
	Program wait	PW	A program memory access is performed.
	Program data receive	PR	The fetch packet is at the CPU boundary.
Program decode	Dispatch	DP	The next execute packet in the fetch packet is determined and sent to the appropriate functional units to be decoded.
	Decode	DC	Instructions are decoded in functional units.
Execute	Execute 1	E1	For all instruction types, the conditions for the instructions are evaluated and operands are read.
			For load and store instructions, address generation is performed and address modifications are written to a register file. (1)
			For branch instructions, branch fetch packet in PG phase is affected. (1)
			For single-cycle instructions, results are written to a register file. (1)
			For DP compare, ADDDP/SUBDP, and MPYDP instructions, the lower 32-bits of the sources are read. For all other instructions, the sources are read. (1)
			For MPYSPDP instruction, the <i>src1</i> and the lower 32 bits of <i>src2</i> are read. (1)
			For 2-cycle DP instructions, the lower 32 bits of the result are written to a register file. (1)
	Execute 2	E2	For load instructions, the address is sent to memory. For store instructions, the address and data are sent to memory. $^{(1)}$
			Single-cycle instructions that saturate results set the SAT bit in the control status register (CSR) if saturation occurs. ⁽¹⁾
			For multiply unit, nonmultiply instructions, results are written to a register file. (2)
			For multiply, 2-cycle DP, and DP compare instructions, results are written to a register file. $^{(1)}$
			For DP compare and ADDDP/SUBDP instructions, the upper 32 bits of the source are read. $^{(1)}$
			For MPYDP instruction, the lower 32 bits of $src1$ and the upper 32 bits of $src2$ are read. (1)
			For MPYI and MPYID instructions, the sources are read. (1)
			For MPYSPDP instruction, the <i>src1</i> and the upper 32 bits of <i>src2</i> are read. (1)
	Execute 3	E3	Data memory accesses are performed. Any multiply instructions that saturate results set the SAT bit in the control status register (CSR) if saturation occurs. (1
			For MPYDP instruction, the upper 32 bits of $\mathit{src1}$ and the lower 32 bits of $\mathit{src2}$ are read. $^{(1)}$
			For MPYI and MPYID instructions, the sources are read. (1)
	Execute 4	E4	For load instructions, data is brought to the CPU boundary. (1)
			For multiply extensions, results are written to a register file. (3)
			For MPYI and MPYID instructions, the sources are read. (1)
			For MPYDP instruction, the upper 32 bits of the sources are read. (1)
			For MPYI and MPYID instructions, the sources are read. (1)
			For 4-cycle instructions, results are written to a register file. (1)
			For INTDP and MPYSP2DP instructions, the lower 32 bits of the result are written to a register file. (1)
	Execute 5	E5	For load instructions, data is written into a register. (1)
			For INTDP and MPYSP2DP instructions, the upper 32 bits of the result are written to a register file. (1)
	Execute 6	E6	For ADDDP/SUBDP and MPYSPDP instructions, the lower 32 bits of the result are written to a register file. ⁽¹⁾

⁽¹⁾ This assumes that the conditions for the instructions are evaluated as true. If the condition is evaluated as false, the instruction does not write any results or have any pipeline operation after E1.

⁽²⁾ Multiply unit, nonmultiply instructions are AVG2, AVGU4, BITC4, BITR, DEAL, ROT, SHFL, SSHVL, and SSHVR.

Multiply extensions include MPY2, MPY4, DOTPx2, DOTPU4, MPYHIx, MPYLIx, and MVD.



Table 4-1. Or	perations Occur	rina Durina	Pipeline Phases	(continued)

Stage	Phase	Symbol	During This Phase
	Execute 7	E7	For ADDDP/SUBDP and MPYSPDP instructions, the upper 32 bits of the result are written to a register file. ⁽¹⁾
	Execute 8	E8	Nothing is read or written.
	Execute 9	E9	For MPYI instruction, the result is written to a register file. (1)
			For MPYDP and MPYID instructions, the lower 32 bits of the result are written to a register file. (1)
	Execute 10 E10		For MPYDP and MPYID instructions, the upper 32 bits of the result are written to a register file. (1)

Figure 4-7 shows a functional block diagram of the pipeline stages. The pipeline operation is based on CPU cycles. A CPU cycle is the period during which a particular execute packet is in a particular pipeline phase. CPU cycle boundaries always occur at clock cycle boundaries.

As code flows through the pipeline phases, it is processed by different parts of the DSP. Figure 4-7 shows a full pipeline with a fetch packet in every phase of fetch. One execute packet of eight instructions is being dispatched at the same time that a 7-instruction execute packet is in decode. The arrows between DP and DC correspond to the functional units identified in the code in Example 4-1.

In the DC phase portion of Figure 4-7, one box is empty because a **NOP** was the eighth instruction in the fetch packet in DC and no functional unit is needed for a **NOP**. Finally, Figure 4-7 shows six functional units processing code during the same cycle of the pipeline.

Registers used by the instructions in E1 are shaded in Figure 4-7. The multiplexers used for the input operands to the functional units are also shaded in the figure. The bold cross paths are used by the **MPY** instructions.

Most DSP instructions are single-cycle instructions, which means they have only one execution phase (E1). A small number of instructions require more than one execute phase. The types of instructions, each of which require different numbers of execute phases, are described in Section 4.2.



256 Fetch SADD STH STH SADD SMPYH SMPY SUB PGВ SADD SHR LDW LDW SADD SMPYH SHR PS **SMPYH** STH STH SADD SADD **SMPYH SMPY** SUB В PW LDW LDW SADD SADD SMPYH SHR SHR PR SMPYH 32 32 32 32 32 32 32 Decode STH STH SADD SADD SMPYH SMPY SUB В DP SHR SMPYH SMPYH DC LDW LDW SHR MV Execute E1 SADD В **SMPY SMPYH** MVK SADD .S1 .D1 .D2 .M2 .M1 .S2 .L2 2 5 3 6 5 3 32 31 30 29 28 10 9 8 6 4 0 31 30 29 28 10 9 8 Data 1 ST 1 LD 1 LD 2 4 Data 2 ST 2 Register file B Register file A 64 64 64 64 32 32 DA 1 DA 2 Data cache control

Figure 4-7. Pipeline Phases Block Diagram



Example 4-1. Execute Packet in Figure 4-7

	SADD SADD SMPYH SMPY B MVK	.L1 .L2 .M2X .M1X .S1	A2,A7,A2 B2,B7,B2 B3,A3,B2 B3,A3,A2 LOOP1 117,B1	; El Phase
	LDW LDW MV SMPYH SMPYH SHR SHR	.D2 .D1 .L2X .M1 .M2 .S1	*B4++,B3 *A4++,A3 A1,B0 A2,A2,A0 B2,B2,B10 A2,16,A5 B2,16,B5	; DC Phase
LOOP1:				
 [B1]	STH STH SADD SADD SMPYH SMPY B SUB	.D1 .D2 .L1 .L2 .M2X .M1X .S1	A5,*A8++[2] B5,*B8++[2] A2,A7.A2 B2,B7,B2 B3,A3,B2 B3,A3,A2 LOOP1 B1,1,B1	; DP, PW, and PG Phases
	LDW LDW SADD SADD SMPYH SMPYH SHR SHR	.D2 .D1 .L1 .L2 .M1 .M2 .S1	*B4++,B3 *A4++,A3 A0,A1,A1 B10,B0,B0 A2,A2,A0 B2,B2,B10 A2,16,A5 B2,16,B5	; PR and PS Phases



4.2 Pipeline Execution of Instruction Types

The pipeline operation of the C674x DSP instructions can be categorized into fourteen instruction types. Thirteen of these (**NOP** is not included) are shown in Table 4-2, Table 4-3, Table 4-4, and Table 4-5, which is a mapping of operations occurring in each execution phase for the different instruction types. The delay slots and functional unit latency associated with each instruction type are listed in the bottom row. See section Section 3.8.12 for any instruction constraints.

The execution of instructions is defined in terms of delay slots. A delay slot is a CPU cycle that occurs after the first execution phase (E1) of an instruction. Results from instructions with delay slots are not available until the end of the last delay slot. For example, a multiply instruction has one delay slot, which means that one CPU cycle elapses before the results of the multiply are available for use by a subsequent instruction. However, results are available from other instructions finishing execution during the same CPU cycle in which the multiply is in a delay slot.

Table 4-2. Execution Stage Length Description for Each Instruction Type - Part A

	Instruction Type								
Execution Phase (1) (2)	Single Cycle	16 × 16 Single Multiply/.M Unit Nonmultiply	Store	Multiply Extensions	Load	Branch			
E1	Compute result and write to register	Read operands and start computations	Compute address	Reads operands and start computations	Compute address	Target code in PG (3)			
E2		Compute result and write to register	Send address and data to memory		Send address to memory				
E3			Access memory		Access memory				
E4				Write results to register	Send data back to CPU				
E5					Write data into register				
Delay slots	0	1	0 ⁽⁴⁾	3	4 ⁽⁴⁾	5 ⁽³⁾			
Functional unit latency	1	1	1	1	1	1			

⁽¹⁾ This table assumes that the condition for each instruction is evaluated as true. If the condition is evaluated as false, the instruction does not write any results or have any pipeline operation after E1.

⁽²⁾ **NOP** is not shown and has no operation in any of the execution phases.

⁽³⁾ See Section 4.2.6 for more information on branches.

⁽⁴⁾ See Section 4.2.3 and Section 4.2.5 for more information on execution and delay slots for stores and loads.



Table 4-3. Execution Stage Length Description for Each Instruction Type - Part B

	Instruction Type						
Execution Phase ⁽¹⁾ (2)	2-Cycle DP	4-Cycle	INTDP	DP Compare			
E1	Compute the lower results and write to register	Read sources and start computation	Read sources and start computation	Read lower sources and start computation			
E2	Compute the upper results and write to register	Continue computation	Continue computation	Read upper sources, finish computation, and write results to register			
E3		Continue computation	Continue computation				
E4		Complete computation and write results to register	Continue computation and write lower results to register				
E5			Complete computation and write upper results to register				
Delay slots	1	3	4	1			
Functional unit latency	1	1	1	2			

⁽¹⁾ This table assumes that the condition for each instruction is evaluated as true. If the condition is evaluated as false, the instruction does not write any results or have any pipeline operation after E1.

Table 4-4. Execution Stage Length Description for Each Instruction Type - Part C

	Instruction Type							
Execution Phase ⁽¹⁾ (2)	ADDDP/SUBDP	MPYI	MPYID	MPYDP				
E1	Read lower sources and start computation	Read sources and start computation	Read sources and start computation	Read lower sources and start computation				
E2	Read upper sources and continue computation	Read sources and continue computation	Read sources and continue computation	Read lower src1 and upper src2 and continue computation				
E3	Continue computation	Read sources and continue computation	Read sources and continue computation	Read lower src2 and upper src1 and continue computation				
E4	Continue computation	Read sources and continue computation	Read sources and continue computation	Read upper sources and continue computation				
E5	Continue computation	Continue computation	Continue computation	Continue computation				
E6	Compute the lower results and write to register	Continue computation	Continue computation	Continue computation				
E7	Compute the upper results and write to register	Continue computation	Continue computation	Continue computation				
E8		Continue computation	Continue computation	Continue computation				
E9		Complete computation and write results to register	Continue computation and write lower results to register	Continue computation and write lower results to register				
E10			Complete computation and write upper results to register	Complete computation and write upper results to register				
Delay slots	6	8	9	9				
Functional unit latency	2	4	4	4				

⁽¹⁾ This table assumes that the condition for each instruction is evaluated as true. If the condition is evaluated as false, the instruction does not write any results or have any pipeline operation after E1.

⁽²⁾ **NOP** is not shown and has no operation in any of the execution phases.

⁽²⁾ **NOP** is not shown and has no operation in any of the execution phases.



Table 4-5. Execution Stage Length Description for Each Instruction Type - Part D

	Instruction Type						
Execution Phase ⁽¹⁾ (2)	MPYSPDP	MPYSP2DP					
E1	Read src1 and lower src2 and start computation	Read sources and start computation					
E2	Read src1 and upper src2 and continue computation	Continue computation					
E3	Continue computation	Continue computation					
E4	Continue computation	Continue computation and write lower results to register					
E5	Continue computation	Complete computation and write upper results to register					
E6	Continue computation and write lower results to register						
E7	Complete computation and write upper results to register						
Delay slots	6	4					
Functional unit latency	3	2					

⁽¹⁾ This table assumes that the condition for each instruction is evaluated as true. If the condition is evaluated as false, the instruction does not write any results or have any pipeline operation after E1.

⁽²⁾ **NOP** is not shown and has no operation in any of the execution phases.



4.2.1 Single-Cycle Instructions

Single-cycle instructions complete execution during the E1 phase of the pipeline (Table 4-6). Figure 4-8 shows the fetch, decode, and execute phases of the pipeline that the single-cycle instructions use.

Figure 4-9 shows the single-cycle execution diagram. The operands are read, the operation is performed, and the results are written to a register, all during E1. Single-cycle instructions have no delay slots.

Table 4-6. Single-Cycle Instruction Execution

Pipeline Stage	E1
Read	src1, src2
Written	dst
Unit in use	.L, .S, .M, or .D

Figure 4-8. Single-Cycle Instruction Phases





Figure 4-9. Single-Cycle Instruction Execution Block Diagram





4.2.2 Two-Cycle Instructions and .M Unit Nonmultiply Operations

Two-cycle or multiply instructions use both the E1 and E2 phases of the pipeline to complete their operations (Table 4-7). Figure 4-10 shows the fetch, decode, and execute phases of the pipeline that the two-cycle instructions use.

Figure 4-11 shows the operations occurring in the pipeline for a multiply instruction. In the E1 phase, the operands are read and the multiply begins. In the E2 phase, the multiply finishes, and the result is written to the destination register. Multiply instructions have one delay slot. Figure 4-11 also applies to the other .M unit nonmultiply operations.


Table 4-7. Multiply Instruction Execution

Pipeline Stage	E1	E2
Read	src1, src2	
Written		dst
Unit in use	.M	

Figure 4-10. Two-Cycle Instruction Phases



Figure 4-11. Single 16 x 16 Multiply Instruction Execution Block Diagram





4.2.3 Store Instructions

Store instructions require phases E1 through E3 of the pipeline to complete their operations (Table 4-8). Figure 4-12 shows the fetch, decode, and execute phases of the pipeline that the store instructions use.

Figure 4-13 shows the operations occurring in the pipeline phases for a store instruction. In the E1 phase, the address of the data to be stored is computed. In the E2 phase, the data and destination addresses are sent to data memory. In the E3 phase, a memory write is performed. The address modification is performed in the E1 stage of the pipeline. Even though stores finish their execution in the E3 phase of the pipeline, they have no delay slots. There is additional explanation of why stores have zero delay slots in Section 4.2.5.

Table 4-8. Store Instruction Execution

Pipeline Stage	E1	E2	E3
Read	baseR, offsetR, src		
Written	baseR		
Unit in use	.D2		

Figure 4-12. Store Instruction Phases





Figure 4-13. Store Instruction Execution Block Diagram







When you perform a load and a store to the same memory location, these rules apply (i = cycle):

When a load is executed before a store, the old value is loaded and the new value is stored.

```
i LDW i+1 STW
```

· When a store is executed before a load, the new value is stored and the new value is loaded.

```
i STW i+1 LDW
```

• When the instructions are executed in parallel, the old value is loaded first and then the new value is stored, but both occur in the same phase.

```
i STWi || LDW
```



4.2.4 Extended Multiply Instructions

The extended multiply instructions use phases E1 through E4 to complete their operations (Table 4-9). Figure 4-14 shows the fetch, decode, and execute phases of the pipeline that the extended multiply instructions.

Figure 4-15 shows the operations occurring in the pipeline for the multiply extensions. In the E1 phase, the operands are read and the multiplies begin. In the E4 phase, the multiplies finish, and the results are written to the destination register. Extended multiply instructions have three delay slots.

Table 4-9. Extended Multiply Instruction Execution

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			
Written				dst
Unit in use	.M			

Figure 4-14. Extended Multiply Instruction Phases





Figure 4-15. Extended Multiply Instruction Execution Block Diagram





4.2.5 Load Instructions

Data loads require all five, E1 through E5, of the pipeline execute phases to complete their operations (Table 4-10). Figure 4-16 shows the fetch, decode, and execute phases of the pipeline that the load instructions use.

Figure 4-17 shows the operations occurring in the pipeline phases for a load. In the E1 phase, the data address pointer is modified in its register. In the E2 phase, the data address is sent to data memory. In the E3 phase, a memory read at that address is performed.

Table 4-10. Load Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5
Read	baseR, offsetR, src				
Written	baseR				dst
Unit in use	.D				

Figure 4-16. Load Instruction Phases





Figure 4-17. Load Instruction Execution Block Diagram





In the E4 stage of a load, the data is received at the CPU core boundary. Finally, in the E5 phase, the data is loaded into a register. Because data is not written to the register until E5, load instructions have four delay slots. Because pointer results are written to the register in E1, there are no delay slots associated with the address modification.

In the following code, pointer results are written to the A4 register in the first execute phase of the pipeline and data is written to the A3 register in the fifth execute phase.

Because a store takes three execute phases to write a value to memory and a load takes three execute phases to read from memory, a load following a store accesses the value placed in memory by that store in the cycle after the store is completed. This is why the store is considered to have zero delay slots.

4.2.6 Branch Instructions

Although branch instructions take one execute phase, there are five delay slots between the execution of the branch and execution of the target code (Table 4-11). Figure 4-18 shows the pipeline phases used by the branch instruction and branch target code. The delay slots are shaded.


Figure 4-19 shows a branch instruction execution block diagram. If a branch is in the E1 phase of the pipeline (in the .S2 unit in Figure 4-19), its branch target is in the fetch packet that is in PG during that same cycle (shaded in the figure). Because the branch target has to wait until it reaches the E1 phase to begin execution, the branch takes five delay slots before the branch target code executes.

On the DSP, a stall is inserted if a branch is taken to an execute packet that spans fetch packets to give time to fetch the second packet. Normally the assembler compensates for this by preventing branch targets from spanning fetch packets. The one case in which this cannot be done is in the case that an interrupt or exception occurred and the return target is a fetch packet spanning execute packet.

Table 4-11. Branch Instruction Execution

		Target Instruction					
Pipeline Stage	E1	PS	PW	PR	DP	DC	E1
Read	src2						
Written							
Branch taken							✓
Unit in use	.\$2						

Figure 4-18. Branch Instruction Phases



594 Pipeline SPRUFE8B-July 2010



Fetch 256 STH STH SADD SADD SMPYH SMPY SUB В PG SADD SADD SHR SHR SMPYH SMPYH LDW LDW PS STH STH SADD SADD SMPYH **SMPY** SUB В PW PR LDW LDW SHR SHR SMPYH SMPYH MV NOP 32 32 32 32 32 32 32 Decode SMPYH SMPY SADD SADD В MVK DΡ DC LDW LDW Execute Ε1 MVK **SMPY SMPYH** В .L1 .D1 .D2 .S1 .M1 .M2 .S2 .L2

Figure 4-19. Branch Instruction Execution Block Diagram



4.2.7 Two-Cycle DP Instructions

Two-cycle DP instructions use both the E1 and E2 phases of the pipeline to complete their operations (see Table 4-12). The following instructions are two-cycle DP instructions:

- ABSDP
- RCPDP
- RSQDP
- SPDP

The lower and upper 32 bits of the DP source are read on E1 using the *src1* and *src2* ports, respectively. The lower 32 bits of the DP source are written on E1 and the upper 32 bits of the DP source are written on E2. The two-cycle DP instructions are executed on the .S units. The status is written to the FAUCR on E1. Figure 4-20 shows the fetch, decode, and execute phases of the pipeline that the two-cycle DP instructions use.

Table 4-12. Two-Cycle DP Instruction Execution

Pipeline Stage	E1	E2
Read	src2_l, src2_h	
Written	dst_I	dst_h
Unit in use	.S	

Figure 4-20. Two-Cycle DP Instruction Phases

PG	PS	PW	PR	DP	DC	E1	E2	1 delay slot
----	----	----	----	----	----	----	----	--------------



4.2.8 Four-Cycle Instructions

Four-cycle instructions use the E1 through E4 phases of the pipeline to complete their operations (see Table 4-13). The following instructions are four-cycle instructions:

- ADDSP
- DPINT
- DPSP
- DPTRUNC
- INTSP
- MPYSP
- SPINT
- SPTRUNC
- SUBSP

The sources are read on E1 and the results are written on E4. The four-cycle instructions are executed on the .L or .M units. The status is written to the floating-point multiplier configuration register (FMCR) or the floating-point adder configuration register (FADCR) on E4. Figure 4-21 shows the fetch, decode, and execute phases of the pipeline that the four-cycle instructions use.

Table 4-13. Four-Cycle Instruction Execution

Pipeline Stage	E1	E2	E3	E4
Read	src1, src2			_
Written				dst
Unit in use	.L or .M			

Figure 4-21. Four-Cycle Instruction Phases



3 delay slots




4.2.9 INTDP Instruction

The **INTDP** instruction uses the E1 through E5 phases of the pipeline to complete its operations (see Table 4-14). *src2* is read on E1, the lower 32 bits of the result are written on E4, and the upper 32 bits of the result are written on E5. The **INTDP** instruction is executed on the .L unit. The status is written to the floating-point adder configuration register (FADCR) on E4. Figure 4-22 shows the fetch, decode, and execute phases of the pipeline that the **INTDP** instruction uses.

Table 4-14. INTDP Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5
Read	src2				
Written				dst_l	dst_h
Unit in use	.L				

Figure 4-22. INTDP Instruction Phases



4 delay slots

4.2.10 Double-Precision (DP) Compare Instructions

The double-precision (DP) compare instructions use the E1 and E2 phases of the pipeline to complete their operations (see Table 4-15). The lower 32 bits of the sources are read on E1, the upper 32 bits of the sources are read on E2, and the results are written on E2. The following instructions are DP compare instructions:

- CMPEQDP
- CMPLTDP
- CMPGTDP

The DP compare instructions are executed on the .S unit. The functional unit latency for DP compare instructions is 2. The status is written to the floating-point auxiliary register (FAUCR) on E2. Figure 4-23 shows the fetch, decode, and execute phases of the pipeline that the DP compare instruction uses.

Table 4-15. DP Compare Instruction Execution

Pipeline Stage	E1	E2
Read	src1_l, src2_l	src1_h, src2_h
Written		dst
Unit in use	.S	.S

Figure 4-23. DP Compare Instruction Phases






4.2.11 ADDDP/SUBDP Instructions

The **ADDDP/SUBDP** instructions use the E1 through E7 phases of the pipeline to complete their operations (see Table 4-16). The lower 32 bits of the result are written on E6, and the upper 32 bits of the result are written on E7. The **ADDDP/SUBDP** instructions are executed on the .L or .S units. The functional unit latency for **ADDDP/SUBDP** instructions is 2. The status is written to the floating-point adder configuration register (FADCR) on E6. Figure 4-24 shows the fetch, decode, and execute phases of the pipeline that the **ADDDP/SUBDP** instructions use.

Table 4-16. ADDDP/SUBDP Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5	E6	E 7
Read	src1_l, src2_l	src1_h, src2_h					
Written						dst_l	dst_h
Unit in use	.L or .S	.L or .S					

Figure 4-24. ADDDP/SUBDP Instruction Phases



6 delay slots

4.2.12 MPYI Instruction

The **MPYI** instruction uses the E1 through E9 phases of the pipeline to complete its operations (see Table 4-17). The sources are read on cycles E1 through E4 and the result is written on E9. The **MPYI** instruction is executed on the .M unit. The functional unit latency for the **MPYI** instruction is 4. Figure 4-25 shows the fetch, decode, and execute phases of the pipeline that the **MPYI** instruction uses.

Table 4-17. MPYI Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5	E6	E 7	E8	E9
Read	src1, src2	src1, src2	src1, src2	src1, src2					
Written									dst
Unit in use	.M	.M	.M	.M					

Figure 4-25. MPYI Instruction Phases



8 delay slots



4.2.13 MPYID Instruction

The **MPYID** instruction uses the E1 through E10 phases of the pipeline to complete its operations (see Table 4-18). The sources are read on cycles E1 through E4, the lower 32 bits of the result are written on E9, and the upper 32 bits of the result are written on E10. The **MPYID** instruction is executed on the .M unit. The functional unit latency for the **MPYID** instruction is 4. Figure 4-26 shows the fetch, decode, and execute phases of the pipeline that the **MPYID** instruction uses.

Table 4-18. MPYID Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7	E8	E9	E10
Read	src1, src2	src1, src2	src1, src2	src1, src2						
Written									dst_l	dst_h
Unit in use	.M	.M	.M	.M						

Figure 4-26. MPYID Instruction Phases



9 delay slots

4.2.14 MPYDP Instruction

The **MPYDP** instruction uses the E1 through E10 phases of the pipeline to complete its operations (see Table 4-19). The lower 32 bits of *src1* are read on E1 and E2, and the upper 32 bits of *src1* are read on E3 and E4. The lower 32 bits of *src2* are read on E1 and E3, and the upper 32 bits of *src2* are read on E2 and E4. The lower 32 bits of the result are written on E9, and the upper 32 bits of the result are written on E10. The **MPYDP** instruction is executed on the .M unit. The functional unit latency for the **MPYDP** instruction is 4. The status is written to the floating-point multiplier configuration register (FMCR) on E9. Figure 4-27 shows the fetch, decode, and execute phases of the pipeline that the **MPYDP** instruction uses.

Table 4-19. MPYDP Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5	E6	E7	E8	E9	E10
Read	src1_l,	src1_l,	src1_h,	src1_h,						
	src2_I	src2_h	src2_l	src2_h						
Written									dst_l	dst_h
Unit in use	.M	.M	.M	.M						

Figure 4-27. MPYDP Instruction Phases



9 delay slots



4.2.15 MPYSPDP Instruction

The **MPYSPDP** instruction uses the E1 through E7 phases of the pipeline to complete its operations (see Table 4-20). *src1* is read on E1 and E2. The lower 32 bits of *src2* are read on E1, and the upper 32 bits of *src2* are read on E2. The lower 32 bits of the result are written on E6, and the upper 32 bits of the result are written on E7. The **MPYSPDP** instruction is executed on the .M unit. The functional unit latency for the **MPYSPDP** instruction is 3. Figure 4-28 shows the fetch, decode, and execute phases of the pipeline that the **MPYSPDP** instruction uses.

Table 4-20. MPYSPDP Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5	E6	E 7
Read	src1, src2_l	src1, src2_h					
Written						dst_l	dst_h
Unit in use	.M	.M					

Figure 4-28. MPYSPDP Instruction Phases



6 delay slots


4.2.16 MPYSP2DP Instruction

The **MPYSP2DP** instruction uses the E1 through E5 phases of the pipeline to complete its operations (see Table 4-21). *src1* and *src2* are read on E1. The lower 32 bits of the result are written on E4, and the upper 32 bits of the result are written on E5. The **MPYSP2DP** instruction is executed on the .M unit. The functional unit latency for the **MPYSP2DP** instruction is 2. Figure 4-29 shows the fetch, decode, and execute phases of the pipeline that the **MPYSP2DP** instruction uses.

Table 4-21. MPYSP2DP Instruction Execution

Pipeline Stage	E1	E2	E3	E4	E5
Read	src1, src2				
Written				dst_l	dst_h
Unit in use	.M				

Figure 4-29. MPYSP2DP Instruction Phases



4 delay slots



Functional Unit Constraints www.ti.com

4.3 Functional Unit Constraints

If you want to optimize your instruction pipeline, consider the instructions that are executed on each unit. Sources and destinations are read and written differently for each instruction. If you analyze these differences, you can make further optimization improvements by considering what happens during the execution phases of instructions that use the same functional unit in each execution packet.

The following sections provide information about what happens during each execute phase of the instructions within a category for each of the functional units.

4.3.1 .S-Unit Constraints

Table 4-22 shows the instruction constraints for single-cycle instructions executing on the .S unit.

Table 4-22. Single-Cycle .S-Unit Instruction Constraints

		Instruction Execution	
Cycle	1	2	
Single-cycle	RW		
Instruction Type		Subsequent Same-Unit Instruction Executable	
Single-cycle		✓	
DP compare		✓	
2-cycle DP		✓	
Branch		✓	
Instruction Type		Same Side, Different Unit, Both Using Cross Path Executable	•
Single-cycle		✓	
Load		✓	
Store		✓	
INTDP		✓	
ADDDP/SUBDP		✓	
16 x 16 multiply		✓	
4-cycle		✓	
MPYI		✓	
MPYID		✓	
MPYDP		1	

LEGEND: Shaded column = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Sources rea



www.ti.com Functional Unit Constraints

Table 4-23 shows the instruction constraints for DP compare instructions executing on the .S unit.

Table 4-23. DP Compare .S-Unit Instruction Constraints

		Instruction Execution								
Cycle	1	2	3							
DP compare	R	RW								
Instruction Type			Subsequent Same-Unit Instruction Executable							
Single-cycle		Xrw	✓							
DP compare		Xr	✓							
2-cycle DP		Xrw	✓							
ADDDP/SUBDP		Xr	✓							
ADDSP/SUBSP		Xr	✓							
Branch ⁽¹⁾		Xr	✓							
Instruction Type		Same	Same Side, Different Unit, Both Using Cross Path Executable							
Single-cycle		Xr	✓							
Load		Xr	✓							
Store		Xr	✓							
INTDP		Xr	✓							
ADDDP/SUBDP		Xr	✓							
16 × 16 multiply		Xr	✓							
4-cycle		Xr	✓							
MPYI		Xr	✓							
MPYID		Xr	✓							
MPYDP		Xr	✓							

⁽¹⁾ The branch on register instruction is the only branch instruction that reads a general-purpose register

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

✓ = Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xrw = Next instruction cannot enter E1 during cycle-read/decode/write constraint



Functional Unit Constraints www.ti.com

Table 4-24 shows the instruction constraints for 2-cycle DP instructions executing on the .S unit.

Table 4-24. 2-Cycle DP .S-Unit Instruction Constraints

				Instruction Execution				
Cycle	1	2	3					
2-cycle	RW	W						
Instruction Type			Subsequ	ent Same-Unit Instruction Executable				
Single-cycle		Xw	✓					
DP compare		✓	✓					
2-cycle DP		Xw	✓					
Branch		✓	✓					
Instruction Type		Same	me Side, Different Unit, Both Using Cross Path Executable					
Single cycle		✓	✓					
Load		✓	✓					
Store		✓	✓					
INTDP		✓	✓					
ADDDP/SUBDP		✓	✓					
16 × 16 multiply		✓	✓					
4-cycle		✓	✓					
MPYI		✓	✓					
MPYID		✓	✓					
MPYDP		✓	✓					

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

Table 4-25 shows the instruction constraints for ADDSP/SUBSP instructions executing on the .S unit.

Table 4-25. ADDSP/SUBSP .S-Unit Instruction Constraints

				Ins	struction Execution	
Cycle	1	2	3	4		
ADDSP/SUBSP	R			W		
Instruction Type	Subsequent Same-Unit Instruction Executable					
Single-cycle		✓	✓	Xw		
2-cycle DP		✓	Xw	Xw		
DP compare		✓	Xw	✓		
ADDDP/SUBDP		✓	✓	✓		
ADDSP/SUBSP		✓	✓	✓		
Branch		✓	✓	✓		

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction:

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint



www.ti.com Functional Unit Constraints

Table 4-26 shows the instruction constraints for ADDDP/SUBDP instructions executing on the .S unit.

Table 4-26. ADDDP/SUBDP .S-Unit Instruction Constraints

		Instruction Execution									
Cycle	1	2	3	4	5	6	7				
ADDDP/SUBDP	R	R				W	W				
Instruction Type	Subsequent Same-Unit Instruction Executable										
Single-cycle		Xr	✓	✓	✓	Xw	Xw				
2-cycle DP		Xr	✓	✓	Xw	Xw	Xw				
DP compare		Xr	✓	✓	Xw	Xw	✓				
ADDDP/SUBDP		Xr	✓	✓	✓	✓	✓				
ADDSP/SUBSP		Xr	Xw	Xw	✓	✓	✓				
Branch		Xr	✓	✓	✓	✓	✓				

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

✓ = Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint

Table 4-27 shows the instruction constraints for branch instructions executing on the .S unit.

Table 4-27. Branch .S-Unit Instruction Constraints

					Instruc	tion Ex	ecution	l
Cycle	1	2	3	4	5	6	7	8
Branch ⁽¹⁾	R							
Instruction Type			Subs	equent	Same-	Unit Ins	tructio	n Executable
Single-cycle		✓	✓	✓	✓	✓	✓	✓
DP compare		✓	✓	✓	✓	✓	✓	✓
2-cycle DP		✓	✓	✓	✓	✓	✓	✓
Branch		✓	✓	✓	✓	✓	✓	✓
Instruction Type		Same	Side, I	Differen	t Unit,	Both Us	sing Cro	oss Path Executable
Single-cycle		✓	✓	✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓	✓	✓
INTDP		✓	✓	✓	✓	✓	✓	✓
ADDDP/SUBDP		✓	✓	✓	✓	✓	✓	✓
16 × 16 multiply		✓	✓	✓	✓	✓	✓	✓
4-cycle		✓	✓	✓	✓	✓	✓	✓
MPYI		✓	✓	✓	✓	✓	✓	✓
MPYID		✓	✓	✓	✓	✓	✓	✓
MPYDP		✓	✓	✓	✓	✓	✓	✓

⁽¹⁾ The branch on register instruction is the only branch instruction that reads a general-purpose register

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; ✓ = Next instruction can enter E1 during cycle



Functional Unit Constraints www.ti.com

4.3.2 .M-Unit Constraints

Table 4-28 shows the instruction constraints for 16×16 multiply instructions executing on the .M unit.

Table 4-28. 16 × 16 Multiply .M-Unit Instruction Constraints

			Instruction Execution	
Cycle	1	2	3	
16 × 16 multiply	R	W		
Instruction Type			Subsequent Same-Unit Instruction Executable	
16 × 16 multiply		✓	✓	
4-cycle		✓	✓	
MPYI		✓	✓	
MPYID		✓	✓	
MPYDP		✓	✓	
Instruction Type		Same	Side, Different Unit, Both Using Cross Path Exe	cutable
Single-cycle		✓	✓	
Load		✓	✓	
Store		✓	✓	
DP compare		✓	✓	
2-cycle DP		✓	✓	
Branch		✓	✓	
4-cycle		✓	✓	
INTDP		✓	✓	
ADDDP/SUBDP		✓	✓	

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{√ =} Next instruction can enter E1 during cycle



www.ti.com Functional Unit Constraints

Table 4-29 shows the instruction constraints for 4-cycle instructions executing on the .M unit.

Table 4-29. 4-Cycle .M-Unit Instruction Constraints

	Instruction Execution 1 2 3 4 5 R W Subsequent Same-Unit Instruction Executable ✓ Xw ✓ ✓							
Cycle	1	2	3	4	5			
4-cycle	R			W				
Instruction Type			Subs	equent	Same-Unit Instruction Executable			
16 x 16 multiply		✓	Xw	✓	✓			
4-cycle		✓	✓	✓	✓			
MPYI		✓	✓	✓	✓			
MPYID		✓	✓	✓	✓			
MPYDP		✓	✓	✓	✓			
Instruction Type		Same	e Side, [Differen	nt Unit, Both Using Cross Path Executable			
Single-cycle		✓	✓	✓	✓			
Load		✓	✓	✓	✓			
Store		✓	✓	✓	✓			
DP compare		✓	✓	✓	✓			
2-cycle DP		✓	✓	✓	✓			
Branch		✓	✓	✓	✓			
4-cycle		✓	✓	✓	✓			
INTDP		✓	✓	✓	✓			
ADDDP/SUBDP		✓	✓	✓	✓			

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint



Functional Unit Constraints www.ti.com

Table 4-30 shows the instruction constraints for MPYI instructions executing on the .M unit.

Table 4-30. MPYI .M-Unit Instruction Constraints

		Instruction Execution								
Cycle	1	2	3	4	5	6	7	8	9	10
MPYI	R	R	R	R					W	
Instruction Type	Subsequent Same-Unit Instruction Executable									
16 × 16 multiply		Xr	Xr	Xr	✓	✓	✓	Xw	✓	✓
4-cycle		Xr	Xr	Xr	Xu	Xw	Xu	✓	✓	✓
MPYI		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
MPYID		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
MPYDP		Xr	Xr	Xr	Xu	Xu	Xu	✓	✓	✓
MPYSPDP		Xr	Xr	Xr	Xu	Xu	Xu	✓	✓	✓
MPYSP2DP		Xr	Xr	Xr	Xw	Xw	Xu	✓	✓	✓
Instruction Type		Same	Side, I	Differen	t Unit,	Both Us	sing Cr	oss Pat	h Exec	utable
Single-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓	✓	✓	✓	✓
DP compare		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
2-cycle DP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
Branch		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
4-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
INTDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓
ADDDP/SUBDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{✓ =} Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xu = Next instruction cannot enter E1 during cycle-other resource conflict



www.ti.com Functional Unit Constraints

Table 4-31 shows the instruction constraints for MPYID instructions executing on the .M unit.

Table 4-31. MPYID .M-Unit Instruction Constraints

		Instruction Execution									
Cycle	1	2	3	4	5	6	7	8	9	10	11
MPYID	R	R	R	R					W	W	
Instruction Type	Subsequent Same-Unit Instruction Executable										
16 x 16 multiply		Xr	Xr	Xr	✓	✓	✓	Xw	Xw	✓	✓
4-cycle		Xr	Xr	Xr	Xu	Xw	Xw	✓	✓	✓	✓
MPYI		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
MPYID		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
MPYDP		Xr	Xr	Xr	Xu	Xu	Xu	✓	✓	✓	✓
MPYSPDP		Xr	Xr	Xr	Xw	Xu	Xu	✓	✓	✓	✓
MPYSP2DP		Xr	Xr	Xr	Xw	Xw	Xw	✓	✓	✓	✓
Instruction Type	S	Same Side, Different Unit, Both Using Cross Path Executable									
Single-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
DP compare		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
2-cycle DP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
Branch		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
4-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
INTDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
ADDDP/SUBDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

✓ = Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xu = Next instruction cannot enter E1 during cycle-other resource conflict



Functional Unit Constraints www.ti.com

Table 4-32 shows the instruction constraints for MPYDP instructions executing on the .M unit.

Table 4-32. MPYDP .M-Unit Instruction Constraints

		Instruction Execution									
Cycle	1	2	3	4	5	6	7	8	9	10	11
MPYDP	R	R	R	R					W	W	
Instruction Type		Subsequent Same-Unit Instruction Executable									
16 × 16 multiply		Xr	Xr	Xr	✓	✓	✓	Xw	Xw	✓	✓
4-cycle		Xr	Xr	Xr	Xu	Xw	Xw	✓	✓	✓	✓
MPYI		Xr	Xr	Xr	Xu	Xu	Xu	✓	✓	✓	✓
MPYID		Xr	Xr	Xr	Xu	Xu	Xu	✓	✓	✓	✓
MPYDP		Xr	Xr	Xr	n	n	n	✓	✓	✓	✓
MPYSPDP		Xr	Xr	Xr	Xw	Xu	Xu	✓	✓	✓	✓
MPYSP2DP		Xr	Xr	Xr	Xw	Xw	Xw	✓	✓	✓	✓
Instruction Type		Same	Side, I	Differen	t Unit,	Both Us	sing Cr	oss Pat	h Execu	ıtable	
Single-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
DP compare		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
2-cycle DP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
Branch		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
4-cycle		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
INTDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓
ADDDP/SUBDP		Xr	Xr	Xr	✓	✓	✓	✓	✓	✓	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{✓ =} Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xu = Next instruction cannot enter E1 during cycle-other resource conflict



www.ti.com Functional Unit Constraints

Table 4-33 shows the instruction constraints for MPYSP instructions executing on the .M unit.

Table 4-33. MPYSP .M-Unit Instruction Constraints

	Instruction Execution							
Cycle	1	2	3	4				
MPYSP	R			W				
nstruction Type			Subs	equent Sam	e-Unit Instruction Execu	table		
MPYSPDP		✓	✓	✓				
MPYSP2DP		✓	✓	✓				
nstruction Type		Same	Side, l	Different Uni	t, Both Using Cross Path	n Executable		
Single-cycle		✓	✓	✓				
oad		✓	✓	✓				
Store		✓	✓	✓				
OP compare		✓	✓	✓				
-cycle DP		✓	✓	✓				
ranch		✓	✓	✓				
I-cycle		✓	✓	✓				
NTDP		✓	✓	✓				
.DDDP/SUBDP		✓	✓	✓				

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{√ =} Next instruction can enter E1 during cycle



Functional Unit Constraints www.ti.com

Table 4-34 shows the instruction constraints for MPYSPDP instructions executing on the .M unit.

Table 4-34. MPYSPDP .M-Unit Instruction Constraints

		Instruction Execution 1 2 3 4 5 6 7							
Cycle	1	2	3	4	5	6	7		
MPYSPDP	R	R				W	W		
Instruction Type		Subsequent Same-Unit Instruction Executable							
16 × 16 multiply		Xr	✓	✓	Xw	Xw	✓		
MPYDP		Xr	Xu	Xu	✓	✓	✓		
MPYI		Xr	Xu	Xu	✓	✓	✓		
MPYID		Xr	Xu	Xu	✓	✓	✓		
MPYSP		Xr	Xw	Xw	✓	✓	✓		
MPYSPDP		Xr	Xu	✓	✓	✓	✓		
MPYSP2DP		Xr	Xw	Xw	✓	✓	✓		
Instruction Type Same Side, Different Unit, Both U							sing Cross Path Executable		
Single-cycle		Xr	✓	✓	✓	✓	✓		
Load		Xr	✓	✓	✓	✓	✓		
Store		Xr	✓	✓	✓	✓	✓		
DP compare		Xr	✓	✓	✓	✓	✓		
2-cycle DP		Xr	✓	✓	✓	✓	✓		
Branch		Xr	✓	✓	✓	✓	✓		
4-cycle		Xr	✓	✓	✓	✓	✓		
INTDP		Xr	✓	✓	✓	✓	✓		
ADDDP/SUBDP		Xr	✓	✓	✓	✓	✓		

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{✓ =} Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xu = Next instruction cannot enter E1 during cycle-other resource conflict



www.ti.com Functional Unit Constraints

Table 4-35 shows the instruction constraints for MPYSP2DP instructions executing on the .M unit.

Table 4-35. MPYSP2DP .M-Unit Instruction Constraints

					Instruct	ion Execution
Cycle	1	2	3	4	5	
MPYSP2DP	R	R		W	W	
Instruction Type			Subs	equent	Same-U	Init Instruction Executable
16 x 16 multiply		1	Xw	Xw	✓	
MPYDP		Xu	✓	✓	✓	
MPYI		Xu	✓	✓	✓	
MPYID		Xu	✓	✓	✓	
MPYSP		Xw	✓	✓	✓	
MPYSPDP		Xu	✓	✓	✓	
MPYSP2DP		Xw	✓	✓	✓	
Instruction Type		Same	Side, l	Differen	t Unit, E	Both Using Cross Path Executable
Single-cycle		Xr	✓	✓	✓	
Load		Xr	✓	✓	✓	
Store		Xr	✓	✓	✓	
DP compare		Xr	✓	✓	✓	
2-cycle DP		Xr	✓	✓	✓	
Branch		Xr	✓	✓	✓	
4-cycle		Xr	✓	✓	✓	
INTDP		Xr	✓	✓	✓	
ADDDP/SUBDP		Xr	✓	✓	✓	

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

✓ = Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xu = Next instruction cannot enter E1 during cycle-other resource conflict

SPRUFE8B-July 2010 Pipeline 613



Functional Unit Constraints www.ti.com

4.3.3 L-Unit Constraints

Table 4-36 shows the instruction constraints for single-cycle instructions executing on the .L unit.

Table 4-36. Single-Cycle .L-Unit Instruction Constraints

·		Instruction Execution	
Cycle	1	2	
Single-cycle	RW		
Instruction Type		Subsequent Same-Unit Instruction Executab	le
Single-cycle		✓	
4-cycle		✓	
INTDP		✓	
ADDDP/SUBDP		✓	
Instruction Type		Same Side, Different Unit, Both Using Cross Path Ex	cecutable
Single-cycle		✓	
DP compare		✓	
2-cycle DP		✓	
4-cycle		✓	
Load		✓	
Store		✓	
Branch		✓	
16 × 16 multiply		✓	
MPYI		✓	
MPYID		✓	
MPYDP		✓	

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{√ =} Next instruction can enter E1 during cycle



www.ti.com Functional Unit Constraints

Table 4-37 shows the instruction constraints for 4-cycle instructions executing on the .L unit.

Table 4-37. 4-Cycle .L-Unit Instruction Constraints

					nstruction Execution	
Cycle	1	2	3	4	5	
4-cycle	R			W		
Instruction Type			Subs	sequent	Same-Unit Instruction Executable	
Single-cycle		✓	✓	Xw	✓	
4-cycle		✓	✓	✓	✓	
INTDP		✓	✓	✓	✓	
ADDDP/SUBDP		✓	✓	✓	✓	
Instruction Type		Same	e Side,	Differen	Unit, Both Using Cross Path Execu	table
Single-cycle		✓	✓	✓	✓	
DP compare		✓	✓	✓	✓	
2-cycle DP		✓	✓	✓	✓	
4-cycle		✓	✓	✓	✓	
Load		✓	✓	✓	✓	
Store		✓	✓	✓	✓	
Branch		✓	✓	✓	✓	
16 × 16 multiply		✓	✓	✓	✓	
MPYI		✓	✓	✓	✓	
MPYID		✓	✓	✓	✓	
MPYDP		✓	✓	✓	✓	

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

SPRUFE8B-July 2010 Pipeline 615

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint



Functional Unit Constraints www.ti.com

Table 4-38 shows the instruction constraints for INTDP instructions executing on the .L unit.

Table 4-38. INTDP .L-Unit Instruction Constraints

				Ir	nstructi	on Execution
Cycle	1	2	3	4	5	6
INTDP	R			W	W	
Instruction Type			Subse	quent S	Same-U	nit Instruction Executable
Single-cycle		✓	✓	Xw	Xw	✓
4-cycle		Xw	✓	✓	✓	✓
INTDP		Xw	✓	✓	✓	✓
ADDDP/SUBDP		✓	✓	✓	✓	✓
Instruction Type	•	Same S	ide, Di	fferent	Unit, B	oth Using Cross Path Executable
Single-cycle		✓	✓	✓	✓	✓
DP compare		✓	✓	✓	✓	✓
2-cycle DP		✓	✓	✓	✓	✓
4-cycle		✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓
Branch		✓	✓	✓	✓	✓
16 × 16 multiply		✓	✓	✓	✓	✓
MPYI		✓	✓	✓	✓	✓
MPYID		✓	✓	✓	✓	✓
MPYDP		✓	✓	✓	✓	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint



www.ti.com Functional Unit Constraints

Table 4-39 shows the instruction constraints for ADDDP/SUBDP instructions executing on the .L unit.

Table 4-39. ADDDP/SUBDP .L-Unit Instruction Constraints

				ı	nstruc	tion Ex	ecution	1
Cycle	1	2	3	4	5	6	7	8
ADDDP/SUBDP	R	R				W	W	
Instruction Type			Subse	quent	Same-l	Jnit Ins	tructio	n Executable
Single-cycle		Xr	✓	✓	✓	Xw	Xw	✓
4-cycle		Xr	Xw	Xw	✓	✓	✓	✓
INTDP		Xrw	Xw	Xw	✓	✓	✓	✓
ADDDP/SUBDP		Xr	✓	✓	✓	✓	✓	✓
Instruction Type	S	Same S	Side, D	ifferent	Unit, E	3oth Us	ing Cr	oss Path Executable
Single-cycle		Xr	✓	✓	✓	✓	✓	✓
DP compare		Xr	✓	✓	✓	✓	✓	✓
2-cycle DP		Xr	✓	✓	✓	✓	✓	✓
4-cycle		Xr	✓	✓	✓	✓	✓	✓
Load		✓	✓	✓	✓	✓	✓	✓
Store		✓	✓	✓	✓	✓	✓	✓
Branch		Xr	✓	✓	✓	✓	✓	✓
16 × 16 multiply		Xr	✓	✓	✓	✓	✓	✓
MPYI		Xr	✓	✓	✓	✓	✓	✓
MPYID		Xr	✓	✓	✓	✓	✓	✓
MPYDP		Xr	✓	✓	✓	✓	✓	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

SPRUFE8B-July 2010 Pipeline 617

^{✓ =} Next instruction can enter E1 during cycle; Xr = Next instruction cannot enter E1 during cycle-read/decode constraint; Xw = Next instruction cannot enter E1 during cycle-write constraint; Xrw = Next instruction cannot enter E1 during cycle-read/decode/write constraint



Functional Unit Constraints www.ti.com

4.3.4 D-Unit Instruction Constraints

Table 4-40 shows the instruction constraints for load instructions executing on the .D unit.

Table 4-40. Load .D-Unit Instruction Constraints

	Instruction Execution
Cycle	1 2 3 4 5 6
Load	RW W
Instruction Type	Subsequent Same-Unit Instruction Executable
Single-cycle	√ √ √ √
Load	✓ ✓ ✓ ✓ ✓
Store	✓ ✓ ✓ ✓ ✓
Instruction Type	Same Side, Different Unit, Both Using Cross Path Executable
16 x 16 multiply	✓ ✓ ✓ ✓ ✓
MPYI	✓ ✓ ✓ ✓ ✓
MPYID	✓ ✓ ✓ ✓ ✓
MPYDP	✓ ✓ ✓ ✓ ✓
Single-cycle	✓ ✓ ✓ ✓ ✓
DP compare	✓ ✓ ✓ ✓ ✓
2-cycle DP	✓ ✓ ✓ ✓ ✓
Branch	✓ ✓ ✓ ✓ ✓
4-cycle	✓ ✓ ✓ ✓ ✓
INTDP	✓ ✓ ✓ ✓ ✓
ADDDP/SUBDP	✓ ✓ ✓ ✓ ✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

^{√ =} Next instruction can enter E1 during cycle



www.ti.com Functional Unit Constraints

Table 4-41 shows the instruction constraints for store instructions executing on the .D unit.

Table 4-41. Store .D-Unit Instruction Constraints

	Instruction Execution
Cycle	1 2 3 4
Store	RW
Instruction Type	Subsequent Same-Unit Instruction Executable
Single-cycle	√ √ √
Load	✓ ✓ ✓
Store	✓ ✓ ✓
Instruction Type	Same Side, Different Unit, Both Using Cross Path Executable
16 x 16 multiply	√ √ √
MPYI	✓ ✓ ✓
MPYID	✓ ✓ ✓
MPYDP	✓ ✓ ✓
Single-cycle	✓ ✓ ✓
DP compare	✓ ✓ ✓
2-cycle DP	✓ ✓ ✓
Branch	✓ ✓ ✓
4-cycle	✓ ✓ ✓
INTDP	✓ ✓ ✓
ADDDP/SUBDP	✓ ✓ ✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

SPRUFE8B-July 2010 Pipeline 619

^{√ =} Next instruction can enter E1 during cycle



Functional Unit Constraints www.ti.com

Table 4-42 shows the instruction constraints for single-cycle instructions executing on the .D unit.

Table 4-42. Single-Cycle .D-Unit Instruction Constraints

			Instruction Execution
Cycle	1	2	
Single-cycle	RW		
Instruction Type			Subsequent Same-Unit Instruction Executable
Single-cycle		✓	
Load		✓	
Store		✓	
Instruction Type		Same	Side, Different Unit, Both Using Cross Path Executable
16 × 16 multiply		✓	
MPYI		✓	
MPYID		✓	
MPYDP		✓	
Single-cycle		✓	
DP compare		✓	
2-cycle DP		✓	
Branch		✓	
4-cycle		✓	
INTDP		✓	
ADDDP/SUBDP		✓	

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction;

Table 4-43 shows the instruction constraints for LDDW instructions executing on the .D unit.

Table 4-43. LDDW Instruction With Long Write Instruction Constraints

					Instruc	tion Execution
Cycle	1	2	3	4	5	6
LDDW	RW				W	
Instruction Type			Subs	equent	Same-l	Jnit Instruction Executable
Instruction with long result		✓	✓	✓	Xw	✓

LEGEND: Shaded text = E1 phase of the single-cycle instruction; R = Sources read for the instruction; W = Destinations written for the instruction:

^{√ =} Next instruction can enter E1 during cycle

^{✓ =} Next instruction can enter E1 during cycle; Xw = Next instruction cannot enter E1 during cycle-write constraint



4.4 Performance Considerations

The DSP pipeline is most effective when it is kept as full as the algorithms in the program allow it to be. It is useful to consider some situations that can affect pipeline performance.

A fetch packet (FP) is a grouping of eight instructions. Each FP can be split into from one to eight execute packets (EPs). Each EP contains instructions that execute in parallel. Each instruction executes in an independent functional unit. The effect on the pipeline of combinations of EPs that include varying numbers of parallel instructions, or just a single instruction that executes serially with other code, is considered here.

In general, the number of execute packets in a single FP defines the flow of instructions through the pipeline. Another defining factor is the instruction types in the EP. Each type of instruction has a fixed number of execute cycles that determines when this instruction's operations are complete. Section 4.4.2 covers the effect of including a multicycle **NOP** in an individual EP.

Finally, the effect of the memory system on the operation of the pipeline is considered. The access of program and data memory is discussed, along with memory stalls.

4.4.1 Pipeline Operation With Multiple Execute Packets in a Fetch Packet

Referring to Figure 4-6, pipeline operation is shown with eight instructions in every fetch packet. Figure 4-30, however, shows the pipeline operation with a fetch packet that contains multiple execute packets. Code for Figure 4-30 might have this layout:

```
instruction A ;
                            EP k
                                              FP n
\prod
        instruction B ;
        instruction C ;
                           EP k + 1
                                              FP n
        instruction D
        instruction E
        instruction F ;
                            EP k + 2
                                              FP n
        instruction G
        instruction H
        instruction I ;
                           EP k + 3
                                             FP n + 1
        instruction J
        instruction K
        instruction L
        instruction M
        instruction N
        instruction 0
        instruction P
```

... continuing with EPs k+4 through k+8, which have eight instructions in parallel, like k+3.

SPRUFE8B-July 2010 Pipeline 621



Performance Considerations www.ti.com

Figure 4-30. Pipeline Operation: Fetch Packets With Different Numbers of Execute Packets

Fetch packet **Execute packet** 6 7 (FP) (EP) 2 3 4 5 8 9 10 11 12 13 PG PR DP DC E1 E2 E3 E5 n k n k+1 DP DC: E1 E2 F3 E4 E5 k+2 DC E1 E2 E3 E4 E5 n k+3 PG PS PW DP DC E1 E2 E3 E4 PG PS PW Pipeline DP DC E2 n+2 PR E1 E3 k+4 k+5 PG PS stall PW PR DP DC E1 E2 PW PG PS PR DP DC E1 k+6 n+4 PS PW PR DP DC PG PS PW DP n+6 k+8 PR

In Figure 4-30, fetch packet n, which contains three execute packets, is shown followed by six fetch packets (n + 1 through n + 6), each with one execute packet (containing eight parallel instructions). The first fetch packet (n) goes through the program fetch phases during cycles 1-4. During these cycles, a program fetch phase is started for each of the fetch packets that follow.

In cycle 5, the program dispatch (DP) phase, the CPU scans the p-bits and detects that there are three execute packets (k through k + 2) in fetch packet n. This forces the pipeline to stall, which allows the DP phase to start for execute packets k + 1 and k + 2 in cycles 6 and 7. Once execute packet k + 2 is ready to move on to the DC phase (cycle 8), the pipeline stall is released.

The fetch packets n + 1 through n + 4 were all stalled so the CPU could have time to perform the DP phase for each of the three execute packets (k through k + 2) in fetch packet n + 5 was also stalled in cycles 6 and 7: it was not allowed to enter the PG phase until after the pipeline stall was released in cycle 8. The pipeline continues operation as shown with fetch packets n + 5 and n + 6 until another fetch packet containing multiple execution packets enters the DP phase, or an interrupt occurs.



4.4.2 Multicycle NOPs

The **NOP** instruction has an optional operand, *count*, that allows you to issue a single instruction for multicycle **NOPs**. A **NOP 2**, for example, fills in extra delay slots for the instructions in its execute packet and for all previous execute packets. If a **NOP 2** is in parallel with an **MPY** instruction, the **MPY** result is available for use by instructions in the next execute packet.

Figure 4-31 shows how a multicycle **NOP** drives the execution of other instructions in the same execute packet. Figure 4-31(a) shows a **NOP** in an execute packet (in parallel) with other code. The results of the **LD**, **ADD**, and **MPY** is available during the proper cycle for each instruction. Hence, **NOP** has no effect on the execute packet.

Figure 4-31(b) shows the replacement of the single-cycle **NOP** with a multicycle **NOP** (**NOP 5**) in the same execute packet. The **NOP5** causes no operation to perform other than the operations from the instructions inside its execute packet. The results of the **LD**, **ADD**, and **MPY** cannot be used by any other instructions until the **NOP5** period has completed.




Figure 4-31. Multicycle NOP in an Execute Packet

Figure 4-32 shows how a multicycle **NOP** can be affected by a branch. If the delay slots of a branch finish while a multicycle **NOP** is still dispatching **NOP**s into the pipeline, the branch overrides the multicycle **NOP** and the branch target begins execution five delay slots after the branch was issued.

SPRUFE8B-July 2010 Pipeline 623



Performance Considerations www.ti.com

Pipeline Phase Cycle # Branch **Target** 1 EP1 . . . E1 PG (A) 2 EP2 EP without branch PS (A) 3 EP3 EP without branch PW (A) EP4 EP without branch PR 4 (A) EP without branch DΡ 5 EP5 (A) LD MPY ADD NOP5 6 EP6 DC Branch Branch will execute here E1 EP7 8 9 10 Normal See Figure 4-32 (b) 11 EP7

Figure 4-32. Branching and Multicycle NOPs

A Delay slots of the branch


In one case, execute packet 1 (EP1) does not have a branch. The **NOP 5** in EP6 forces the CPU to wait until cycle 11 to execute EP7.

In the other case, EP1 does have a branch. The delay slots of the branch coincide with cycles 2 through 6. Once the target code reaches E1 in cycle 7, it executes.

4.4.3 Memory Considerations

The DSP has a memory configuration with program memory in one physical space and data memory in another physical space. Data loads and program fetches have the same operation in the pipeline, they just use different phases to complete their operations. With both data loads and program fetches, memory accesses are broken into multiple phases. This enables the DSP to access memory at a high speed. These phases are shown in Figure 4-33.

Figure 4-33. Pipeline Phases Used During Memory Accesses



To understand the memory accesses, compare data loads and instruction fetches/dispatches. The comparison is valid because data loads and program fetches operate on internal memories of the same speed on the DSP and perform the same types of operations (listed in Table 4-44) to accommodate those memories. Table 4-44 shows the operation of program fetches pipeline versus the operation of a data load.



www.ti.com Performance Considerations

Table 4-44. Program Memory Accesses Versus Data Load Accesses

Operation	Program Memory Access Phase	Data Load Access Phase
Compute address	PG	E1
Send address to memory	PS	E2
Memory read/write	PW	E3
Program memory: receive fetch packet at CPU boundary	PR	E4
Data load: receive data at CPU boundary		
Program memory: send instruction to functional units	DP	E5
Data load: send data to register		

Depending on the type of memory and the time required to complete an access, the pipeline may stall to ensure proper coordination of data and instructions.

A memory stall occurs when memory is not ready to respond to an access from the CPU. This access occurs during the PW phase for a program memory access and during the E3 phase for a data memory access. The memory stall causes all of the pipeline phases to lengthen beyond a single clock cycle, causing execution to take additional clock cycles to finish. The results of the program execution are identical whether a stall occurs or not. Figure 4-34 illustrates this point.

Figure 4-34. Program and Data Memory Stalls

Clock cycle Fetch packet (FP) 4 10 11 13 15 16 E4 PG PS PW PR DP DC E3 E1 E2 E5 n+1 PG PS PW DP DC Ε1 E2 ЕЗ E4 PW DP PG PS PR DC Ε1 E2 n+2 Program E3 PS memory stall n+3 PG DC Data E1 E2 PG PS PW PR DP memory stall DC E1 PG PS PW PR DP DC n+5 n+6 PG PS PW PR DP PG PS PW PR n+7 PG PS PW PG PS n+9 n+10 PG

SPRUFE8B-July 2010 Pipeline 625

626 Pipeline SPRUFE8B-July 2010



Interrupts

This chapter describes CPU interrupts, including reset and the nonmaskable interrupt (NMI). It details the related CPU control registers and their functions in controlling interrupts. It also describes interrupt processing, the method the CPU uses to detect automatically the presence of interrupts and divert program execution flow to your interrupt service code. Finally, this chapter describes the programming implications of interrupts.

Topic Page

5.1	Overview	
5.2	Globally Enabling and Disabling Interrupts	634
5.3	Individual Interrupt Control	637
5.4	Interrupt Detection and Processing	639
5.5	Performance Considerations	648
5.6	Programming Considerations	648



Overview www.ti.com

5.1 Overview

Typically, DSPs work in an environment that contains multiple external asynchronous events. These events require tasks to be performed by the DSP when they occur. An interrupt is an event that stops the current process in the CPU so that the CPU can attend to the task needing completion because of the event. These interrupt sources can be on chip or off chip, such as timers, analog-to-digital converters, or other peripherals.

Servicing an interrupt involves saving the context of the current process, completing the interrupt task, restoring the registers and the process context, and resuming the original process. There are eight registers that control servicing interrupts.

An appropriate transition on an interrupt pin sets the pending status of the interrupt within the interrupt flag register (IFR). If the interrupt is properly enabled, the CPU begins processing the interrupt and redirecting program flow to the interrupt service routine.

5.1.1 Types of Interrupts and Signals Used

There are four types of interrupts on the CPU.

- Reset
- Maskable
- Nonmaskable
- Exception

NOTE: The nonmaskable interrupt (NMI) is not supported on all C6000 devices, see your device-specific data manual for more information.

These first three types are differentiated by their priorities, as shown in Table 5-1. The reset interrupt has the highest priority and corresponds to the RESET signal. The nonmaskable interrupt (NMI) has the second highest priority and corresponds to the NMI signal. The lowest priority interrupts are interrupts 4-15 corresponding to the INT4-INT15 signals. RESET, NMI, and some of the INT4-INT15 signals are mapped to pins on C6000 devices. Some of the INT4-INT15 interrupt signals are used by internal peripherals and some may be unavailable or can be used under software control. Check your device-specific datasheet to see your interrupt specifications.

The CPU supports exceptions as another type of interrupt. When exceptions are enabled, the NMI input behaves as an exception. This chapter does not deal in depth with exceptions, as it assumes for discussion of NMI as an interrupt that they are disabled. Chapter 6 discusses exceptions including NMI behavior as an exception.

CAUTION

Code Compatibility

The CPU code compatibility with existing code compiled for the CPU using NMI as an interrupt is only assured when exceptions are not enabled. Any additional or modified code requiring the use of NMI as an exception to ensure correct behavior will likely require changes to the pre-existing code to adjust for the additional functionality added by enabling exceptions.



www.ti.com Overview

Table 5-1. Interrupt Priorities

Priority	Interrupt Name	Interrupt Type
Highest	Reset	Reset
	NMI	Nonmaskable
	INT4	Maskable
	INT5	Maskable
	INT6	Maskable
	INT7	Maskable
	INT8	Maskable
	INT9	Maskable
	INT10	Maskable
	INT11	Maskable
	INT12	Maskable
	INT13	Maskable
	INT14	Maskable
Lowest	INT15	Maskable

5.1.1.1 Reset (RESET)

Reset is the highest priority interrupt and is used to halt the CPU and return it to a known state. The reset interrupt is unique in a number of ways:

- RESET is an active-low signal. All other interrupts are active-high signals.
- RESET must be held low for 10 clock cycles before it goes high again to reinitialize the CPU properly.
- The instruction execution in progress is aborted and all registers are returned to their default states.
- The reset interrupt service fetch packet must be located at a specific address which is specific to the specific device. See the device datasheet for more information.
- RESET is not affected by branches.

5.1.1.2 Nonmaskable Interrupt (NMI)

NOTE: The nonmaskable interrupt (NMI) is not supported on all C6000 devices, see your device-specific data manual for more information.

NMI is the second-highest priority interrupt and is generally used to alert the CPU of a serious hardware problem such as imminent power failure.

For NMI processing to occur, the nonmaskable interrupt enable (NMIE) bit in the interrupt enable register (IER) must be set to 1. If NMIE is set to 1, the only condition that can prevent NMI processing is if the NMI occurs during the delay slots of a branch (whether the branch is taken or not).

NMIE is cleared to 0 at reset to prevent interruption of the reset. It is cleared at the occurrence of an NMI to prevent another NMI from being processed. You cannot manually clear NMIE, but you can set NMIE to allow nested NMIs. While NMI is cleared, all maskable interrupts (INT4-INT15) are disabled.

On the CPU, if an NMI is recognized within an SPLOOP operation, the behavior is the same as for an NMI with exceptions enabled. The SPLOOP operation terminates immediately (loop does not wind down as it does in case of an interrupt). The SPLX bit in the NMI/exception task state register (NTSR) is set for status purposes. The NMI service routine must look at this as one of the factors on whether a return to the interrupted code is possible. If the SPLX bit in NTSR is set, then a return to the interrupted code results in incorrect operation. See Section 7.13 for more information.

SPRUFE8B-July 2010 Interrupts 629



Overview www.ti.com

5.1.1.3 Maskable Interrupts (INT4-INT15)

The CPUs have 12 interrupts that are maskable. These have lower priority than the NMI and reset interrupts as well as all exceptions. These interrupts can be associated with external devices, on-chip peripherals, software control, or not be available.

Assuming that a maskable interrupt does not occur during the delay slots of a branch (this includes conditional branches that do not complete execution due to a false condition), the following conditions must be met to process a maskable interrupt:

- The global interrupt enable bit (GIE) bit in the control status register (CSR) is set to1.
- The NMIE bit in the interrupt enable register (IER) is set to1.
- The corresponding interrupt enable (IE) bit in the IER is set to1.
- The corresponding interrupt occurs, which sets the corresponding bit in the interrupt flags register (IFR) to 1 and there are no higher priority interrupt flag (IF) bits set in the IFR.

5.1.2 Interrupt Service Table (IST)

When the CPU begins processing an interrupt, it references the interrupt service table (IST). The IST is a table of fetch packets that contain code for servicing the interrupts. The IST consists of 16 consecutive fetch packets. Each interrupt service fetch packet (ISFP) contains up to 14 instructions (either 8 32-bit instructions in a nonheader-based fetch packet or up to 14 instructions in a compact header-based fetch packet). A simple interrupt service routine may fit in an individual fetch packet.

The addresses and contents of the IST are shown in Figure 5-1. Because each fetch packet contains eight 32-bit instruction words (or 32 bytes), each address in the table is incremented by 32 bytes (20h) from the one adjacent to it.

xxxx 000h RESET ISFP xxxx 020h NMI ISEP xxxx 040h Reserved xxxx 060h Reserved xxxx 080h INT4 ISFP xxxx 0A0h INT5 ISFP xxxx 0C0h INT6 ISFP xxxx 0E0h INT7 ISFP xxxx 100h **INT8 ISFP** xxxx 120h INT9 ISFP xxxx 140h INT10 ISFP xxxx 160h INT11 ISFP xxxx 180h INT12 ISFP xxxx 1A0h INT13 ISFP xxxx 1C0h INT14 ISFP xxxx 1E0h INT15 ISFP

Figure 5-1. Interrupt Service Table

Program memory



www.ti.com Overview

5.1.2.1 Interrupt Service Fetch Packet (ISFP)

An ISFP is a fetch packet used to service an interrupt. Figure 5-2 shows an ISFP that contains an interrupt service routine small enough to fit in a single fetch packet (FP). To branch back to the main program, the FP contains a branch to the interrupt return pointer instruction (B IRP). This is followed by a NOP 5 instruction to allow the branch target to reach the execution stage of the pipeline.

NOTE: The ISFP should be exactly 8 words long. To prevent the compiler from using compact instructions (see Section 3.10), the interrupt service table should be preceded by a .nocmp directive. See the TMS320C6000 Assembly Language Tools User's Guide (SPRU186).

If the NOP 5 was not in the routine, the CPU would execute the next five execute packets (some of which are likely to be associated with the next ISFP) because of the delay slots associated with the B IRP instruction. See Section 4.2.6 for more information.




Figure 5-2. Interrupt Service Fetch Packet

If the interrupt service routine for an interrupt is too large to fit in a single fetch packet, a branch to the location of additional interrupt service routine code is required. Figure 5-3 shows that the interrupt service routine for INT4 was too large for a single fetch packet, and a branch to memory location 1234h is required to complete the interrupt service routine.


NOTE: The instruction B LOOP branches into the middle of a fetch packet and processes code starting at address 1234h. The CPU ignores code from address 1220h-1230h, even if it is in parallel to code at address 1234h.

SPRUFE8B-July 2010 631 Interrupts



Overview www.ti.com

Figure 5-3. Interrupt Service Table With Branch to Additional Interrupt Service Code Located Outside the IST





www.ti.com Overview

5.1.2.2 Interrupt Service Table Pointer (ISTP)

The reset fetch packet must be located at the default location (see device data manual for more information), but the rest of the IST can be at any program memory location that is on a 256-word boundary (that is, any 1K byte boundary). The location of the IST is determined by the interrupt service table base (ISTB) field of the interrupt service table pointer register (ISTP). The ISTP is shown in Figure 2-12 and described in Table 2-15. Example 5-1 shows the relationship of the ISTB to the table location.

Since the HPEINT field in ISTP gives the value of the highest priority interrupt that is both pending and enabled, the whole of ISTP gives the address of the highest priority interrupt that is both pending and enabled

Example 5-1. Relocation of Interrupt Service Table

		IST
	0	RESET ISFP
(a) Relocating the IST to 800h		
 Copy IST, located between 0h and 200h, to the memory locat between 800h and A00h. 	ion	
O) White cook to ICTD: MW// cook Ac	xxxx 800h	RESET ISFP
2) Write 800h to ISTP: MVK 800h, A2 MVC A2, ISTP	xxxx 820h	NMI ISFP
	xxxx 840h	Reserved
ISTP = 800h = 1000 0000 0000b	xxxx 860h	Reserved
(I) He should be only the OPH of the control of the OPH of the OPH of the Control of the OPH of t	xxxx 880h	INT4 ISFP
(b) How the ISTP directs the CPU to the appropriate ISFP in the relocated IST	xxxx 8A0h	INT5 ISFP
	xxxx 8C0h	INT6 ISFP
Assume: IFR = BBC0h = 1011 1011 1100 0000b	xxxx 8E0h	INT7 ISFP
IER = 1230h = 0001 0010 0011 0001b	xxxx 900h	INT8 ISFP
2 enabled interrupts pending: INT9 and INT12	xxxx 920h	INT9 ISFP
The 1s in IFR indicate pending interrupts; the 1s in IER	xxxx 940h	INT10 ISFP
indicate the interrupts that are enabled. INT9 has a higher priority than INT12, so HPEINT is encoded with the value for INT9,	xxxx 96h0	INT11 ISFP
01001b.	xxxx 980h	INT12 ISFP
HPEINT corresponds to bits 9-5 of the ISTP:	xxxx 9A0h	INT13 ISFP
ISTP = 1001 0010 0000b = 920h = address of INT9	xxxx 9C0h	INT14 ISFP
	xxxx 9E0h	INT15 ISFP
		Program memory

SPRUFE8B-July 2010 Interrupts 633



5.1.3 Summary of Interrupt Control Registers

Table 5-2 lists the interrupt control registers on the CPU.

Table 5-2. Interrupt Control Registers

Acronym	Register Name	Description	Section
CSR	Control status register	Allows you to globally set or disable interrupts	Section 2.8.4
ICR	Interrupt clear register	Allows you to clear flags in the IFR manually	Section 2.8.6
IER	Interrupt enable register	Allows you to enable interrupts	Section 2.8.7
IFR	Interrupt flag register	Shows the status of interrupts	Section 2.8.8
IRP	Interrupt return pointer register	Contains the return address used on return from a maskable interrupt. This return is accomplished via the B IRP instruction.	Section 2.8.9
ISR	Interrupt set register	Allows you to set flags in the IFR manually	Section 2.8.10
ISTP	Interrupt service table pointer register	Pointer to the beginning of the interrupt service table	Section 2.8.11
ITSR	Interrupt task state register	Interrupted (non-NMI) machine state.	Section 2.9.9
NRP	Nonmaskable interrupt return pointer register	Contains the return address used on return from a nonmaskable interrupt. This return is accomplished via the B NRP instruction.	Section 2.8.12
NTSR	Nonmaskable interrupt task state register	Interrupted (NMI) machine state.	Section 2.9.10
TSR	Task state register	Allows you to globally set or disable interrupts. Contains status of current machine state.	Section 2.9.15

5.2 Globally Enabling and Disabling Interrupts

The control status register (CSR) contains two fields that control interrupts: GIE and PGIE, as shown in Figure 2-4 and described in Table 2-9.

On the CPU, there is one physical GIE bit that is mapped to bit 0 of both CSR and TSR. Similarly, there is one physical PGIE bit. It is mapped as CSR.PGIE (bit 1) and ITSR.GIE (bit 0). Modification to either of these bits is reflected in both of the mappings. In the following discussion, references to the GIE bit in CSR also refer to the GIE bit in TSR, and references to the PGIE bit in CSR also refer to the GIE bit in ITSR.

The global interrupt enable (GIE) allows you to enable or disable all maskable interrupts by controlling the value of a single bit. GIE is bit 0 of both the control status register (CSR) and the task state register (TSR).

- GIE = 1 enables the maskable interrupts so that they are processed.
- GIE = 0 disables the maskable interrupts so that they are not processed.

The CPU detects interrupts in parallel with instruction execution. As a result, the CPU may begin interrupt processing in the same cycle that an **MVC** instruction writes 0 to GIE to disable interrupts. The PGIE bit (bit 1 of CSR) records the value of GIE after the CPU begins interrupt processing, recording whether the program was in the process of disabling interrupts.

During maskable interrupt processing, the CPU finishes executing the current execute packet. The CPU then copies the current value of GIE to PGIE, overwriting the previous value of PGIE. The CPU then clears GIE to prevent another maskable interrupt from occurring before the handler saves the machine's state. (Section 5.6.2 discusses nesting interrupts.)

When the interrupt handler returns to the interrupted code with the **B IRP** instruction, the CPU copies PGIE back to GIE. When the interrupted code resumes, GIE reflects the last value written by the interrupted code.

Because interrupt detection occurs in parallel with CPU execution, the CPU can take an interrupt in the cycle immediately following an **MVC** instruction that clears GIE. The behavior of PGIE and the **B IRP** instruction ensures, however, that interrupts do not occur after subsequent execute packets. Consider the code in Example 5-2.



Example 5-2. Interrupts Versus Writes to GIE

```
;Assume GIE = 1
MVC
     CSR, B0
                    ; (1) Get CSR
AND
     -2,B0,B0
                    ; (2) Get ready to clear GIE
MVC
     B0,CSR
                   ; (3) Clear GIE
     A0,A1,A2
ADD
                   ; (4)
     A3,A4,A5
                    ; (5)
ADD
```

In Example 5-2, the CPU may service an interrupt between instructions 1 and 2, between instructions 2 and 3, or between instructions 3 and 4. The CPU will not service an interrupt between instructions 4 and 5.

If the CPU services an interrupt between instructions 1 and 2 or between instructions 2 and 3, the PGIE bit will hold the value 1 when arriving at the interrupt service routine. If the CPU services an interrupt between instructions 3 and 4, the PGIE bit will hold the value 0. Thus, when the interrupt service routine resumes the interrupted code, it will resume with GIE set as the interrupted code intended.

On the CPU, programs must directly manipulate the GIE bit in CSR to disable and enable interrupts. Example 5-3 and Example 5-4 show code examples for disabling and enabling maskable interrupts globally, respectively.

Example 5-3. Code Sequence to Disable Maskable Interrupts Globally

```
MVC CSR,B0 ; get CSR
AND -2,B0,B0 ; get ready to clear GIE
MVC B0,CSR ; clear GIE
```

Example 5-4. Code Sequence to Enable Maskable Interrupts Globally

```
MVC CSR,B0 ; get CSR
OR 1,B0,B0 ; get ready to set GIE
MVC B0,CSR ; set GIE
```

The CPU handles this process differently, in a manner that is backward compatible with the techniques that the CPU requires. When it begins processing of a maskable interrupt, the CPU copies TSR to ITSR, thereby, saving the old value of GIE. It then clears TSR.GIE. (ITSR.GIE is physically the same bit as CSR.PGIE and TSR.GIE is physically the same bit as CSR.GIE.) When returning from an interrupt with the **B IRP** instruction, the CPU restores the TSR state by copying ITSR back to TSR.

The CPU provides two new instructions that allow for simpler and safer manipulation of the GIE bit.

- The **DINT** instruction disables interrupts by:
 - Copies the value of CSR.GIE (and TSR.GIE) to TSR.SGIE
 - Clears CSR.GIE and TSR.GIE to 0 (disabling interrupts immediately)

The CPU will not service an interrupt between the execute packet containing **DINT** and the execute packet that follows it.

- The RINT instruction restores interrupts to the previous state by:
 - Copies the value of TSR.SGIE to CSR.GIE (and TSR.GIE)
 - Clears TSR.SGIE to 0

If SGIE bit in TSR when **RINT** executes, interrupts are enabled immediately and the CPU may service an interrupt in the cycle immediately following the execute packet containing **RINT**.



Example 5-5 illustrates the use and timing of the **DINT** instruction in disabling maskable interrupts globally and Example 5-6 shows how to enable maskable interrupts globally using the complementary **RINT** instruction.

Example 5-5. Code Sequence with Disable Global Interrupt Enable

```
;Assume GIE = 1
ADD B0,1,B0 ; Interrupt possible between ADD and DINT
DINT ; No interrupt between DINT and SUB
SUB B0,1,B0 ;
```

Example 5-6. Code Sequence with Restore Global Interrupt Enable

```
;Assume SGIE == 1, GIE = 0

ADD B0,1,B0 ; No Interrupt between ADD and RINT

RINT ; Interrupt possible between RINT and SUB

SUB B0,1,B0 ;
```

Example 5-7 shows a code fragment in which a load/modify/store is executed with interrupts disabled so that the register cannot be modified by an interrupt between the read and write operation. Since the **DINT** instruction saves the CSR.GIE bit to the TSR.SGIE bit and the **RINT** instruction copies the TSR.SGIE bit back to the CSR.GIE bit, if interrupts were disabled before the **DINT** instruction, they will still be disabled after the **RINT** instruction. If they were enabled before the **DINT** instruction, they will be enabled after the **RINT** instruction.

Example 5-7. Code Sequence with Disable Reenable Interrupt Sequence

```
DINT
                    ; Disable interrupts
      *B0,B1
T.DW
                    ; Load data
NOP
      3
                    ; Wait for data to reach register
                    ; Set bit in word
OR
      B1,1,B1
STW
      B1,*B0
                    ; Store modified data back to original location
RINT
                    ; Re-enable interrupts
```

NOTE: The use of DINT and RINT instructions in a nested manner, like the following code:

DINT DINT RINT RINT

leaves interrupts disabled after the second **RINT** instruction. The successive use of the **DINT** instruction leaves the TSR.SGIE bit cleared to 0, so the **RINT** instructions copy zero to the GIE bit.



5.3 Individual Interrupt Control

Servicing interrupts effectively requires individual control of all three types of interrupts: reset, nonmaskable, and maskable. Enabling and disabling individual interrupts is done with the interrupt enable register (IER). The status of pending interrupts is stored in the interrupt flag register (IFR). Manual interrupt processing can be accomplished through the use of the interrupt set register (ISR) and interrupt clear register (ICR). The interrupt return pointers restore context after servicing nonmaskable and maskable interrupts.

5.3.1 Enabling and Disabling Interrupts

You can enable and disable individual interrupts by setting and clearing bits in the IER that correspond to the individual interrupts. An interrupt can trigger interrupt processing only if the corresponding bit in the IER is set. Bit 0, corresponding to reset, is not writeable and is always read as 1, so the reset interrupt is always enabled. You cannot disable the reset interrupt. Bits IE4-IE15 can be written as 1 or 0, enabling or disabling the associated interrupt, respectively. The IER is shown in Figure 2-8 and described in Table 2-12.

When NMIE = 0, all nonreset interrupts are disabled, preventing interruption of an NMI. The NMIE bit is cleared at reset to prevent any interruption of process or initialization until you enable NMI. After reset, you must set the NMIE bit to enable the NMI and to allow INT15-INT4 to be enabled by the GIE bit in CSR and the corresponding IER bit. You cannot manually clear the NMIE bit; the NMIE bit is unaffected by a write of 0. The NMIE bit is also cleared by the occurrence of an NMI. If cleared, the NMIE bit is set only by completing a **B NRP** instruction or by a write of 1 to the NMIE bit. Example 5-8 and Example 5-9 show code for enabling and disabling individual interrupts, respectively.

Example 5-8. Code Sequence to Enable an Individual Interrupt (INT9)

```
MVK 200h,B1 ; set bit 9
MVC IER,B0 ; get IER
OR B1,B0,B0 ; get ready to set IE9
MVC B0,IER ; set bit 9 in IER
```

Example 5-9. Code Sequence to Disable an Individual Interrupt (INT9)

```
MVK FDFFh,Bl ; clear bit 9
MVC IER,B0
AND B1,B0,B0 ; get ready to clear IE9
MVC B0,IER ; clear bit 9 in IER
```

5.3.2 Status of Interrupts

The interrupt flag register (IFR) contains the status of INT4-INT15 and NMI. Each interrupt's corresponding bit in IFR is set to 1 when that interrupt occurs; otherwise, the bits have a value of 0. If you want to check the status of interrupts, use the **MVC** instruction to read IFR. The IFR is shown in Figure 2-9 and described in Table 2-13.



5.3.3 Setting and Clearing Interrupts

The interrupt set register (ISR) and the interrupt clear register (ICR) allow you to set or clear maskable interrupts manually in IFR. Writing a 1 to IS4-IS15 in ISR causes the corresponding interrupt flag to be set in IFR. Similarly, writing a 1 to a bit in ICR causes the corresponding interrupt flag to be cleared. Writing a 0 to any bit of either ISR or ICR has no effect. Incoming interrupts have priority and override any write to ICR. You cannot set or clear any bit in ISR or ICR to affect NMI or reset. The ISR is shown in Figure 2-11 and described in Table 2-14. The ICR is shown in Figure 2-7 and described in Table 2-11.

NOTE: Any write to the ISR or ICR (by the MVC instruction) effectively has one delay slot because the results cannot be read (by the MVC instruction) in IFR until two cycles after the write to ISR or ICR.

Any write to ICR is ignored by a simultaneous write to the same bit in ISR.

Example 5-10 and Example 5-11 show code examples to set and clear individual interrupts.

Example 5-10. Code to Set an Individual Interrupt (INT6) and Read the Flag Register



Example 5-11. Code to Clear an Individual Interrupt (INT6) and Read the Flag Register

5.3.4 Returning From Interrupt Servicing

Returning control from interrupts is handled differently for all three types of interrupts: reset, nonmaskable, and maskable.

5.3.4.1 CPU State After RESET

After RESET, the control registers and bits contain the following values:

- AMR, ISR, ICR, and IFR = 0
- ISTP = Default value varies by device (See data manual for correct value)
- IER = 1
- IRP and NRP = undefined
- CSR bits 15-0
 - = 100h in little-endian mode
 - = 000h in big-endian mode
- TSR = 0
- ITSR = 0
- NTSR = 0

The program execution begins at the address specified by the ISTB field in ISTP.



5.3.4.2 Returning From Nonmaskable Interrupts

The NMI return pointer register (NRP), shown in Figure 2-13, contains the return pointer that directs the CPU to the proper location to continue program execution after NMI processing. A branch using the address in NRP (**B NRP**) in your interrupt service routine returns to the program flow when NMI servicing is complete. Example 5-12 shows how to return from an NMI.

The NTSR register will be copied back into the TSR register during the transfer of control out of the interrupt.

Example 5-12. Code to Return From NMI

```
B NRP ; return, sets NMIE
NOP 5 ; delay slots
```

5.3.4.3 Returning From Maskable Interrupts

The interrupt return pointer register (IRP), shown in Figure 2-10, contains the return pointer that directs the CPU to the proper location to continue program execution after processing a maskable interrupt. A branch using the address in IRP (**B IRP**) in your interrupt service routine returns to the program flow when interrupt servicing is complete. Example 5-13 shows how to return from a maskable interrupt.

The ITSR will be copied back into the TSR during the transfer of control out of the interrupt.

Example 5-13. Code to Return from a Maskable Interrupt

```
B IRP ; return, moves PGIE to GIE
NOP 5 ; delay slots
```

5.4 Interrupt Detection and Processing

This section describes interrupts on the CPU.

When an interrupt occurs, it sets a flag in the interrupt flag register (IFR). Depending on certain conditions, the interrupt may or may not be processed. This section discusses the mechanics of setting the flag bit, the conditions for processing an interrupt, and the order of operation for detecting and processing an interrupt. The similarities and differences between reset and nonreset interrupts are also discussed.

5.4.1 Setting the Nonreset Interrupt Flag

Figure 5-4 shows the processing of a nonreset interrupt (INTm) for the CPU. The flag (IFm) for INTm in IFR is set following the low-to-high transition of the INTm signal on the CPU boundary. This transition is detected on a clock-cycle by clock-cycle basis and is not affected by memory stalls that might extend a CPU cycle. Once there is a low-to-high transition on an interrupt pin, the interrupt is detected as pending inside the CPU. When the interrupt signal has been detected (cycle 4). Two clock cycles after detection, the interrupt's corresponding flag bit in IFR is set (cycle 6).

In Figure 5-4, IFm is set during CPU cycle 6. You could attempt to clear bit IFm by using an **MVC** instruction to write a 1 to bit m of ICR in execute packet n + 3 (during CPU cycle 4). However, in this case, the automated write by the interrupt detection logic takes precedence and IFm remains set.

Figure 5-4 assumes INTm is the highest priority pending interrupt and is enabled by the GIE and NMIE bits, as necessary. If it is not the highest priority pending interrupt, IFm remains set until either you clear it by writing a 1 to bit m of ICR, or the processing of INTm occurs.



5.4.1.1 Detection of Missed Interrupts

Each INTm input has a corresponding output that indicates if a low-to-high transition occurred on the input while the pending flag for that input had not yet been cleared. These outputs may be used by the interrupt controller to create an exception back to the CPU to notify the user of the missed interrupt. See your device-specific data manual to verify your device supports this feature.

5.4.2 Conditions for Processing a Nonreset Interrupt

In clock cycle 4 of Figure 5-4, a nonreset interrupt in need of processing is detected. For this interrupt to be processed, the following conditions must be valid on the same clock cycle and are evaluated every clock cycle:

- IFm is set during CPU cycle 6. (This determination is made in CPU cycle 4 by the interrupt logic.)
- There is not a higher priority IFm bit set in IFR.
- The corresponding bit in IER is set (IEm = 1).
- GIE = 1
- NMIE = 1
- The five previous execute packets (n through n + 4) do not contain a branch (even if the branch is not taken) and are not in the delay slots of a branch.
- The two previous execute packets and the current execute packet (n + 3 through n + 5) do note contain an **SPLOOPD**, or **SPLOOPW** instruction.
- If an SPLOOP is active, then the conditions set forth in Section 7.13.1 apply.

Any pending interrupt will be taken as soon as pending branches are completed.






Figure 5-4. Nonreset Interrupt Detection and Processing: Pipeline Operation

A After this point, interrupts are still disabled. All nonreset interrupts are disabled when NMIE = 0. All maskable interrupts are disabled when GIE = 0.

SPRUFE8B–July 2010 Interrupts 641




Figure 5-5. Return from Interrupt Execution and Processing: Pipeline Operation

5.4.3 Saving TSR Context in Nonreset Interrupt Processing

When control is transferred to the interrupt processing sequence, the context needed to return from the ISR is saved in the interrupt task state register (ITSR). The task state register (TSR) is set for the default interrupt processing context. Table 5-3 shows the behavior for each bit in TSR. Figure 5-4 shows the timing of the changes to the TSR bits as well as the CPU outputs used in interrupt processing.

The current execution mode is held in a piped series of register bits allowing a change in the mode to progress from the PS phase through the E1 phase. Fetches from program memory use the PS-valid register which is only loaded at the start of a transfer of control. This value is an output on the program memory interface and is shown in the timing diagram as PCXM. As the target execute packet progresses through the pipeline, the new mode is registered for that stage. Each stage uses its registered version of the execution mode. The field in TSR is the E1-valid version of CXM. It always indicates the execution mode for the instructions executing in E1. The mode is used in the data memory interface, and is registered for all load/store instructions when they execute in E1. This is shown in the timing diagram as DCXM. Note that neither PCXM nor DCXM is visible in any register to you.



Bit	Field	Action
0	GIE	Saved to GIE bit in ITSR (will be 1). Cleared to 0.
1	SGIE	Saved to SGIE bit in ITSR. Cleared to 0.
2	GEE	Saved to GEE bit in ITSR. Unchanged.
3	XEN	Saved to XEN bit in ITSR. Cleared to 0.
7-6	CXM	Saved to CXM bits in ITSR. Cleared to 0 (Supervisor mode).
9	INT	Saved to INT bit in ITSR. Set to 1.
10	EXC	Saved to EXC bit in ITSR. Cleared to 0.
14	SPLX	SPLX is set in the TSR by the SPLOOP buffer whenever it is in operation. Upon interrupt, if the SPLOOP buffer is operating (thus SPLX = 1), then ITSR.SPLX will be set to 1, and the TSR.SPLX bit will be cleared to 0 after the SPLOOP buffer winds down and the interrupt vector is taken. See Section 7.4.5 for more information on SPLOOP.
15	IB	Saved to IB bit in ITSR (will be 0). Set by CPU control logic.

5.4.4 Actions Taken During Nonreset Interrupt Processing

During CPU cycles 6-14 of Figure 5-4, the following interrupt processing actions occur:

- Processing of subsequent nonreset interrupts is disabled.
- The PGIE bit is set to the value of the GIE bit and then the GIE bit is cleared. TSR context is saved into ITSR, and TSR is set to default interrupt processing values as shown in Table 5-3. Explicit (MVC) writes to the TSR are completed before the TSR is saved to the ITSR.
- The next execute packets (from n + 5 on) are annulled. If an execute packet is annulled during a particular pipeline stage, it does not modify any CPU state. Annulling also forces an instruction to be annulled in future pipeline stages.
- The address of the first annulled execute packet (n + 5) is loaded in IRP.
- A branch to the address formed from ISTP (the pointer to the ISFP for INTm) is forced into the E1
 phase of the pipeline during cycle 9.
- IFm is cleared during cycle 8.

5.4.5 Conditions for Processing a Nonmaskable Interrupt

In clock cycle 4 of Figure 5-6, a nonmaskable interrupt (NMI) in need of processing is detected. For this interrupt to be processed, the following conditions must be valid on the same clock cycle and are evaluated every clock cycle:

- The NMIF bit is set during CPU cycle 6. (This determination is made in CPU cycle 4 by the interrupt logic.)
- · Reset is not active.
- NMIE = 1
- The five previous execute packets (n through n + 4) do not contain a branch (even if the branch is not taken) and are not in the delay slots of a branch. Note that this functionality has changed when exceptions are enabled, see Chapter 6 for more information.

A pending NMI will be taken as soon as pending branches are completed.







Figure 5-6. CPU Nonmaskable Interrupt Detection and Processing: Pipeline Operation

A After this point, interrupts are still disabled. All nonreset interrupts are disabled when NMIE = 0. All maskable interrupts are disabled when GIE = 0.



Figure 5-7. CPU Return from Nonmaskable Interrupt Execution and Processing: Pipeline Operation



SPRUFE8B-July 2010 Interrupts 645



5.4.6 Saving of Context in Nonmaskable Interrupt Processing

When control is transferred to the interrupt processing sequence, the context needed to return from the ISR is saved in the nonmaskable interrupt task state register (NTSR). The task state register (TSR) is set for the default NMI processing context. Table 5-4 shows the behavior for each bit in TSR. Figure 5-6 shows the timing of the changes to the TSR bits as well as the CPU outputs used in interrupt processing.

Table 5-4. TSR Field Behavior When an NMI Interrupt is Taken

Bit	Field	Action
0	GIE	Saved to GIE bit in NTSR. Unchanged.
1	SGIE	Saved to SGIE bit in NTSR. Cleared to 0.
2	GEE	Saved to GEE bit in NTSR. Unchanged.
3	XEN	Saved to XEN bit in NTSR. Cleared to 0.
7-6	CXM	Saved to CXM bits in NTSR. Cleared to 0 (Supervisor mode).
9	INT	Saved to INT bit in NTSR. Set to 1.
10	EXC	Saved to EXC bit in NTSR. Cleared to 0.
14	SPLX	SPLX is set in the TSR by the SPLOOP buffer whenever it is in operation. Upon interrupt, if the SPLOOP buffer is operating (thus SPLX = 1), then ITSR.SPLX will be set to 1, and the TSR.SPLX bit will be cleared to 0 after the SPLOOP buffer winds down and the interrupt vector is taken. See Section 7.4.5 for more information on SPLOOP.
15	IB	Saved to IB bit in NTSR. Set by CPU control logic.

5.4.7 Actions Taken During Nonmaskable Interrupt Processing

During CPU cycles 6-14 of Figure 5-6, the following interrupt processing actions occur:

- Processing of subsequent nonreset interrupts is disabled.
- The GIE and PGIE bits are unchanged. TSR context is saved into NTSR, and TSR is set to default NMI processing values as shown in Table 5-4.
- The NMIE bit is cleared.
- The next execute packets (from n + 5 on) are annulled. If an execute packet is annulled during a particular pipeline stage, it does not modify any CPU state. Annulling also forces an instruction to be annulled in future pipeline stages.
- The address of the first annulled execute packet (n + 5) is loaded in NRP.
- A branch to the NMI ISFP (derived from ISTP) is forced into the E1 phase of the pipeline during cycle 9.
- NMIF is cleared during cycle 8.

5.4.8 Setting the RESET Interrupt Flag

RESET must be held low for a minimum of 10 clock cycles. Four clock cycles after RESET goes high, processing of the reset vector begins. The flag for RESET (IF0) in the IFR is set by the low-to-high transition of the RESET signal on the CPU boundary. In Figure 5-8, IF0 is set during CPU cycle 15. This transition is detected on a clock-cycle by clock-cycle basis and is not affected by memory stalls that might extend a CPU cycle.



5.4.9 Actions Taken During RESET Interrupt Processing

A low signal on the RESET pin is the only requirement to process a reset. Once RESET makes a high-to-low transition, the pipeline is flushed and CPU registers are returned to their reset values. The GIE bit, the NMIE bit, and the ISTB bits in ISTP are cleared. For the CPU state after reset, see Section 5.3.4.1.

Note that a nested exception can force an internally-generated reset that does not reset all the registers to their hardware reset state. See Section 6.3.4 for more information.

During CPU cycles 15-21 of Figure 5-8, the following reset processing actions occur:

- Processing of subsequent nonreset interrupts is disabled because the GIE and NMIE bits are cleared.
- A branch to the address held in ISTP (the pointer to the ISFP for INT0) is forced into the E1 phase of the pipeline during cycle 16.
- IF0 is cleared during cycle 17.

NOTE: Code that starts running after reset must explicitly enable the GIE bit, the NMIE bit, and IER to allow interrupts to be processed.




Figure 5-8. RESET Interrupt Detection and Processing: Pipeline Operation

- A IF0 is set on the next CPU cycle boundary after a 4-clock cycle delay after the rising edge of .
- B After this point, interrupts are still disabled. All nonreset interrupts are disabled when NMIE = 0. All maskable interrupts are disabled when GIE = 0.

SPRUFE8B–July 2010 Interrupts 647



Performance Considerations www.ti.com

5.5 Performance Considerations

The interaction of the C6000 CPU and sources of interrupts present performance issues for you to consider when you are developing your code.

5.5.1 General Performance

- Overhead. Overhead for all CPU interrupts is 9 cycles. You can see this in Figure 5-4 and Figure 5-5, where no new instructions are entering the E1 pipeline phase during CPU cycles 6 through 14.
- Latency. Interrupt latency is 13 cycles (21 cycles for RESET). In Figure 5-6, although the interrupt is active in cycle 2, execution of interrupt service code does not begin until cycle 15.
- **Frequency**. The logic clears the nonreset interrupt (IFm) on cycle 8, with any incoming interrupt having highest priority. Thus, an interrupt is can be recognized every second cycle. Also, because a low-to-high transition is necessary, an interrupt can occur only every second cycle. However, the frequency of interrupt processing depends on the time required for interrupt service and whether you reenable interrupts during processing, thereby allowing nested interrupts. Effectively, only two occurrences of a specific interrupt can be recognized in two cycles.

5.5.2 Pipeline Interaction

Because the serial or parallel encoding of fetch packets does not affect the DC and subsequent phases of the pipeline, no conflicts between code parallelism and interrupts exist. There are three operations or conditions that can affect or are affected by interrupts:

- **Branches.** Nonreset interrupts are delayed, if any execute packets n through n + 4 in contain a branch or are in the delay slots of a branch.
- Memory stalls. Memory stalls delay interrupt processing, because they inherently extend CPU cycles.
- Multicycle NOPs. Multicycle NOPs (including the IDLE instruction) operate like other instructions
 when interrupted, except when an interrupt causes annulment of any but the first cycle of a multicycle
 NOP. In that case, the address of the next execute packet in the pipeline is saved in NRP or IRP. This
 prevents returning to an IDLE instruction or a multicycle NOP that was interrupted.

5.6 Programming Considerations

The interaction of the C6000 CPUs and sources of interrupts present programming issues for you to consider when you are developing your code.

5.6.1 Single Assignment Programming

Using the same register to store different variables (called here: multiple assignment) can result in unpredictable operation when the code can be interrupted.

To avoid unpredictable operation, you must employ the single assignment method in code that can be interrupted. When an interrupt occurs, all instructions entering E1 prior to the beginning of interrupt processing are allowed to complete execution (through E5). All other instructions are annulled and refetched upon return from interrupt. The instructions encountered after the return from the interrupt do not experience any delay slots from the instructions prior to processing the interrupt. Thus, instructions with delay slots prior to the interrupt can appear, to the instructions after the interrupt, to have fewer delay slots than they actually have.

Example 5-14 shows a code fragment which stores two variables into A1 using multiple assignment. Example 5-15 shows equivalent code using the single assignment programming method which stores the two variables into two different registers.

For example, before reaching the code in Example 5-14, suppose that register A1 contains 0 and register A0 points to a memory location containing a value of 10. The **ADD** instruction, which is in a delay slot of the **LDW**, sums A2 with the value in A1 (0) and the result in A3 is just a copy of A2. If an interrupt occurred between the **LDW** and **ADD**, the **LDW** would complete the update of A1 (10), the interrupt would be processed, and the **ADD** would sum A1 (10) with A2 and place the result in A3 (equal to A2 + 10). Obviously, this situation produces incorrect results.



In Example 5-15, the single assignment method is used. The register A1 is assigned only to the **ADD** input and not to the result of the **LDW**. Regardless of the value of A6 with or without an interrupt, A1 does not change before it is summed with A2. Result A3 is equal to A2.

Example 5-14. Code Without Single Assignment: Multiple Assignment of A1

```
LDW .D1 *A0,A1
ADD .L1 A1,A2,A3
NOP 3
MPY .M1 A1,A4,A5 ; uses new A1
```

Example 5-15. Code Using Single Assignment

```
LDW .D1 *A0,A6
ADD .L1 A1,A2,A3
NOP 3
MPY .M1 A6,A4,A5 ; uses A6
```

Another method for preventing problems with nonsingle-assignment programming would be to disable interrupts before using multiple assignment, then reenable them afterwards. Of course, you must be careful with the tradeoff between high-speed code that uses multiple-assignment and increasing interrupt latency. When using multiple assignment within software pipelined code, the SPLOOP buffer on the CPU can help you deal with the tradeoff between performance and interruptibility. See Chapter 7 for more information.

5.6.2 Nested Interrupts

Generally, when the CPU enters an interrupt service routine, interrupts are disabled. However, when the interrupt service routine is for one of the maskable interrupts (INT4-INT15), an NMI can interrupt processing of the maskable interrupt. In other words, an NMI can interrupt a maskable interrupt, but neither an NMI nor a maskable interrupt can interrupt an NMI.

Also, there may be times when you want to allow an interrupt service routine to be interrupted by another (particularly higher priority) interrupt. Even though the processor by default does not allow interrupt service routines to be interrupted unless the source is an NMI, it is possible to nest interrupts under software control. To allow nested interrupts, the interrupt service routine must perform the following initial steps in addition to its normal work of saving any registers (including control registers) that it modifies:

- 1. The contents of IRP (or NRP) must be saved
- 2. The contents of the PGIE bit must be saved
- 3. The contents of ITSR must be saved
- 4. The GIE bit must be set to 1



Prior to returning from the interrupt service routine, the code must restore the registers saved above as follows:

- 1. The GIE bit must be first cleared to 0
- 2. The PGIE bit saved value must be restored
- 3. The contents of ITSR must be restored
- 4. The IRP (or NRP) saved value must be restored

Although steps 2, 3, and 4 above may be performed in any order, it is important that the GIE bit is cleared first. This means that the GIE and PGIE bits must be restored with separate writes to CSR. If these bits are not restored separately, then it is possible that the PGIE bit is overwritten by nested interrupt processing just as interrupts are being disabled.

NOTE: When coding nested interrupts for the CPU, the ITSR should be saved and restored to prevent corruption by the nested interrupt.

5.6.3 Manual Interrupt Processing (polling)

You can poll IFR and IER to detect interrupts manually and then branch to the value held in the ISTP as shown below in Example 5-16.

The code sequence begins by copying the address of the highest priority interrupt from the ISTP to the register B2. The next instruction extracts the number of the interrupt, which is used later to clear the interrupt. The branch to the interrupt service routine comes next with a parallel instruction to set up the ICR word.

The last five instructions fill the delay slots of the branch. First, the 32-bit return address is stored in the B2 register and then copied to the interrupt return pointer (IRP). Finally, the number of the highest priority interrupt, stored in B1, is used to shift the ICR word in B1 to clear the interrupt.

Example 5-16. Manual Interrupt Processing

```
ISTP.B2
          MV/C
                                          ; get related ISFP address
                 B2,23,27,B1
          EXTU
                                          ; extract HPEINT
     [B1] B
                 B2
                                         ; branch to interrupt
\prod
     [B1] MVKL
                 1,A0
                                         ; setup ICR word
     [B1] MVKL
                 RET ADR, B2
                                          ; create return address
     [B1] MVKH
                 RET_ADR,B2
     [B1] MVC
                 B2,IRP
                                         ; save return address
     [B1] SHL
                                         ; create ICR word
                 A0,B1,B1
     [B1] MVC
                 B1,ICR
                                          ; clear interrupt flag
                     (Post interrupt service routine Code)
          RET ADR:
```



5.6.4 Traps

A trap behaves like an interrupt, but is created and controlled with software. The trap condition can be stored in any one of the conditional registers: A0, A1, A2, B0, B1, or B2. If the trap condition is valid, a branch to the trap handler routine processes the trap and the return.

Example 5-17 and Example 5-18 show a trap call and the return code sequence, respectively. In the first code sequence, the address of the trap handler code is loaded into register B0 and the branch is called. In the delay slots of the branch, the context is saved in the B0 register, the GIE bit is cleared to disable maskable interrupts, and the return pointer is stored in the B1 register.

The trap is processed with the code located at the address pointed to by the label TRAP_HANDLER. If the B0 or B1 registers are needed in the trap handler, their contents must be stored to memory and restored before returning. The code shown in Example 5-18 should be included at the end of the trap handler code to restore the context prior to the trap and return to the TRAP_RETURN address.

Example 5-17. Code Sequence to Invoke a Trap

```
TRAP HANDLER, BO
    [A1] MVKT.
                                        ; load 32-bit trap address
    [A1] MVKH TRAP_HANDLER,B0
    [A1] B
                В0
                                       ; branch to trap handler
    [A1] MVC
                CSR, B0
                                        ; read CSR
   [A1] AND -2,B0,B1
                                       ; disable interrupts: GIE = 0
                B1,CSR
   [A1] MVC
                                       ; write to CSR
    [A1] MVKL
               TRAP_RETURN, B1
                                       ; load 32-bit return address
   [A1] MVKH TRAP_RETURN,B1
         TRAP RETURN:
                         (post-trap code)
Note: A1 contains the trap condition.
```

Example 5-18. Code Sequence for Trap Return

```
B B1 ; return
MVC B0,CSR ; restore CSR
NOP 4 ; delay slots
```

Often traps are used to handle unexpected conditions in the execution of the code. The CPU provides explicit exception handling support which may be used for this purpose.

Another alternative to using traps as software triggered interrupts is the software interrupt capability (SWI) provided by the DSP/BIOS real-time kernel.

652 Interrupts SPRUFE8B-July 2010



CPU Exceptions

This chapter describes CPU exceptions on the CPU. It details the related CPU control registers and their functions in controlling exceptions. It also describes exception processing, the method the CPU uses to detect automatically the presence of exceptions and divert program execution flow to your exception service code. Finally, the chapter describes the programming implications of exceptions.

Topic Page

6.2 6.3	Overview Exception Control Exception Detection and Processing Performance Considerations	657 659
-	Programming Considerations	

SPRUFE8B-July 2010 CPU Exceptions 653



Overview www.ti.com

6.1 Overview

The exception mechanism on the CPU is intended to support error detection and program redirection to error handling service routines. Error signals generated outside of the CPU are consolidated to one exception input to the CPU. Exceptions generated within the CPU are consolidated to one internal exception flag with information as to the cause in a register. Fatal errors detected outside of the CPU are consolidated and incorporated into the NMI input to the CPU.

6.1.1 Types of Exceptions and Signals Used

There are three types of exceptions on the CPU.

- one externally generated maskable exception
- one externally generated nonmaskable exception,
- a set of internally generated nonmaskable exceptions

Check the device-specific data manual for your external exception specifications.

6.1.1.1 Reset (RESET)

While reset can be classified as an exception, its behavior is fully described in the chapter on interrupts and its operation is independent of the exception mechanism.

6.1.1.2 Nonmaskable Interrupt (NMI)

NMI is also described in the interrupt chapter, and as stated there it is generally used to alert the CPU of a serious hardware problem. The intent of NMI on C6000 devices was clearly for use as an exception. However, the inability of NMI to interrupt program execution independent of branch delay slots lessens its usefulness as an exception input. By default the NMI input retains its behavior for backward compatibility. When used in conjunction with the exception mechanism it will be treated as a nonmaskable exception with the primary behavioral difference being that branch delay slots will not prevent the recognition of NMI. The new behavior is enabled when exceptions are globally enabled. This is accomplished by setting the global exception enable (GEE) bit in the task state register (TSR) to 1. Once the exception mechanism has been enabled, it remains enabled until a reset occurs (GEE can only be cleared by reset). When the GEE bit is set to 1, NMI behaves as an exception. All further discussion of NMI in this chapter is in reference to its behavior as an exception.

For NMI processing to occur, the nonmaskable interrupt enable (NMIE) bit in the interrupt enable register (IER) must be set to 1. If the NMIE bit is set to 1, the only condition that can prevent NMI processing is the CPU being stalled.

The NMIE bit is cleared to 0 at reset to prevent interruption of the reset processing. It is cleared at the occurrence of an NMI to prevent another NMI from being processed. You cannot manually clear NMIE, but you can set NMIE to allow nested NMIs. While NMIE is cleared, all external exceptions are disabled. Internal exceptions are not affected by NMIE.

When NMI is recognized as pending, the NMI exception flag (NXF) bit in the exception flag register (EFR) is set. Unlike the NMIF bit in the interrupt flag register (IFR), the NXF bit is not cleared automatically upon servicing of the NMI. The NXF bit remains set until manually cleared in the exception service routine.

Transitions on the NMI input while the NXF bit is set are ignored. In the event an attempt to clear the flag using the MVC instruction coincides with the automated write by the exception detection logic, the automatic write takes precedence and the NXF bit remains set.

6.1.1.3 Exception (EXCEP)

EXCEP is the maskable external exception input to the CPU. It is enabled by the XEN bit in TSR. For this exception to be recognized, the XEN bit must be set to 1, the GEE bit must be set to 1, and the NMIE bit must be set to 1.

When EXCEP is recognized as pending, the external exception flag (EXF) bit in EFR is set. The EXF bit remains set until manually cleared in the exception service routine.



www.ti.com Overview

6.1.1.4 Internal Exceptions

Internal exceptions are those generated within the CPU. There are multiple causes for internal exceptions. Examples are illegal opcodes, illegal behavior within an instruction, and resource conflicts. Once enabled by the GEE bit, internal exceptions cannot be disabled. They are recognized independently of the state of the NMIE and XEN exception enable bits.

Instructions that have already entered E1 before a context switch begins are allowed to complete. Any internal exceptions generated by these completing instructions are ignored. This is true for both interrupt and exception context switches.

When an internal exception is recognized as pending, the internal exception flag (IXF) bit in EFR is set. The IXF bit remains set until manually cleared in the exception service routine.

6.1.1.5 Exception Acknowledgment

The exception processing (EXC) bit in TSR is provided as an output at the CPU boundary. This signal in conjunction with the IACK signal alerts hardware external to the CPU that an exception has occurred and is being processed.

6.1.2 Exception Service Vector

When the CPU begins processing an exception, it references the interrupt service table (IST). The NMI interrupt service fetch packet (ISFP) is the fetch packet used to service all exceptions (external, internal, and NMI).

In general, the exception service routine for an exception is too large to fit in a single fetch packet, so a branch to the location of additional exception service routine code is required. This is shown in Figure 6-1.

6.1.3 Summary of Exception Control Registers

Table 6-1 lists the control registers related to exceptions on the CPU.

Table 6-1. Exception-Related Control Registers


Acronym	Register Name	Description	Section
ECR	Exception clear register	Used to clear pending exception flags	Section 2.9.3
EFR	Exception flag register	Contains pending exception flags	Section 2.9.4
IER	Interrupt enable register	Contains NMI exception enable (NMIE) bit	Section 2.8.7
IERR	Internal exception report register	Indicates cause of an internal exception	Section 2.9.7
ISTP	Interrupt service table pointer register	Pointer to the beginning of the interrupt service table that contains the exception interrupt service fetch packet	Section 2.8.11
NRP	Nonmaskable interrupt return pointer register	Contains the return address used on return from an exception. This return is accomplished via the B NRP instruction	Section 2.8.12
NTSR	Nonmaskable interrupt/exception task state register	Stores contents of TSR upon taking an exception	Section 2.9.10
REP	Restricted entry point address register	Contains the address to where the SWENR instruction transfers control	Section 2.9.11
TSR	Task state register	Contains global exception enable (GEE) and exception enable (XEN) bits	Section 2.9.15

SPRUFE8B-July 2010 CPU Exceptions 655



Overview www.ti.com

Figure 6-1. Interrupt Service Table With Branch to Additional Exception Service Code Located Outside the IST



656 CPU Exceptions SPRUFE8B-July 2010



www.ti.com Exception Control

6.2 Exception Control

Enabling and disabling individual exceptions is done with the task state register (TSR) and the interrupt enable register (IER). The status of pending exceptions is stored in the exception flag register (EFR). The nonmaskable interrupt return pointer register (NRP) and the nonmaskable interrupt/exception task state register (NTSR) are used to restore context after servicing exceptions. In many cases it is not possible to return to the interrupted code since exceptions can be taken at noninterruptible points.

6.2.1 Enabling and Disabling External Exceptions

Exceptions are globally enabled by the GEE bit in TSR. This bit must be set to 1 to enable any exception processing. Once it is set to 1, the GEE bit can only be cleared by a reset. The GEE bit is the only enable for internal exceptions. Therefore, once internal exceptions have been enabled they cannot be disabled. Global enabling of exceptions also causes the NMI input to be treated as an exception rather than an interrupt.

External exceptions are also qualified by the NMIE bit in IER. An external exception (EXCEP or NMI) can trigger exception processing only if this bit is set. Internal exceptions are not affected by NMIE. The IER is shown in Figure 2-8 and described in Table 2-12. The EXCEP exception input can also be disabled by clearing the XEN bit in TSR.

When NMIE = 0, all interrupts and external exceptions are disabled, preventing interruption of an exception service routine. The NMIE bit is cleared at reset to prevent any interruption of processor initialization until you enable exceptions. After reset, you must set the NMIE bit to enable external exceptions and to allow INT15-INT4 to be enabled by the GIE bit and the appropriate IER bit. You cannot manually clear the NMIE bit; the NMIE bit is unaffected by a write of 0. The NMIE bit is also cleared by the occurrence of an NMI. If cleared, the NMIE bit is set only by completing a **B NRP** instruction or by a write of 1 to NMIE.

6.2.2 Pending Exceptions

EFR contains four bits that indicate which exceptions have been detected. It is possible for all four bits to be set when entering the exception service routine. The prioritization and handling of multiple exceptions is left to software. Clearing of the exception flags is done by writing a 1 to the bit position to be cleared in the exception clear register (ECR). Bits that are written as 0 to ECR have no effect. The EFR is shown in Figure 2-17 and described in Table 2-18.

6.2.3 Exception Event Context Saving

TSR contains the CPU execution context that is saved into NTSR at the start of exception processing. TSR is then set to indicate the transition to supervisor mode and that exception processing is active. The TSR is shown in Figure 2-28 and described in Table 2-23.

Execution of a **B NRP** instruction causes the saved context in NTSR to be loaded into TSR to resume execution. Similarly, a **B IRP** instruction restores context from ITSR into TSR.

Information about the CPU context at the point of an exception is retained in NTSR. Table 6-2 shows the behavior for each bit in NTSR. The information in NTSR is used upon execution of a **B NRP** instruction to restore the CPU context before resuming the interrupted instruction execution. The HWE bit in NTSR is set when an internal or external exception is taken. The HWE bit is cleared by the **SWE** and **SWENR** instructions. The NTSR is shown in Figure 2-23 and described in Table 2-21.

SPRUFE8B-July 2010 CPU Exceptions 657



Exception Control www.ti.com

		Table 6-2. NTSR Field Behavior When an Exception is Taken
Bit	Field	Action
0	GIE	GIE bit in TSR at point exception is taken.
1	SGIE	SGIE bit in TSR at point exception is taken.
2	GEE	GEE bit in TSR at point exception is taken (must be 1).
3	XEN	XEN bit in TSR at point exception is taken.
7-6	CXM	CXM bits in TSR at point exception is taken.
9	INT	INT bit in TSR at point exception is taken.
10	EXC	EXC bit in TSR at point exception is taken (must be 0).
14	SPLX	Terminated an SPLOOP
15	IB	Exception occurred while interrupts were blocked.
16	HWE	Hardware exception taken (NMI, EXCEP, or internal).

6.2.4 Returning From Exception Servicing

The NMI return pointer register (NRP) stores the return address used by the CPU to resume correct program execution after NMI processing. A branch using the address in the NRP (**B NRP**) in your exception service routine causes the program to exit the exception service routine and return to normal program execution.

It is not always possible to safely exit the exception handling routine. Conditions that can prevent a safe return from exceptions include:

- SPLOOPs that are terminated by an exception cannot be resumed correctly. The SPLX bit in NTSR should be verified to be 0 before returning.
- Exceptions that occur when interrupts are blocked cannot be resumed correctly. The IB bit in NTSR should be verified to be 0 before returning.
- Exceptions that occur at any point in the code that cannot be interrupted safely (for example, a tight
 loop containing multiple assignments) cannot be safely returned to. The compiler will normally disable
 interrupts at these points in the program; check the GIE bit in NTSR to be 1 to verify that this condition
 is met.

Example 6-1 shows code that checks these conditions.

If the exception cannot be safely returned from, the appropriate response will be different based on the specific cause of the exception. In some cases, a warm reset will be required. In other cases, restarting a user task may be sufficient.

The NRP contains the 32-bit address of the first execute packet in the program flow that was not executed because of an exception. Although you can write a value to this register, any subsequent exception processing may overwrite that value. The NRP is shown in Figure 2-13.

Example 6-1. Code to Return From Exception

```
STNDW B1:B0,*SP--
                            ; save B0 and B1
     MVC
           NTSR,B0
                                ; read NTSR
B0,16,30,B1
     EXTU
                               ; B1 = NTSR.IB and NTSR.SPLX
           B0,1,B0
     AND
                               ; B0 = NTSR.GIE
[B1]
           0,B0
     MVK
                               ; B0 = 1 if resumable
                               ; if B0 != 0, return
[B0] B
           NRP
     LDNDW *SP++,B1:B0
                               ; restore B0 and B1
     NOP
                                ; delay slots
cant_restart:
     ; code to handle non-resumable case starts here
```



6.3 Exception Detection and Processing

When an exception occurs, it sets a flag in the exception flag register (EFR). Depending on certain conditions, the exception may or may not be processed. This section discusses the mechanics of setting the flag bit, the conditions for processing an exception, and the order of operation for detecting and processing an exception.

6.3.1 Setting the Exception Pending Flag

Figure 6-2 shows the processing of an external exception (EXCEP) for the CPU. The internal pending flag for EXCEP is set following the low-to-high transition of the EXCEP signal on the CPU boundary. This transition is detected on a clock-cycle by clock-cycle basis and is not affected by memory stalls that might extend a CPU cycle. Two clock cycles after detection, the EXCEP exception's corresponding flag bit (EXF) in EFR is set (cycle 6).

Figure 6-2 assumes EXCEP is enabled by the XEN, NMIE, and GEE bits, as necessary.

6.3.2 Conditions for Processing an External Exception

In clock cycle 4 of Figure 6-2, a nonreset exception in need of processing is detected. For this exception to be processed, the following conditions must be valid on the same clock cycle and are evaluated every clock cycle:

- EXF or NXF bit is set during CPU cycle 6. (This determination is made in CPU cycle 4 by the exception/interrupt logic.)
- NMIE = 1
- GEE = 1
- For EXCEP, XEN = 1

Any pending exception will be taken as soon as any stalls are completed.

When control is transferred to the interrupt processing sequence the context needed to return from the ISR is saved in ITSR. TSR is set for the default interrupt processing context. Table 6-3 shows the behavior for each bit in TSR. Figure 6-2 shows the timing of the changes to the TSR bits as well as the CPU outputs used in exception processing.

Fetches from program memory use the PS-valid register that is only loaded at the start of a context switch. This value is an output on the program memory interface and is shown in the timing diagram as PCXM. As the target execute packet progresses through the pipeline, the new mode is registered for that stage. Each stage uses its registered version of the execution mode. The field in TSR is the E1-valid version of CXM. It always indicates the execution mode for the instructions executing in E1. The mode is used in the data memory interface, and is registered for all load/store instructions when they execute in E1. This is shown in the timing diagram as DCXM.

Figure 6-3 shows the transitions in the case of a return from exception initiated by executing a **B NRP** instruction.



CPU cycle $9 \ \vdots \ 10 \ \vdots \ 11 \ \vdots \ 12 \ \vdots \ 13 \ \vdots \ 14 \ \vdots \ 15 \ \vdots \ 16 \ \vdots \ 17 \ \vdots \ 18 \ \vdots \ 19 \ \vdots \ 20 \ \vdots \ 21 \ \vdots \ 22$ EXCEP at CPU bdry EFR.EXF PCXM at point of exception **PCXM** DCXM at point of exception DCXM EXC IER.NMIE TSR.GIE GIE at point of exception TSR.XEN CXM at point of exception TSR.CXM INT at point of exception TSR.INT TSR.EXC SPLX at point of exception TSR.SPLX TSR NTSR Execute packet E1: E2: E3: E4: E5: E6 E7: E8: E9: E10 n n+1 DP: F1 E2: E3: E4: E5: E6: F7 E8: DC E9 E10 n+2 PR: DP DC E1: E2 E3 E4 E5: E7 E8 PW PR DP DC: E4: E5 E8 E9 E10 n+3 E2: E3: E6: E7 E1: n+4 PS: PW PR: DP: DC: E1: E2: E3: E4: E5 E6 E7 E8 E9 E10 n+5 PS PWPR DP DC E1 PS: PW PR DP n+6 E2 PG PS: PW PR DP* n+7 Annulled Instructions n+8 PG PS PW PR* PG PS: PW⁻ n+9 n+10 PG: PS. n+11 PG: Cycles 6-14: Nonreset interrupt processing is disabled PG PS PW PR DP DC **ISFP** E1 E2 E3 E4 E5 E6 E7 CPU cycle 10 11 12 13 15 : 16 : 2 3 9 14 17 18 : 19 :


Figure 6-2. External Exception (EXCEP) Detection and Processing: Pipeline Operation



Table 6-3. TSR Field Behavior When an Exception is Taken (EXC = 0)

Bit	Field	Action
0	GIE	Saved to GIE bit in NTSR. Cleared to 0.
1	SGIE	Saved to SGIE bit in NTSR. Cleared to 0.
2	GEE	Saved to GEE bit in NTSR (will be 1). Unchanged.
3	XEN	Saved to XEN bit in NTSR. Cleared to 0.
7-6	CXM	Saved to CXM bits in NTSR. Set to Supervisor mode.
9	INT	Saved to INT bit in NTSR. Cleared to 0.
10	EXC	Saved to EXC bit in NTSR. Set to 1.
14	SPLX	Saved to SPLX bit in NTSR. Cleared to 0.
15	IB	Saved to IB bit in NTSR. Set by CPU control logic.

Figure 6-3. Return from Exception Processing: Pipeline Operation



SPRUFE8B-July 2010 CPU Exceptions 661



Performance Considerations www.ti.com

6.3.3 Actions Taken During External Exception (EXCEP) Processing

During CPU cycles 6-14 of Figure 6-2, the following exception processing actions occur:

- Processing of subsequent EXCEP exceptions is disabled by clearing the XEN bit in TSR.
- Processing of interrupts is disabled by clearing the GIE bit in TSR.
- The next execute packets (from n + 5 on) are annulled. If an execute packet is annulled during a particular pipeline stage, it does not modify any CPU state. Annulling also forces an instruction to be annulled in future pipeline stages.
- The address of the first annulled execute packet (n + 5) is loaded in to NRP.
- A branch to the NMI ISFP is forced into the E1 phase of the pipeline during cycle 9.
- During cycle 7, IACK and EXC are asserted to indicate the exception is being processed. INUM is also valid in this cycle with a value of 1.

6.3.4 Nested Exceptions

When the CPU enters an exception service routine, the EXC bit in TSR is set to indicate an exception is being processed. If a new exception is recognized while this bit is set, then the reset vector is used when redirecting program execution to service the second exception. In this case, NTSR and NRP are left unchanged. TSR is copied to ITSR and the current PC is copied to IRP. TSR is set to the default exception processing value and the NMIE bit in IER is cleared in this case preventing any further external exceptions.

The NTSR, ITSR, IRP, and the NRP can be tested in the users boot code to determine if reset pin initiated reset or a reset caused by a nested exception.

6.4 Performance Considerations

6.4.1 General Performance

- Overhead. Overhead for all CPU exceptions on the CPU is 9 cycles. You can see this in Figure 6-2, where no new instructions are entering the E1 pipeline phase during CPU cycles 6 through 14.
- Latency. Exception latency is 13 cycles. If the exception is active in cycle 2, execution of exception service code does not begin until cycle 15.
- **Frequency**. The pending exceptions are not automatically cleared upon servicing as is the case with interrupts.

6.4.2 Pipeline Interaction

Because the serial or parallel encoding of fetch packets does not affect the DC and subsequent phases of the pipeline, no conflicts between code parallelism and exceptions exist. There are two operations or conditions that can affect, or are affected by, exceptions:

- Memory stalls. Memory stalls delay exception processing, because they inherently extend CPU cycles.
- **Multicycle NOPs.** Multicycle NOPs (including the **IDLE** instruction) operate like other instructions when interrupted by an exception, except when an exception causes annulment of any but the first cycle of a multicycle **NOP**. In that case, the address of the next execute packet in the pipeline is saved in NRP. This prevents returning to an **IDLE** instruction or a multicycle **NOP** that was interrupted.



Figure 6-4. NMI Exception Detection and Processing: Pipeline Operation 9 10 11 12 13 14 15 16 17 18 19 20 21 22 CPU cycle NMI at CPU bdry EFR.NXF **PCXM** PCXM at point of exception DCXM DCXM at point of exception EXC IER.NMIE TSR.GIE GIE at point of exception TSR.XEN TSR.CXM CXM at point of exception TSR.INT INT at point of exception TSR.EXC TSR.SPLX SPLX at point of exception TSR: NTSR Execute packet DC: E1: E2: E3: E4: E5: E6: E7: E8 E9 E10 n n+1 DP: DC E1: E2: E3 E4: F5: E6: E7: E8: E9:E10 n+2 PR DP DC E1 E2 E3 E4: E5 E6 E7 E8 E9 E10 PW PR: DP E3 : E4: n+3 DC E2 E5 E6 E7 E8 E9 E10 E1 DP: E2 E3 E4 E5 E6 E7 E8 E9 E10 n+4 PS: PW: PR: DC E1: n+5 PS PWPR DP DC E1 PG: PS PW: PR DP n+6 E2 * PS: PG PW PR DP * n+7 Annulled Instructions n+8 PG PS PWPR* PS: PW* n+9 PG n+10 PG PS * n+11 PG • Cycles 6-14: Nonreset interrupt processing is disabled E1 E2 E3 E4 **ISFP** PG PS PW PR DP DC E5 E6 E7 CPU cycle 5 10 11 12 : 13 : 14 15 16 17 18 | 19 20

SPRUFE8B-July 2010 CPU Exceptions 663



Performance Considerations www.ti.com




Figure 6-5. Double Exception Detection and Processing: Pipeline Operation

CPU cycle

8

9 : 10

11 12 13

14 | 15 | 16 | 17 | 18 | 19 | 20 |



6.5 Programming Considerations

There are two types of exceptions that can result directly from instruction execution. The first is an intentional use via the **SWE** or **SWENR** instructions. The second is execution error detection exceptions that are internally generated within the CPU. These internal exceptions are primarily intended to facilitate program debug.

6.5.1 Internal Exceptions

Causes of internal exceptions:

- Fetch error
 - Program memory fetch error (privilege, parity, etc.)
 - Single input from L1P returned with data indicates error
 - Two branches taken in same execute packet
 - Branch to middle of 32-bit instruction in header-based fetch packet
 - Branch to header
- Illegal fetch packets
 - Reserved fetch packet header
- Illegal opcode
 - Specified set of reserved opcodes
 - Header not in word 7
- Privilege violation
 - Access to restricted control register
 - Attempt to execute restricted instruction
- · Register write conflicts
- Loop buffer exceptions (SPLOOP, SPKERNEL)
 - Unit conflicts
 - Missed (but required) stall
 - Attempt to enter early-exit in reload while draining
 - Unexpected SPKERNEL
 - Write to ILC or RILC in prohibited timing window
 - Multicycle NOP prior to SPKERNEL or SPKERNELR instruction

6.5.2 Internal Exception Report Register (IERR)

The internal exception report register (IERR) contains flags that indicate the cause of the internal exception. In the case of simultaneous internal exceptions, the same flag may be set by different exception sources. In this case, it may not be possible to determine the exact causes of the individual exceptions. The IERR is shown in Figure 2-20 and described in Table 2-19.

SPRUFE8B-July 2010 CPU Exceptions 665



6.5.3 Software Exception

6.5.3.1 SWE Instruction

When an **SWE** instruction is executed, the SXF bit in EFR is set. On the following cycle, the exception detection logic sees the SXF bit in EFR as a 1, and takes an exception. This instruction can be used to effect a system call while running in User mode. Execution of the instruction results in transfer of control to the exception service routine operating in Supervisor mode. If the SXF bit is the only bit set in EFR, then the exception can be interpreted as a system service request. An appropriate calling convention using the general-purpose registers may be adopted to provide parameters for the call. This is left as a programming choice. An example of code to quickly detect the system call case at the beginning of the exception service routine is shown in Example 6-2. Since other exceptions are in general error conditions and interrupt program execution at nonreturnable points, the need to process these is not particularly time critical.

Example 6-2. Code to Quickly Detect OS Service Request

```
B0.*SP--
      STW
                                     ; save B0
             EFR,B0
                                     ; read EFR
Ш
      MVC
                                    ; is SEF the only exception?
      CMPEO B0,1,B0
[B0]
     В
             OS_Service
                                    ; if so,
[B0]
                                     ; conditionally execute service
      . . .
                                     ; code until branch takes effect
[B0]
```

6.5.3.2 SWENR Instruction

The **SWENR** instruction causes a software exception to be taken similarly to that caused by the **SWE** instruction. It is intended for use in systems supporting a secure operating mode. The **SWENR** instruction can be used as a mechanism for nonsecure programs to return to secure Supervisor mode services such as an interrupt dispatcher. It differs from the **SWE** instruction in four ways:

- 1. TSR is not copied into NTSR
- 2. No return address is placed in NRP (it stays unmodified)
- 3. A branch to restricted entry point control register (REP) is forced in the context switch rather than the ISTP-based exception (NMI) register.
- 4. The IB bit in TSR is set to 1. This is observable only in the case where another exception is recognized simultaneously.

If another exception (internal or external) is recognized simultaneously with the **SWENR**-raised exception, then the other exceptions(s) take priority and normal exception behavior occurs; that is, NTSR and NRP are used, execution is directed to the NMI vector. In this case, the setting of the IB bit in TSR by the **SWENR** instruction is registered in NTSR. Assuming the **SWE** or **SWENR** instruction was not placed in an execute slot where interrupts are architecturally blocked (as should always be the case), then the IB bit in NTSR will differentiate whether the simultaneous exception occurred with **SWE** or **SWENR**.

The **SWENR** instruction causes a change in control to the address contained in REP. It should have been previously initialized to a correct value by a privileged supervisor mode process.

666 CPU Exceptions SPRUFE8B-July 2010



Software Pipelined Loop (SPLOOP) Buffer

This chapter describes the software pipelined loop (SPLOOP) buffer hardware and software mechanisms.

Under normal circumstances, the compiler/assembly optimizer will do a good job coding SPLOOPs and it will not be necessary for the programmer to hand code usage of the SPLOOP buffer. This chapter is intended to describe the functioning of the buffer hardware and the instructions that control it.

Topic Page

7.1	Software Pipelining	668
7.2	Software Pipelining	
7.3	Terminology	
7.4	SPLOOP Hardware Support	
7.5	SPLOOP-Related Instructions	
7.6	Basic SPLOOP Example	
7.7	Loop Buffer	
7.8	Execution Patterns	
7.9	Loop Buffer Control Using the Unconditional SPLOOP(D) Instruction	
7.10	Loop Buffer Control Using the SPLOOPW Instruction	
7.11	Using the SPMASK Instruction	692
7.12	Program Memory Fetch Control	
7.13	Interrupts	
7.14	Branch Instructions	
7.15	Instruction Resource Conflicts and SPMASK Operation	699
7.16	Restrictions on Cross Path Stalls	700
7.17	Restrictions on AMR-Related Stalls	700
7.18	Restrictions on Instructions Placed in the Loop Buffer	701



Software Pipelining www.ti.com

7.1 Software Pipelining

Software pipelining is a type of instruction scheduling that exploits instruction level parallelism (ILP) across loop iterations. Modulo scheduling is a form of software pipelining that initiates loop iterations at a constant rate, called the initiation interval (ii). To construct a modulo scheduled loop, a single loop iteration is divided into a sequence of stages, each with length ii. In the steady state of the execution of the software pipelined loop, each of the stages is executing in parallel.

The instruction schedule for a modulo scheduled loop has three components: a kernel, a prolog, and an epilog (Figure 7-1). The kernel is the instruction schedule that executes the pipeline steady state. The prolog and epilog are the instruction schedules that setup and drain the execution of the loop kernel. In Figure 7-1, the steady state has four stages, each from a different iteration, executing in parallel. A single iteration produces a result in the time it takes four stages to complete, but in the steady state of the software pipeline, a result is available every stage (that is, every ii cycles).

The first prolog stage, P0, is equal to the first loop stage, S0. Each prolog stage, Pn (where n > 0), is made up of the loop stage, Sn, plus all the loop stages in the previous prolog stage, Pn - 1. The kernel includes all the loop stages. The first epilog stage, E0, is made up of the kernel stage minus the first loop stage, S0. Each epilog stage, En (where n > 0), is made up of the previous epilog stage, En - 1, minus the loop stage, Sn.

The dynamic length (dynlen) of the loop is the number of instruction cycles required for one iteration of the loop to complete. The length of the prolog is (dynlen – ii). The length of the epilog is the same as the length of the prolog.




Figure 7-1. Software Pipelined Execution Flow

7.2 Software Pipelining

The SPLOOP facility on the DSP stores a single iteration of loop in a specialized buffer and contains hardware that will selectively overlay copies of the single iteration in a software pipeline manner to construct an optimized execution of the loop.

This provides the following benefits.

- Since the prolog and epilog do not need to be explicitly code, code size is significantly reduced.
- The SPLOOP version of the loop can be easily interrupted unlike the non- SPLOOP version of the same loop.
- Since the instructions in the loop do not need to be fetched on each cycle, the memory bandwidth and power requirements are reduced.
- Since the loop executes out of a buffer, the branch to the start of loop is implicit (hence not required).
 In some cases this may permit a tighter loop since a .S unit is freed.



www.ti.com Terminology

7.3 Terminology

The following terminology is used in the discussion in this chapter.

- Iteration interval (ii) is the interval (in instruction cycles) between successive iterations of the loop.
- A stage is the code executed in one iteration interval.
- Dynamic length (dynlen) is the length (in instruction cycles) of a single iteration of the loop. It is therefore equal to the number of stages times the iteration interval.5
- The kernel is the period when the loop is executing in a steady state with the maximum number of loop iterations executing simultaneously. For example: in Figure 7-1 the kernel is the set of instructions contained in stage 0, stage 1, stage, 2, and stage 3.
- The prolog is the period before the loop reaches the kernel in which the loop is winding up. The length of the prolog will by the dynamic length minus the iteration interval (dynlen ii).
- The epilog is the period after the loop leaves the kernel in which the loop is winding down. The length of the prolog will by the dynamic length minus the iteration interval (dynlen ii).

7.4 SPLOOP Hardware Support

The basic hardware support for the SPLOOP operation is:

- · Loop buffer
- Loop buffer count register (LBC)
- Inner loop count register (ILC)
- Reload inner loop count register (RILC)
- Task state register (TSR)
- Interrupt task state register (ITSR)
- NMI/Exception task state register (NTSR)

7.4.1 Loop Buffer

The loop buffer is used to store the instructions that comprise the loop and information describing the sequence that the instructions were added to the buffer and the state (active or inactive) of each instruction.

The loop buffer has enough storage for up to 14 execute packets.

7.4.2 Loop Buffer Count Register (LBC)

A loop buffer count register (LBC) is maintained as an index into the loop buffer. It is cleared to 0 when an **SPLOOP, SPLOOPD** or **SPLOOPW** instruction is encountered and is incremented by 1 at the end of each cycle. When LBC becomes equal to the iteration interval (ii) specified by the **SPLOOP, SPLOOPD** or **SPLOOPW** instruction, then a stage boundary has been reached and LBC is reset to 0 and the inner loop count register (ILC) is decremented.

There are two LBCs to support overlapped nested loops. LBC is not a user-visible register.

7.4.3 Inner Loop Count Register (ILC)

The inner loop count register (ILC) is used as a down counter to determine when the SPLOOP is complete when the SPLOOP is initiated by either a **SPLOOP** or **SPLOOPD** instruction. When the loop is initiated using a **SPLOOPW** instruction, the ILC is not used to determine when the SPLOOP is complete. It is decremented once each time a stage boundary is encountered; that is, whenever the loop buffer count register (LBC) becomes equal to the iteration interval (ii).

There is a 4 cycle latency between when ILC is loaded and when its contents are available for use. When used with the **SPLOOP** instruction, it should be loaded 4 cycles before the **SPLOOP** instruction is encountered. ILC must be loaded explicitly using the **MVC** instruction.



7.4.4 Reload Inner Loop Count Register (RILC)

The reload inner loop count register (RILC) is used for resetting the inner loop count register (ILC) for the next invocation of a nested inner loop. There is a 4 cycle latency between when RILC is loaded with the **MVC** instructions and when the value loaded to RILC is available for use. RILC must be loaded explicitly using the **MVC** instruction.

7.4.5 Task State Register (TSR), Interrupt Task State Register (ITSR), and NMI/Exception Task State Register (NTSR)

The SPLX bit in the task state register (TSR) indicates whether an SPLOOP is currently executing or not executing.

When an interrupt occurs, the contents of TSR (including the SPLX bit) is copied to the interrupt task state register (ITSR).

When an exception or non-maskable interrupt occurs, the contents of TSR (including the SPLX bit) is copied to the NMI/Exception task state register (NTSR).

See Section 2.9.15 for more information on TSR. See Section 2.9.9 for more information on ITSR. See Section 2.9.10 for more information on NTSR.

7.5 SPLOOP-Related Instructions

The following instructions are used to control the operation of an SPLOOP:

- SPLOOP, SPLOOPD, and SPLOOPW
- SPKERNEL and SPKERNELR
- SPMASK and SPMASKR

7.5.1 SPLOOP, SPLOOPD, and SPLOOPW Instructions

One of the **SPLOOPD**, **SPLOOPD**, or **SPLOOPW** (collectively called **SPLOOP(D/W)**) instructions are used to invoke the loop buffer mechanism. They each fulfil the same basic purpose, but differ in details. In each case, they must be the first instruction of the execute packet containing it. They cannot be placed in the same execute packet as any instruction that initiates a multicycle NOP (for example: **BNOP** or **NOP** *n*).

When you know in advance the number of iterations that the loop will execute, you can use the **SPLOOP** or **SPLOOPD** instructions. If you do not know the exact number of iterations that the loop should execute, you can use the **SPLOOPW** in a fashion similar to a do-while loop.

The **SPLOOP(D/W)** instructions each clear the loop buffer count register (LBC), load the iteration interval (ii), and start the LBC counting.

7.5.1.1 SPLOOP Instruction

The **SPLOOP** instruction is coded as:

[cond] SPLOOP ii

The ii parameter is the iteration interval which specifies the interval (in instruction cycles) between successive iterations of the loop.

The **SPLOOP** instruction is used when the number of loop iterations is known in advance. The number of loop iterations is determined by the value loaded to the inner loop count register (ILC). ILC should be loaded with an initial value 4 cycles before the **SPLOOP** instruction is encountered.

The (optional) conditional predication is used to indicate when and if a nested loop should be reloaded. The contents of the reload inner loop counter (RILC) is copied to ILC when either a **SPKERNELR** or a **SPMASKR** instruction is executed with the predication condition on the **SPLOOP** instruction true. If the loop is not nested, then the conditional predication should not be used.



7.5.1.2 SPLOOPD Instruction

The **SPLOOPD** instruction is coded as:

[cond] SPLOOPD ii

The ii parameter is the iteration interval which specifies the interval (in instruction cycles) between successive iterations of the loop.

The **SPLOOPD** instruction is used to initiate a loop buffer operation when the known minimum iteration count of the loop is great enough that the inner loop count register (ILC) can be loaded in parallel with the **SPLOOPD** instruction and the 4 cycle latency will have passed before the last iteration of the loop.

Unlike the **SPLOOP** instruction, the load of ILC is performed in parallel with the **SPLOOPD** instruction. Due to the inherent latency of the load to ILC, the value to ILC should be predecremented to account for the 4 cycle latency. The amount of the predecrement is given in Table 7-4.

The number of loop iterations is determined by the value loaded to ILC.

The (optional) conditional predication is used to indicate when and if a nested loop should be reloaded. The contents of the reload inner loop counter (RILC) is copied to ILC when either a **SPKERNELR** or a **SPMASKR** instruction is executed with the predication condition on the **SPLOOP** instruction true. If the loop is not nested, then the conditional predication should not be used.

The use of the **SPLOOPD** instruction can result in reducing the time spent in setting up the loop by eliminating up to 4 cycles that would otherwise be spent in setting up ILC. The tradeoff is that the **SPLOOPD** instruction cannot be used if the loop is not long enough to accommodate the 4 cycle delay.

7.5.1.3 SPLOOPW Instruction

The **SPLOOPW** instruction is coded as:

[cond] SPLOOPW ii

The ii parameter is the iteration interval which specifies the interval (in instruction cycles) between successive iterations of the loop.

The **SPLOOPW** instruction is used to initiate a loop buffer operation when the total number of loops required is not known in advance. The **SPLOOPW** instruction must be predicated. The loop terminates if the predication condition is not true. The value in the inner loop count register (ILC) is not used to determine the number of loops.

Unlike the **SPLOOPD** and **SPLOOPD** instructions, predication on the **SPLOOPW** instruction does not imply a nested SPLOOP operation. The **SPLOOPW** instruction cannot be used in a nested SPLOOP operation.

When using the **SPLOOPW** instruction, the predication condition is used to determine the exit condition for the loop. The ILC is not used for this purpose when using the **SPLOOPW** instruction.

When the **SPLOOPW** instruction is used to initiate a loop buffer operation, the epilog is skipped when the loop terminates.

7.5.2 SPKERNEL and SPKERNELR Instructions

The **SPKERNEL** or the **SPKERNELR** (collectively called **SPKERNEL(R)**) instruction is used to mark the end of the software pipelined loop. The **SPKERNEL(R)** instruction is placed in parallel with the last execute packet of the SPLOOP code body indicating that there are no more instructions to load to the loop buffer.

The **SPKERNEL(R)** instruction also controls the point in the epilog that the execution of post-SPLOOP instructions begin.

In each case, the **SPKERNEL(R)** instruction must be the first instruction in an execute packet and cannot be placed in the same execute packet as any instruction that initiates multicycle NOPs.



7.5.2.1 SPKERNEL Instruction

The **SPKERNEL** instruction is coded as:

SPKERNEL (fstg, fcyc)

The (optional) *fstg* and *fcyc* parameters specify the delay interval between the **SPKERNEL** instruction and the start of the post epilog code. The *fstg* specifies the number of complete stages and the *fcyc* specifies the number of cycles in the last stage in the delay.

The **SPKERNEL** instruction has arguments that instruct the SPLOOP hardware to begin execution of post-SPLOOP instructions by an amount of delay (stages/cycles) after the start of the epilog.

Note that the post-epilog instructions are fetched from program memory and overlaid with the epilog instructions fetched from the SPLOOP buffer. Functional unit conflicts can be avoided by either coding for a sufficient delay using the **SPKERNEL** instruction arguments or by using the **SPMASK** instruction to inhibit the operation of instructions from the buffer that might conflict with the instructions from the epilog.

7.5.2.2 SPKERNELR Instruction

The SPKERNELR instruction is coded as:

SPKERNELR

The **SPKERNELR** instruction is used to support nested SPLOOP execution where a loop needs to be restarted with perfect overlap of the prolog of the second loop with the epilog of the first loop.

If a reload is required with a delay between the **SPKERNEL** and the point of reload (that is, nonperfect overlap) use the **SPMASKR** instruction with the **SPKERNEL** (not **SPKERNELR**) to indicate the point of reload.

The **SPKERNELR** instruction has no arguments. The execution of post-SPLOOP instructions commences simultaneous with the first cycle of epilog. If the predication of the **SPLOOP** instruction indicates that the loop is being reloaded, the instructions are fetched from both the SPLOOP buffer and of program memory.

The **SPKERNELR** instruction cannot be used in the same SPLOOP operation as the **SPMASKR** instruction.

7.5.3 SPMASK and SPMASKR Instructions

The **SPMASK** and **SPMASKR** (collectively called **SPMASK(R)**) instructions are used to inhibit the operation of instructions on specified functional units within the current execute packet.

- If there is an instruction from the buffer that would utilize the specified functional unit in the current cycle, the execution of that instruction is inhibited.
- If the buffer is in the loading stage and there is an instruction (regardless of functional unit) that is scheduled for execution during that cycle, the execution of that instruction proceeds, but the instruction is not loaded into the buffer.
- If the case where an SPMASK(R) instruction is encountered while the loop is resuming after returning
 from an interrupt, the SPMASK(R) instruction causes the instructions coming from the buffer to
 execute, but instructions coming from program memory to be inhibited and are not loaded to the buffer.

The **SPMASKR** instruction is identical to the function of the **SPMASK** instruction with one additional operation. In the case of nested loops where it is not desired that the reload of the buffer happen immediately after the **SPKERNEL** instruction, the **SPMASKR** instruction can be used to mark the point in the epilog that the reload should begin.

The **SPMASKR** instruction cannot be used in the same SPLOOP operation as the **SPKERNELR** instruction.

The SPMASK and SPMASKR instructions are coded as:

SPMASK (unitmask)
SPMASKR (unitmask)



www.ti.com Basic SPLOOP Example

The unitmask parameter specifies which functional units are masked by the **SPMASK** or **SPMASKR** instruction. The units may alternatively be specified by marking the instructions with a caret (^) symbol. The following two forms are equivalent and will each mask the .D1 unit. Example 7-1 and Example 7-2 show the two ways of specifying the masked instructions.

Example 7-1. SPMASK Using Unit Mask to Indicate Masked Unit

```
SPMASK D1 ;Mask .D1 unit
|| LDW .D1 *A0,A1 ;This instruction is masked
|| MV .L1 A2,A3 ;This instruction is NOT masked
```

Example 7-2. SPMASK Using Caret to Indicate Masked Unit

```
SPMASK ;Mask .D1 unit
||^ LDW .D1 *A0,A1 ;This instruction is masked
|| MV .L1 A2,A3 ;This instruction is NOT masked
```

7.6 Basic SPLOOP Example

This section discusses a simple SPLOOP example. Example 7-3 shows an example of a loop coded in C and Example 7-4 shows an implementation of the same loop using the **SPLOOP** instruction. The loop copies a number of words from one location in memory to another.

Example 7-3. Copy Loop Coded as C Fragment

```
for (I=0; i<val; I++) {
         dest[i]=source[i];
     }</pre>
```

Example 7-4. SPLOOP Implementation of Copy Loop

```
MVC
               .S2
                    8.ILC
                                   ;Do 8 loops
   NOP
              3
                                    ;4 cycle for ILC to load
   SPLOOP
              1
                                   ;Iteration interval is 1
               *A1++,A2
   LDW
                                   ;Load source
                                   ;Wait for source to load
   MV
              .L2X A2,B2
                                   ;Position data for write
   SPKERNEL
                                    ; End loop and store value
              6,0
              B2,*B0++
|| STW
```

Example 7-5 is an alternate implementation of the same loop using the **SPLOOPD** instruction. The load of the inner loop count register (ILC) can be made in the same cycle as the **SPLOOPD** instruction, but due to the inherent delay between loading the ILC and its use, the value needs to be predecremented to account for the 4 cycle delay.

Example 7-5. SPLOOPD Implementation of Copy Loop

```
SPLOOPD
                                 ;Iteration interval is 1
             .S2 8-4,ILC
Ш
   MVC
                                 ;Do 8 iterations
             *A1++,A2
   LDW
                                 ;Load source
   NOP
             4
                                 ;Wait for source to load
   MV
             .L1X A2,B2
                                 ;Position data for write
   SPKERNEL
             6,0
                                 ; End loop and store value
  STW
             B2,*B0++
```

Basic SPLOOP Example www.ti.com

Table 7-1. SPLOOP Instruction Flow for Example 7-4 and Example 7-5

					Loop			
Cycle	1	2	3	4	5	6	7	8
1	LDW							
2	NOP	LDW						
3	NOP	NOP	LDW					
4	NOP	NOP	NOP	LDW				
5	NOP	NOP	NOP	NOP	LDW			
6	MV	NOP	NOP	NOP	NOP	LDW		
7	STW	MV	NOP	NOP	NOP	NOP	LDW	
8		STW	MV	NOP	NOP	NOP	NOP	LDW
9			STW	MV	NOP	NOP	NOP	NOP
10				STW	MV	NOP	NOP	NOP
11					STW	MV	NOP	NOP
12						STW	MV	NOP
13							STW	MV
14								STW

7.6.1 Some Points About the Basic SPLOOP Example

Note the following points about Example 7-4, Example 7-5, and Table 7-1.

- In Example 7-4, due to the 4 cycle latency of loading ILC, the load to ILC happens at least 4 cycles before the SPLOOP instruction is encountered. In this case, the MVC instruction that loads ILC is followed by 3 cycles of NOP.
- In Example 7-5, the use of the SPLOOPD instruction allows you to load ILC in the same cycle of the SPLOOPD instruction; but the value loaded to ILC is adjusted to account for the inherent 4 cycle delay between loading the ILC and its use.
- The iteration interval (ii) is specified in the argument of the SPLOOP instruction.
- The termination condition (ILC equal to 0) is tested at every stage boundary. In this example, with ii equal to 1, it is tested at each instruction cycle. Once the termination condition is true, the loop starts draining.
- Cycles 1 through 6 constitute the prolog. Until cycle 7, the pipeline is filling.
- Cycles 7 and 8 each constitute a single iteration of the kernel. During each of these cycles, the pipeline
 is filled as full as it is going to be.
- Cycles 9 through 14 constitute the epilog. During this interval, the pipeline is draining.
- In this example, the iteration interval is 1. A new iteration of the loop is started each cycle.
- The dynamic length (dynlen) is 7. One cycle for the **LDW** instruction. One cycle for the **MV** instruction. One instruction for the **SPKERNEL** and **STW** instructions executed in parallel. Four cycles of NOP.
- The length of the prolog is (dynlen ii) = 6 cycles. The length of the epilog is equal to the length of the prolog.
- There is no branch back to the start of the loop. The instructions are executed from the SPLOOP buffer and the SPKERNEL instruction marks the point that the execution is reset to the start of the buffer.
- The body of the SPLOOP is a single scheduled iteration without pipeline optimization. The execution of the SPLOOP overlays the execution of the instructions to optimize the execution of the loop.
- The argument in the **SPKERNEL** instruction indicates that the post-epilog code is delayed until after the epilog (6 cycles) completes.
- The MV instruction needs to be there to move the data between the A side and the B side. If it were
 not there, there would eventually be a unit conflict between the LDW and STW instructions as they try
 to execute in the same cycle.



www.ti.com Basic SPLOOP Example

7.6.2 Same Example Using the SPLOOPW Instruction

For completeness, Example 7-6 shows an example of a loop coded in C and Example 7-7 is the same example using the **SPLOOPW** instruction. The **SPLOOPW** instruction is intended to support while–loop constructions in which the number of loops is not known in advance and (in general) is determined as the loop progresses.

Example 7-6. Example C Coded Loop

Example 7-7. SPLOOPW Implementation of C Coded Loop

```
8,A0
                                      ;Do 8 loops
       MVK
   [!A0] SPLOOPW
                                         ;Check loop
       LDW
                 .D1
                       *A1++,A2
                                      ;Load source value
       NOP
                 1
       SUB
                 .S1
                       A0,1,A0
                                      ;Adjust loop counter
       NOP
                 2
                                      ;Wait for source to load
                 .L2X A2,B2
                                     ;Position data for write
       MV
       SPKERNEL
                0,0
                                      ;End loop
                 .D2 B2,*B0++
STW
                                     ;Store value
```

Table 7-2. SPLOOPW Instruction Flow for Example 7-7

	Loop											
Cycle	1	2	3	4	5	6	7	8	9	10	11	12
1	LDW											
2	NOP	LDW										
3	SUB	NOP	LDW									
4	NOP	SUB	NOP	LDW								
5	NOP	NOP	SUB	NOP	LDW							
6	MV	NOP	NOP	SUB	NOP	LDW						
7	STW	MV	NOP	NOP	SUB	NOP	LDW					
8		STW	MV	NOP	NOP	SUB	NOP	LDW				
9			STW	MV	NOP	NOP	SUB	NOP	LDW			
10				STW	MV	NOP	NOP	SUB	NOP	LDW		
11					STW	MV	NOP	NOP	SUB	NOP	LDW	
12						STW	MV	NOP	NOP	SUB	NOP	LDW



Loop Buffer www.ti.com

7.6.3 Some Points About the SPLOOPW Example

Note the following points about Example 7-7 and Table 7-2.

• Unlike the **SPLOOP** and **SPLOOPD** instructions, the number of loops does not depend on ILC. It depends, instead, on the value in the predication register used with the **SPLOOPW** instruction (in this case, the value in A0).

- The termination condition (A0 equal to 0) is tested at every stage boundary. In this example, with ii equal to 1, it is tested at each instruction cycle. Once the termination condition is true, the loop terminates abruptly without executing the epilog.
- The termination condition (A0 equal to 0) needs to be true 3 cycles before you actually test it, so the
 value of A0 needs to be adjusted 4 cycles before the SPKERNEL instruction. In this case, the SUB
 instruction was positioned using the NOP instructions so that its result would be available 3 cycles
 before the SPKERNEL.
- Unlike the SPLOOP and SPLOOPD instructions, the SPLOOPW instruction causes the loop to exit
 without an epilog. In cycle 13, the loop terminates abruptly.
- Loop 9 through loop 14 begin, but they do not finish. The loop exits abruptly on the stage boundary 3 cycles after the termination condition becomes true. It is important that the loop is coded so that the extra iterations of the early instructions do not cause problems by overwriting significant locations. For example: if the loop contains an early write to a buffer we might find that in incorrectly coded loop might write beyond the end of the buffer overwriting data unintentionally.

7.7 Loop Buffer

The basic facility to support software pipelined loops is the loop buffer. The loop buffer has storage for up to 14 execute packets. The buffer is filled from the SPLOOP body that follows an **SPLOOP(D/W)** instruction and ends with the first execute packet containing an **SPKERNEL** instruction.

The SPLOOP body is a single, scheduled iteration of the loop. It consists of one or more stages of ii cycles each. The execution of the prolog, kernel, and epilog are generated from copies of this single iteration time shifted by multiples of ii cycles and overlapped for simultaneous execution. The final stage may contain fewer than ii cycles, omitting the final cycles if they have only **NOP** instructions.

The dynamic length (dynlen) is the length of the SPLOOP body in cycles starting with the cycle after the **SPLOOP(D)** instruction. The dynamic length counts both execute packets and NOP cycles, but does not count stall cycles. The loop buffer can accommodate a SPLOOP body of up to 48 cycles.

Example 7-8 demonstrates counting of dynamic length. There are 4 cycles of NOP that could be combined into a single **NOP 4**. It is split up here to be clearer about the cycle and stage boundaries.

Example 7-8. SPLOOP, SPLOOP Body, and SPKERNEL

```
SPLOOP
                                       ;ii=2, dynlen=7
                 A0,A1
                                       ; save previous cond reg
       MV
;----Start of stage 0
                                    ;cycle 1
                 *B7[A0],A5
       LDW
       NOP
                                      ;cycle 2
;----stage boundary. End of stage 0, start of stage 1
                                      ;cycles 3 and 4
;----stage boundary. End of stage 1, start of stage 2
                                      ;cycle 5
       NOP
                 A5,12,7,A6
       EXTU
                                      ;cycle 6
;----stage boundary. End of stage 2, start of stage 3
                 U,U ;last exe pkt of SPLOOOP body
.Dl A6,A7,A7 ;accumulate ;
       SPKERNEL 0,0
ADD
       NOP
                                      ; can omit final NOP of last stage
;----stage boundary. End of stage 3
```



www.ti.com Loop Buffer

7.7.1 Software Pipeline Execution From the Loop Buffer

The loop buffer is the mechanism that both generates the execution of the loop prolog, kernel, and epilog, and saves the repeated fetching and decoding of instructions in the loop. As the SPLOOP body is fetched and executed the first time, it is loaded into the loop buffer. By the time the entire SPLOOP body has been loaded into the loop buffer, the loop kernel is present in the loop buffer and the execution of the loop kernel can be entirely from the loop buffer. The last portion of the software pipeline is the epilog; which is generated by removing instructions from the buffer in the order that they were loaded into it.

In Table 7-3, the instructions in the CPU pipeline are executed from program memory. The instructions in the SPL buffer are executed from the SPLOOP buffer. At K0 for example, stage3 is being executed from program memory and stage0, stage1, and stage2 are being executed from the SPLOOP buffer. At Kn and later, by contrast, all stages are being executed from the SPLOOP buffer.

	•		•	•		
Execution Flow	low CPU Pipeline		SPL I	SPL Buffer		
P0	stage0	-				
P1	stage1	stage0				
P2	stage2	stage0	stage1			
K0	stage3	stage0	stage1	stage2		
Kn	-	stage0	stage1	stage2	stage3	
E0	-	-	stage1	stage2	stage3	
E1	-	-	-	stage2	stage3	
E2	-	-	-	-	stage3	

Table 7-3. Software Pipeline Instruction Flow Using the Loop Buffer

7.7.2 Stage Boundary Terminology

A stage boundary is reached every ii cycles. The following terminology is used to describe specific stage boundaries.

- First loading stage boundary: The first stage boundary after the SPLOOP(D/W) instruction. The stage boundary at the end of P0 in Table 7-3.
- Last loading stage boundary: The first stage boundary that occurs in parallel with or after the SPKERNEL instruction. The stage boundary at the end of K0 in Table 7-3. This is the same as the first kernel stage boundary.
- First kernel stage boundary: The same as the last loading stage boundary.
- Last kernel stage boundary: The last stage boundary before the loop is only executing epilog instructions. The stage boundary at the end of Kn in Table 7-3.



Loop Buffer www.ti.com

7.7.3 Loop Buffer Operation

On the cycle after an **SPLOOP(D/W)** instruction is encountered, instructions are loaded into the loop buffer. A loop buffer count register (LBC) is maintained as an index into the loop buffer. At the end of each cycle, LBC is incremented by 1. If LBC becomes equal to the ii, then a stage boundary has been reached and LBC is reset to 0. There are two LBCs to support overlapped nested loops.

The loop buffer has four basic operations:

- Load: instructions fetched from program memory are executed and written into the loop buffer at the current LBC and marked as valid on the next cycle
- **Fetch:** valid instructions are fetched from the loop buffer at the current LBC and executed in parallel with any instructions fetched from program memory.
- Drain: instructions at the current LBC are marked as invalid on the current cycle and not executed.
- Reload: instructions at the current LBC are marked as valid on the current cycle and executed.

The execution of a software pipeline prolog and the first kernel stage are implemented by fetching valid instructions from the loop buffer and executing them in parallel with instructions fetched from program memory. The instructions fetched from program memory are loaded into the loop buffer and marked as valid on the next cycle. The execution of the remaining kernel stages is implemented by exclusively fetching valid instructions from the loop buffer. The execution of a software pipeline epilog is implemented by draining the loop buffer by marking instructions as invalid, while fetching the remaining valid instructions from the loop buffer.

For example: referring to Example 7-4 and Table 7-1; as each instruction in loop 1 is reached in turn, it is fetched from program memory, executed and stored in the loop buffer. When each instruction is reached in loop 2 through loop 12, it is fetched from the loop buffer and executed. As cycles 8 through 12 execute, instructions in the loop buffer are marked as invalid so that for each cycle fewer instructions are fetched from the loop buffer.

The loop buffer supports the execution of a nested software pipelined loop by reenabling the instructions stored in the loop buffer. The reexecution of the software pipeline prolog is implemented by reenabling instructions in the loop buffer (by marking them as valid) and then fetching valid instructions from the loop buffer. The point of reload for the nested loop is signaled by the **SPKERNELR** or **SPMASKR** instruction.

The loop buffer also supports do-while type of constructs in which the number of iterations is not known in advance, but is determined in the course of the execution of the loop. In this case, the loop immediately completes after the last kernel stage without executing the epilog.

7.7.3.1 Interrupt During SPLOOP Operation

If an interrupt occurs while a software pipeline is executing out of the loop buffer, the loop will pipe down by executing an epilog and then service the interrupt. The interrupt return address stored in the interrupt return pointer register (IRP) or the nonmaskable interrupt return pointer register (NRP) is the address of the execute packet containing the **SPLOOP** instruction. The task state register (TSR) is copied into the interrupt task state register (ITSR) or the NMI/exception task state register (NTSR) with the SPLX bit set to 1. On return from the interrupt with ITSR or NTSR copied back into TSR and the SPLX bit set to 1, execution is resumed at the address of the **SPLOOP(D/W)** instruction, and the loop is piped back up by executing a prolog.

7.7.3.2 Loop Buffer Active or Idle

After reset the loop buffer is idle. The loop buffer becomes active when an **SPLOOP(D/W)** instruction is encountered. The loop buffer remains active until one of the following conditions occur:

- The loop buffer is not reloading and after the last delay slot of a taken branch.
- The SPLOOPW loop stage boundary termination condition is true.
- An interrupt occurs and the loop finishes draining in preparation for interrupt (prior to taking interrupt).
- The SPLOOP(D) loop is finished draining and the loop is not reloading.

When the loop buffer is active, the SPLX bit in TSR is set to 1; when the loop buffer is idle, the SPLX bit in TSR is cleared to 0.



www.ti.com Loop Buffer

There is one case where the SPLX bit is set to 1 when the loop buffer is idle. When executing a **B IRP** instruction to return to an interrupted SPLOOP, the ITSR is copied back into TSR in the E1 stage of the branch. The SPLX bit is set to 1 beginning in the E2 stage of the branch, which is before the loop buffer has restarted. If the loop buffer state machine is started in the branch delay slots of a **B IRP** or **B NRP** instruction, it uses the SPLX bit to determine if this is a restart of an interrupted SPLOOP. The SPLX bit is not checked if starting an SPLOOP outside the delay slots of one of these branches.

7.7.3.3 Loading Instructions into the Loop Buffer

A loading counter is used to keep track of the current offset from the beginning of the loop and to determine the dynlen. The loading counter is incremented each cycle until an **SPKERNEL** instruction is encountered. When an **SPLOOP(D/W)** instruction is encountered, LBC and the loading counter are cleared to 0. On each cycle thereafter, the instructions fetched from program memory are stored in the loop buffer indexed by LBC along with a record of the loading counter. On the next cycle, these instructions appear as valid in the loop buffer.

When the **SPKERNEL** instruction is encountered, the loop is finished loading, the dynlen is assigned the current value of the loading counter, and program memory fetch is disabled. If the SPKERNEL is on the last kernel stage boundary, program memory fetch may immediately be reenabled (or effectively never disabled).

SPMASKed instructions from program memory are not stored in the loop buffer. The **BNOP** <displacement> instruction does not use a functional unit and cannot be specified by the **SPMASK** instruction, so this instruction is treated in the same way as an **SPMASK**ed instruction.

When returning to an **SPLOOP(D)** instruction with the SPLX bit in TSR set to 1, **SPMASK**ed instructions from program memory execute like a **NOP**. The NOP cycles associated with **ADDKPC**, **BNOP**, or protected **LD** instructions that are masked, are always executed when resuming an interrupted SPLOOP(D).

A warning or error (detected by the assembler) occurs when loading if:

- An MVC, ADDKPC, or S-unit B (branch) instruction appears in the SPLOOP body and the instruction is not masked by an SPMASK instruction.
- Another SPLOOP(D) instruction is encountered.
- The loading counter reaches 48 before an SPKERNEL instruction is encountered.
- · A resource conflict occurs when storing an instruction in the loop buffer.
- The dynlen is less than ii + 1 for SPLOOP(D) or dynlen < ii for SPLOOPW.

The assembler will ensure that there are no resource conflicts that would occur if the first kernel stage were actually reached.

7.7.3.4 Fetching (Dispatching) Instructions from the Loop Buffer

After the first loading stage boundary, instructions marked as valid in the loop buffer at the current LBC are fetched from the loop buffer and executed in parallel with any instructions fetched from program memory. Once fetching begins, it continues until the loop buffer is no longer active for the given loop.

Instructions fetched from the loop buffer that are masked by an **SPMASK** instruction are not executed. An instruction fetched from program memory may execute on the units that were used by an **SPMASK**ed instruction. (See Section 7.15).

7.7.3.5 Disabling (Draining) Instructions in the Loop Buffer

The loop buffer starts draining:

- On the cycle after the loop termination condition is true
- On the cycle after the interrupt is detected and the conditions required for taking the interrupt are met (see Section 7.13).

The draining counter is used to retrace the order in which instructions were loaded into the loop buffer. The draining counter is initialized to 0 and then incremented by 1 each cycle. Instructions in the loop buffer are marked as invalid in the order that they were loaded.



Execution Patterns www.ti.com

Instructions in the loop buffer indexed by LBC are marked as invalid if their loading counter value (from when they were loaded into the loop buffer) is equal to the draining counter value.

When the draining counter is equal to (dynlen - ii), draining is complete. Any remaining valid instructions for the loop (with a loading counter > (dynlen - ii)) are all marked as invalid.

If the loop is interrupt draining, then program memory fetch remains disabled until the interrupt is taken. If the loop is normal draining, program memory fetch is enabled after a delay specified by the **SPKERNEL(R)** instruction.

7.7.3.6 Enabling (Reloading) Instructions in the Loop Buffer

On the cycle after the reload condition is true (see Section 7.9.6), the loop buffer begins reloading instructions in the loop buffer. Instructions in the loop buffer are marked as valid in the order that they were originally loaded.

The reloading counter is initialized to 0 and then incremented by 1 each cycle until it equals the dynlen. The reloading counter is used to retrace the order in which instructions were loaded into the loop buffer.

Instructions in the loop buffer indexed by LBC are marked as valid, if their loading counter value (from when they were written into the loop buffer) is equal to the reloading counter value.

Reloading does not have to start on a stage boundary. Reloading and draining may access different offsets in the loop buffer. Therefore, there are two LBCs. When reload begins, the unused LBC (the one not being used for draining) is allocated for reloading.

When the reloading counter is equal to the dynlen, the reloading of the software pipeline loop is complete, all the original loop instructions have been reenabled, and the reloading counter stops incrementing.

Program memory fetch of the epilog is disabled when the reload counter equals the dynlen or after the last delay slot of a branch that executed with a true condition. In general, the branch is used in a nested loop to place the PC back at the address of the execute packet after the **SPKERNEL(R)** instruction to reuse the same epilog code between each execution of the inner loop.

A hardware exception is raised while reloading if the termination condition is true and the draining counter for the previous invocation of the loop has not reached the value of dynlen – ii. This describes a condition where both invocations of the loop are attempting to drain at the same time (this could happen, for example, if the RILC value was smaller than the ILC value).

7.8 Execution Patterns

The four loop buffer operations (load, fetch, drain, and reload) are combined in ways that implement various software pipelined loop execution patterns. The three execution patterns are:

- Full execution of a single loop (Section 7.8.1)
- Early exit from a loop (Section 7.8.2)
- Reload of a loop (Section 7.8.3)

7.8.1 Prolog, Kernel, and Epilog Execution Patterns

Figure 7-2 shows a generalization of the basic prolog, kernel, and epilog execution pattern. For simplicity these patterns assume that the **SPKERNEL** instruction appears on a stage boundary.

In Figure 7-3, the termination condition is true on the first kernel stage boundary K0, and falling through to the epilog, the software pipeline only executes a single kernel stage.



www.ti.com Execution Patterns

Execution pattern Coperation

P0
P1
P2
K0
Kn
E0


E1

E2

Figure 7-2. General Prolog, Kernel, and Epilog Execution Pattern

Figure 7-3. Single Kernel Stage Execution Pattern

Drain



7.8.2 Early-Exit Execution Pattern

If the termination condition is true before an **SPKERNEL(R)** instruction is encountered, then the epilog execution pattern begins before the prolog execution pattern is complete. Since the loop has started draining before it has finished loading, this is referred to as an early-exit.

The execution of a software pipeline early-exit is implemented by beginning to drain the loop buffer by disabling instructions in the order that they were originally loaded, fetching the remaining valid instructions from the loop buffer, and then loading the instructions fetched from program memory into the loop buffer and marking them as valid on the next cycle. An early-exit execution pattern is shown in Figure 7-4. In this case the termination condition was found to be true at the end of P1.

If the termination condition is encountered on the first stage boundary (end of P0) as in Figure 7-5, then no instructions actually execute from the loop buffer. In this special case of early-exit, the loop is only executing a single iteration.



Execution Patterns www.ti.com

Figure 7-4. Early-Exit Execution Pattern





Figure 7-5. Single Loop Iteration Execution Pattern



7.8.3 Reload Execution Pattern

The loop buffer can reload a software pipeline by reactivating the instructions that are stored in the loop buffer. A reload prolog uses the information stored in the loop buffer to reenable instructions in the order that they were originally loaded during the initial prolog.

In Figure 7-6, the loop buffer begins executing a reload prolog while completing the epilog of a previous invocation of the same loop.

The execution of a reload early-exit is implemented by reloading (marking as valid) instructions in the loop buffer, disabling (marking as invalid) instructions in the loop buffer, and then fetching the remaining valid instructions from the loop buffer. A reload early-exit execution pattern is shown in Figure 7-7.




www.ti.com Execution Patterns

Loop buffer Execution pattern operation P0₁ P1₁ P2₁ $K0_1$ Fetch Kn_1 E0₁ $P0_2$ Drain E1₁ P1₂ Load E2₁ P2₂ K0₂Fetch Kn_2 $E0_2$ Drain $E1_2$

Figure 7-6. Reload Execution Pattern

Figure 7-7. Reload Early-Exit Execution Pattern

 $E2_2$





7.9 Loop Buffer Control Using the Unconditional SPLOOP(D) Instruction

The unconditional form of the **SPLOOP(D)** instruction uses an inner loop count register (ILC) as a down counter, it can delay execution of program memory instructions overlapped with epilog instructions, and it can reload to support nested loops.

7.9.1 Initial Termination Condition Test and ILC Decrement

The termination condition is the set of conditions which determine whether or not to continue the execution of an SPLOOP. The initial termination condition is the value of the termination condition upon entry to the SPLOOP. When using the SPLOOPW or SPLOOPD, the initial termination condition is always false. When using the SPLOOP, the initial termination condition is true if ILC is equal to zero, false otherwise.

If the initial termination condition is true, then the following occur:

- Non-SPMASKed instructions are stored in the loop buffer as disabled.
- Non-SPMASKed instructions execute as NOPs.
- SPMASKed program memory instructions execute as normal.

If the initial termination condition is true and the **SPKERNEL** instruction is unconditional, the loop buffer is idle after the last loading stage boundary. If the **SPKERNEL** instruction is not on a stage boundary, the loop buffer issues NOPs until the last loading stage boundary. If the **SPKERNEL** instruction is conditional, indicating a possible reload, then the reload condition is evaluated at the last loading stage boundary.

When all of the following conditions are true, ILC is decremented:

- An unconditional SPLOOP (not SPLOOPD) instruction is encountered.
- ILC is not 0.

The bottom line is, the minimum number of iterations:

- is zero for an SPLOOP:
- depends on the iteration interval, but will be at least one iteration for an SPLOOPD;
- will be at least one iteration for an SPLOOPW.

7.9.2 Stage Boundary Termination Condition Test and ILC Decrement

The stage boundary termination condition is true when a stage boundary is reached and ILC is equal to 0; otherwise, the stage boundary termination condition is false. When the stage boundary termination condition is true, the loop buffer starts draining instructions.

When all of the following conditions are true, ILC is decremented:

- · A stage boundary has been reached.
- ILC is not 0.
- The loop is not interrupt draining.
- The loop will not start interrupt draining on the next cycle.

For the first 3 cycles of a loop initiated by an unconditional **SPLOOPD** instruction, the stage boundary termination condition is always false, ILC decrement is disabled, and the loop cannot be interrupted.

If the loop is interrupted and after interrupt draining is complete, ILC contains the current number of remaining loop iterations.

Example 7-9 shows a case in which the value loaded to ILC is determined at run time. The loop may begin draining at any point whenever the ILC decrements to zero (that is, the loop may execute 0 or more iterations). The comments in the example show the stage number (N), the test for termination and the conditional decrement of ILC. ILC will not decrement below zero.



Example 7-9. Using ILC With the SPLOOP Instruction

```
MVC
                A1,ILC
                                   ; ILC = A1
   NOP
                                   ;delay slot 1
    NOP
                                   ;delay slot 2
    ZERO
                Δ3
                                   ;delay slot 3
    SPLOOP
                1
                                   ;Initial, term_condition=!ILC, if (ILC) ILC--;
                                  ;Stage 0, term_condition=!ILC, if (ILC) ILC--;;Stage 1, term_condition=!ILC, if (ILC) ILC--;
                *A5++,A2
    LDW
   NOP
   NOP
                                   ;Stage 2, term_condition=!ILC, if (ILC) ILC--;
   NOP
                                   ;Stage 3, term_condition=!ILC, if (ILC) ILC--;
   NOP
                                   ;Stage 4, term_condition=!ILC, if (ILC) ILC--;
                5,0
                                   ;Delay fetch until done with epilog;
    SPKERNEL
ADD
                A2,A3,A3
                                   ;StageN, term_condition=!ILC, if (ILC) ILC--;
    MV
                A3,A4
```

7.9.3 Using SPLOOPD for Loops with Known Minimum Iteration Counts

For loops with known iteration counts, the unconditional **SPLOOPD** instruction is used to compensate for the 4-cycle latency to the assignment of ILC. The unconditional **SPLOOPD** instruction differs from the **SPLOOP** instruction in the following ways:

- The initial termination condition test is always false and the initial ILC decrement is disabled. The loop must execute at least one iteration.
- The stage boundary termination condition is forced to false, and ILC decrement is disabled for the first 3 cycles of the loop.
- The loop cannot be interrupted for the first 3 cycles of the loop.

The **SPLOOPD** will test the SPLX bit in the TSR to determine if it is already set to one (indicating a return from interrupt). In this case the **SPLOOPD** instruction executes like an unconditional **SPLOOP** instruction.

The **SPLOOPD** instruction is used when the loop is known to execute for a minimum number of loop iterations. The required minimum of number of iterations is a function of ii, as shown in Table 7-4.

Table 7-4. SPLOOPD Minimum Loop Iterations

ii	Minimum Number of Loop Iterations
1	4
2	2
3	2
≥ 4	1

When using the **SPLOOPD** instruction, ILC must be loaded with a value that is biased to compensate for the required minimum number of loop iterations. As shown in Example 7-10, for a loop with an ii equal to 1 that will execute 100 iterations, ILC is loaded with 96.



Example 7-10. Using ILC With a SPLOOPD Instruction

```
MVK
             96,B1 ;Execute 96+4 iterations
   SPLOOPD
             1
                             ;Initial, term condition=false
   MVC
             B1,ILC
                             ;ILC=A1 (E1 Stage)
   ZERO
             Δ3
   LDW
             *A1++,A2
                           ;Stage0, term condition=false
   NOP
                             ;Stagel, term condition=false
   NOP
                             ;Stage2, term condition=false
   NOP
                             ;Stage3, term_cond=!ILC; if (ILC) ILC--;
                             ;Stage3, term_cond=!ILC; if (ILC) ILC--;
   NOP
   SPKERNEL
                             ;StageN, term_cond=!ILC; if (ILC) ILC--;
            A2,A3,A3
|| ADD
```

7.9.4 Program Memory Fetch Enable Delay During Epilog

After the last kernel stage boundary, program memory fetch is enabled such that instructions are fetched from program memory and executed in parallel with instructions fetched from the loop buffer. This provides for overlapping post-loop instructions with loop epilog instructions.

Program memory fetch enable is delayed until a specific stage and cycle in the execution of the epilog. The **SPKERNEL** instruction fstg and fcyc operands are combined (by the assembler) to calculate the delay in instruction cycles:

$$delay = (fstg * ii) + fcyc$$

Program memory fetch is delayed until the following conditions are all true:

- The loop has reached the last kernel stage boundary
- The loop is not interrupt draining
- The draining counter has reached the delay value specified by fstg and fcyc.

Referring back to Example 7-4, the program memory fetch delay is set to start fetching after the last epilog instruction.

If the loop buffer goes to idle (for example, if the epilog is smaller than the specified delay or if the loop early-exit execution pattern), program memory fetch is enabled and the fetch enable delay is ignored.

7.9.5 Stage Boundary and SPKERNEL(R) Position

An **SPKERNEL(R)** instruction does not have to occur on a stage boundary. If an **SPKERNEL(R)** instruction is not on a stage boundary and the loop executes 0 or 1 iteration, then the loop buffer executes until the last loading stage boundary. If there are instructions in between the **SPKERNEL(R)** instruction and the last loading stage boundary, the loop buffer issues **NOP** instructions and program memory fetch remains disabled.

If the loop is reloading and the loop executes 0 or 1 iteration, then the loop buffer executes until the last reloading stage boundary. Between when the reloading counter becomes equal to the dynlen and the last reloading stage boundary, the loop buffer issues **NOP** instructions.

7.9.6 Loop Buffer Reload

Using the conditional form of the **SPLOOP(D)** instruction, the loop buffer supports the execution of a nested loop by reloading a new loop invocation while draining the previous invocation of the loop. A loop that reloads must have either an **SPKERNELR** instruction to end the loop body or an **SPMASKR** instruction in the post-**SPLOOP** code.

Under all of the following conditions, the reload condition is true.

- The loop is on the last kernel stage boundary (that is, ILC = 0).
- The SPLOOP(D) instruction condition is true 4 cycles before the last kernel stage boundary.



7.9.6.1 Reload Start

When the reload condition is true, reenabling of instructions in the loop buffer begins on the cycle after:

- the last kernel stage boundary for loops using SPKERNELR
- an **SPMASKR** is encountered in the post-**SPLOOP** instruction stream.

The reload does not have to start on a stage boundary of the draining loop as indicated by the second and third conditions above.

7.9.6.2 Resetting ILC With RILC

The reload inner loop count register (RILC) is used for resetting the inner loop count register (ILC) for the next invocation of the nested inner loop. There is a 4-cycle latency (3 delay slots) between an instruction that writes a value to RILC and the value appearing to the loop buffer.

If the initial termination condition is false, then the value stored in RILC is extracted, decremented and copied into ILC and normal reloading begins. The value of RILC is unchanged.

If RILC is equal to 0 on the cycle before the reload begins, the initial termination condition is true for the reloaded loop. If the initial termination condition is true, then the reloaded loop invocation is skipped: the instructions in the loop buffer execute as NOPs until the last reloading stage boundary and the reload condition is evaluated again.

7.9.6.3 Program Memory Fetch Disable During Reload

After the reload condition becomes true, program memory fetch is disabled after the last delay slot of a branch that executed with a true condition or after the reload counter equals the dynlen.

The PC remains at its current location when program memory fetch is disabled. If a branch disabled program memory fetch, then the PC remains at the branch target address.

Note that the first condition above is the only time that the loop buffer will not go to idle after the last delay slot of a taken branch.

7.9.6.4 Restrictions on Interruptible Loops that Reload

When the loop buffer has finished loading after returning from an interrupt, the PC points at the address after the **SPKERNEL** instruction. A reloaded loop is not interruptible if a branch does not execute during reloading that places the PC back at the execute packet after the **SPKERNEL** instruction. You should disable interrupts around these types of loops.

7.9.6.5 Restrictions on Reload Enforced by the Assembler

By enforcing the following restrictions by issuing either errors or warnings, the assembler enforces the most common and useful cases for using reload. An assembler switch disables these checks for advanced users.

There must be at least one valid outer loop branch that will always execute with a true condition when the loop is reloading. An outer loop branch is valid under all of the following conditions:

- The branch always executes if the reload condition was true.
- The branch target is the execute packet after the SPKERNEL execute packet.
- The last delay slot of the branch occurs before the reloading counter equals the dynlen. Note that this restriction implies a minimum for dynlen of 6 cycles.

There may be one or more valid post loop branch instructions that will always execute with a false condition when the loop is reloading, and that may execute with a true condition when the loop is not reloading.



For loops initiated with a conditional **SPLOOP** or **SPLOOPD** instruction, an exception (detected by the assembler) occurs if:

- There is not a valid outer loop branch instruction after the **SPKERNEL(R)** instruction.
- A reload has not been initiated by an SPMASKR instruction before the delay slots of the outer branch have completed.
- There is a branch instruction after the **SPKERNEL** instruction that may execute when the loop is reloading that is neither a valid outer loop branch nor a valid post loop branch.
- An SPMASKR is encountered for a loop that uses SPKERNELR.
- An SPMASKR is encountered for an unconditional (nonreload) loop.

Example 7-11 is a nested loop using the reload condition. Figure 7-8 shows the instruction execution flow for an invocation of the inner loop, the outer loop code, and then another inner loop. Notice that the reload starts after the first epilog stage of the inner loop as specified by the **SPMASKR** instruction in the last cycle of that stage.

Example 7-11. Using ILC With a SPLOOPD Instruction

```
i* for (i=0; i<32; i++)
;* for (I=0; i<32; I++)
;* y[j] += x[i+j] * h[i]
;* x=a4, h=b4, y=a6
                 32,B0
        .S2
    MVK
    MVC
              .S2
                   B0,ILC
                                     ;Inner loop count
            3
    NOP
[B0] SPLOOP 2
        .S2 B0,RILC
.D2 B0,1,B0
    MVC
                                      ;Reload inner loop count
                                      ;Outer loop count
    SUB
    MVK
             .S1 62,A5
                                      ;X delta
             .L2
    MV
                   B4,B5
                                      Copy h
    ZERO
             .D1
                   Α7
                                      ;Sum = 0
;*-----Start of loop-----
    LDH .D1T1 *A4++,A2 ;t1 = *x
LDH
             .D2T2 *B4++,B2
                                      ;t2 = *h
    NOP
             4
         .M1X A2,B2,A2
    MPY
                                      ip = t1*t2
    NOP
    SPKERNEL 0
ADD
           .L1
                   A2,A7,A7
                                      ;sum += p
outer:
;*----start epilog
                   A4,A5,A4
                                      ;x -= 62
    SUB
M\7
             .D2
                   B4.B5
                                      ;h -= 64
    SPMASKR
;*----start reload, I=0
[B0] BNOP .S1 outer, 4
             .S2
[B0] SUB
                   B0,1,b0
                                      ;j -= 1
    STH .D1 A7,*A
MVK .S1 0,A7
                   A7,*A6++
                                       ;*Y++ = sum
                                       ;Sum = 0
;*----branch, stop fetching
```



Figure 7-8. Instruction Flow Using Reload

CPU Pipeline	SPL Buffer	G
LD LD		
nop		
nop	LD LD	
nop	 	
nop MPY	 TD TD	
nop	LD LD	
ADD	MPY	
	LD LD	
	MPY ADD	
	•	
•	•	
	LD LD	
	MPY ADD	
SUB MV SPMASKR	MPY ADD	<- ILC = RILC
[B0] BNOP [B0] SUB	1.1	LD LD <- first reload cycle
nop	MPY ADD	ED ED TITED TOTOGG OFFICE
nop	11	LD LD
nop	ADD	<- last epilog cycle
nop		LD LD
STH MVK		MPY
		LD LD
		MPY ADD
•	•	
• ==	LD LD	
	MPY ADD	
SUB MV		
SPMASKR	MPY ADD	<- ILC = RILC
[B0] BNOP [B0] SUB	4.4	LD LD <- first reload cycle
nop	MPY ADD	11
nop	7 DD	LD LD
nop nop	ADD	<pre><- last epilog cycle LD LD</pre>
STH MVK		MPY
		LD LD
		MPY ADD
•	•	
•	•	



7.9.7 Restrictions on Accessing ILC and RILC

There is a 4-cycle latency (3 delay slots) between an instruction that writes a value to the inner loop count register (ILC) or the reload inner loop count register (RILC) and a read of the register by the loop buffer.

If an **SPLOOP** (not SPLOOPD or SPLOOPW) instruction is used, then ILC is used for the 3 cycles before the **SPLOOP** instruction and until the loop buffer is draining and not reloading.

If an **SPLOOPD** instruction is used, then ILC is used on the first cycle after the **SPLOOPD** instruction and until the loop buffer is draining and not reloading.

In general, it is an error to read or write ILC or RILC while the loop buffer is using them. This error is enforced by the following hardware and assembler exceptions. The value obtained by reading ILC during loading is not assured to be consistent across different implementations, due to potential differences in timing of the decrement of the register by the loop hardware.

An exception (detected by hardware) occurs if:

- RILC is written in the 3 cycles before the loop buffer reads it on the cycle before reloading begins.
- ILC is written in the 3 cycles before an unconditional **SPLOOP** (not SPLOOPD) instruction.

An error or warning (detected by the assembler) occurs if:

- An MVC instruction that writes ILC appears in parallel or in the 3 executes packets preceding an SPLOOP (not SPLOOPD) instruction.
- An MVC instruction that reads or writes ILC appears in the SPLOOP body.
- An MVC instruction that writes the RILC appears in the 3 execute packets preceding the execute packet before a reload prolog is initiated.
- An MVC instruction that reads or writes the ILC appears in an execute packet after an SPKERNEL
 instruction in a nested loop, and the MVC instruction may execute during or in three cycles preceding
 the reload prolog of the loop.

7.10 Loop Buffer Control Using the SPLOOPW Instruction

For the **SPLOOPW** instruction, the termination condition is determined by evaluating the **SPLOOPW** instruction condition operand. When the **SPLOOPW** instruction is encountered, the condition operand is recorded by the loop buffer. The initial termination testing is the same as for the **SPLOOPD** instruction, that is, no checking is done for the first four cycles of the loop.

The **SPLOOPW** instruction is intended to be used for do-while loops. These are loops whose termination condition is more complex than a simple down counter by 1. In addition, these types of loops compute the loop termination condition and exit without executing an epilog. This technique may require over executing (or speculating) some instructions.

When using the **SPLOOPW** instruction condition operand as the termination condition, the following behavior occurs:

- Termination is determined by the SPLOOPW instruction condition that will be on a stage boundary.
- · ILC and RILC are not accessed or modified.
- The loop cannot be reloaded.
- After the last kernel stage boundary, the loop buffer goes idle.
- The stage boundary termination condition is evaluated while interrupt draining.
- The SPKERNEL fetch delay must be 0.
- When returning to a conditional SPLOOPW from an interrupt with the SPLX bit set to 1 in TSR, the SPLOOPW retains its delayed initial termination testing behavior. This is different from the SPLOOPD instruction.



7.10.1 Initial Termination Condition Using the SPLOOPW Condition

The initial termination condition is always false when an **SPLOOPW** instruction is encountered. The loop must execute at least one iteration.

7.10.2 Stage Boundary Termination Condition Using the SPLOOPW Condition

The stage boundary termination condition is true when a stage boundary is reached and the **SPLOOPW** instruction condition operand evaluates as false 3 cycles before the stage boundary; otherwise, the termination condition is false. The termination condition is always false for the first 3 cycles of the loop.

7.10.3 Interrupting the Loop Buffer When Using SPLOOPW

If the loop is interrupted when using the conditional form of the **SPLOOPW** instruction, the stage boundary termination condition is evaluated on each stage boundary while interrupt draining. If the stage boundary termination condition is true while interrupt draining, the loop buffer goes to idle, execution resumes at the instruction after the loop body, and that instruction is interrupted.

The instruction that defines the termination condition register must occur at least 4 cycles before a stage boundary and at least 4 cycles before the last instruction in the loop. If the termination condition is determined in the last loading stage, the dynlen must be a multiple of ii. These restrictions ensure that on return from an interrupt to a **SPLOOPW** instruction, the loop executes 1 or more iterations.

Note that when returning to a **SPLOOPW** instruction from an interrupt service routine with the SPLX bit set to 1 in TSR, the **SPLOOPW** instruction termination condition behavior is unchanged, that is, the initial termination condition is always false, and the stage boundary termination condition is always false for the first 3 cycles of the loop.

An exception occurs if the termination condition register is not defined properly to ensure correct interrupt behavior.

Example 7-12 shows a loop with a loop counter that down counts by an unknown value. For this loop, it must be safe to over-execute the **LDH** instructions 8 times.

Example 7-13 shows a string copy implementation. Figure 7-9 shows the execution flow if the source points to a null string. In this version, it must be safe to over-execute the **LDB** instruction 4 times.

Example 7-12. Using the SPLOOPW Instruction

```
; * do {
     sum += *x++ * *y++;
;
      n -= m;
      \} while (n >= 0)
[!A1] SPLOOPW 1
      MVK .S1
                   0x0,A1
                                            ;C = false
.D1T1 *A5++,A3
      L'DH
                                            it1 = *x++
             .D2T2 *B5++,B6
                                            it2 = *y++
LDH
      NOP
             2
      SUB
             .L2
                   B4,B7,B4
                                            ;n -=m
      CMPLT .L2 B4,0,A1
                                            ic = n < 0
                                                          // term_cond = !A1
             .M1X B6,A3,A4
                                            ;p = t1 * t2  // delay slot 1
      MPY
      NOP
             1
                                                          // delay slot 2
                                            ;sum += p;
             .L1
                                                          // delay slot 3
      ADD
                   A4,A6,A6
      SPKERNEL
                                            ;if (c) break; // cycle term_cond used
```



Example 7-13. strcpy() Using the SPLOOPW Instruction

```
; * do {
     t = *src++;
     *dst++ = t;
    } while (t != 0)
   [A0] SPLOOPW 1
    MVK .S2 1,B0
        MVK
              .S1 1,A0
.D1 *A4++,A0
[A0] LDB
                                      ;t = *src++
   NOP 4
[B0] MV .L2X A0,B0
NOP 2
                                     ;if (!t) break;
                                      ;Ensure A0 set 4 cycles early
SPKERNEL
|| [B0] STB .D2 B0,*B4++
                                     i*dest++ = t
      STB B0,*B4
                                      ;*t = '/0'
```

Figure 7-9. Instruction Flow for strcpy() of Null String

```
CPU Pipeline
                                     SPL buffer
                                     -----
[a0] LDB *a4++,a0
                 [a0] LDB *a4++,a0
        nop
                                     [a0] LDB *a4++,a0
        nop
nop [a0] LDB *a4++,a0
nop [a0] LDB *a4++,a0
nop [a0] LDB *a4++,a0
0 written to a0 in this cycle
[b0] mv a0,b0 [a0] LDB *a4++,a0 <- a0 = 0, term_cond = true
nop [a0] LDB *a4++,a0 || [b0] mv a0,b0 <- b0 = 0
nop [a0] LDB *a4++,a0 || [b0] mv a0,b0
[b0] STB b0,*b4++
STB b0,*a4 - terminate string in post epi
                                                                        terminate string in post epilog with /0
```

7.10.4 Under-Execution of Early Stages of SPLOOPW When Termination Condition Becomes True While Interrupt Draining

Usually an SPLOOPW block terminates abruptly when the termination condition is true without executing an epilog; however, when an SPLOOPW block is interrupted, it executes an epilog to drain the loop prior to servicing the interrupt.

If the termination condition becomes true while interrupt draining, the action of interrupt draining results in the under-execution of the early stages of the loop body in comparison to the same loop when not interrupted. The loop body must be coded such that the under-execution of the early stages of the loop body are safe.

7.11 Using the SPMASK Instruction

A logical progression for a loop might be:

- Do initial setup
- Execute the loop
- Do post loop operations

If the loop were to be reloaded, the progression might loop like:

- Do initial setup
- Execute the loop
- Adjust setup for reloaded loop
- Reload the loop
- Do post loop operations



The initial setup, the post loop operations, and adjusting the setup for the reloaded loop are all overhead that may be minimized by moving their execution to within the same instruction cycles as the operation of the SPLOOP.

If some setup code is required to do some initialization that is not used until late in the loop; you can save instruction cycles by using the **SPMASK** instruction to overlay the setup code with the first few cycles of the SPLOOP. The **SPMASK** will cause the masked instructions to be executed once without being loaded to the SPLOOP buffer. Example 7-14 shows how this might be done.

If the **SPMASK** is used in the outer loop code (that is, post epilog code), it will force the substitution of the **SPMASK**ed instructions in the outer loop code for the instruction using the same functional unit in the SPLOOP buffer for the first iteration of the reloaded inner loop. For example, if pointers need to be reset at the point that a loop is reloaded, the instructions that do the reset can be inhibited using the **SPMASK** instruction so that the instructions that originally adjusted the pointers are replaced in the execution flow with instruction in the outer loop that are marked with the **SPMASK** instruction. Example 7-15 shows how this might be done.

7.11.1 Using SPMASK to Merge Setup Code Example

Example 7-14 copies a number of words (the number is passed in the A6 register from one buffer to an offset into another buffer). The size of the offset is passed in the B6 register. Due to the use of the **SPMASK** instruction, the ADD instruction is executed only once and is not loaded to the SPLOOP buffer. The caret (^) symbol is used to identify the instructions masked by the **SPMASK** instruction. Table 7-5 shows the instruction flow for the first three iterations of the loop.

Example 7-14. Using the SPMASK Instruction to Merge Setup Code with SPLOOPW

```
; dst=&(dst[n])
; * do {
      t = *src++;
      *dst++ = ti
      } while (count--)
;
;A4 = Source address
;B4 = Destination address
;A6 = Number of words to copy
;B6 = Offset into destination to do copy
;*_____
[A1] SPLOOPW 1
                           Position loop cnt to valid reg
            .L1 A6,1,A1
     ADD
                                 ;Adjust offset for size of WORD
     SHL
             .S2 B6,2,B6
SPMASK
             .L2 B6,B4,B4
                                ;Add offset into buffer to dest
     ADD
     LDW
              .D1 *A4++,A0
                                 ;Load word and inc ptr
     NOP
              1
                                  ;Wait for portion of delay
[A1] SUB
              .S1 A1,1,A1
                                 ;Decrement loop count
     NOP
              2
                                 ;Complete necessary wait
              .L2X A0,B0
                                  ;Position Word for write
     MV
     SPKERNEL 0,0
     STW
.D2 B0,*B4++
                                  ;Store word
```



Table 7-5. SPLOOP Instruction Flow for First Three Cycles of Example 7-14

-	Loop			
Cycle	1	2	3	Notes
0	ADD SHL			Instructions are in parallel with the SPLOOP, so they execute only once.
1	ADD LDW			The ADD is SPMASKed so it executes only once. The LDW is loaded to the SPLOOP buffer.
2	NOP	LDW		The ADD was not added to the SPLOOP buffer in cycle 2, so it is not executed here.
3	SUB	NOP	LDW	The SUB is a conditional instruction and may not execute.
4	NOP	SUB	NOP	The SUB is a conditional instruction and may not execute.
5	NOP	NOP	SUB	The SUB is a conditional instruction and may not execute.
6	MV	NOP	NOP	
7	STW	MV	NOP	
8		STW	MV	
9			STW	

7.11.2 Some Points About the SPMASK to Merge Setup Code Example

Note the following points about the execution of Example 7-14:

- The **ADD** and **SHL** instructions in the same execute packet as the **SPLOOPW** instruction are only executed once. They are not loaded to the SPLOOP buffer.
- Because of the SPMASK instruction in the execute packet, the ADD in the same execute packet as
 the SPMASK instruction is executed only once and is not loaded to the SPLOOP buffer. Without the
 SPMASK, the ADD would conflict with the MV instruction.
- The SHL and the 2nd ADD instructions could have been placed before the start of the SPLOOP, but by placing the SHL in parallel with the SPLOOP instruction and by using the SPMASK to restrict the ADD to a single execution, you have saved a couple of instruction cycles.



7.11.3 Using SPMASK to Merge Reset Code Example

Example 7-15 copies a number of words (the number is passed in the A8 register from one buffer to another buffer). The loop is reloaded and the contents of a second source buffer are copied to a second destination buffer. Table 7-6 shows the instruction flow for the first 13 cycles of the example.

Example 7-15. Using the SPMASK Instruction to Merge Reset Code with SPLOOP

```
; dst=&(dst[n])
; * do {
       t = *src++;
       *dst++ = t;
      } while (count--)
  adjust buffer pointers
; * do {
       t = *src++;
       *dst++ = t;
;
       } while (count--)
;A4 = 1st source address
;B4 = 1st destination address
;A6 = 2nd source address
;B6 = 2nd destination address
;A8 = number of locations to copy from each buffer
         MVC
                 A8,ILC
                                            ;Setup number of loops
         MVC
                  A8,RILC
                                            ;Reload count
          MVK
                   1,A1
                                             ;Reload flag
                                            ; Wait for ILC load to complete
         NOP
                                        ;Start SPLOOP with ii=1
;Load value from buffer
;Wait for it to arrive
    [A1] SPLOOP
                   1
          LDW
                   .D1
                         *A4++,A0
          NOP
                   4
          MV
                   .L2X A0,B0
                                            ; Move it to other side for xfer
          SPKERNELR
                                            ; End of SPLOOP, immediate reload
                   .D2 B0,*B4++
          STW
                                            ;...and store value to buffer
BR_TARGET:
                                            ; Mask LDW instruction
          SPMASK D1
    [A1]
         В
                   BR_TARGET
                                            ;Branch to start if post-epilog
                   .S1 A1, 1, A1
    [A1]
         SUB
                                            ;Adjust reload flag
    [A1] LDW
                        *A6,A0
                   .D1
                                            ;Load first word of 2nd buffer
         ADD
    [A1]
                   .L1 A6,4,A4
                                             ;Select new source buffer
                                            ; Keep in sync with SPLOOP body
         NOP
                   4
          OR
                   .S2 B6,0,B4
                                            ; Adjust destination to 2nd buffer
         NOP
```



Table 7-6. SPLOOP Instruction Flow for Example 7-15 Loop 1 2 3 4 5 7 9 6 8 10 11 12 Cycle 13 1 LDW LDW 2 NOP NOP 3 NOP LDW NOP NOP NOP 4 LDW NOP NOP NOP NOP LDW 5 NOP LDW 6 MV NOP NOP NOP 7 STW MV NOP NOP NOP NOP LDW STW MV NOP NOP NOP IDW 8 NOP SUB ADD STW NOP NOP LDW 9 ΜV NOP NOP STW MV NOP NOP NOP NOP LDW 10 11 STW MV NOP NOP NOP NOP LDW STW 12 MV NOP NOP NOP NOP LDW 13 STW MV NOP NOP NOP NOP LDW OR 14 STW MV NOP NOP NOP NOP

7.11.4 Some Points About the SPMASK to Merge Reset Code Example

Note the following points about the execution of Example 7-15 (see Table 7-6 for the instruction flow)::

- The loop begins reloading from the SPLOOP buffer immediately after the SPKERNELR instruction with no delay. In Table 7-6, the SPKERNELR is in cycle 7 and the reload happens in cycle 8.
- Because of the SPMASK instruction, the LDW instruction in the post epilog code replaces the LDW instruction within the loop, so that the first word copied in the reloaded loop is from the new input buffer. The ADD instruction is used to adjust the source buffer address for subsequent iterations within the SPLOOP body. In Table 7-6, this happens in loop 8. Note that the D1 operand in the SPMASK instruction indicates that the SPMASK applies to the .D1 unit. This could have been indicated by marking the LDW instruction with a caret (^) instead.
- The OR instructions are used to adjust the destination address. It is positioned in the post-epilog code
 as the MV instruction is within the SPLOOP body so that it will not corrupt the data from the STW
 instructions within the SPLOOP epilog still executing from before the reload. In Table 7-6, this happens
 in cycle 13 (loop 8).
- The B instruction is used to reset the program counter to the start of the epilog between executions of the inner loop.

7.11.5 Returning from an Interrupt

When an SPLOOP is piping up after returning from an interrupt, the **SPMASK**ed instructions coming from the buffer are executed and instructions coming from program memory are not executed.

7.12 Program Memory Fetch Control

When the loop buffer is active and program memory fetch is enabled, then instructions are fetched from program memory and the loop buffer and executed in parallel.

When the loop buffer is active and under certain conditions as described below, instruction execution from program memory is suspended. When this occurs, instructions are only fetched and executed from the loop buffer and the PC is unchanged.



www.ti.com Interrupts

7.12.1 Program Memory Fetch Disable

Instruction fetch from program memory is disabled under the following conditions:

- When loading: on the cycle after the SPKERNEL instruction is encountered, and that cycle is either a kernel cycle or a draining cycle where fetch has not yet been reenabled.
- When reloading: on the cycle after the last delay slot of a branch that executes with a true condition or after the reload counter equals the dynlen.

If program memory fetch is disabled on the last loading or reloading stage boundary, the stage boundary termination condition is true, and the program memory fetch enable delay has completed, then program memory fetch is not disabled.

Program memory fetch remains disabled while interrupt draining or until a specific stage and cycle during noninterrupt draining as determined by the program fetch enable delay operand of the **SPKERNEL** instruction.

7.12.2 Program Memory Fetch Enable

Program memory fetch is enabled, if the loop buffer goes idle.

7.13 Interrupts

When an **SPLOOP(D/W)** instruction is encountered, the address of the execute packet containing the **SPLOOP(D/W)** instruction is recorded. If the loop buffer is interrupted, the address stored in the interrupt return pointer register (IRP) is the address of the execute packet containing the **SPLOOP(D/W)** instruction.

7.13.1 Interrupting the Loop Buffer

Interrupts are automatically disabled 2 cycles before an **SPLOOP(D/W)** instruction is encountered. When all of the following conditions are true, the loop buffer begins interrupt draining.

- An enabled interrupt is pending and not architecturally blocked (for example, in branch delay slots).
- The loop is on a stage boundary.
- The termination condition is false.
- The loop is not loading.
- The loop is not draining.
- The loop is not reloading or waiting to reload.
- The loop is not within the first 3 CPU cycles after an SPLOOPD or SPLOOPW instruction. This means
 that a minimum number of 4 cycles of an SPLOOP(D/W) loop must be executed before an interrupt
 can be taken.
- The loop is not within the first 3 CPU cycles after an SPLOOPD or SPLOOPW instruction.
- For **SPLOOP** or **SPLOOPD** instructions, the current ILC >= ceil(dynlen/ii). This prevents returning to a loop that would early-exit. The value of ceil(dynlen/ii) is equal to the number of loading stages.

When the loop is finished draining and all pending register writes are complete the interrupt is taken. This means that the interrupt latency has increased by the number of instruction cycles in the epilog compared to the non-SPLOOP case.

The above conditions mean SPLOOP loops starting initial execution or starting reload with ILC < = (ceil(dynlen / ii) + 3) are not interruptible because there are not enough kernel stages to allow an interrupt to be taken without violating the last requirement.

After an **SPLOOP(D/W)** instruction is encountered, the SPLX bit is set to 1 in TSR. While the loop buffer is active, the SPLX bit is 1. When the loop buffer is idle, the SPLX bit in TSR is cleared to 0.

Program memory fetch is disabled when interrupt draining. When the draining is finished, the address of the execute packet that contains the **SPLOOP** instruction is stored in IRP or NRP, and TSR is copied to ITSR or NTSR. The SPLX bit in TSR is cleared to 0. The SPLX bit in ITSR or NTSR is set to 1.



Interrupts www.ti.com

Interrupt service routines must save and restore the ITSR or NTSR, ILC, and RILC registers. A **B IRP** instruction copies ITSR to TSR, and a **B NRP** restores TSR from NTSR. The value of the SPLX bit in ITSR or NTSR when the return branch is executed is used to alter the behavior of **SPLOOP(D/W)** when it is restarted upon returning from the interrupt.

7.13.2 Returning to an SPLOOP(D/W) After an Interrupt

When returning from an interrupt to an SPLOOP(D/W) instruction with the SPLX bit set to 1 in ITSR, the loop buffer executes normally with the following exceptions:

- Instructions executing in parallel with the SPLOOP(D/W) instruction are not executed.
- SPMASKed instructions from program memory execute as a NOP.
- SPMASKed instructions in the loop buffer execute as normal the SPMASK is ignored.
- BNOP *label,n* instructions are executed as NOP *n* + 1
- An SPLOOPD instruction executes as an SPLOOP instruction.

Note that if returning to an unconditional **SPLOOP(D)** instruction, the interrupt return code must restore the value of ILC 4 cycles before the **SPLOOP(D)** instruction is executed (if the ISR modified ILC).

7.13.3 Exceptions

If an internal or external exception occurs while the loop buffer is active, then the following occur:

- · The exception is recognized immediately and the loop buffer becomes idle.
- The loop buffer does not execute an epilog to drain the currently executing loop.
- TSR is copied into NTSR with the SPLX bit set to 1 in NTSR and cleared to 0 in TSR.

7.13.4 Branch to Interrupt, Pipe-Down Sequence

- 1. Hardware detects an interrupt.
- 2. Execute until the end of a stage boundary (if termination condition is false).
- 3. Pipe-down the SPLOOP by draining.
- 4. Fetch enable condition is false.
- 5. Store return address of SPLOOP in IRP or NRP.
- 6. Copy TSR to ITSR or NTSR with SPLX bit set to 1.
- 7. Complete all pending register writes (drain pipeline).
- 8. Begin execution at interrupt service routine target address.

7.13.5 Return from Interrupt, Pipe-Up Sequence

- 1. Copy ITSR or NTSR to TSR.
- 2. Pipe-up the SPLOOP.
- 3. The **SPLOOPD** instruction executes like the **SPLOOP** instruction.
- 4. The **SPMASK**ed instructions from program memory are executed like NOPs.
- 5. The SPMASKed instructions in the loop buffer execute as normal.
- 6. Instructions in parallel with the SPLOOP(D/W) instruction are executed like NOPs.

7.13.6 Disabling Interrupts During Loop Buffer Operation

Instructions that disable interrupts should not be executed within 4 cycles of reaching dynlen while loading or reloading. If this condition is violated, there is a possibility that an interrupt is recognized as enabled causing the loop to drain for an interrupt with the interrupt no longer enabled when draining is completed. In this case, the loop terminates and execution continues with the post-**SPKERNEL** instruction stream with no interrupt being serviced at that point.



www.ti.com Branch Instructions

7.14 Branch Instructions

If a branch executes with a true condition or is unconditional, then the branch is taken on the cycle after the 5 delay slots have expired.

If a branch is taken and the loop buffer is not reloading, the loop buffer becomes idle, and execution continues from the branch target address.

If a branch executes with a false condition (the branch is not taken), the execution of the **SPLOOP(D/W)** instruction is unaffected by the presence of the untaken branch except that interrupts are blocked during the delay slots of the branch.

This behavior allows the code in Example 7-16 to run as you expect, branching around the loop if the condition is false before beginning.

If a branch is taken anytime while the loop buffer is active, except when in reloading, the loop buffer goes to idle, and execution continues from the branch target address. If a branch is taken while reloading, the PC is assigned the branch target and program memory fetch is disabled.

Example 7-16. Initiating a Branch Prior to SPLOOP Body

```
[!A0] B around
|| MVC A0,ILC
NOP 3
SPLOOP ii
; loop body
...
; end of loop body
around:
; code following loop
```

7.15 Instruction Resource Conflicts and SPMASK Operation

There are three execution candidates for each unit: prolog instructions coming from the buffer (BP), epilog instructions coming from the buffer (BE), and nonbuffer instructions coming from program memory (PM). There are four phases where conflict can occur:

- Loading phase, between BP and PM
- Draining only phase, between BE and PM
- Draining/reload phase, between BE, BP, and PM
- Reload only phase, between BP and PM

In the case of any conflict, an **SPMASK(R)** instruction must be present specifying all units having conflicts. SPMASKed units for that cycle:

- Disable execution of any loop buffer instructions: BP, BE, or both.
- Execute a PM instruction, if present, with no effect on the buffer contents.

The only special behavior is in the case of restarting SPLOOP(D/W) after return from interrupt. In this case, during loading SPMASKed units:

- Do not disable execution of any loop buffer instructions.
- Do not execute a present PM instruction.

If an **SPMASK** instruction is encountered when the loop buffer is idle or not loading or not draining, the **SPMASK** instruction executes as a NOP.



7.15.1 Program Memory and Loop Buffer Resource Conflicts

A hardware exception occurs if:

- An instruction fetched from program memory has a resource conflict with an instruction fetched from the loop buffer and the instruction coming from the loop buffer is not masked by an SPMASK(R) instruction.
- An instruction fetched from the loop buffer as part of draining has a resource conflict with an instruction fetched from the loop buffer for reload and the unit with the conflict is not masked by an SPMASK(R) instruction.

7.15.2 Restrictions on Stall Detection Within SPLOOP Operation

There are two CPU stalls that occur because of certain back-to-back execute packets. In both of these cases, the CPU generates a 1-cycle stall between the instruction doing the write and instruction using the written value.

- The cross path register file read stall where the source for an instruction executing on one side of the
 datapath is a register from the opposite side and that register was written in the previous cycle. No stall
 is required or inserted when the register being read has data placed by a load instruction. See
 Section 3.8.4 for more information.
- The AMR use stall where an instruction uses an address register in the cycle immediately following a write to the addressing mode register (AMR).

Stall detection is one critical speed path in the CPU design. Adding to that path for the case where instructions are coming from the loop buffer is undesirable and unnecessary. There are no compelling cases where you would want to schedule a stall within the loop body. In fact, the compiler works to ensure this does not happen. For these reasons, the CPU will not stall for instructions coming from the loop buffer that read/use values written on the previous cycle that require a stall for correct behavior.

In the event that a case occurs where a stall is required for correct operation but did not occur, an internal exception is generated. This internal exception sets the LBX and MSX bits in the internal exception report register (IERR), indicating a missed stall with loop buffer operation. The exception is only generated in the event that the stall is actually required.

There is one special case that causes an unnecessary stall in normal operation and can be generated by the compiler. It is the case where the two instructions involved in the stall detection are predicated on opposite conditions. This means only one of the instructions actually executes and a stall was not required for correct behavior. Since the stall detection is earlier in the pipeline, the decision to stall must be made before it is known whether the instructions execute. Thus a stall is caused, even though it later turns out not to be needed. In this case, the lack of detection for the instruction coming from the loop buffer does not cause incorrect behavior. This allows the compiler to continue to generate code using this case that can result in improved scheduling and performance. The internal exception is not generated in this case.

7.16 Restrictions on Cross Path Stalls

The following restriction is enforced by the assembler (that is, an assembly error will be signaled): an instruction fetched from the loop buffer that reads a source operand from the register file cross path must be scheduled such that the read does not require a cross path stall (the register being read cannot be written in the previous cycle).

It is possible for the assembly language programmer to place an instruction in the delay slots of a branch to an SPLOOP that causes a pipelined write to happen while the loop buffer is active. It is also possible for the assembly language programmer to predicate the write and reads with different predicate values that are not mutually exclusive. The assembler cannot prevent these cases from occurring; if they do the internal exception will occur.

7.17 Restrictions on AMR-Related Stalls

The following restriction is enforced by the assembler: an instruction fetched from the loop buffer that uses an address register (A4–A7 or B4–B7) must be scheduled such that a write to the addressing mode register (AMR) does not occur in the preceding cycle.



7.18 Restrictions on Instructions Placed in the Loop Buffer

The following instructions cannot be placed in the loop buffer and must be masked by **SPMASK(R)** when occurring in the loop body: **ADDKPC**, **B** reg, **BNOP** reg, **CALLP**, and **MVC**.

The **NOP**, **NOP** n, and **BNOP** instructions are the only unitless instructions allowed to be used in an SPLOOP(D/W) body. The assembler disallows the use of any other unitless instruction in the loop body.



CPU Privilege

This chapter describes the CPU privilege system.

Topic Page

8.1	Overview	704
8.2	Execution Modes	704
8.3	Interrupts and Exception Handling	706
8.4	Operating System Entry	706

SPRUFE8B-July 2010 CPU Privilege 703



Overview www.ti.com

8.1 Overview

The CPU includes support for a form of protected-mode operation with a two-level system of privileged program execution.

The privilege system is designed to support several objectives:

- Support the emergence of higher capability operating systems on the C6000 family architecture.
- Support more robust end-equipment, especially in conjunction with exceptions.
- Provide protection to support system features such as memory protection.

The support for powerful operating systems is especially important. By dividing operation into privileged and unprivileged modes, the operating mode for the operating system is differentiated from applications, allowing the operating system to have special privilege to manage the processor and system. In particular, privilege allows the operating system to:

- control the operation of unprivileged software
- protect access to critical system resources (that is, interrupts)
- · control entry to itself

The privilege system allows two distinct types of operation.

- Supervisor-only execution. This is used for programs that require full access to all control registers, and have no need to run unprivileged (User mode) programs.
- Two-tiered system. This is where the OS and trusted applications execute in Supervisor mode, and less trusted applications execute in User mode.

8.2 Execution Modes

There are two execution modes:

- Supervisor Mode
- User Mode

8.2.1 Privilege Mode After Reset

Reset forces the CPU to the Supervisor mode. Execution of the reset interrupt service fetch packet (ISFP) begins in Supervisor mode.

8.2.2 Execution Mode Transitions

Mode transitions occur only on the following events:

- Interrupt: goes to Supervisor mode and saves mode (return with B IRP instruction)
- B IRP instruction: returns to saved mode from interrupt
- Nonmaskable interrupt (NMI): goes to Supervisor mode and saves mode (return with B NRP instruction)
- Exception: goes to Supervisor mode and saves mode (return with **B NRP** instruction, if restartable)
- Operating system service request: goes to Supervisor mode and saves mode (return with B NRP instruction)
- B NRP instruction: returns to saved mode from NMI or exception

8.2.3 Supervisor Mode

The Supervisor mode serves two purposes:

- 1. It is the compatible execution mode.
- 2. It is the privileged execution mode where all functions of the processor are available. In User mode, the privileged operations and resources that are restricted are listed in Section 8.2.4.



www.ti.com Execution Modes

8.2.4 User Mode

The User mode provides restricted capabilities such that more privileged supervisory software may manage the machine with complete authority. User mode restricts access to certain instructions and control registers to prevent an unprivileged program from bypassing the management of the hardware by the supervisory software.

8.2.4.1 Restricted Control Register Access in User Mode

Certain control registers are not available for use in User mode. An attempt to access one of these registers in User mode results in an exception. The resource access exception (RAX) and privilege exception (PRX) bits are set in the internal exception report register (IERR) when this exception occurs. The following control registers are restricted from access in User mode:

- Exception clear register (ECR)
- Exception flags register (EFR)
- Interrupt clear register (ICR)
- Interrupt enable register (IER)
- Internal exception report register (IERR)
- Interrupt flags register (IFR)
- Interrupt service table pointer register (ISTP)
- Interrupt task state register (ITSR)
- NMI/exception task state register (NTSR)
- Restricted entry point register (REP)

8.2.4.2 Partially Restricted Control Register Access in User Mode

The following control registers are partially restricted from access in User mode:

- Control status register (CSR)
- Task state register (TSR)

All bits in these registers can be read in User mode; however, only certain bits in these registers can be written while in User mode. Writes to these restricted bits have no effect. Since access to some bits is allowed, there is no exception caused by access to these registers.

8.2.4.2.1 Restrictions on Using CSR in User Mode

The following functions of CSR are restricted when operating in User mode:

- PGIE, PWRD, PCC, and DCC bits cannot be written in User mode. Writes to these bits have no effect.
- GIE and SAT bits are not restricted in User mode, and their behavior is the same as in Supervisor mode.

8.2.4.2.2 Restrictions on Using TSR in User Mode

The GIE and SGIE bits are not restricted in User mode. All other bits are restricted from being written; writes to these bits have no effect.

8.2.4.3 Restricted Instruction Execution in User Mode

Certain instructions are not available for use in User mode. An attempt to execute one of these instructions results in an exception. The opcode exception (OPX) and privilege exception (PRX) bits are set in the internal exception report register (IERR) when this exception occurs. The following instructions are restricted in User mode:

- B IRP
- B NRP
- IDLE

SPRUFE8B-July 2010 CPU Privilege 705



8.3 Interrupts and Exception Handling

As described in Section 8.2.2, mode switching mostly occurs for interrupt or exception handling. This section describes the execution mode behavior of interrupt and exception processing.

8.3.1 Inhibiting Interrupts in User Mode

The GIE bit in the control status register (CSR) can be used to inhibit interrupts in User mode. This allows a usage model where User mode programs may be written to conform to a required level of interruptibility while still protecting segments of code that cannot be interrupted safely. Nonconforming behavior may be detected at the system level, and control can be taken from the User mode program by asserting the EXCEP input to the CPU.

8.3.2 Privilege and Interrupts

When an interrupt occurs, the interrupted execution mode and other key information is saved in the interrupt task state register (ITSR). The CXM bit in the task state register (TSR) is set to indicate that the current execution mode is Supervisor mode. Explicit (MVC) writes to TSR are completed before being saving to ITSR.

The interrupt handler begins executing at the address formed by adding the offset for the particular interrupt event to the value of the interrupt service table pointer register (ISTP). The return from interrupt (**B IRP**) instruction restores the saved values from ITSR into TSR, causing execution to resume in the execution mode of the interrupted program.

The transition to the restored execution mode is coincident to the execution of the return branch target. Execution of instructions in the delay slot of the branch are in Supervisor mode.

8.3.3 Privilege and Exceptions

When an exception occurs, the interrupted execution mode and other key information is saved in the NMI/exception task state register (NTSR). The CXM bit the task state register (TSR) is set to indicate that the current execution mode is Supervisor mode. Explicit (MVC) writes to TSR are completed before saved to ITSR.

The exception handler begins executing at the address formed by adding the offset for the exception/NMI event to the value of the interrupt service table pointer register (ISTP). The return from exception (**B NRP**) instruction restores the saved values from NTSR into TSR.

8.3.4 Privilege and Memory Protection

The data and program memory interfaces at the boundary of the CPU include signals indicating the execution mode in which an access was initiated. This information can be used at the system level to raise an exception in the event of an access rights violation.

8.4 Operating System Entry

A protected interface is needed so that User mode code can safely enter the operating system to request service.

There is one potential problem with allowing direct calling into the operating system: the caller can chose where to enter the OS and, if allowed to choose any OS location to enter, can:

- bypass operand checking by OS routines
- · access undocumented interfaces
- · defeat protection
- corrupt OS data structures by bypassing consistency checks or locking

In short, allowing unrestricted entry into an OS is a very bad idea. Instead, you need to give a very controlled way of entering the operating system and switching from User mode to Supervisor mode. The mechanism chosen is essentially an exception, where the handler decodes the requested operation and dispatches to a Supervisor mode routine that validates the arguments and services the request.



www.ti.com Operating System Entry

8.4.1 Entering User Mode from Supervisor Mode

There are two reasons that the CPU might need to enter User mode while operating in Supervisor mode:

- To spawn a User mode task
- To return to User mode after an interrupt or exception3

Both cases are handled by one of two related procedures:

- Place the address in NRP, ensure that the NTSR.CXM bit is set to 1, and execute a **B NRP** instruction to force a context switch to the User mode task.
- Place the desired address in IRP, ensure that the ITSR.CXM bit is set to 1, and execute a B IRP instruction to force a context switch to the User mode task.

When returning from an interrupt or exception, the IRP or NRP should already have the correct return address and the ITSR.CXM or NTSR.CXM bit should already be set to 1.

When spawning a user mode task, the appropriate CXM bit and the IRP or NRP will need to be initialized explicitely with the entry point address of the User mode task. In addition, the restricted entry point address register (REP) should be loaded with the desired return address that the User mode task will use when it terminates.

8.4.2 Entering Supervisor Mode from User Mode

The operating mode will change from User mode to Supervisor mode in the following cases:

- While processing any interrupt
- · While processing an exception

The User mode task can force a change to Supervisor mode by forcing an exception by executing either an **SWE** or **SWENR** instruction.

The **SWE** and **SWENR** instructions both force a software exception. The **SWE** instruction is used when a return from the exception back to the point of the exception is desired. The **SWENR** instruction is used when a return to the User mode routine is not desired.

OS entry and switching from User to Supervisor mode is accomplished by forcing a software exception using either the **SWE** or **SWENR** instructions. See Section 6.5.3 for information about software exceptions.

Execution of an **SWE** instruction results in an exception being taken before the next execute packet is processed. The return pointer stored in the nonmaskable interrupt return pointer register (NRP) points to this unprocessed packet. The value of the task state register (TSR) is copied to the NMI/exception task state register (NTSR) at the end of the cycle containing the **SWE** instruction, and the interrupt/exception default value is written to TSR. The **SWE** instruction should not be placed in the delay slots of a branch since all instructions behind the **SWE** instruction in the pipe are annulled. All writes to registers in the pipe from instructions executed before and in parallel with the **SWE** instruction will complete before execution of the exception service routine, therefore, the instructions prior to the **SWE** will complete (along with all their delay slots) before the instructions after the **SWE**.

If the **SWE** instruction is executed while in User mode, the mode is changed to Supervisor mode as part of the exception servicing process. The TSR is copied to NTSR, the return address is placed in the NRP register, and a transfer of control is forced to the NMI/Exception vector pointed to by current value of the ISTP. Any code necessary to interpret a User mode request should reside in the exception service routine. After processing the request the exception handler will return control to the user task by executing a **B NRP** command.

The **SWENR** instruction can also be used to terminate a user mode task. The **SWENR** instruction is similar to the **SWE** instruction except that no provision is made for returning to the user mode task and the transfer of control is to the address pointed to by REP instead of the NMI/exception vector. The supervisor mode should have earlier placed the correct address in REP.

SPRUFE8B-July 2010 CPU Privilege 707

708 CPU Privilege SPRUFE8B-July 2010



Instruction Compatibility

Table A-1 lists the instructions that are common to the C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs.

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs

Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
ABS	✓	✓	✓	✓	✓	✓
ABS2		✓	✓			✓
ABSDP				✓	✓	✓
ABSSP				✓	✓	✓
ADD	✓	✓	√ ⁽¹⁾	✓	✓	✓
ADDAB	✓	✓	✓	✓	✓	✓
ADDAD		✓	✓	✓	✓	✓
ADDAH	✓	✓	✓	✓	✓	✓
ADDAW	✓	✓	√ ⁽¹⁾	✓	✓	✓
ADDDP				✓	✓	✓
ADDK	✓	✓	√ ⁽¹⁾	✓	✓	✓
ADDKPC		✓	✓			✓
ADDSP				✓	✓	✓
ADDSUB			✓			✓
ADDSUB2			✓			✓
ADDU	✓	✓	✓	✓	✓	✓
ADD2	✓	✓	✓	✓	✓	✓
ADD4		✓	✓			✓
AND	✓	✓	√ ⁽¹⁾	✓	✓	✓
ANDN		✓	✓			✓
AVG2		✓	✓			✓
AVGU4		✓	✓			✓
B displacement	✓	✓	✓	✓	✓	✓
B register	✓	✓	✓	✓	✓	✓
B IRP	✓	✓	✓	✓	✓	✓
B NRP	✓	✓	✓	✓	✓	✓
BDEC		✓	✓			✓
BITC4		✓	✓			✓
BITR		✓	✓			✓
BNOP displacement		✓	√ ⁽¹⁾			✓
BNOP register		✓	✓			✓
BPOS		✓	✓			✓
CALLP			√ ⁽¹⁾			✓
CLR	✓	✓	√ ⁽¹⁾	✓	✓	✓
CMPEQ	✓	✓	√ ⁽¹⁾	✓	✓	✓
CMPEQ2		✓	✓			✓

⁽¹⁾ Instruction also available in compact form, see Section 3.10.

SPRUFE8B-July 2010 Instruction Compatibility 709



Appendix A www.ti.com

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs (continued)

			imueu)			
Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
CMPEQ4		✓	✓			✓
CMPEQDP				✓	✓	✓
CMPEQSP				✓	✓	✓
CMPGT	✓	✓	✓ ⁽¹⁾	✓	✓	✓
CMPGT2		✓	✓			✓
CMPGTDP				✓	✓	✓
CMPGTSP				✓	✓	✓
CMPGTU	✓	✓	√ ⁽¹⁾	✓	✓	✓
CMPGTU4		✓	✓			✓
CMPLT	✓	✓	✓ ⁽¹⁾	✓	✓	✓
CMPLT2		✓	✓			✓
CMPLTDP				✓	✓	✓
CMPLTSP				✓	✓	✓
CMPLTU	✓	✓	√ ⁽²⁾	✓	✓	✓
CMPLTU4		✓	✓			✓
CMPY			✓			✓
CMPYR			✓			✓
CMPYR1			✓			✓
DDOTP4			✓			✓
DDOTPH2			· ✓			√
DDOTPH2R			√			√
DDOTPL2			√			√
DDOTPL2R			√			√
DEAL		✓	↓			√
DINT		v	√			√
DMV			√			√
DOTP2		✓	√			√
DOTPN2			√			√
DOTPNRSU2		√				
		√	√			√
DOTPNRUS2		√	√			√
DOTPRSU2		√	√			√
DOTPRUS2		√	√			√
DOTPSU4		V	√			V
DOTPUS4		√	√			√
DOTPU4		✓	√			√
DPACK2			√			√
DPACKX2			✓		_	√
DPINT				√	√	√
DPSP				√	√	√
DPTRUNC			. (0)	✓	✓	√
EXT	✓	✓	✓ ⁽²⁾	✓	✓	✓
EXTU	✓	✓	√ ⁽²⁾	✓	✓	✓
GMPY			✓			✓
GMPY4		✓	✓			✓
IDLE	✓	✓	✓	✓	✓	✓
INTDP				✓	✓	✓

 $^{\,^{(2)}}$ $\,$ Instruction also available in compact form, see Section 3.10.



www.ti.com Appendix A

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs (continued)

Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
INTDPU				✓	√	✓
INTSP				✓	✓	✓
INTSPU				✓	✓	✓
LDB	✓	✓	✓ ⁽²⁾	✓	✓	✓
LDB (15-bit offset)	✓	✓	✓ ⁽²⁾	✓	✓	✓
LDBU	✓	✓	√ ⁽²⁾	✓	✓	✓
LDBU (15-bit offset)	✓	✓	✓	✓	✓	✓
LDDW		✓	√ ⁽²⁾	✓	✓	✓
LDH	✓	✓	√ ⁽²⁾	✓	✓	✓
LDH (15-bit offset)	✓	✓	✓	✓	✓	✓
LDHU	✓	✓	√ ⁽²⁾	✓	✓	✓
LDHU (15-bit offset)	✓	✓	✓	✓	✓	✓
LDNDW		✓	√ ⁽²⁾			✓
LDNW		✓	✓ ⁽²⁾			✓
LDW	✓	· ✓	√ ⁽³⁾	✓	✓	✓
LDW (15-bit offset)	√	✓	✓	√ ·	✓	✓
LMBD	√	√	√	· ✓	√	✓
MAX2	•	✓	√	•	•	✓
MAXU4		✓	✓			· ✓
MIN2		√	√			· ✓
MINU4		√	√			√
MPY	✓	√	√ (3)	✓	✓	√
MPYDP	•	·	·	↓	√	√
MPYH	✓	✓	√ ⁽³⁾	√	√	√
MPYHI	•	√	√	v	v	√
MPYHIR		√	√			√
MPYHL	✓	√	√ (3)	✓	✓	√
MPYHLU	√	√	√	√	√	√
MPYHSLU	v	√	√	√	√	√
MPYHSU	√	√	√	√	√	√
MPYHU	V					
MPYHULS	√	√ /	√ √	√	√ √	√ √
	v	√ /		√ /	V	v
MPYHUS MPYI	v	√	✓	V	V	V
				V	V	√
MPYID		,	,	✓	✓	√
MPYIH		√	√			√
MPYIHR		√	√			√
MPYIL		√	√			√
MPYILR		√	√	,	,	√
MPYLH	√	√	√ ⁽³⁾	√	√	√
MPYLHU	✓	√	√	✓	✓	√
MPYLI		✓	✓			✓
MPYLIR		✓	✓			✓
MPYLSHU	✓	✓	✓	✓	✓	✓
MPYLUHS	✓	✓	✓	✓	✓	✓
MPYSP				✓	✓	✓

⁽³⁾ Instruction also available in compact form, see Section 3.10.



Appendix A www.ti.com

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs (continued)

Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
MPYSPDP				✓	√	✓
MPYSP2DP				✓	✓	✓
MPYSU	✓	✓	✓	✓	✓	✓
MPYSU4		✓	✓			✓
MPYU	✓	✓	✓	✓	✓	✓
MPYU4		✓	✓			✓
MPYUS	✓	✓	✓	✓	✓	✓
MPYUS4		✓	✓			✓
MPY2		✓	✓			✓
MPY2IR			✓			✓
MPY32 (32-bit result)			✓			✓
MPY32 (64-bit result)			✓			✓
MPY32SU			✓			✓
MPY32U			✓			✓
MPY32US			√			✓
MV	✓	✓	√ ⁽⁴⁾	✓	✓	· ✓
MVC	✓	✓	√ ⁽⁴⁾	√	√	✓
MVD	·	✓	✓	•	•	√
MVK	✓	✓	√ ⁽⁴⁾	✓	✓	· ✓
MVKH	<i>'</i>	√	√	· ✓	√	√
MVKL	√	√	√	↓	√	√
MVKLH	√	√	√	↓	√	√
NEG	√	√	√ ⁽⁴⁾	↓	√	√
NOP	√	√	√ ⁽⁴⁾	√	√	√
NORM	√	√	√	√	√	√
NOT	V	√	√	√	√	√
OR	√	√	√ ⁽⁴⁾	√	√	√
PACK2	•	√	√	v	v	√
PACKH2		√	√			√
PACKH4		√	√			√
PACKHL2		√	√			√
PACKIH2			√			√
		√ ./				v
PACKL4 RCPDP		✓	✓	,	,	V
				√	√	√
RCPSP			,	✓	✓	√
RINT		,	√			√
ROTL		✓	√			√
RPACK2			✓	,	,	√
RSQRDP				√	√	√
RSQRSP	_	_	z (4)	√	√	√
SADD	✓	√	√ ⁽⁴⁾	✓	✓	✓
SADD2		✓	✓			✓
SADDSUB			✓			✓
SADDSUB2			✓			✓
SADDSU2		✓	✓			✓
SADDUS2		✓	✓			✓

 $^{\,^{(4)}}$ $\,$ Instruction also available in compact form, see Section 3.10.



www.ti.com Appendix A

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs (continued)

		(COIII	iinuea)			
Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
SADDU4		✓	✓			✓
SAT	✓	✓	✓	✓	✓	✓
SET	✓	✓	✓ ⁽⁴⁾	✓	✓	✓
SHFL		✓	✓			✓
SHFL3			✓			✓
SHL	✓	✓	✓ ⁽⁴⁾	✓	✓	✓
SHLMB		✓	✓			✓
SHR	✓	✓	√ ⁽⁴⁾	✓	✓	✓
SHR2		✓	✓			✓
SHRMB		✓	✓			✓
SHRU	✓	✓	√ ⁽⁴⁾	✓	✓	✓
SHRU2		✓	✓			✓
SMPY	✓	✓	√ ⁽⁴⁾	✓	✓	✓
SMPYH	✓	✓	√ ⁽⁴⁾	✓	✓	✓
SMPYHL	✓	✓	✓ ⁽⁵⁾	✓	✓	✓
SMPYLH	✓	✓	√ ⁽⁵⁾	✓	✓	✓
SMPY2		✓	✓			✓
SMPY32			✓			✓
SPACK2		✓	✓			✓
SPACKU4		✓	✓			✓
SPDP				✓	✓	✓
SPINT				✓	✓	✓
SPKERNEL			✓ ⁽⁵⁾			✓
SPKERNELR			✓			✓
SPLOOP			√ ⁽⁵⁾			✓
SPLOOPD			✓ ⁽⁵⁾			✓
SPLOOPW			✓			✓
SPMASK			√ ⁽⁵⁾			✓
SPMASKR			✓ ⁽⁵⁾			✓
SPTRUNC				✓	✓	✓
SSHL	✓	✓	✓ ⁽⁵⁾	✓	✓	✓
SSHVL		✓	✓			✓
SSHVR		✓	✓			✓
SSUB	✓	✓	√ ⁽⁵⁾	✓	✓	✓
SSUB2			✓			✓
STB	✓	✓	✓ ⁽⁵⁾	✓	✓	✓
STB (15-bit offset)	✓	✓	✓	✓	✓	✓
STDW		✓	✓ ⁽⁵⁾			✓
STH	✓	✓	✓ ⁽⁵⁾	✓	✓	✓
STH (15-bit offset)	✓	✓	✓	✓	✓	✓
STNDW		✓	✓ ⁽⁵⁾			✓
STNW		✓	√ ⁽⁵⁾			✓
STW	✓	✓	√ ⁽⁵⁾	✓	✓	✓
STW (15-bit offset)	✓	✓	√ ⁽⁵⁾	✓	✓	✓
SUB	✓	✓	√ ⁽⁵⁾	✓	✓	✓
SUBAB	✓	✓	✓	✓	✓	✓

⁽⁵⁾ Instruction also available in compact form, see Section 3.10.



Appendix A www.ti.com

Table A-1. Instruction Compatibility Between C62x, C64x, C64x+, C67x, C67x+, and C674x DSPs (continued)

		,				
Instruction	C62x DSP	C64x DSP	C64x+ DSP	C67x DSP	C67x+ DSP	C674x DSP
SUBABS4		✓	✓			✓
SUBAH	✓	✓	✓	✓	✓	✓
SUBAW	✓	✓	√ ⁽⁵⁾	✓	✓	✓
SUBC	✓	✓	✓	✓	✓	✓
SUBDP				✓	✓	✓
SUBSP				✓	✓	✓
SUBU	✓	✓	✓	✓	✓	✓
SUB2	✓	✓	✓	✓	✓	✓
SUB4		✓	✓			✓
SWAP2		✓	✓			✓
SWAP4		✓	✓			✓
SWE			✓			✓
SWENR			✓			✓
UNPKHU4		✓	✓			✓
UNPKLU4		✓	✓			✓
XOR	✓	✓	√ ⁽⁶⁾	✓	✓	✓
XORMPY			✓			✓
XPND2		✓	✓			✓
XPND4		✓	✓			✓
ZERO	✓	✓	✓	✓	✓	✓

⁽⁶⁾ Instruction also available in compact form, see Section 3.10.



Mapping Between Instruction and Functional Unit

Table B-1 lists the instructions that execute on each functional unit.

Table B-1. Instruction to Functional Unit Mapping

	Functional Unit						
Instruction	.L Unit	.M Unit	.S Unit	.D Unit			
ABS	✓						
ABS2	✓						
ABSDP			✓				
ABSSP			✓				
ADD	✓		✓	✓			
ADDAB				✓			
ADDAD				✓			
ADDAH				✓			
ADDAW				✓			
ADDDP	✓		✓				
ADDK			✓				
ADDKPC			√ ⁽¹⁾				
ADDSP	✓		✓				
ADDSUB	✓						
ADDSUB2	✓						
ADDU	✓						
ADD2	✓		✓	✓			
ADD4	✓						
AND	✓		✓	✓			
ANDN	✓		✓	✓			
AVG2		✓					
AVGU4		✓					
B displacement			✓				
B register			√ ⁽¹⁾				
B IRP			√ ⁽¹⁾				
B NRP			√ ⁽¹⁾				
BDEC			✓				
BITC4		✓					
BITR		✓					
BNOP displacement			✓				
BNOP register			✓				
BPOS			✓				
CALLP			✓				
CLR			✓				
CMPEQ	✓						

⁽¹⁾ S2 only



Appendix B www.ti.com

Table B-1. Instruction to Functional Unit Mapping (continued)

	Table B-1. Instruction to Functional Unit Mapping (continued) Functional Unit							
Instruction	.L Unit	.M Unit	.S Unit	.D Unit				
CMPEQ2			✓					
CMPEQ4			✓					
CMPEQDP			✓					
CMPEQSP			✓					
CMPGT	✓							
CMPGT2			✓					
CMPGTDP			✓					
CMPGTSP			✓					
CMPGTU	✓							
CMPGTU4			✓					
CMPLT	✓							
CMPLT2			✓					
CMPLTDP			✓					
CMPLTSP			✓					
CMPLTU	✓							
CMPLTU4			✓					
CMPY		✓						
CMPYR		✓						
CMPYR1		✓						
DDOTP4		✓						
DDOTPH2		✓						
DDOTPH2R		✓						
DDOTPL2		✓						
DDOTPL2R		✓						
DEAL		✓						
DINT		No	unit					
DMV			✓					
DOTP2		✓						
DOTPN2		✓						
DOTPNRSU2		✓						
DOTPNRUS2		✓						
DOTPRSU2		✓						
DOTPRUS2		✓						
DOTPSU4		✓						
DOTPUS4		✓						
DOTPU4		✓						
DPACK2	✓							
DPACKX2	✓							
DPINT	✓							
DPSP	✓							
DPTRUNC	✓							
EXT			✓					
EXTU			✓					
GMPY		✓						
GMPY4		✓						
IDLE		No	unit					



www.ti.com Appendix B

Table B-1. Instruction to Functional Unit Mapping (continued)

Instruction	-1. Instruction to Functional Unit Mapping (continued) Functional Unit				
	.L Unit	.M Unit	.S Unit	.D Unit	
INTDP	✓				
INTDPU	✓				
INTSP	✓				
INTSPU	✓				
LDB				✓	
LDB (15-bit offset)				√ ⁽²⁾	
LDBU				✓	
LDBU (15-bit offset)				√ ⁽²⁾	
LDDW				✓	
LDH				✓	
LDH (15-bit offset)				√ ⁽²⁾	
LDHU				✓	
LDHU (15-bit offset)				√ ⁽²⁾	
LDNDW				✓	
LDNW				✓	
LDW				✓	
LDW (15-bit offset)				✓ ⁽³⁾	
LMBD	✓				
MAX2	✓		✓		
MAXU4	✓				
MIN2	✓		✓		
MINU4	✓				
MPY		✓			
MPYDP		✓			
MPYH		✓			
MPYHI		✓			
MPYHIR		✓			
MPYHL		✓			
MPYHLU		✓			
MPYHSLU		✓			
MPYHSU		✓			
MPYHU		✓			
MPYHULS		✓			
MPYHUS		✓			
MPYI		✓			
MPYID		✓			
MPYIH		✓			
MPYIHR		✓			
MPYIL		✓			
MPYILR		✓			
MPYLH		✓			
MPYLHU		✓			
MPYLI		✓			
MPYLIR		✓			
MPYLSHU		✓			

⁽²⁾ D2 only

⁽³⁾ D2 only



Appendix B www.ti.com

Table B-1. Instruction to Functional Unit Mapping (continued)

	B-1. Instruction to Functional Unit Mapping (continued) Functional Unit				
Instruction	.L Unit	.M Unit	.S Unit	.D Unit	
MPYLUHS		✓			
MPYSP		✓			
MPYSPDP		✓			
MPYSP2DP		✓			
MPYSU		✓			
MPYSU4		✓			
MPYU		✓			
MPYU4		✓			
MPYUS		✓			
MPYUS4		✓			
MPY2		✓			
MPY2IR		✓			
MPY32 (32-bit result)		✓			
MPY32 (64-bit result)		✓			
MPY32SU		✓			
MPY32U		✓			
MPY32US		✓			
MV	✓		✓	✓	
MVC			✓ ⁽⁴⁾		
MVD		✓			
MVK	\checkmark		✓	✓	
MVKH			✓		
MVKL			✓		
MVKLH			✓		
NEG	✓		✓		
NOP		No	unit		
NORM	✓				
NOT	✓		✓	✓	
OR	✓		✓	✓	
PACK2	✓		✓		
PACKH2	✓		✓		
PACKH4	✓				
PACKHL2	✓		✓		
PACKLH2	✓		✓		
PACKL4	✓				
RCPDP			✓		
RCPSP			✓		
RINT			unit		
ROTL		✓			
RPACK2			✓		
RSQRDP			✓		
RSQRSP			✓		
SADD	✓		✓		
SADD2			✓		
SADDSUB	✓				

⁽⁴⁾ S2 only



www.ti.com Appendix B

Table B-1. Instruction to Functional Unit Mapping (continued)

	B-1. Instruction to Functional Unit Mapping (continued) Functional Unit				
Instruction	.L Unit .M Unit .S Unit .D U				
SADDSUB2	✓				
SADDSU2			✓		
SADDUS2			✓		
SADDU4			✓		
SAT	✓				
SET			✓		
SHFL		✓			
SHFL3	✓				
SHL			✓		
SHLMB	✓		✓		
SHR			✓		
SHR2			✓		
SHRMB	✓		✓		
SHRU			✓		
SHRU2			✓		
SMPY		✓			
SMPYH		✓			
SMPYHL		✓			
SMPYLH		✓			
SMPY2		✓			
SMPY32		✓			
SPACK2			✓		
SPACKU4			✓		
SPDP			✓		
SPINT	✓				
SPKERNEL		No unit			
SPKERNELR		No	unit		
SPLOOP		No	unit		
SPLOOPD		No	unit		
SPLOOPW		No	unit		
SPMASK		No	unit		
SPMASKR		No	unit		
SPTRUNC	✓				
SSHL			✓		
SSHVL		✓			
SSHVR		✓			
SSUB	✓				
SSUB2	✓				
STB				✓	
STB (15-bit offset)				✓ ⁽⁵⁾	
STDW				✓	
STH				✓	
STH (15-bit offset)				✓ ⁽⁵⁾	
STNDW				✓	
STNW				✓	

⁽⁵⁾ D2 only



Appendix B www.ti.com

Table B-1. Instruction to Functional Unit Mapping (continued)

Instruction	Functional Unit					
	.L Unit	.M Unit	.S Unit	.D Unit		
STW				✓		
STW (15-bit offset)				✓ ⁽⁵⁾		
SUB	✓		✓	✓		
SUBAB				✓		
SUBABS4	✓					
SUBAH				✓		
SUBAW				✓		
SUBC	✓					
SUBDP	✓		✓			
SUBSP	✓		✓			
SUBU	✓					
SUB2	✓		✓	✓		
SUB4	✓					
SWAP2	✓		✓			
SWAP4	✓					
SWE		No unit				
SWENR		No unit				
UNPKHU4	✓		✓			
UNPKLU4	✓		✓			
XOR	✓		✓	✓		
XORMPY		✓				
XPND2		✓				
XPND4		✓				
ZERO	✓		✓	✓		



.D Unit Instructions and Opcode Maps

This appendix lists the instructions that execute in the .D functional unit and illustrates the opcode maps for these instructions.

Topic Page

C.1	Instructions Executing in the .D Functional Unit	722
C.2	Opcode Map Symbols and Meanings	722
C.3	32-Bit Opcode Maps	724
C.4	16-Bit Opcode Maps	725



C.1 Instructions Executing in the .D Functional Unit

Table C-1 lists the instructions that execute in the .D functional unit.

Table C-1. Instructions Executing in the .D Functional Unit

Instruction	Format	Instruction	Format
ADD	Figure C-1, Figure C-2	MV	Figure C-1, Figure C-2
ADDAB	Figure C-1, Figure C-3	MVK	Figure C-1
ADDAD	Figure C-1	NOT	Figure C-2
ADDAH	Figure C-1, Figure C-3	OR	Figure C-2
ADDAW	Figure C-1, Figure C-3	STB	Figure C-4
ADD2	Figure C-2	STB (15-bit offset) (1)	Figure C-5
AND	Figure C-2	STDW	Figure C-6
ANDN	Figure C-2	STH	Figure C-4
LDB	Figure C-4	STH (15-bit offset) (1)	Figure C-5
LDB (15-bit offset) (1)	Figure C-5	STNDW	Figure C-7
LDBU	Figure C-4	STNW	Figure C-4
LDBU (15-bit offset) (1)	Figure C-5	STW	Figure C-4
LDDW	Figure C-6	STW (15-bit offset) (1)	Figure C-5
LDH	Figure C-4	SUB	Figure C-1, Figure C-2
LDH (15-bit offset) (1)	Figure C-5	SUBAB	Figure C-1
LDHU	Figure C-4	SUBAH	Figure C-1
LDHU (15-bit offset) (1)	Figure C-5	SUBAW	Figure C-1
LDNDW	Figure C-7	SUB2	Figure C-2
LDNW	Figure C-4	XOR	Figure C-2
LDW	Figure C-4	ZERO	Figure C-1, Figure C-2
LDW (15-bit offset) (1)	Figure C-5		-

⁽¹⁾ D2 only

C.2 Opcode Map Symbols and Meanings

Table C-2 lists the symbols and meanings used in the opcode maps.

Table C-2. .D Unit Opcode Map Symbol Definitions

Symbol	Meaning
baseR	base address register
creg	3-bit field specifying a conditional register
dst	destination. For compact instructions, dst is coded as an offset from either A16 or B16 depending on the value of the t bit.
dw	doubleword; 0 = word, 1 = doubleword
ld/st	load or store; 0 = store, 1 = load
mode	addressing mode, see Table C-3
na	nonaligned; 0 = aligned, 1 = nonaligned
offsetR	register offset
ор	opfield; field within opcode that specifies a unique instruction
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel
ptr	offset from either A4-A7 or B4-B7 depending on the value of the s bit. The ptr field is the 2 least-significant bits of the src2 (baseR) field—bit 2 of register address is forced to 1.
r	LDDW/LDNDW/LDNW instruction
s	side A or B for destination; $0 = \text{side A}$, $1 = \text{side B}$. For compact instructions, side of base address (ptr) register; $0 = \text{side A}$, $1 = \text{side B}$.



Table C-2. .D Unit Opcode Map Symbol Definitions (continued)

Symbol	Meaning
src	source. For compact instructions, <i>src</i> is coded as an offset from either A16 or B16 depending on the value of the <i>t</i> bit.
src1	source 1
src2	source 2
SZ	data size select; 0 = primary size, 1 = secondary size (see Section 3.10.2.2)
t	side of source/destination (src/dst) register; 0 = side A, 1 = side B
ucst _n	bit n of the unsigned constant field
x	cross path for src2; 0 = do not use cross path, 1 = use cross path
У	.D1 or .D2 unit; 0 = .D1 unit, 1 = .D2 unit
z	test for equality with zero or nonzero

Table C-3. Address Generator Options for Load/Store

	mode	Field		Syntax	Modification Performed
0	0	0	0	*-R[<i>ucst5</i>]	Negative offset
0	0	0	1	*+R[ucst5]	Positive offset
0	1	0	0	*-R[offsetR]	Negative offset
0	1	0	1	*+R[offsetR]	Positive offset
1	0	0	0	*R[<i>ucst5</i>]	Predecrement
1	0 0 1		*++R[<i>ucst5</i>]	Preincrement	
1	0	1	0	*R[<i>ucst5</i>]	Postdecrement
1	0	1	1	*R++[<i>ucst5</i>]	Postincrement
1	1	0	0	*R[offsetR]	Predecrement
1	1	0	1	*++R[offsetR]	Preincrement
1	1	1	0	*R[offsetR]	Postdecrement
1	1 1 1 1			*R++[offsetR]	Postincrement



C.3 32-Bit Opcode Maps

The CPU 32-bit opcodes used in the .D unit are mapped in the following figures.

Figure C-1. 1 or 2 Sources Instruction Format

31	29	28	27	23	22 18	8 17	13	 12	7	6	5	4	3	2	1	0
cre	g	Z		dst	src2		src1	ор		1	0	0	0	0	s	p
3		1		5	5		5	6							1	1

Figure C-2. Extended .D Unit 1 or 2 Sources Instruction Format

31	29	28	27	23	22	18	17	13	12	11	10	9	6	5	4	3	2	1	0
creg		Z		dst	src2		src1		Х	1	0	ор		1	1	0	0	s	p
3		1		5	5		5		1			4						1	1

Figure C-3. ADDAB/ADDAH/ADDAW Long-Immediate Operations

31	30	29	28	27 23	22 8	7	6		4	3	2	1	0
0	0	0	1	dst	offsetR	У		ор		1	1	s	р
				5	15	1		3				1	1

Figure C-4. Load/Store Basic Operations

31	29	28	27	23	22	18	17		13	12	9	8	7	6	4	3	2	1	0
cre	g	z		src/dst	baseR			offsetR		mode		r	У	ор		0	1	s	p
3		1		5	5			5		4		1	1	3				1	1

Figure C-5. Load/Store Long-Immediate Operations

31 29	28	27 23	22 8	7	6	4	3	2	1	0
creg	Z	src/dst	offsetR	У	ор		1	1	s	р
3	1	5	15	1	3				1	1

Figure C-6. Load/Store Doubleword Instruction Format

	31	29	28	27	23	22	18	17	13	17		9	8	7	6	4	3	,	2	1	0
	creg	9	Z		src/dst	baseR		offse	tR		mode		1	У	C	p	C)	1	s	p
_	3		1		5	5		5			4			1	(3				1	1

Figure C-7. Load/Store Nonaligned Doubleword Instruction Format

31 29	28	27	24	23	22	18	17		13	12	9	8	7	6	4	3	2	1	0
creg	Z		src/dst	sc	baseR			offsetR		mode		1	У	ор		0	1	s	p
3	1		4	1	5			5		4			1	3				1	1



C.4 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the .D unit for compact instructions are mapped in the following figures. See Section 3.10 for more information about compact instructions.

Figure C-8. Doff4 Instruction Format

15	13	12	11	10	9	8	7	6	4	3	2	1	0
	ucst ₂₋₀	t	ucst ₃	0	SZ	pti	r	src/dst		ld/st	1	0	s
	3	1	1		1	2		3		1			1

-	DSZ		SZ	ld/st	Mnemonic
0	Х	Х	0	0	STW (.unit) src, *ptr[ucst4]
0	Х	Х	0	1	LDW (.unit) *ptr[ucst4], dst
0	0	0	1	0	STB (.unit) src, *ptr[ucst4]
0	0	0	1	1	LDBU (.unit) *ptr[ucst4], dst
0	0	1	1	0	STB (.unit) src, *ptr[ucst4]
0	0	1	1	1	LDB (.unit) *ptr[ucst4], dst
0	1	0	1	0	STH (.unit) src, *ptr[ucst4]
0	1	0	1	1	LDHU (.unit) *ptr[ucst4], dst
0	1	1	1	0	STH (.unit) src, *ptr[ucst4]
0	1	1	1	1	LDH (.unit) *ptr[ucst4], dst
1	0	0	1	0	STW (.unit) src, *ptr[ucst4]
1	0	0	1	1	LDW (.unit) *ptr[ucst4], dst
1	0	1	1	0	STB (.unit) src, *ptr[ucst4]
1	0	1	1	1	LDB (.unit) *ptr[ucst4], dst
1	1	0	1	0	STNW (.unit) src, *ptr[ucst4]
1	1	0	1	1	LDNW (.unit) *ptr[ucst4], dst
1	1	1	1	0	STH (.unit) src, *ptr[ucst4]
1	1	1	1	1	LDH (.unit) *ptr[ucst4], dst

Figure C-9. Doff4DW Instruction Format

15	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
ucst	2-0	t	ucst ₃	0	SZ	ptr		src/	'dst	na	ld/st	1	0	s	
3		1	1		1	2		2)	1	1			1	

NOTE: src/dst register address formed from op6:op5:0 (even registers)

	DSZ		SZ	ld/st	na	Mnemonic
1	Х	х	0	0	0	STDW (.unit) src, *ptr[ucst4]
1	Х	х	0	1	0	LDDW (.unit) *ptr[ucst4], dst
1	Х	х	0	0	1	STNDW (.unit) src, *ptr[ucst4] (ucst4 unscaled only)
1	Х	х	0	1	1	LDNDW (.unit) *ptr[ucst4], dst (ucst4 unscaled only)



	Figure C-10. Dind Instruction Format													
15		13	12	11	10	9	8	7	6	4	3	2	1	0
	src1		t	0	1	SZ	р	tr	S	src/dst	ld/st	1	0	s
	3		1			1	2	2		3	1			1

Opcode map field used	For operand type
src1	sint

-	DSZ		SZ	ld/st	Mnemonic
0	Х	Х	0	0	STW (.unit) src, *ptr[src1]
0	Х	х	0	1	LDW (.unit) *ptr[src1], dst
0	0	0	1	0	STB (.unit) src, *ptr[src1]
0	0	0	1	1	LDBU (.unit) *ptr[src1], dst
0	0	1	1	0	STB (.unit) src, *ptr[src1]
0	0	1	1	1	LDB (.unit) *ptr[src1], dst
0	1	0	1	0	STH (.unit) src, *ptr[src1]
0	1	0	1	1	LDHU (.unit) *ptr[src1], dst
0	1	1	1	0	STH (.unit) src, *ptr[src1]
0	1	1	1	1	LDH (.unit) *ptr[src1], dst
1	0	0	1	0	STW (.unit) src, *ptr[src1]
1	0	0	1	1	LDW (.unit) *ptr[src1], dst
1	0	1	1	0	STB (.unit) src, *ptr[src1]
1	0	1	1	1	LDB (.unit) *ptr[src1], dst
1	1	0	1	0	STNW (.unit) src, *ptr[src1]
1	1	0	1	1	LDNW (.unit) *ptr[src1], dst
1	1	1	1	0	STH (.unit) src, *ptr[src1]
1	1	1	1	1	LDH (.unit) *ptr[src1], dst



					Fig	ure C-1	1. Dind	DW In	struction	on For	mat				
15		13	12	11	10	9	8	7	6	5	4	3	2	1	0
	src1		t	0	1	SZ	pt	r	src	/dst	na	ld/st	1	0	s
	3		1			1	2		2	2	1	1			1

NOTE: src/dst register address formed from op6:op5:0 (even registers)

Opcode map field used	For operand type
src1	sint

	DSZ		SZ	ld/st	na	Mnemonic
1	Х	Х	0	0	0	STDW (.unit) src, *ptr[src1]
1	Х	х	0	1	0	LDDW (.unit) *ptr[src1], dst
1	Х	х	0	0	1	STNDW (.unit) src, *ptr[src1] (src1 unscaled only)
1	Х	х	0	1	1	LDNDW (.unit) *ptr[src1], dst (src1 unscaled only)

Figure C-12. Dinc Instruction Format

15	14	13	12	11	10	9	8	7	6	4	3	2	1	0
0	0	ucst ₀	t	1	1	SZ	pt	r	src/dst		ld/st	1	0	s
		1	1			1	2		3		1			1

NOTE: $ucst2 = ucst_0 + 1$

	DSZ		SZ	ld/st	Mnemonic
0	Х	Х	0	0	STW (.unit) src, *ptr[ucst2]++
0	Х	х	0	1	LDW (.unit) *ptr[ucst2]++, dst
0	0	0	1	0	STB (.unit) src, *ptr[ucst2]++
0	0	0	1	1	LDBU (.unit) *ptr[ucst2]++, dst
0	0	1	1	0	STB (.unit) src, *ptr[ucst2]++
0	0	1	1	1	LDB (.unit) *ptr[ucst2]++, dst
0	1	0	1	0	STH (.unit) src, *ptr[ucst2]++
0	1	0	1	1	LDHU (.unit) *ptr[ucst2]++, dst
0	1	1	1	0	STH (.unit) src, *ptr[ucst2]++
0	1	1	1	1	LDH (.unit) *ptr[ucst2]++, dst
1	0	0	1	0	STW (.unit) src, *ptr[ucst2]++
1	0	0	1	1	LDW (.unit) *ptr[ucst2]++, dst
1	0	1	1	0	STB (.unit) src, *ptr[ucst2]++
1	0	1	1	1	LDB (.unit) *ptr[ucst2]++, dst
1	1	0	1	0	STNW (.unit) src, *ptr[ucst2]++
1	1	0	1	1	LDNW (.unit) *ptr[ucst2]++, dst
1	1	1	1	0	STH (.unit) src, *ptr[ucst2]++
1	1	1	1	1	LDH (.unit) *ptr[ucst2]++, dst



	Figure C-13. DincDW Instruction Format														
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	ucst ₀	t	1	1	SZ	pt	ptr		/dst	na	ld/st	1	0	s
		1	1			1	2		2		1	1			1

NOTES:

- 1. $ucst2 = ucst_0 + 1$
- 2. src/dst register address formed from op6:op5:0 (even registers)

	DSZ		SZ	ld/st	na	Mnemonic
1	Х	Х	0	0	0	STDW (.unit) src, *ptr[ucst2]++
1	X	Х	0	1	0	LDDW (.unit) *ptr[ucst2]++, dst
1	X	Х	0	0	1	STNDW (.unit) src, *ptr[ucst2]++ (ucst2 scaled only)
1	х	х	0	1	1	LDNDW (.unit) *ptr[ucst2]++, dst (ucst2 scaled only)

Figure C-14. Ddec Instruction Format

15	5	14	13	12	11	10	9	8 7	6	4	3	2	1	0
0)	1	ucst ₀	t	1	1	SZ	ptr		src/dst	ld/st	1	0	s
			1	1			1	2		3	1			1

NOTE: $ucst2 = ucst_0 + 1$

	DSZ		sz	ld/st	Mnemonic
0	Х	х	0	0	STW (.unit) src, *ptr[ucst2]
0	Х	х	0	1	LDW (.unit) *ptr[ucst2], dst
0	0	0	1	0	STB (.unit) src, *ptr[ucst2]
0	0	0	1	1	LDBU (.unit) *ptr[ucst2], dst
0	0	1	1	0	STB (.unit) src, *ptr[ucst2]
0	0	1	1	1	LDB (.unit) *ptr[ucst2], dst
0	1	0	1	0	STH (.unit) src, *ptr[ucst2]
0	1	0	1	1	LDHU (.unit) *ptr[ucst2], dst
0	1	1	1	0	STH (.unit) src, *ptr[ucst2]
0	1	1	1	1	LDH (.unit) *ptr[ucst2], dst
1	0	0	1	0	STW (.unit) src, *ptr[ucst2]
1	0	0	1	1	LDW (.unit) *ptr[ucst2], dst
1	0	1	1	0	STB (.unit) src, *ptr[ucst2]
1	0	1	1	1	LDB (.unit) *ptr[ucst2], dst
1	1	0	1	0	STNW (.unit) src, *ptr[ucst2]
1	1	0	1	1	LDNW (.unit) *ptr[ucst2], dst
1	1	1	1	0	STH (.unit) src, *ptr[ucst2]
1	1	1	1	1	LDH (.unit) *ptr[ucst2], dst



	Figure C-15. DdecDW Instruction Format														
15	14	13	12	11	10 9 8 7 6 5 4 3 2 1										
0	1	ucst ₀	t	1	1	SZ	pti	ptr		'dst	na	ld/st	1	0	s
<u> </u>		1	1			1	2		2	!	1	1			1

NOTES:

- 1. $ucst2 = ucst_0 + 1$
- 2. src/dst register address formed from op6:op5:0 (even registers)

	DSZ		SZ	ld/st	na	Mnemonic
1	Х	Х	0	0	0	STDW (.unit) src, *ptr[ucst2]
1	Х	х	0	1	0	LDDW (.unit) *ptr[ucst2], dst
1	Х	х	0	0	1	STNDW (.unit) src, *ptr[ucst2] (ucst2 scaled only)
1	Х	Х	0	1	1	LDNDW (.unit) *ptr[ucst2], dst (ucst2 scaled only)

Figure C-16. Dstk Instruction Format

15	14	13	12	11	10	9	7	6	4	3	2	1	0
1	ucst ₁₋₀		t	1	1	ucst ₄₋₂		src/dst		ld/st	1	0	s
)	1			3		3		1			1

NOTE: ptr = B15, s = 1

ld/st	Mnemonic
0	STW (.unit) src,*B15[ucst5]
1	LDW (.unit)*B15[ucst5], dst

Figure C-17. Dx2op Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0
src1/ds	t	х	ор	0	src2		0	1	1	0	1	1	s
3		1	1		3								1

Opcode map field used	For operand type
src1/dst	sint
src2	xsint

ор	Mnemonic
0	ADD (.unit) src1, src2, dst (src1 = dst)
1	SUB (.unit) src1, src2, dst (src1 = dst, dst = src1 - src2



	Figure C-18. Dx5 Instruction Format													
15	13	12	11	10	9		7	6	5	4	3	2	1	0
ucst ₂₋₀ ucst ₄₋₃			st ₄₋₃	1		dst		0	1	1	0	1	1	S
3 2					3								1	

NOTE: src2 = B15

Opcode map field used	For operand type
dst	sint

Mnemonic	
ADDAW (.unit)B15, ucst5, dst	

Figure C-19. Dx5p Instruction Format

15	13	12	11	10	9	8	7	6	5	4	3	2	1	0
uc	st ₂₋₀	0	1	1	ucs	st ₄₋₃	ор	1	1	1	0	1	1	1
	3)	1							s = 1

NOTE: src2 = dst = B15

ор	Mnemonic
0	ADDAW (.unit)B15, <i>ucst5</i> , B15
1	SUBAW (.unit)B15, <i>ucst5</i> , B15

Figure C-20. Dx1 Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0	
ор		1	1	0	src2	/dst	1	1	1	0	1	1	S	
3					.3								1	

Opcode map field used	For operand type
src2/dst	sint

	ор		Mnemonic
0	0	0	see LSDx1, Figure G-4
0	0	1	see LSDx1, Figure G-4
0	1	0	Reserved
0	1	1	SUB (.unit) <i>src</i> 2, 1, <i>dst</i> (src2 = dst, dst = src2 - 1)
1	0	0	Reserved
1	0	1	see LSDx1, Figure G-4
1	1	0	Reserved
1	1	1	see LSDx1, Figure G-4



Figure C-21. Dpp Instruction Format

15	14	13	12	11	10	7	6	5	4	3	2	1	0
dw	dl/st	ucst ₀	t	0	src/dst		1	1	1	0	1	1	1
1	1	1	1		4								

NOTES:

- 1. ptr = B15
- 2. $ucst2 = ucst_0 + 1$
- 3. src/dst is from A0-A15, B0-B15
- 4. RS header bit is ignored

dw	ld/st	Mnemonic				
0	0	STW (.unit) src,*B15[ucst2]				
0	1	DW (.unit)*++B15[ucst2], dst				
1	0	TDW (.unit) src,*B15[ucst2]				
1	1	LDDW (.unit)*++B15[ucst2], dst				

t	src/dst	Source/Destination	t	src/dst	Source/Destination
0	0000	A0	1	0000	В0
0	0001	A1	1	0001	B1
0	0010	A2	1	0010	B2
0	0011	A3	1	0011	B3
0	0100	A4	1	0100	B4
0	0101	A5	1	0101	B5
0	0110	A6	1	0110	B6
0	0111	A7	1	0111	B7
0	1000	A8	1	1000	B8
0	1001	A9	1	1001	B9
0	1010	A10	1	1010	B10
0	1011	A11	1	1011	B11
0	1100	A12	1	1100	B12
0	1101	A13	1	1101	B13
0	1110	A14	1	1110	B14
0	1111	A15	1	1111	B15



.L Unit Instructions and Opcode Maps

This appendix lists the instructions that execute in the .L functional unit and illustrates the opcode maps for these instructions.

Topic Page

D.1	Instructions Executing in the .L Functional Unit	734
D.2	Opcode Map Symbols and Meanings	735
D.3	32-Bit Opcode Maps	735
D.4	16-Bit Opcode Maps	736
	•	



D.1 Instructions Executing in the .L Functional Unit

Table D-1 lists the instructions that execute in the .L functional unit.

Table D-1. Instructions Executing in the .L Functional Unit

Instruction	Format	Instruction	Format
ABS	Figure D-1	NORM	Figure D-1
ABS2	Figure D-2	NOT	Figure D-1
ADD	Figure D-1	OR	Figure D-1
ADDDP	Figure D-1	PACK2	Figure D-1
ADDSP	Figure D-1	PACKH2	Figure D-1
ADDSUB	Figure D-3	PACKH4	Figure D-1
ADDSUB2	Figure D-3	PACKHL2	Figure D-1
ADDU	Figure D-1	PACKLH2	Figure D-1
ADD2	Figure D-1	PACKL4	Figure D-1
ADD4	Figure D-1	SADD	Figure D-1
AND	Figure D-1	SADDSUB	Figure D-3
ANDN	Figure D-1	SADDSUB2	Figure D-3
CMPEQ	Figure D-1	SAT	Figure D-1
CMPGT	Figure D-1	SHFL3	Figure D-3
CMPGTU	Figure D-1	SHLMB	Figure D-1
CMPLT	Figure D-1	SHRMB	Figure D-1
CMPLTU	Figure D-1	SPINT	Figure D-1
DPACK2	Figure D-3	SPTRUNC	Figure D-1
DPACKX2	Figure D-3	SSUB	Figure D-1
DPINT	Figure D-1	SSUB2	Figure D-1
DPSP	Figure D-1	SUB	Figure D-1
DPTRUNC	Figure D-1	SUBABS4	Figure D-1
INTDP	Figure D-1	SUBC	Figure D-1
INTDPU	Figure D-1	SUBDP	Figure D-1
INTSP	Figure D-1	SUBSP	Figure D-1
INTSPU	Figure D-1	SUBU	Figure D-1
LMBD	Figure D-1	SUB2	Figure D-1
MAX2	Figure D-1	SUB4	Figure D-1
MAXU4	Figure D-1	SWAP2	Figure D-1
MIN2	Figure D-1	SWAP4	Figure D-2
MINU4	Figure D-1	UNPKHU4	Figure D-2
MV	Figure D-1	UNPKLU4	Figure D-2
MVK	Figure D-2	XOR	Figure D-1
NEG	Figure D-1	ZERO	Figure D-1



D.2 Opcode Map Symbols and Meanings

Table D-2 lists the symbols and meanings used in the opcode maps.

Table D-2. .L Unit Opcode Map Symbol Definitions

Symbol	Meaning
creg	3-bit field specifying a conditional register
cstn	n-bit constant field
dst	destination
ор	opfield; field within opcode that specifies a unique instruction
op_n	bit n of the opfield
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel
s	side A or B for destination; 0 = side A, 1 = side B
scst _n	bit n of the signed constant field
sn	sign
src1	source 1
src2	source 2
ucstn	n-bit unsigned constant field
x	cross path for src2; 0 = do not use cross path, 1 = use cross path
z	test for equality with zero or nonzero

D.3 32-Bit Opcode Maps

The CPU 32-bit opcodes used in the .L unit are mapped in the following figures.

Figure D-1. 1 or 2 Sources Instruction Format

31 2	29 28	27	23	22 18	17 13	12	11	5	4	3	2	1	0
creg	Z		dst	src2	src1	х	ор		1	1	0	s	p
3	1		5	5	5	1	7					1	1

Figure D-2. Unary Instruction Format

31 29	28	27	23) 22	18	17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	Z		dst	src2	?		ор		Х	0	0	1	1	0	1	0	1	1	0	s	р
3	1		5	5			5		1											1	1

Figure D-3. 1 or 2 Sources, Nonconditional Instruction Format

31	30	29	28	27	23 22	18 17	13 12	11	5 4	3	2	1	0
0	0	0	1	dst	src2	src1	х	ор	1	1	0	s	р
				5	5	5	1	7				1	1



D.4 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the .L unit for compact instructions are mapped in the following figures. See Section 3.10 for more information about compact instructions.

Figure D-4. L3 Instruction Format

15	13	12	11	10	9	7	6	4	3	2	1	0
sro	:1	х	ор	0	src2		dst		0	0	0	S
3		1	1		3		3					1

Opcode map field used	For operand type	_
src1	sint	
src2	xsint	
dst	sint	

ор	SAT	Mnemonic
0	0	ADD (.unit) src1, src2, dst
0	1	SADD (.unit) src1, src2, dst
1	0	SUB (.unit) <i>src1</i> , <i>src2</i> , <i>dst</i> (dst = src1 - src2)
1	1	SSUB (.unit) <i>src1</i> , <i>src2</i> , <i>dst</i> (dst = src1 - src2)

Figure D-5. L3i Instruction Format



Opcode map field used	For operand type
src2	xsint

		32-Bit Opco	-Bit Opcode cst Equivalent			32-Bit Opcode cst Equivalent				
sn	cst3	scst5	Decimal Value	sn	cst3	scst5	Decimal Value			
0	000	01000	8	1	000	11000	-8			
0	001	00001	1	1	001	11001	-7			
0	010	00010	2	1	010	11010	-6			
0	011	00011	3	1	011	11011	-5			
0	100	00100	4	1	100	11100	-4			
0	101	00101	5	1	101	11101	-3			
0	110	00110	6	1	110	11110	-2			
0	111	00111	7	1	111	11111	-1			



ADD (.unit) scst5, src2, dst



Figure D-6. Ltbd Instruction Format															
15	14	13	12	11	10	9		7	6	5	4	3	2	1	0
			х		0		src2					1	0	0	S
•			1				3								1

Opcode map field used	For operand type
src2	xsint

Figure D-7. L2c Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0
src1	1	х	op ₂	1	src2		op ₁	-0	dst	1	0	0	s
3		1	1		3		2		1				1

NOTE: dst = A0, A1 or B0, B1 as selected by dst and s

Opcode map field used	For operand type
src1	sint
src2	xsint

	ор		Mnemonic
0	0	0	AND (.unit) src1, src2, dst
0	0	1	OR (.unit) src1, src2, dst
0	1	0	XOR (.unit) src1, src2, dst
0	1	1	CMPEQ (.unit) src1, src2, dst
1	0	0	CMPLT (.unit) src1, src2, dst (dst = src1 < src2 , signed compare)
1	0	1	CMPGT (.unit) src1, src2, dst (dst = src1 > src2 , signed compare)
1	1	0	CMPLTU (.unit) src1, src2, dst (dst = src1 < src2 , unsigned compare)
1	1	1	CMPGTU (.unit) <i>src1</i> , <i>src2</i> , <i>dst</i> (dst = src1 > src2 , unsigned compare)



15	13	1	12	11	10	9		7	6	5	4	3	2	1	0
	scst ₂₋₀		scst ₄	-3	1		dst		0	1	0	0	1	1	s
	3		2				3								1

Opcode map field used	For operand type
dst	sint

Mnemonic

MVK (.unit) scst5, dst

Figure D-9. Lx3c Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0	
ucst3	3	0	dst	0	src2		0	1	0	0	1	1	s	
3			1		3								1	

NOTE: dst = A0, A1 or B0, B1 as selected by dst and s

Opcode map field used	For operand type
src2	sint

Mnemonic

CMPEQ (.unit) ucst3, src2, dst



14

15

ор

2

www.ti.com 16-Bit Opcode Maps

NOTE: dst = A0, A1 or B0, B1 as selected by dst and s

13

ucst1

Opcode map field used	For operand type
src2	sint

3

	ор	Mnemonic
0	0	CMPLT (.unit) ucst1, src2, dst (dst = ucst1 < src2 , signed compare)
0	1	CMPGT (.unit) ucst1, src2, dst (dst = ucst1 > src2 , signed compare)
1	0	CMPLTU (.unit) ucst1, src2, dst (dst = ucst1 < src2 , unsigned compare)
1	1	CMPGTU (.unit) ucst1, src2, dst (dst = ucst1 > src2 , unsigned compare)

Figure D-11. Lx1 Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0	
ор		1	1	0	src2/a	lst	1	1	0	0	1	1	s	
3					3								1	

	ор		Mnemonic
0	0	0	see LSDx1, Figure G-4
0	0	1	see LSDx1, Figure G-4
0	1	0	SUB (.unit)0, src2, dst (src2 = dst; dst = 0 - src2)
0	1	1	ADD (.unit)-1, src2, dst (src2 = dst)
1	0	0	Reserved
1	0	1	see LSDx1, Figure G-4
1	1	0	Reserved
1	1	1	see LSDx1, Figure G-4



.M Unit Instructions and Opcode Maps

This appendix lists the instructions that execute in the .M functional unit and illustrates the opcode maps for these instructions.

Topic Page

E.1	Instructions Executing in the .M Functional Unit	742
E.2	Opcode Map Symbols and Meanings	743
E.3	32-Bit Opcode Maps	743
E.4	16-Bit Opcode Maps	744
	•	



E.1 Instructions Executing in the .M Functional Unit

Table E-1 lists the instructions that execute in the .M functional unit.

Table E-1. Instructions Executing in the .M Functional Unit

Instruction	Format	Instruction	Format
AVG2	Figure E-1	MPYIHR	Figure E-1
AVGU4	Figure E-1	MPYIL	Figure E-1
BITC4	Figure E-2	MPYILR	Figure E-1
BITR	Figure E-2	MPYLH	Figure E-4
CMPY	Figure E-3	MPYLHU	Figure E-4
CMPYR	Figure E-3	MPYLI	Figure E-1
CMPYR1	Figure E-3	MPYLIR	Figure E-1
DDOTP4	Figure E-3	MPYLSHU	Figure E-4
DDOTPH2	Figure E-3	MPYLUHS	Figure E-4
DDOTPH2R	Figure E-3	MPYSP	Figure E-4
DDOTPL2	Figure E-3	MPYSPDP	Figure E-1
DDOTPL2R	Figure E-3	MPYSP2DP	Figure E-1
DEAL	Figure E-2	MPYSU	Figure E-4
DOTP2	Figure E-1	MPYSU4	Figure E-1
DOTPN2	Figure E-1	MPYU	Figure E-4
DOTPNRSU2	Figure E-1	MPYU4	Figure E-1
DOTPNRUS2	Figure E-1	MPYUS	Figure E-4
DOTPRSU2	Figure E-1	MPYUS4	Figure E-1
DOTPRUS2	Figure E-1	MPY2	Figure E-1
DOTPSU4	Figure E-1	MPY2IR	Figure E-1
DOTPUS4	Figure E-1	MPY32 (32-bit result)	Figure E-4
DOTPU4	Figure E-1	MPY32 (64-bit result)	Figure E-4
GMPY	Figure E-3	MPY32SU	Figure E-4
GMPY4	Figure E-1	MPY32U	Figure E-1
MPY	Figure E-4	MPY32US	Figure E-1
MPYDP	Figure E-4	MVD	Figure E-2
MPYH	Figure E-4	ROTL	Figure E-1
MPYHI	Figure E-1	SHFL	Figure E-2
MPYHIR	Figure E-1	SMPY	Figure E-4
MPYHL	Figure E-4	SMPYH	Figure E-4
MPYHLU	Figure E-4	SMPYHL	Figure E-4
MPYHSLU	Figure E-4	SMPYLH	Figure E-4
MPYHSU	Figure E-4	SMPY2	Figure E-1
MPYHU	Figure E-4	SMPY32	Figure E-3
MPYHULS	Figure E-4	SSHVL	Figure E-1
MPYHUS	Figure E-4	SSHVR	Figure E-1
MPYI	Figure E-4	XORMPY	Figure E-3
MPYID	Figure E-4	XPND2	Figure E-2
MPYIH	Figure E-1	XPND4	Figure E-2



E.2 Opcode Map Symbols and Meanings

Table E-2 lists the symbols and meanings used in the opcode maps.

Table E-2. .M Unit Opcode Map Symbol Definitions

Symbol	Meaning
creg	3-bit field specifying a conditional register
dst	destination
ор	opfield; field within opcode that specifies a unique instruction
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel
s	side A or B for destination; 0 = side A, 1 = side B
src1	source 1
src2	source 2
x	cross path for src2; 0 = do not use cross path, 1 = use cross path
z	test for equality with zero or nonzero

E.3 32-Bit Opcode Maps

The CPU 32-bit opcodes used in the .M unit are mapped in the following figures.

Figure E-1. Extended M-Unit with Compound Operations

31	29	28	27	23	22 18	17	13	12	11	10	6	5	4	3	2	1	0
creg		Z	(dst	src2	src1		Х	0	ор		1	1	0	0	s	р
3		1		5	5	5		1		5						1	1

Figure E-2. Extended .M-Unit Unary Instruction Format

;	31 29	28	27	23	22 18	3 17		13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst		src2		ор		Х	0	0	0	0	1	1	1	1	0	0	s	р
	3	1	5		5		5		1											1	1

Figure E-3. Extended .M Unit 1 or 2 Sources, Nonconditional Instruction Format

31	30	29	28	27	23	22 1	8	17 1	13	12	11	10	6	5	4	3	2	1	0
0	0	0	1	dst		src2		src1		Х	0	ор		1	1	0	0	s	p
				5		5		5		1		5						1	1

Figure E-4. MPY Instruction Format


31 29	28	27	23	22 18	17	13 12	11	7	6	5	4	3	2	1	0
creg	Z		dst	src2	src1	х	ор		0	0	0	0	0	s	р
3	1		5	5	5	1	5							1	1



E.4 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the .M unit for compact instructions are mapped in the following figure. See Section 3.10 for more information about compact instructions.

Figure E-5. M3 Instruction Format



NOTE: RS = 0: dst from [A0, A2, A4, A6], [B0, B2, B4, B6]; RS = 1: dst from [A16, A18, A20, A22], [B16, B18, B20, B22]

Opcode map field used	For operand type
src1	sint
dst	sint
src2	xsint

SAT	0	р	Mnemonic
0	0	0	MPY (.unit) src1, src2, dst
0	0	1	MPYH (.unit) src1, src2, dst
0	1	0	MPYLH (.unit) src1, src2, dst
0	1	1	MPYHL (.unit) src1, src2, dst
1	0	0	SMPY (.unit) src1, src2, dst
1	0	1	SMPYH (.unit) src1, src2, dst
1	1	0	SMPYLH (.unit) src1, src2, dst
1	1	1	SMPYHL (.unit) src1, src2, dst



.S Unit Instructions and Opcode Maps

This appendix lists the instructions that execute in the .S functional unit and illustrates the opcode maps for these instructions.

Topic Page

F.1	Instructions Executing in the .S Functional Unit	746
F.2	Opcode Map Symbols and Meanings	747
F.3	32-Bit Opcode Maps	747
F.4	16-Bit Opcode Maps	750



F.1 Instructions Executing in the .S Functional Unit

Table F-1 lists the instructions that execute in the .S functional unit.

Table F-1. Instructions Executing in the .S Functional Unit

Instruction	Format	Instruction	Format
ABSDP	Figure F-1	MVKL	Figure F-13
ABSSP	Figure F-1	MVKLH	Figure F-13
ADD	Figure F-1	NEG	Figure F-1
ADDDP	Figure F-2	NOT	Figure F-1
ADDK	Figure F-3	OR	Figure F-1
ADDKPC (1)	Figure F-4	PACK2	Figure F-5
ADDSP	Figure F-2	PACKH2	Figure F-1
ADD2	Figure F-1	PACKHL2	Figure F-1
AND	Figure F-1	PACKLH2	Figure F-1
ANDN	Figure F-5	RCPDP	Figure F-1
B displacement	Figure F-6	RCPSP	Figure F-1
B register (1)	Figure F-7	RPACK2	Figure F-14
B IRP (1)	Figure F-8	RSQRDP	Figure F-1
B NRP (1)	Figure F-8	RSQRSP	Figure F-1
BDEC	Figure F-9	SADD	Figure F-1
BNOP displacement	Figure F-10	SADD2	Figure F-5
BNOP register	Figure F-11	SADDSU2	Figure F-5
BPOS	Figure F-9	SADDUS2	Figure F-5
CALLP	Figure F-12	SADDU4	Figure F-5
CLR	Figure F-1, Figure F-16	SET	Figure F-1, Figure F-16
CMPEQ2	Figure F-1	SHL	Figure F-1
CMPEQ4	Figure F-1	SHLMB	Figure F-5
CMPEQDP	Figure F-1	SHR	Figure F-1
CMPEQSP	Figure F-1	SHR2	Figure F-5
CMPGT2	Figure F-1	SHRMB	Figure F-5
CMPGTDP	Figure F-1	SHRU	Figure F-1
CMPGTSP	Figure F-1	SHRU2	Figure F-5
CMPGTU4	Figure F-1	SPACK2	Figure F-5
CMPLT2	Figure F-1	SPACKU4	Figure F-5
CMPLTDP	Figure F-1	SPDP	Figure F-1
CMPLTSP	Figure F-1	SSHL	Figure F-1
CMPLTU4	Figure F-1	SUB	Figure F-1
DMV	Figure F-5	SUBDP	Figure F-2
EXT	Figure F-1, Figure F-16	SUBSP	Figure F-2
EXTU	Figure F-1, Figure F-16	SUB2	Figure F-1
MAX2	Figure F-5	SWAP2	Figure F-1
MIN2	Figure F-5	UNPKHU4	Figure F-15
MV	Figure F-1	UNPKLU4	Figure F-15
MVC ⁽¹⁾	Figure F-1	XOR	Figure F-1
MVK	Figure F-13	ZERO	Figure F-1
MVKH	Figure F-13		

⁽¹⁾ S2 only



F.2 Opcode Map Symbols and Meanings

Table F-2 lists the symbols and meanings used in the opcode maps.

Table F-2. .S Unit Opcode Map Symbol Definitions

Symbol	Meaning
creg	3-bit field specifying a conditional register
csta	constant a
cstb	constant b
cstn	n-bit constant field
dst	destination
h	MVK, MVKH/MVKLH, or MVKL instruction
N3	3-bit field
ор	opfield; field within opcode that specifies a unique instruction
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel
S	side A or B for destination; 0 = side A, 1 = side B
scstn	n-bit signed constant field
src1	source 1
src2	source 2
ucstn	n-bit unsigned constant field
ucst _n	bit n of the unsigned constant field
x	cross path for src2; 0 = do not use cross path, 1 = use cross path
Z	test for equality with zero or nonzero

F.3 32-Bit Opcode Maps

The CPU 32-bit opcodes used in the .S unit are mapped in the following figures.

Figure F-1. 1 or 2 Sources Instruction Format

3	1 29	28	27	23	22 18	17	13	12	11	6	5	4	3	2	1	0
	creg	Z	dst	!	src2	src1		Х	ор		1	0	0	0	s	p
	3	1	5		5	5		1	6						1	1

Figure F-2. ADDDP/ADDSP and SUBDP/SUBSP Instruction Format

31 29	28	27 23	22 18	17 13	12	11	5	4	3	2	1	0
creg	Z	dst	src2	src1	Х	ор		1	1	0	s	p
3	1	5	5	5	1	7					1	1

Figure F-3. ADDK Instruction Format





Figure F-4. ADDKPC Instruction Format

31	29	28	27	23	22 16	3 1	15	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z		dst	src1		src2		0	0	0	0	1	0	1	1	0	0	0	s	р
3		1		5	7		3													1	1

Figure F-5. Extended .S Unit 1 or 2 Sources Instruction Format

31	29	28	27	23	22 18	17	13	12	11	10	9	6	5	4	3	2	1	0
cre	g	Z		dst	src2	src1		Х	1	1	ор		1	1	0	0	s	р
3		1		5	5	5		1			4						1	1

Figure F-6. Branch Using a Displacement Instruction Format

3	1 29	28	27	7	6	5	4	3	2	1	0
	creg	Z	cst21		0	0	1	0	0	s	p
	3	1	21							1	1

Figure F-7. Branch Using a Register Instruction Format

3	31	29	28	27	26	25	24	23	22	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg		Z	0	0	0	0	0	src2		0	0	0	0	0	Х	0	0	1	1	0	1	1	0	0	0	s	р
	3		1						5							1											1	1

Figure F-8. Branch Using a Pointer Instruction Format

31	29	28	27	26	25	24	23	22	21	20	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
cr	eg	Z	0	0	0	0	0	0	0	op)	0	0	0	0	0	0	0	0	0	0	1	1	1	0	0	0	1	р
3	3	1								3																			1

Figure F-9. BDEC/BPOS Instruction Format

3	1 29	28	27 23	22 13	3 1	2 1	1 10	9	8	7	6	5	4	3	2	1	0
	creg	Z	dst	src		n (0	0	0	0	0	1	0	0	0	S	р
	3	1	5	10		1										1	1

Figure F-10. Branch Using a Displacement with NOP Instruction Format

31 2	29	28	27	16	15	•	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		Z	src2			src1		0	0	0	0	1	0	0	1	0	0	0	s	p
3		1	12			3													1	1

Figure F-11. Branch Using a Register with NOP Instruction Format

							_				_		_														
31	2	9	28	27	26	25	24	23	22	18	17	16	15	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	creg		z	0	0	0	0	1	src2		0	0	src	1	Х	0	0	1	1	0	1	1	0	0	0	1	p
	3		1						5				3		1												1



Figure F-12. Call Nonconditional, Immediate with Implied NOP 5 Instruction Format

3	1	30	29	28	27 7	6)	5	4	3	2	1	0
(0	0	1	cst21	C)	0	1	0	0	S	р
					21							1	1

Figure F-13. Move Constant Instruction Format

31	29	28	27 2	22	7	6	5	4	3	2	1	0
	creg	Z	dst	cst16		h	1	0	1	0	s	p
	3	1	5	16		1					1	1

Figure F-14. Extended .S Unit 1 or 2 Sources, Nonconditional Instruction Format

31	30	29	28	27 23	. 22 10	17 13	3 12	11	10	9	6	5 4	3	2	1	0
0	0	0	1	dst	src2	src1	х	1	1	ор		1 1	0	0	S	р
				5	5	5	1			4					1	1

Figure F-15. Unary Instruction Format

31	29	28	27	2	3 22	18	17	1	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg	9	Z		dst		src2		ор		Х	1	1	1	1	0	0	1	0	0	0	s	р
3		1		5		5		5		1											1	1

Figure F-16. Field Operations

31	29	28	27	23	22	18	17	1,	3	12	8	7	6	5	4	3	2	1	0
creg	1	Z		dst	src2			csta		cstb		C	p	0	0	1	0	s	р
3		1		5	5			5		5		•	2					1	1



F.4 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the .S unit for compact instructions are mapped in the following figures. See Section 3.10 for more information about compact instructions.


Figure F-17. Sbs7 Instruction Format

15	13	12		6	5	4	3	2	1	0
1	V 3		scst7		0	0	1	0	1	S
	3		7							1

NOTE: N3 = 0, 1, 2, 3, 4, or 5

BR	Mnemonic
1	BNOP (.unit) scst7, N3

Figure F-18. Sbu8 Instruction Format



BR	Mnemonic
1	BNOP (.unit) ucst8, 5

Figure F-19. Scs10 Instruction Format



NOTE: NextPC > B3, A3

BR	Mnemonic
1	CALLP (.unit) scst10, 5



Figure F-20. Sbs7c Instruction Format 15 13 12 6 5 4 3 2 1 0 N3 scst7 1 z 1 0 1 s 3 7 1 1 1 1

NOTE: N3 = 0, 1, 2, 3, 4, or 5

BR	s	Z	Mnemonic
1	0	0	[A0] BNOP .S1 scst7, N3
1	0	1	[!A0] BNOP .S1 scst7, N3
1	1	0	[B0] BNOP .S2 scst7, N3
1	1	1	[!B0] BNOP .S2 scst7, N3

Figure F-21. Sbu8c Instruction Format

15	14	13		6	5	4	3	2	1	0	
1	1		ucst8		1	z	1	0	1	S	
			8			1				1	

BR	s	Z	Mnemonic
1	0	0	[A0] BNOP .S1 ucst8, 5
1	0	1	[!A0] BNOP .S1 ucst8, 5
1	1	0	[B0] BNOP .S2 ucst8, 5
1	1	1	[!B0] BNOP .S2 ucst8, 5

Figure F-22. S3 Instruction Format

15	13	12	11	10	9	7	6	4	3	2	1	0
src	1	х	ор	0	src2		dst		1	0	1	s
3		1	1		3		3					1

Opcode map field used	For operand type
src1	sint
src2	xsint
dst	sint

BR	SAT	ор	Mnemonic
0	0	0	ADD (.unit) src1, src2, dst
0	1	0	SADD (.unit) src1, src2, dst
0	х	1	SUB (.unit) <i>src1</i> , <i>src2</i> , <i>dst</i> (dst = src1 - src2)



1

16-Bit Opcode Maps www.ti.com

				F	igure F-23	. S3i Instr	uction F	ormat				
15	13	12	11	10	9	7	6	4	3	2	1	0
	cst3	х	ор	1	sro	:2		dst	1	0	1	s

3

3

Opcode map field used	For operand type
src2	xsint

	32-Bit Opcode cst Translation					
cst3	ucst5	Decimal Value				
000	10000	16				
001	00001	1				
010	00010	2				
011	00011	3				
100	00100	4				
101	00101	5				
110	00110	6				
111	01000	8				

BR	ор	Mnemonic
0	0	SHL (.unit) src2, ucst5, dst
0	1	SHR (.unit) src2, ucst5, dst

Figure F-24. Smvk8 Instruction Format

15	13	12	11	10	9		7	6	5	4	3	2	1	0	
	ucst ₂₋₀	uc	st ₄₋₃	ucst ₇		dst		ucs	t ₆₋₅	1	0	0	1	s	
	3		2	1		3		2						1	

Opcode map field used	For operand type
dst	sint

Mnemonic	
MVK (.unit) ucst8, dst	

3



Figure F-25. Ssh5 Instruction Format

15		13	12	11	10	9	7	6	5	4	3	2	1	0
	ucst ₂₋₀		ucs		1		src2/dst	op)	0	0	0	1	S
	2		,)			2	2						1

NOTE: x = 0, src and dst on the same side.

Opcode map field used	For operand type
src2/dst	sint

SAT	C	р	Mnemonic
Х	0	0	SHL (.unit) src2, ucst5, dst (src2 = dst)
Х	0	1	SHR (.unit) src2, ucst5, dst (src2 = dst)
0	1	0	SHRU (.unit) src2, ucst5, dst (src2 = dst)
1	1	0	SSHL (.unit) <i>src2</i> , <i>ucst5</i> , <i>dst</i> (src2 = dst)
х	1	1	see S2sh, Figure F-26

Figure F-26. S2sh Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0
src1	1	C	р	1	src	2/dst	1	1	0	0	0	1	s
3			2			3							1

NOTE: x = 0, src and dst on the same side.

Opcode map field used	For operand type						
src2/dst	sint						

	ор	Mnemonic
0	0	SHL (.unit) src2, src1, dst (src2 = dst, dst = src2 << src1)
0	1	SHR (.unit) src2, src1, dst (src2 = dst, dst = src2 >> src1)
1	0	SHRU (.unit) src2, src1, dst (src2 = dst, dst = src2 << src1)
1	1	SSHL (.unit) src2, src1, dst (src2 = dst, dst = src2 sshl src1)



Figure F-27. Sc5 Instruction Format

						G									
	15	13	12	11	10	9	7		6	5	4	3	2	1	0
ucst ₂₋₀		ucs	st ₄₋₃	0		src2/dst		ор)	0	0	0	1	s	
3		2)			3		2						1	

NOTES:

- 1. x = 0, src and dst on the same side
- 2. s = 0, dst = A0; s = 1, dst = B0

Opcode map field used	For operand type
src2/dst	sint

ор		Mnemonic
0	0	EXTU (.unit) <i>src2</i> , <i>ucst5</i> ,31, A0/B0
0	1	SET (.unit) <i>src2</i> , <i>ucst5</i> , <i>ucst5</i> , <i>dst</i> (src = dst, ucst5 = ucst5)
1	0	CLR (.unit) src2, ucst5, ucst5, dst (src = dst, ucst5 = ucst5)
1	1	see S2ext, Figure F-28

Figure F-28. S2ext Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0	
dst		0	p	0	src	2	1	1	0	0	0	1	s	
3)		3								1	

NOTE: x = 0, src and dst on the same side.

Opcode map field used	For operand type
dst	sint
src2	sint

(ор	Mnemonic
0	0	EXT (.unit) <i>src</i> ,16, 16, <i>dst</i>
0	1	EXT (.unit) <i>src</i> ,24, 24, <i>dst</i>
1	0	EXTU (.unit) <i>src</i> ,16, 16, <i>dst</i>
1	1	EXTU (.unit) <i>src</i> ,24, 24, <i>dst</i>



15	13	12	11	10	9	7	6	5	4	3	2	1	0
src1/ds	st	х	ор	0	,	src2	0	1	0	1	1	1	S
3		1	1			3							1

Opcode map field used	For operand type
src1/dst	sint
src2	xsint

ор	Mnemonic
0	ADD (.unit) src1, src2, dst (src1 = dst)
1	SUB (.unit) src1, src2, dst (src1 = dst, dst = src1 - src2)

Figure F-30. Sx5 Instruction Format

15	13	12	11	10	9	7	6	5	4	3	2	1	0
ис	st ₂₋₀	uc	st ₄₋₃	1		src2/dst	0	1	0	1	1	1	S
	3		2			3							1

Opcode map field used	For operand type
src2/dst	sint

Mnemonic		
ADDK (.unit) ucst5, dst		



Figure F-31. Sx1 Instruction Format														
15		13	12	11	10	9	7	6	5	4	3	2	1	0
	ор		1	1	0		src2/dst	1	1	0	1	1	1	S
	3						3							1

Opcode map field used	For operand type
src2/dst	sint

	ор		Mnemonic
0	0	0	see LSDx1, Figure G-4
0	0	1	see LSDx1, Figure G-4
0	1	0	SUB (.unit)0, <i>src2</i> , <i>dst</i> (src2 = dst, dst = 0 - src2)
0	1	1	ADD (.unit)-1, <i>src2</i> , <i>dst</i> (src2 = dst)
1	0	0	Reserved
1	0	1	see LSDx1, Figure G-4
1	1	0	MVC (.unit) <i>src</i> , ILC (s = 1)
1	1	1	see LSDx1, Figure G-4

Figure F-32. Sx1b Instruction Format

15	13	12	11	10	7	6	5	4	3	2	1	0
N3		0	0	src2		1	1	0	1	1	1	S
3				1								1

NOTE: src2 from B0-B15

Opcode map field used	For operand type
src2	uint

Mnemonic	
BNOP (.unit) src2, N3	



.D, .L, or .S Unit Opcode Maps

This appendix illustrates the opcode maps that execute in the .D, .L, or .S functional units.

For a list of the instructions that execute in the .D functional unit, see Appendix C. For a list of the instructions that execute in the .L functional unit, see Appendix D. For a list of the instructions that execute in the .S functional unit, see Appendix F.

Topic Page

G.1	Opcode Map Symbols and Meanings	758
G.2	32-Bit Opcode Maps	758
G.3	16-Bit Opcode Maps	759



G.1 Opcode Map Symbols and Meanings

Table G-1 lists the symbols and meanings used in the opcode maps.

Table G-1. .D, .L, and .S Units Opcode Map Symbol Definitions

Symbol	Meaning
CC	
dst	destination
dstms	
ор	opfield; field within opcode that specifies a unique instruction
s	side A or B for destination; 0 = side A, 1 = side B
src	source
src2	source 2
srcms	
ucstn	n-bit unsigned constant field
unit	unit decode
x	cross path for src2; 0 = do not use cross path, 1 = use cross path

G.2 32-Bit Opcode Maps

For the CPU 32-bit opcodes used in the .D functional unit, see Appendix C. For the CPU 32-bit opcodes used in the .L functional unit, see Appendix D. For the CPU 32-bit opcodes used in the .S functional unit, see Appendix F.




www.ti.com 16-Bit Opcode Maps

G.3 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the .D, .L, or .S units for compact instructions are mapped in Figure G-1 through Figure G-4. See Section 3.10 for more information about compact instructions.

Figure G-1. LSDmvto Instruction Format



Opcode map field used	For operand type
dst	sint
src2	xsint

	unit	Mnemonic
0	0	MV (.Ln) src, dst
0	1	MV (.Sn) src, dst
1	0	MV (.Dn) src, dst

Figure G-2. LSDmvfr Instruction Format



Opcode map field used	For operand type
dst	sint
src2	xsint

unit		Mnemonic
0	0	MV (.Ln) src, dst
0	1	MV (.Sn) src, dst
1	0	MV (.Dn) src, dst



16-Bit Opcode Maps www.ti.com

	Figure G-3. LSDx1c Instruction Format										
11	10	9		7	6	5	4	3	2	1	0
1	0		dst		1	1	u	nit	1	1	s

Opcode map field used	For operand type
dst	sint

	CC	Mnemonic			
0	0	A0] MVK (.unit) ucst1, dst			
0	1	[!A0] MVK (.unit) ucst1, dst			
1	0	[B0] MVK (.unit) ucst1, dst			
1	1	[!B0] MVK (.unit) ucst1, dst			

(CC		nit	Mnemonic
0	0	0	0	[A0] MVK (.Ln) ucst1, dst
		0	1	[A0] MVK (.Sn) ucst1, dst
		1	0	[A0] MVK (.Dn) ucst1, dst

	CC		nit	Mnemonic
0	1	0 0		[!A0] MVK (.Ln) ucst1, dst
		0	1	[!A0] MVK (.Sn) ucst1, dst
		1	0	[!A0] MVK (.Dn) ucst1, dst

	CC		C unit		Mnemonic
1		0	0 0		[B0] MVK (.Ln) ucst1, dst
			0	1	[B0] MVK (.Sn) ucst1, dst
			1	0	[B0] MVK (.Dn) ucst1, dst

	CC	ur	nit	Mnemonic
1	1	0	0	[!B0] MVK (.Ln) ucst1, dst
		0	1	[!B0] MVK (.Sn) ucst1, dst
		1	0	[!B0] MVK (.Dn) ucst1, dst

CC

ucst1



www.ti.com 16-Bit Opcode Maps

Figure G-4. LSDx1 Instruction Format														
15		13	12	11	10	9	7	6	5	4	3	2	1	0
	ор		1	1	0		src/dst	1	1	unit		1	1	s
3							3				2			1

Opcode map field used	For operand type
src/dst	sint

	ор		Mnemonic
0	0	0	MVK (.unit)0, dst
0	0	1	MVK (.unit)1, dst
0	1	0	See Dx1, Figure C-20; Lx1, Figure D-11; and Sx1, Figure F-31
0	1	1	See Dx1, Figure C-20; Lx1, Figure D-11; and Sx1, Figure F-31
1	0	0	See Dx1, Figure C-20; Lx1, Figure D-11; and Sx1, Figure F-31
1	0	1	ADD (.unit) <i>src</i> , 1, <i>dst</i> (<i>src</i> = <i>dst</i>)
1	1	0	See Dx1, Figure C-20; Lx1, Figure D-11; and Sx1, Figure F-31
1	1	1	XOR (.unit) src, 1, dst (src = dst)

ор			ur	nit	Mnemonic
0	0	0	0 0		MVK (.L <i>n</i>)0, <i>dst</i>
			0	1	MVK (.S <i>n</i>)0, <i>dst</i>
			1	0	MVK (.D <i>n</i>)0, <i>dst</i>

ор		ш	nit	Mnemonic	
0	0	1	0 0		MVK (.L <i>n</i>)1, <i>dst</i>
			0	1	MVK (.S <i>n</i>)1, <i>dst</i>
			1	0	MVK (.D <i>n</i>)1, <i>dst</i>

ор		uı	nit	Mnemonic	
1	0	1	0 0		ADD (.Ln) src, 1, dst
			0	1	ADD (.Sn) src, 1, dst
			1	0	ADD (.Dn) src, 1, dst

-	ор		ш	nit	Mnemonic								
1	1	1	0	0	XOR (.Ln) src, 1, dst								
			0	1	XOR (.Sn) src, 1, dst								
			1	0	XOR (.Dn) src, 1, dst								

762 .D, .L, or .S Unit Opcode Maps SPRUFE8B-July 2010



No Unit Specified Instructions and Opcode Maps

This appendix lists the instructions that execute with no unit specified and illustrates the opcode maps for these instructions.

For a list of the instructions that execute in the .D functional unit, see Appendix C. For a list of the instructions that execute in the .L functional unit, see Appendix D. For a list of the instructions that execute in the .M functional unit, see Appendix E. For a list of the instructions that execute in the .S functional unit, see Appendix F.

Topic Page

H.1	Instructions Executing With No Unit Specified	764
H.2	Opcode Map Symbols and Meanings	764
H.3	32-Bit Opcode Maps	765
H.4	16-Bit Opcode Maps	765
	•	



H.1 Instructions Executing With No Unit Specified

Table H-1 lists the instructions that execute with no unit specified.

Table H-1. Instructions Executing With No Unit Specified

Instruction	Format
DINT	Figure H-1
IDLE	Figure H-2
NOP	Figure H-2
RINT	Figure H-1
SPKERNEL	Figure H-3
SPKERNELR	Figure H-3
SPLOOP	Figure H-4
SPLOOPD	Figure H-4
SPLOOPW	Figure H-4
SPMASK	Figure H-3
SPMASKR	Figure H-3
SWE	Figure H-1
SWENR	Figure H-1

H.2 Opcode Map Symbols and Meanings

Table H-2 lists the symbols and meanings used in the opcode maps.

Table H-2. No Unit Specified Instructions Opcode Map Symbol Definitions

Symbol	Meaning
creg	3-bit field specifying a conditional register
csta	constant a
cstb	constant b
cstn	n-bit constant field
ii _n	bit n of the constant ii
N3	3-bit field
ор	opfield; field within opcode that specifies a unique instruction
p	parallel execution; 0 = next instruction is not executed in parallel, 1 = next instruction is executed in parallel
s	side A or B for destination; 0 = side A, 1 = side B.
stg _n	bit n of the constant stg
z	test for equality with zero or nonzero



www.ti.com 32-Bit Opcode Maps

H.3 32-Bit Opcode Maps

The CPU 32-bit opcodes used in the no unit instructions are mapped in the following figures.

Figure H-1. DINT and RINT, SWE and SWENR Instruction Format

31	30	29	28	27 24	23	22	21	20	19	18	17	16		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	1	Reserved (0)	0	0	0	0	0	0	0		ор		0	0	0	0	0	0	0	0	0	0	0	0	p
				4									4														1

Figure H-2. IDLE and NOP Instruction Format

31	30	29	28	27	18	17	16		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	0	Reserved (0)		0		ор		0	0	0	0	0	0	0	0	0	0	0	0	р
				10				4														1

Figure H-3. Loop Buffer, Nonconditional Instruction Format

31	30	29	28	27	23	22	18	17	16		13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	0	0	0	cstb		csta		1		ор		0	0	0	0	0	0	0	0	0	0	0	S	р
				5		5				4													1	1

Figure H-4. Loop Buffer Instruction Format

31 2	9 2	28	27 23		18	17	16	13	12	11	10	9	8	7	6	5	4	3	2	1	0
creg		z	cstb	csta		1	ор		0	0	0	0	0	0	0	0	0	0	0	s	р
3		1	5	5			4													1	1

H.4 16-Bit Opcode Maps

The CPU 16-bit opcodes used in the no unit instructions for compact instructions are mapped in the following figures. See Section 3.10 for more information about compact instructions.

Figure H-5. Uspl Instruction Format

15	14	13	12	11	10	9	7	6	5	4	3	2	1	0
0	ii ₃	0	0	1	1	ii ₂₋₀		1	1	0	0	1	1	ор
	1					3								1

NOTE: Supports ii of 1-16

ор	Mnemonic
0	SPLOOP ii (ii = real ii - 1)
1	SPLOOPD ii



16-Bit Opcode Maps www.ti.com

					Fig	gure H	-6. Uspl	dr Ins	tructio	n Form	at				
15	14	13	12	11	10	9		7	6	5	4	3	2	1	0
1	ii ₃	0	0	1	1		ii ₂₋₀		1	1	0	0	1	1	ор
	1						3								1

NOTE: Supports ii of 1-16

ор	Mnemonic
0	[A0] SPLOOPD ii (ii = real ii - 1)
1	[B0] SPLOOPD ii

Figure H-7. Uspk Instruction Format

15	14	13	12	11	10	9	7	6	5	4	3	2	1	0
ii/st	g ₄₋₃	0	1	1	1	ii/stg ₂₋₀		1	1	0	0	1	1	ii/stg ₅
2)					3								1

Mnemonic

SPKERNEL ii/stage

Figure H-8. Uspm Instruction Format

a) SPMASK Instruction

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
D2	D1	1	0	1	1	S2	S1	L2	1	1	0	0	1	1	L1
1	1					1	1	1							1

NOTE: Supports masking of D1, D2, L1, L2, S1, and S2 instructions (not M1 or M2)

Mnemonic

SPMASK unitmask

b) SPMASKR Instruction

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
D2	D1	1	1	1	1	S2	S1	L2	1	1	0	0	1	1	L1
1	1					1	1	1							1

NOTE: Supports masking of D1, D2, L1, L2, S1, and S2 instructions (not M1 or M2)

Mnemonic

SPMASKR unitmask



www.ti.com 16-Bit Opcode Maps

					Fi	gure F	I-9. Und	op Inst	ruction	Form	at				
15		13	12	11	10	9	8	7	6	5	4	3	2	1	0
	N3		0	1	1	0	0	0	1	1	0	1	1	1	0
	3							•	•						

Mnemonic	 		
Minemonic			
NOB V/3			



Revision History

Table I-1 lists the changes made since the previous version of this document.

Table I-1. Document Revision History

Reference	Additions/Modifications/Deletions
Section 2.9.14.4	Added Caution.
SPACKU4	Changed figure.

SPRUFE8B-July 2010 Revision History 769

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications		
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio	
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive	
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications	
DSP	<u>dsp.ti.com</u>	Computers and Peripherals	www.ti.com/computers	
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps	
Interface	interface.ti.com	Energy	www.ti.com/energy	
Logic	logic.ti.com	Industrial	www.ti.com/industrial	
Power Mgmt	power.ti.com	Medical	www.ti.com/medical	
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security	
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense	
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video	
		Wireless	www.ti.com/wireless-apps	